









**SF47/SF47p..**

**SAF47/SAF47p..**

## SHF47/SHF47p..



| (→ 📖 4.1) | DRN  |     |      |     |      |      |     |     |     |       |         |
|-----------|------|-----|------|-----|------|------|-----|-----|-----|-------|---------|
|           | 63MS | 63M | 71MS | 71M | 80MK | 80MS | 80M | 90S | 90L | 100LS | 100L/LM |
| AC        | 115  | 115 | 139  | 139 | 156  | 156  | 156 | 179 | 179 | 197   | 197     |
| AD        | 98   | 98  | 118  | 118 | 128  | 128  | 128 | 140 | 140 | 157   | 157     |
| ADS       | 98   | 98  | 129  | 129 | 139  | 139  | 139 | 150 | 150 | 158   | 158     |
| L         | 361  | 375 | 377  | 397 | 408  | 425  | 454 | 455 | 487 | 485   | 535     |
| LS        | 417  | 431 | 444  | 464 | 489  | 506  | 535 | 549 | 581 | 579   | 629     |
| LB        | 190  | 204 | 206  | 226 | 237  | 254  | 283 | 284 | 316 | 314   | 364     |
| LBS       | 246  | 260 | 273  | 293 | 318  | 335  | 364 | 378 | 410 | 408   | 458     |