





KA19..**KA19..****KH19..**

(→ 4.1)	DRN							
	63MS	63M	71MS	71M	80MK	80MS	80M	90S
AC	115	115	139	139	156	156	156	179
AD	98	98	118	118	128	128	128	140
ADS	98	98	129	129	139	139	139	150
L	356	370	372	392	403	420	449	450
LS	412	426	439	459	484	501	530	544
LB	190	204	206	226	237	254	283	284
LBS	246	260	273	293	318	335	364	378