





KA39..



KA39..



KH39..



(→ 📖 4.1)	DRN										
	63M	71MS	71M	80MK	80MS	80M	90S	90L	100LS	100L/LM	112M
AC	115	139	139	156	156	156	179	179	197	197	221
AD	98	118	118	128	128	128	140	140	157	157	170
ADS	98	129	129	139	139	139	150	150	158	158	172
L	449	450	470	481	498	527	529	561	556	606	637
LS	505	518	538	562	579	608	622	654	650	700	749
LB	198	199	219	230	247	276	278	310	305	355	386
LBS	254	267	287	311	328	357	371	403	399	449	498