








K49..**KA49B..****ø 40 H7****ø 35 H7****KH49B..**

(→ 4.1)	DRN											
	71MS	71M	80MK	80MS	80M	90S	90L	100LS	100L/LM	112M	132S	132M
AC	139	139	156	156	156	179	179	197	197	221	221	261
AD	118	118	128	128	128	140	140	157	157	170	170	228
ADS	129	129	139	139	139	150	150	158	158	172	172	228
L	499	519	530	547	576	578	610	605	655	686	736	754
LS	567	587	611	628	657	671	703	699	749	798	848	892
LB	192	212	223	240	269	271	303	298	348	379	429	447
LBS	260	280	304	321	350	364	396	392	442	491	541	585