



K107..



KA107B..



(→ 📖 4.1)	DRN										
	100LS	100L/LM	112M	132S	132M	132L	160..	180..	200L	225..	250M
AC	197	197	221	221	261	261	314	357	394	434	495
AD	157	157	170	170	228	228	253	268	283	305	394
ADS	158	158	172	172	228	228	253	268	283	305	394
L	823	873	904	954	972	998	1064	1087	1197	1171	1308
LS	917	967	1016	1066	1110	1135	1253	1276	1402	1376	1548
LB	282	332	363	413	431	457	523	546	656	630	767
LBS	376	426	475	525	569	594	712	735	861	835	1007