





WA29HG..




W.. /T




WA29HG..





WH29HG..



ø 25 H7



ø 20 H7



(→ 4.1)	DRN							
	63MS	63M						
AC	115	115						
AD	98	98						
ADS	98	98						
L	361	375						
LS	417	431						
LB	188	202						
LBS	244	258						