










WF39HG..**ø 160****ø 200****WAF39HG..****ø 160****ø 200****ø 30^{H7}**
DIN 6885-3**ø 25^{H7}**

(→ 4.1)	DRN							
	63MS	63M	71MS					
AC	115	115	139					
AD	98	98	118					
ADS	98	98	129					
L	380	394	395					
LS	436	450	463					
LB	188	202	203					
LBS	244	258	271					