









WA49HG..**W.. /T****WA49HG..****WH49HG..** **$\varnothing 35^{H7}$** **$\varnothing 30^{H7}$** 

(→ 4.1)	DRN							
	63MS	63M	71MS	71M				
AC	115	115	139	139				
AD	98	98	118	118				
ADS	98	98	129	129				
L	402	416	417	437				
LS	458	472	485	505				
LB	182	196	197	217				
LBS	238	252	265	285				