





DRN80..




ø 18 H7




ø 20 H7



ø 110



ø 120



 4.1	DRN							
	63MS	63M	71MS	71M	80MK	80MS		
AC	115	115	139	139	156	156		
AD	98	98	118	118	128	128		
ADS	98	98	129	129	139	139		
L	299	313	315	335	350	368		
LS	355	369	382	402	431	449		
LB	148	162	164	184	189	207		
LBS	204	218	231	251	270	288		