



W30..**DRN80..**

(→  4.1)	DRN							
	63MS	63M	71MS	71M	80MK	80M		
AC	115	115	139	139	156	156		
AD	98	98	118	118	128	128		
ADS	98	98	129	129	139	139		
L	323	337	339	359	367	413		
LS	379	393	406	426	448	494		
LB	148	162	164	184	189	235		
LBS	204	218	231	251	270	316		