






WF19..



ø 110




ø 120




WAF19..


ø 110




ø 120



ø 20 H7



ø 18 H7



(→ 4.1)	DR2S	DRN						
	56..	63MS	63M	71MS	71M	80MK	80MS	80M
AC	109	115	115	139	139	156	156	156
AD	87	98	98	118	118	128	128	128
ADS	87	98	98	129	129	139	139	139
L	303	333	347	349	369	380	392	426
LS	339	389	403	416	436	461	473	507
LB	160	190	204	206	226	237	249	283
LBS	196	246	260	273	293	318	330	364