









WA49..**W.. /T****WA49..****WH49..****ø 35 H7****ø 30 H7**

(→ 📖 4.1)	DRN										
	63MS	63M	71MS	71M	80MK	80MS	80M	90S	90L	100LS	100L/LM
AC	115	115	139	139	156	156	156	179	179	197	197
AD	98	98	118	118	128	128	128	140	140	157	157
ADS	98	98	129	129	139	139	139	150	150	158	158
L	404	418	419	439	450	467	496	498	530	525	575
LS	460	474	487	507	531	548	577	591	623	619	669
LB	184	198	199	219	230	247	276	278	310	305	355
LBS	240	254	267	287	311	328	357	371	403	399	449