






# RXF107..



## ø 350



## ø 450



| <div> <div></div> <div>(→ 4.1)</div> </div> | DRN     |      |      |      |      |       |       |      |       |      |
|---------------------------------------------|---------|------|------|------|------|-------|-------|------|-------|------|
|                                             | 100L/LM | 112M | 132S | 132M | 132L | 160.. | 180.. | 200L | 225.. | 250M |
| AC                                          | 197     | 221  | 221  | 261  | 261  | 314   | 357   | 394  | 434   | 495  |
| AD                                          | 157     | 170  | 170  | 228  | 228  | 253   | 268   | 283  | 305   | 394  |
| ADS                                         | 158     | 172  | 172  | 228  | 228  | 253   | 268   | 283  | 305   | 394  |
| L                                           | 696     | 727  | 777  | 795  | 821  | 887   | 910   | 1020 | 994   | 1131 |
| LS                                          | 790     | 839  | 889  | 933  | 958  | 1076  | 1099  | 1225 | 1199  | 1371 |
| LB                                          | 332     | 363  | 413  | 431  | 457  | 523   | 546   | 656  | 630   | 767  |
| LBS                                         | 426     | 475  | 525  | 569  | 594  | 712   | 735   | 861  | 835   | 1007 |