






R77..



R77F..



(→ 📖 4.1)	DRN														
	63M	71MS	71M	80MK	80MS	80M	90S	90L	100LS	100L/LM	112M	132S	132M	132L	160..
AC	115	139	139	156	156	156	179	179	197	197	221	221	261	261	314
AD	98	118	118	128	128	128	140	140	157	157	170	170	228	228	253
ADS	98	129	129	139	139	139	150	150	158	158	172	172	228	228	253
L	491	492	512	523	540	569	571	603	598	648	679	729	747	773	839
LS	547	560	580	604	621	650	664	696	692	742	791	841	885	910	1028
LB	191	192	212	223	240	269	271	303	298	348	379	429	447	473	539
LBS	247	260	280	304	321	350	364	396	392	442	491	541	585	610	728