




RF167..




ø 550



ø 660



RM167..



(→ 4.1)	DRN									
	132L	160..	180..	200L	225..	250M	280S	280M	315S-M	315ME-H
AC	261	314	357	394	434	495	495	495	624	624
AD	228	253	268	283	305	394	394	394	506	506
ADS	228	253	268	283	305	394	394	394	506	506
L	1224	1290	1313	1423	1397	1534	1534	1629	1731	1861
LS	1361	1479	1502	1628	1602	1774	1774	1869	1982	2112
LB	434	500	523	633	607	744	744	839	941	1071
LBS	571	689	712	838	812	984	984	1079	1192	1322