





DR2S56..




ø 16 H7



ø 80



ø 120



(→ 4.1)	DR2S	DRN						
	56..	63MS	63M	71MS	71M			
AC	109	115	115	139	139			
AD	87	98	98	118	118			
ADS	87	98	98	129	129			
L	255	285	299	301	321			
LS	291	341	355	368	388			
LB	136	148	162	164	184			
LBS	172	204	218	231	251			