





**F27..****FA27B..****FH27B..**  
max. DR71..**FV27B..**

| (→ 📖 4.1) | DRN  |     |      |     |      |      |     |     |     |       |         |
|-----------|------|-----|------|-----|------|------|-----|-----|-----|-------|---------|
|           | 63MS | 63M | 71MS | 71M | 80MK | 80MS | 80M | 90S | 90L | 100LS | 100L/LM |
| AC        | 115  | 115 | 139  | 139 | 156  | 156  | 156 | 179 | 179 | 197   | 197     |
| AD        | 98   | 98  | 118  | 118 | 128  | 128  | 128 | 140 | 140 | 157   | 157     |
| ADS       | 98   | 98  | 129  | 129 | 139  | 139  | 139 | 150 | 150 | 158   | 158     |
| L         | 336  | 350 | 352  | 372 | 383  | 400  | 429 | 430 | 462 | 460   | 510     |
| LS        | 392  | 406 | 419  | 439 | 464  | 481  | 510 | 524 | 556 | 554   | 604     |
| LB        | 190  | 204 | 206  | 226 | 237  | 254  | 283 | 284 | 316 | 314   | 364     |
| LBS       | 246  | 260 | 273  | 293 | 318  | 335  | 364 | 378 | 410 | 408   | 458     |