








(→ 📖 4.1)	DRN							
	63MS	63M	71MS	71M	80MS			
AC	115	115	139	139	156			
AD	98	98	118	118	128			
ADS	98	98	129	129	139			
L	342	356	358	378	406			
LS	398	412	425	445	487			
LB	190	204	206	226	254			
LBS	246	260	273	293	335			