




FF57..




42 035 00 14



FAF57..

FHF57..
max. DRN100L

FVF57..



(→ 📁 4.1)	DRN														
	63MS	63M	71MS	71M	80MK	80MS	80M	90S	90L	100LS	100L/LM	112M	132S	132M	
AC	115	115	139	139	156	156	156	179	179	197	197	221	221	261	
AD	98	98	118	118	128	128	128	140	140	157	157	170	170	228	
ADS	98	98	129	129	139	139	139	150	150	158	158	172	172	228	
L	427	441	442	462	473	490	519	521	553	548	598	629	683	701	
LS	483	497	510	530	554	571	600	614	646	642	692	741	795	839	
LB	184	198	199	219	230	247	276	278	310	305	355	386	440	458	
LBS	240	254	267	287	311	328	357	371	403	399	449	498	552	596	