




FF67..




42 040 00 14



FAF67..

FHF67..
max. DRN132S

FVF67..



(→ 📖 4.1)	DRN												
	63M	71MS	71M	80MK	80MS	80M	90S	90L	100LS	100L/LM	112M	132S	132M
AC	115	139	139	156	156	156	179	179	197	197	221	221	261
AD	98	118	118	128	128	128	140	140	157	157	170	170	228
ADS	98	129	129	139	139	139	150	150	158	158	172	172	228
L	462	463	483	494	511	540	542	574	569	619	650	704	722
LS	518	531	551	575	592	621	635	667	663	713	762	816	860
LB	198	199	219	230	247	276	278	310	305	355	386	440	458
LBS	254	267	287	311	328	357	371	403	399	449	498	552	596