



F77..**FA77B..****FH77B..**
max. DRN132L**FV77B..**

(→ 📖 4.1)	DRN													
	71MS	71M	80MK	80MS	80M	90S	90L	100LS	100L/LM	112M	132S	132M	132L	160..
AC	139	139	156	156	156	179	179	197	197	221	221	261	261	314
AD	118	118	128	128	128	140	140	157	157	170	170	228	228	253
ADS	129	129	139	139	139	150	150	158	158	172	172	228	228	253
L	486	506	517	534	563	565	597	592	642	673	723	741	767	833
LS	554	574	598	615	644	658	690	686	736	785	835	879	904	1022
LB	192	212	223	240	269	271	303	298	348	379	429	447	473	539
LBS	260	280	304	321	350	364	396	392	442	491	541	585	610	728