



42 045 00 14



FVF77..



(→ 🏠 4.1)	DRN													
	71MS	71M	80MK	80MS	80M	90S	90L	100LS	100L/LM	112M	132S	132M	132L	160..
AC	139	139	156	156	156	179	179	197	197	221	221	261	261	314
AD	118	118	128	128	128	140	140	157	157	170	170	228	228	253
ADS	129	129	139	139	139	150	150	158	158	172	172	228	228	253
L	522	542	553	570	599	601	633	628	678	709	759	777	803	869
LS	590	610	634	651	680	694	726	722	772	821	871	915	940	1058
LB	192	212	223	240	269	271	303	298	348	379	429	447	473	539
LBS	260	280	304	321	350	364	396	392	442	491	541	585	610	728