





FAZ77..




FAZ77..



FHZ77..
max. DRN132L



FVZ77..



(→ 4.1)	DRN											132L	160..
	71MS	71M	80MK	80MS	80M	90S	90L	100LS	100L/LM	112M	132S		
AC	139	139	156	156	156	179	179	197	197	221	221	261	314
AD	118	118	128	128	128	140	140	157	157	170	170	228	253
ADS	129	129	139	139	139	150	150	158	158	172	172	228	253
L	398	418	429	446	475	477	509	504	554	585	635	679	745
LS	466	486	510	527	556	570	602	598	648	697	747	791	934
LB	192	212	223	240	269	271	303	298	348	379	429	447	539
LBS	260	280	304	321	350	364	396	392	442	491	541	585	728