









FA107..

FH107..

FV107..



(→ 4.1)	DRN										
	100LS	100L/LM	112M	132S	132M	132L	160..	180..	200L	225..	250M
AC	197	197	221	221	261	261	314	357	394	434	495
AD	157	157	170	170	228	228	253	268	283	305	394
ADS	158	158	172	172	228	228	253	268	283	305	394
L	594	644	675	725	743	769	835	858	968	942	1079
LS	688	738	787	837	881	906	1024	1047	1173	1147	1319
LB	282	332	363	413	431	457	523	546	656	630	767
LBS	376	426	475	525	569	594	712	735	861	835	1007