




F127..



FA127B..



FH127B..



($\rightarrow$ 4.1)	DRN									
	132S	132M	132L	160..	180..	200L	225..	250M	280S	280M
AC	221	261	261	314	357	394	434	495	495	495
AD	170	228	228	253	268	283	305	394	394	394
ADS	172	228	228	253	268	283	305	394	394	394
L	983	1001	1027	1093	1116	1226	1200	1337	1337	1432
LS	1095	1139	1164	1282	1305	1431	1405	1577	1577	1672
LB	398	416	442	508	531	641	615	752	752	847
LBS	510	554	579	697	720	846	820	992	992	1087