






## FA157..



**FH157..**



| (→ 🏠 4.1) | DRN  |       |       |      |       |      |      |      |        |         |
|-----------|------|-------|-------|------|-------|------|------|------|--------|---------|
|           | 132L | 160.. | 180.. | 200L | 225.. | 250M | 280S | 280M | 315S-M | 315ME-H |
| AC        | 261  | 314   | 357   | 394  | 434   | 495  | 495  | 495  | 624    | 624     |
| AD        | 228  | 253   | 268   | 283  | 305   | 394  | 394  | 394  | 506    | 506     |
| ADS       | 228  | 253   | 268   | 283  | 305   | 394  | 394  | 394  | 506    | 506     |
| L         | 889  | 955   | 978   | 1088 | 1062  | 1199 | 1199 | 1294 | 1396   | 1526    |
| LS        | 1026 | 1144  | 1167  | 1293 | 1267  | 1439 | 1439 | 1534 | 1647   | 1777    |
| LB        | 434  | 500   | 523   | 633  | 607   | 744  | 744  | 839  | 941    | 1071    |
| LBS       | 571  | 689   | 712   | 838  | 812   | 984  | 984  | 1079 | 1192   | 1322    |