










WF29..**ø 120****ø 160****WAF29..****ø 120****ø 160****ø 25^{H7}****ø 20^{H7}**

(4.1)	DRN							
	63MS	63M	71MS	71M	80MK	80MS	80M	90S
AC	115	115	139	139	156	156	156	179
AD	98	98	118	118	128	128	128	140
ADS	98	98	129	129	139	139	139	150
L	363	377	379	399	410	427	456	457
LS	419	433	446	466	491	508	537	551
LB	190	204	206	226	237	254	283	284
LBS	246	260	273	293	318	335	364	378