








WT59..



(→ 📖 4.1)	DRN											
	63MS	63M	71MS	71M	80MK	80MS	80M	90S	90L	100LS	100L/LM	112M
AC	115	115	139	139	156	156	156	179	179	197	197	221
AD	98	98	118	118	128	128	128	140	140	157	157	170
ADS	98	98	129	129	139	139	139	150	150	158	158	172
L	426	440	441	461	472	489	518	520	552	547	597	628
LS	482	496	509	529	553	570	599	613	645	641	691	740
LB	184	198	199	219	230	247	276	278	310	305	355	386
LBS	240	254	267	287	311	328	357	371	403	399	449	498