










WF29HG..**ø 120****ø 160****WAF29HG..****ø 120****ø 160****ø 25^{H7}****ø 20^{H7}**

(→ 4.1)	DRN							
	63MS	63M						
AC	115	115						
AD	98	98						
ADS	98	98						
L	361	375						
LS	417	431						
LB	188	202						
LBS	244	258						