





F27..

**FA27B..**

FH27B..



FV27B..



(↔ 📖 -)	ADC DCA...-4LP			
	DCA63S-4LP	DCA63M-4LP	DCA63L-4LP	DCA80M-4LP
AC	75	75	75	93
AD	88	88	88	97
L	324	344	364	364
LS	344	364	384	394
LB	178	198	218	218
LBS	198	218	238	248
X	127	127	127	127
X9	12	12	12	12
Y	73	73	73	73
Y1	5.5	5.5	5.5	5.5