






FF27..



FAF27..




FHF27..




FVF27..




(→ 📖 -)	ADC DCA...4LP			
	DCA63S-4LP	DCA63M-4LP	DCA63L-4LP	DCA80M-4LP
AC	75	75	75	93
AD	88	88	88	97
L	343	363	383	383
LS	363	383	403	413
LB	178	198	218	218
LBS	198	218	238	248
X	127	127	127	127
X9	12	12	12	12
Y	73	73	73	73
Y1	5.5	5.5	5.5	5.5




FV27..



(→ 📖 -)	ADC DCA...-4LP			
	DCA63S-4LP	DCA63M-4LP	DCA63L-4LP	DCA80M-4LP
AC	75	75	75	93
AD	88	88	88	97
L	273	293	313	313
LS	293	313	333	343
LB	178	198	218	218
LBS	198	218	238	248
X	127	127	127	127
X9	12	12	12	12
Y	73	73	73	73
Y1	5.5	5.5	5.5	5.5



FZ27..



($\rightarrow$ -)	ADC DCA...4LP			
	DCA63S-4LP	DCA63M-4LP	DCA63L-4LP	DCA80M-4LP
AC	75	75	75	93
AD	88	88	88	97
L	324	344	364	364
LS	344	364	384	394
LB	178	198	218	218
LBS	198	218	238	248
X	127	127	127	127
X9	12	12	12	12
Y	73	73	73	73
Y1	5.5	5.5	5.5	5.5