


R07..



R07F..



(-) (-) (-)	ADC DCA...4LP			
	DCA63S-4LP	DCA63M-4LP	DCA63L-4LP	DCA80M-4LP
AC	75	75	75	93
AD	88	88	88	97
L	319	339	359	359
LS	339	359	379	389
LB	178	198	218	218
LBS	198	218	238	248
X	127	127	127	127
X9	12	12	12	12
Y	73	73	73	73
Y1	5.5	5.5	5.5	5.5