






KF57..







KAF57..



KHF57..



KVF57..



(→ 4.1)	DRN													
	63MS	63M	71MS	71M	80MK	80MS	80M	90S	90L	100LS	100L/LM	112M	132S	132M
AC	115	115	139	139	156	156	156	179	179	197	197	221	221	261
AD	98	98	118	118	128	128	128	140	140	157	157	170	170	228
ADS	98	98	129	129	139	139	139	150	150	158	158	172	172	228
L	453	467	468	488	499	516	545	547	579	574	624	655	709	727
LS	509	523	536	556	580	597	626	640	672	668	718	767	821	865
LB	184	198	199	219	230	247	276	278	310	305	355	386	440	458
LBS	240	254	267	287	311	328	357	371	403	399	449	498	552	596