







FT57..



(> 4.1)	DRN							
	63MS	63M	71MS	71M	80MK	80MS	80M	90S
AC	115	115	139	139	156	156	156	179
AD	98	98	118	118	128	128	128	140
ADS	98	98	129	129	139	139	139	150
L	354	368	369	389	400	417	446	448
LS	410	424	437	457	481	498	527	541
LB	184	198	199	219	230	247	276	278
LBS	240	254	267	287	311	328	357	371