


(→  4.1)	DRN									
	132L	160..	180..	200L	225..	250M	280S	280M	315S-M	315ME-H
<b>AC</b>	261	314	357	394	434	495	495	495	624	624
<b>AD</b>	228	253	268	283	305	394	394	394	506	506
<b>ADS</b>	228	253	268	283	305	394	394	394	506	506
<b>L</b>	1099	1165	1188	1298	1272	1409	1409	1504	1606	1736
<b>LS</b>	1236	1354	1377	1503	1477	1649	1649	1744	1857	1987
<b>LB</b>	434	500	523	633	607	744	744	839	941	1071
<b>LBS</b>	571	689	712	838	812	984	984	1079	1192	1322