



(→ 4.1)	AC	L	LS	LB	LBS
S..37R17 DRN63MS	115	323	379	190	246
S..37R17 DRN63M	115	337	393	204	260
S..37R17 DRN71MS	139	339	406	206	273
S..47R17 DRN63MS	115	323	379	190	246
S..47R17 DRN63M	115	337	393	204	260
S..47R17 DRN71MS	139	339	406	206	273
S..47R17 DRN71M	139	359	426	226	293
S..47R17 DRN80MK	156	370	451	237	318
S..57R17 DRN63M	115	337	393	204	260
S..57R17 DRN71MS	139	339	406	206	273
S..57R17 DRN71M	139	359	426	226	293
S..57R17 DRN80MK	156	370	451	237	318
S..57R17 DRN80M	156	416	497	283	364
S..67R37 DRN71MS	139	371	438	206	273
S..67R37 DRN71M	139	391	458	226	293
S..67R37 DRN80MK	156	402	483	237	318
S..67R37 DRN80M	156	448	529	283	364
S..67R37 DRN90S	179	449	543	284	378
S..77R37 DRN71MS	139	363	430	206	273
S..77R37 DRN80MK	156	394	475	237	318
S..77R37 DRN80M	156	440	521	283	364
S..77R37 DRN90S	179	441	535	284	378
S..77R37 DRN90L	179	473	567	316	410
S..87R57 DRN80MK	156	458	539	230	311
S..87R57 DRN80M	156	504	585	276	357
S..87R57 DRN90S	179	505	599	278	371
S..87R57 DRN90L	179	537	631	310	403
S..87R57 DRN100LS	197	533	626	305	399
S..87R57 DRN100L/LM	197	583	676	355	449
S..97R57 DRN80MK	156	453	534	230	311
S..97R57 DRN90L	179	532	626	310	403
S..97R57 DRN100LS	197	528	621	305	399
S..97R57 DRN100L/LM	197	578	671	355	449
S..97R57 DRN112M	221	609	721	386	498
S..97R57 DRN132S	221	663	775	440	552