



(→ 4.1)	AC	L	LS	LB	LBS
W..29R17 DRN63MS	115	323	379	190	246
W..29R17 DRN63M	115	337	393	204	260
W..39R17 DRN63MS	115	323	379	190	246
W..39R17 DRN63M	115	337	393	204	260
W..39R17 DRN71MS	139	339	406	206	273
W..49R17 DRN63MS	115	323	379	190	246
W..49R17 DRN63M	115	337	393	204	260
W..49R17 DRN71MS	139	339	406	206	273
W..49R17 DRN71M	139	359	426	226	293
W..49R17 DRN80MK	156	370	451	237	318
W..59R37 DRN63MS	115	355	411	190	246
W..59R37 DRN63M	115	369	425	204	260
W..59R37 DRN71MS	139	371	438	206	273
W..59R37 DRN71M	139	391	458	226	293
W..59R37 DRN80MK	156	402	483	237	318