


## R07..



## R07F..



|     | ADC DCA...4LP |            |
|-----|---------------|------------|
|     | DCA63L-4LP    | DCA80M-4LP |
| AC  | 75            | 93         |
| AD  | 88            | 97         |
| L   | 407           | 407        |
| LS  | 427           | 437        |
| LB  | 218           | 218        |
| LBS | 238           | 248        |
| X   | 127           | 127        |
| X9  | 12            | 12         |
| Y   | 73            | 73         |
| Y1  | 5.5           | 5.5        |