




WF19..



∅ 110




∅ 120




WAF19..


∅ 110




∅ 120



∅ 20 H7



∅ 18 H7



| | ADC DCA...4LP | | |
|-----|---------------|------------|------------|
| | DCA63M-4LP | DCA63L-4LP | DCA80M-4LP |
| AC | 75 | 75 | 93 |
| AD | 88 | 88 | 97 |
| L | 388 | 408 | 408 |
| LS | 408 | 428 | 438 |
| LB | 198 | 218 | 218 |
| LBS | 218 | 238 | 248 |
| X | 127 | 127 | 127 |
| X9 | 12 | 12 | 12 |
| Y | 73 | 73 | 73 |
| Y1 | 5.5 | 5.5 | 5.5 |