

Keeping it simple
MOVI4R-U® in IP54

Frequency inverters



MOVI4R-U® frequency inverters in IP54

MOVI4R-U® frequency inverters offer the ideal solution for simple applications in drive technology. Without any unnecessary additional features, the focus of SEW-EURODRIVE for MOVI4R-U® is on the essentials: the simple open-loop speed control of asynchronous motors with a new, simple, and intuitive operating concept. The high degree of protection IP54 further allows for the use of MOVI4R-U® outside the control cabinet, e.g. close to the application for controlling conveyor belts.

The advantages at a glance

- Intuitive operating concept for short startup times and simple handling
- Modular design for fast unit replacement
- Degree of protection IP54 for wall mounting outside the control cabinet
- Guaranteed integration into cycle of materials: MOVI4R-U® is based on a sustainable product concept that allows for re-integration into material and raw material cycles. More information will be available soon at www.sew-eurodrive.com.



Technical data:

Voltage supply V_{AC}: 1x 200 ... 240 \pm 10%				
MOVI4R-U® type	Power [kW]	Output current [A]	Degree of protection	Dimensions W x H x D [mm]
MUWA025-231-S00-00	0.25	1.2	IP54	70 x 191 x 176
MUWA037-231-S00-00	0.37	2.0		
MUWA055-231-S00-00/PF	0.55	2.7		
Input frequency Hz: 50 ... 60 \pm 5%				

Voltage supply V_{AC}: 3x 200 ... 240 \pm 10%				
MOVI4R-U® type	Power [kW]	Output current [A]	Degree of protection	Dimensions W x H x D [mm]
MUWA025-233-S00-00	0.25	1.2	IP54	70 x 191 x 176
MUWA037-233-S00-00	0.37	2.0		
MUWA055-233-S00-00	0.55	2.7		
Input frequency Hz: 50 ... 60 \pm 5%				

Voltage supply V_{AC}: 3x 380 ... 400 \pm 10%				
MOVI4R-U® type	Power [kW]	Output current [A]	Degree of protection	Dimensions W x H x D [mm]
MUWA075-403-S00-00	0.75	1.7	IP54	70 x 191 x 176
Input frequency Hz: 50 ... 60 \pm 5%				

Voltage supply V_{AC}: 3x 380 ... 500 \pm 10%				
MOVI4R-U® type	Power [kW]	Output current [A]	Degree of protection	Dimensions W x H x D [mm]
MUWA025-503-S00-00	0.25	0.7	IP54	70 x 191 x 176
MUWA037-503-S00-00	0.37	1.1		
MUWA055-503-S00-00	0.55	1.6		
MUWA075-503-S00-00/PF	0.75	1.7		
MUWA110-503-S00-00/PF	1.1	2.5		
Input frequency Hz: 50 ... 60 \pm 5%				

SEW-EURODRIVE is right there for you:

Argentina

Tel. +54 3327 4572-84
Fax +54 3327 4572-21
sewar@sew-eurodrive.com.ar

Australia

Tel. +61 3 9933-1000
Fax +61 3 9933-1003
enquires@sew-eurodrive.com.au

Austria

Tel. +43 1 617 55 00-0
Fax +43 1 617 55 00-30
sew@sew-eurodrive.at

Belarus

Tel. +375 17 298 47 56
Fax +375 17 298 47 54
sales@sew.by

Belgium

Tel. +32 16 386-311
Fax +32 16 386-336
info@sew-eurodrive.be

Brazil

Tel. +55 19 3835-8000
sew@sew.com.br

Canada

Tel. +1 905 791-1553
Fax +1 905 791-2999
marketing@sew-eurodrive.ca

Chile

Tel. +56 2 2757 7000
Fax +56 2 2757 7001
ventas@sew-eurodrive.cl

China

Tel. +86 22 25322612
Fax +86 22 25323273
info@sew-eurodrive.cn

Colombia

Tel. +57 1 54750-50
Fax +57 1 54750-44
sew@sew-eurodrive.com.co

Czech Republic

Tel. +420 255 709 601
Fax +420 235 350 613
sew@sew-eurodrive.cz

Denmark

Tel. +45 43 9585-00
Fax +45 43 9585-09
sew@sew-eurodrive.dk

Finland

Tel. +358 201 589-300
Fax +358 3 7806-211
sew@sew.fi

France

Tel. +33 3 88 73 67 00
Fax +33 3 88 73 66 00
sew@usocome.com

Great Britain

Tel. +44 1924 893-855
Fax +44 1924 893-702
info@sew-eurodrive.co.uk

Hungary

Tel. +36 1 437 06-58
Fax +36 1 437 06-50
office@sew-eurodrive.hu

India

Tel. +91 265 3045200
Fax +91 265 3045300
marketing@seweurodriveindia.com

Italy

Tel. +39 02 96 9801
Fax +39 02 96 980 999
sewit@sew-eurodrive.it

Ivory Coast

Tel. +225 21 21 81 05
Fax +225 21 25 30 47
info@sew-eurodrive.ci

Japan

Tel. +81 538 373811
Fax +81 538 373814
sewjapan@sew-eurodrive.co.jp

Kazakhstan

Tel. +7 727 238 1404
Fax +7 727 243 2696
sew@sew-eurodrive.kz

Malaysia

Tel. +60 7 3549409
Fax +60 7 3541404
sales@sew-eurodrive.com.my

Mexico

Tel. +52 442 1030-300
Fax +52 442 1030-301
scmexico@seweurodrive.com.mx

Mongolia

Tel. +976 77109997
Fax +976 77109997
sew@sew-eurodrive.mn

Morocco

Tel. +212 523 32 27 80/81
Fax +212 523 32 27 89
sew@sew-eurodrive.ma

Netherlands

Tel. +31 10 4463-700
Fax +31 10 4155-552
info@sew-eurodrive.nl

New Zealand

Tel. +64 9 2745627
Fax +64 9 2740165
sales@sew-eurodrive.co.nz

Norway

Tel. +47 69 241-020
Fax +47 69 241-040
sew@sew-eurodrive.no

Paraguay

Tel. +595 991 519695
Fax +595 21 3285539
sewpy@sew-eurodrive.com.py

Peru

Tel. +51 1 3495280
Fax +51 1 3493002
sewperu@sew-eurodrive.com.pe

Poland

Tel. +48 42 676 53 00
Fax +48 42 676 53 49
sew@sew-eurodrive.pl

Portugal

Tel. +351 231 20 9670
Fax +351 231 20 3685
infosew@sew-eurodrive.pt

Russia

Tel. +7 812 3332522
Fax +7 812 3332523
sew@sew-eurodrive.ru

Singapore

Tel. +65 68621701
Fax +65 68612827
sewsingapore@sew-eurodrive.com

Slovakia

Tel. +421 2 33595 202
Fax +421 2 33595 200
sew@sew-eurodrive.sk

South Africa

Tel. +27 11 248 7000
Fax +27 11 248 7289
info@sew.co.za

South Korea

Tel. +82 31 492-8051
Fax +82 31 492-8056
master.korea@sew-eurodrive.com

Spain

Tel. +34 94 4318470
Fax +34 94 4318471
sew.spain@sew-eurodrive.es

Sweden

Tel. +46 36 3442 00
Fax +46 36 3442 80
info@sew-eurodrive.se

Switzerland

Tel. +41 61 41717-17
Fax +41 61 41717-00
info@imhof-sew.ch

Tanzania

Tel. +255 22 277 5780
Fax +255 22 277 5788
uroos@sew.co.tz

Thailand

Tel. +66 38 454281
Fax +66 38 454288
sewthailand@sew-eurodrive.com

Turkey

Tel. +90 262 999 1000-04
Fax +90 262 999 1009
sew@sew-eurodrive.com.tr

Ukraine

Tel. +380 56 370 3211
Fax +380 56 372 2078
sew@sew-eurodrive.ua

Uruguay

Tel. +598 2 2118189
Fax +598 2 2118190
sewuy@sew-eurodrive.com.uy

USA

Tel. +1 864 439-7537
Fax +1 864 439-7830
csllyman@seweurodrive.com

Venezuela

Tel. +58 241 832-9804
Fax +58 241 838-6275
ventas@sew-eurodrive.com.ve

How we're driving the world



SEW-EURODRIVE
Driving the world

SEW
EURODRIVE

SEW-EURODRIVE GmbH & Co KG
P.O.Box 30 23
76642 Bruchsal/Germany
Tel. +49 7251 75-0
Fax +49 7251 75-1970
sew@sew-eurodrive.com

→ www.sew-eurodrive.com