

Index

A

AC motors	
Mounting position designations.....	89
Additional documentation.....	12
Add-on encoder cables	579, 585
Anti-condensation heating.....	500

B

Backstop	471
BE brake technical data	375
Actuating force for manual brake release	398
Bake control wiring diagram.....	399
BE brake – operating currents	389
BE05, BE1, BE2 brake.....	390
BE30, BE32 brake	392
BE5, BE11, BE20 brake.....	391
Brake BE120, BE122	393
braking work, working air gap, braking torque, brake spring	375
Dimension sheets brake controls.....	412
Permissible braking work for working brake ac- tions	376
Permitted braking work in the case of emergen- cy switching off.....	385
Pulse frequencies of the BE brake.....	388
Resistance brake coils	394
Bearings	474
BMG02 brake	644
BR03 brake	645
Brake.....	345
Basic design.....	346
BE brake in detail.....	351
Braking torque.....	355
Braking torque in lifting applications	355
BSR current relay.....	365
Description	345
Design of BE brake	351
Determining the number of cycles until mainte- nance	359
Determining the required braking torque	355
Determining the required braking work	356
Function	346
Holding brake with emergency switching off ca- pacity.....	357

Increased emergency braking work for power- train applications	358
Installation in the wiring space of the motor with additional switching relay BSR, BUR	365
Installation of brake control in control cabinet.....	363
Installation of brake control in motor wiring space	363
Modular brake controls	361
Motor/brake assignment	353
Project planning notes	354
Project planning procedure	354
Selecting the brake control system	360
Selecting the brake size and braking torque.....	355
Selecting the brake voltage.....	360
Selection criteria	354
Short response times at switch-off.....	349
Short response times at switch-on.....	347
Working brake	356
Working capacity.....	356
Brake control block diagrams	
BG brake control	400
BGE brake control.....	401
BME brake control	406
BMH brake control	410
BMK brake control	411
BMP 3.1 brake control (control cabinet).....	409
BMP brake control	407
BMP3.1 brake control (motor).....	408
BMS brake control	405
BMV brake control	411
BS brake control	402
BSG brake control.....	402
BSR brake control	403
BUR brake control.....	404
Wiring diagram.....	399
Brake monitoring	522
Brake monitoring for diagnostic unit.....	522
Brakes	
Actuating force for manual brake release	398
Auxiliary terminal strip	412
Bake control wiring diagram.....	399
BE brake – operating currents	389
BMP3.1	414

Brake springs	375
Brake voltage supply via motor terminal board	367
Brakes for global motors	373
Brakes with DC 24 V supply	370
Braking torques	375
BST brake module - technical data	429
BST break module block diagram	429
BST safety-related brake control	428
BUR voltage relay	366
Connection type	374
Dimension drawings BG, BGE, BS, BSG	412
Dimension drawings BMS, BME, BMH, BMP, BMK, BMV	413
Dimension drawings SR10, SR11, SR15, UR11, UR15	412
Dimension drawings SR19	413
Dimensioning and routing of the cable	369
EMC (Electromagnetic compatibility)	374
Emergency stop features	642
Important design information	374
Maintenance intervals	374
Measuring principles	374
Motor overload circuit breaker	371
Parallel operation of several brakes with one controller	367
Permissible braking work for working brake actions	376
Permitted braking work in the case of emergency switching off	385
Pulse frequencies of the BE brake	388
Resistance brake coils	394
Safety-rated BE brake	415
Selecting the braking contactor	368
Technical data	375
Varistor overvoltage protection with direct DC voltage supply	370
Braking contactor	661
BSR brake control system	650
BST break module block diagram	429
BST safety-related brake control	428
Built-in encoder cable	591

C

Cable

Brakemotor cable for decentralized MOVI-SWITCH®	574
---	-----

Brakemotor cable with IS	572
Encoder cable with conductor end sleeve and 2 D-sub	583
Encoder cable with conductor end sleeves and D-sub	580, 589
Encoder cable with connection cover and 2 D-sub	581
Encoder cable with connection cover and D-sub	579, 585
Encoder cable with M23 and D-sub	584, 587
Encoder cable with one M12	591, 593
Encoder extension cable with conductor end sleeves and M23	596
Encoder extension cable with connection cover and M23	595
Encoder extension cable with M23 and D-sub	598
Encoder extension cable with two M23	597
Power cable	572
Project planning for cable cross section	563
Cable dimensioning to EN 60204	564
Cable specification of encoder cables	603
Cable specifications of the power cables	599
Condensation drain hole	476
Conformity with standards	17
Connection alternatives	
Han® 10 and modular plug connectors	512
IS integrated plug connector	509
Other industrial plug connectors	521
Terminal strip with cage clamp	518
Connection technology MOVI-SWITCH®-1E	536
Contact rating of plug connectors	621
Corrosion protection	57

D

Degree of protection	483
Degrees of protection pursuant to EN 60034	139
Dimension sheets	
WPU smooth pole-change unit	529
Documentation, additional	12
DRL.. project planning notes	
Absolute encoder	186
Dynamics package D1 or D2	186
Forced cooling fan	187
Inverter utilization	187
Sine encoder	186
DRL.. series asynchronous servomotors	50

DRM.. torque motor.....	53	Electrical interface SSI (Multi-Turn) + TTL (RS422).....	440
DT56, DR63 AC motor with brake		Electrical interface TTL (RS422).....	440
Brake control.....	642	Electrical interfaces.....	436
General information	641	Encoder connection	438
Technical data.....	654	Encoder mounting adapter.....	450
DT56, DR63 AC motors		Encoder mounting adapters.....	435, 436
CCC	608	Encoders provided by the customer	435
CSA/NEMA/UL-R.....	608	General information on project planning	438
Electrical characteristics	613	HTL built-in encoder data.....	453
Frequency and voltage	613	HTL sensor	445
JIS/JEC	608	Incremental encoder	435
Motor options, overview	612	Mechanical interface for mounting non-SEW encoders	433
Motor voltage	613	Non-SEW encoder mounting	433
Motors for the USA and Canada.....	614	Overview of absolute encoders.....	440
Overhung load conversion	619	Overview of built-in encoders.....	439
Overhung loads and axial forces	619	Overview of incremental encoders.....	439
Overview of encoders	627	Overview of the electrical interfaces	439
Power reduction	617	Pin assignment	432
Protection canopy C.....	633	Product description	431
Selecting the speed sensor.....	627	RS485 (Multi-Turn) + Sin / Cos.....	447
V.I.K.	608	Safety-rated encoder technical data	452
DT56, DR63 encoder cables.....	628	Sin / Cos encoder data	452
DT56, DR63 incremental rotary encoders		Sin/Cos encoder	441
Technical data.....	632	Speed sensors	438
DT56, DR63 multi-motor operation	652	SSI (Multi-Turn) + Sin / Cos	448
DT56, DR63 order information		SSI (Multi-Turn) Sin/Cos or TTL (RS422)	449
Position of motor terminal box and cable entry	611	Standardized mounting device for encoder ..	432
E		Technical data.....	441
Electrical characteristics.....	121	TTL (RS422)	443
EMC measures	77	Type designation.....	431
Encoders	431	Extension cable.....	595
Absolute encoder	435	F	
Built-in encoder	433	Fan guards	489
Connection alternatives	438	Features of DRL.. motors.....	50
Data on the multi-turn SSI in connection with Sin / Cos encoders.....	454	Dynamics	50
Data on the RS485 in connection with Sin / Cos encoders	453	Inverter combinations.....	51
Designs	435	Rated speeds.....	51
Electrical interface HTL.....	439	Startup	52
Electrical interface RS485 (Multi-Turn) + Sin / Cos with 1 VSS.....	440	First shaft end	468
Electrical interface Sin / Cos with 1 VSS	439	Forced cooling fan.....	485, 503
Electrical interface SSI (Multi-Turn) + Sin / Cos with 1 VSS	440		

G

Global motor	
Design specifications	45
Voltages	45

H

Humidity and acid protection and tropicalization	501
Humidity/acid protection and tropicalization	58

I

Installed plug connectors	512
Insulation	499
Integrated plug connectors	509
Inverter operation	77
IS integrated plug connector	
Technical data	624

K

KCC, KC1	518
----------------	-----

M

Motor identification for MOVIMOT®	560
Motor operating temperatures	59
Motor protection	493
Motor protection switch trigger temperatures	493
Thermal motor information with KTY84 - 130	496
Thermal motor information with PT100	497
Thermal motor protection with bimetallic switch NC contact	495
Thermal motor protection with PTC resistor	494
Motors at a glance	60
Motors at a glance, technical data	65
Mounting positions for AC motors	90
MOVI-SWITCH® 1E drives in IP66	533
MOVI-SWITCH® 2S drives in IP66	534
MOVI-SWITCH®-2S connection technology	
CB0 version (binary control)	539
CK0 version (AS-Interface)	542

O

Oil seals	471
Operating modes	131
Options and variants	
Anti-condensation heating	500

Backstop	471
Bearing options	474
Brake monitoring	522
Condensation drain hole	476
Degree of protection	483
Fan guard options	489
First shaft end	468
Forced cooling fan	503
Installed plug connectors	512
Insulation	499
Integrated plug connectors	509
Motor protection	493
Oil seals	471
Other industrial plug connectors	521
Pole-changing motors	502
Second shaft end	469
Terminal box	506
Terminal strip with cage clamp	518
Ventilation options	485
Vibration monitoring	527
Winding protection	501
WPU smooth pole-change unit	528
Output types of the motors	
7 series gearmotor	461
7 series gearmotor with feet	462
Foot-mounted motors	455
Gearmotor	461
Gearmotor with feet	462
IEC flange-mounted motor with boreholes	457
Overhung and axial loads	
Overhung and axial loads at the second shaft end	158
Overhung load diagrams for 2-, 4-, 6-, 12-pole motors	159
Overhung loads – DR., DRL.	156
Permitted axial load	158
Permitted overhung load – 2-, 4-, 6-, 12-pole motors	157
Permitted overhung load of DRL. motors	157
Permitted overhung load of DRM. motors	158
Permitted overhung load of pole-changing motors	157
Torques and duty types	158
Overview of encoders	
Absolute encoder	440
Built-in encoder	439

Incremental encoder	439	Limit characteristic curves in inverter operation	192
P		Motor voltage	121
Plug connector, integrated IS		Motor voltage for the global motor	124
Technical data	624	Motors on non-SEW inverters	198
Plug connectors AC., AS..		MOVIMOT®	561
Technical data	625	MOVI-SWITCH®	532
Plug connectors AM., AB., AD., AK..		No-load starting frequency	137
Technical data	626	Permitted starting frequency of the motor	138
Pole-changing motors	502	Permitted work done by the brake	138
Power cable	572	Pole-changing motors	170
Prefabricated cables	562	Power reduction	129
Intermediate sockets	570	Product characteristics of inverters	182, 185
Product Description		Project planning procedure – controlled	179
Asynchronous servomotors	50	Reinforced insulation for inverter operation > 500 V AC	191
Current-insulated rolling bearings	474	Standard connections for 50 Hz motors	127
DRM.. torque motor	53	Starting frequency	137
Global motor	45	Thermal classification	129
Mounting positions	90	Thermally permitted torque	192
MOVIMOT®	559	Vibration class	139
MOVI-SWITCH®	531	Project planning notes for BE brake	
Product description DT56, DR63		DUB10A brake monitoring diagnostic unit	523
General information	607	Project planning notes for connection alternatives	
Product description for DT56, DR63		Contact rating depending on temperature	517
Brakemotors	607	R	
Product groups	9	Rated data	17
Product names	13	Reinforced insulation	499
Project planning	121	Reinforced winding insulation with increased resistance against partial discharge	499
Tolerances	18	S	
Project planning for AC motors		Safe switching of inductances	78
Rated data	17	safety-rated brake	
Project planning for cable cross section	563	Braking work, working air gap, braking torques of the BE.. brakes (FS)	417
Project planning notes		BST brake module - technical data	429
50 Hz motor on the 60 Hz grid	127	BST break module block diagram	429
60 Hz motors	128	BST safety-related brake control	428
Asynchronous DRL.. servomotors	186	Definition of the categories	416
Brake voltage	126	Description	415
Center of gravity of motors	168	Performance Level	415
Degrees of protection pursuant to EN / ISO 60034-5	139	Permitted braking work for emergency switching off for brakes on horizontal drives	419
Drive selection – non-controlled operation	169	Permitted maximum braking work for emergency switching off for BE..(FS)	418
DRM.. torque motors	176		
Forced cooling fan voltage	124		
Frequency and voltage	121		
Inverter suitability	121		

Second shaft end	469
Serial number	84
SEW-EURODRIVE	
Group of companies	8
SEW-EURODRIVE	
Products	9
Systems	9
Standard conformity	17
Surface protection	57
Switching of inductances	78

T



Technical data	91	Technical data for DT56, DR63	
AC motors DT56, DR63	605	Brakes	654
Backstop	473	Technical data for encoder	441
Brake coil resistance for DT56, DR63	655	Encoder mounting adapter	450
DR63, DRS., DRE., DRP.. motors, 50 Hz, 6-pole, S1	106	HTL sensor	445
DRL.. servomotors, 4-pole, 50 Hz, 400 V	117	Overview of absolute encoders	440
DRM.. motors, 50 Hz, 12-pole	116	Overview of incremental encoders	439
DRS.. motor, 50 Hz, 4/2-pole, Dahlander connection S1	112	RS485 (Multi-Turn) + Sin / Cos	447
DRS.. motor, 50 Hz, 8/2-pole, separate winding, S3 40/60%	113	Sin/Cos encoder	441
DRS.. motor, 50 Hz, 8/4-pole, Dahlander connection S1	114	SSI (Multi-Turn) + Sin / Cos	448
DRS.. motors, 50/60 Hz, 2- and 4-pole, S1	109, 110	SSI (Multi-Turn) Sin/Cos or TTL (RS422)	449
DT56, DR63 incremental rotary encoders	632	TTL (RS422)	443
Global motor, 50/60 Hz, 2-pole, S1	92	Technical data for encoders	
Global motor, 50/60 Hz, 4-pole	93	Overview of built-in encoders	439
Global motor, 50/60 Hz, 6pole	95	Technical data for MOVI-SWITCH®	
IS integrated plug connector	624	DRP.. (Europa) 6-pole	554
Motors DR63, DRS., DRE., DRP., 50 Hz, 2-pole, S1	96	Technical data MOVI-SWITCH®	
Motors DT56, DR63, DRS., DRE., DRP., 50 Hz, 4-pole, S1	99	DRE.. (Europe) 6-pole	553
MOVIMOT®	561	DRE../MSW-1E 2-pole	547
Permitted work done by BM(G) brake	656	DRE../MSW-1E 4-pole	550
Plug connectors AM., AB., AD., AK.	626	DRP../MSW-1E 2-pole	548
Plug connectors AS., AC.	625	DRP../MSW-1E 4-pole	551
Setting different braking torques for DT56, DR63	654	DRS../MSW-1E 2-pole	546
Technical data at a glance	60	DRS../MSW-1E 4-pole	549
Technical data for BE brake		DRS../MSW-1E 6-pole	552
Motor/brake assignment	353	Temperature range, operating temperatures	59
		Terminal box	506
		Terminal strip with cage clamp	518
		Thermal characteristics	129
		Trademarks	13
		Type designation	
		Additional options	83
		Connection variants	82
		Encoders	81
		Examples	85
		Explosion-proof motors	83
		Mechanical attachments	81
		Motor series	80
		Output types, output types	80
		Storage	83
		Temperature sensor and temperature detection	81
		Ventilation	82
		Type designation for DT56, DR63 AC motors	610
		Type designation: AC motors and options	80


V

Ventilation	485
Additional flywheel mass.....	485
Air filter.....	490
Aluminum fan	486
Built-in encoder (pole ring).....	488
Canopy.....	489
Low noise fan guard.....	490
Metal fan	486
Non-ventilated design	492
Vibration monitoring	527

W

Winding protection	501
WPU smooth pole-change unit	528
Dimension sheets	529





SEW-EURODRIVE
Driving the world

SEW
EURODRIVE

SEW-EURODRIVE GmbH & Co KG
P.O. Box 3023
76642 BRUCHSAL
GERMANY
Phone +49 7251 75-0
Fax +49 7251-1970
sew@sew-eurodrive.com
→ www.sew-eurodrive.com