





**KA29B..**



Ø 30 H7
DIN 6885-3



Ø 25 H7



KH29B..



(→ 📖 4.1)	DRN										
	63MS	63M	71MS	71M	80MK	80MS	80M	90S	90L	100LS	100L/LM
AC	115	115	139	139	156	156	156	179	179	197	197
AD	98	98	118	118	128	128	128	140	140	157	157
ADS	98	98	129	129	139	139	139	150	150	158	158
L	387	401	403	423	434	451	480	481	513	511	561
LS	443	457	470	490	515	532	561	575	607	605	655
LB	190	204	206	226	237	254	283	284	316	314	364
LBS	246	260	273	293	318	335	364	378	410	408	458