



Technical drawing of a mechanical part, showing a side view and a cross-section.

Side View Dimensions:

- Total length: 370
- Central bore diameter: $\varnothing 350$
- Flange diameter: 395

Cross-section Dimensions:

- Central bore diameter: $\varnothing 60 \text{ H7}$
- Total length: 363
- Flange thickness: 18
- Distance from end to flange: 37

Callout: ISO 4017 M20x50-8.8

(→ 📖 4.1)	DRN												
	80MK	80M	90S	90L	100LS	100L/LM	112M	132S	132M	132L	160..	180..	200L
AC	156	156	179	179	197	197	221	221	261	261	314	357	394
AD	128	128	140	140	157	157	170	170	228	228	253	268	283
ADS	139	139	150	150	158	158	172	172	228	228	253	268	283
L	713	759	761	793	788	838	869	919	937	963	1029	1052	1162
LS	794	840	854	886	882	932	981	1031	1075	1100	1218	1241	1367
LB	218	264	266	298	293	343	374	424	442	468	534	557	667
LBS	299	345	359	391	387	437	486	536	580	605	723	746	872