



SEW
EURODRIVE


Multi-Speed Geared Motors

Edition

09/2001











Catalog
1053 301x / EN



SEW-EURODRIVE





	<p>1 Important Information on Selection Tables..... 4</p> <p>1.1 Selection tables for R, F, K and S multi-speed geared motors 4</p> <p>1.2 Selection tables for W multi-speed geared motors..... 5</p>	1
	<p>2 Multi-Speed Helical Geared Motors 6</p> <p>2.1 Designs 6</p> <p>2.2 Selection tables 4/2 poles (tapped wound) 7</p> <p>2.3 Selection tables 8/4 poles (tapped wound) 32</p> <p>2.4 Selection tables 6/2 poles (separately wound)..... 57</p> <p>2.5 Selection tables 8/2 poles (separately wound)..... 76</p> <p>2.6 Selection tables 12/2 poles (separately wound)..... 97</p>	2
	<p>3 Multi-Speed Parallel Shaft Helical Geared Motors..... 111</p> <p>3.1 Designs 111</p> <p>3.2 Selection tables 4/2 poles (tapped wound) 113</p> <p>3.3 Selection tables 8/4 poles (tapped wound) 135</p> <p>3.4 Selection tables 6/2 poles (separately wound)..... 154</p> <p>3.5 Selection tables 8/2 poles (separately wound)..... 170</p> <p>3.6 Selection tables 12/2 poles (separately wound)..... 188</p>	3
	<p>4 Multi-Speed Helical-Bevel Geared Motors..... 201</p> <p>4.1 Designs 201</p> <p>4.2 Selection tables 4/2 poles (tapped wound) 203</p> <p>4.3 Selection tables 8/4 poles (tapped wound) 221</p> <p>4.4 Selection tables 6/2 poles (separately wound)..... 238</p> <p>4.5 Selection tables 8/2 poles (separately wound)..... 253</p> <p>4.6 Selection tables 12/2 poles (separately wound)..... 268</p>	4
	<p>5 Multi-Speed Spiroplan® Geared Motors 278</p> <p>5.1 Designs 278</p> <p>5.2 Selection tables 4/2 poles (tapped wound) 279</p> <p>5.3 Selection tables 8/4 poles (tapped wound) 281</p> <p>5.4 Selection tables 6/2 poles (separately wound)..... 282</p> <p>5.5 Selection tables 8/2 poles (separately wound)..... 283</p>	5
	<p>6 Multi-Speed Helical-Worm Geared Motors 284</p> <p>6.1 Designs 284</p> <p>6.2 Selection tables 4/2 poles (tapped wound) 286</p> <p>6.3 Selection tables 8/4 poles (tapped wound) 299</p> <p>6.4 Selection tables 6/2 poles (separately wound)..... 312</p> <p>6.5 Selection tables 8/2 poles (separately wound)..... 323</p> <p>6.6 Selection tables 12/2 poles (separately wound)..... 335</p>	6
	<p>Address List</p>	

Use only with "Geared Motors" catalog, edition 05/2001.

Please note:

This "Multi-Speed Geared Motors" catalog, edition 08/2001, contains only selection tables. You will find any additional information required for drive selection in the "Geared Motors" catalog, edition 05/2001.




1 Important Information on Selection Tables

1.1 Selection tables for R, F, K and S multi-speed geared motors

Structure of the selection tables

The following figure shows the structure of the selection tables for R, F, K and S multi-speed geared motors:



05254AEN

Fig. 1: Structure of the selection tables for R, F, K and S multi-speed geared motors

Key

* Finite gear unit reduction ratio


1) Overhung load specified for foot-mounted gear unit with solid shaft



1.2 Selection tables for W multi-speed geared motors

Structure of the selection tables

The following figure shows the structure of the selection tables for W (Spiroplan®) multi-speed geared motors.



05255AEN

Fig. 2: Structure of the selection tables for W multi-speed geared motors

Key

- * Finite gear unit reduction ratio
- 1) Overhung load specified for foot-mounted gear unit with solid shaft