



10 Kegelrad-Getriebemotoren

10.1 Ausführungsarten K..DRN..




K.9DR..




KA.9DR..


10



K..7DR..








KA..7BDR..
KV..7BDR..




KH..7BDR..

18014407174236299


**KF..7DR..****KAF..7DR..
KVF..7DR..****KT..7/TDR..****KHF..7DR..****KA..7/TDR..
KV..7/TDR..**

9007207919497227

21933170/DE – 11/2015




KH..7/TDR..




**KAZ..7DR..
KVZ..7DR..**

10



KHZ..7DR..



KZ..7DR..

27021606882178955

10.2 Geometrisch mögliche Kombinationen K..DRN..

K19, $n_e=1400$ 1/min						80 Nm	
n_a rpm	M_{amax} Nm	F_{Ra} N	$\varphi_{(R)}$ °	i	DR63S DR63M DR63L	DRS71S DRS71M	DRN80M DRN90S
 2							
24	70	4330	-	58.68			
26	70	4330	-	53.88			
28	70	4330	-	49.69			
31	69	4340	-	44.48			
34	67	4350	-	40.63			
41	64	4370	-	34.29			
44	80	4260	-	31.74			
48	61	4200	-	29.29			
48	80	4120	-	29.14			
52	60	4090	-	27.16			
52	80	3990	-	26.88			
58	80	3820	-	24.06			
64	80	3680	-	21.98			
75	80	3430	-	18.55			
88	80	3210	-	15.84			
95	80	3110	-	14.69			
110	80	2930	-	12.70			
118	79	2850	-	11.84			
136	76	2720	-	10.32			
146	63	2910	-	9.58			
173	80	2590	-	8.09			
203	80	2420	-	6.91			
218	80	2340	-	6.41			
253	80	2200	-	5.54			
271	80	2140	-	5.16			
311	80	2010	-	4.50			

K29, $n_e=1400$ 1/min						130 Nm			
n_a rpm	M_{amax} Nm	F_{Ra} N	$\varphi_{(R)}$ °	i	DR63S DR63M DR63L	DRS71S DRS71M	DRN80M DRN90S	DRN90L	DRN100LS
 2									
19	130	4980	-	71.93					
21	130	4980	-	66.25					
23	130	4980	-	61.28					
26	130	4980	-	54.89					
28	130	4980	-	50.35					
33	128	4790	-	42.87					
36	130	4720	-	38.90					
38	122	4560	-	36.96					
39	130	4560	-	35.83					
42	130	4410	-	33.15					
46	115	4250	-	30.11					
47	130	4210	-	29.69					
51	130	4060	-	27.23					
56	109	3980	-	24.91					
60	130	3790	-	23.19					

K29, $n_e=1400$ 1/min					130 Nm				
n_a rpm	M_{amax} Nm	F_{Ra} N	$\Phi_{(R)}$ °	i	DR63S DR63M DR63L	DRS71S DRS71M	DRN80M DRN90S	DRN90L	DRN100LS
63	105	3820	-	22.08					
70	130	3550	-	19.99					
86	130	3240	-	16.29					
104	130	2970	-	13.47					
117	130	2810	-	11.94					
141	110	3000	-	9.90					
153	130	2470	-	9.17					
164	122	2740	-	8.53					
187	123	2300	-	7.48					
201	112	2580	-	6.95					
243	112	2370	-	5.75					
275	110	2260	-	5.10					
357	126	1910	-	3.92					
439	110	1830	-	3.19					

10

K37, $n_e=1400$ 1/min					200 Nm			
n_a rpm	M_{amax} Nm	F_{Ra} N	$\Phi_{(R)}$ °	i	DR63S DR63M DR63L DRS71S DRS71M	DRN80M DRN90S	DRN90L	DRN100LS DRN100L
 3								
13	200	5640	6.8	106.38				
14	200	5640	6.8	97.81				
17	200	5640	6.9	83.69				
19	200	5520	6.9	72.54				
21	200	5360	6.9	67.80				
24	200	5020	6.9	58.60				
28	200	4660	7	49.79				
31	200	4420	7	44.46				
37	200	4100	7	37.97				
39	200	3970	7.1	35.57				
47	200	3650	7.1	29.96				
49	200	3580	8.1	28.83				
56	200	3330	8.1	24.99				
60	195	3260	8.2	23.36				
69	185	3110	8.3	20.19				
82	180	2900	8.4	17.15				
91	175	2780	8.5	15.31				
107	165	2650	8.6	13.08				
115	160	2600	11.9	12.14				
133	160	2410	12.2	10.49				
157	160	2200	12.4	8.91				
176	155	2110	12.5	7.96				
206	150	1980	12.8	6.80				
220	145	1950	12.9	6.37				
261	140	1810	13.2	5.36				
352	125	1660	13	3.98				

21933170/DE – 11/2015

K37R17, n _e =1400 1/min						200 Nm
n _a rpm	M _{amax} Nm	F _{Ra} N	Φ _(/R) °	i	DR63S DR63M DR63L DRS71S DRS71M	DRN80M
 3  3						
0.20	200	5640	-	6832		
0.24	200	5640	-	5922		
0.25	200	5640	-	5491		
0.29	200	5640	-	4759		
0.34	200	5640	-	4160		
0.38	200	5640	-	3645		
0.44	200	5640	-	3205		
0.50	200	5640	-	2801		
0.57	200	5640	-	2454		
0.65	200	5640	-	2166		
0.74	200	5640	-	1891		
0.84	200	5640	-	1660		
0.95	200	5640	-	1466		
1.1	200	5640	-	1288		
1.2	200	5640	-	1136		
 3  2						
1.4	200	5640	-	996		
1.6	200	5640	-	876		
1.8	200	5640	-	761		
2.1	200	5640	-	671		
2.4	200	5640	-	585		
2.7	200	5640	-	512		
3.1	200	5640	-	451		
3.5	200	5640	-	396		
4.0	200	5640	-	346		
4.6	200	5640	-	304		
5.2	200	5640	-	267		
6.0	200	5640	-	234		
6.8	200	5640	-	205		
7.7	200	5640	-	181		
8.8	200	5640	-	160		
10	200	5640	-	136		
11	200	5640	-	127		
13	200	5640	-	110		
15	200	5640	-	96		

K39, $n_e=1400$ 1/min						300 Nm			
n_a rpm	M_{amax} Nm	F_{Ra} N	$\varphi_{(R)}$ °	i	DR63S DR63M DR63L DRS71S DRS71M	DRN80M DRN90S	DRN90L	DRN100LS DRN100L	DRN112M
 2									
24	300	7500	-	58.24					
28	300	7440	-	49.69					
32	300	7000	-	43.45					
34	300	6840	-	41.28					
39	300	6440	-	36.22					

K39, $n_e=1400$ 1/min

300 Nm

n_a rpm	M_{amax} Nm	F_{Ra} N	$\Phi_{(R)}$ °	i	DR63S DR63M DR63L DRS71S DRS71M	DRN80M DRN90S	DRN90L	DRN100LS DRN100L	DRN112M
46	300	5960	-	30.72					
50	300	5670	-	27.73					
57	300	5330	-	24.40					
61	300	5180	-	23.04					
71	295	4820	-	19.62					
79	290	4630	-	17.83					
82	115	6360	-	17.06					
91	280	4380	-	15.44					
96	190	5570	-	14.56					
104	270	4160	-	13.44					
110	250	4930	-	12.73					
116	255	4790	-	12.09					
132	285	4360	-	10.61					
146	250	3640	-	9.60					
156	300	3950	-	9.00					
172	300	3760	-	8.12					
196	300	3530	-	7.15					
207	300	3430	-	6.75					
243	275	3300	-	5.75					
268	260	3240	-	5.22					
310	240	3130	-	4.52					
355	215	3070	-	3.94					
498	170	2870	-	2.81					

K39R17, $n_e=1400$ 1/min

300 Nm



n_a rpm	M_{amax} Nm	F_{Ra} N	$\Phi_{(R)}$ °	i	DR63S DR63M DR63L DRS71S DRS71M	DRN80M
 2  3						
0.35	300	7500	-	4057		
0.42	300	7500	-	3370		
0.48	300	7500	-	2906		
0.56	300	7500	-	2508		
0.59	300	7500	-	2367		
0.65	300	7500	-	2162		
0.74	300	7500	-	1881		
0.79	300	7500	-	1762		
0.86	300	7500	-	1622		
0.94	300	7500	-	1494		
1.1	300	7500	-	1321		
1.2	300	7500	-	1169		
1.3	300	7500	-	1093		
 2  2						
1.5	300	7500	-	956		
1.7	300	7500	-	814		
2.0	300	7500	-	711		
2.3	300	7500	-	605		
2.8	300	7500	-	504		

21933170/DE – 11/2015

K39R17, $n_e=1400$ 1/min					300 Nm	
n_a rpm	M_{amax} Nm	F_{Ra} N	$\Phi_{(R)}$ °	i	DR63S DR63M DR63L DRS71S DRS71M	DRN80M
3.1	300	7500	-	454		
3.5	300	7500	-	399		
3.8	300	7500	-	365		
4.5	300	7500	-	312		
4.7	300	7500	-	299		
5.5	300	7500	-	254		
6.0	300	7500	-	234		
6.7	300	7500	-	210		
7.4	300	7500	-	189		
8.0	300	7500	-	174		
9.0	300	7500	-	156		
9.9	300	7500	-	142		
12	300	7500	-	117		
19	295	7500	-	75		

K47, $n_e=1400$ 1/min					400 Nm			
n_a rpm	M_{amax} Nm	F_{Ra} N	$\Phi_{(R)}$ °	i	DR63S DR63M DR63L DRS71S DRS71M	DRN80M DRN90S	DRN90L	DRN100LS DRN100L
 3								
11	400	5920	6.4	131.87*				
12	400	5920	6.4	121.48*				
13	400	5920	6.4	104.37				
15	400	5920	6.4	90.86				
16	400	5920	6.4	85.12*				
19	400	5920	6.5	75.20*				
20	400	5920	6.5	69.84				
22	400	5920	6.5	63.30*				
25	400	5920	6.5	56.83				
29	400	5920	6.6	48.95*				
30	400	5920	6.6	46.03*				
35	400	5920	6.6	39.61				
40	400	5920	6.7	35.39				
45	400	5700	7.5	31.30				
48	400	5520	7.5	29.32				
54	400	5170	7.6	25.91				
58	400	4970	7.7	24.06				
64	400	4710	7.7	21.81				
72	400	4440	7.7	19.58				
83	380	4220	7.8	16.86				
88	380	4080	7.9	15.86				
103	360	3890	8	13.65				
115	350	3720	8.3	12.19				
119	280	4060	10.5	11.77				
133	280	3830	10.6	10.56				
154	280	3540	10.7	9.10				
164	270	3500	10.8	8.56				
190	250	3380	11	7.36				

K47, n _e =1400 1/min					400 Nm			
n _a rpm	M _{amax} Nm	F _{Ra} N	φ _(/R) °	i	DR63S DR63M DR63L DRS71S DRS71M	DRN80M DRN90S	DRN90L	DRN100LS DRN100L
213	240	3270	11.5	6.58				
241	230	3140	11.8	5.81				
302	205	2980	12	4.64				

K47R37, n _e =1400 1/min					400 Nm			
n _a rpm	M _{amax} Nm	F _{Ra} N	φ _(/R) °	i	DR63S DR63M DR63L DRS71S DRS71M	DRN80M DRN90S	DRN90L	DRN100LS DRN100L
 3 3								
0.14	400	5920	-	10138				
0.16	400	5920	-	8534				
0.18	400	5920	-	7662				
0.21	400	5920	-	6826				
0.23	400	5920	-	5983				
0.27	400	5920	-	5159				
0.30	400	5920	-	4601*				
0.36	400	5920	-	3940				
0.40	400	5920	-	3477				
0.46	400	5920	-	3043				
0.51	400	5920	-	2733				
0.59	400	5920	-	2354				
0.68	400	5920	-	2063				
0.77	400	5920	-	1819				
0.88	400	5920	-	1586				
1.0	400	5920	-	1388				
 3 2								
1.1	400	5920	-	1222				
1.3	400	5920	-	1097				
1.5	400	5920	-	945				
1.7	400	5920	-	831*				
1.9	400	5920	-	718*				
2.2	400	5920	-	639				
2.5	400	5920	-	552				
2.8	400	5920	-	495				
3.3	400	5920	-	426				
3.7	400	5920	-	375				
4.3	400	5920	-	327				
4.8	400	5920	-	289				
5.5	400	5920	-	256				
6.2	400	5920	-	225				
7.1	400	5920	-	198				
8.2	400	5920	-	171				
9.2	400	5920	-	153				
11	400	5920	-	131				
12	400	5920	-	112				
14	400	5920	-	99				
15	400	5920	-	94				

K49, $n_e=1400$ 1/min										500 Nm
n_a rpm	M_{amax} Nm	F_{Ra} N	$\Phi_{(R)}$ °	i	DR63S DR63M DR63L DRS71S DRS71M	DRN80M DRN90S	DRN90L	DRN100LS DRN100L	DRN112M	DRN132S DRN132M
 2										
19	475	9000	-	75.20						
20	445	9000	-	70.19						
23	500	9000	-	60.27						
26	500	8590	-	52.94						
28	500	8380	-	50.29						
32	500	7900	-	44.44						
37	500	7310	-	37.98						
40	500	7000	-	34.81						
46	500	6550	-	30.55						
48	500	6370	-	28.95						
55	500	5940	-	25.34						
61	500	5610	-	22.83						
62	150	8470	-	22.50						
67	140	8310	-	21.00						
70	500	5220	-	20.03						
78	260	7300	-	18.04						
79	500	4860	-	17.67						
88	340	6570	-	15.84						
89	490	4590	-	15.67						
93	325	6500	-	15.05						
105	470	4320	-	13.38						
105	420	5740	-	13.30						
123	495	5000	-	11.37						
134	480	4860	-	10.42						
153	500	4460	-	9.14						
162	500	4340	-	8.66						
185	500	4050	-	7.58						
205	500	3840	-	6.83						
234	500	3570	-	5.99						
265	485	3400	-	5.29						
299	465	3270	-	4.69						
350	440	3110	-	4.00						

K49R37, $n_e=1400$ 1/min										500 Nm
n_a rpm	M_{amax} Nm	F_{Ra} N	$\Phi_{(R)}$ °	i	DR63S DR63M DR63L DRS71S DRS71M	DRN80M DRN90S	DRN90L	DRN100LS DRN100L		
 2  3										
0.20	500	9000	-	7137						
0.23	500	9000	-	5991						
0.27	500	9000	-	5120						
0.35	500	9000	-	4034						
0.39	500	9000	-	3580						
0.45	500	9000	-	3081						
0.50	500	9000	-	2773						
0.55	500	9000	-	2545						
0.59	500	9000	-	2372						

K49R37, $n_e=1400$ 1/min					500 Nm			
n_a rpm	M_{amax} Nm	F_{Ra} N	$\Phi_{(R)}$ °	i	DR63S DR63M DR63L DRS71S DRS71M	DRN80M DRN90S	DRN90L	DRN100LS DRN100L
0.66	500	9000	-	2118				
0.72	500	9000	-	1941				
0.80	500	9000	-	1741				
0.86	500	9000	-	1632				
0.92	500	9000	-	1521				
1.1	500	9000	-	1228				
1.4	500	9000	-	1000				
 2  2								
0.98	500	9000	-	1424				
1.1	500	9000	-	1309				
1.2	500	9000	-	1120				
1.5	500	9000	-	908				
1.7	500	9000	-	802				
2.0	500	9000	-	701				
2.2	500	9000	-	645				
2.4	500	9000	-	595				
2.6	500	9000	-	543				
2.8	500	9000	-	501				
3.1	500	9000	-	449				
3.5	500	9000	-	401				
3.9	500	9000	-	360				
4.2	500	9000	-	330				
4.7	500	9000	-	300				
5.1	500	9000	-	274				
5.8	500	9000	-	243				
6.5	500	9000	-	217				
7.3	500	9000	-	193				
8.0	500	9000	-	176				
9.2	500	9000	-	152				
11	500	9000	-	125				
14	500	9000	-	99				

K57, $n_e=1400$ 1/min					600 Nm				
n_a rpm	M_{amax} Nm	F_{Ra} N	$\Phi_{(R)}$ °	i	DR63S DR63M DR63L DRS71S DRS71M	DRN80M DRN90S	DRN90L	DRN100LS DRN100L	DRN112M
 3									
9.6	600	7630	5.9	145.14*					
11	600	7630	5.9	123.85					
13	600	7630	5.9	108.29					
14	600	7630	5.9	102.88*					
16	600	7630	5.9	90.26*					
18	600	7630	5.9	76.56*					
20	600	7630	6	69.12					
23	600	7630	6	60.81*					
24	600	7630	6	57.42*					
29	600	7630	6	48.89					
32	600	7630	6.1	44.43					

21933170/DE – 11/2015

K57, $n_e=1400$ 1/min					600 Nm				
n_a rpm	M_{amax} Nm	F_{Ra} N	$\varphi_{(R)}$ °	i	DR63S DR63M DR63L DRS71S DRS71M	DRN80M DRN90S	DRN90L	DRN100LS DRN100L	DRN112M
36	600	7630	6.1	38.49					
39	600	7630	6.8	35.70					
46	600	7300	6.9	30.28					
51	600	6930	6.9	27.34					
58	600	6480	6.9	24.05					
62	600	6280	6.9	22.71					
72	575	5910	7	19.34					
80	555	5740	7.2	17.57					
92	535	5430	7.3	15.22					
106	510	5190	7.4	13.25					
117	415	5150	9.4	11.92					
124	415	4990	9.5	11.26					
146	405	4650	9.6	9.59					
161	390	4520	10	8.71					
185	365	4360	10.2	7.55					
213	345	4180	10.4	6.57					
299	300	3800	11	4.69					

K57R37, $n_e=1400$ 1/min					600 Nm			
n_a rpm	M_{amax} Nm	F_{Ra} N	$\varphi_{(R)}$ °	i	DR63S DR63M DR63L DRS71S DRS71M	DRN80M DRN90S	DRN90L	DRN100LS DRN100L
 3  3								
0.12	600	7630	-	12169				
0.13	600	7630	-	11162*				
0.15	600	7630	-	9503				
0.16	600	7630	-	8547				
0.19	600	7630	-	7277				
0.22	600	7630	-	6478*				
0.25	600	7630	-	5662*				
0.28	600	7630	-	5033				
0.32	600	7630	-	4340				
0.36	600	7630	-	3854				
0.41	600	7630	-	3390				
0.48	600	7630	-	2924				
0.54	600	7630	-	2593				
0.62	600	7630	-	2249				
0.70	600	7630	-	1986				
 3  2								
0.80	600	7630	-	1743				
0.91	600	7630	-	1539				
1.0	600	7630	-	1354				
1.2	600	7630	-	1174				
1.4	600	7630	-	1036*				
1.5	600	7630	-	906*				
1.7	600	7630	-	806				
2.0	600	7630	-	699				
2.3	600	7630	-	615				

K57R37, $n_e=1400$ 1/min					600 Nm			
n_a rpm	M_{amax} Nm	F_{Ra} N	$\Phi_{(R)}$ °	i	DR63S DR63M DR63L DRS71S DRS71M	DRN80M DRN90S	DRN90L	DRN100LS DRN100L
2.6	600	7630	-	544*				
3.0	600	7630	-	473				
3.3	600	7630	-	421				
3.9	600	7630	-	362				
4.4	600	7630	-	319				
5.0	600	7630	-	280				
5.7	600	7630	-	246				
6.5	600	7630	-	215				
7.3	600	7630	-	192				
8.4	600	7630	-	166				
9.7	600	7630	-	145				
11	600	7630	-	129				
13	600	7630	-	111				
14	600	7630	-	97				

K67, $n_e=1400$ 1/min					820 Nm					
n_a rpm	M_{amax} Nm	F_{Ra} N	$\Phi_{(R)}$ °	i	DR63S DR63M DR63L DRS71S DRS71M	DRN80M DRN90S	DRN90L	DRN100LS DRN100L	DRN112M	DRN132S DRN132M
 3										
9.7	820	10300	6.2	144.79*						
11	820	10300	6.2	123.54						
13	820	10300	6.1	108.03						
14	820	10300	6.1	102.62						
16	820	10300	6.2	90.04						
18	820	10300	6.2	76.37						
20	820	10300	6.2	68.95						
23	820	10300	6.2	60.66						
24	820	10300	6.2	57.28						
29	820	10300	6.3	48.77						
32	820	10300	6.3	44.32						
36	800	10500	6.4	38.39						
39	820	10300	7.1	35.62						
46	820	10300	7.1	30.22						
51	820	10300	7.1	27.28						
58	800	10500	7.2	24.00						
62	780	10700	7.2	22.66						
73	760	10800	7.3	19.30						
80	740	11000	7.5	17.54						
92	700	11300	7.5	15.19						
106	670	11500	7.6	13.22						
112	530	12300	8.6	12.48						
132	500	11800	8.8	10.63						
145	480	11500	9.1	9.66						
167	440	11100	9.3	8.37						
192	420	10700	9.4	7.28						
269	350	9860	10	5.20						

21933170/DE – 11/2015

K67R37, $n_e=1400$ 1/min					820 Nm			
n_a rpm	M_{amax} Nm	F_{Ra} N	$\Phi_{(R)}$ °	i	DR63S DR63M DR63L DRS71S DRS71M	DRN80M DRN90S	DRN90L	DRN100LS DRN100L
 3  3								
0.12	820	10300	-	12139				
0.13	820	10300	-	11134				
0.15	820	10300	-	9479				
0.17	820	10300	-	8173				
0.19	820	10300	-	7259				
0.22	820	10300	-	6462				
0.25	820	10300	-	5648				
0.29	820	10300	-	4846				
0.32	820	10300	-	4329				
0.37	820	10300	-	3750				
0.42	820	10300	-	3315				
0.48	820	10300	-	2917				
0.55	820	10300	-	2532				
0.62	820	10300	-	2244				
0.71	820	10300	-	1981				
 3  2								
0.81	820	10300	-	1739				
0.91	820	10300	-	1535				
1.0	820	10300	-	1351				
1.2	820	10300	-	1171				
1.4	820	10300	-	1034				
1.6	820	10300	-	903				
1.8	820	10300	-	793				
2.0	820	10300	-	697				
2.3	820	10300	-	613				
2.6	820	10300	-	542				
3.0	820	10300	-	471				
3.3	820	10300	-	420				
3.9	820	10300	-	361				
4.3	820	10300	-	323				
5.0	820	10300	-	279				
5.7	820	10300	-	246				
6.5	820	10300	-	217				
7.3	820	10300	-	191				
8.4	820	10300	-	166				
9.7	820	10300	-	144				
11	820	10300	-	122				

K77, $n_e=1400$ 1/min					1550 Nm						
n_a rpm	M_{amax} Nm	F_{Ra} N	$\Phi_{(R)}$ °	i	DR63S DR63M DR63L DRS71S DRS71M	DRN80M DRN90S	DRN90L	DRN100LS DRN100L	DRN112M	DRN132S DRN132M	DRN132L DRN160M DRN160L
 3											
7.3	1450	16100	5.4	192.18							
7.8	1450	16100	5.4	179.37							
9.1	1550	15400	5.4	154.02							

K77, $n_e=1400$ 1/min											1550 Nm
n_a rpm	M_{amax} Nm	F_{Ra} N	$\Phi_{(R)}$ °	i	DR63S DR63M DR63L DRS71S DRS71M	DRN80M DRN90S	DRN90L	DRN100LS DRN100L	DRN112M	DRN132S DRN132M	DRN132L DRN160M DRN160L
10	1550	15400	5.4	135.28							
11	1550	15400	5.4	128.52							
12	1550	15400	5.4	113.56							
14	1550	15400	5.4	97.05							
16	1550	15400	5.4	88.97							
18	1550	15400	5.4	78.07							
19	1550	15400	5.4	73.99							
22	1550	15400	5.5	64.75							
24	1550	15400	5.5	58.34							
27	1550	15400	5.5	51.18							
31	1550	15400	5.5	45.16							
35	1550	15400	5.6	40.04							
36	1500	15700	6	38.39							
40	1550	15400	6	35.20							
45	1550	15400	6.1	30.89							
48	1550	15400	6.1	29.27							
55	1550	15400	6.1	25.62							
61	1550	15400	6.3	23.08							
69	1500	15700	6.3	20.25							
78	1450	16100	6.3	17.87							
88	1400	15500	6.4	15.84							
104	1340	14800	6.5	13.52							
113	1000	15100	7.9	12.36							
129	990	14400	7.8	10.84							
146	940	13900	7.9	9.56							
165	890	13500	8.2	8.48							
193	820	13100	8.3	7.24							

K77R37, n _e =1400 1/min						1550 Nm		
n _a rpm	M _{amax} Nm	F _{Ra} N	φ _(/R) °	i	DR63S DR63M DR63L DRS71S DRS71M	DRN80M DRN90S	DRN90L	DRN100LS DRN100L
 3  3								
0.09	1550	15400	-	15310				
0.10	1550	15400	-	14043				
0.12	1550	15400	-	11955				
0.14	1550	15400	-	10217				
0.16	1550	15400	-	8809				
0.19	1550	15400	-	7528				
0.21	1550	15400	-	6606				
0.24	1550	15400	-	5774				
0.28	1550	15400	-	5089				
0.31	1550	15400	-	4489				
0.35	1550	15400	-	3961				
0.40	1550	15400	-	3485				
0.48	1550	15400	-	2901				
0.52	1550	15400	-	2717				
0.59	1550	15400	-	2370				

K77R37, $n_e=1400$ 1/min

1550 Nm

n_a rpm	M_{amax} Nm	F_{Ra} N	$\Phi_{(R)}$ °	i	DR63S DR63M DR63L DRS71S DRS71M	DRN80M DRN90S	DRN90L	DRN100LS DRN100L
 3  2								
0.68	1550	15400	-	2050				
0.79	1550	15400	-	1772				
0.92	1550	15400	-	1514				
1.0	1550	15400	-	1388				
1.1	1550	15400	-	1218				
1.3	1550	15400	-	1053				
1.5	1550	15400	-	924				
1.7	1550	15400	-	815				
2.0	1550	15400	-	709				
2.3	1550	15400	-	622				
2.5	1550	15400	-	552				
2.9	1550	15400	-	485				
3.3	1550	15400	-	428				
3.8	1550	15400	-	367				
4.3	1550	15400	-	328				
4.8	1550	15400	-	290				
5.6	1550	15400	-	252				
6.3	1550	15400	-	221				
7.2	1550	15400	-	195				
8.0	1550	15400	-	175				
9.1	1550	15400	-	154				

K87, $n_e=1400$ 1/min

2700 Nm

n_a rpm	M_{amax} Nm	F_{Ra} N	$\Phi_{(R)}$ °	i	DRS71M	DRN80M DRN90S	DRN90L	DRN100LS DRN100L	DRN112M	DRN132S DRN132M	DRN132L DRN160M DRN160L	DRN180M DRN180L	DRN200L
 3													
7.1	2700	27300	5.3	197.37									
8.0	2700	27300	5.3	174.19									
8.5	2700	27300	5.3	164.34*									
9.5	2700	27300	5.4	147.32*									
11	2700	27300	5.4	126.91*									
12	2700	27300	5.4	115.82									
14	2700	27300	5.4	102.71*									
16	2700	27300	5.4	86.34									
18	2700	27300	5.4	79.34									
20	2700	27300	5.4	70.46									
22	2700	26200	5.4	63.00*									
25	2700	25000	5.5	56.64									
28	2700	23500	5.5	49.16									
32	2600	22800	5.5	44.02									
38	2500	21400	5.5	36.52*									
45	2700	19200	6.1	31.39									
50	2600	18500	6.1	27.88									
56	2500	18000	6.1	24.92									
62	2300	17900	6.2	22.41									
72	2300	16800	6.3	19.45									
80	2200	16300	6.3	17.42									

21933170/DE – 11/2015

K87, $n_e=1400$ 1/min						2700 Nm							
n_a rpm	M_{amax} Nm	F_{Ra} N	$\Phi_{(R)}$ '	i	DRS71M	DRN80M DRN90S	DRN90L	DRN100LS DRN100L	DRN112M	DRN132S DRN132M	DRN132L DRN160M DRN160L	DRN180M DRN180L	DRN200L
88	1800	16000	6.5	16.00									
97	2100	15300	6.4	14.45									
111	2000	14800	6.5	12.56									
125	1500	14900	6.7	11.17									
140	1500	14200	6.8	10.00									
169	1400	13500	7	8.29									
194	1300	13200	7.1	7.21									

K87R57, n _e =1400 1/min						2700 Nm				
n _a rpm	M _{amax} Nm	F _{Ra} N	Φ _(/R) '	i	DR63S DR63M DR63L DRS71S DRS71M	DRN80M DRN90S	DRN90L	DRN100LS DRN100L	DRN112M	DRN132S DRN132M
 3  3										
0.09	2700	27300	-	14829						
0.11	2700	27300	-	13168						
0.12	2700	27300	-	11737						
0.14	2700	27300	-	10217						
0.15	2700	27300	-	9073						
0.18	2700	27300	-	7854						
0.20	2700	27300	-	6832						
0.24	2700	27300	-	5930						
0.27	2700	27300	-	5240						
0.31	2700	27300	-	4562						
0.35	2700	27300	-	4037						
0.39	2700	27300	-	3609						
0.45	2700	27300	-	3107						
0.51	2700	27300	-	2728						
0.59	2700	27300	-	2371						
 3  2										
0.67	2700	27300	-	2088						
0.76	2700	27300	-	1854						
0.84	2700	27300	-	1657						
0.99	2700	27300	-	1415						
1.1	2700	27300	-	1229						
1.3	2700	27300	-	1078						
1.5	2700	27300	-	951						
1.7	2700	27300	-	837						
1.9	2700	27300	-	726						
2.2	2700	27300	-	638						
2.5	2700	27300	-	562*						
3.0	2700	27300	-	474*						
3.3	2700	27300	-	426						
3.8	2700	27300	-	373						
4.2	2700	27300	-	330						
4.8	2700	27300	-	294						
5.6	2700	27300	-	250						
5.9	2700	27300	-	236						
7.0	2700	27300	-	201						
7.7	2700	27300	-	183						

21933170/DE – 11/2015

K87R57, $n_e=1400$ 1/min										2700 Nm
n_a rpm	M_{amax} Nm	F_{Ra} N	$\Phi_{(R)}$ °	i	DR63S DR63M DR63L DRS71S DRS71M	DRN80M DRN90S	DRN90L	DRN100LS DRN100L	DRN112M	DRN132S DRN132M
8.8	2700	27300	-	159						
9.9	2600	27400	-	141						

K97, n _e =1400 1/min										4300 Nm		
n _a rpm	M _{amax} Nm	F _{Ra} N	Φ _(R) °	i	DRN80M DRN90S	DRN90L	DRN100LS DRN100L	DRN112M	DRN132S DRN132M	DRN132L DRN160M DRN160L	DRN180M DRN180L	DRN200L DRN225S
3												
8.0	4300	40000	6.8	176.05*								
9.1	4300	40000	6.8	153.21*								
10.0	4300	40000	6.8	140.28								
11	4300	40000	6.8	123.93*								
13	4300	40000	6.8	105.13								
14	4300	40000	6.8	96.80								
16	4300	38800	6.8	86.52								
18	4300	37100	6.8	77.89*								
20	4300	35600	6.9	70.54								
22	4300	33800	6.9	62.55								
25	4300	32300	6.9	56.55								
29	4300	30000	6.9	47.93*								
33	4300	28300	6.9	41.87								
37	4300	27100	7.4	38.30								
41	4300	25700	7.5	34.23								
45	4300	24500	7.5	30.82								
50	4300	23300	7.5	27.91								
57	4300	22000	7.6	24.75								
63	4300	20900	7.6	22.37								
74	4300	19100	7.6	18.96								
85	4300	17800	7.7	16.56								
101	4300	16100	7.7	13.85								
117	3890	16200	7.8	11.99								
134	2870	16400	9.7	10.41								
161	2660	15800	9.8	8.71								
186	2400	15700	10	7.54								

K97R57, $n_e=1400$ 1/min										4300 Nm
n_a rpm	M_{amax} Nm	F_{Ra} N	$\Phi_{(R)}$ °	i	DR63S DR63M DR63L DRS71S DRS71M	DRN80M DRN90S	DRN90L	DRN100LS DRN100L	DRN112M	DRN132S DRN132M
 3  3										
0.08	4300	40000	-	18091						
0.08	4300	40000	-	16666						
0.09	4300	40000	-	14897						
0.11	4300	40000	-	13182						
0.12	4300	40000	-	11677						
0.14	4300	40000	-	10317						
0.15	4300	40000	-	9083						
0.17	4300	40000	-	8054						

K97R57, $n_e=1400$ 1/min										4300 Nm
n_a rpm	M_{amax} Nm	F_{Ra} N	$\Phi_{(R)}$ °	i	DR63S DR63M DR63L DRS71S DRS71M	DRN80M DRN90S	DRN90L	DRN100LS DRN100L	DRN112M	DRN132S DRN132M
0.20	4300	40000	-	6970						
0.23	4300	40000	-	6027						
0.26	4300	40000	-	5391						
0.30	4300	40000	-	4669						
0.34	4300	40000	-	4082						
0.39	4300	40000	-	3583						
0.45	4300	40000	-	3108*						
0.51	4300	40000	-	2757						
 3  2										
0.58	4300	40000	-	2419						
0.66	4300	40000	-	2123						
0.75	4300	40000	-	1856						
0.86	4300	40000	-	1625						
0.98	4300	40000	-	1430						
1.1	4300	40000	-	1261						
1.3	4300	40000	-	1102						
1.5	4300	40000	-	957						
1.6	4300	40000	-	855						
1.9	4300	40000	-	743						
2.1	4300	40000	-	652*						
2.4	4300	40000	-	573						
2.8	4300	40000	-	504						
3.2	4300	40000	-	437						
3.7	4300	40000	-	382*						
4.1	4300	40000	-	342*						
4.6	4300	40000	-	305						
5.4	4300	40000	-	258						
6.0	4300	40000	-	232						
7.0	4300	40000	-	199						

K107, n _e =1400 1/min										8000 Nm	
n _a rpm	M _{amax} Nm	F _{Ra} N	Φ _(/R) ,	i	DRN100LS DRN100L	DRN112M	DRN132S DRN132M	DRN132L DRN160M DRN160L	DRN180M DRN180L	DRN200L DRN225S DRN225M	DRN250M
 3											
9.8	8000	65000	5.7	143.47*							
12	8000	61500	5.7	121.46							
12	8000	59300	5.8	112.41*							
14	8000	56200	5.8	100.75							
15	8000	53500	5.8	90.96*							
17	8000	50900	5.8	82.61							
19	8000	47900	5.8	73.30							
21	8000	45400	5.8	66.52*							
24	8000	41700	5.8	57.17*							
28	7840	39300	5.8	49.90							
33	7360	37900	5.8	42.33*							
38	7200	35800	5.8	37.00*							
43	7200	33200	6.4	32.69							
45	6800	34200	5.9	31.28*							

K107, n _e =1400 1/min											8000 Nm
n _a rpm	M _{amax} Nm	F _{Ra} N	Φ _(/R) °	i	DRN100LS DRN100L	DRN112M	DRN132S DRN132M	DRN132L DRN160M DRN160L	DRN180M DRN180L	DRN200L DRN225S DRN225M	DRN250M
48	7200	30700	6.5	29.00							
53	7200	28800	6.4	26.32							
62	7200	25800	6.5	22.62							
71	7200	23200	6.5	19.74							
84	7050	21000	6.5	16.75							
96	6890	19500	6.6	14.64							
104	4300	29200	8.8	13.43							
119	4300	27500	8.8	11.73							
141	4190	25800	8.9	9.94							
161	4070	24600	9	8.69							
190	3600	24400	9	7.35							

K107R77, n _e =1400 1/min											8000 Nm
n _a rpm	M _{amax} Nm	F _{Ra} N	φ _(/R) °	i	DR63S DR63M DR63L DRS71S DRS71M	DRN80M DRN90S	DRN90L	DRN100LS DRN100L	DRN112M	DRN132S DRN132M	DRN132L DRN160M DRN160L
 3  3											
0.10	8000	65000	-	14311*							
0.11	8000	65000	-	12211							
0.13	8000	65000	-	10677							
0.15	8000	65000	-	9524							
0.17	8000	65000	-	8328							
0.19	8000	65000	-	7270							
0.23	8000	65000	-	6184							
0.25	8000	65000	-	5662							
0.27	8000	65000	-	5138							
0.32	8000	65000	-	4359*							
0.37	8000	65000	-	3810*							
0.42	8000	65000	-	3358							
0.47	8000	65000	-	2977*							
0.54	8000	65000	-	2599							
0.61	8000	65000	-	2286							
0.72	8000	65000	-	1939							
 3  2											
0.82	8000	65000	-	1713							
0.90	8000	65000	-	1554							
1.0	8000	65000	-	1336*							
1.2	8000	65000	-	1166							
1.4	8000	65000	-	1030							
1.5	8000	65000	-	904							
1.8	8000	65000	-	793*							
2.0	8000	65000	-	696*							
2.3	8000	65000	-	615							
2.7	8000	65000	-	522							
3.0	8000	65000	-	461*							
3.4	8000	65000	-	408*							
3.8	8000	65000	-	364							
4.4	8000	65000	-	318							
4.9	8000	65000	-	286*							

K107R77, $n_e=1400$ 1/min											8000 Nm
n_a rpm	M_{amax} Nm	F_{Ra} N	$\Phi_{(R)}$ °	i	DR63S DR63M DR63L DRS71S DRS71M	DRN80M DRN90S	DRN90L	DRN100LS DRN100L	DRN112M	DRN132S DRN132M	DRN132L DRN160M DRN160L
5.6	8000	65000	-	251							
6.3	8000	65000	-	222*							
7.1	8000	65000	-	196*							
8.0	7200	65000	-	174							
9.1	7200	65000	-	154							
10	7200	65000	-	140							

K127, $n_e=1400$ 1/min											13000 Nm
n_a rpm	M_{amax} Nm	F_{Ra} N	$\Phi_{(R)}$ °	i	DRN132S DRN132M	DRN132L DRN160M DRN160L	DRN180M DRN180L	DRN200L DRN225S DRN225M	DRN250M DRN280S DRN280M		
 3											
9.6	13000	79200	5.2	146.07							
10	13000	79200	5.2	136.14							
11	13000	79200	5.2	122.48							
13	13000	79200	5.2	110.18							
16	13000	75100	5.2	89.89							
17	13000	72100	5.3	81.98							
20	13000	67700	5.3	70.95*							
22	13000	64000	5.3	62.60							
26	13000	59800	5.3	54.07							
29	13000	56500	5.3	47.82							
35	13000	52000	5.3	40.19							
39	13000	49400	5.6	36.25							
45	13000	45900	5.6	31.37							
51	13000	43000	5.7	27.68							
59	13000	39800	5.7	23.91							
66	13000	37200	5.7	21.15							
79	13000	32600	5.8	17.77							
98	12100	31000	5.8	14.35							
109	8530	35400	8	12.79							
130	8000	33900	8.1	10.74							
161	7230	32500	8.1	8.68							

K127R77, $n_e=1400$ 1/min											13000 Nm
n_a rpm	M_{amax} Nm	F_{Ra} N	$\Phi_{(R)}$ °	i	DR63S DR63M DR63L DRS71S DRS71M	DRN80M DRN90S	DRN90L	DRN100LS DRN100L	DRN112M	DRN132S DRN132M	DRN132L DRN160M DRN160L
 3  3											
0.08	13000	79200	-	17550							
0.09	13000	79200	-	16006							
0.09	13000	79200	-	14975							
0.11	13000	79200	-	12440							
0.13	13000	79200	-	10915							
0.14	13000	79200	-	9819							
0.17	13000	79200	-	8443							
0.19	13000	79200	-	7482							
0.21	13000	79200	-	6565							

K127R77, $n_e=1400$ 1/min											13000 Nm
n_a rpm	M_{amax} Nm	F_{Ra} N	$\Phi_{(R)}$ °	i	DR63S DR63M DR63L DRS71S DRS71M	DRN80M DRN90S	DRN90L	DRN100LS DRN100L	DRN112M	DRN132S DRN132M	DRN132L DRN160M DRN160L
0.24	13000	79200	-	5804							
0.28	13000	79200	-	5027							
0.32	13000	79200	-	4423							
0.36	13000	79200	-	3889							
0.42	13000	79200	-	3311							
0.47	13000	79200	-	3009							
0.54	13000	79200	-	2607							
0.62	13000	79200	-	2268							
 3  2											
0.73	13000	79200	-	1926							
0.80	13000	79200	-	1757							
0.91	13000	79200	-	1541							
1.0	13000	79200	-	1342							
1.2	13000	79200	-	1177							
1.4	13000	79200	-	1025							
1.6	13000	79200	-	899							
1.8	13000	79200	-	790							
2.0	13000	79200	-	704							
2.3	13000	79200	-	610							
2.6	13000	79200	-	549							
2.9	13000	79200	-	477							
3.3	13000	79200	-	418							

K127R87, n _e =1400 1/min										13000 Nm		
n _a rpm	M _{amax} Nm	F _{Ra} N	Φ _(/R) °	i	DRN80M DRN90S	DRN90L	DRN100LS DRN100L	DRN112M	DRN132S DRN132M	DRN132L DRN160M DRN160L	DRN180M DRN180L	DRN200L
 3 												
2.6	13000	79200	-	536								
3.0	13000	79200	-	473								
3.3	13000	79200	-	418								
3.8	13000	79200	-	367								
4.2	13000	79200	-	330								
4.9	13000	79200	-	287								
5.5	13000	79200	-	253								
6.6	13000	79200	-	213								
7.0	12000	79700	-	200								
8.4	12000	79700	-	166								
9.5	12000	79700	-	147								

K157, n _e =1400 1/min										18000 Nm
n _a rpm	M _{amax} Nm	F _{Ra} N	Φ _(/R) °	i	DRN132L DRN160M DRN160L	DRN180M DRN180L	DRN200L DRN225S DRN225M	DRN250M DRN280S DRN280M	DRN315S DRN315M	DRN315L DRN315H
 3										
9.3	18000	112200	5.2	150.41						
11	18000	106500	5.2	122.39						
14	18000	98000	5.2	100.22						
15	18000	94400	5.2	91.65						

K157, $n_e=1400$ 1/min										18000 Nm
n_a rpm	M_{amax} Nm	F_{Ra} N	$\Phi_{(R)}$ °	i	DRN132L DRN160M DRN160L	DRN180M DRN180L	DRN200L DRN225S DRN225M	DRN250M DRN280S DRN280M	DRN315S DRN315M	DRN315L DRN315H
18	18000	88900	5.2	79.75						
20	18000	84200	5.2	70.38						
23	18000	79000	5.2	61.02						
26	18000	74900	5.2	54.29						
30	18000	70000	5.2	46.79						
37	18000	63400	5.3	38.02						
45	18000	57500	5.6	31.30						
51	18000	54000	5.6	27.62						
58	18000	50000	5.6	23.95						
66	18000	47000	5.6	21.31						
76	18000	43200	5.7	18.37						
94	18000	38200	5.8	14.92						
111	17000	36600	5.8	12.65						

K157R97, n _e =1400 1/min											18000 Nm		
n _a rpm	M _{amax} Nm	F _{Ra} N	Φ _(/R) °	i	DRS71M	DRN80M DRN90S	DRN90L	DRN100LS DRN100L	DRN112M	DRN132S DRN132M	DRN132L DRN160M DRN160L	DRN180M DRN180L	DRN200L DRN225S
3 3													
0.08	18000	112200	-	17679									
0.09	18000	112200	-	15729									
0.10	18000	112200	-	14721									
0.11	18000	112200	-	13097									
0.12	18000	112200	-	11368									
0.14	18000	112200	-	10114									
0.16	18000	112200	-	8718									
0.18	18000	112200	-	7734									
0.20	18000	112200	-	6881									
0.24	18000	112200	-	5931									
0.28	18000	112200	-	5074									
0.31	18000	112200	-	4514									
0.35	18000	112200	-	3979									
0.40	18000	112200	-	3516									
0.46	18000	112200	-	3051									
0.54	18000	112200	-	2610									
0.60	18000	112200	-	2322									
0.69	18000	112200	-	2029									
0.78	18000	112200	-	1805									
3 2													
0.84	18000	112200	-	1659									
1.0	18000	112200	-	1365									
1.1	18000	112200	-	1229*									
1.3	18000	112200	-	1093*									
1.5	18000	112200	-	942									
1.6	18000	112200	-	854									
1.9	18000	112200	-	756*									
2.1	18000	112200	-	661									
2.5	18000	112200	-	567									
2.8	18000	112200	-	504									
3.2	18000	112200	-	434*									
3.7	18000	112200	-	379									

K157R97, $n_e=1400$ 1/min**18000 Nm**

n_a rpm	M_{amax} Nm	F_{Ra} N	$\Phi_{(R)}$ °	i	DRS71M	DRN80M DRN90S	DRN90L	DRN100LS DRN100L	DRN112M	DRN132S DRN132M	DRN132L DRN160M DRN160L	DRN180M DRN180L	DRN200L DRN225S
4.2	18000	112200	-	333									
4.8	18000	112200	-	291									

K157R107, $n_e=1400$ 1/min**18000 Nm**

n_a rpm	M_{amax} Nm	F_{Ra} N	$\Phi_{(R)}$ °	i	DRN100LS DRN100L	DRN112M	DRN132S DRN132M	DRN132L DRN160M DRN160L	DRN180M DRN180L	DRN200L DRN225S DRN225M
 3  2										
3.6	18000	112200	-	385						
4.3	18000	112200	-	325						
4.7	18000	112200	-	299						
5.5	18000	112200	-	253						
6.1	18000	112200	-	230						
6.6	18000	112200	-	213						
7.5	18000	112200	-	187						
8.9	18000	112200	-	157						
11	18000	106500	-	122						
13	18000	100700	-	107						

K167, $n_e=1400$ 1/min**32000 Nm**

n_a rpm	M_{amax} Nm	F_{Ra} N	$\Phi_{(R)}$ °	i	DRN132L DRN160M DRN160L	DRN180M DRN180L	DRN200L DRN225S DRN225M	DRN250M DRN280S DRN280M	DRN315S DRN315M	DRN315L DRN315H
 3										
8.5	32000	150000	4.5	164.50						
10	32000	150000	4.5	134.99						
13	32000	150000	4.5	109.83						
16	32000	147200	4.5	87.86						
18	32000	140100	4.5	78.14						
21	32000	132000	4.5	68.07						
23	32000	125600	4.5	60.74						
27	32000	117000	4.6	51.77						
33	32000	107400	4.6	42.89						
38	32000	99700	4.6	36.61						
43	32000	93700	4.8	32.25						
49	32000	88600	4.8	28.77						
57	32000	81700	4.9	24.52						
69	32000	74000	4.9	20.32						
81	32000	67900	5	17.34						

K167R97, $n_e=1400$ 1/min**32000 Nm**

n_a rpm	M_{amax} Nm	F_{Ra} N	$\Phi_{(R)}$ °	i	DRS71M	DRN80M DRN90S	DRN90L	DRN100LS DRN100L	DRN112M	DRN132S DRN132M	DRN132L DRN160M DRN160L	DRN180M DRN180L	DRN200L DRN225S
 3  3													
0.07	32000	150000	-	19723									
0.08	32000	150000	-	17406									
0.09	32000	150000	-	15000									
0.11	32000	150000	-	13238									
0.12	32000	150000	-	11573									
0.14	32000	150000	-	10264									

K167R97, $n_e=1400$ 1/min										32000 Nm			
n_a rpm	M_{amax} Nm	F_{Ra} N	$\Phi_{(R)}$ '	i	DRS71M	DRN80M DRN90S	DRN90L	DRN100LS DRN100L	DRN112M	DRN132S DRN132M	DRN132L DRN160M DRN160L	DRN180M DRN180L	DRN200L DRN225S
0.16	32000	150000	-	8628									
0.21	32000	150000	-	6562									
0.26	32000	150000	-	5355									
0.29	32000	150000	-	4788									
0.34	32000	150000	-	4079									
0.41	32000	150000	-	3376									
0.51	32000	150000	-	2755									
0.62	32000	150000	-	2263									
 3 													
0.64	32000	150000	-	2182									
0.82	32000	150000	-	1704									
0.99	32000	150000	-	1408									
1.1	32000	150000	-	1296									
1.3	32000	150000	-	1101									
1.5	32000	150000	-	944									
1.7	32000	150000	-	843									
1.8	32000	150000	-	757									
2.2	32000	150000	-	632									
2.5	32000	150000	-	561									
2.9	32000	150000	-	481									
3.3	32000	150000	-	423									
3.8	32000	150000	-	369									

10

K167R107, n _e =1400 1/min										32000 Nm
n _a rpm	M _{amax} Nm	F _{Ra} N	φ _(/R) '	i	DRN100LS DRN100L	DRN112M	DRN132S DRN132M	DRN132L DRN160M DRN160L	DRN180M DRN180L	DRN200L DRN225S DRN225M
 3 										
4.4	32000	150000	-	318						
5.0	32000	150000	-	278						
5.7	32000	150000	-	244						
6.6	32000	150000	-	213						
6.8	32000	150000	-	206						
7.8	32000	150000	-	180						
8.8	32000	150000	-	160						
10	32000	150000	-	135						
12	32000	150000	-	118						

K187, n _e =1400 1/min										50000 Nm
n _a rpm	M _{amax} Nm	F _{Ra} N	Φ _(/R) '	i	DRN132L DRN160M DRN160L	DRN180M DRN180L	DRN200L DRN225S DRN225M	DRN250M DRN280S DRN280M	DRN315S DRN315M	DRN315L DRN315H
 3										
7.8	50000	190000	3.8	179.86						
8.5	50000	190000	3.8	165.21						
9.7	50000	186200	3.8	144.59						
11	50000	177700	3.8	129.69						
12	50000	167100	3.8	112.60						
14	50000	160100	3.8	102.16						
16	50000	149700	3.8	88.00						


21933170/DE – 11/2015

K187, $n_e=1400$ 1/min										50000 Nm
n_a rpm	M_{amax} Nm	F_{Ra} N	$\Phi_{(R)}$ °	i	DRN132L DRN160M DRN160L	DRN180M DRN180L	DRN200L DRN225S DRN225M	DRN250M DRN280S DRN280M	DRN315S DRN315M	DRN315L DRN315H
19	50000	138100	3.8	73.96						
22	50000	129000	3.8	64.04						
26	50000	118100	3.9	53.36						
31	50000	108900	3.9	45.50*						
33	50000	105200	4.1	42.51						
36	50000	99900	4.1	38.57						
42	50000	92200	4.2	33.23						
50	50000	83500	4.2	27.92						
58	47600	80500	4.2	24.18						
69	43900	78000	4.3	20.15						
81	41400	75000	4.3	17.18						


K187R97, n _e =1400 1/min													50000 Nm	
n _a rpm	M _{amax} Nm	F _{Ra} N	Φ _(/R) '	i	DRS71M	DRN80M DRN90S	DRN90L	DRN100LS DRN100L	DRN112M	DRN132S DRN132M	DRN132L DRN160M DRN160L	DRN180M DRN180L	DRN200L DRN225S	
 3  3														
0.04	50000	190000	-	32625										
0.05	50000	190000	-	27165										
0.06	50000	190000	-	24353										
0.07	50000	190000	-	19144										
0.08	50000	190000	-	16978										
0.10	50000	190000	-	14272										
0.11	50000	190000	-	13116										
0.12	50000	190000	-	11647										
0.13	50000	190000	-	10413										
0.15	50000	190000	-	9363										
0.17	50000	190000	-	8126										
0.19	50000	190000	-	7343										
0.21	50000	190000	-	6747										
0.23	50000	190000	-	5991										
0.26	50000	190000	-	5358										
0.29	50000	190000	-	4817										
0.32	50000	190000	-	4370										
0.50	50000	190000	-	2818*										
 3  2														
0.39	50000	190000	-	3609										
0.46	50000	190000	-	3062										
0.56	50000	190000	-	2519										
0.62	50000	190000	-	2268										
0.68	50000	190000	-	2054										
0.77	50000	190000	-	1821										
0.87	50000	190000	-	1605										
1.0	50000	190000	-	1395										
1.2	50000	190000	-	1196										
1.3	50000	190000	-	1046										
1.5	50000	190000	-	945										
1.9	50000	190000	-	738										
2.3	50000	190000	-	621										
2.7	50000	190000	-	527										


K187R107, n_e=1400 1/min					50000 Nm					
n_a rpm	M_{amax} Nm	F_{Ra} N	φ_(R) °	i	DRN100LS DRN100L	DRN112M	DRN132S DRN132M	DRN132L DRN160M DRN160L	DRN180M DRN180L	DRN200L DRN225S DRN225M
 3  2										
1.7	50000	190000	-	835						
1.9	50000	190000	-	729						
2.3	50000	190000	-	622						
2.7	50000	190000	-	520						
3.1	50000	190000	-	454						
3.9	50000	190000	-	355						
5.4	50000	190000	-	261						
6.3	50000	190000	-	221						
7.3	50000	190000	-	193						
8.6	50000	190000	-	163						

10.3 Auswahltabellen K..DRN.. in kW


P _m = 0.12 kW										
n _a rpm	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
0.08	10800	17550	80300	1.20						
0.09	9890	16006	80700	1.30						
0.09	9260	14975	81000	1.40						
0.11	7690	12440	81600	1.70						
0.13	6750	10915	81900	1.95						
0.14	6070	9819	82000	2.1						
0.16	5180	8443	82300	2.5						
0.18	4620	7482	82400	2.8						
0.10	8850	14311	65000	0.90						
0.11	7550	12211	65000	1.05						
0.13	6600	10677	65000	1.20						
0.14	5890	9524	65000	1.35						
0.17	5150	8328	65000	1.55						
0.19	4490	7270	65000	1.80						
0.22	3700	6184	65000	2.2						
0.24	3210	5662	65000	2.5						
0.27	2910	5138	65000	2.7						
0.32	2670	4359	65000	3.0						
0.17	5460	8054	39400	0.80						
0.20	4420	6970	40000	0.95						
0.23	4000	6027	40000	1.05						
0.26	3650	5391	40000	1.20						
0.30	3020	4669	40000	1.40						
0.34	2730	4082	40000	1.55						
0.39	2370	3583	40000	1.80						
0.44	2090	3108	40000	2.0						
0.50	1770	2757	40000	2.4						
0.57	1650	2419	40000	2.6						
0.65	1420	2123	40000	3.0						
0.74	1270	1856	40000	3.4						
0.85	1040	1625	40000	4.1						
0.96	890	1430	40000	4.8						
1.1	860	1261	40000	5.0						
1.2	755	1102	40000	5.7						
0.26	3470	5240	26200	0.80						
0.30	2890	4562	27000	0.95						
0.34	2680	4037	27300	1.00						
0.38	2390	3609	27600	1.15						
0.44	2060	3107	28000	1.30						
0.51	1730	2728	28300	1.55						
0.58	1530	2371	28400	1.75						
0.66	1430	2088	28500	1.90						
0.74	1270	1854	28600	2.1						
0.83	1130	1657	28700	2.4						
0.97	960	1415	28800	2.8						
1.1	830	1229	28900	3.2						
1.3	720	1078	28900	3.7						
1.4	610	951	29000	4.4						
1.6	520	837	29000	5.2						
1.9	450	726	29000	5.9						
0.51	1840	2717	11500	0.85	K	77R37	DR	63S4	69	631
0.58	1530	2370	15500	1.00	KF	77R37	DR	63S4	78	631
					KA	77R37	DR	63S4	62	631
					KAF	77R37	DR	63S4	70	631

P_m = 0.12 kW

n _a rpm	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
0.67	1430	2050	16100	1.10	K KF KA KAF	77R37	DR	63S4	69	631
0.78	1220	1772	17300	1.25						
0.91	1040	1514	18100	1.50						
0.99	960	1388	18500	1.60						
1.1	840	1218	18900	1.85						
1.3	735	1053	19200	2.1						
1.5	645	924	19400	2.4						
1.7	570	815	19600	2.7						
2.0	445	709	19800	3.5	K KF KA KAF	67R37	DR	63S4	45	631
2.2	390	622	19900	3.9						
1.0	960	1351	6940	0.85						
1.2	820	1171	10300	1.00						
1.3	720	1034	11100	1.15						
1.5	600	903	11900	1.35						
1.7	570	793	12100	1.45						
2.0	455	697	12600	1.80						
2.2	400	613	12800	2.0						
2.6	350	542	13000	2.3						
2.9	325	471	13000	2.5						
3.3	270	420	13000	3.0						
3.8	245	361	13000	3.3						
4.3	215	323	13000	3.8						
5.0	181	279	13000	4.5						
5.6	159	246	13000	5.2						
6.4	139	217	13000	5.9						
1.5	605	906	7580	1.00	K KF KA KAF	57R37	DR	63S4	39	631
1.7	545	806	8060	1.10						
2.0	455	699	8620	1.30						
2.2	400	615	8870	1.50						
2.5	350	544	9080	1.70						
2.9	320	473	9190	1.85						
3.3	270	421	9390	2.2						
3.8	245	362	9470	2.4						
4.3	215	319	9570	2.8						
4.9	181	280	9690	3.3						
5.6	160	246	9760	3.8						
6.4	141	215	9810	4.3						
7.2	126	192	9850	4.8	K KF KA KAF	49R37	DR	63S4	43	631
1.5	615	908	9000	0.80						
1.7	545	802	9000	0.90						
2.0	460	701	9000	1.10						
2.1	445	645	9000	1.10						
2.3	385	595	9000	1.30						
2.5	360	543	9000	1.35						
2.8	315	501	9000	1.60						
3.1	285	449	9000	1.75						
3.4	245	401	9000	2.0						
3.8	225	360	9000	2.2						
4.2	205	330	9000	2.4						
4.6	197	300	9000	2.5						
5.0	172	274	9000	2.9						
5.7	149	243	9000	3.3						
6.4	138	217	9000	3.6						
7.2	130	193	9000	3.9	K KF KA KAF	47R37	DR	63S4	33	631
2.5	380	552	6170	1.05						
2.8	320	495	6840	1.25						
3.2	285	426	7160	1.40						
3.7	240	375	7510	1.65						
4.2	225	327	7620	1.75	K KF KA KAF	47R37	DR	63S4	32	631
4.8	198	289	7780	2.0						


P _m = 0.12 kW																
n _a rpm	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg							
2.7	330	504	7500	0.90	K KF KA KAF	39R17	DR	63S4	24	631						
3.0	315	454	7500	0.95												
3.5	265	399	7500	1.10												
3.8	250	365	7500	1.20												
4.4	205	312	7500	1.45												
4.6	200	299	7500	1.50												
5.4	172	254	7500	1.75												
5.9	154	234	7500	1.95												
6.6	140	210	7500	2.1												
7.3	128	189	7500	2.3												
7.9	120	174	7500	2.5												
8.8	104	156	7500	2.9												
9.7	96	142	7500	3.1												
12	78	117	7500	3.8												
4.0	240	346	3540	0.80	K KF KA KAF	37R17	DR	63S4	19	631						
4.5	205	304	5570	0.95												
5.2	189	267	5760	1.05												
5.9	163	234	6010	1.20												
6.7	142	205	6180	1.40												
7.6	124	181	6300	1.60												
8.6	109	160	6400	1.85												
10	91	136	6490	2.2												
6.2	184	144.79*	13000	4.4	K	67	DR	63M6	34	585						
					KF	67	DR	63M6	40	586						
					KA	67	DR	63M6	31	587						
					KAF	67	DR	63M6	37	586						
6.2	185	145.14*	9680	3.2	K KF KA KAF	57	DR	63M6	28	579						
7.3	158	123.85	9760	3.8												
8.3	138	108.29	9820	4.4												
8.8	131	102.88*	9840	4.6												
10.0	115	90.26*	9880	5.2												
12	98	76.56*	9930	6.2												
9.5	120	145.14*	9870	5.0	K KF KA KAF	57	DR	63S4	28	579						
11	103	123.85	9920	5.8												
13	90	108.29	9950	6.7												
13	85	102.88*	9960	7.0												
15	75	90.26*	9990	8.0												
6.8	168	131.87*	7930	2.4	K KF KA KAF	47	DR	63M6	22	569						
7.4	155	121.48*	7990	2.6												
8.6	133	104.37	8070	3.0							KA	47	DR	63M6	22	571
											KAF	47	DR	63M6	24	570
10	110	131.87*	8140	3.6	K	47	DR	63S4	22	569						
					KF	47	DR	63S4	26	570						
					KA	47	DR	63S4	22	571						
					KAF	47	DR	63S4	24	570						
8.5	136	106.38	6230	1.50	K KF KA KAF	37	DR	63M6	16	559						
9.2	124	97.81	6300	1.60												
11	107	83.69	6410	1.90												
12	92	72.54	6480	2.2												
13	88	106.38	6500	2.3	K KF KA KAF	37	DR	63S4	16	559						
14	81	97.81	6530	2.5												
16	70	83.69	6570	2.9												
19	60	72.54	6600	3.3												
20	56	67.80	6610	3.6							KA	37	DR	63S4	16	561
											KAF	37	DR	63S4	17	560
19	60	71.93	5190	2.2	K KF KA KAF	29	DR	63S4	10	552						
21	55	66.25	5200	2.4												
23	51	61.28	5210	2.6												
25	46	54.89	5230	2.8												
27	42	50.35	5240	3.1												
32	36	42.87	5260	3.6												

P_m = 0.12 kW

n _a rpm	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
24	49	58.68	4460	1.45						
26	45	53.88	4480	1.55						
28	41	49.69	4500	1.70						
31	37	44.48	4500	1.85						
34	34	40.63	4500	2.00						
40	28	34.29	4500	2.2						
43	26	31.74	4500	3.0						
47	24	29.29	4500	2.5						
47	24	29.14	4500	3.3	K	19	DR	63S4	8.5	546
51	23	27.16	4500	2.7	KF	19	DR	63S4	8.8	549
51	22	26.88	4500	3.6	KA	19	DR	63S4	8.0	551
57	20	24.06	4460	4.0	KAF	19	DR	63S4	8.4	549
63	18	21.98	4340	4.4						
74	15	18.55	4120	5.2						
87	13	15.84	3920	6.1						
94	12	14.69	3830	6.6						
109	11	12.70	3660	7.6						
117	9.8	11.84	3580	8.0						
134	8.6	10.32	3430	8.9						
144	8.0	9.58	3370	7.9						


10

P_m = 0.18 kW


n _a rpm	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
0.09	15700	14975	74400	0.80						
0.11	13100	12440	79100	1.00						
0.12	11500	10915	80000	1.15						
0.13	10300	9819	80500	1.25						
0.16	8870	8443	81100	1.45	K	127R77	DR	63M4	470	631
0.18	7880	7482	81500	1.65	KF	127R77	DR	63M4	510	631
0.20	6910	6565	81800	1.90	KA	127R77	DR	63M4	440	631
0.23	5880	5804	82100	2.2	KAF	127R77	DR	63M4	480	631
0.26	5210	5027	82300	2.5						
0.30	4480	4423	82400	2.9						
0.34	3900	3889	82500	3.3						
0.40	3240	3311	82600	4.0						
0.16	8770	8328	65000	0.90						
0.18	7660	7270	65000	1.05						
0.21	6410	6184	65000	1.25						
0.23	5690	5662	65000	1.40						
0.26	5160	5138	65000	1.55	K	107R77	DR	63M4	310	631
0.30	4580	4359	65000	1.75	KF	107R77	DR	63M4	320	631
0.35	4000	3810	65000	2.0	KA	107R77	DR	63M4	280	631
0.39	3400	3358	65000	2.4	KAF	107R77	DR	63M4	305	631
0.44	3080	2977	65000	2.6						
0.51	2690	2599	65000	3.0						
0.58	2310	2286	65000	3.4						
0.28	5050	4669	39800	0.85	K	97R57	DR	63M4	180	631
0.32	4530	4082	40000	0.95	KF	97R57	DR	63M4	200	631
0.37	3940	3583	40000	1.10	KA	97R57	DR	63M4	160	631
0.42	3450	3108	40000	1.25	KAF	97R57	DR	63M4	185	631
0.48	2980	2757	40000	1.45						
0.55	2720	2419	40000	1.60						
0.62	2360	2123	40000	1.80						
0.71	2090	1856	40000	2.1						
0.81	1760	1625	40000	2.4						
0.92	1520	1430	40000	2.8	K	97R57	DR	63M4	180	631
1.0	1420	1261	40000	3.0	KF	97R57	DR	63M4	200	631
1.2	1240	1102	40000	3.5	KA	97R57	DR	63M4	160	631
1.4	1080	957	40000	4.0	KAF	97R57	DR	63M4	185	631
1.5	970	855	40000	4.4						
1.8	770	743	40000	5.6						
2.0	690	652	40000	6.2						

21933170/DE – 11/2015


P_m = 0.18 kW

n_a rpm	M_a Nm	i	F_{Ra}¹⁾ N	SEW f_B					m kg	
0.42	3430	3107	26200	0.80	K	87R57	DR	63M4	120	631
0.48	2920	2728	27000	0.90	KF	87R57	DR	63M4	130	631
0.56	2560	2371	27400	1.05	KA	87R57	DR	63M4	105	631
					KAF	87R57	DR	63M4	120	631
0.63	2350	2088	27700	1.15	K	87R57	DR	63M4	120	631
0.71	2080	1854	28000	1.30		87R57	DR	63M4	125	631
0.80	1860	1657	28200	1.45		87R57	DR	63M4	105	631
0.93	1590	1415	28400	1.70		87R57	DR	63M4	120	631
1.1	1380	1229	28600	1.95		87R57	DR	63M4	125	631
1.2	1200	1078	28700	2.2		87R57	DR	63M4	105	631
1.4	1030	951	28800	2.6		87R57	DR	63M4	120	631
1.6	890	837	28800	3.0		87R57	DR	63M4	120	631
1.8	775	726	28900	3.5		87R57	DR	63M4	120	631
0.87	1710	1514	14100	0.90	K	77R37	DR	63M4	69	631
0.95	1570	1388	15200	1.00						
1.1	1380	1218	16500	1.10						
1.2	1200	1053	17400	1.30						
1.4	1050	924	18100	1.45						
1.6	930	815	18600	1.65						
1.9	760	709	19100	2.0						
2.1	665	622	19300	2.3						
2.4	600	552	19500	2.6						
2.7	525	485	19600	2.9						
3.1	465	428	19800	3.3						
3.6	410	367	19800	3.8						
1.7	920	793	9240	0.90	K	67R37	DR	63M4	45	631
1.9	760	697	10800	1.05						
2.2	670	613	11500	1.20						
2.4	590	542	12000	1.40						
2.8	535	471	12200	1.50						
3.2	455	420	12600	1.80						
3.6	405	361	12800	2.0						
4.1	360	323	12900	2.3						
4.7	300	279	13000	2.7						
2.4	590	544	7690	1.00	K	57R37	DR	63M4	39	631
2.8	535	473	8150	1.10						
3.1	455	421	8620	1.30						
3.6	405	362	8840	1.45						
4.1	360	319	9050	1.65						
4.7	300	280	9270	1.95						
5.4	265	246	9400	2.2						
6.1	235	215	9510	2.5						
6.9	210	192	9600	2.8						
7.9	182	166	9690	3.3						
2.4	595	543	9000	0.85	K	49R37	DR	63M4	43	631
2.6	530	501	9000	0.95						
2.9	475	449	9000	1.05						
3.3	415	401	9000	1.20						
3.7	380	360	9000	1.30						
4.0	345	330	9000	1.45						
4.4	325	300	9000	1.55						
4.8	285	274	9000	1.70						
5.4	250	243	9000	1.95						
6.1	230	217	9000	2.2						
6.8	210	193	9000	2.4						
7.5	190	176	9000	2.6						
8.7	158	152	9000	3.2						
11	133	125	9000	3.8						
3.5	405	375	5600	1.00						
4.0	365	327	6320	1.10						
4.6	325	289	6800	1.20						
5.2	275	256	7240	1.45						
5.9	250	225	7450	1.60						
6.7	215	198	7680	1.85						
7.7	188	171	7840	2.1						
8.6	168	153	7930	2.4						
10	147	131	8020	2.7						
3.5	405	375	5600	1.00	K	47R37	DR	63M4	33	631
4.0	365	327	6320	1.10						
4.6	325	289	6800	1.20						
5.2	275	256	7240	1.45						
5.9	250	225	7450	1.60						
6.7	215	198	7680	1.85						
7.7	188	171	7840	2.1						
8.6	168	153	7930	2.4						
10	147	131	8020	2.7						


P_m = 0.18 kW

n _a rpm	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
4.2	335	312	7500	0.90	K KF KA KAF	39R17	DR	63M4	24	631
4.4	325	299	7500	0.90						
5.2	280	254	7500	1.05						
5.6	250	234	7500	1.20						
6.3	225	210	7500	1.30						
7.0	205	189	7500	1.45						
7.6	195	174	7500	1.55						
8.4	171	156	7500	1.75						
9.3	157	142	7500	1.90						
11	128	117	7500	2.3						
18	81	75	7500	3.6	K KF KA KAF	37R17	DR	63M4	19	631
6.4	230	205	4860	0.85						
7.3	200	181	5590	1.00						
8.2	180	160	5860	1.10						
9.7	151	136	6110	1.35						
10	145	127	6160	1.40	K KF KA KAF	67	DR	63L6	35	585
6.0	285	144.79*	13000	2.9						
7.0	240	123.54	13000	3.4						
8.0	210	108.03	13000	3.8						
8.5	200	102.62	13000	4.0	K KF KA KAF	67	DR	63M4	34	585
9.1	188	144.79*	13000	4.4						
11	161	123.54	13000	5.1						
12	141	108.03	13000	5.8						
6.0	285	145.14*	9340	2.1	K KF KA KAF	57	DR	63L6	29	579
7.0	240	123.85	9480	2.4						
8.0	210	108.29	9590	2.8						
8.5	200	102.88*	9620	3.0						
9.6	178	90.26*	9700	3.4	K KF KA KAF	57	DR	63M4	28	579
11	161	123.85	9750	3.7						
12	141	108.29	9810	4.3						
13	134	102.88*	9830	4.5						
15	118	90.26*	9880	5.1						
17	100	76.56*	9920	6.0	K KF KA KAF	47	DR	63L6	23	569
6.6	260	131.87*	7380	1.55						
7.2	240	121.48*	7530	1.65						
8.3	205	104.37	7740	1.95						
9.6	180	90.86	7880	2.2						
10	168	85.12*	7930	2.4	K KF KA KAF	47	DR	63M4	22	569
10	172	131.87*	7910	2.3						
11	158	121.48*	7970	2.5						
13	136	104.37	8060	2.9						
15	118	90.86	8120	3.4						
16	111	85.12*	8140	3.6	K KF KA KAF	37	DR	63L6	17	559
8.2	210	106.38	5520	0.95						
8.9	193	97.81	5710	1.05						
10	165	83.69	5990	1.20						
12	143	72.54	6170	1.40	K KF KA KAF	37	DR	63M4	16	559
12	138	106.38	6210	1.45						
14	127	97.81	6280	1.55						
16	109	83.69	6400	1.85						
18	94	72.54	6470	2.1						
19	88	67.80	6500	2.3						
23	76	58.60	6280	2.6						
27	65	49.79	6010	3.1						
30	58	44.46	5830	3.4	K KF KA KAF	37	DR	63M4	18	560
35	49	37.97	5580	4.0						


P_m = 0.18 kW


n _a rpm	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
18	94	71.93	5090	1.40						
20	86	66.25	5110	1.50						
22	80	61.28	5130	1.65						
24	71	54.89	5160	1.80						
26	66	50.35	5170	2.00						
31	56	42.87	5200	2.3	K	29	DR	63M4	10	552
34	51	38.90	5220	2.6	KF	29	DR	63M4	11	556
36	48	36.96	5220	2.5	KA	29	DR	63M4	9.8	558
37	47	35.83	5230	2.8	KAF	29	DR	63M4	11	556
40	43	33.15	5240	3.0						
44	39	30.11	5110	2.9						
44	39	29.69	5130	3.4						
48	35	27.23	5010	3.7						
53	32	24.91	4840	3.4						
22	76	58.68	4280	0.90						
24	70	53.88	4330	1.00						
27	65	49.69	4360	1.10						
30	58	44.48	4410	1.20						
32	53	40.63	4440	1.25						
38	45	34.29	4480	1.45						
42	41	31.74	4500	1.95						
45	38	29.29	4500	1.60						
45	38	29.14	4500	2.1						
49	35	27.16	4490	1.70	K	19	DR	63M4	8.5	546
49	35	26.88	4500	2.3	KF	19	DR	63M4	8.8	549
55	31	24.06	4410	2.6	KA	19	DR	63M4	8.0	551
60	29	21.98	4300	2.8	KAF	19	DR	63M4	8.4	549
71	24	18.55	4090	3.3						
83	21	15.84	3900	3.9						
90	19	14.69	3820	4.2						
104	17	12.70	3650	4.8						
111	15	11.84	3580	5.1						
128	13	10.32	3430	5.7						
138	12	9.58	3380	5.0						
163	11	8.09	3200	7.6						
191	9.0	6.91	3050	8.9						

P_m = 0.25 kW


n _a rpm	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
0.13	15100	9819	75600	0.85						
0.15	13000	8443	79200	1.00						
0.17	11500	7482	79900	1.10						
0.20	10100	6565	80600	1.30	K	127R77	DR	63L4	470	631
0.22	8750	5804	81200	1.50	KF	127R77	DR	63L4	510	631
0.26	7690	5027	81600	1.70	KA	127R77	DR	63L4	440	631
0.29	6660	4423	81900	1.95	KAF	127R77	DR	63L4	480	631
0.33	5820	3889	82100	2.2						
0.39	4870	3311	82300	2.7						
0.21	9460	6184	65000	0.85						
0.23	8480	5662	65000	0.95						
0.25	7690	5138	65000	1.05						
0.30	6730	4359	65000	1.20	K	107R77	DR	63L4	310	631
0.34	5880	3810	65000	1.35	KF	107R77	DR	63L4	320	631
0.39	5060	3358	65000	1.60	KA	107R77	DR	63L4	285	631
0.44	4550	2977	65000	1.75	KAF	107R77	DR	63L4	305	631
0.50	3970	2599	65000	2.0						
0.57	3440	2286	65000	2.3						
0.67	2920	1939	65000	2.7						
0.76	2670	1713	65000	3.0	K	107R77	DR	63L4	310	631
0.84	2430	1554	65000	3.3	KF	107R77	DR	63L4	320	631
0.97	2080	1336	65000	3.8	KA	107R77	DR	63L4	280	631
					KAF	107R77	DR	63L4	305	631


P_m = 0.25 kW

n_a rpm	M_a Nm	i	F_{Ra}¹⁾ N	SEW f_B					m kg	
0.42	4980	3108	39900	0.85	K	97R57	DR	63L4	180	631
0.47	4350	2757	40000	1.00	KF	97R57	DR	63L4	200	631
					KA	97R57	DR	63L4	160	631
					KAF	97R57	DR	63L4	185	631
0.54	3920	2419	40000	1.10	K	97R57	DR	63L4	180	631
0.61	3420	2123	40000	1.25		97R57	DR	63L4	200	631
0.70	3010	1856	40000	1.40		97R57	DR	63L4	160	631
0.80	2570	1625	40000	1.65		97R57	DR	63L4	185	631
0.91	2240	1430	40000	1.90		97R57	DR	63L4		
1.0	2050	1261	40000	2.1		97R57	DR	63L4		
1.2	1790	1102	40000	2.4		97R57	DR	63L4		
1.4	1560	957	40000	2.7	KF	97R57	DR	63L4	120	631
1.5	1400	855	40000	3.1		97R57	DR	63L4	125	631
0.62	3390	2088	26300	0.80		87R57	DR	63L4	105	631
0.70	3010	1854	26900	0.90		87R57	DR	63L4	120	631
0.78	2690	1657	27300	1.00		87R57	DR	63L4		
0.92	2290	1415	27800	1.15		87R57	DR	63L4		
1.1	1990	1229	28100	1.35		87R57	DR	63L4		
1.2	1730	1078	28300	1.55	KA	87R57	DR	63L4		
1.4	1500	951	28500	1.80		87R57	DR	63L4		
1.6	1310	837	28600	2.1		87R57	DR	63L4		
1.8	1130	726	28700	2.4		87R57	DR	63L4		
2.0	1010	638	28800	2.7		87R57	DR	63L4		
1.2	1720	1053	14000	0.90		77R37	DR	63L4	70	631
1.4	1510	924	15600	1.00	KF	77R37	DR	63L4	78	631
1.6	1330	815	16700	1.15		77R37	DR	63L4	62	631
1.8	1110	709	17800	1.40		77R37	DR	63L4	70	631
2.1	970	622	18400	1.60		77R37	DR	63L4		
2.4	870	552	18700	1.75		77R37	DR	63L4		
2.7	765	485	19100	2.0		77R37	DR	63L4		
3.0	675	428	19300	2.3	KA	77R37	DR	63L4		
3.5	590	367	19500	2.6		77R37	DR	63L4		
4.0	525	328	19600	2.9		77R37	DR	63L4		
4.5	465	290	19700	3.3		77R37	DR	63L4		
5.2	400	252	19900	3.8		77R37	DR	63L4		
5.9	350	221	19900	4.4		77R37	DR	63L4		
6.7	310	195	20000	5.0	KAF	77R37	DR	63L4		
7.4	270	175	20000	5.6		77R37	DR	63L4		
2.1	970	613	5680	0.85		67R37	DR	63L4	46	631
2.4	860	542	9920	0.95	KF	67R37	DR	63L4	51	631
2.8	775	471	10700	1.05		67R37	DR	63L4	43	631
3.1	665	420	11500	1.25		67R37	DR	63L4	49	631
3.6	590	361	11900	1.40		67R37	DR	63L4		
4.0	520	323	12300	1.55		67R37	DR	63L4		
4.7	440	279	12600	1.85		67R37	DR	63L4		
5.3	390	246	12800	2.1	KA	67R37	DR	63L4		
6.0	345	217	13000	2.4		67R37	DR	63L4		
3.1	665	421	4200	0.90		57R37	DR	63L4	40	631
3.6	590	362	7690	1.00		57R37	DR	63L4	45	631
4.1	520	319	8260	1.15		57R37	DR	63L4	38	631
4.6	440	280	8680	1.35		57R37	DR	63L4	43	631
5.3	390	246	8920	1.55	KAF	57R37	DR	63L4		
6.0	345	215	9110	1.75		57R37	DR	63L4		
6.8	305	192	9260	1.95		57R37	DR	63L4		
7.8	265	166	9410	2.3		57R37	DR	63L4		
9.0	230	145	9530	2.6		57R37	DR	63L4		
10	210	129	9600	2.8		57R37	DR	63L4		
12	178	111	9700	3.4		57R37	DR	63L4		
13	156	97	9770	3.8		57R37	DR	63L4		


P _m = 0.25 kW										
n _a rpm	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
3.2	610	401	9000	0.80						
3.6	550	360	9000	0.90						
3.9	505	330	9000	1.00						
4.3	470	300	9000	1.05						
4.7	420	274	9000	1.20						
5.3	370	243	9000	1.35						
6.0	335	217	9000	1.50						
6.7	305	193	9000	1.65						
7.4	275	176	9000	1.80						
8.6	230	152	9000	2.2						
10	194	125	9000	2.6						
13	151	99	9000	3.3						
5.6	365	234	7500	0.80						
6.2	330	210	7500	0.90						
6.9	300	189	7500	1.00						
7.5	275	174	7500	1.10						
8.3	245	156	7500	1.20						
9.2	225	142	7500	1.35						
11	185	117	7500	1.60						
17	117	75	7500	2.5						
4.7	510	192.18	19700	2.8	K	77	DRS	71S6	62	591
5.0	475	179.37	19700	3.0	KF	77	DRS	71S6	71	592
5.8	410	154.02	19800	3.8	KA	77	DRS	71S6	55	593
6.6	360	135.28	19900	4.3	KAF	77	DRS	71S6	63	592
6.2	385	144.79*	12900	2.1	K	67	DRS	71S6	36	585
7.2	325	123.54	13000	2.5	KF	67	DRS	71S6	42	586
8.3	285	108.03	13000	2.8	KA	67	DRS	71S6	34	587
8.7	270	102.62	13000	3.0	KAF	67	DRS	71S6	39	586
9.0	265	144.79*	13000	3.1	K	67	DR	63L4	35	585
11	225	123.54	13000	3.6	KF	67	DR	63L4	40	586
12	198	108.03	13000	4.1	KA	67	DR	63L4	32	587
13	188	102.62	13000	4.4	KAF	67	DR	63L4	38	586
6.2	385	145.14*	8940	1.55						
7.2	330	123.85	9170	1.80						
8.3	285	108.29	9330	2.1						
8.7	270	102.88*	9380	2.2						
9.9	240	90.26*	9500	2.5						
12	200	76.56*	9620	2.9						
9.0	265	145.14*	9410	2.2						
10	225	123.85	9540	2.6						
12	199	108.29	9640	3.0						
13	189	102.88*	9670	3.2						
14	166	90.26*	9740	3.6						
17	141	76.56*	9810	4.3						
17	138	75.20	9000	3.4	K	49	DR	63L4	35	575
19	129	70.19	9000	3.4	KF	49	DR	63L4	37	576
					KA	49	DR	63L4	32	577
					KAF	49	DR	63L4	37	576
6.8	350	131.87*	6540	1.15	K	47	DRS	71S6	25	569
7.4	320	121.48*	6830	1.25	KF	47	DRS	71S6	28	570
8.6	275	104.37	7240	1.45	KA	47	DRS	71S6	24	571
					KAF	47	DRS	71S6	27	570
9.8	240	90.86	7510	1.65	K	47	DRS	71S6	25	569
11	225	85.12*	7610	1.75	KF	47	DRS	71S6	28	570
					KA	47	DRS	71S6	24	571
					KAF	47	DRS	71S6	27	570
9.9	240	131.87*	7510	1.65						
11	220	121.48*	7640	1.80						
12	192	104.37	7820	2.1						
14	167	90.86	7930	2.4						
15	156	85.12*	7980	2.6						
22	107	58.24	7500	2.8	K	39	DR	63L4	22	565
26	91	49.69	7500	3.3	KF	39	DR	63L4	23	566
					KA	39	DR	63L4	21	567
					KAF	39	DR	63L4	22	566

P_m = 0.25 kW

n _a rpm	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
11	220	83.69	5350	0.90	K	37	DRS	71S6	19	559
12	194	72.54	5710	1.05	KF	37	DRS	71S6	21	560
13	181	67.80	5840	1.10	KA	37	DRS	71S6	18	561
15	156	58.60	6070	1.30	KAF	37	DRS	71S6	20	560
18	133	49.79	6250	1.50						
12	195	106.38	5690	1.00						
13	180	97.81	5860	1.10						
16	154	83.69	6090	1.30						
18	133	72.54	6240	1.50						
19	124	67.80	6220	1.60	K	37	DR	63L4	17	559
22	108	58.60	6030	1.85	KF	37	DR	63L4	19	560
26	91	49.79	5810	2.2	KA	37	DR	63L4	16	561
29	82	44.46	5650	2.4	KAF	37	DR	63L4	18	560
34	70	37.97	5430	2.9						
37	65	35.57	5340	3.1						
43	55	29.96	5100	3.6						
45	53	28.83	5050	3.8						
18	132	71.93	4970	1.00						
20	122	66.25	5000	1.05						
21	113	61.28	5030	1.15						
24	101	54.89	5070	1.30						
26	92	50.35	5090	1.40						
30	79	42.87	5130	1.65						
33	71	38.90	5170	1.80	K	29	DR	63L4	11	552
35	68	36.96	5170	1.80	KF	29	DR	63L4	12	556
36	66	35.83	5180	2.00	KA	29	DR	63L4	10	558
39	61	33.15	5170	2.1	KAF	29	DR	63L4	11	556
43	55	30.11	4980	2.1						
44	55	29.69	5020	2.4						
48	50	27.23	4900	2.6						
52	46	24.91	4740	2.4						
56	43	23.19	4690	3.0						
59	41	22.08	4580	2.6						
65	37	19.99	4500	3.5						
29	82	44.48	4240	0.85						
32	75	40.63	4300	0.90						
38	63	34.29	4380	1.00						
41	58	31.74	4400	1.35						
44	54	29.29	4410	1.15						
45	54	29.14	4430	1.50						
48	50	27.16	4330	1.20						
48	49	26.88	4430	1.60						
54	44	24.06	4300	1.80						
59	40	21.98	4200	2.00	K	19	DR	63L4	9.2	546
70	34	18.55	4010	2.4	KF	19	DR	63L4	9.5	549
82	29	15.84	3840	2.8	KA	19	DR	63L4	8.7	551
88	27	14.69	3760	3.0	KAF	19	DR	63L4	9.1	549
102	23	12.70	3600	3.4						
110	22	11.84	3530	3.6						
126	19	10.32	3390	4.0						
136	18	9.58	3360	3.6						
161	15	8.09	3190	5.4						
188	13	6.91	3040	6.3						
203	12	6.41	2960	6.8						
235	10	5.54	2830	7.9						
252	9.5	5.16	2770	8.4						

P _m = 0.37 kW										
n _a rpm	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
0.18	16500	7482	72700	0.80	K KF KA KAF	127R77	DRS	71S4	470	631
0.21	14500	6565	76900	0.90						
0.24	12600	5804	79400	1.05						
0.27	11000	5027	80200	1.20						
0.31	9610	4423	80800	1.35						
0.35	8410	3889	81300	1.55						
0.42	7080	3311	81800	1.85						
0.72	4280	1926	82400	3.0	K KF KA KAF	127R77	DRS	71S4	470	631
0.79	3900	1757	82500	3.3						
0.90	3390	1541	82600	3.8						
0.36	8420	3810	65000	0.95	K KF KA KAF	107R77	DRS	71S4	310	631
0.41	7290	3358	65000	1.10						
0.46	6530	2977	65000	1.20						
0.53	5700	2599	65000	1.40						
0.60	4960	2286	65000	1.60						
0.71	4210	1939	65000	1.90						
0.81	3830	1713	65000	2.1	K KF KA KAF	107R77	DRS	71S4	310	631
0.89	3470	1554	65000	2.3						
1.0	2990	1336	65000	2.7						
1.2	2600	1166	65000	3.1						
0.65	4850	2123	40000	0.90	K KF KA KAF	97R57	DRS	71S4	180	631
0.74	4270	1856	40000	1.00						
0.85	3670	1625	40000	1.15						
0.96	3200	1430	40000	1.35						
1.1	2900	1261	40000	1.50						
1.2	2530	1102	40000	1.70						
1.4	2220	957	40000	1.95						
1.6	1980	855	40000	2.2						
1.9	1640	743	40000	2.6						
2.1	1450	652	40000	3.0						
2.4	1310	573	40000	3.3						
0.97	3250	1415	26500	0.85	K KF KA KAF	87R57	DRS	71S4	120	631
1.1	2820	1229	27100	0.95						
1.3	2460	1078	27600	1.10						
1.4	2140	951	27900	1.25						
1.6	1870	837	28200	1.45						
1.9	1620	726	28400	1.65						
2.2	1440	638	28500	1.85						
2.5	1250	562	28600	2.2						
2.9	1050	474	28800	2.6						
3.2	950	426	28800	2.8						
3.7	830	373	28900	3.2						
1.7	1880	815	7450	0.80	K KF KA KAF	77R37	DRS	71S4	72	631
2.0	1590	709	15100	0.95						
2.2	1390	622	16400	1.10						
2.5	1250	552	17200	1.25						
2.8	1090	485	17900	1.40						
3.2	960	428	18400	1.60						
3.8	840	367	18900	1.85						
4.2	745	328	19100	2.1						
4.8	665	290	19400	2.3						
5.5	570	252	19600	2.7						
6.2	500	221	19700	3.1						
7.1	440	195	19800	3.5						
7.9	390	175	19900	4.0						
9.0	345	154	19900	4.5						


P_m = 0.37 kW


n _a rpm	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
3.3	940	420	8130	0.85	K KF KA KAF	67R37	DRS	71S4	48	631
3.8	830	361	10200	1.00						
4.3	740	323	10900	1.10						
5.0	630	279	11700	1.30						
5.6	555	246	12100	1.50						
6.4	490	217	12400	1.65						
7.2	430	191	12700	1.90						
8.3	370	166	12900	2.2						
9.6	325	144	13000	2.5						
11	275	122	13000	2.9						
4.9	630	280	7350	0.95	K KF KA KAF	57R37	DRS	71S4	42	631
5.6	555	246	7980	1.10						
6.4	490	215	8460	1.20						
7.2	435	192	8720	1.40						
8.3	375	166	8980	1.60						
9.6	330	145	9170	1.80						
11	295	129	9290	2.0						
12	250	111	9460	2.4						
14	220	97	9560	2.7	K KF KA KAF	49R37	DRS	71S4	46	631
5.0	600	274	9000	0.85						
5.7	530	243	9000	0.95						
6.4	475	217	9000	1.05						
7.2	430	193	9000	1.15						
7.8	390	176	9000	1.30						
9.1	330	152	9000	1.50						
11	275	125	9000	1.80						
14	215	99	9000	2.3	K KF KA KAF	39R17	DRS	71S4	26	631
8.8	345	156	7500	0.85						
9.7	315	142	7500	0.95						
12	260	117	7500	1.15						
18	166	75	7500	1.75	K KF KA KAF	87	DRS	71M6	99	597
4.6	770	197.37	28900	3.5						
5.2	680	174.19	28900	4.0						
5.9	600	154.02	19500	2.6						
6.7	525	135.28	19600	2.9	K KF KA KAF	77	DRS	71M6	64	591
7.0	500	128.52	19700	3.1						
8.0	440	113.56	19800	3.5						
7.2	490	192.18	19700	3.0						
7.7	455	179.37	19800	3.2	K KF KA KAF	77	DRS	71S4	62	591
9.0	390	154.02	19900	3.9						
7.3	480	123.54	12500	1.70						
8.4	420	108.03	12700	1.95						
8.8	400	102.62	12800	2.0	K KF KA KAF	67	DRS	71M6	38	585
10	350	90.04	13000	2.3						
9.5	370	144.79*	12900	2.2						
11	315	123.54	13000	2.6						
13	275	108.03	13000	3.0	K KF KA KAF	67	DRS	71S4	36	585
15	230	90.04	13000	3.6						
18	196	76.37	13000	4.2						
7.3	480	123.85	8500	1.25	K KF KA KAF	57	DRS	71M6	32	579
8.4	420	108.29	8780	1.40						
8.8	400	102.88*	8880	1.50						
10	350	90.26*	9080	1.70						
12	295	76.56*	9290	2.0						
13	265	69.12	9400	2.2						
9.5	370	145.14*	9000	1.60	K KF KA KAF	57	DRS	71S4	31	579
11	315	123.85	9220	1.90						
13	275	108.29	9370	2.2						
13	260	102.88*	9420	2.3						
15	230	90.26*	9530	2.6						
18	196	76.56*	9640	3.1						
20	177	69.12	9700	3.4						

21933170/DE – 11/2015


P _m = 0.37 kW										
n _a rpm	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
18	193	75.20	9000	2.5	K	49	DRS	71S4	37	575
20	180	70.19	9000	2.5	KF	49	DRS	71S4	39	576
23	154	60.27	9000	3.2	KA	49	DRS	71S4	34	577
					KAF	49	DRS	71S4	39	576
8.7	405	104.37	5720	1.00	K	47	DRS	71M6	26	569
10.0	350	90.86	6500	1.15	KF	47	DRS	71M6	29	570
11	330	85.12*	6750	1.20	KA	47	DRS	71M6	25	571
12	290	75.20*	7120	1.35	KAF	47	DRS	71M6	28	570
10	335	131.87*	6690	1.20	K	47	DRS	71S4	25	569
11	310	121.48*	6960	1.30	KF	47	DRS	71S4	28	570
13	265	104.37	7330	1.50	KA	47	DRS	71S4	24	571
					KAF	47	DRS	71S4	27	570
15	230	90.86	7580	1.70	K	47	DRS	71S4	25	569
16	215	85.12*	7670	1.85	KF	47	DRS	71S4	28	570
18	192	75.20*	7810	2.1	KA	47	DRS	71S4	24	571
20	179	69.84	7880	2.2	KAF	47	DRS	71S4	27	570
22	162	63.30*	7960	2.5						
24	149	58.24	7500	2.0	K	39	DRS	71S4	24	565
28	127	49.69	7500	2.4	KF	39	DRS	71S4	25	566
32	111	43.45	7500	2.7	KA	39	DRS	71S4	23	567
33	106	41.28	7500	2.8	KAF	39	DRS	71S4	24	566
38	93	36.22	7500	3.2						
14	250	97.81	2520	0.80						
16	210	83.69	5470	0.95						
19	186	72.54	5690	1.10						
20	174	67.80	5630	1.15						
24	150	58.60	5500	1.35						
28	128	49.79	5350	1.55						
31	114	44.46	5230	1.75	K	37	DRS	71S4	19	559
36	97	37.97	5060	2.1	KF	37	DRS	71S4	21	560
39	91	35.57	4990	2.2	KA	37	DRS	71S4	18	561
46	77	29.96	4800	2.6	KAF	37	DRS	71S4	20	560
48	74	28.83	4750	2.7						
55	64	24.99	4590	3.1						
59	60	23.36	4510	3.3						
68	52	20.19	4350	3.6						
80	44	17.15	4160	4.1						
25	141	54.89	4940	0.90						
27	129	50.35	4980	1.00						
32	110	42.87	5000	1.15						
37	95	36.96	4860	1.30						
46	77	30.11	4650	1.50	K	29	DRS	71S4	13	552
46	76	29.69	4720	1.70	KF	29	DRS	71S4	14	556
51	70	27.23	4620	1.85	KA	29	DRS	71S4	12	558
55	64	24.91	4450	1.70	KAF	29	DRS	71S4	13	556
60	59	23.19	4440	2.2						
62	57	22.08	4330	1.85						
69	51	19.99	4270	2.5						
85	42	16.29	4050	3.1						
47	75	29.29	4050	0.80						
51	70	27.16	3990	0.85						
57	62	24.06	4030	1.30						
63	56	21.98	3940	1.40						
74	47	18.55	3780	1.70						
87	41	15.84	3640	1.95						
94	38	14.69	3570	2.1						
109	33	12.70	3430	2.5	K	19	DRS	71S4	11	546
117	30	11.84	3370	2.6	KF	19	DRS	71S4	11	549
134	26	10.32	3240	2.9	KA	19	DRS	71S4	11	551
144	25	9.58	3230	2.6	KAF	19	DRS	71S4	11	549
171	21	8.09	3080	3.9						
200	18	6.91	2930	4.5						
215	16	6.41	2870	4.9						
249	14	5.54	2740	5.6						
267	13	5.16	2680	6.0						
307	12	4.50	2570	6.9						

P_m = 0.55 kW


n _a rpm	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
0.08	55000	16978	190000	0.90	K KH	187R97 187R97	DRS DRS	71M4 71M4	1770 1700	632 632
0.10	46200	14272	190000	1.10						
0.10	42000	13116	190000	1.20						
0.12	36600	11647	190000	1.35						
0.19	23700	7343	190000	2.1						
0.12	37400	11573	150000	0.85	K KH	167R97 167R97	DRS DRS	71M4 71M4	1190 1150	632 632
0.13	33200	10264	150000	0.95						
0.16	27900	8628	150000	1.15						
0.21	21200	6562	150000	1.50						
0.25	16800	5355	150000	1.90						
0.33	13000	4079	150000	2.4						
0.20	22200	6881	109700	0.80	K	157R97	DRS	71M4	790	632
0.23	19200	5931	111600	0.95	KF	157R97	DRS	71M4	870	632
0.34	12800	3979	114400	1.40	KA	157R97	DRS	71M4	750	632
0.45	9870	3051	115300	1.80	KAF	157R97	DRS	71M4	810	632
0.31	14900	4423	76100	0.85	K KF KA KAF	127R77 127R77 127R77 127R77	DRS DRS DRS DRS	71M4 71M4 71M4 71M4	475 520 445 485	631 631 631 631
0.35	13000	3889	79100	1.00						
0.41	11000	3311	80200	1.20						
0.45	9990	3009	80700	1.30						
0.52	8580	2607	81200	1.50						
0.71	6620	1926	81900	1.95	K KF KA KAF	127R77 127R77 127R77 127R77	DRS DRS DRS DRS	71M4 71M4 71M4 71M4	475 510 445 480	631 631 631 631
0.77	6040	1757	82000	2.2						
0.88	5260	1541	82200	2.5						
1.0	4610	1342	82400	2.8						
1.2	4020	1177	82500	3.2						
1.3	3520	1025	82600	3.7						
0.46	10100	2977	65000	0.80	K KF KA KAF	107R77 107R77 107R77 107R77	DRS DRS DRS DRS	71M4 71M4 71M4 71M4	315 325 285 310	631 631 631 631
0.52	8820	2599	65000	0.90						
0.59	7710	2286	65000	1.05						
0.70	6540	1939	65000	1.20						
0.79	5910	1713	65000	1.35	K KF KA KAF	107R77 107R77 107R77 107R77	DRS DRS DRS DRS	71M4 71M4 71M4 71M4	310 325 285 310	631 631 631 631
0.87	5360	1554	65000	1.50						
1.0	4610	1336	65000	1.75						
1.2	4020	1166	65000	2.00						
1.3	3460	1030	65000	2.3						
1.5	3010	904	65000	2.6						
1.7	2720	793	65000	2.9						
2.0	2370	696	65000	3.4						
2.2	2050	615	65000	3.9						
0.95	4940	1430	40000	0.85	K KF KA KAF	97R57 97R57 97R57 97R57	DRS DRS DRS DRS	71M4 71M4 71M4 71M4	180 200 165 190	631 631 631 631
1.1	4430	1261	40000	0.95						
1.2	3870	1102	40000	1.10						
1.4	3390	957	40000	1.25						
1.6	3030	855	40000	1.40						
1.8	2540	743	40000	1.70						
2.1	2240	652	40000	1.90						
2.4	2010	573	40000	2.1						
2.7	1720	504	40000	2.5						
3.1	1480	437	40000	2.9						
3.6	1320	382	40000	3.3						
4.5	1060	305	40000	4.0						
1.4	3300	951	26400	0.80	K KF KA KAF	87R57 87R57 87R57 87R57	DRS DRS DRS DRS	71M4 71M4 71M4 71M4	120 130 110 120	631 631 631 631
1.6	2890	837	27000	0.95						
1.9	2510	726	27500	1.10						
2.1	2210	638	27800	1.20						
2.4	1940	562	28100	1.40						
2.9	1630	474	28400	1.65						
3.2	1470	426	28500	1.85						
3.6	1290	373	28600	2.1						
4.1	1120	330	28700	2.4						
4.6	1000	294	28800	2.7						
5.4	870	250	28800	3.1						
5.8	820	236	28900	3.3						
6.8	695	201	28900	3.9						

P _m = 0.55 kW																
n _a rpm	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg							
2.8	1680	485	14300	0.90	K KF KA KAF	77R37	DRS	71M4	73	631						
3.2	1480	428	15800	1.05												
3.7	1280	367	17000	1.20												
4.2	1140	328	17700	1.35												
4.7	1010	290	18200	1.50												
5.4	870	252	18700	1.75												
6.2	770	221	19100	2.0												
7.0	680	195	19300	2.3												
7.8	600	175	19500	2.6	K KF KA KAF	67R37	DRS	71M4	49	631						
8.8	530	154	19600	2.9												
4.9	970	279	6400	0.85												
5.5	850	246	9990	0.95												
6.2	760	217	10800	1.10												
7.1	665	191	11500	1.25												
8.2	575	166	12000	1.40												
9.4	505	144	12400	1.60												
11	425	122	12700	1.90	K KF KA KAF	57R37	DRS	71M4	52	631						
7.1	665	192	4080	0.90												
8.2	575	166	7800	1.05												
9.4	505	145	8360	1.20												
11	455	129	8630	1.30												
12	385	111	8930	1.55												
14	340	97	9120	1.75												
7.7	595	176	9000	0.85							K KF KA KAF	49R37	DRS	71M4	47	631
9.0	505	152	9000	1.00												
11	420	125	9000	1.20												
14	330	99	9000	1.50												
18	255	75	7500	1.15	K KF KA KAF	39R17	DRS	71M4	28	631						
4.6	1130	197.37	28700	2.4												
5.2	990	174.19	28800	2.7												
5.6	940	164.34*	28800	2.9												
6.2	840	147.32*	28900	3.2	K KF KA KAF	87	DRS	80S6	100	597						
5.9	880	154.02	18700	1.75												
6.8	775	135.28	19100	2.0												
7.1	735	128.52	19200	2.1												
8.1	650	113.56	19400	2.4	K KF KA KAF	77	DRS	80S6	66	591						
8.8	590	154.02	19500	2.6												
10	520	135.28	19700	3.0												
11	495	128.52	19700	3.1												
12	435	113.56	19800	3.5	K KF KA KAF	77	DRS	71M4	56	593						
14	370	97.05	19900	4.1												
7.4	705	123.54	11200	1.15							K KF KA KAF	67	DRS	80S6	40	585
8.5	620	108.03	11800	1.30												
8.9	585	102.62	12000	1.40												
10	515	90.04	12300	1.60												
12	435	76.37	12700	1.85	K KF KA KAF	67	DRS	80S6	46	586						
11	475	123.54	12500	1.70												
13	415	108.03	12800	1.95												
15	345	90.04	13000	2.4												
18	290	76.37	13000	2.8	K KF KA KAF	67	DRS	80S6	37	587						
8.4	620	108.29	7450	0.95												
8.9	590	102.88*	7710	1.00												
10	515	90.26*	8280	1.15												
12	435	76.56*	8710	1.35	K KF KA KAF	57	DRS	80S6	32	581						
13	395	69.12	8900	1.50												
15	345	60.81*	9100	1.70												
16	325	57.42*	9170	1.80												


P_m = 0.55 kW

n _a rpm	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
11	475	123.85	8520	1.25	K KF KA KAF	57	DRS	71M4	32	579
13	415	108.29	8800	1.45						
13	395	102.88*	8890	1.50						
15	345	90.26*	9100	1.70						
18	295	76.56*	9300	2.0						
20	265	69.12	9410	2.2						
22	230	60.81*	9520	2.6						
24	220	57.42*	9560	2.7						
18	290	75.20	9000	1.65	K KF KA KAF	49	DRS	71M4	38	575
19	270	70.19	9000	1.65						
23	230	60.27	9000	2.2						
26	200	52.94	9000	2.4						
27	194	50.29	9000	2.6						
31	172	44.44	9000	2.9						
36	147	37.98	9000	3.4						
13	400	104.37	5880	1.00	K KF KA KAF	47	DRS	71M4	26	569
15	350	90.86	6550	1.15						
16	325	85.12*	6790	1.20						
18	290	75.20*	7140	1.40						
19	265	69.84	7310	1.50						
21	240	63.30*	7500	1.65	K KF KA KAF	47	DRS	71M4	26	569
24	215	56.83	7660	1.80						
28	189	48.95*	7830	2.1						
30	178	46.03*	7880	2.2						
23	220	58.24	7500	1.35	K KF KA KAF	39	DRS	71M4	25	565
27	192	49.69	7500	1.55						
31	168	43.45	7500	1.80						
33	159	41.28	7500	1.90						
38	140	36.22	7500	2.1						
44	119	30.72	7500	2.5						
49	107	27.73	7410	2.8						
56	94	24.40	7170	3.2						
59	89	23.04	7070	3.4						
23	225	58.60	4840	0.90	K KF KA KAF	37	DRS	71M4	20	559
27	192	49.79	4790	1.05						
31	172	44.46	4740	1.15						
36	147	37.97	4640	1.35						
38	137	35.57	4600	1.45						
45	116	29.96	4470	1.75						
47	111	28.83	4440	1.80						
54	96	24.99	4320	2.1						
58	90	23.36	4260	2.2						
67	78	20.19	4130	2.4						
79	66	17.15	3980	2.7						
89	59	15.31	3880	3.0						
104	51	13.08	3730	3.3						
112	47	12.14	3660	3.4						
130	41	10.49	3520	4.0						
37	143	36.96	4410	0.85	K KF KA KAF	29	DRS	71M4	14	552
45	116	30.11	4290	1.00						
46	115	29.69	4400	1.15						
50	105	27.23	4330	1.25						
55	96	24.91	4160	1.15						
59	90	23.19	4200	1.45						
62	85	22.08	4060	1.25						
68	77	19.99	4060	1.70						
84	63	16.29	3880	2.1						
101	52	13.47	3700	2.5						
114	46	11.94	3590	2.8						
137	38	9.90	3510	2.9						
159	33	8.53	3360	3.7						


P_m = 0.55 kW


n _a rpm	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
57	93	24.06	3730	0.85						
62	85	21.98	3670	0.95						
73	72	18.55	3560	1.10						
86	61	15.84	3450	1.30						
93	57	14.69	3390	1.40						
107	49	12.70	3280	1.65						
115	46	11.84	3230	1.75	K	19	DRS	71M4	12	546
132	40	10.32	3120	1.90	KF	19	DRS	71M4	13	549
142	37	9.58	3150	1.70	KA	19	DRS	71M4	12	551
168	31	8.09	3010	2.6	KAF	19	DRS	71M4	12	549
197	27	6.91	2880	3.0						
212	25	6.41	2820	3.2						
246	21	5.54	2700	3.7						
263	20	5.16	2640	4.0						
302	17	4.50	2540	4.6						

P_m = 0.75 kW


n _a rpm	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
0.11	55300	13116	190000	0.90						
0.12	48400	11647	190000	1.05						
0.20	31200	7343	190000	1.60	K	187R97	DRN	80M4	1770	632
0.21	28400	6747	190000	1.75	KH	187R97	DRN	80M4	1700	632
0.24	24900	5991	190000	2.0						
0.17	36600	8628	150000	0.85						
0.22	27900	6562	150000	1.15						
0.27	22200	5355	150000	1.45	K	167R97	DRN	80M4	1190	632
0.35	17200	4079	150000	1.85	KH	167R97	DRN	80M4	1150	632
0.43	14300	3376	150000	2.2						
0.36	16900	3979	112700	1.05	K	157R97	DRN	80M4	800	632
0.47	12900	3051	114400	1.40	KF	157R97	DRN	80M4	870	632
					KA	157R97	DRN	80M4	760	632
					KAF	157R97	DRN	80M4	820	632
0.87	7130	1659	116000	2.5	K	157R97	DRN	80M4	790	632
1.0	5740	1365	116200	3.1	KF	157R97	DRN	80M4	870	632
					KA	157R97	DRN	80M4	760	632
					KAF	157R97	DRN	80M4	810	632
0.43	14400	3311	77100	0.90	K	127R77	DRN	80M4	480	631
0.48	13000	3009	79100	1.00	KF	127R77	DRN	80M4	520	631
0.55	11200	2607	80100	1.15	KA	127R77	DRN	80M4	450	631
					KAF	127R77	DRN	80M4	490	631
0.75	8610	1926	81200	1.50						
0.82	7860	1757	81500	1.65						
0.93	6860	1541	81800	1.90	K	127R77	DRN	80M4	475	631
1.1	6000	1342	82100	2.2	KF	127R77	DRN	80M4	520	631
					KA	127R77	DRN	80M4	450	631
					KAF	127R77	DRN	80M4	485	631
1.2	5240	1177	82200	2.5						
1.4	4580	1025	82400	2.8						
1.6	4000	899	82500	3.2						
0.84	7690	1713	65000	1.05						
0.93	6980	1554	65000	1.15						
1.1	5990	1336	65000	1.35						
1.2	5230	1166	65000	1.55	K	107R77	DRN	80M4	315	631
1.4	4530	1030	65000	1.75	KF	107R77	DRN	80M4	330	631
1.6	3940	904	65000	2.0	KA	107R77	DRN	80M4	290	631
1.8	3540	793	65000	2.3	KAF	107R77	DRN	80M4	315	631
2.1	3090	696	65000	2.6						
2.3	2680	615	65000	3.0						

P_m = 0.75 kW

n _a rpm	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
1.3	5010	1102	39900	0.85	K KF KA KAF	97R57	DRN	80M4	185	631
1.5	4400	957	40000	1.00						
1.7	3930	855	40000	1.10						
1.9	3310	743	40000	1.30						
2.2	2920	652	40000	1.45						
2.5	2610	573	40000	1.65						
2.9	2240	504	40000	1.90						
3.3	1930	437	40000	2.2						
3.8	1710	382	40000	2.5						
4.7	1380	305	40000	3.1						
5.6	1160	258	40000	3.7	K KF KA KAF	87R57	DRN	80M4	125	631
6.2	1050	232	40000	4.1						
7.2	890	199	40000	4.8						
2.0	3260	726	26500	0.85						
2.3	2870	638	27100	0.95						
2.6	2520	562	27500	1.05						
3.0	2120	474	27900	1.25						
3.4	1910	426	28100	1.40						
3.9	1680	373	28300	1.60						
4.4	1460	330	28500	1.85						
4.9	1310	294	28600	2.1	K KF KA KAF	77R37	DRN	80M4	78	631
5.8	1130	250	28700	2.4						
6.1	1070	236	28700	2.5						
7.2	900	201	28800	3.0						
3.9	1660	367	14500	0.95						
4.4	1480	328	15800	1.05						
5.0	1310	290	16800	1.20						
5.7	1130	252	17700	1.35						
6.5	1000	221	18300	1.55						
12	545	125	9000	0.90	K KF KA KAF	49R37	DRN	80M4	51	631
15	430	99	9000	1.15						
19	330	75	7500	0.90						
7.3	980	197.37	28800	2.8						
8.3	860	174.19	28800	3.1						
8.8	810	164.34*	28900	3.3						
9.8	730	147.32*	28900	3.7						
9.4	765	154.02	19100	2.0						
11	670	135.28	19300	2.3						
11	635	128.52	19400	2.4	K KF KA KAF	77	DRN	80M4	68	591
13	560	113.56	19600	2.7						
15	480	97.05	19700	3.2						
12	610	123.54	11800	1.35						
13	535	108.03	12200	1.55						
16	445	90.04	12600	1.85						
19	375	76.37	12900	2.2						
21	340	68.95	13000	2.4						
24	300	60.66	13000	2.7						
25	280	57.28	13000	2.9						
12	615	123.85	7500	0.95	K KF KA KAF	57	DRN	80M4	37	579
13	535	108.29	8120	1.10						
14	510	102.88*	8330	1.15						
16	445	90.26*	8660	1.35						
19	380	76.56*	8960	1.60						
21	340	69.12	9120	1.75						
24	300	60.81*	9280	2.00						
25	285	57.42*	9340	2.1						
29	240	48.89	9490	2.5						
32	220	44.43	9560	2.7						


P _m = 0.75 kW										
n _a rpm	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
24	295	60.27	9000	1.65	K	49	DRN	80M4	43	575
27	260	52.94	9000	1.90						
29	250	50.29	9000	2.0						
32	220	44.44	9000	2.3						
38	189	37.98	9000	2.6						
41	173	34.81	9000	2.9						
47	152	30.55	8960	3.3						
50	144	28.95	8840	3.5						
19	370	75.20*	6270	1.05	K	47	DRN	80M4	31	569
21	345	69.84	6590	1.15	KF	47	DRN	80M4	34	570
23	310	63.30*	6920	1.25	KA	47	DRN	80M4	30	571
					KAF	47	DRN	80M4	33	570
25	280	56.83	7210	1.40	K	47	DRN	80M4	31	569
29	240	48.95*	7500	1.65						
31	225	46.03*	7600	1.75						
36	197	39.61	7790	2.0						
41	176	35.39	7690	2.3						
46	156	31.30	7480	2.6						
29	245	49.69	7500	1.20	K	39	DRN	80M4	30	565
33	215	43.45	7500	1.40						
35	205	41.28	7500	1.45						
40	180	36.22	7390	1.65						
47	153	30.72	7140	1.95						
52	138	27.73	6990	2.2						
59	121	24.40	6790	2.5						
62	115	23.04	6700	2.6						
73	98	19.62	6440	3.0						
81	89	17.83	6290	3.3						
93	77	15.44	6060	3.6						
32	220	44.46	4170	0.90	K	37	DRN	80M4	24	559
38	189	37.97	4140	1.05						
40	177	35.57	4130	1.15						
48	149	29.96	4060	1.35						
50	143	28.83	4040	1.40						
58	124	24.99	3970	1.60						
62	116	23.36	3930	1.70						
71	100	20.19	3840	1.85						
84	85	17.15	3720	2.1						
94	76	15.31	3640	2.3						
110	65	13.08	3520	2.5						
119	60	12.14	3460	2.6						
137	52	10.49	3340	3.1						
162	44	8.91	3210	3.6						
181	40	7.96	3120	3.9						
58	124	24.91	3780	0.90	K	29	DRN	80M4	19	552
62	115	23.19	3870	1.15						
65	110	22.08	3720	0.95						
72	99	19.99	3780	1.30						
88	81	16.29	3630	1.60						
107	67	13.47	3490	1.95						
121	59	11.94	3400	2.2						
146	49	9.90	3370	2.2						
157	46	9.17	3190	2.8						
169	42	8.53	3230	2.9						
193	37	7.48	3030	3.3						
207	35	6.95	3050	3.2						


P_m = 0.75 kW

n _a rpm	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
78	92	18.55	3260	0.85						
91	79	15.84	3190	1.00						
98	73	14.69	3150	1.10						
113	63	12.70	3060	1.25						
122	59	11.84	3020	1.35	K	19	DRN	80M4	17	546
140	51	10.32	2940	1.50	KF	19	DRN	80M4	17	549
178	40	8.09	2870	2.00	KA	19	DRN	80M4	16	551
208	34	6.91	2760	2.3	KAF	19	DRN	80M4	17	549
225	32	6.41	2700	2.5						
260	28	5.54	2600	2.9						
279	26	5.16	2550	3.1						
320	22	4.50	2450	3.6						


10


P_m = 1.1 kW


n _a rpm	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
0.16	57100	9363	190000	0.85						
0.18	48800	8126	190000	1.00						
0.20	46400	7343	190000	1.10						
0.22	42400	6747	190000	1.20	K	187R97	DRN	90S4	1780	632
0.24	37300	5991	190000	1.35	KH	187R97	DRN	90S4	1710	632
0.27	33000	5358	190000	1.50						
0.30	29400	4817	190000	1.70						
0.33	26600	4370	190000	1.85						
0.27	33300	5355	150000	0.95						
0.30	29500	4788	150000	1.10	K	167R97	DRN	90S4	1190	632
0.36	25600	4079	150000	1.25	KH	167R97	DRN	90S4	1160	632
0.43	21300	3376	150000	1.50						
0.53	17100	2755	150000	1.85						
0.67	13900	2182	150000	2.3	K	167R97	DRN	90S4	1190	632
0.85	10800	1704	150000	3.0	KH	167R97	DRN	90S4	1150	632
1.0	9000	1408	150000	3.6						
1.1	8240	1296	150000	3.9						
0.41	21600	3516	110100	0.85	K	157R97	DRN	90S4	800	632
0.48	19200	3051	111500	0.95	KF	157R97	DRN	90S4	880	632
0.56	15900	2610	113200	1.15	KA	157R97	DRN	90S4	760	632
0.63	14100	2322	113900	1.25	KAF	157R97	DRN	90S4	820	632
0.88	10600	1659	115100	1.70						
1.1	8600	1365	115600	2.1	K	157R97	DRN	90S4	800	632
1.2	7670	1229	115900	2.4	KF	157R97	DRN	90S4	880	632
1.3	6820	1093	116000	2.6	KA	157R97	DRN	90S4	760	632
1.5	5880	942	116200	3.1	KAF	157R97	DRN	90S4	820	632
1.7	5270	854	116300	3.4						
0.76	12600	1926	79400	1.05						
0.83	11500	1757	80000	1.15						
0.94	10000	1541	80600	1.30						
1.1	8810	1342	81200	1.45						
1.2	7700	1177	81600	1.70	K	127R77	DRN	90S4	480	631
1.4	6730	1025	81900	1.95	KF	127R77	DRN	90S4	520	631
1.6	5880	899	82100	2.2	KA	127R77	DRN	90S4	455	631
1.8	5060	790	82300	2.6	KAF	127R77	DRN	90S4	490	631
2.1	4580	704	82400	2.8						
2.4	3940	610	82500	3.3						
2.6	3560	549	82600	3.6						
3.0	3060	477	82600	4.2						

P _m = 1.1 kW										
n _a rpm	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
1.2	7680	1166	65000	1.05	K KF KA KAF	107R77	DRN	90S4	320	631
1.4	6680	1030	65000	1.20						
1.6	5840	904	65000	1.35						
1.8	5200	793	65000	1.55						
2.1	4550	696	65000	1.75						
2.4	3970	615	65000	2.0						
2.8	3370	522	65000	2.4						
3.2	2960	461	65000	2.7						
3.6	2610	408	65000	3.1						
4.0	2360	364	65000	3.4						
4.6	2070	318	65000	3.9						
2.0	4870	743	40000	0.90	K KF KA KAF	97R57	DRN	90S4	195	631
2.2	4280	652	40000	1.00						
2.5	3830	573	40000	1.10						
2.9	3300	504	40000	1.30						
3.3	2840	437	40000	1.50						
3.8	2510	382	40000	1.70						
4.2	2220	342	40000	1.95						
3.1	3120	474	26700	0.85	K KF KA KAF	87R57	DRN	90S4	130	631
3.4	2800	426	27200	0.95						
3.9	2470	373	27600	1.10						
4.4	2160	330	27900	1.25						
5.0	1930	294	28100	1.40						
5.8	1660	250	28300	1.60						
6.2	1570	236	28400	1.70						
7.2	1330	201	28600	2.0						
8.3	1270	176.05*	40000	3.4	K	97	DRN	90S4	170	603
9.5	1100	153.21*	40000	3.9	KF	97	DRN	90S4	190	604
10	1010	140.28	40000	4.2	KA	97	DRN	90S4	150	605
					KAF	97	DRN	90S4	175	604
8.4	1250	174.19	28600	2.2	K KF KA KAF	87	DRN	90S4	110	597
8.8	1180	164.34*	28700	2.3						
9.9	1060	147.32*	28800	2.5						
11	910	126.91*	28800	3.0						
13	830	115.82	28900	3.2						
11	970	135.28	18400	1.60	K	77	DRN	90S4	73	591
11	920	128.52	18600	1.65	KF	77	DRN	90S4	82	592
13	810	113.56	18900	1.90	KA	77	DRN	90S4	66	593
					KAF	77	DRN	90S4	74	592
15	700	97.05	19300	2.2	K KF KA KAF	77	DRN	90S4	73	591
16	640	88.97	19400	2.4						
19	560	78.07	19600	2.8						
20	530	73.99	19600	2.9						
13	775	108.03	10700	1.05	K KF KA KAF	67	DRN	90S4	49	585
14	740	102.62	11000	1.10						
16	650	90.04	11600	1.25						
19	550	76.37	12200	1.50						
21	495	68.95	12400	1.65						
24	435	60.66	12700	1.85	K KF KA KAF	67	DRN	90S4	49	585
25	410	57.28	12800	2.00						
30	350	48.77	13000	2.3						
33	315	44.32	13000	2.6						
38	275	38.39	13000	2.9						
16	650	90.26*	6280	0.90	K KF KA KAF	57	DRN	90S4	43	579
19	550	76.56*	8010	1.10						
21	495	69.12	8420	1.20						
24	435	60.81*	8710	1.35						
25	410	57.42*	8820	1.45						
30	350	48.89	9080	1.70						
33	320	44.43	9210	1.85						


P_m = 1.1 kW

n _a rpm	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
38	275	38.49	9370	2.2	K KF KA KAF	57	DRN	90S4	43	579
41	255	35.70	9440	2.3						
48	215	30.28	9570	2.7						
53	197	27.34	9430	3.0						
60	174	24.05	9130	3.5						
64	164	22.71	9000	3.7						
75	140	19.34	8640	4.1						
83	127	17.57	8420	4.4						
96	110	15.22	8100	4.9						
110	96	13.25	7790	5.3						
122	86	11.92	7490	4.8						
129	81	11.26	7370	5.1						
152	69	9.59	7040	5.8						
167	63	8.71	6850	6.2						
193	54	7.55	6570	6.7						
222	47	6.57	6310	7.3						
310	34	4.69	5700	8.9						
24	435	60.27	9000	1.15	K KF KA KAF	49	DRN	90S4	48	575
27	380	52.94	9000	1.30						
29	360	50.29	9000	1.40						
33	320	44.44	9000	1.55						
38	270	37.98	8800	1.80						
42	250	34.81	8660	2.00						
48	220	30.55	8430	2.3						
50	205	28.95	8340	2.4						
57	183	25.34	8100	2.7						
64	165	22.83	7900	3.0						
73	145	20.03	7660	3.5						
26	410	56.83	5430	0.95	K KF KA KAF	47	DRN	90S4	37	569
30	350	48.95*	6520	1.15						
32	330	46.03*	6750	1.20						
37	285	39.61	7160	1.40	K KF KA KAF	47	DRN	90S4	37	569
41	255	35.39	7050	1.55						
46	225	31.30	6920	1.75						
50	210	29.32	6840	1.90						
56	187	25.91	6690	2.1						
67	157	21.81	6460	2.5						
74	141	19.58	6310	2.8						
29	355	49.69	6810	0.85	K KF KA KAF	39	DRN	90S4	36	565
33	310	43.45	6760	0.95						
35	295	41.28	6740	1.00						
40	260	36.22	6660	1.15						
47	220	30.72	6520	1.35						
52	200	27.73	6420	1.50						
60	176	24.40	6290	1.70						
63	166	23.04	6230	1.80						
74	142	19.62	6040	2.1						
82	129	17.83	5920	2.2						
94	111	15.44	5740	2.5						
108	97	13.44	5560	2.8						
114	92	12.73	5760	2.7						
120	87	12.09	5680	2.9						
137	77	10.61	5480	3.7						


P _m = 1.1 kW										
n _a rpm	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
49	215	29.96	3430	0.90	K KF KA KAF	37	DRN	90S4	30	559
58	180	24.99	3440	1.10						
62	169	23.36	3430	1.15						
72	146	20.19	3410	1.25						
85	124	17.15	3360	1.45						
95	111	15.31	3310	1.60						
111	94	13.08	3240	1.75						
120	88	12.14	3200	1.85						
139	76	10.49	3120	2.1						
163	64	8.91	3020	2.5						
183	57	7.96	2950	2.7						
214	49	6.80	2850	3.1						
229	46	6.37	2800	3.2						
271	39	5.36	2690	3.6						
366	29	3.98	2490	4.4						
73	144	19.99	3360	0.90	K KF KA KAF	29	DRN	90S4	25	552
89	118	16.29	3290	1.10						
108	97	13.47	3210	1.35						
122	86	11.94	3150	1.50						
147	71	9.90	3210	1.55						
159	66	9.17	2990	1.95						
171	62	8.53	3100	2.00						
195	54	7.48	2870	2.3						
209	50	6.95	2940	2.2						
253	42	5.75	2800	2.7						
285	37	5.10	2710	3.0						
115	92	12.70	2760	0.85	K KF KA KAF	19	DRN	90S4	23	546
123	85	11.84	2740	0.90						
141	74	10.32	2690	1.00						
180	58	8.09	2720	1.35						
211	50	6.91	2620	1.60						
227	46	6.41	2580	1.75						
263	40	5.54	2490	2.0						
282	37	5.16	2440	2.2						
323	32	4.50	2360	2.5						

P _m = 1.5 kW										
n _a rpm	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
0.22	58500	6747	190000	0.85	K KH	187R97	DRN	90L4	1780	632
0.24	51600	5991	190000	0.95						
0.27	45800	5358	190000	1.10						
0.30	40800	4817	190000	1.20						
0.33	37100	4370	190000	1.35						
0.40	31800	3609	190000	1.55	K KH	187R97	DRN	90L4	1780	632
0.48	26900	3062	190000	1.85						
0.58	21900	2519	190000	2.3						
0.64	19600	2268	190000	2.6						
0.36	35300	4079	150000	0.90	K KH	167R97	DRN	90L4	1200	632
0.43	29300	3376	150000	1.10						
0.53	23700	2755	150000	1.35						
0.67	19200	2182	150000	1.65	K KH	167R97	DRN	90L4	1190	632
0.86	14900	1704	150000	2.1						
1.0	12400	1408	150000	2.6						
1.1	11300	1296	150000	2.8						
0.63	19700	2322	111300	0.90	K	157R97	DRN	90L4	800	632
					KF	157R97	DRN	90L4	880	632
					KA	157R97	DRN	90L4	770	632
					KAF	157R97	DRN	90L4	830	632


P_m = 1.5 kW

n _a rpm	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
0.88	14600	1659	113700	1.25	K KF KA KAF	157R97	DRN	90L4	800	632
1.1	11900	1365	114700	1.50						
1.2	10600	1229	115100	1.70						
1.3	9460	1093	115400	1.90						
1.6	8150	942	115700	2.2						
1.7	7330	854	115900	2.4						
2.6	4810	567	116300	3.7						
2.9	4280	504	116400	4.2	K KF KA KAF	127R87	DRN	90L4	510	631
2.7	4640	536	82400	2.8						
3.5	3660	418	82600	3.6						
4.0	3220	367	82600	4.0						
0.83	15700	1757	74400	0.80	K KF KA KAF	127R77	DRN	90L4	485	631
0.95	13800	1541	78300	0.95						
1.1	12000	1342	79700	1.10						
1.2	10500	1177	80400	1.25						
1.4	9200	1025	81000	1.40						
1.6	8050	899	81400	1.60						
1.8	6970	790	81800	1.85						
2.1	6280	704	82000	2.1						
2.4	5420	610	82200	2.4						
2.7	4890	549	82300	2.7						
3.1	4210	477	82500	3.1	K KF KA KAF	107R77	DRN	90L4	325	631
3.5	3720	418	82500	3.5						
1.4	9170	1030	65000	0.85						
1.6	8020	904	65000	1.00						
1.8	7120	793	65000	1.10						
2.1	6230	696	65000	1.30						
2.4	5460	615	65000	1.45						
2.8	4630	522	65000	1.75						
3.2	4070	461	65000	1.95						
3.6	3600	408	65000	2.2						
4.0	3240	364	65000	2.5	K KF KA KAF	97R57	DRN	90L4	195	631
4.6	2830	318	65000	2.8						
2.6	5220	573	39600	0.80						
2.9	4510	504	40000	0.95						
3.4	3900	437	40000	1.10						
3.8	3440	382	40000	1.25						
4.3	3040	342	40000	1.40						
4.8	2770	305	40000	1.55						
5.7	2340	258	40000	1.85						
6.3	2100	232	40000	2.0	K KF KA KAF	87R57	DRN	90L4	135	631
7.3	1800	199	40000	2.4						
4.4	2950	330	27000	0.90						
5.0	2650	294	27400	1.00						
5.8	2270	250	27800	1.20						
6.2	2140	236	27900	1.25						
7.3	1820	201	28200	1.50						
8.0	1650	183	28400	1.65						
8.3	1720	176.05*	40000	2.5	K KF KA KAF	97	DRN	90L4	170	603
9.5	1500	153.21*	40000	2.9						
10	1370	140.28	40000	3.1						
12	1210	123.93*	40000	3.5						
8.4	1700	174.19	28300	1.60	K KF KA KAF	87	DRN	90L4	110	597
8.9	1610	164.34*	28400	1.70						
9.9	1440	147.32*	28500	1.85						
12	1240	126.91*	28600	2.2						
13	1130	115.82	28700	2.4						
14	1000	102.71*	28800	2.7						
17	840	86.34	28900	3.2	K KF KA KAF	77	DRN	90L4	77	591
11	1320	135.28	16800	1.15						
11	1260	128.52	17100	1.25						
13	1110	113.56	17800	1.40						
15	950	97.05	18500	1.65						
16	870	88.97	18800	1.80						


21933170/DE – 11/2015


P_m = 1.5 kW										
n_a rpm	M_a Nm	i	F_{Ra}¹⁾ N	SEW f_B					m kg	
19	765	78.07	19100	2.0	K	77	DRN	90L4	77	591
20	725	73.99	19200	2.1						
23	630	64.75	19400	2.4						
25	570	58.34	19600	2.7						
29	500	51.18	19700	3.1						
32	440	45.16	19800	3.5						
36	390	40.04	19900	4.0	KF	77	DRN	90L4	85	592
23	630	64.75	19400	2.4						
25	570	58.34	19600	2.7						
29	500	51.18	19700	3.1						
32	440	45.16	19800	3.5						
36	390	40.04	19900	4.0						
16	880	90.04	9710	0.95	KA	67	DRN	90L4	52	585
19	745	76.37	10900	1.10						
21	675	68.95	11400	1.20						
24	590	60.66	11900	1.40						
26	560	57.28	12100	1.45						
30	475	48.77	12500	1.70						
33	430	44.32	12700	1.90	KAF	67	DRN	90L4	55	586
38	375	38.39	12900	2.1						
41	345	35.62	13000	2.4						
48	295	30.22	13000	2.8						
54	265	27.28	13000	3.1						
61	235	24.00	13000	3.4						
24	595	60.81*	7660	1.00	K	57	DRN	90L4	46	579
25	560	57.42*	7930	1.05						
30	475	48.89	8520	1.25						
33	435	44.43	8720	1.40						
38	375	38.49	8980	1.60						
41	350	35.70	9090	1.70						
48	295	30.28	9130	2.0	KF	57	DRN	90L4	51	580
53	265	27.34	8950	2.2						
61	235	24.05	8710	2.5						
64	220	22.71	8600	2.7						
76	190	19.34	8300	3.0						
28	515	52.94	8280	0.95	KA	49	DRN	90L4	53	576
29	490	50.29	8260	1.00						
33	435	44.44	8200	1.15						
38	370	37.98	8080	1.35						
42	340	34.81	7990	1.45						
48	295	30.55	7850	1.65						
50	280	28.95	7780	1.75	KAF	49	DRN	90L4	48	577
58	245	25.34	7610	2.0						
64	220	22.83	7470	2.2						
73	196	20.03	7280	2.6						
83	173	17.67	7090	2.9						
93	154	15.67	6900	3.2						
109	131	13.38	6650	3.6	K	47	DRN	90L4	40	569
37	385	39.61	6080	1.05						
41	345	35.39	6340	1.15						
47	305	31.30	6290	1.30						
50	285	29.32	6250	1.40						
56	250	25.91	6160	1.55	KF	47	DRN	90L4	44	570
67	210	21.81	6020	1.85						
75	192	19.58	5920	2.1						
87	165	16.86	5760	2.3						
92	155	15.86	5690	2.4						
107	134	13.65	5520	2.7						
120	120	12.19	5390	2.9	KA	47	DRN	90L4	39	571
124	115	11.77	5300	2.4						

P_m = 1.5 kW


n _a rpm	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
40	355	36.22	5840	0.85	K KF KA KAF	39	DRN	90L4	39	565
48	300	30.72	5830	1.00						
53	270	27.73	5800	1.10						
60	235	24.40	5740	1.25						
63	225	23.04	5700	1.35						
74	192	19.62	5600	1.55						
82	175	17.83	5520	1.65						
95	151	15.44	5390	1.85						
109	132	13.44	5260	2.0						
115	125	12.73	5560	2.0						
121	119	12.09	5490	2.2						
138	104	10.61	5310	2.7						
162	88	9.00	5080	3.4						
180	80	8.12	4950	3.8						
63	225	23.36	2880	0.85	K KF KA KAF	37	DRN	90L4	33	559
72	198	20.19	2920	0.95						
85	168	17.15	2950	1.05						
95	150	15.31	2940	1.15						
112	128	13.08	2920	1.30						
120	119	12.14	2910	1.35						
139	103	10.49	2870	1.55						
164	87	8.91	2810	1.85						
184	78	7.96	2760	2.00						
215	67	6.80	2680	2.2						
229	62	6.37	2650	2.3						
272	53	5.36	2560	2.7						
367	39	3.98	2400	3.2						
90	160	16.29	2910	0.80						
108	132	13.47	2890	1.00						
122	117	11.94	2860	1.10						
159	90	9.17	2780	1.45						
171	84	8.53	2940	1.45						
195	73	7.48	2690	1.70						
210	68	6.95	2820	1.65						
254	56	5.75	2690	2.00						
287	50	5.10	2620	2.2						
373	38	3.92	2440	3.3						
458	31	3.19	2310	3.5						


P_m = 2.2 kW


n_a rpm	M_a Nm	i	$F_{Ra}^{1)}$ N	SEW f_B					m kg	
0.33	56000	4370	190000	0.90	K	187R97	DRN	100LS4	1780	632
0.51	35200	2818	190000	1.40	KH	187R97	DRN	100LS4	1720	632
0.40	47600	3609	190000	1.05	K KH	187R97 187R97	DRN DRN	100LS4 100LS4	1780 1710	632 632
0.47	40300	3062	190000	1.25						
0.58	32900	2519	190000	1.50						
0.64	29500	2268	190000	1.70						
0.71	26600	2054	190000	1.90						
0.80	23400	1821	190000	2.1						
0.90	20800	1605	190000	2.4						
0.53	35600	2755	150000	0.90	K	167R97	DRN	100LS4	1200	632
0.64	28600	2263	150000	1.10	KH	167R97	DRN	100LS4	1160	632
0.66	28800	2182	150000	1.10	K KH	167R97 167R97	DRN DRN	100LS4 100LS4	1200 1160	632 632
0.85	22400	1704	150000	1.45						
1.0	18500	1408	150000	1.70						
1.1	17000	1296	150000	1.90						
1.3	14100	1101	150000	2.3						
1.5	12200	944	150000	2.6						

P _m = 2.2 kW										
n _a rpm	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
0.87	21800	1659	110000	0.80	K KF KA KAF	157R97	DRN	100LS4	800	632
1.1	17800	1365	112300	1.00						
1.2	16000	1229	113100	1.10						
1.3	14200	1093	113900	1.25						
1.5	12200	942	114600	1.45						
1.7	11000	854	115000	1.65						
1.9	9570	756	115400	1.90						
2.7	6980	536	81800	1.85	K KF KA KAF	127R87	DRN	100LS4	510	631
3.1	6110	473	82000	2.1						
3.5	5500	418	82200	2.4						
4.0	4830	367	82300	2.7						
4.4	4320	330	82400	3.0						
1.4	13600	1025	78600	0.95	K KF KA KAF	127R77	DRN	100LS4	490	631
1.6	11900	899	79700	1.10						
1.8	10400	790	80500	1.25						
2.1	9360	704	80900	1.40						
2.4	8090	610	81400	1.60						
2.6	7290	549	81700	1.80						
3.0	6300	477	82000	2.1						
3.5	5550	418	82200	2.3	K KF KA KAF	107R77	DRN	100LS4	330	631
2.4	8150	615	65000	1.00						
2.8	6910	522	65000	1.15						
3.2	6080	461	65000	1.30						
3.6	5380	408	65000	1.50						
4.0	4830	364	65000	1.65						
4.6	4220	318	65000	1.90						
5.1	3800	286	65000	2.1						
5.8	3330	251	65000	2.4	K KF KA KAF	97R57	DRN	100LS4	200	631
3.8	5110	382	39800	0.85						
4.2	4540	342	40000	0.95						
4.8	4120	305	40000	1.05						
5.6	3470	258	40000	1.25						
6.2	3130	232	40000	1.35						
7.3	2680	199	40000	1.60	K KF KA KAF	97	DRN	100LS4	175	603
8.2	2550	176.05*	40000	1.70						
9.5	2210	153.21*	40000	1.95						
10	2030	140.28	40000	2.1						
12	1790	123.93*	40000	2.4	K KF KA KAF	97	DRN	100LS4	175	603
14	1520	105.13	40000	2.8						
15	1400	96.80	40000	3.1						
9.8	2130	147.32*	27900	1.25						
11	1830	126.91*	28200	1.45						
13	1670	115.82	28300	1.60	K KF KA KAF	87	DRN	100LS4	115	597
14	1480	102.71*	28500	1.80						
17	1250	86.34	28600	2.2						
18	1140	79.34	28700	2.4						
21	1020	70.46	28800	2.6						
23	910	63.00*	28800	3.0						
13	1640	113.56	14700	0.95						
15	1400	97.05	16300	1.10						
16	1280	88.97	17000	1.20	K KF KA KAF	77	DRN	100LS4	81	591
19	1130	78.07	17800	1.35						
20	1070	73.99	18000	1.45						
22	930	64.75	18500	1.65						
25	840	58.34	18800	1.85						
28	740	51.18	19200	2.1						
32	650	45.16	19400	2.4						
36	580	40.04	19500	2.7						
41	505	35.20	19700	3.0						
47	445	30.89	19800	3.5	K KF KA KAF	77	DRN	100LS4	81	592
50	420	29.27	19800	3.7						
57	370	25.62	19900	4.2						


P_m = 2.2 kW


n _a rpm	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
24	870	60.66	9750	0.95	K KF KA KAF	67	DRN	100LS4	56	585
25	820	57.28	10200	1.00						
30	705	48.77	11200	1.15						
33	640	44.32	11600	1.30						
38	555	38.39	12100	1.45						
41	515	35.62	12300	1.60						
48	435	30.22	12700	1.85	K KF KA KAF	67	DRN	100LS4	56	585
53	395	27.28	12800	2.1						
60	345	24.00	13000	2.3						
64	325	22.66	13000	2.4						
75	275	19.30	13000	2.7						
83	250	17.54	13000	2.9						
95	220	15.19	13000	3.2						
110	191	13.22	13000	3.5						
116	181	12.48	13000	2.9						
136	154	10.63	13000	3.2						
150	140	9.66	13000	3.4						
173	121	8.37	13000	3.6						
199	105	7.28	12700	4.0						
279	75	5.20	11600	4.6						
33	640	44.43	7040	0.95	K KF KA KAF	57	DRN	100LS4	50	579
38	555	38.49	7970	1.10						
41	515	35.70	8290	1.15						
48	435	30.28	8230	1.35						
53	395	27.34	8140	1.50	K KF KA KAF	57	DRN	100LS4	50	579
60	345	24.05	8000	1.70						
64	325	22.71	7930	1.80						
75	280	19.34	7730	2.0						
83	250	17.57	7590	2.2						
95	220	15.22	7380	2.4						
109	192	13.25	7170	2.7						
122	173	11.92	6850	2.4						
129	163	11.26	6770	2.5	K KF KA KAF	49	DRN	100LS4	55	575
38	550	37.98	6820	0.90						
42	500	34.81	6840	1.00						
47	440	30.55	6840	1.15						
50	415	28.95	6830	1.20						
57	365	25.34	6780	1.35						
64	330	22.83	6720	1.50						
72	290	20.03	6620	1.70						
82	255	17.67	6510	1.95						
93	225	15.67	6400	2.2						
108	194	13.38	6220	2.4						
128	165	11.37	6450	3.0						
139	151	10.42	6310	3.2						
159	132	9.14	6090	3.8						
56	375	25.91	5260	1.05	K KF KA KAF	47	DRN	100LS4	44	569
66	315	21.81	5260	1.25						
74	280	19.58	5240	1.40						
86	240	16.86	5180	1.55						
91	225	15.86	5140	1.65	K KF KA KAF	47	DRN	100LS4	44	569
106	198	13.65	5050	1.80						
119	177	12.19	4970	2.00						
123	170	11.77	4870	1.65						
137	153	10.56	4790	1.85						
159	132	9.10	4660	2.1						

P_m = 2.2 kW										
n_a rpm	M_a Nm	i	F_{Ra}¹⁾ N	SEW f_B					m kg	
59	350	24.40	4770	0.85	K KF KA KAF	39	DRN	100LS4	43	565
63	330	23.04	4800	0.90						
74	280	19.62	4820	1.05						
81	255	17.83	4820	1.10						
94	220	15.44	4790	1.25						
108	195	13.44	4730	1.40						
137	154	10.61	5040	1.85						
161	130	9.00	4860	2.3						
178	118	8.12	4740	2.6						
203	104	7.15	4600	2.9						
215	98	6.75	4530	3.1						
252	83	5.75	4350	3.3						
278	76	5.22	4240	3.4						
320	66	4.52	4080	3.7						
368	57	3.94	3930	3.8						
111	190	13.08	2380	0.85	K KF KA KAF	37	DRN	100LS4	37	559
138	152	10.49	2430	1.05						
163	129	8.91	2440	1.25						
182	115	7.96	2430	1.35						
213	98	6.80	2400	1.50						
228	92	6.37	2390	1.55						
270	78	5.36	2340	1.80						
364	58	3.98	2240	2.2						


P_m = 3.0 kW										
n_a rpm	M_a Nm	i	F_{Ra}¹⁾ N	SEW f_B					m kg	
0.52	48700	2818	190000	1.05	K KH	187R97	DRN	100L4	1790	632
0.48	55100	3062	190000	0.90	K KH	187R97	DRN	100L4	1790	632
0.58	45100	2519	190000	1.10						
0.64	40500	2268	190000	1.25						
0.71	36500	2054	190000	1.35						
0.80	32200	1821	190000	1.55						
0.91	28500	1605	190000	1.75						
1.0	24400	1395	190000	2.0						
1.2	21100	1196	190000	2.4						
0.85	30600	1704	150000	1.05	K KH	167R97	DRN	100L4	1210	632
1.0	25300	1408	150000	1.25						
1.1	23300	1296	150000	1.35						
1.3	19500	1101	150000	1.65						
1.5	16800	944	150000	1.90						
1.7	14700	843	150000	2.2						
1.9	13300	757	150000	2.4	K KF KA KAF	157R97	DRN	100L4	810	632
1.2	21900	1229	109900	0.80						
1.3	19500	1093	111400	0.90						
1.5	16800	942	112800	1.05						
1.7	15200	854	113500	1.20						
1.9	13200	756	114300	1.35						
2.6	10000	567	115300	1.80						
2.9	8930	504	115600	2.0						
2.7	9580	536	80900	1.35	K KF KA KAF	127R87	DRN	100L4	520	631
3.1	8400	473	81300	1.55						
3.5	7550	418	81600	1.70						
4.0	6610	367	81900	1.95						
4.4	5920	330	82100	2.2						
5.1	5080	287	82300	2.6						
1.8	14200	790	77400	0.90	K KF KA KAF	127R77	DRN	100L4	495	631
2.1	12700	704	79300	1.00						
2.4	11000	610	80200	1.20						
2.6	9950	549	80700	1.30						
3.0	8610	477	81200	1.50						
3.5	7580	418	81600	1.70						

P_m = 3.0 kW


n _a rpm	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
3.2	8310	461	65000	0.95	K KF KA KAF	107R77	DRN	100L4	335	631
3.6	7360	408	65000	1.10						
4.0	6590	364	65000	1.20						
4.6	5760	318	65000	1.40						
5.1	5190	286	65000	1.55						
5.8	4540	251	65000	1.75						
6.6	4000	222	65000	2.0						
7.4	3540	196	65000	2.3						
8.4	3170	174	65000	2.3						
9.4	2800	154	65000	2.6						
10	2540	140	65000	2.8	K KF KA KAF	97R57	DRN	100L4	205	631
5.6	4730	258	40000	0.90						
6.3	4260	232	40000	1.00						
7.3	3660	199	40000	1.15						
10	2820	143.47*	65000	2.8						
12	2380	121.46	65000	3.4						
8.3	3460	176.05*	40000	1.25						
9.5	3010	153.21*	40000	1.45						
10	2760	140.28	40000	1.55						
12	2430	123.93*	40000	1.75						
14	2060	105.13	40000	2.1	K KF KA KAF	97	DRN	100L4	185	603
15	1900	96.80	40000	2.3						
17	1700	86.52	40000	2.5						
19	1530	77.89*	40000	2.8						
21	1380	70.54	40000	3.1						
23	1230	62.55	40000	3.5						
26	1110	56.55	40000	3.9						
9.9	2890	147.32*	27000	0.95						
11	2490	126.91*	27500	1.10						
13	2270	115.82	27800	1.20						
14	2020	102.71*	28000	1.35	K KF KA KAF	87	DRN	100L4	125	597
17	1690	86.34	28300	1.60						
18	1560	79.34	28400	1.75						
21	1380	70.46	28600	1.95						
23	1230	63.00*	28600	2.2						
26	1110	56.64	28700	2.4						
30	960	49.16	28800	2.8						
33	860	44.02	28800	3.0						
40	715	36.52*	28200	3.5						
16	1750	88.97	13800	0.90						
19	1530	78.07	15500	1.00	K KF KA KAF	77	DRN	100L4	88	591
20	1450	73.99	16000	1.05						
22	1270	64.75	17100	1.20						
25	1140	58.34	17700	1.35						
28	1000	51.18	18300	1.55						
32	880	45.16	18700	1.75						
36	785	40.04	19000	1.95						
41	690	35.20	19300	2.2						
47	605	30.89	19500	2.6						
33	870	44.32	9820	0.95						
38	755	38.39	10900	1.05	K KF KA KAF	67	DRN	100L4	63	585
41	700	35.62	11300	1.15						
48	590	30.22	11900	1.40						
53	535	27.28	12200	1.55						
61	470	24.00	12500	1.70						

P _m = 3.0 kW										
n _a rpm	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
64	445	22.66	12600	1.75	K KF KA KAF	67	DRN	100L4	63	585
75	375	19.30	12900	2.0						
83	340	17.54	13000	2.2						
96	295	15.19	13000	2.3						
110	260	13.22	13000	2.6						
117	245	12.48	13000	2.2						
137	205	10.63	13000	2.4						
151	190	9.66	13000	2.5						
48	595	30.28	7190	1.00	K KF KA KAF	57	DRN	100L4	57	579
53	535	27.34	7190	1.10						
61	470	24.05	7170	1.25						
64	445	22.71	7150	1.35	K KF KA KAF	57	DRN	100L4	57	579
75	380	19.34	7060	1.50						
83	345	17.57	6980	1.60						
96	295	15.22	6860	1.80						
110	260	13.25	6710	1.95						
122	230	11.92	6380	1.75						
129	220	11.26	6330	1.85						
152	189	9.59	6160	2.2						
167	171	8.71	6040	2.3						
193	148	7.55	5870	2.5						
222	129	6.57	5700	2.7						
310	92	4.69	5270	3.2						
48	600	30.55	5690	0.85	K KF KA KAF	49	DRN	100L4	63	575
50	565	28.95	5740	0.90						
57	495	25.34	5820	1.00						
64	445	22.83	5860	1.10						
73	390	20.03	5860	1.25						
82	345	17.67	5840	1.45						
93	305	15.67	5800	1.60						
109	260	13.38	5710	1.80						
128	220	11.37	6160	2.2						
140	200	10.42	6050	2.3						
159	180	9.14	5860	2.8						
168	170	8.66	5790	2.9						
192	149	7.58	5600	3.4						
213	134	6.83	5460	3.7						
74	385	19.58	4450	1.05	K KF KA KAF	47	DRN	100L4	51	569
86	330	16.86	4500	1.15						
92	310	15.86	4510	1.20						
107	265	13.65	4500	1.35	K KF KA KAF	47	DRN	100L4	51	569
119	235	12.19	4480	1.45						
124	230	11.77	4360	1.20						
138	205	10.56	4340	1.35						
160	179	9.10	4280	1.55						
170	168	8.56	4250	1.60						
198	145	7.36	4160	1.75						
221	129	6.58	4090	1.85						
250	114	5.81	4000	2.0						
314	91	4.64	3830	2.2						
82	350	17.83	4010	0.85	K KF KA KAF	39	DRN	100L4	50	565
94	300	15.44	4090	0.90						
108	260	13.44	4120	1.00						
137	205	10.61	4720	1.35						
162	177	9.00	4580	1.70						
179	160	8.12	4490	1.90						
204	141	7.15	4380	2.1						
216	133	6.75	4320	2.3						
253	113	5.75	4170	2.4						
279	103	5.22	4080	2.5						
322	89	4.52	3940	2.7						
370	77	3.94	3800	2.8						
518	55	2.81	3480	3.1						

P_m = 3.0 kW


n _a rpm	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
163	175	8.91	2020	0.90						
183	157	7.96	2050	1.00	K	37	DRN	100L4	45	559
214	134	6.80	2080	1.10	KF	37	DRN	100L4	47	560
229	125	6.37	2090	1.15	KA	37	DRN	100L4	44	561
271	106	5.36	2090	1.35	KAF	37	DRN	100L4	46	560
366	78	3.98	2040	1.60						

P_m = 4.0 kW


n _a rpm	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
1.8	19400	835	190000	2.6	K	187R107	DRN	112M4	1840	632
2.8	12200	520	190000	4.1	KH	187R107	DRN	112M4	1780	632
0.58	60200	2519	190000	0.85						
0.65	54100	2268	190000	0.90						
0.71	48800	2054	190000	1.00						
0.80	43100	1821	190000	1.15						
0.91	38200	1605	190000	1.30	K	187R97	DRN	112M4	1800	632
1.0	32700	1395	190000	1.55	KH	187R97	DRN	112M4	1730	632
1.2	28300	1196	190000	1.75						
1.4	24700	1046	190000	2.0						
1.6	22300	945	190000	2.2						
1.0	33800	1408	150000	0.95						
1.1	31000	1296	150000	1.05						
1.3	26100	1101	150000	1.25						
1.6	22400	944	150000	1.40	K	167R97	DRN	112M4	1210	632
1.7	19800	843	150000	1.60	KH	167R97	DRN	112M4	1180	632
1.9	17800	757	150000	1.80						
2.3	14900	632	150000	2.1						
1.7	20300	854	110900	0.90	K	157R97	DRN	112M4	820	632
1.9	17700	756	112300	1.00	KF	157R97	DRN	112M4	900	632
2.6	13400	567	114200	1.35	KA	157R97	DRN	112M4	780	632
2.9	11900	504	114700	1.50	KAF	157R97	DRN	112M4	840	632
3.4	10100	434	115200	1.75						
2.7	12700	536	79300	1.00						
3.1	11200	473	80100	1.15	K	127R87	DRN	112M4	530	631
3.5	10000	418	80600	1.30	KF	127R87	DRN	112M4	570	631
4.0	8810	367	81200	1.50	KA	127R87	DRN	112M4	500	631
4.4	7900	330	81500	1.65	KAF	127R87	DRN	112M4	540	631
5.1	6800	287	81800	1.90						
5.8	6010	253	82100	2.2						
2.4	14700	610	76600	0.90	K	127R77	DRN	112M4	510	631
2.7	13200	549	79000	1.00	KF	127R77	DRN	112M4	550	631
3.1	11400	477	80000	1.15	KA	127R77	DRN	112M4	480	631
3.5	10000	418	80600	1.30	KAF	127R77	DRN	112M4	520	631
4.0	8770	364	65000	0.90						
4.6	7670	318	65000	1.05						
5.1	6900	286	65000	1.15						
5.8	6050	251	65000	1.30	K	107R77	DRN	112M4	345	631
6.6	5330	222	65000	1.50	KF	107R77	DRN	112M4	360	631
7.4	4720	196	65000	1.70	KA	107R77	DRN	112M4	320	631
8.4	4220	174	65000	1.70	KAF	107R77	DRN	112M4	340	631
9.5	3730	154	65000	1.95						
10	3390	140	65000	2.1						
7.3	4860	199	40000	0.90	K	97R57	DRN	112M4	215	631
					KF	97R57	DRN	112M4	235	631
					KA	97R57	DRN	112M4	200	631
					KAF	97R57	DRN	112M4	225	631


P _m = 4.0 kW										
n _a rpm	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
10	3740	143.47*	65000	2.1	K KF KA KAF	107	DRN	112M4	305	609
12	3160	121.46	65000	2.5						
13	2930	112.41*	65000	2.7						
15	2620	100.75	65000	3.0						
16	2370	90.96*	65000	3.4						
18	2150	82.61	65000	3.7						
20	1910	73.30	65000	4.2						
9.6	3990	153.21*	40000	1.10	K	97	DRN	112M4	190	603
10	3660	140.28	40000	1.15	KF	97	DRN	112M4	210	604
12	3230	123.93*	40000	1.35	KA	97	DRN	112M4	175	605
					KAF	97	DRN	112M4	200	604
14	2740	105.13	40000	1.55	K KF KA KAF	97	DRN	112M4	190	603
15	2520	96.80	40000	1.70						
17	2250	86.52	40000	1.90						
19	2030	77.89*	40000	2.1						
21	1840	70.54	40000	2.3						
13	3020	115.82	26900	0.90	K	87	DRN	112M4	135	597
14	2670	102.71*	27300	1.00	KF	87	DRN	112M4	140	598
17	2250	86.34	27800	1.20	KA	87	DRN	112M4	120	599
18	2070	79.34	28000	1.30	KAF	87	DRN	112M4	135	598
21	1830	70.46	28200	1.45	K KF KA KAF	87	DRN	112M4	135	597
23	1640	63.00*	28400	1.65						
26	1470	56.64	28500	1.85						
30	1280	49.16	28600	2.1						
33	1140	44.02	28200	2.3						
40	950	36.52*	27200	2.6						
23	1680	64.75	14300	0.90	K KF KA KAF	77	DRN	112M4	97	591
25	1520	58.34	15600	1.00						
29	1330	51.18	16700	1.15						
32	1170	45.16	17500	1.30						
37	1040	40.04	18100	1.50						
38	1000	38.39	18300	1.50						
42	910	35.20	18600	1.70	K KF KA KAF	77	DRN	112M4	97	591
47	800	30.89	19000	1.90						
50	760	29.27	19100	2.0						
57	665	25.62	19300	2.3						
63	600	23.08	19500	2.6						
72	525	20.25	19600	2.8						
48	785	30.22	10600	1.05	K KF KA KAF	67	DRN	112M4	72	585
54	710	27.28	11200	1.15						
61	625	24.00	11700	1.30						
65	590	22.66	11900	1.30						
76	500	19.30	12400	1.50	K KF KA KAF	67	DRN	112M4	72	585
84	455	17.54	12600	1.60						
96	395	15.19	12800	1.75						
111	340	13.22	13000	1.95						
117	325	12.48	13000	1.65						
138	275	10.63	13000	1.80						
152	250	9.66	12800	1.90						
175	215	8.37	12400	2.0						
201	190	7.28	12000	2.2						
282	136	5.20	11100	2.6						
61	625	24.05	6140	0.95	K KF KA KAF	57	DRN	112M4	67	579
64	590	22.71	6180	1.00						
76	500	19.34	6230	1.15						
83	455	17.57	6230	1.20						
96	395	15.22	6200	1.35						
110	345	13.25	6140	1.50						
123	310	11.92	5800	1.35						
130	290	11.26	5780	1.40						
153	250	9.59	5680	1.60						
168	225	8.71	5620	1.70						
194	197	7.55	5500	1.85						
223	171	6.57	5380	2.0						
312	122	4.69	5030	2.4						

P_m = 4.0 kW


n _a rpm	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
64	595	22.83	4780	0.85						
73	520	20.03	4920	0.95						
83	460	17.67	5010	1.10						
93	405	15.67	5060	1.20						
109	345	13.38	5080	1.35						
129	295	11.37	5810	1.65	K	49	DRN	112M4	72	575
141	270	10.42	5720	1.75	KF	49	DRN	112M4	73	576
160	235	9.14	5580	2.1	KA	49	DRN	112M4	69	577
169	225	8.66	5520	2.2	KAF	49	DRN	112M4	74	576
193	198	7.58	5360	2.5						
214	178	6.83	5240	2.8						
244	156	5.99	5080	3.2						
277	138	5.29	4930	3.5						
312	122	4.69	4780	3.8						
163	230	9.00	4240	1.30						
180	210	8.12	4180	1.40						
205	187	7.15	4100	1.60	K	39	DRN	112M4	60	565
217	176	6.75	4060	1.70	KF	39	DRN	112M4	61	566
255	150	5.75	3950	1.85	KA	39	DRN	112M4	59	567
280	136	5.22	3880	1.90	KAF	39	DRN	112M4	60	566
324	118	4.52	3760	2.0						
372	103	3.94	3650	2.1						
521	73	2.81	3370	2.3						

P_m = 5.5 kW


n _a rpm	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
0.80	59900	1821	190000	0.85						
0.91	52900	1605	190000	0.95						
1.0	45600	1395	190000	1.10						
1.2	39300	1196	190000	1.25	K	187R97	DRN	132S4	1810	632
1.4	34400	1046	190000	1.45	KH	187R97	DRN	132S4	1740	632
1.6	31000	945	190000	1.60						
2.0	24200	738	190000	2.1						
2.4	20300	621	190000	2.4						
1.3	36200	1101	150000	0.90						
1.6	31100	944	150000	1.05						
1.7	27500	843	150000	1.15						
1.9	24800	757	150000	1.30	K	167R97	DRN	132S4	1230	632
2.3	20800	632	150000	1.55	KH	167R97	DRN	132S4	1190	632
2.6	18200	561	150000	1.75						
3.0	15800	481	150000	2.0						
3.4	13700	423	150000	2.3						
2.2	21500	661	110200	0.85						
2.6	18600	567	111900	0.95	K	157R97	DRN	132S4	830	632
2.9	16500	504	112900	1.10	KF	157R97	DRN	132S4	910	632
3.4	14100	434	113900	1.25	KA	157R97	DRN	132S4	800	632
3.8	12300	379	114600	1.45	KAF	157R97	DRN	132S4	850	632
4.4	10800	333	115000	1.65						
3.5	13900	418	78000	0.95						
4.0	12100	367	79600	1.05						
4.4	10900	330	80200	1.20	K	127R87	DRN	132S4	540	631
5.1	9440	287	80900	1.40	KF	127R87	DRN	132S4	580	631
5.8	8350	253	81300	1.55	KA	127R87	DRN	132S4	510	631
6.9	7010	213	81800	1.85	KAF	127R87	DRN	132S4	550	631
7.3	6680	200	81900	1.80						
8.8	5530	166	82200	2.2						
10.0	4880	147	82300	2.5						
6.6	7370	222	65000	1.10	K	107R77	DRN	132S4	355	631
7.4	6530	196	65000	1.20	KF	107R77	DRN	132S4	370	631
8.4	5830	174	65000	1.25	KA	107R77	DRN	132S4	330	631
9.5	5170	154	65000	1.40	KAF	107R77	DRN	132S4	355	631
10	4690	140	65000	1.55						

P_m = 5.5 kW										
n_a rpm	M_a Nm	i	F_{Ra}¹⁾ N	SEW f_B					m kg	
10	5150	143.47*	65000	1.55	K	107	DRN	132S4	315	609
12	4360	121.46	65000	1.85					330	610
13	4040	112.41*	65000	2.00					290	611
14	3620	100.75	65000	2.2					315	610
16	3260	90.96*	65000	2.4						
18	2960	82.61	65000	2.7	KAF	107	DRN	132S4		
12	4450	123.93*	40000	0.95	K	97	DRN	132S4	205	603
14	3770	105.13	40000	1.15	KF	97	DRN	132S4	225	604
15	3470	96.80	40000	1.25	KA	97	DRN	132S4	185	605
17	3110	86.52	40000	1.40	KAF	97	DRN	132S4	210	604
19	2800	77.89*	40000	1.55	K	97	DRN	132S4	205	603
21	2530	70.54	40000	1.70	KF	97	DRN	132S4	225	604
23	2240	62.55	40000	1.90	KA	97	DRN	132S4	185	605
26	2030	56.55	39600	2.1	KAF	97	DRN	132S4	210	604
30	1720	47.93*	38400	2.5						
17	3100	86.34	26700	0.85	K	87	DRN	132S4	145	597
18	2850	79.34	27100	0.95	KF	87	DRN	132S4	155	598
21	2530	70.46	27500	1.05	KA	87	DRN	132S4	130	599
23	2260	63.00*	27400	1.20	KAF	87	DRN	132S4	145	598
26	2030	56.64	27200	1.35						
30	1760	49.16	26800	1.55	K	87	DRN	132S4	145	597
33	1580	44.02	26400	1.65	KF	87	DRN	132S4	155	598
40	1310	36.52*	25700	1.90	KA	87	DRN	132S4	130	599
47	1120	31.39	25100	2.4	KAF	87	DRN	132S4	145	598
52	1000	27.88	24600	2.6						
32	1620	45.16	14800	0.95	K	77	DRN	132S4	110	591
36	1430	40.04	16100	1.10	KF	77	DRN	132S4	115	592
47	1110	30.89	17900	1.40	KA	77	DRN	132S4	100	593
50	1050	29.27	18100	1.45	KAF	77	DRN	132S4	110	592
57	920	25.62	18600	1.70						
63	820	23.08	18900	1.85	K	77	DRN	132S4	110	591
72	725	20.25	19200	2.1	KF	77	DRN	132S4	115	592
82	640	17.87	19400	2.3	KA	77	DRN	132S4	100	593
92	565	15.84	19100	2.5	KAF	77	DRN	132S4	110	592
108	485	13.52	18500	2.8						
118	440	12.36	17800	2.2						
135	385	10.84	17400	2.5						
61	860	24.00	9910	0.95	K	67	DRN	132S4	84	585
64	810	22.66	10400	0.95	KF	67	DRN	132S4	90	586
76	690	19.30	11300	1.10	KA	67	DRN	132S4	81	587
83	630	17.54	11700	1.15	KAF	67	DRN	132S4	87	586
96	545	15.19	12200	1.30						
111	475	13.22	12500	1.40						
117	445	12.48	12600	1.20	K	67	DRN	132S4	84	585
137	380	10.63	12400	1.30	KF	67	DRN	132S4	90	586
151	345	9.66	12200	1.40	KA	67	DRN	132S4	81	587
175	300	8.37	11900	1.45	KAF	67	DRN	132S4	87	586
201	260	7.28	11600	1.60						
281	187	5.20	10800	1.85						
93	560	15.67	3950	0.85	K	49	DRN	132S4	83	575
109	480	13.38	4130	1.00	KF	49	DRN	132S4	85	576
160	325	9.14	5160	1.50	KA	49	DRN	132S4	80	577
169	310	8.66	5130	1.60	KAF	49	DRN	132S4	85	576
193	270	7.58	5020	1.85						
214	245	6.83	4930	2.0						
244	215	5.99	4810	2.3						
276	190	5.29	4690	2.6						
312	169	4.69	4570	2.8						
365	144	4.00	4410	3.1						

P_m = 7.5 kW


n _a rpm	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
1.8	37100	835	190000	1.35	K	187R107	DRN	132M4	1870	632
2.0	32200	729	190000	1.55	KH	187R107	DRN	132M4	1810	632
2.4	27500	622	190000	1.80						
1.2	53700	1196	190000	0.95						
1.4	46900	1046	190000	1.05						
1.6	42300	945	190000	1.20	K	187R97	DRN	132M4	1830	632
2.0	33100	738	190000	1.50	KH	187R97	DRN	132M4	1760	632
2.4	27800	621	190000	1.80						
2.8	23500	527	190000	2.1						
1.7	37700	843	150000	0.85						
1.9	33900	757	150000	0.95						
2.3	28300	632	150000	1.15	K	167R97	DRN	132M4	1240	632
2.6	24900	561	150000	1.30	KH	167R97	DRN	132M4	1210	632
3.0	21500	481	150000	1.50						
3.5	18800	423	150000	1.70						
4.0	16400	369	150000	1.95						
3.4	19300	434	111500	0.95	K	157R97	DRN	132M4	850	632
3.9	16800	379	112700	1.05	KF	157R97	DRN	132M4	930	632
4.4	14800	333	113600	1.20	KA	157R97	DRN	132M4	810	632
5.0	12900	291	114400	1.40	KAF	157R97	DRN	132M4	870	632
4.4	14900	330	76200	0.85						
5.1	12800	287	79300	1.00	K	127R87	DRN	132M4	560	631
5.8	11300	253	80000	1.15	KF	127R87	DRN	132M4	600	631
6.9	9570	213	80900	1.35	KA	127R87	DRN	132M4	530	631
7.3	9110	200	81000	1.30	KAF	127R87	DRN	132M4	560	631
8.8	7540	166	81600	1.60						
10	6650	147	81900	1.80						
10	7120	146.07	81700	1.80						
11	6640	136.14	81900	1.95	K	127	DRN	132M4	490	615
12	5970	122.48	82100	2.2	KF	127	DRN	132M4	530	616
13	5370	110.18	82200	2.4	KA	127	DRN	132M4	460	617
16	4380	89.89	82400	3.0	KAF	127	DRN	132M4	500	616
18	3990	81.98	82500	3.2						
21	3460	70.95*	82600	3.8						
10	6990	143.47*	65000	1.15	K	107	DRN	132M4	335	609
12	5920	121.46	65000	1.35	KF	107	DRN	132M4	350	610
13	5480	112.41*	65000	1.45	KA	107	DRN	132M4	310	611
					KAF	107	DRN	132M4	330	610
15	4910	100.75	65000	1.65						
16	4430	90.96*	64000	1.80						
18	4030	82.61	63000	2.00	K	107	DRN	132M4	335	609
20	3570	73.30	61700	2.2	KF	107	DRN	132M4	350	610
22	3240	66.52*	60600	2.5	KA	107	DRN	132M4	310	611
26	2780	57.17*	58800	2.9	KAF	107	DRN	132M4	330	610
29	2430	49.90	57100	3.2						
35	2060	42.33*	55100	3.6						
40	1800	37.00*	53500	4.0						
15	4720	96.80	38400	0.90	K	97	DRN	132M4	220	603
17	4220	86.52	38300	1.00	KF	97	DRN	132M4	240	604
19	3800	77.89*	38100	1.15	KA	97	DRN	132M4	205	605
21	3440	70.54	37800	1.25	KAF	97	DRN	132M4	230	604
23	3050	62.55	37400	1.40						
26	2750	56.55	37000	1.55	K	97	DRN	132M4	220	603
31	2330	47.93*	36200	1.85	KF	97	DRN	132M4	240	604
35	2040	41.87	35500	2.1	KA	97	DRN	132M4	205	605
38	1860	38.30	35000	2.3	KAF	97	DRN	132M4	230	604
43	1660	34.23	34300	2.6						
23	3070	63.00*	24100	0.90	K	87	DRN	132M4	160	597
26	2760	56.64	24200	1.00	KF	87	DRN	132M4	170	598
30	2390	49.16	24200	1.15	KA	87	DRN	132M4	150	599
33	2140	44.02	24100	1.20	KAF	87	DRN	132M4	165	598
40	1780	36.52*	23800	1.40						


10

P _m = 7.5 kW																
n _a rpm	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg							
47	1530	31.39	23400	1.75	K	87	DRN	132M4	160	597						
53	1350	27.88	23100	1.90												
59	1210	24.92	22700	2.1												
66	1090	22.41	22400	2.1												
75	940	19.45	21800	2.4												
84	840	17.42	21400	2.6												
92	780	16.00	20500	2.3	KAF	87	DRN	132M4	165	598						
102	700	14.45	20600	3.0												
											K	77	DRN	132M4	125	591
48	1500	30.89	15700	1.05												
50	1420	29.27	16200	1.10												
57	1240	25.62	17200	1.25												
64	1120	23.08	17800	1.40												
73	980	20.25	18400	1.50	KAF	77	DRN	132M4	125	592						
											K	77	DRN	132M4	125	591
82	870	17.87	18500	1.65												
93	770	15.84	18200	1.80												
109	655	13.52	17700	2.0												
119	600	12.36	17000	1.65												
135	525	10.84	16600	1.85	KA	77	DRN	132M4	120	593						
154	465	9.56	16200	2.0												
173	410	8.48	15800	2.2												
203	350	7.24	15300	2.3												
											KAF	77	DRN	132M4	125	592
82	870	17.87	18500	1.65												
93	770	15.84	18200	1.80												
109	655	13.52	17700	2.0												
119	600	12.36	17000	1.65												
135	525	10.84	16600	1.85	K	49	DRN	132M4	100	575						
154	465	9.56	16200	2.0												
173	410	8.48	15800	2.2												
203	350	7.24	15300	2.3												
											KF	49	DRN	132M4	105	576
161	445	9.14	4610	1.10												
169	420	8.66	4600	1.20												
194	365	7.58	4560	1.35												
215	330	6.83	4510	1.50												
245	290	5.99	4440	1.70	KA	49	DRN	132M4	98	577						
278	255	5.29	4370	1.90												
313	225	4.69	4280	2.0												
367	195	4.00	4170	2.2												
											KAF	49	DRN	132M4	105	576
161	445	9.14	4610	1.10												
169	420	8.66	4600	1.20												
194	365	7.58	4560	1.35												
215	330	6.83	4510	1.50												


P _m = 9.2 kW										
n _a rpm	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
1.8	45700	835	190000	1.10	K KH	187R107 187R107	DRN DRN	132L4 132L4	1880 1810	632 632
2.0	39700	729	190000	1.25						
2.4	33900	622	190000	1.45						
2.8	28700	520	190000	1.75						
3.2	25000	454	190000	2.0						
1.4	57600	1046	190000	0.85	K KH	187R97 187R97	DRN DRN	132L4 132L4	1830 1770	632 632
1.6	52000	945	190000	0.95						
2.0	40600	738	190000	1.25						
2.4	34100	621	190000	1.45						
2.8	28900	527	190000	1.75						
4.6	17500	318	150000	1.80	K KH	167R107 167R107	DRN DRN	132L4 132L4	1300 1260	632 632
5.3	15200	278	150000	2.1						
6.0	13200	244	150000	2.4						
6.9	11500	213	150000	2.8						
7.1	11200	206	150000	2.8						
2.3	34800	632	150000	0.90	K KH	167R97 167R97	DRN DRN	132L4 132L4	1250 1210	632 632
2.6	30700	561	150000	1.05						
3.1	26500	481	150000	1.20						
3.5	23100	423	150000	1.40						
4.0	20200	369	150000	1.60						
3.8	20800	385	110600	0.85	K KF KA KAF	157R107 157R107 157R107 157R107	DRN DRN DRN DRN	132L4 132L4 132L4 132L4	910 980 870 930	632 632 632 632
4.5	17400	325	112500	1.05						
4.9	16200	299	113000	1.10						
5.8	13700	253	114100	1.30						
6.4	12300	230	114600	1.45						
3.9	20700	379	110700	0.85	K KF KA KAF	157R97 157R97 157R97 157R97	DRN DRN DRN DRN	132L4 132L4 132L4 132L4	860 940 820 880	632 632 632 632
4.4	18200	333	112000	1.00						
5.0	15900	291	113200	1.15						

P_m = 9.2 kW


n _a rpm	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
5.8	13900	253	78000	0.95	K	127R87	DRN	132L4	560	631
6.9	11700	213	79900	1.10	KF	127R87	DRN	132L4	610	631
7.3	11100	200	80100	1.05	KA	127R87	DRN	132L4	540	631
8.8	9260	166	81000	1.30	KAF	127R87	DRN	132L4	570	631
10	8170	147	81400	1.45						
11	8130	136.14	81400	1.60	K	127	DRN	132L4	500	615
12	7320	122.48	81700	1.80	KF	127	DRN	132L4	540	616
13	6580	110.18	81900	1.95	KA	127	DRN	132L4	470	617
16	5370	89.89	82200	2.4	KAF	127	DRN	132L4	510	616
18	4890	81.98	82300	2.6						
13	6710	112.41*	62300	1.20	K	107	DRN	132L4	345	609
15	6020	100.75	61700	1.35	KF	107	DRN	132L4	355	610
16	5430	90.96*	61000	1.45	KA	107	DRN	132L4	315	611
					KAF	107	DRN	132L4	340	610
18	4930	82.61	60300	1.60						
20	4380	73.30	59300	1.85	K	107	DRN	132L4	345	609
22	3970	66.52*	58400	2.0	KF	107	DRN	132L4	355	610
26	3410	57.17*	56900	2.3	KA	107	DRN	132L4	315	611
29	2980	49.90	55500	2.6	KAF	107	DRN	132L4	340	610
35	2520	42.33*	53700	2.9						
19	4650	77.89*	35100	0.90	K	97	DRN	132L4	230	603
21	4210	70.54	35100	1.00	KF	97	DRN	132L4	250	604
24	3730	62.55	35000	1.15	KA	97	DRN	132L4	210	605
26	3370	56.55	34800	1.25	KAF	97	DRN	132L4	235	604
31	2860	47.93*	34400	1.50						
35	2500	41.87	33900	1.70	K	97	DRN	132L4	230	603
38	2280	38.30	33500	1.90	KF	97	DRN	132L4	250	604
43	2040	34.23	33000	2.1	KA	97	DRN	132L4	210	605
48	1840	30.82	32400	2.3	KAF	97	DRN	132L4	235	604
53	1660	27.91	31900	2.6						
59	1470	24.75	31200	2.9						
30	2930	49.16	22000	0.90	K	87	DRN	132L4	170	597
33	2630	44.02	22200	1.00	KF	87	DRN	132L4	180	598
40	2180	36.52*	22200	1.15	KA	87	DRN	132L4	160	599
47	1870	31.39	22000	1.45	KAF	87	DRN	132L4	170	598
53	1660	27.88	21900	1.55						
59	1480	24.92	21600	1.70						
66	1330	22.41	21400	1.70						
76	1160	19.45	21000	2.00	K	87	DRN	132L4	170	597
84	1040	17.42	20600	2.1	KF	87	DRN	132L4	180	598
92	950	16.00	19700	1.90	KA	87	DRN	132L4	160	599
102	860	14.45	20000	2.4	KAF	87	DRN	132L4	170	598
117	750	12.56	19500	2.7						
132	665	11.17	18500	2.2						
147	595	10.00	18200	2.5						
64	1370	23.08	16500	1.10	K	77	DRN	132L4	135	591
73	1200	20.25	17400	1.25	KF	77	DRN	132L4	145	592
82	1060	17.87	17600	1.35	KA	77	DRN	132L4	125	593
93	940	15.84	17300	1.50	KAF	77	DRN	132L4	135	592
109	800	13.52	17000	1.65						
119	735	12.36	16200	1.35	K	77	DRN	132L4	135	591
136	645	10.84	15900	1.55	KF	77	DRN	132L4	145	592
154	570	9.56	15600	1.65	KA	77	DRN	132L4	125	593
173	505	8.48	15300	1.75	KAF	77	DRN	132L4	135	592
203	430	7.24	14900	1.90						

P_m = 11.0 kW										
n_a rpm	M_a Nm	i	F_{Ra}¹⁾ N	SEW f_B					m kg	
1.8	54700	835	190000	0.90	K KH	187R107 187R107	DRN DRN	160M4 160M4	1910 1850	632 632
2.0	47600	729	190000	1.05						
2.4	40600	622	190000	1.25						
2.8	34400	520	190000	1.45						
3.2	29900	454	190000	1.65						
4.1	23100	355	190000	2.2	K KH	187R97 187R97	DRN DRN	160M4 160M4	1870 1800	632 632
2.0	48600	738	190000	1.05						
2.4	40800	621	190000	1.20						
2.8	34500	527	190000	1.45						
4.6	21000	318	150000	1.50						
5.3	18300	278	150000	1.75	K KH	167R107 167R107	DRN DRN	160M4 160M4	1330 1290	632 632
6.0	15800	244	150000	2.0						
6.9	13800	213	150000	2.3						
7.2	13400	206	150000	2.4						
2.6	36700	561	150000	0.85						
3.1	31600	481	150000	1.00	K KH	167R97 167R97	DRN DRN	160M4 160M4	1280 1250	632 632
3.5	27700	423	150000	1.15						
4.0	24200	369	150000	1.30						
4.4	21800	333	110000	0.80						
5.1	19000	291	111600	0.95						
6.9	14000	213	77900	0.95	K KF KA KAF	157R97 157R97 157R97 157R97	DRN DRN DRN DRN	160M4 160M4 160M4 160M4	890 970 850 910	632 632 632 632
7.4	13300	200	79000	0.90						
8.9	11000	166	80200	1.10						
10	9770	147	80800	1.25						
9.0	11700	164.50	150000	2.7						
11	9620	134.99	150000	3.3	K KH KF KA KAF	167 167 157 157 157	DRN DRN DRN DRN DRN	160M4 160M4 160M4 160M4 160M4	1160 1120 760 840 730	627 628 621 622 622
9.8	10700	150.41	115100	1.70						
12	8720	122.39	115600	2.1						
15	7140	100.22	116000	2.5						
16	6530	91.65	116100	2.8						
11	9700	136.14	80800	1.35	K KF KA KAF	127 127 127 127	DRN DRN DRN DRN	160M4 160M4 160M4 160M4	530 570 500 540	615 616 617 616
12	8730	122.48	81200	1.50						
13	7850	110.18	81500	1.65						
16	6410	89.89	82000	2.0						
18	5840	81.98	82100	2.2						
21	5050	70.95*	82300	2.6	K KF KA KAF	107 107 107 107	DRN DRN DRN DRN	160M4 160M4 160M4 160M4	375 390 350 375	609 610 611 610
13	8010	112.41*	57800	1.00						
15	7180	100.75	58200	1.10						
16	6480	90.96*	57900	1.25						
18	5890	82.61	57400	1.35						
20	5220	73.30	56700	1.55	K KF KA KAF	107 107 107 107	DRN DRN DRN DRN	160M4 160M4 160M4 160M4	375 390 350 375	609 610 611 610
22	4740	66.52*	56100	1.70						
26	4070	57.17*	54900	1.95						
30	3550	49.90	53800	2.2						
35	3010	42.33*	52300	2.4						
40	2630	37.00*	51000	2.7	K KF KA KAF	97 97 97 97	DRN DRN DRN DRN	160M4 160M4 160M4 160M4	265 285 245 270	603 604 605 604
21	5030	70.54	32300	0.85						
24	4460	62.55	32500	0.95						
26	4030	56.55	32500	1.05						
31	3410	47.93*	32400	1.25						
35	2980	41.87	32200	1.45	K KF KA KAF	97 97 97 97	DRN DRN DRN DRN	160M4 160M4 160M4 160M4	265 285 245 270	603 604 605 604
38	2730	38.30	31900	1.55						
43	2440	34.23	31600	1.75						
48	2190	30.82	31200	1.95						
53	1980	27.91	30700	2.2						
60	1760	24.75	30200	2.4	K KF KA KAF	87 87 87 87	DRN DRN DRN DRN	160M4 160M4 160M4 160M4	205 210 190 205	597 598 599 598
66	1590	22.37	29700	2.7						
33	3130	44.02	20100	0.85						
40	2600	36.52*	20500	0.95						
47	2230	31.39	20600	1.20						
53	1980	27.88	20500	1.30						
59	1770	24.92	20400	1.40						


P_m = 11.0 kW

n _a rpm	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
66	1590	22.41	20300	1.45	K KF KA KAF	87	DRN	160M4	205	597
76	1380	19.45	20000	1.65						
85	1240	17.42	19800	1.75						
92	1140	16.00	18800	1.60						
102	1030	14.45	19300	2.0						
117	890	12.56	18900	2.2						
132	795	11.17	17900	1.90						
147	710	10.00	17600	2.1						
178	590	8.29	17000	2.4	K KF KA KAF	77	DRN	160M4	165	591
204	510	7.21	16600	2.5						
64	1640	23.08	14700	0.95						
73	1440	20.25	16100	1.05						
82	1270	17.87	16600	1.15						
93	1120	15.84	16500	1.25						
109	960	13.52	16200	1.40						
119	880	12.36	15500	1.15						
136	770	10.84	15300	1.30	K KF KA KAF	77	DRN	160M4	175	592
154	680	9.56	15000	1.40						
174	600	8.48	14800	1.45						
203	515	7.24	14400	1.60						


P_m = 15.0 kW

n _a rpm	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
2.4	55600	622	190000	0.90	K KH	187R107	DRN	160L4	1930	632
2.8	47100	520	190000	1.05						
3.2	41000	454	190000	1.20						
4.2	31700	355	190000	1.60						
5.6	23500	261	190000	2.1						
4.6	28800	318	150000	1.10	K KH	167R107	DRN	160L4	1350	632
5.3	25000	278	150000	1.30						
6.0	21700	244	150000	1.45						
6.9	18900	213	150000	1.70						
7.2	18400	206	150000	1.75						
8.2	15900	180	150000	2.0						
9.2	14400	160	150000	2.2						
6.4	20400	230	110900	0.90	K KF KA KAF	157R107	DRN	160L4	950	632
6.9	19100	213	111600	0.95						
7.9	16500	187	112900	1.10						
9.4	14000	157	113900	1.30						
12	11000	122	115000	1.65						
14	9610	107	115400	1.85	K KH	167	DRN	160L4	1170	627
9.0	15900	164.50	150000	2.0						
11	13100	134.99	150000	2.4	K KF KA KAF	157	DRN	160L4	780	621
9.8	14600	150.41	113700	1.25						
12	11800	122.39	114700	1.50						
15	9730	100.22	114000	1.85						
16	8900	91.65	112300	2.0						
18	7750	79.75	109400	2.3						
11	13200	136.14	79000	1.00						
12	11900	122.48	79800	1.10	K KF KA KAF	127	DRN	160L4	550	615
13	10700	110.18	80400	1.20						
16	8730	89.89	81200	1.50						
18	7960	81.98	81500	1.65						
21	6890	70.95*	81400	1.90						
24	6080	62.60	79800	2.1	K KF KA KAF	107	DRN	160L4	395	609
27	5250	54.07	77800	2.5						
31	4640	47.82	76100	2.8						
16	8830	90.96*	48300	0.90						
18	8020	82.61	49500	1.00						
20	7120	73.30	50500	1.10	K KF KA KAF	107	DRN	160L4	405	610
22	6460	66.52*	51000	1.25						


P_m = 15.0 kW


n _a rpm	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
26	5550	57.17*	50600	1.45	K KF KA KAF	107	DRN	160L4	395	609
30	4840	49.90	50000	1.60						
35	4110	42.33*	49000	1.80						
40	3590	37.00*	48100	2.0						
45	3170	32.69	47200	2.3						
47	3030	31.28*	46900	2.2						
51	2810	29.00	46300	2.6	K KF KA KAF	97	DRN	160L4	280	603
31	4650	47.93*	28100	0.90						
35	4060	41.87	28400	1.05						
38	3720	38.30	28500	1.15						
43	3320	34.23	28500	1.30						
48	2990	30.82	28400	1.45						
53	2710	27.91	28200	1.60	K KF KA KAF	97	DRN	160L4	280	603
60	2400	24.75	28000	1.80						
66	2170	22.37	27700	2.00						
78	1840	18.96	27100	2.3						
89	1600	16.56	26600	2.7						
47	3040	31.39	17300	0.90	K KF KA KAF	87	DRN	160L4	220	597
53	2700	27.88	17600	0.95						
59	2420	24.92	17900	1.05						
66	2170	22.41	18000	1.05						
76	1880	19.45	18000	1.20						
85	1690	17.42	18000	1.30						
92	1550	16.00	16800	1.15	K KF KA KAF	87	DRN	160L4	220	597
102	1400	14.45	17800	1.50						
117	1220	12.56	17600	1.65						
132	1080	11.17	16600	1.40						
147	970	10.00	16400	1.55						
178	800	8.29	16000	1.75						
204	700	7.21	15700	1.85	K KF KA KAF	87	DRN	160L4	220	598
47	3040	31.39	17300	0.90						
53	2700	27.88	17600	0.95						
59	2420	24.92	17900	1.05						
66	2170	22.41	18000	1.05						
76	1880	19.45	18000	1.20						

P_m = 18.5 kW


n _a rpm	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
2.8	58000	520	190000	0.85	K KH	187R107	DRN	180M4	1950	632
3.3	50500	454	190000	1.00						
4.2	39100	355	190000	1.30						
5.7	29000	261	190000	1.70						
6.7	24600	221	190000	2.0						
4.6	35500	318	150000	0.90	K KH	167R107	DRN	180M4	1370	632
5.3	30900	278	150000	1.05						
6.1	26800	244	150000	1.20						
6.9	23400	213	150000	1.35						
7.2	22800	206	150000	1.40						
8.2	19700	180	150000	1.60						
9.3	17700	160	150000	1.80	K KF KA KAF	157R107	DRN	180M4	980	632
11	15000	135	150000	2.1						
12	13100	118	150000	2.4						
7.9	20400	187	110800	0.90						
9.4	17300	157	112500	1.05						
12	13600	122	113800	1.30						
14	11800	107	111900	1.50	K KH	187	DRN	180M4	1780	629
8.2	21400	179.86	190000	2.3						
9.0	19700	165.21	190000	2.5						
10	17200	144.59	190000	2.9						
11	15500	129.69	190000	3.2						
11	16100	134.99	150000	2.00	K KH	167	DRN	180M4	1200	627
13	13100	109.83	150000	2.4						
17	10500	87.86	150000	3.0						

P _m = 18.5 kW										
n _a rpm	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
12	14600	122.39	111500	1.25					800	621
15	11900	100.22	109000	1.50						
16	10900	91.65	107700	1.65						
19	9530	79.75	105400	1.90						
21	8410	70.38	103200	2.1						
24	7290	61.02	100600	2.5						
27	6480	54.29	98300	2.8						
32	5590	46.79	95400	3.2						
39	4540	38.02	91200	4.0						
13	13100	110.18	79100	1.00	K	127	DRN	180M4	570	615
16	10700	89.89	79000	1.20	KF	127	DRN	180M4	610	616
18	9790	81.98	78500	1.35	KA	127	DRN	180M4	540	617
					KAF	127	DRN	180M4	580	616
21	8480	70.95*	77400	1.55					570	615
24	7480	62.60	76300	1.75						
27	6460	54.07	74700	2.0						
31	5710	47.82	73300	2.3						
37	4800	40.19	71100	2.7						
41	4330	36.25	69800	3.0						
47	3740	31.37	67800	3.5						
53	3300	27.68	66100	3.9						
20	8760	73.30	42900	0.90	K	107	DRN	180M4	415	609
22	7950	66.52*	44300	1.00	KF	107	DRN	180M4	425	610
26	6830	57.17*	45800	1.15	KA	107	DRN	180M4	385	611
30	5960	49.90	46600	1.30	KAF	107	DRN	180M4	410	610
35	5050	42.33*	46200	1.45					415	609
40	4420	37.00*	45700	1.65						
45	3900	32.69	45000	1.85						
47	3730	31.28*	44800	1.80						
51	3460	29.00	44300	2.1						
56	3140	26.32	43700	2.3						
65	2700	22.62	42700	2.7						
75	2350	19.74	41700	3.0						
88	2000	16.75	40400	3.5						
35	5000	41.87	25100	0.85	K	97	DRN	180M4	300	603
48	3680	30.82	26000	1.15	KF	97	DRN	180M4	320	604
53	3330	27.91	26000	1.30	KA	97	DRN	180M4	280	605
60	2950	24.75	26000	1.45	KAF	97	DRN	180M4	305	604
66	2670	22.37	25900	1.60					300	603
78	2260	18.96	25600	1.90						
89	1970	16.56	25300	2.2						
107	1650	13.85	24700	2.6						
123	1430	11.99	24200	2.7						
59	2970	24.92	15600	0.85					240	597
66	2670	22.41	15900	0.85						
76	2320	19.45	16200	1.00						
85	2080	17.42	16400	1.05						
102	1720	14.45	16500	1.20						
118	1500	12.56	16400	1.35						
132	1330	11.17	15400	1.10						
148	1190	10.00	15300	1.25						
178	990	8.29	15100	1.40						
205	860	7.21	14900	1.50						


P _m = 22 kW										
n _a rpm	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
3.2	60300	454	190000	0.85	K KH	187R107	DRN	180L4	1970	632
4.2	46600	355	190000	1.05						
5.7	34600	261	190000	1.45						
6.7	29300	221	190000	1.70						
7.6	25600	193	190000	1.95						
9.0	21500	163	190000	2.3						


P _m = 22 kW										
n _a rpm	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
5.3	36800	278	150000	0.85	K KH	167R107 167R107	DRN DRN	180L4 180L4	1380 1350	632 632
6.1	32000	244	150000	1.00						
6.9	27900	213	150000	1.15						
7.2	27200	206	150000	1.15						
8.2	23500	180	150000	1.35						
9.2	21200	160	150000	1.50						
11	17900	135	150000	1.80						
12	15600	118	150000	2.0						
9.4	20700	157	109400	0.85	K KF	157R107 157R107	DRN DRN	180L4 180L4	990 1070	632 632
12	16200	122	108100	1.10	KA	157R107	DRN	180L4	950	632
14	14100	107	106900	1.25	KAF	157R107	DRN	180L4	1010	632
8.2	25500	179.86	190000	1.95	K KH	187 187	DRN DRN	180L4 180L4	1790 1730	629 630
8.9	23400	165.21	190000	2.1						
10	20500	144.59	190000	2.4						
11	18400	129.69	190000	2.7						
11	19100	134.99	150000	1.65	K KH	167 167	DRN DRN	180L4 180L4	1210 1170	627 628
13	15600	109.83	150000	2.0						
17	12400	87.86	150000	2.6						
19	11100	78.14	150000	2.9						
12	17400	122.39	105500	1.05	K KF KA KAF	157 157 157 157	DRN DRN DRN DRN	180L4 180L4 180L4 180L4	820 900 780 840	621 622 622 622
15	14200	100.22	104000	1.25						
16	13000	91.65	103100	1.40						
19	11300	79.75	101500	1.60						
21	10000	70.38	99700	1.80						
24	8670	61.02	97500	2.1						
27	7720	54.29	95600	2.3						
32	6650	46.79	93100	2.7						
39	5400	38.02	89300	3.3						
16	12700	89.89	73900	1.00	K	127	DRN	180L4	580	615
18	11600	81.98	73800	1.10	KF	127	DRN	180L4	630	616
21	10000	70.95*	73400	1.30	KA	127	DRN	180L4	560	617
24	8900	62.60	72700	1.45	KAF	127	DRN	180L4	590	616
27	7690	54.07	71700	1.70	K KF KA KAF	127 127 127 127	DRN DRN DRN DRN	180L4 180L4 180L4 180L4	580 630 560 590	615 616 617 616
31	6800	47.82	70600	1.90						
37	5710	40.19	68900	2.3						
41	5150	36.25	67700	2.5						
47	4460	31.37	66100	2.9						
53	3930	27.68	64500	3.3						
62	3390	23.91	62700	3.8						
70	3000	21.15	61100	4.3						
26	8130	57.17*	39800	1.00	K	107	DRN	180L4	430	609
30	7090	49.90	41600	1.10	KF	107	DRN	180L4	440	610
35	6020	42.33*	42900	1.20	KA	107	DRN	180L4	400	611
					KAF	107	DRN	180L4	425	610
40	5260	37.00*	43200	1.35	K KF KA KAF	107 107 107 107	DRN DRN DRN DRN	180L4 180L4 180L4 180L4	430 440 400 425	609 610 611 610
45	4640	32.69	42900	1.55						
47	4440	31.28*	42700	1.55						
51	4120	29.00	42400	1.75						
56	3740	26.32	42000	1.90						
65	3210	22.62	41200	2.2						
75	2800	19.74	40300	2.6						
88	2380	16.75	39300	3.0						
101	2080	14.64	38300	3.3						
110	1910	13.43	36700	2.2						
126	1660	11.73	35800	2.6						
149	1410	9.94	34700	3.0						
48	4380	30.82	23500	1.00	K	97	DRN	180L4	315	603
53	3960	27.91	23800	1.10	KF	97	DRN	180L4	335	604
60	3510	24.75	24100	1.20	KA	97	DRN	180L4	300	605
66	3180	22.37	24200	1.35	KAF	97	DRN	180L4	325	604


P_m = 22 kW

n _a rpm	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
78	2690	18.96	24100	1.60	K KF KA KAF	97	DRN	180L4	315	603
89	2350	16.56	24000	1.85						
107	1960	13.85	23700	2.2						
123	1700	11.99	23300	2.3						
142	1480	10.41	21800	1.95						
170	1230	8.71	21300	2.2						
76	2760	19.45	14500	0.85	K KF KA KAF	87	DRN	180L4	255	597
85	2470	17.42	14800	0.90						
102	2050	14.45	15200	1.00						
118	1780	12.56	15300	1.10						
132	1580	11.17	14200	0.95						
148	1420	10.00	14300	1.05						
178	1170	8.29	14300	1.20						
205	1020	7.21	14200	1.25						


P_m = 30 kW

n _a rpm	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
5.7	47300	261	190000	1.05	K KH	187R107	DRN	200L4	2080	632
6.7	40000	221	190000	1.25						
7.6	34900	193	190000	1.45						
9.0	29500	163	190000	1.70						
6.9	38100	213	150000	0.85	K KH	167R107	DRN	200L4	1490	632
7.2	37200	206	150000	0.85						
8.2	32100	180	150000	1.00						
9.3	28900	160	150000	1.10						
11	24500	135	150000	1.30						
13	21300	118	150000	1.50						
8.2	34800	179.86	190000	1.45	K KH	187	DRN	200L4	1900	629
9.0	31900	165.21	190000	1.55						
10	27900	144.59	190000	1.80						
11	25100	129.69	190000	2.00						
13	21700	112.60	190000	2.3						
14	19700	102.16	190000	2.5						
17	17000	88.00	190000	2.9						
13	21200	109.83	150000	1.50	K KH	167	DRN	200L4	1320	627
17	17000	87.86	150000	1.90						
19	15100	78.14	150000	2.1						
22	13100	68.07	150000	2.4						
24	11700	60.74	150000	2.7						
15	19400	100.22	92700	0.95	K KF KA KAF	157	DRN	200L4	930	621
16	17700	91.65	92700	1.00						
19	15400	79.75	92400	1.15						
21	13600	70.38	91700	1.30						
24	11800	61.02	90600	1.50						
27	10500	54.29	89500	1.70						
32	9050	46.79	87700	2.00						
39	7350	38.02	85000	2.4						
47	6050	31.30	82100	3.0						
21	13700	70.95*	64200	0.95	K KF KA KAF	127	DRN	200L4	690	615
24	12100	62.60	64600	1.05						
27	10400	54.07	64700	1.25						
31	9250	47.82	64400	1.40						
37	7770	40.19	63700	1.65						
41	7010	36.25	63000	1.85						
47	6070	31.37	62000	2.1						
53	5350	27.68	60900	2.4						
62	4620	23.91	59600	2.8						
35	8190	42.33*	32500	0.90	K KF KA KAF	107	DRN	200L4	540	609
40	7160	37.00*	34800	1.00						
47	6050	31.28*	36600	1.10						


P _m = 30 kW																
n _a rpm	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg							
51	5610	29.00	37200	1.30	K	107	DRN	200L4	540	609						
56	5090	26.32	37700	1.40												
65	4370	22.62	37700	1.65												
75	3820	19.74	37300	1.90												
88	3240	16.75	36700	2.2												
101	2830	14.64	36100	2.4												
110	2590	13.43	34300	1.65												
126	2260	11.73	33700	1.90												
149	1920	9.94	32900	2.2	KF	107	DRN	200L4	550	610						
170	1680	8.69	32200	2.4												
60	4780	24.75	19600	0.90							KA	97	DRN	200L4	405	605
66	4320	22.37	20200	1.00												
78	3660	18.96	20700	1.15												
89	3200	16.56	21000	1.35												
107	2680	13.85	21200	1.60												
123	2320	11.99	21100	1.70												
142	2010	10.41	19500	1.40												
170	1680	8.71	19400	1.60	KAF	97	DRN	200L4	430	604						

P _m = 37 kW										
n _a rpm	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
5.7	58300	261	190000	0.85	K KH	187R107 187R107	DRN DRN	225S4 225S4	2110 2040	632 632
6.7	49400	221	190000	1.00						
7.7	43100	193	190000	1.15						
9.1	36400	163	190000	1.35						
8.2	39700	180	150000	0.80	K KH	167R107 167R107	DRN DRN	225S4 225S4	1530 1490	632 632
9.3	35600	160	150000	0.90						
11	30200	135	150000	1.05						
13	26400	118	150000	1.20						
8.2	42800	179.86	190000	1.15	K KH	187 187	DRN DRN	225S4 225S4	1930 1870	629 630
9.0	39300	165.21	190000	1.25						
10	34400	144.59	190000	1.45						
11	30900	129.69	190000	1.60						
13	26800	112.60	190000	1.85						
15	24300	102.16	190000	2.0						
17	20900	88.00	190000	2.4						
13	26100	109.83	150000	1.20	K KH	167 167	DRN DRN	225S4 225S4	1350 1310	627 628
17	20900	87.86	150000	1.55						
19	18600	78.14	150000	1.70						
22	16200	68.07	150000	1.95						
24	14400	60.74	150000	2.2						
29	12300	51.77	150000	2.6						
16	21800	91.65	83700	0.80	K KF KA KAF	157 157 157 157	DRN DRN DRN DRN	225S4 225S4 225S4 225S4	960 1040 920 980	621 622 622 622
19	19000	79.75	84500	0.95						
21	16700	70.38	84800	1.05						
24	14500	61.02	84600	1.25						
27	12900	54.29	84100	1.40	K KF KA KAF	157 157 157 157	DRN DRN DRN DRN	225S4 225S4 225S4 225S4	960 1040 920 980	621 622 622 622
32	11100	46.79	83100	1.60						
39	9060	38.02	81200	2.00						
47	7460	31.30	79000	2.4						
24	14900	62.60	57500	0.85	K KF KA KAF	127 127 127 127	DRN DRN DRN DRN	225S4 225S4 225S4 225S4	720 770 700 730	615 616 617 616
27	12800	54.07	58600	1.00						
31	11400	47.82	59000	1.15						
37	9580	40.19	59100	1.35						


P_m = 37 kW

n _a rpm	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
41	8640	36.25	58900	1.50	K KF KA KAF	127	DRN	225S4	720	615
47	7470	31.37	58400	1.75						
54	6590	27.68	57800	1.95						
62	5690	23.91	56800	2.3						
70	5040	21.15	55900	2.6						
83	4230	17.77	54500	3.1						
103	3420	14.35	52500	3.5						
116	3040	12.79	50200	2.8						
138	2560	10.74	48600	3.1	K KF KA KAF	107	DRN	225S4	570	609
171	2060	8.68	46500	3.5						
40	8820	37.00*	26000	0.80						
47	7450	31.28*	29800	0.90						
51	6910	29.00	31100	1.05						
56	6270	26.32	32300	1.15						
66	5390	22.62	33700	1.35						
75	4700	19.74	34400	1.55						
89	3990	16.75	34500	1.75						
101	3480	14.64	34100	1.95						
110	3200	13.43	32300	1.35						
126	2790	11.73	31900	1.55						
149	2370	9.94	31400	1.75						
171	2070	8.69	30800	1.95						

P_m = 45 kW

n _a rpm	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
6.7	60200	221	190000	0.85	K KH	187R107	DRN	225M4	2110	632
7.7	52500	193	190000	0.95						
9.1	44300	163	190000	1.15						
11	36800	135	150000	0.85	K KH	167R107	DRN	225M4	1530	632
13	32100	118	150000	1.00						
8.2	52100	179.86	190000	0.95	K KH	187	DRN	225M4	1930	629
9.0	47900	165.21	190000	1.05						
10	41900	144.59	190000	1.20						
11	37600	129.69	190000	1.35						
13	32600	112.60	189800	1.55						
15	29600	102.16	187600	1.70						
17	25500	88.00	183700	1.95						
20	21400	73.96	178700	2.3						
13	31800	109.83	150000	1.00	K KH	167	DRN	225M4	1350	627
17	25400	87.86	150000	1.25						
19	22600	78.14	150000	1.40						
22	19700	68.07	150000	1.60						
24	17600	60.74	148900	1.80						
29	15000	51.77	145100	2.1						
35	12400	42.89	140400	2.6						
21	20400	70.38	76800	0.90	K KF KA KAF	157	DRN	225M4	960	621
24	17600	61.02	77700	1.00						
27	15700	54.29	77900	1.15						
32	13500	46.79	77800	1.35						
39	11000	38.02	76900	1.65						
47	9070	31.30	75400	2.00						
54	8000	27.62	74300	2.2						
62	6940	23.95	72700	2.6						
70	6170	21.31	71400	2.9						
81	5320	18.37	69600	3.4						
31	13800	47.82	52800	0.95	K KF KA KAF	127	DRN	225M4	720	615
37	11600	40.19	53900	1.10						
41	10500	36.25	54300	1.25						


P_m = 45 kW

n _a rpm	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
47	9090	31.37	54400	1.45	K KF KA KAF	127	DRN	225M4	720	615
54	8020	27.68	54200	1.60						
62	6930	23.91	53800	1.90						
70	6120	21.15	53200	2.1						
83	5150	17.77	52200	2.5						
103	4160	14.35	50600	2.9						
116	3700	12.79	48300	2.3						
138	3110	10.74	47000	2.6	K KF KA KAF	107	DRN	225M4	570	609
171	2510	8.68	45200	2.9						
51	8400	29.00	23000	0.85						
56	7620	26.32	25400	0.95						
66	6550	22.62	28100	1.10						
75	5720	19.74	29800	1.25						
89	4850	16.75	31100	1.45						
101	4240	14.64	31700	1.60	K KF KA KAF	107	DRN	225M4	570	609
110	3890	13.43	29900	1.10						
126	3390	11.73	29900	1.25						
149	2880	9.94	29600	1.45						
171	2510	8.69	29300	1.60						


P_m = 55 kW

n _a rpm	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
10	51200	144.59	179800	1.00	K KH	187	DRN	250M4	2080	629
11	45900	129.69	179600	1.10						
13	39900	112.60	178600	1.25						
15	36200	102.16	177400	1.40						
17	31100	88.00	174900	1.60						
20	26200	73.96	171300	1.90						
23	22600	64.04	167800	2.2						
17	31100	87.86	145300	1.05	K KH	167	DRN	250M4	1500	627
19	27600	78.14	144600	1.15						
22	24100	68.07	143200	1.35						
24	21500	60.74	141700	1.50						
29	18300	51.77	139000	1.75						
35	15200	42.89	135300	2.1						
40	12900	36.61	131800	2.5						
24	21600	61.02	69100	0.85	K KF KA KAF	157	DRN	250M4	1110	621
27	19200	54.29	70300	0.95						
32	16500	46.79	71200	1.10						
39	13400	38.02	71500	1.35						
47	11000	31.30	71000	1.60						
54	9780	27.62	70400	1.85						
62	8480	23.95	69400	2.1						
70	7550	21.31	68400	2.4						
81	6500	18.37	67000	2.8						
99	5280	14.92	64700	3.4						
117	4480	12.65	62800	3.8	K KF KA KAF	127	DRN	250M4	870	615
37	14200	40.19	47400	0.90						
47	11100	31.37	49300	1.15						
54	9800	27.68	49700	1.35						
62	8470	23.91	49900	1.55	K KF KA KAF	127	DRN	250M4	870	615
70	7490	21.15	49800	1.75						
83	6290	17.77	49300	2.1						
103	5080	14.35	48300	2.4						
116	4530	12.79	45900	1.90						
138	3800	10.74	45000	2.1						
171	3070	8.68	43600	2.4	K KF KA KAF	127	DRN	250M4	850	617
62	8470	23.91	49900	1.55						
70	7490	21.15	49800	1.75						
83	6290	17.77	49300	2.1						
103	5080	14.35	48300	2.4						
116	4530	12.79	45900	1.90						


P_m = 75 kW

n _a rpm	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
11	62600	129.69	153800	0.80	K KH	187 187	DRN DRN	280S4 280S4	2130 2070	629 630
13	54400	112.60	156200	0.90						
15	49300	102.16	157000	1.00						
17	42500	88.00	157400	1.20						
20	35700	73.96	156500	1.40						
23	30900	64.04	155000	1.60						
28	25700	53.36	152200	1.95						
33	21900	45.50*	149100	2.3						
19	37700	78.14	126200	0.85	K KH	167 167	DRN DRN	280S4 280S4	1550 1510	627 628
22	32800	68.07	127200	0.95						
24	29300	60.74	127300	1.10						
29	25000	51.77	126800	1.30						
35	20700	42.89	125200	1.55						
40	17600	36.61	123200	1.80						
46	15500	32.25	121200	2.0						
52	13900	28.77	119300	2.3	K KF KA KAF	157 157 157 157	DRN DRN DRN DRN	280S4 280S4 280S4 280S4	1160 1240 1120 1180	621 622 622 622
60	11800	24.52	116300	2.7						
39	18300	38.02	60800	1.00						
47	15100	31.30	62200	1.20						
54	13300	27.62	62600	1.35						
62	11500	23.95	62600	1.55						
70	10200	21.31	62400	1.75						
81	8870	18.37	61800	2.0	K KF KA KAF	127 127 127 127	DRN DRN DRN DRN	280S4 280S4 280S4 280S4	920 960 890 930	615 616 617 616
99	7210	14.92	60500	2.5						
117	6110	12.65	59200	2.8						
47	15100	31.37	38000	0.85						
54	13300	27.68	40800	0.95						
62	11500	23.91	42200	1.15						
70	10200	21.15	43000	1.25						
83	8580	17.77	43600	1.50	K KF KA KAF	127 127 127 127	DRN DRN DRN DRN	280S4 280S4 280S4 280S4	920 960 890 930	615 616 617 616
103	6930	14.35	43700	1.75						
116	6170	12.79	41100	1.40						
138	5190	10.74	41000	1.55						
171	4190	8.68	40400	1.70						

P_m = 90 kW

n _a rpm	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
14	59200	102.16	141700	0.85	K KH	187 187	DRN DRN	280M4 280M4	2250 2180	629 630
17	51000	88.00	144200	1.00						
20	42900	73.96	145500	1.15						
23	37100	64.04	145400	1.35						
28	30900	53.36	144200	1.60						
33	26400	45.50*	142300	1.90						
35	24600	42.51	141300	2.0						
38	22300	38.57	139700	2.2	K KH	167 167	DRN DRN	280M4 280M4	1670 1630	627 628
22	39500	68.07	115100	0.80						
24	35200	60.74	116600	0.90						
29	30000	51.77	117600	1.05						
35	24800	42.89	117600	1.30						
40	21200	36.61	116700	1.50						
46	18700	32.25	115500	1.70						
51	16600	28.77	114200	1.90	K KF KA KAF	157 157 157 157	DRN DRN DRN DRN	280M4 280M4 280M4 280M4	1270 1350 1230 1290	621 622 622 622
60	14200	24.52	111900	2.2						
73	11700	20.32	108800	2.7						
85	10000	17.34	105900	3.2						
39	22000	38.02	52700	0.80						
62	13800	23.95	57500	1.30						
70	12300	21.31	57900	1.45						
81	10600	18.37	57900	1.70	K KF KA KAF	157 157 157 157	DRN DRN DRN DRN	280M4 280M4 280M4 280M4	1270 1350 1230 1290	621 622 622 622
99	8650	14.92	57400	2.1						
117	7340	12.65	56600	2.3						


P_m = 90 kW

n _a rpm	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
62	13800	23.91	35500	0.95	K KF KA KAF	127	DRN	280M4	1040	615
70	12200	21.15	37800	1.05						
83	10300	17.77	39200	1.25						
103	8320	14.35	40200	1.45						
116	7410	12.79	37600	1.15						
138	6230	10.74	38000	1.30						
171	5030	8.68	38000	1.45					1050	616


P_m = 110 kW

n _a rpm	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
17	62100	88.00	126800	0.80	K KH	187	DRN	315S4	2490	629
20	52200	73.96	130800	0.95						
23	45200	64.04	132700	1.10						
28	37600	53.36	133600	1.35						
33	32100	45.50*	133200	1.55						
35	30000	42.51	132800	1.65	K KH	187	DRN	315S4/ERF/NS	2490	629
						187	DRN	315S4/ERF/NS	2420	630
39	27200	38.57	131900	1.85	K KH	187	DRN	315S4	2490	629
45	23400	33.23	130200	2.1						
53	19700	27.92	127500	2.5						
29	36500	51.77	105500	0.90	K KH	167	DRN	315S4	1910	627
35	30200	42.89	107500	1.05						
41	25800	36.61	108100	1.25						
46	22700	32.25	107900	1.40	K KH	167	DRN	315S4/ERF/NS	1910	627
						167	DRN	315S4/ERF/NS	1870	628
52	20300	28.77	107400	1.60	K KH	167	DRN	315S4	1910	627
61	17300	24.52	106100	1.85						
73	14300	20.32	104000	2.2						
86	12200	17.34	101800	2.6						
62	16900	23.95	50800	1.05	K KF KA KAF	157	DRN	315S4/ERF/NS	1520	621
						157	DRN	315S4/ERF/NS	1590	622
						157	DRN	315S4/ERF/NS	1480	622
						157	DRN	315S4/ERF/NS	1540	622
70	15000	21.31	51900	1.20	K KF KA KAF	157	DRN	315S4	1520	621
81	12900	18.37	52700	1.40						
100	10500	14.92	53200	1.70						
118	8930	12.65	53000	1.90						


P_m = 132 kW

n _a rpm	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
20	62600	73.96	114700	0.80	K KH	187	DRN	315M4	2510	629
23	54200	64.04	118700	0.90						
28	45200	53.36	121900	1.10						
33	38500	45.50*	123300	1.30						
35	36000	42.51	123500	1.40	K KH	187	DRN	315M4/ERF/NS	2510	629
39	32600	38.57	123500	1.55						
45	28100	33.23	122900	1.80	K KH	187	DRN	315M4	2510	629
53	23600	27.92	121400	2.1						
62	20400	24.18	119600	2.3						
74	17000	20.15	116800	2.6						
87	14500	17.18	114000	2.8						
35	36300	42.89	96400	0.90	K KH	167	DRN	315M4	1930	627
41	31000	36.61	98600	1.05						
46	27300	32.25	99600	1.15	K KH	167	DRN	315M4/ERF/NS	1930	627
52	24300	28.77	99900	1.30						
61	20700	24.52	99800	1.55	K KH	167	DRN	315M4	1930	627
73	17200	20.32	98700	1.85						
86	14600	17.34	97300	2.2						


P_m = 132 kW

n _a rpm	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
62	20200	23.95	43400	0.90	K	157	DRN	315M4/ERF/NS	1540	621
70	18000	21.31	45300	1.00	KF	157	DRN	315M4/ERF/NS	1610	622
					KA	157	DRN	315M4/ERF/NS	1500	622
					KAF	157	DRN	315M4/ERF/NS	1560	622
81	15500	18.37	47000	1.15	K	157	DRN	315M4	1540	621
100	12600	14.92	48500	1.40	KF	157	DRN	315M4	1610	622
118	10700	12.65	49100	1.60	KA	157	DRN	315M4	1500	622
					KAF	157	DRN	315M4	1560	622


P_m = 160 kW


n _a rpm	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
28	54800	53.36	107100	0.90	K KH	187	DRN	315L4	2640	629
33	46700	45.50*	110600	1.05						
45	34100	33.23	113700	1.45						
53	28700	27.92	113600	1.75						
61	24800	24.18	112900	1.90						
74	20700	20.15	111200	2.1						
86	17600	17.18	109300	2.3						
41	37600	36.61	86500	0.85	K KH	167	DRN	315L4	2060	627
61	25200	24.52	91700	1.25						
73	20800	20.32	92000	1.55						
86	17800	17.34	91600	1.80						
81	18800	18.37	39800	0.95	K	157	DRN	315L4	1670	621
100	15300	14.92	42600	1.15	KF	157	DRN	315L4	1750	622
117	13000	12.65	44100	1.30	KA	157	DRN	315L4	1630	622
					KAF	157	DRN	315L4	1690	622








P_m = 200 kW


n _a rpm	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
33	58300	45.50*	92600	0.85	K	187	DRN	315H4	2760	629
					KH	187	DRN	315H4	2700	630
45	42600	33.23	100500	1.15	K	187	DRN	315H4/ERF/NS	2760	629
					KH	187	DRN	315H4/ERF/NS	2700	630
53	35800	27.92	102500	1.40	K KH	187	DRN	315H4	2760	629
62	31000	24.18	103300	1.55						
74	25800	20.15	103200	1.70						
87	22000	17.18	102400	1.90						
61	31400	24.52	80200	1.00	K	167	DRN	315H4/ERF/NS	2180	627
					KH	167	DRN	315H4/ERF/NS	2140	628
73	26000	20.32	82500	1.25	K	167	DRN	315H4	2180	627
86	22200	17.34	83400	1.45	KH	167	DRN	315H4	2140	628
100	19100	14.92	34300	0.95	K	157	DRN	315H4	1790	621
118	16200	12.65	37000	1.05	KF	157	DRN	315H4	1860	622
					KA	157	DRN	315H4	1750	622
					KAF	157	DRN	315H4	1810	622


10.4 Auswahltabellen für niedrige Abtriebsdrehzahlen K..R..DRN.. in Nm


M_{a max} = 200 Nm								
n_a rpm	i	F_{Ra}¹⁾ N					m kg	
0.20	6832	5640	K KF KA KAF	37R17	DR	63S4	19	631
0.23	5922	5640						
0.25	5491	5640						
0.29	4759	5640						
0.33	4160	5640						
0.38	3645	5640						
0.43	3205	5640						
0.49	2801	5640						
0.56	2454	5640						
0.64	2166	5640						
0.73	1891	5640						
0.83	1660	5640						
0.94	1466	5640						
1.1	1288	5640						
1.2	1136	5640						
1.4	996	5640	K KF KA KAF	37R17	DR	63S4	19	631
1.6	876	5640						
1.8	761	5640						
2.1	671	5640						
2.4	585	5640						
2.7	512	5640						
3.1	451	5640						
3.5	396	5640						
4.0	346	5640	K KF KA KAF	37R17	DR	63M4	19	631
4.5	304	5640						
4.9	267	5640						
5.6	234	5640						
6.4	205	5640						
7.3	181	5640	K KF KA KAF	37R17	DR	63L4	20	631
8.1	160	5640						
9.5	136	5640						
10	127	5640						
12	110	5640	K KF KA KAF	37R17	DRS	71S4	21	631
14	96	5640						


M_{a max} = 295 Nm								
n_a rpm	i	F_{Ra}¹⁾ N					m kg	
19	75	7500	K KF KA KAF	39R17 39R17 39R17 39R17	DRN DRN DRN DRN	80M4 80M4 80M4 80M4	32 34 31 33	631 631 631 631


M _{a max} = 300 Nm															
n _a rpm	i	F _{Ra} ¹⁾ N					m kg								
0.34	4057	7500		K	39R17	DR	63S4	24	631						
0.41	3370	7500													
0.47	2906	7500													
0.55	2508	7500													
0.58	2367	7500													
0.64	2162	7500													
0.73	1881	7500													
0.78	1762	7500													
0.85	1622	7500													
0.92	1494	7500													
1.0	1321	7500													
1.2	1169	7500													
1.3	1093	7500													
1.4	956	7500		K	39R17	DR	63S4	24	631						
1.7	814	7500													
1.9	711	7500													
2.3	605	7500													
2.7	504	7500													
3.0	454	7500													
3.3	399	7500		K	39R17	DR	63M4	24	631						
3.6	365	7500													
4.2	312	7500													
4.4	299	7500													
5.1	254	7500		K	39R17	DR	63L4	25	631						
5.6	234	7500													
6.2	210	7500													
6.9	189	7500													
7.9	174	7500		K	39R17	DRS	71S4	26	631						
8.8	156	7500													
9.7	142	7500													
12	117	7500		K	39R17	DRS	71M4	28	631						
										KF	39R17	DRS	71M4	29	631
										KA	39R17	DRS	71M4	27	631
										KAF	39R17	DRS	71M4	28	631


M _{a max} = 400 Nm								
n _a rpm	i	F _{Ra} ¹⁾ N					m kg	
0.14	10138	5920						
0.16	8534	5920						
0.18	7662	5920						
0.20	6826	5920						
0.23	5983	5920						
0.27	5159	5920						
0.30	4601	5920						
0.35	3940	5920						
0.40	3477	5920						
0.45	3043	5920						
0.51	2733	5920						
0.59	2354	5920						
0.67	2063	5920						
0.76	1819	5920						
0.87	1586	5920						
0.99	1388	5920						
1.1	1222	5920	K	47R37	DR	63S4	34	631
1.3	1097	5920	KF	47R37	DR	63S4	37	631
1.5	945	5920	KA	47R37	DR	63S4	33	631
1.7	831	5920	KAF	47R37	DR	63S4	36	631
1.9	718	5920						
2.2	639	5920						


M_{a max} = 400 Nm								
n_a rpm	i	F_{Ra}¹⁾ N					m kg	
2.4	552	5920	K	47R37	DR	63M4	33	631
2.7	495	5920	KF	47R37	DR	63M4	36	631
3.1	426	5920	KA	47R37	DR	63M4	32	631
3.5	375	5920	KAF	47R37	DR	63M4	35	631
4.0	327	5920	K	47R37	DR	63L4	34	631
4.5	289	5920	KF	47R37	DR	63L4	37	631
5.1	256	5920	KA	47R37	DR	63L4	33	631
			KAF	47R37	DR	63L4	36	631
6.2	225	5920	K	47R37	DRS	71S4	36	631
7.0	198	5920	KF	47R37	DRS	71S4	39	631
			KA	47R37	DRS	71S4	35	631
			KAF	47R37	DRS	71S4	38	631
8.0	171	5920	K	47R37	DRS	71M4	37	631
8.9	153	5920	KF	47R37	DRS	71M4	40	631
10	131	5920	KA	47R37	DRS	71M4	36	631
			KAF	47R37	DRS	71M4	39	631


M_{a max} = 500 Nm								
n_a rpm	i	F_{Ra}¹⁾ N					m kg	
0.19	7137	9000						
0.23	5991	9000						
0.27	5120	9000						
0.34	4034	9000						
0.39	3580	9000						
0.45	3081	9000						
0.50	2773	9000	K	49R37	DR	63S4	43	631
0.54	2545	9000	KF	49R37	DR	63S4	45	631
0.58	2372	9000	KA	49R37	DR	63S4	40	631
0.65	2118	9000	KAF	49R37	DR	63S4	45	631
0.71	1941	9000						
0.79	1741	9000						
0.85	1632	9000						
0.91	1521	9000						
1.1	1228	9000						
1.4	1000	9000						
0.97	1424	9000	K	49R37	DR	63S4	43	631
1.0	1309	9000	KF	49R37	DR	63S4	45	631
1.2	1120	9000	KA	49R37	DR	63S4	40	631
1.5	908	9000	KAF	49R37	DR	63S4	45	631
1.7	802	9000						
1.9	701	9000	K	49R37	DR	63M4	43	631
2.0	645	9000	KF	49R37	DR	63M4	45	631
2.2	595	9000	KA	49R37	DR	63M4	40	631
2.4	543	9000	KAF	49R37	DR	63M4	45	631
2.6	501	9000						
2.9	449	9000	K	49R37	DR	63L4	44	631
3.2	401	9000	KF	49R37	DR	63L4	45	631
3.6	360	9000	KA	49R37	DR	63L4	41	631
3.9	330	9000	KAF	49R37	DR	63L4	46	631
4.6	300	9000	K	49R37	DRS	71S4	46	631
5.0	274	9000	KF	49R37	DRS	71S4	47	631
5.7	243	9000	KA	49R37	DRS	71S4	43	631
			KAF	49R37	DRS	71S4	48	631
6.3	217	9000	K	49R37	DRS	71M4	47	631
7.0	193	9000	KF	49R37	DRS	71M4	48	631
7.7	176	9000	KA	49R37	DRS	71M4	44	631
9.0	152	9000	KAF	49R37	DRS	71M4	49	631
12	125	9000	K	49R37	DRN	80M4	51	631
			KF	49R37	DRN	80M4	53	631
			KA	49R37	DRN	80M4	48	631
			KAF	49R37	DRN	80M4	53	631


M_{a max} = 500 Nm								
n_a rpm	i	F_{Ra}¹⁾ N					m kg	
15	99	9000	K	49R37	DRN	90S4	57	631
			KF	49R37	DRN	90S4	59	631
			KA	49R37	DRN	90S4	54	631
			KAF	49R37	DRN	90S4	59	631


M_{a max} = 600 Nm								
n_a rpm	i	F_{Ra}¹⁾ N					m kg	
0.11	12169	7630						
0.12	11162	7630						
0.15	9503	7630						
0.16	8547	7630						
0.19	7277	7630						
0.21	6478	7630						
0.24	5662	7630	K	57R37	DR	63S4	39	631
0.27	5033	7630	KF	57R37	DR	63S4	44	631
0.32	4340	7630	KA	57R37	DR	63S4	37	631
0.36	3854	7630	KAF	57R37	DR	63S4	43	631
0.41	3390	7630						
0.47	2924	7630						
0.53	2593	7630						
0.61	2249	7630						
0.70	1986	7630						
0.79	1743	7630						
0.90	1539	7630	K	57R37	DR	63S4	39	631
1.0	1354	7630	KF	57R37	DR	63S4	44	631
1.2	1174	7630	KA	57R37	DR	63S4	37	631
1.3	1036	7630	KAF	57R37	DR	63S4	43	631
1.5	906	7630						
1.6	806	7630	K	57R37	DR	63M4	39	631
1.9	699	7630	KF	57R37	DR	63M4	44	631
2.2	615	7630	KA	57R37	DR	63M4	37	631
			KAF	57R37	DR	63M4	43	631
2.4	544	7630	K	57R37	DR	63L4	40	631
2.8	473	7630	KF	57R37	DR	63L4	45	631
3.1	421	7630	KA	57R37	DR	63L4	38	631
			KAF	57R37	DR	63L4	43	631
3.8	362	7630	K	57R37	DRS	71S4	42	631
4.3	319	7630	KF	57R37	DRS	71S4	47	631
4.9	280	7630	KA	57R37	DRS	71S4	40	631
			KAF	57R37	DRS	71S4	45	631
5.5	246	7630	K	57R37	DRS	71M4	43	631
6.3	215	7630	KF	57R37	DRS	71M4	48	631
7.1	192	7630	KA	57R37	DRS	71M4	41	631
			KAF	57R37	DRS	71M4	47	631
8.7	166	7630	K	57R37	DRN	80M4	48	631
10.0	145	7630	KF	57R37	DRN	80M4	52	631
			KA	57R37	DRN	80M4	45	631
			KAF	57R37	DRN	80M4	51	631
11	129	7630	K	57R37	DRN	90S4	53	631
13	111	7630	KF	57R37	DRN	90S4	58	631
15	97	7630	KA	57R37	DRN	90S4	51	631
			KAF	57R37	DRN	90S4	57	631


M_{a max} = 820 Nm							
n_a rpm	i	F_{Ra}¹⁾ N					m kg 
0.11	12139	10300	K KF KA KAF	67R37	DR	63S4	45 631
0.12	11134	10300					
0.15	9479	10300					
0.17	8173	10300					
0.19	7259	10300					
0.21	6462	10300					
0.24	5648	10300					
0.28	4846	10300					
0.32	4329	10300					
0.37	3750	10300					
0.42	3315	10300					
0.47	2917	10300					
0.55	2532	10300					
0.62	2244	10300					
0.70	1981	10300					
0.79	1739	10300	K	67R37	DR	63S4	45 631
0.90	1535	10300	KF	67R37	DR	63S4	51 631
1.0	1351	10300	KA	67R37	DR	63S4	42 631
1.2	1171	10300	KAF	67R37	DR	63S4	48 631
1.3	1034	10300	K	67R37	DR	63M4	45 631
1.5	903	10300	KF	67R37	DR	63M4	51 631
1.7	793	10300	KA	67R37	DR	63M4	42 631
			KAF	67R37	DR	63M4	48 631
1.9	697	10300	K	67R37	DR	63L4	46 631
2.1	613	10300	KF	67R37	DR	63L4	51 631
2.4	542	10300	KA	67R37	DR	63L4	43 631
			KAF	67R37	DR	63L4	49 631
2.9	471	10300	K	67R37	DRS	71S4	48 631
3.3	420	10300	KF	67R37	DRS	71S4	53 631
3.8	361	10300	KA	67R37	DRS	71S4	45 631
			KAF	67R37	DRS	71S4	51 631
4.2	323	10300	K	67R37	DRS	71M4	49 631
4.9	279	10300	KF	67R37	DRS	71M4	54 631
5.5	246	10300	KA	67R37	DRS	71M4	46 631
			KAF	67R37	DRS	71M4	52 631
6.6	217	10300	K	67R37	DRN	80M4	53 631
			KF	67R37	DRN	80M4	59 631
7.5	191	10300	KA	67R37	DRN	80M4	51 631
			KAF	67R37	DRN	80M4	56 631


M_{a max} = 1550 Nm							
n_a rpm	i	F_{Ra}¹⁾ N					m kg 
0.09	15310	15400	K KF KA KAF	77R37	DR	63S4	69 631
0.10	14043	15400					
0.12	11955	15400					
0.14	10217	15400					
0.16	8809	15400					
0.18	7528	15400					
0.21	6606	15400					
0.24	5774	15400					
0.27	5089	15400					
0.31	4489	15400					
0.35	3961	15400					
0.40	3485	15400					
0.48	2901	15400					
0.51	2717	15400					
0.56	2370	15400	K	77R37	DR	63M4	69 631
			KF	77R37	DR	63M4	78 631
			KA	77R37	DR	63M4	62 631
			KAF	77R37	DR	63M4	70 631


M_{a max} = 1550 Nm								
n_a rpm	i	F_{Ra}¹⁾ N					m kg	
0.64	2050	15400	K	77R37	DR	63M4	69	631
0.75	1772	15400	KF	77R37	DR	63M4	77	631
0.87	1514	15400	KA	77R37	DR	63M4	62	631
0.95	1388	15400	KAF	77R37	DR	63M4	70	631
1.1 1.2	1218	15400	K	77R37	DR	63L4	70	631
	1053	15400	KF	77R37	DR	63L4	78	631
			KA	77R37	DR	63L4	62	631
			KAF	77R37	DR	63L4	70	631
1.5 1.7 2.0	924	15400	K	77R37	DRS	71S4	72	631
	815	15400	KF	77R37	DRS	71S4	80	631
			KA	77R37	DRS	71S4	64	631
	709	15400	KAF	77R37	DRS	71S4	72	631
2.2 2.5 2.8	622	15400	K	77R37	DRS	71M4	73	631
	552	15400	KF	77R37	DRS	71M4	81	631
			KA	77R37	DRS	71M4	65	631
	485	15400	KAF	77R37	DRS	71M4	73	631
3.4 3.9	428	15400	K	77R37	DRN	80M4	78	631
			KF	77R37	DRN	80M4	86	631
			KA	77R37	DRN	80M4	70	631
	367	15400	KAF	77R37	DRN	80M4	78	631
4.4 5.0 5.8	328	15400	K	77R37	DRN	90S4	83	631
	290	15400	KF	77R37	DRN	90S4	92	631
			KA	77R37	DRN	90S4	76	631
	252	15400	KAF	77R37	DRN	90S4	84	631


M_{a max} = 2700 Nm								
n_a rpm	i	F_{Ra}¹⁾ N					m kg	
0.09	14829	27300	K KF KA KAF	87R57	DR	63S4	120	631
0.10	13168	27300						
0.12	11737	27300						
0.14	10217	27300						
0.15	9073	27300						
0.18	7854	27300						
0.20	6832	27300						
0.23	5930	27300						
0.26	5240	27300	K KF KA KAF	87R57	DR	63M4	120	631
0.30	4562	27300						
0.33	4037	27300						
0.37	3609	27300						
0.42	3107	27300						
0.48	2728	27300						
0.55	2371	27300						
0.62 0.70	2088	27300						
	1854	27300						
0.83 0.97 1.1	1657	27300			DRS	71S4	120	631
	1415	27300				71S4	130	631
						71S4	110	631
	1229	27300				71S4	120	631
1.3 1.4 1.6	1078	27300			DRS	71M4	120	631
	951	27300				71M4	130	631
						71M4	110	631
	837	27300				71M4	120	631
2.0 2.3	726	27300			DRN	80M4	125	631
						80M4	135	631
						80M4	115	631
	638	27300				80M4	125	631


M_{a max} = 2700 Nm								
n_a rpm	i	F_{Ra}¹⁾ N					m kg	
2.6	562	27300	K	87R57	DRN	90S4	130	631
3.1	474	27300	KF	87R57	DRN	90S4	140	631
3.4	426	27300	KA	87R57	DRN	90S4	120	631
			KAF	87R57	DRN	90S4	135	631
3.9	373	27300	K	87R57	DRN	90L4	135	631
4.4	330	27300	KF	87R57	DRN	90L4	145	631
			KA	87R57	DRN	90L4	125	631
			KAF	87R57	DRN	90L4	135	631
4.9	294	27300	K	87R57	DRN	100LS4	140	631
5.8	250	27300	KF	87R57	DRN	100LS4	150	631
6.1	236	27300	KA	87R57	DRN	100LS4	125	631
7.2	201	27300	KAF	87R57	DRN	100LS4	140	631


M_{a max} = 4300 Nm								
n_a rpm	i	F_{Ra}¹⁾ N					m kg	
0.08	18091	40000	K KF KA KAF	97R57	DR	63S4	180	631
0.08	16666	40000		97R57	DR	63S4	200	631
0.09	14897	40000		97R57	DR	63S4	160	631
0.10	13182	40000		97R57	DR	63S4	185	631
0.12	11677	40000		97R57	DR	63S4		
0.13	10317	40000		97R57	DR	63S4		
0.15	9083	40000		97R57	DR	63S4		
0.17	8054	40000		97R57	DR	63S4		
0.20	6970	40000		97R57	DR	63S4		
0.22	6027	40000	K	97R57	DR	63M4	180	631
0.24	5391	40000	KF	97R57	DR	63M4	200	631
0.28	4669	40000	KA	97R57	DR	63M4	160	631
0.32	4082	40000	KAF	97R57	DR	63M4	185	631
0.36	3583	40000	K	97R57	DR	63L4	180	631
0.42	3108	40000	KF	97R57	DR	63L4	200	631
0.47	2757	40000	KA	97R57	DR	63L4	160	631
			KAF	97R57	DR	63L4	185	631
0.57	2419	40000	K	97R57	DRS	71S4	180	631
0.65	2123	40000	KF	97R57	DRS	71S4	200	631
			KA	97R57	DRS	71S4	165	631
			KAF	97R57	DRS	71S4	185	631
0.73	1856	40000	K	97R57	DRS	71M4	180	631
0.84	1625	40000	KF	97R57	DRS	71M4	200	631
0.95	1430	40000	KA	97R57	DRS	71M4	165	631
1.1	1261	40000	KAF	97R57	DRS	71M4	190	631
1.3	1102	40000	K	97R57	DRN	80M4	185	631
1.5	957	40000	KF	97R57	DRN	80M4	205	631
			KA	97R57	DRN	80M4	170	631
			KAF	97R57	DRN	80M4	195	631
1.7	855	40000	K	97R57	DRN	90S4	195	631
2.0	743	40000	KF	97R57	DRN	90S4	215	631
			KA	97R57	DRN	90S4	175	631
			KAF	97R57	DRN	90S4	200	631
2.2	652	40000	K	97R57	DRN	90L4	195	631
2.6	573	40000	KF	97R57	DRN	90L4	215	631
2.9	504	40000	KA	97R57	DRN	90L4	180	631
			KAF	97R57	DRN	90L4	205	631
3.3	437	40000	K	97R57	DRN	100LS4	200	631
3.8	382	40000	KF	97R57	DRN	100LS4	220	631
4.2	342	40000	KA	97R57	DRN	100LS4	180	631
			KAF	97R57	DRN	100LS4	205	631
4.8	305	40000	K	97R57	DRN	100L4	205	631
5.6	258	40000	KF	97R57	DRN	100L4	225	631
			KA	97R57	DRN	100L4	190	631
			KAF	97R57	DRN	100L4	215	631


M_{a max} = 4300 Nm								
n_a rpm	i	F_{Ra}¹⁾ N					m kg	
6.3	232	40000	K	97R57	DRN	112M4	215	631
7.3	199	40000	KF	97R57	DRN	112M4	235	631
			KA	97R57	DRN	112M4	200	631
			KAF	97R57	DRN	112M4	225	631

M_{a max} = 8000 Nm								
n_a rpm	i	F_{Ra}¹⁾ N					m kg	
0.10	14311	65000	K	107R77	DR	63S4	310	631
			KF	107R77	DR	63S4	320	631
			KA	107R77	DR	63S4	280	631
			KAF	107R77	DR	63S4	305	631
0.11	12211	65000	K	107R77	DR	63M4	310	631
0.12	10677	65000	KF	107R77	DR	63M4	320	631
0.14	9524	65000	KA	107R77	DR	63M4	280	631
0.16	8328	65000	KAF	107R77	DR	63M4	305	631
0.18	7270	65000	K	107R77	DR	63L4	310	631
0.21	6184	65000	KF	107R77	DR	63L4	320	631
0.23	5662	65000	KA	107R77	DR	63L4	285	631
			KAF	107R77	DR	63L4	305	631
0.27	5138	65000	K	107R77	DRS	71S4	310	631
0.32	4359	65000	KF	107R77	DRS	71S4	325	631
0.36	3810	65000	KA	107R77	DRS	71S4	285	631
			KAF	107R77	DRS	71S4	310	631
0.41	3358	65000	K	107R77	DRS	71M4	315	631
0.46	2977	65000	KF	107R77	DRS	71M4	325	631
0.52	2599	65000	KA	107R77	DRS	71M4	285	631
			KAF	107R77	DRS	71M4	310	631
0.63	2286	65000	K	107R77	DRN	80M4	320	631
0.74	1939	65000	KF	107R77	DRN	80M4	330	631
			KA	107R77	DRN	80M4	290	631
			KAF	107R77	DRN	80M4	315	631
0.85	1713	65000	K	107R77	DRN	90S4	320	631
0.94	1554	65000	KF	107R77	DRN	90S4	335	631
1.1	1336	65000	KA	107R77	DRN	90S4	295	631
			KAF	107R77	DRN	90S4	320	631
1.2	1166	65000	K	107R77	DRN	90L4	325	631
1.4	1030	65000	KF	107R77	DRN	90L4	335	631
1.6	904	65000	KA	107R77	DRN	90L4	300	631
			KAF	107R77	DRN	90L4	320	631
1.8	793	65000	K	107R77	DRN	100LS4	330	631
2.1	696	65000	KF	107R77	DRN	100LS4	340	631
2.4	615	65000	KA	107R77	DRN	100LS4	300	631
			KAF	107R77	DRN	100LS4	325	631
2.8	522	65000	K	107R77	DRN	100L4	335	631
3.2	461	65000	KF	107R77	DRN	100L4	350	631
			KA	107R77	DRN	100L4	310	631
			KAF	107R77	DRN	100L4	335	631
3.6	408	65000	K	107R77	DRN	112M4	345	631
4.0	364	65000	KF	107R77	DRN	112M4	360	631
			KA	107R77	DRN	112M4	320	631
			KAF	107R77	DRN	112M4	340	631
4.6	318	65000	K	107R77	DRN	132S4	355	631
5.1	286	65000	KF	107R77	DRN	132S4	370	631
5.8	251	65000	KA	107R77	DRN	132S4	330	631
			KAF	107R77	DRN	132S4	355	631

M_{a max} = 13000 Nm								
n_a rpm	i	F_{Ra}¹⁾ N					m kg	
0.08	17550	79200	K	127R77	DR	63M4	470	631
0.08	16006	79200	KF	127R77	DR	63M4	510	631
0.09	14975	79200	KA	127R77	DR	63M4	440	631
0.11	12440	79200	KAF	127R77	DR	63M4	480	631
0.12	10915	79200	K	127R77	DR	63L4	470	631
0.13	9819	79200	KF	127R77	DR	63L4	510	631
0.15	8443	79200	KA	127R77	DR	63L4	440	631
			KAF	127R77	DR	63L4	480	631
0.18	7482	79200	K	127R77	DRS	71S4	470	631
			KF	127R77	DRS	71S4	510	631
0.21	6565	79200	KA	127R77	DRS	71S4	445	631
			KAF	127R77	DRS	71S4	480	631
0.23	5804	79200	K	127R77	DRS	71M4	475	631
0.27	5027	79200	KF	127R77	DRS	71M4	520	631
0.31	4423	79200	KA	127R77	DRS	71M4	445	631
0.35	3889	79200	KAF	127R77	DRS	71M4	485	631
0.43	3311	79200	K	127R77	DRN	80M4	480	631
			KF	127R77	DRN	80M4	520	631
0.48	3009	79200	KA	127R77	DRN	80M4	450	631
			KAF	127R77	DRN	80M4	490	631
0.56	2607	79200	K	127R77	DRN	90S4	485	631
			KF	127R77	DRN	90S4	530	631
0.64	2268	79200	KA	127R77	DRN	90S4	455	631
			KAF	127R77	DRN	90S4	495	631
0.76	1926	79200	K	127R77	DRN	90L4	485	631
0.83	1757	79200	KF	127R77	DRN	90L4	530	631
0.95	1541	79200	KA	127R77	DRN	90L4	455	631
			KAF	127R77	DRN	90L4	495	631
1.1	1342	79200	K	127R77	DRN	100LS4	490	631
1.2	1177	79200	KF	127R77	DRN	100LS4	530	631
1.4	1025	79200	KA	127R77	DRN	100LS4	460	631
			KAF	127R77	DRN	100LS4	500	631
1.6	899	79200	K	127R77	DRN	100L4	495	631
			KF	127R77	DRN	100L4	540	631
1.8	790	79200	KA	127R77	DRN	100L4	470	631
			KAF	127R77	DRN	100L4	510	631
2.1	704	79200	K	127R77	DRN	112M4	510	631
2.4	610	79200	KF	127R77	DRN	112M4	550	631
2.7	549	79200	KA	127R77	DRN	112M4	480	631
			KAF	127R77	DRN	112M4	520	631
3.1	477	79200	K	127R77	DRN	132S4	520	631
			KF	127R77	DRN	132S4	560	631
3.5	418	79200	KA	127R77	DRN	132S4	490	631
			KAF	127R77	DRN	132S4	530	631
2.7	536	79200	K	127R87	DRN	132S4	540	631
3.1	473	79200	KF	127R87	DRN	132S4	580	631
3.5	418	79200	KA	127R87	DRN	132S4	510	631
			KAF	127R87	DRN	132S4	550	631
4.0	367	79200	K	127R87	DRN	132M4	560	631
4.4	330	79200	KF	127R87	DRN	132M4	600	631
			KA	127R87	DRN	132M4	530	631
			KAF	127R87	DRN	132M4	560	631
5.1	287	79200	K	127R87	DRN	132L4	560	631
5.8	253	79200	KF	127R87	DRN	132L4	610	631
			KA	127R87	DRN	132L4	540	631
			KAF	127R87	DRN	132L4	570	631

M_{a max} = 18000 Nm								
n_a rpm	i	F_{Ra}¹⁾ N					m kg	
0.08	17679	112200	K	157R97	DRS	71M4	790	632
0.09	15729	112200		157R97	DRS	71M4	870	632
0.09	14721	112200		157R97	DRS	71M4	750	632
0.10	13097	112200		157R97	DRS	71M4	810	632
0.12	11368	112200		157R97	DRS	71M4		
0.13	10114	112200		157R97	DRS	71M4		
0.16	8718	112200		157R97	DRS	71M4		
0.18	7734	112200		157R97	DRS	71M4		
0.28	5074	112200	K	157R97	DRN	80M4	800	632
0.32	4514	112200	KF	157R97	DRN	80M4	870	632
			KA	157R97	DRN	80M4	760	632
			KAF	157R97	DRN	80M4	820	632
0.37	3979	112200	K	157R97	DRN	90S4	800	632
0.41	3516	112200	KF	157R97	DRN	90S4	880	632
0.48	3051	112200	KA	157R97	DRN	90S4	760	632
			KAF	157R97	DRN	90S4	820	632
0.56	2610	112200	K	157R97	DRN	90L4	800	632
0.63	2322	112200	KF	157R97	DRN	90L4	880	632
			KA	157R97	DRN	90L4	770	632
			KAF	157R97	DRN	90L4	830	632
0.71	2029	112200	K	157R97	DRN	100LS4	810	632
0.80	1805	112200	KF	157R97	DRN	100LS4	890	632
			KA	157R97	DRN	100LS4	770	632
			KAF	157R97	DRN	100LS4	830	632
0.87	1659	112200	K	157R97	DRN	100LS4	800	632
			KF	157R97	DRN	100LS4	880	632
			KA	157R97	DRN	100LS4	770	632
			KAF	157R97	DRN	100LS4	830	632
1.1	1365	112200	K	157R97	DRN	100L4	810	632
1.2	1229	112200	KF	157R97	DRN	100L4	890	632
1.3	1093	112200	KA	157R97	DRN	100L4	780	632
			KAF	157R97	DRN	100L4	830	632
1.6	942	112200	K	157R97	DRN	112M4	820	632
1.7	854	112200	KF	157R97	DRN	112M4	900	632
			KA	157R97	DRN	112M4	780	632
			KAF	157R97	DRN	112M4	840	632
1.9	756	112200	K	157R97	DRN	132S4	830	632
2.2	661	112200	KF	157R97	DRN	132S4	910	632
2.6	567	112200	KA	157R97	DRN	132S4	800	632
			KAF	157R97	DRN	132S4	850	632
2.9	504	112200	K	157R97	DRN	132M4	850	632
3.4	434	112200	KF	157R97	DRN	132M4	930	632
			KA	157R97	DRN	132M4	810	632
			KAF	157R97	DRN	132M4	870	632
3.9	379	112200	K	157R97	DRN	132L4	860	632
4.4	333	112200	KF	157R97	DRN	132L4	940	632
			KA	157R97	DRN	132L4	820	632
			KAF	157R97	DRN	132L4	880	632
5.1	291	112200	K	157R97	DRN	160M4	890	632
			KF	157R97	DRN	160M4	970	632
			KA	157R97	DRN	160M4	850	632
			KAF	157R97	DRN	160M4	910	632
3.8	385	112200	K	157R107	DRN	132L4	910	632
			KF	157R107	DRN	132L4	980	632
			KA	157R107	DRN	132L4	870	632
			KAF	157R107	DRN	132L4	930	632
4.5	325	112200	K	157R107	DRN	160M4	940	632
4.9	299	112200	KF	157R107	DRN	160M4	1020	632
			KA	157R107	DRN	160M4	900	632
			KAF	157R107	DRN	160M4	960	632
5.8	253	112200	K	157R107	DRN	160L4	950	632
6.4	230	112200	KF	157R107	DRN	160L4	1030	632
6.9	213	112200	KA	157R107	DRN	160L4	920	632
			KAF	157R107	DRN	160L4	980	632

M_{a max} = 32000 Nm								
n_a rpm	i	F_{Ra}¹⁾ N					m kg	
0.07	19723	150000	K KH	167R97	DRS	71M4	1190 1150	632 632
0.08	17406	150000						
0.09	15000	150000						
0.10	13238	150000						
0.12	11573	150000						
0.13	10264	150000						
0.17	8628	150000	K KH	167R97	DRN	80M4	1190 1150	632 632
0.22	6562	150000						
0.27	5355	150000	K KH	167R97	DRN	90S4	1190 1160	632 632
0.31	4788	150000						
0.36	4079	150000	K KH	167R97	DRN	90L4	1200 1160	632 632
0.43	3376	150000						
0.53	2755	150000	K KH	167R97	DRN	100LS4	1200 1160	632 632
0.64	2263	150000						
0.67	2182	150000	K KH	167R97	DRN	100L4	1210 1170	632 632
0.86	1704	150000						
1.0	1408	150000	K KH	167R97	DRN	112M4	1210 1180	632 632
1.1	1296	150000						
1.3	1101	150000	K KH	167R97	DRN	132S4	1230 1190	632 632
1.6	944	150000						
1.7	843	150000	K KH	167R97	DRN	132M4	1240 1210	632 632
1.9	757	150000						
2.3	632	150000	K KH	167R97	DRN	132L4	1250 1210	632 632
2.6	561	150000						
3.1	481	150000	K KH	167R97	DRN	160M4	1280 1250	632 632
3.5	423	150000						
4.0	369	150000	K KH	167R97	DRN	160L4	1300 1260	632 632
4.6	318	150000						
5.3	278	150000	K KH	167R107	DRN	180M4	1370 1330	632 632
6.1	244	150000						
6.9	213	150000	K KH	167R107	DRN	180L4	1380 1350	632 632
7.2	206	150000						
8.2	180	150000	K KH	167R107	DRN	200L4	1490 1460	632 632
9.3	160	150000						
11	135	150000	K KH	167R107	DRN	225S4	1530 1490	632 632
13	118	150000						



M_{a max} = 50000 Nm								
n_a rpm	i	F_{Ra}¹⁾ N					m kg	
0.04	32625	190000	K KH	187R97	DRS	71M4	1770 1700	632 632
0.05	27165	190000						
0.06	24353	190000						
0.07	19144	190000						
0.08	16978	190000						
0.10	14272	190000	K KH	187R97	DRN	80M4	1770 1700	632 632
0.11	13116	190000						
0.12	11647	190000	K KH	187R97	DRN	90S4	1780 1710	632 632
0.14	10413	190000						
0.16	9363	190000						

$M_{a \max} = 50000 \text{ Nm}$





n_a rpm	i	$F_{Ra}^{1)}$ N					m kg	
0.18	8126	190000	K KH	187R97	DRN	90L4	1780	632
0.20	7343	190000		187R97	DRN	90L4	1710	632
0.22	6747	190000						
0.24	5991	190000						
0.27	5358	190000	K KH	187R97	DRN	100LS4	1780	632
0.30	4817	190000		187R97	DRN	100LS4	1720	632
0.33	4370	190000						
0.40	3609	190000	K KH	187R97	DRN	100L4	1790	632
0.48	3062	190000		187R97	DRN	100L4	1720	632
0.58	2519	190000	K KH	187R97	DRN	112M4	1800	632
0.65	2268	190000		187R97	DRN	112M4	1730	632
0.71	2054	190000	K KH	187R97	DRN	132S4	1810	632
0.80	1821	190000		187R97	DRN	132S4	1740	632
0.91	1605	190000						
1.0	1395	190000	K KH	187R97	DRN	132M4	1830	632
1.2	1196	190000		187R97	DRN	132M4	1760	632
1.4	1046	190000	K KH	187R97	DRN	132L4	1830	632
1.6	945	190000		187R97	DRN	132L4	1770	632
2.0	738	190000	K KH	187R97	DRN	160L4	1880	632
2.4	621	190000		187R97	DRN	160L4	1820	632
2.8	527	190000	K KH	187R97	DRN	180M4	1900	632
				187R97	DRN	180M4	1840	632
1.8	835	190000	K KH	187R107	DRN	160M4	1910	632
				187R107	DRN	160M4	1850	632
2.0	729	190000	K KH	187R107	DRN	160L4	1930	632
2.4	622	190000		187R107	DRN	160L4	1860	632
2.8	520	190000	K KH	187R107	DRN	180M4	1950	632
3.3	454	190000		187R107	DRN	180M4	1880	632
4.2	355	190000	K KH	187R107	DRN	200L4	2080	632
				187R107	DRN	200L4	2010	632
5.7	261	190000	K KH	187R107	DRN	225S4	2110	632
				187R107	DRN	225S4	2040	632
6.7	221	190000	K KH	187R107	DRN	225M4	2110	632
7.7	193	190000		187R107	DRN	225M4	2040	632

33 008 00 15

K19..




KA19B..

**KH19B..**

(→ 📄 155)	DR63..	DR71S	DR71M	DRN80M	DRN90S			
AC	132	139	139	156	179			
AD	105	119	119	128	140			
ADS	105	129	129	139	150			
L	357	368	393	448	449			
LS	412	436	461	529	543			
LB	191	202	227	282	283			
LBS	246	270	295	363	377			


33 009 00 15

KF19B..





KAF19B..

ø 120
max. DR71M




ø 160



(→ 155)	DR63..	DR71S	DR71M	DRN80M	DRN90S			
AC	132	139	139	156	179			
AD	105	119	119	128	140			
ADS	105	129	129	139	150			
L	357	368	393	448	449			
LS	412	436	461	529	543			
LB	191	202	227	282	283			
LBS	246	270	295	363	377			

33 010 00 15


KHF19B..

(→ 155)	DR63..	DR71S	DR71M	DRN80M	DRN90S			
AC	132	139	139	156	179			
AD	105	119	119	128	140			
ADS	105	129	129	139	150			
L	357	368	393	448	449			
LS	412	436	461	529	543			
LB	191	202	227	282	283			
LBS	246	270	295	363	377			

21933170/DE – 11/2015


33 011 00 15

KF19..





KAF19..

**$\varnothing 120$
max. DR71M**




$\varnothing 160$



(→ 155)	DR63..	DR71S	DR71M	DRN80M	DRN90S			
AC	132	139	139	156	179			
AD	105	119	119	128	140			
ADS	105	129	129	139	150			
L	357	368	393	448	449			
LS	412	436	461	529	543			
LB	191	202	227	282	283			
LBS	246	270	295	363	377			



33 013 00 15

KHF19..




(→ 155)	DR63..	DR71S	DR71M	DRN80M	DRN90S			
AC	132	139	139	156	179			
AD	105	119	119	128	140			
ADS	105	129	129	139	150			
L	357	368	393	448	449			
LS	412	436	461	529	543			
LB	191	202	227	282	283			
LBS	246	270	295	363	377			

KA19..





33 014 00 15





10

KA19..



KH19..




21933170/DE – 11/2015

(→ 155)	DR63..	DR71S	DR71M	DRN80M	DRN90S			
AC	132	139	139	156	179			
AD	105	119	119	128	140			
ADS	105	129	129	139	150			
L	357	368	393	448	449			
LS	412	436	461	529	543			
LB	191	202	227	282	283			
LBS	246	270	295	363	377			


SEW
EURODRIVE

33 364 00 15


KA29B..




KA29B..





KH29B..



Ø 30 H7
DIN 6885-3








Ø 25 H7



21933170/DE – 11/2015

(→ 155)	DR63..	DR71S	DR71M	DRN80M	DRN90S	DRN90L		
AC	132	139	139	156	179	179		
AD	105	119	119	128	140	140		
ADS	105	129	129	139	150	150		
L	388	399	424	479	480	512		
LS	443	467	492	560	574	606		
LB	191	202	227	282	283	315		
LBS	246	270	295	363	377	409		


33 016 00 15

KF29B..**KAF29B..****160**
max. DR71M**200****30 H7**
DIN 6985-3**25 H7**




(→ 155)	DR63..	DR71S	DR71M	DRN80M	DRN90S	DRN90L		
AC	132	139	139	156	179	179		
AD	105	119	119	128	140	140		
ADS	105	129	129	139	150	150		
L	388	399	424	479	480	512		
LS	443	467	492	560	574	606		
LB	191	202	227	282	283	315		
LBS	246	270	295	363	377	409		

33 017 00 15

KHF29B..



10




21933170/DE – 11/2015


(→ 155)	DR63..	DR71S	DR71M	DRN80M	DRN90S	DRN90L		
AC	132	139	139	156	179	179		
AD	105	119	119	128	140	140		
ADS	105	129	129	139	150	150		
L	388	399	424	479	480	512		
LS	443	467	492	560	574	606		
LB	191	202	227	282	283	315		
LBS	246	270	295	363	377	409		

33 018 00 15



KF29..




KAF29..

ø 160
max. DR71M

ø 200

ø 30 H7
DIN 6985-3


ø 25 H7






(→ 155)	DR63..	DR71S	DR71M	DRN80M	DRN90S	DRN90L		
AC	132	139	139	156	179	179		
AD	105	119	119	128	140	140		
ADS	105	129	129	139	150	150		
L	386	397	422	477	478	510		
LS	441	465	490	558	572	604		
LB	191	202	227	282	283	315		
LBS	246	270	295	363	377	409		

KHF29..

33 019 00 15



10






21933170/DE – 11/2015

(→ 155)	DR63..	DR71S	DR71M	DRN80M	DRN90S	DRN90L		
AC	132	139	139	156	179	179		
AD	105	119	119	128	140	140		
ADS	105	129	129	139	150	150		
L	386	397	422	477	478	510		
LS	441	465	490	558	572	604		
LB	191	202	227	282	283	315		
LBS	246	270	295	363	377	409		

33 037 00 14

K37..







10

21933170/DE – 11/2015

(→ 155)	DR63..	DR71S	DR71M	DRN80M	DRN90S	DRN90L	DRN100LS	DRN100L
AC	132	139	139	156	179	179	197	197
AD	105	119	119	128	140	140	157	157
ADS	105	129	129	139	150	150	158	158
L	393	404	429	484	485	517	516	566
LS	448	472	497	565	579	611	610	660
LB	191	202	227	282	283	315	314	364
LBS	246	270	295	363	377	409	408	458



33 038 00 14

KF37..**KAF37..****KHF37..****KVF37..**

(→ 155)	DR63..	DR71S	DR71M	DRN80M	DRN90S	DRN90L	DRN100LS	DRN100L
AC	132	139	139	156	179	179	197	197
AD	105	119	119	128	140	140	157	157
ADS	105	129	129	139	150	150	158	158
L	402	413	438	493	494	526	525	575
LS	457	481	506	574	588	620	619	669
LB	191	202	227	282	283	315	314	364
LBS	246	270	295	363	377	409	408	458

KA37..




33 039 00 14



KA37..

KH37..



KV37..



21933170/DE – 11/2015

(→ 155)	DR63..	DR71S	DR71M	DRN80M	DRN90S	DRN90L	DRN100LS	DRN100L
AC	132	139	139	156	179	179	197	197
AD	105	119	119	128	140	140	157	157
ADS	105	129	129	139	150	150	158	158
L	402	413	438	493	494	526	525	575
LS	457	481	506	574	588	620	619	669
LB	191	202	227	282	283	315	314	364
LBS	246	270	295	363	377	409	408	458


33 040 00 14

KAZ37..**KAZ37..****KHZ37..****KVZ37..**

(→ 155)	DR63..	DR71S	DR71M	DRN80M	DRN90S	DRN90L	DRN100LS	DRN100L
AC	132	139	139	156	179	179	197	197
AD	105	119	119	128	140	140	157	157
ADS	105	129	129	139	150	150	158	158
L	402	413	438	493	494	526	525	575
LS	457	481	506	574	588	620	619	669
LB	191	202	227	282	283	315	314	364
LBS	246	270	295	363	377	409	408	458

KZ37..

33 232 00 15




10

21933170/DE – 11/2015

(→ 155)	DR63..	DR71S	DR71M	DRN80M	DRN90S	DRN90L	DRN100LS	DRN100L
AC	132	139	139	156	179	179	197	197
AD	105	119	119	128	140	140	157	157
ADS	105	129	129	139	150	150	158	158
L	402	413	438	493	494	526	525	575
LS	457	481	506	574	588	620	619	669
LB	191	202	227	282	283	315	314	364
LBS	246	270	295	363	377	409	408	458

KT37..

33 041 00 14



(→ 155)	DR63..	DR71S	DR71M	DRN80M	DRN90S	DRN90L	DRN100LS	DRN100L
AC	132	139	139	156	179	179	197	197
AD	105	119	119	128	140	140	157	157
ADS	105	129	129	139	150	150	158	158
L	402	413	438	493	494	526	525	575
LS	457	481	506	574	588	620	619	669
LB	191	202	227	282	283	315	314	364
LBS	246	270	295	363	377	409	408	458





21933170/DE – 11/2015

[illegible]

SEW
EURODRIVE

21933170/DE – 11/2015




33 022 00 14

KF39..**KAF39..****Ø 30 H7****Ø 35 H7**


(→ 155)	DR63..	DR71S	DR71M	DRN80M	DRN90S	DRN90L	DRN100LS	DRN100L	DRN112M
AC	132	139	139	156	179	179	197	197	221
AD	105	119	119	128	140	140	157	157	170
ADS	105	129	129	139	150	150	158	158	172
L	436	447	472	526	528	560	556	606	637
LS	491	515	540	607	621	653	650	700	749
LB	185	196	221	275	277	309	305	355	386
LBS	240	264	289	356	370	402	399	449	498

KA39..


33 023 00 14



Ø 30 H7



Ø 35 H7








21933170/DE – 11/2015

(→ 155)	DR63..	DR71S	DR71M	DRN80M	DRN90S	DRN90L	DRN100LS	DRN100L	DRN112M
AC	132	139	139	156	179	179	197	197	221
AD	105	119	119	128	140	140	157	157	170
ADS	105	129	129	139	150	150	158	158	172
L	436	447	472	526	528	560	556	606	637
LS	491	515	540	607	621	653	650	700	749
LB	185	196	221	275	277	309	305	355	386
LBS	240	264	289	356	370	402	399	449	498

KT39..




33 024 00 14





(→ 155)	DR63..	DR71S	DR71M	DRN80M	DRN90S	DRN90L	DRN100LS	DRN100L	DRN112M
AC	132	139	139	156	179	179	197	197	221
AD	105	119	119	128	140	140	157	157	170
ADS	105	129	129	139	150	150	158	158	172
L	436	447	472	526	528	560	556	606	637
LS	491	515	540	607	621	653	650	700	749
LB	185	196	221	275	277	309	305	355	386
LBS	240	264	289	356	370	402	399	449	498

33 042 00 14



K47..





KA47B..



KH47B..







KV47B..



21933170/DE – 11/2015

(→ 155)	DR63..	DR71S	DR71M	DRN80M	DRN90S	DRN90L	DRN100LS	DRN100L
AC	132	139	139	156	179	179	197	197
AD	105	119	119	128	140	140	157	157
ADS	105	129	129	139	150	150	158	158
L	422	433	458	512	514	546	542	592
LS	477	501	526	593	607	639	636	686
LB	185	196	221	275	277	309	305	355
LBS	240	264	289	356	370	402	399	449



33 043 00 14

KF47..**KAF47..****KHF47..****KVF47..**

(→ 155)	DR63..	DR71S	DR71M	DRN80M	DRN90S	DRN90L	DRN100LS	DRN100L
AC	132	139	139	156	179	179	197	197
AD	105	119	119	128	140	140	157	157
ADS	105	129	129	139	150	150	158	158
L	428	439	464	518	520	552	548	598
LS	483	507	532	599	613	645	642	692
LB	185	196	221	275	277	309	305	355
LBS	240	264	289	356	370	402	399	449

KA47..




33 044 00 14



KA47..

KH47..



KV47..



21933170/DE – 11/2015

(→ 155)	DR63..	DR71S	DR71M	DRN80M	DRN90S	DRN90L	DRN100LS	DRN100L
AC	132	139	139	156	179	179	197	197
AD	105	119	119	128	140	140	157	157
ADS	105	129	129	139	150	150	158	158
L	428	439	464	518	520	552	548	598
LS	483	507	532	599	613	645	642	692
LB	185	196	221	275	277	309	305	355
LBS	240	264	289	356	370	402	399	449

33 045 00 14


KAZ47..**KAZ47..****KHZ47..****KVZ47..**

(→ 155)	DR63..	DR71S	DR71M	DRN80M	DRN90S	DRN90L	DRN100LS	DRN100L
AC	132	139	139	156	179	179	197	197
AD	105	119	119	128	140	140	157	157
ADS	105	129	129	139	150	150	158	158
L	428	439	464	518	520	552	548	598
LS	483	507	532	599	613	645	642	692
LB	185	196	221	275	277	309	305	355
LBS	240	264	289	356	370	402	399	449

21933170/DE – 11/2015

KZ47..

33 233 00 15







10

21933170/DE – 11/2015

(→ 155)	DR63..	DR71S	DR71M	DRN80M	DRN90S	DRN90L	DRN100LS	DRN100L
AC	132	139	139	156	179	179	197	197
AD	105	119	119	128	140	140	157	157
ADS	105	129	129	139	150	150	158	158
L	428	439	464	518	520	552	548	598
LS	483	507	532	599	613	645	642	692
LB	185	196	221	275	277	309	305	355
LBS	240	264	289	356	370	402	399	449

KT47..




33 046 00 14



(→ 155)	DR63..	DR71S	DR71M	DRN80M	DRN90S	DRN90L	DRN100LS	DRN100L
AC	132	139	139	156	179	179	197	197
AD	105	119	119	128	140	140	157	157
ADS	105	129	129	139	150	150	158	158
L	428	439	464	518	520	552	548	598
LS	483	507	532	599	613	645	642	692
LB	185	196	221	275	277	309	305	355
LBS	240	264	289	356	370	402	399	449

33 025 00 14

K49..







10

21933170/DE – 11/2015

(→ 155)	DR63..	DR71S	DR71M	DRN80M	DRN90S	DRN90L	DRN100LS	DRN100L	DRN112M	DRN132S	DRN132M
AC	132	139	139	156	179	179	197	197	221	221	261
AD	105	119	119	128	140	140	157	157	170	170	228
ADS	105	129	129	139	150	150	158	158	172	172	228
L	485	496	521	575	577	609	605	655	686	736	754
LS	540	564	589	656	670	702	699	749	798	848	892
LB	178	189	214	268	270	302	298	348	379	429	447
LBS	233	257	282	349	363	395	392	442	491	541	585




33 026 01 14

KF49..**KAF49..** **$\varnothing 35$ H7** **$\varnothing 40$ H7**


(→ 155)	DR63..	DR71S	DR71M	DRN80M	DRN90S	DRN90L	DRN100LS	DRN100L	DRN112M	DRN132S	DRN132M
AC	132	139	139	156	179	179	197	197	221	221	261
AD	105	119	119	128	140	140	157	157	170	170	228
ADS	105	129	129	139	150	150	158	158	172	172	228
L	484	495	520	574	576	608	604	654	685	735	753
LS	539	563	588	655	669	701	698	748	797	847	891
LB	178	189	214	268	270	302	298	348	379	429	447
LBS	233	257	282	349	363	395	392	442	491	541	585

KA49..


33 027 01 14



$\phi 35$ H7








$\phi 40$ H7



(→ 155)	DR63..	DR71S	DR71M	DRN80M	DRN90S	DRN90L	DRN100LS	DRN100L	DRN112M	DRN132S	DRN132M
AC	132	139	139	156	179	179	197	197	221	221	261
AD	105	119	119	128	140	140	157	157	170	170	228
ADS	105	129	129	139	150	150	158	158	172	172	228
L	484	495	520	574	576	608	604	654	685	735	753
LS	539	563	588	655	669	701	698	748	797	847	891
LB	178	189	214	268	270	302	298	348	379	429	447
LBS	233	257	282	349	363	395	392	442	491	541	585

KT49..


33 028 00 14



(→ 155)	DR63..	DR71S	DR71M	DRN80M	DRN90S	DRN90L	DRN100LS	DRN100L	DRN112M	DRN132S	DRN132M
AC	132	139	139	156	179	179	197	197	221	221	261
AD	105	119	119	128	140	140	157	157	170	170	228
ADS	105	129	129	139	150	150	158	158	172	172	228
L	484	495	520	574	576	608	604	654	685	735	753
LS	539	563	588	655	669	701	698	748	797	847	891
LB	178	189	214	268	270	302	298	348	379	429	447
LBS	233	257	282	349	363	395	392	442	491	541	585

33 047 00 14


K57..



KA57B..

KH57B..

KV57B..




21933170/DE – 11/2015

(→ 155)	DR63..	DR71S	DR71M	DRN80M	DRN90S	DRN90L	DRN100LS	DRN100L	DRN112M
AC	132	139	139	156	179	179	197	197	221
AD	105	119	119	128	140	140	157	157	170
ADS	105	129	129	139	150	150	158	158	172
L	438	449	474	528	530	562	558	608	639
LS	493	517	542	609	623	655	652	702	751
LB	185	196	221	275	277	309	305	355	386
LBS	240	264	289	356	370	402	399	449	498

581

KZ57..

33 234 00 15






10

21933170/DE – 11/2015



(→ 155)	DR63..	DR71S	DR71M	DRN80M	DRN90S	DRN90L	DRN100LS	DRN100L	DRN112M
AC	132	139	139	156	179	179	197	197	221
AD	105	119	119	128	140	140	157	157	170
ADS	105	129	129	139	150	150	158	158	172
L	454	465	490	544	546	578	574	624	655
LS	509	533	558	625	639	671	668	718	767
LB	185	196	221	275	277	309	305	355	386
LBS	240	264	289	356	370	402	399	449	498

33 052 00 14



K67..





KA67B..



KH67B..







KV67B..



21933170/DE – 11/2015

(→ 155)	DR63..	DR71S	DR71M	DRN80M	DRN90S	DRN90L	DRN100LS	DRN100L	DRN112M	DRN132S
AC	132	139	139	156	179	179	197	197	221	221
AD	105	119	119	128	140	140	157	157	170	170
ADS	105	129	129	139	150	150	158	158	172	172
L	454	465	490	544	546	578	574	624	655	709
LS	509	533	558	625	639	671	668	718	767	821
LB	185	196	221	275	277	309	305	355	386	440
LBS	240	264	289	356	370	402	399	449	498	552



33 053 00 14

KF67..**KAF67..****KHF67..****KVF67..**

(→ 155)	DR63..	DR71S	DR71M	DRN80M	DRN90S	DRN90L	DRN100LS	DRN100L	DRN112M	DRN132S
AC	132	139	139	156	179	179	197	197	221	221
AD	105	119	119	128	140	140	157	157	170	170
ADS	105	129	129	139	150	150	158	158	172	172
L	459	470	495	549	551	583	579	629	660	714
LS	514	538	563	630	644	676	673	723	772	826
LB	185	196	221	275	277	309	305	355	386	440
LBS	240	264	289	356	370	402	399	449	498	552

587





33 055 00 14

KAZ67..**KAZ67..****KHZ67..****KVZ67..**

(→ 155)	DR63..	DR71S	DR71M	DRN80M	DRN90S	DRN90L	DRN100LS	DRN100L	DRN112M	DRN132S
AC	132	139	139	156	179	179	197	197	221	221
AD	105	119	119	128	140	140	157	157	170	170
ADS	105	129	129	139	150	150	158	158	172	172
L	459	470	495	549	551	583	579	629	660	714
LS	514	538	563	630	644	676	673	723	772	826
LB	185	196	221	275	277	309	305	355	386	440
LBS	240	264	289	356	370	402	399	449	498	552

Technical drawing of a motor with dimensions:


- LS: Total length
- L: Length to the center of the motor
- 274: Distance from the center of the motor to the center of the shaft
- LBS: Length of the shaft
- 179: Distance from the center of the motor to the center of the shaft
- LB: Length of the shaft
- 20: Distance from the center of the motor to the center of the shaft
- 160: Distance from the center of the motor to the center of the shaft
- 125: Distance from the center of the motor to the center of the shaft
- 182: Distance from the center of the motor to the center of the shaft
- AC: Distance from the center of the motor to the center of the shaft



(→ 📄 155)	DR63..	DR71S	DR71M	DRN80M	DRN90S	DRN90L	DRN100LS	DRN100L	DRN112M	DRN132S
AC	132	139	139	156	179	179	197	197	221	221
AD	105	119	119	128	140	140	157	157	170	170
ADS	105	129	129	139	150	150	158	158	172	172
L	459	470	495	549	551	583	579	629	660	714
LS	514	538	563	630	644	676	673	723	772	826
LB	185	196	221	275	277	309	305	355	386	440
LBS	240	264	289	356	370	402	399	449	498	552

KT67..




33 056 00 14





(→ 155)	DR63..	DR71S	DR71M	DRN80M	DRN90S	DRN90L	DRN100LS	DRN100L	DRN112M	DRN132S
AC	132	139	139	156	179	179	197	197	221	221
AD	105	119	119	128	140	140	157	157	170	170
ADS	105	129	129	139	150	150	158	158	172	172
L	459	470	495	549	551	583	579	629	660	714
LS	514	538	563	630	644	676	673	723	772	826
LB	185	196	221	275	277	309	305	355	386	440
LBS	240	264	289	356	370	402	399	449	498	552

33 057 00 14



K77..





KA77B..



KH77B..







KV77B..



(→ 155)	DRN80M	DRN90S	DRN90L	DRN100LS	DRN100L	DRN112M	DRN132S	DRN132M	DRN132L	DRN160M
AC	156	179	179	197	197	221	221	261	261	314
AD	128	140	140	157	157	170	170	228	228	253
ADS	139	150	150	158	158	172	172	228	228	253
L	582	584	616	612	662	693	743	761	787	853
LS	663	677	709	706	756	805	855	899	924	1042
LB	268	270	302	298	348	379	429	447	473	539
LBS	349	363	395	392	442	491	541	585	610	728





33 058 00 14

KF77..**KAF77..****KHF77..****KVF77..**

(→ 155)	DRN80M	DRN90S	DRN90L	DRN100LS	DRN100L	DRN112M	DRN132S	DRN132M	DRN132L	DRN160M
AC	156	179	179	197	197	221	221	261	261	314
AD	128	140	140	157	157	170	170	228	228	253
ADS	139	150	150	158	158	172	172	228	228	253
L	580	582	614	610	660	691	741	759	785	851
LS	661	675	707	704	754	803	853	897	922	1040
LB	268	270	302	298	348	379	429	447	473	539
LBS	349	363	395	392	442	491	541	585	610	728

Technical drawing of a SEW motor showing dimensions in mm. The drawing includes the following dimensions:


- LS: Total length
- L: Length to the center of the motor
- 312: Distance from the center of the motor to the center of the coupling
- LBS: Length of the coupling
- 202: Distance from the center of the motor to the center of the coupling (alternative dimension)
- LB: Length of the coupling (alternative dimension)
- 200: Diameter of the coupling
- 31.3: Distance from the center of the motor to the center of the coupling (alternative dimension)
- 139: Distance from the center of the motor to the center of the coupling (alternative dimension)
- 204: Distance from the center of the motor to the center of the coupling (alternative dimension)
- AC: Distance from the center of the motor to the center of the coupling (alternative dimension)



(→ 📄 155)	DRN80M	DRN90S	DRN90L	DRN100LS	DRN100L	DRN112M	DRN132S	DRN132M	DRN132L	DRN160M
AC	156	179	179	197	197	221	221	261	261	314
AD	128	140	140	157	157	170	170	228	228	253
ADS	139	150	150	158	158	172	172	228	228	253
L	580	582	614	610	660	691	741	759	785	851
LS	661	675	707	704	754	803	853	897	922	1040
LB	268	270	302	298	348	379	429	447	473	539
LBS	349	363	395	392	442	491	541	585	610	728

KT77..

33 061 00 14






(→ 155)	DRN80M	DRN90S	DRN90L	DRN100LS	DRN100L	DRN112M	DRN132S	DRN132M	DRN132L	DRN160M
AC	156	179	179	197	197	221	221	261	261	314
AD	128	140	140	157	157	170	170	228	228	253
ADS	139	150	150	158	158	172	172	228	228	253
L	580	582	614	610	660	691	741	759	785	851
LS	661	675	707	704	754	803	853	897	922	1040
LB	268	270	302	298	348	379	429	447	473	539
LBS	349	363	395	392	442	491	541	585	610	728

21933170/DE – 11/2015

K87..

33 062 00 14









10

KA87B..

KH87B..





KV87B..



21933170/DE – 11/2015

(→ 155)	DRN90L	DRN100LS	DRN100L	DRN112M	DRN132S	DRN132M	DRN132L	DRN160M	DRN160L	DRN180..
AC	179	197	197	221	221	261	261	314	314	357
AD	140	157	157	170	170	228	228	253	253	268
ADS	150	158	158	172	172	228	228	253	253	268
L	686	682	732	763	813	831	857	923	923	946
LS	779	776	826	875	925	969	994	1112	1112	1135
LB	297	293	343	374	424	442	468	534	534	557
LBS	390	387	437	486	536	580	605	723	723	746



33 063 00 14

KF87..**KAF87..****KHF87..****KVF87..**

(→ 155)	DRN90L	DRN100LS	DRN100L	DRN112M	DRN132S	DRN132M	DRN132L	DRN160M	DRN160L	DRN180..
AC	179	197	197	221	221	261	261	314	314	357
AD	140	157	157	170	170	228	228	253	253	268
ADS	150	158	158	172	172	228	228	253	253	268
L	687	683	733	764	814	832	858	924	924	947
LS	780	777	827	876	926	970	995	1113	1113	1136
LB	297	293	343	374	424	442	468	534	534	557
LBS	390	387	437	486	536	580	605	723	723	746

599


33 065 00 14

KAZ87..**KAZ87..****KHZ87..****KVZ87..**

(→ 155)	DRN90L	DRN100LS	DRN100L	DRN112M	DRN132S	DRN132M	DRN132L	DRN160M	DRN160L	DRN180..
AC	179	197	197	221	221	261	261	314	314	357
AD	140	157	157	170	170	228	228	253	253	268
ADS	150	158	158	172	172	228	228	253	253	268
L	687	683	733	764	814	832	858	924	924	947
LS	780	777	827	876	926	970	995	1113	1113	1136
LB	297	293	343	374	424	442	468	534	534	557
LBS	390	387	437	486	536	580	605	723	723	746

KZ87..

33 237 00 15




10

21933170/DE – 11/2015

(→ 155)	DRN90L	DRN100LS	DRN100L	DRN112M	DRN132S	DRN132M	DRN132L	DRN160M	DRN160L	DRN180..
AC	179	197	197	221	221	261	261	314	314	357
AD	140	157	157	170	170	228	228	253	253	268
ADS	150	158	158	172	172	228	228	253	253	268
L	687	683	733	764	814	832	858	924	924	947
LS	780	777	827	876	926	970	995	1113	1113	1136
LB	297	293	343	374	424	442	468	534	534	557
LBS	390	387	437	486	536	580	605	723	723	746

KT87..




33 066 00 14





(→ 155)	DRN90L	DRN100LS	DRN100L	DRN112M	DRN132S	DRN132M	DRN132L	DRN160M	DRN160L	DRN180..
AC	179	197	197	221	221	261	261	314	314	357
AD	140	157	157	170	170	228	228	253	253	268
ADS	150	158	158	172	172	228	228	253	253	268
L	687	683	733	764	814	832	858	924	924	947
LS	780	777	827	876	926	970	995	1113	1113	1136
LB	297	293	343	374	424	442	468	534	534	557
LBS	390	387	437	486	536	580	605	723	723	746

33 067 00 14



K97..





KA97B..



KH97B..







KV97B..



21933170/DE – 11/2015

(→ 155)	DRN100LS	DRN100L	DRN112M	DRN132S	DRN132M	DRN132L	DRN160M	DRN160L	DRN180..	DRN200L
AC	197	197	221	221	261	261	314	314	357	394
AD	157	157	170	170	228	228	253	253	268	283
ADS	158	158	172	172	228	228	253	253	268	283
L	725	775	806	856	874	900	966	966	989	1099
LS	819	869	918	968	1012	1037	1155	1155	1178	1304
LB	288	338	369	419	437	463	529	529	552	662
LBS	382	432	481	531	575	600	718	718	741	867

33 068 00 14


KF97..**KAF97..****KHF97..****KVF97..**

(→ 155)	DRN100LS	DRN100L	DRN112M	DRN132S	DRN132M	DRN132L	DRN160M	DRN160L	DRN180..	DRN200L
AC	197	197	221	221	261	261	314	314	357	394
AD	157	157	170	170	228	228	253	253	268	283
ADS	158	158	172	172	228	228	253	253	268	283
L	723	773	804	854	872	898	964	964	987	1097
LS	817	867	916	966	1010	1035	1153	1153	1176	1302
LB	288	338	369	419	437	463	529	529	552	662
LBS	382	432	481	531	575	600	718	718	741	867

21933170/DE – 11/2015

KA97..


33 069 00 14



KA97..



KH97..

KV97..



(→ 155)	DRN100LS	DRN100L	DRN112M	DRN132S	DRN132M	DRN132L	DRN160M	DRN160L	DRN180..	DRN200L
AC	197	197	221	221	261	261	314	314	357	394
AD	157	157	170	170	228	228	253	253	268	283
ADS	158	158	172	172	228	228	253	253	268	283
L	723	773	804	854	872	898	964	964	987	1097
LS	817	867	916	966	1010	1035	1153	1153	1176	1302
LB	288	338	369	419	437	463	529	529	552	662
LBS	382	432	481	531	575	600	718	718	741	867


33 070 00 14

KAZ97..**KAZ97..****KHZ97..****KVZ97..**

(→ 155)	DRN100LS	DRN100L	DRN112M	DRN132S	DRN132M	DRN132L	DRN160M	DRN160L	DRN180..	DRN200L
AC	197	197	221	221	261	261	314	314	357	394
AD	157	157	170	170	228	228	253	253	268	283
ADS	158	158	172	172	228	228	253	253	268	283
L	723	773	804	854	872	898	964	964	987	1097
LS	817	867	916	966	1010	1035	1153	1153	1176	1302
LB	288	338	369	419	437	463	529	529	552	662
LBS	382	432	481	531	575	600	718	718	741	867

KZ97..

33 238 00 15^L




10

21933170/DE – 11/2015

(→ 155)	DRN100LS	DRN100L	DRN112M	DRN132S	DRN132M	DRN132L	DRN160M	DRN160L	DRN180..	DRN200L
AC	197	197	221	221	261	261	314	314	357	394
AD	157	157	170	170	228	228	253	253	268	283
ADS	158	158	172	172	228	228	253	253	268	283
L	723	773	804	854	872	898	964	964	987	1097
LS	817	867	916	966	1010	1035	1153	1153	1176	1302
LB	288	338	369	419	437	463	529	529	552	662
LBS	382	432	481	531	575	600	718	718	741	867

KT97..

33 071 00 14




(→ 155)	DRN100LS	DRN100L	DRN112M	DRN132S	DRN132M	DRN132L	DRN160M	DRN160L	DRN180..	DRN200L
AC	197	197	221	221	261	261	314	314	357	394
AD	157	157	170	170	228	228	253	253	268	283
ADS	158	158	172	172	228	228	253	253	268	283
L	723	773	804	854	872	898	964	964	987	1097
LS	817	867	916	966	1010	1035	1153	1153	1176	1302
LB	288	338	369	419	437	463	529	529	552	662
LBS	382	432	481	531	575	600	718	718	741	867

21933170/DE – 11/2015

K107..

33 072 00 14




10

KA107B..

KH107B..





KV107B..



21933170/DE – 11/2015

(→ 155)	DRN100L	DRN112M	DRN132S	DRN132M	DRN132L	DRN160M	DRN160L	DRN180..	DRN200L	DRN225..
AC	197	221	221	261	261	314	314	357	394	434
AD	157	170	170	228	228	253	253	268	283	305
ADS	158	172	172	228	228	253	253	268	283	305
L	873	904	954	972	998	1064	1064	1087	1197	1171
LS	967	1016	1066	1110	1135	1253	1253	1276	1402	1376
LB	332	363	413	431	457	523	523	546	656	630
LBS	426	475	525	569	594	712	712	735	861	835



33 073 00 14

KF107..**KAF107..****KHF107..****KVF107..**

(→ 155)	DRN100L	DRN112M	DRN132S	DRN132M	DRN132L	DRN160M	DRN160L	DRN180..	DRN200L	DRN225..
AC	197	221	221	261	261	314	314	357	394	434
AD	157	170	170	228	228	253	253	268	283	305
ADS	158	172	172	228	228	253	253	268	283	305
L	869	900	950	968	994	1060	1060	1083	1193	1167
LS	963	1012	1062	1106	1131	1249	1249	1272	1398	1372
LB	332	363	413	431	457	523	523	546	656	630
LBS	426	475	525	569	594	712	712	735	861	835

KA107..




33 074 00 14



KA107..

KH107..

KV107..




21933170/DE – 11/2015

(→ 155)	DRN100L	DRN112M	DRN132S	DRN132M	DRN132L	DRN160M	DRN160L	DRN180..	DRN200L	DRN225..
AC	197	221	221	261	261	314	314	357	394	434
AD	157	170	170	228	228	253	253	268	283	305
ADS	158	172	172	228	228	253	253	268	283	305
L	869	900	950	968	994	1060	1060	1083	1193	1167
LS	963	1012	1062	1106	1131	1249	1249	1272	1398	1372
LB	332	363	413	431	457	523	523	546	656	630
LBS	426	475	525	569	594	712	712	735	861	835

KZ107..

33 239 00 15







10

21933170/DE – 11/2015

(→ 155)	DRN100L	DRN112M	DRN132S	DRN132M	DRN132L	DRN160M	DRN160L	DRN180..	DRN200L	DRN225..
AC	197	221	221	261	261	314	314	357	394	434
AD	157	170	170	228	228	253	253	268	283	305
ADS	158	172	172	228	228	253	253	268	283	305
L	869	900	950	968	994	1060	1060	1083	1193	1167
LS	963	1012	1062	1106	1131	1249	1249	1272	1398	1372
LB	332	363	413	431	457	523	523	546	656	630
LBS	426	475	525	569	594	712	712	735	861	835

KT107..




33 076 00 14





(→ 155)	DRN100L	DRN112M	DRN132S	DRN132M	DRN132L	DRN160M	DRN160L	DRN180..	DRN200L	DRN225..
AC	197	221	221	261	261	314	314	357	394	434
AD	157	170	170	228	228	253	253	268	283	305
ADS	158	172	172	228	228	253	253	268	283	305
L	869	900	950	968	994	1060	1060	1083	1193	1167
LS	963	1012	1062	1106	1131	1249	1249	1272	1398	1372
LB	332	363	413	431	457	523	523	546	656	630
LBS	426	475	525	569	594	712	712	735	861	835

K127..



33 077 00 14



KA127B..






KH127B..



21933170/DE – 11/2015

(→ 155)	DRN132M	DRN132L	DRN160M	DRN160L	DRN180..	DRN200L	DRN225..	DRN250M	DRN280S	DRN280M
AC	261	261	314	314	357	394	434	495	495	495
AD	228	228	253	253	268	283	305	394	394	394
ADS	228	228	253	253	268	283	305	394	394	394
L	1031	1057	1123	1123	1146	1256	1230	1367	1367	1462
LS	1169	1194	1312	1312	1335	1461	1435	1607	1607	1702
LB	416	442	508	508	531	641	615	752	752	847
LBS	554	579	697	697	720	846	820	992	992	1087


33 078 00 14

KF127..**KAF127..****KHF127..**


(→ 155)	DRN132M	DRN132L	DRN160M	DRN160L	DRN180..	DRN200L	DRN225..	DRN250M	DRN280S	DRN280M
AC	261	261	314	314	357	394	434	495	495	495
AD	228	228	253	253	268	283	305	394	394	394
ADS	228	228	253	253	268	283	305	394	394	394
L	1031	1057	1123	1123	1146	1256	1230	1367	1367	1462
LS	1169	1194	1312	1312	1335	1461	1435	1607	1607	1702
LB	416	442	508	508	531	641	615	752	752	847
LBS	554	579	697	697	720	846	820	992	992	1087

33 079 00 14


KA127..






K../T



KA127..






KH127..



(→ 155)	DRN132M	DRN132L	DRN160M	DRN160L	DRN180..	DRN200L	DRN225..	DRN250M	DRN280S	DRN280M
AC	261	261	314	314	357	394	434	495	495	495
AD	228	228	253	253	268	283	305	394	394	394
ADS	228	228	253	253	268	283	305	394	394	394
L	1031	1057	1123	1123	1146	1256	1230	1367	1367	1462
LS	1169	1194	1312	1312	1335	1461	1435	1607	1607	1702
LB	416	442	508	508	531	641	615	752	752	847
LBS	554	579	697	697	720	846	820	992	992	1087


33 080 00 14

KAZ127..**KAZ127..****KHZ127..**

(→ 155)	DRN132M	DRN132L	DRN160M	DRN160L	DRN180..	DRN200L	DRN225..	DRN250M	DRN280S	DRN280M
AC	261	261	314	314	357	394	434	495	495	495
AD	228	228	253	253	268	283	305	394	394	394
ADS	228	228	253	253	268	283	305	394	394	394
L	1031	1057	1123	1123	1146	1256	1230	1367	1367	1462
LS	1169	1194	1312	1312	1335	1461	1435	1607	1607	1702
LB	416	442	508	508	531	641	615	752	752	847
LBS	554	579	697	697	720	846	820	992	992	1087

33 240 00 15

KZ127..




10

21933170/DE – 11/2015


(→ 155)	DRN132M	DRN132L	DRN160M	DRN160L	DRN180..	DRN200L	DRN225..	DRN250M	DRN280S	DRN280M
AC	261	261	314	314	357	394	434	495	495	495
AD	228	228	253	253	268	283	305	394	394	394
ADS	228	228	253	253	268	283	305	394	394	394
L	1031	1057	1123	1123	1146	1256	1230	1367	1367	1462
LS	1169	1194	1312	1312	1335	1461	1435	1607	1607	1702
LB	416	442	508	508	531	641	615	752	752	847
LBS	554	579	697	697	720	846	820	992	992	1087

33 081 00 14

KT127..



K../T






(→ 155)	DRN132M	DRN132L	DRN160M	DRN160L	DRN180..	DRN200L	DRN225..	DRN250M	DRN280S	DRN280M
AC	261	261	314	314	357	394	434	495	495	495
AD	228	228	253	253	268	283	305	394	394	394
ADS	228	228	253	253	268	283	305	394	394	394
L	1031	1057	1123	1123	1146	1256	1230	1367	1367	1462
LS	1169	1194	1312	1312	1335	1461	1435	1607	1607	1702
LB	416	442	508	508	531	641	615	752	752	847
LBS	554	579	697	697	720	846	820	992	992	1087

DIN 509 F2.5x0.4

K157..




33 082 00 14



10

KA157B..

KH157B..




21933170/DE – 11/2015


(→ 155)	DRN160L	DRN180..	DRN200L	DRN225..	DRN250M	DRN280S	DRN280M	DRN315S-M	DRN315ME-H
AC	314	357	394	434	495	495	495	624	624
AD	253	268	283	305	394	394	394	506	506
ADS	253	268	283	305	394	394	394	506	506
L	1206	1229	1339	1313	1450	1450	1545	1647	1777
LS	1395	1418	1544	1518	1690	1690	1785	1898	2028
LB	500	523	633	607	744	744	839	941	1071
LBS	689	712	838	812	984	984	1079	1192	1322

33 084 00 14


KA157..




K.. /T



KA157..




KH157..



(→ 155)	DRN160L	DRN180..	DRN200L	DRN225..	DRN250M	DRN280S	DRN280M	DRN315S-M	DRN315ME-H
AC	314	357	394	434	495	495	495	624	624
AD	253	268	283	305	394	394	394	506	506
ADS	253	268	283	305	394	394	394	506	506
L	1206	1229	1339	1313	1450	1450	1545	1647	1777
LS	1395	1418	1544	1518	1690	1690	1785	1898	2028
LB	500	523	633	607	744	744	839	941	1071
LBS	689	712	838	812	984	984	1079	1192	1322

33 241 00 15

KZ157..




10

21933170/DE – 11/2015


(→ 155)	DRN160L	DRN180..	DRN200L	DRN225..	DRN250M	DRN280S	DRN280M	DRN315S-M	DRN315ME-H
AC	314	357	394	434	495	495	495	624	624
AD	253	268	283	305	394	394	394	506	506
ADS	253	268	283	305	394	394	394	506	506
L	1206	1229	1339	1313	1450	1450	1545	1647	1777
LS	1395	1418	1544	1518	1690	1690	1785	1898	2028
LB	500	523	633	607	744	744	839	941	1071
LBS	689	712	838	812	984	984	1079	1192	1322

KT157..



33 086 00 14

K../T







(→ 155)	DRN160L	DRN180..	DRN200L	DRN225..	DRN250M	DRN280S	DRN280M	DRN315S-M	DRN315ME-H
AC	314	357	394	434	495	495	495	624	624
AD	253	268	283	305	394	394	394	506	506
ADS	253	268	283	305	394	394	394	506	506
L	1206	1229	1339	1313	1450	1450	1545	1647	1777
LS	1395	1418	1544	1518	1690	1690	1785	1898	2028
LB	500	523	633	607	744	744	839	941	1071
LBS	689	712	838	812	984	984	1079	1192	1322



DIN 509 F2.5x0.4

33 087 00 14

K167..







KH167B..





(→ 155)	DRN160L	DRN180..	DRN200L	DRN225..	DRN250M	DRN280S	DRN280M	DRN315S-M	DRN315ME-H
AC	314	357	394	434	495	495	495	624	624
AD	253	268	283	305	394	394	394	506	506
ADS	253	268	283	305	394	394	394	506	506
L	1337	1360	1470	1444	1581	1581	1676	1778	1908
LS	1526	1549	1675	1649	1821	1821	1916	2029	2159
LB	500	523	633	607	744	744	839	941	1071
LBS	689	712	838	812	984	984	1079	1192	1322

33 089 00 14

K187..




KH187B..



(→ 155)	DRN180..	DRN200L	DRN225..	DRN250M	DRN280S	DRN280M	DRN315S-M	DRN315ME-H
AC	357	394	434	495	495	495	624	624
AD	268	283	305	394	394	394	506	506
ADS	268	283	305	394	394	394	506	506
L	1469	1579	1553	1690	1690	1785	1887	2017
LS	1658	1784	1758	1930	1930	2025	2138	2268
LB	523	633	607	744	744	839	941	1071
LBS	712	838	812	984	984	1079	1192	1322

33 133 00 06



(→ 155)		AC	L	LS	LB	LBS
K..37R17	DR63..	132	324	379	149	204
	DR71S	139	335	403	160	228
K..39R17	DR63..	132	324	379	149	204
	DR71S	139	335	403	160	204
K..47R37	DR63..	132	356	411	191	246
	DR71S	139	367	434	202	269
	DR71M	139	392	459	227	294
	DRN80M	156	446	527	281	362
K..49R37	DR63..	132	348	403	191	246
	DR71S	139	359	426	202	269
	DR71M	139	384	451	227	294
	DRN80M	156	438	519	281	362
	DRN90S	179	440	533	283	376
	DRN90L	179	472	565	315	408
	DRN100LS	197	471	564	314	407
K..57R37	DR63..	132	356	411	191	246
	DR71S	139	367	434	202	269
	DR71M	139	392	459	227	294
	DRN80M	156	446	527	281	362
	DRN90S	179	448	541	283	376
K..67R37	DR63..	132	356	411	191	246
	DR71S	139	367	434	202	269
	DR71M	139	392	459	227	294
	DRN80M	156	446	527	281	362
K..77R37	DR63..	132	348	403	191	246
	DR71S	139	359	426	202	269
	DR71M	139	384	451	227	294
	DRN80M	156	438	519	281	362
K..87R57	DR63..	132	412	467	185	240
	DR71S	139	423	491	196	264
	DR71M	139	448	516	221	289
	DRN80M	156	502	583	275	356
	DRN90S	179	504	597	277	370
	DRN90L	179	536	629	309	402
	DRN100LS	197	533	626	305	398
	DRN100L	197	583	676	355	448
	DRN112M	221	613	725	386	498

(→ 155)		AC	L	LS	LB	LBS
K..97R57	DR63..	132	407	462	185	240
	DR71S	139	418	486	196	264
	DR71M	139	443	511	221	289
	DRN80M	156	497	578	275	356
	DRN90S	179	499	592	277	370
	DRN90L	179	531	624	309	402
	DRN100LS	197	528	621	305	398
	DRN100L	197	578	671	355	448
	DRN112M	221	608	720	386	498
K..107R77	DR63..	132	425	480	178	233
	DR71S	139	436	504	189	257
	DR71M	139	461	529	214	282
	DRN80M	156	515	596	268	349
	DRN90S	179	517	610	270	363
	DRN90L	179	549	642	302	395
	DRN100LS	197	545	638	298	391
	DRN100L	197	595	688	348	441
	DRN112M	221	626	738	379	491
	DRN132S	221	676	788	429	541
K..127R77	DR63..	132	410	465	178	233
	DR71S	139	421	489	189	257
	DR71M	139	446	514	214	282
	DRN80M	156	500	581	268	349
	DRN90S	179	502	595	270	363
	DRN90L	179	534	627	302	395
	DRN100LS	197	530	623	298	391
	DRN100L	197	580	673	348	441
	DRN112M	221	611	723	379	491
	DRN132S	221	661	773	429	541
K..127R87	DRN90L	179	577	670	297	390
	DRN100LS	197	573	666	293	386
	DRN100L	197	623	716	343	436
	DRN112M	221	654	766	374	486
	DRN132S	221	704	816	424	536
	DRN132M	261	720	859	440	579
	DRN132L	261	745	884	465	604
	DRN160M	314	814	1003	534	723
	DRN160L	314	814	1003	534	723

10

(→ 155)		AC	L	LS	LB	LBS
K..157R97	DR71M	139	529	597	204	272
	DRN80M	156	583	664	258	339
	DRN90S	179	585	678	260	353
	DRN90L	179	617	710	292	385
	DRN100LS	197	613	706	288	381
	DRN100L	197	663	756	338	431
	DRN112M	221	694	806	369	481
	DRN132S	221	744	856	419	531
	DRN132M	261	760	899	435	574
	DRN132L	261	785	924	460	599
	DRN160M	314	854	1043	529	718
	DRN160L	314	854	1043	529	718
K..167R97	DR71M	139	529	597	204	272
	DRN80M	156	583	664	258	339
	DRN90S	179	585	678	260	353
	DRN90L	179	617	710	292	385
	DRN100LS	197	613	706	288	381
	DRN100L	197	663	756	338	431
	DRN112M	221	694	806	369	481
	DRN132S	221	744	856	419	531
	DRN132M	261	760	899	435	574
	DRN132L	261	785	924	460	599
	DRN160M	314	854	1043	529	718
	DRN160L	314	854	1043	529	718
K..187R97	DR71M	139	529	597	204	272
	DRN80M	156	583	664	258	339
	DRN90S	179	585	678	260	353
	DRN90L	179	617	710	292	385
	DRN100LS	197	613	706	288	381
	DRN100L	197	663	756	338	431
	DRN112M	221	694	806	369	481
	DRN132S	221	744	856	419	531
	DRN132M	261	760	899	435	574
	DRN132L	261	785	924	460	599
	DRN160M	314	854	1043	529	718
	DRN160L	314	854	1043	529	718
K..157R107	DRN132L	261	836	975	454	593
	DRN160M	314	905	1094	523	712
	DRN160L	314	905	1094	523	712
	DRN180M	357	930	1119	548	737
	DRN180L	357	930	1119	548	737
	DRN200L	394	1038	1243	656	861
K..167R107	DRN132L	261	836	975	454	593
	DRN160M	314	905	1094	523	712
	DRN160L	314	905	1094	523	712
	DRN180M	357	930	1119	548	737
	DRN180L	357	930	1119	548	737
	DRN200L	394	1038	1243	656	861
	DRN225S	434	993	1198	611	816
	DRN225M	434	1083	1288	701	906

(→ 155)		AC	L	LS	LB	LBS
K..187R107	DRN112M	221	745	857	363	475
	DRN132M	261	811	950	429	568
	DRN132L	261	836	975	454	593
	DRN160M	314	905	1094	523	712
	DRN160L	314	905	1094	523	712
	DRN180M	357	930	1119	548	737
	DRN180L	357	930	1119	548	737
	DRN200L	394	1038	1243	656	861
	DRN225S	434	993	1198	611	816
	DRN225M	434	1083	1288	701	906
	DRN250M	495	1149	1389	767	1007