




## 9 Flachgetriebemotoren


## 9.1 Ausführungsarten F..DRN..




F..DR..

FA..B DR..  
FV..B DR..

FH..B DR..




FF..DR..




FT..DR..

13467468043


21933170/DE – 11/2015




FA..DR..  
FV..DR..




FH..DR..



FAF..DR..  
FVF..DR..




FAZ...DR..  
FVZ...DR..




FHF..DR..

13467470603



FHZ..DR..



FZ..DR..

9007212722420875

## 9.2 Geometrisch mögliche Kombinationen F..DRN..

| F27, $n_e=1400$ 1/min                                                                |                  |               |                      |        | 130 Nm                                      |                  |        |                     |
|--------------------------------------------------------------------------------------|------------------|---------------|----------------------|--------|---------------------------------------------|------------------|--------|---------------------|
| $n_a$<br>rpm                                                                         | $M_{amax}$<br>Nm | $F_{Ra}$<br>N | $\varphi_{(R)}$<br>° | i      | DR63S<br>DR63M<br>DR63L<br>DRS71S<br>DRS71M | DRN80M<br>DRN90S | DRN90L | DRN100LS<br>DRN100L |
|  3  |                  |               |                      |        |                                             |                  |        |                     |
| 9.9                                                                                  | 130              | 4500          | -                    | 140.74 |                                             |                  |        |                     |
| 11                                                                                   | 130              | 4500          | -                    | 129.09 |                                             |                  |        |                     |
| 13                                                                                   | 130              | 4500          | -                    | 109.90 |                                             |                  |        |                     |
| 15                                                                                   | 130              | 4500          | -                    | 94.76  |                                             |                  |        |                     |
| 16                                                                                   | 130              | 4500          | -                    | 88.32  |                                             |                  |        |                     |
| 18                                                                                   | 130              | 4500          | -                    | 77.21  |                                             |                  |        |                     |
| 19                                                                                   | 130              | 4500          | -                    | 72.37  |                                             |                  |        |                     |
| 22                                                                                   | 130              | 4400          | -                    | 63.86  |                                             |                  |        |                     |
| 25                                                                                   | 130              | 4180          | -                    | 56.62  |                                             |                  |        |                     |
| 28                                                                                   | 130              | 3980          | -                    | 50.19  |                                             |                  |        |                     |
| 30                                                                                   | 130              | 3860          | -                    | 46.78  |                                             |                  |        |                     |
| 34                                                                                   | 130              | 3640          | -                    | 40.89  |                                             |                  |        |                     |
| 37                                                                                   | 130              | 3530          | -                    | 38.33  |                                             |                  |        |                     |
| 41                                                                                   | 130              | 3340          | -                    | 33.83  |                                             |                  |        |                     |
|  2 |                  |               |                      |        |                                             |                  |        |                     |
| 47                                                                                   | 130              | 3140          | -                    | 29.56  |                                             |                  |        |                     |
| 52                                                                                   | 130              | 3030          | -                    | 27.18  |                                             |                  |        |                     |
| 60                                                                                   | 130              | 2820          | -                    | 23.25  |                                             |                  |        |                     |
| 69                                                                                   | 130              | 2630          | -                    | 20.15  |                                             |                  |        |                     |
| 74                                                                                   | 130              | 2550          | -                    | 18.84  |                                             |                  |        |                     |
| 86                                                                                   | 130              | 2370          | -                    | 16.28  |                                             |                  |        |                     |
| 101                                                                                  | 130              | 2180          | -                    | 13.84  |                                             |                  |        |                     |
| 113                                                                                  | 130              | 2060          | -                    | 12.35  |                                             |                  |        |                     |
| 133                                                                                  | 130              | 1900          | -                    | 10.55  |                                             |                  |        |                     |
| 142                                                                                  | 130              | 1830          | -                    | 9.88   |                                             |                  |        |                     |
| 149                                                                                  | 130              | 1660          | -                    | 9.40   |                                             |                  |        |                     |
| 172                                                                                  | 123              | 1580          | -                    | 8.13   |                                             |                  |        |                     |
| 203                                                                                  | 114              | 1530          | -                    | 6.91   |                                             |                  |        |                     |
| 227                                                                                  | 109              | 1480          | -                    | 6.17   |                                             |                  |        |                     |
| 266                                                                                  | 100              | 1440          | -                    | 5.27   |                                             |                  |        |                     |
| 284                                                                                  | 96               | 1420          | -                    | 4.93   |                                             |                  |        |                     |
| 337                                                                                  | 87               | 1380          | -                    | 4.16   |                                             |                  |        |                     |

| F27R17, n <sub>e</sub> =1400 1/min                                                                                                                                          |                         |                      |                        |      |                                             | 130 Nm |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------|----------------------|------------------------|------|---------------------------------------------|--------|
| n <sub>a</sub><br>rpm                                                                                                                                                       | M <sub>amax</sub><br>Nm | F <sub>Ra</sub><br>N | φ <sub>(/R)</sub><br>' | i    | DR63S<br>DR63M<br>DR63L<br>DRS71S<br>DRS71M | DRN80M |
|  3  3 |                         |                      |                        |      |                                             |        |
| 0.16                                                                                                                                                                        | 130                     | 4500                 | -                      | 8972 |                                             |        |
| 0.18                                                                                                                                                                        | 130                     | 4500                 | -                      | 7736 |                                             |        |
| 0.19                                                                                                                                                                        | 130                     | 4500                 | -                      | 7211 |                                             |        |
| 0.22                                                                                                                                                                        | 130                     | 4500                 | -                      | 6303 |                                             |        |
| 0.26                                                                                                                                                                        | 130                     | 4500                 | -                      | 5435 |                                             |        |
| 0.29                                                                                                                                                                        | 130                     | 4500                 | -                      | 4855 |                                             |        |



F27R17,  $n_e=1400$  1/min

130 Nm

| $n_a$<br>rpm                                                                                                                                                                | $M_{amax}$<br>Nm | $F_{Ra}$<br>N | $\varphi_{(R)}$<br>° | i    | DR63S<br>DR63M<br>DR63L<br>DRS71S<br>DRS71M | DRN80M |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------|---------------|----------------------|------|---------------------------------------------|--------|
| 0.33                                                                                                                                                                        | 130              | 4500          | -                    | 4243 |                                             |        |
| 0.38                                                                                                                                                                        | 130              | 4500          | -                    | 3715 |                                             |        |
| 0.43                                                                                                                                                                        | 130              | 4500          | -                    | 3247 |                                             |        |
| 0.49                                                                                                                                                                        | 130              | 4500          | -                    | 2878 |                                             |        |
| 0.56                                                                                                                                                                        | 130              | 4500          | -                    | 2515 |                                             |        |
| 0.63                                                                                                                                                                        | 130              | 4500          | -                    | 2217 |                                             |        |
|  2  3     |                  |               |                      |      |                                             |        |
| 0.74                                                                                                                                                                        | 130              | 4500          | -                    | 1898 |                                             |        |
| 0.85                                                                                                                                                                        | 130              | 4500          | -                    | 1645 |                                             |        |
| 0.92                                                                                                                                                                        | 130              | 4500          | -                    | 1525 |                                             |        |
| 1.1                                                                                                                                                                         | 130              | 4500          | -                    | 1322 |                                             |        |
| 1.2                                                                                                                                                                         | 130              | 4500          | -                    | 1146 |                                             |        |
| 1.4                                                                                                                                                                         | 130              | 4500          | -                    | 1013 |                                             |        |
| 1.6                                                                                                                                                                         | 130              | 4500          | -                    | 890  |                                             |        |
| 1.8                                                                                                                                                                         | 130              | 4500          | -                    | 778  |                                             |        |
| 2.1                                                                                                                                                                         | 130              | 4500          | -                    | 682  |                                             |        |
| 2.3                                                                                                                                                                         | 130              | 4500          | -                    | 602  |                                             |        |
| 2.7                                                                                                                                                                         | 130              | 4500          | -                    | 520  |                                             |        |
|  3  2 |                  |               |                      |      |                                             |        |
| 0.72                                                                                                                                                                        | 130              | 4500          | -                    | 1948 |                                             |        |
| 0.77                                                                                                                                                                        | 130              | 4500          | -                    | 1826 |                                             |        |
| 0.87                                                                                                                                                                        | 130              | 4500          | -                    | 1610 |                                             |        |
| 1.0                                                                                                                                                                         | 130              | 4500          | -                    | 1399 |                                             |        |
| 1.1                                                                                                                                                                         | 130              | 4500          | -                    | 1230 |                                             |        |
| 1.5                                                                                                                                                                         | 130              | 4500          | -                    | 948  |                                             |        |
| 1.7                                                                                                                                                                         | 130              | 4500          | -                    | 829  |                                             |        |
| 1.9                                                                                                                                                                         | 130              | 4500          | -                    | 731  |                                             |        |
| 2.2                                                                                                                                                                         | 130              | 4500          | -                    | 633  |                                             |        |
| 2.5                                                                                                                                                                         | 130              | 4500          | -                    | 551* |                                             |        |
| 2.9                                                                                                                                                                         | 130              | 4500          | -                    | 489  |                                             |        |
| 3.3                                                                                                                                                                         | 130              | 4500          | -                    | 427  |                                             |        |
| 3.7                                                                                                                                                                         | 130              | 4500          | -                    | 379  |                                             |        |
| 4.3                                                                                                                                                                         | 130              | 4500          | -                    | 326  |                                             |        |
| 4.9                                                                                                                                                                         | 130              | 4500          | -                    | 288  |                                             |        |
| 5.6                                                                                                                                                                         | 130              | 4500          | -                    | 251  |                                             |        |
| 6.3                                                                                                                                                                         | 130              | 4500          | -                    | 221  |                                             |        |
| 8.1                                                                                                                                                                         | 130              | 4500          | -                    | 172  |                                             |        |
| 9.2                                                                                                                                                                         | 130              | 4500          | -                    | 153  |                                             |        |
| 11                                                                                                                                                                          | 130              | 4500          | -                    | 130  |                                             |        |
|  2  2 |                  |               |                      |      |                                             |        |
| 3.1                                                                                                                                                                         | 130              | 4500          | -                    | 458  |                                             |        |
| 3.5                                                                                                                                                                         | 130              | 4500          | -                    | 397  |                                             |        |
| 4.1                                                                                                                                                                         | 130              | 4500          | -                    | 342  |                                             |        |
| 4.6                                                                                                                                                                         | 130              | 4500          | -                    | 302  |                                             |        |
| 5.3                                                                                                                                                                         | 130              | 4500          | -                    | 266  |                                             |        |
| 5.9                                                                                                                                                                         | 130              | 4500          | -                    | 236  |                                             |        |
| 6.6                                                                                                                                                                         | 130              | 4500          | -                    | 211  |                                             |        |
| 7.5                                                                                                                                                                         | 130              | 4500          | -                    | 186  |                                             |        |
| 9.9                                                                                                                                                                         | 130              | 4500          | -                    | 142  |                                             |        |

| F27R17, n <sub>e</sub> =1400 1/min |                         |                      |                        |     | 130 Nm                                      |        |
|------------------------------------|-------------------------|----------------------|------------------------|-----|---------------------------------------------|--------|
| n <sub>a</sub><br>rpm              | M <sub>amax</sub><br>Nm | F <sub>Ra</sub><br>N | φ <sub>(/R)</sub><br>° | i   | DR63S<br>DR63M<br>DR63L<br>DRS71S<br>DRS71M | DRN80M |
| 11                                 | 130                     | 4500                 | -                      | 124 |                                             |        |
| 13                                 | 130                     | 4500                 | -                      | 109 |                                             |        |
| 15                                 | 130                     | 4500                 | -                      | 96  |                                             |        |

| F37, n <sub>e</sub> =1400 1/min                                                       |                         |                      |                        |        | 200 Nm                                      |                  |        |                     |
|---------------------------------------------------------------------------------------|-------------------------|----------------------|------------------------|--------|---------------------------------------------|------------------|--------|---------------------|
| n <sub>a</sub><br>rpm                                                                 | M <sub>amax</sub><br>Nm | F <sub>Ra</sub><br>N | φ <sub>(/R)</sub><br>° | i      | DR63S<br>DR63M<br>DR63L<br>DRS71S<br>DRS71M | DRN80M<br>DRN90S | DRN90L | DRN100LS<br>DRN100L |
|  3   |                         |                      |                        |        |                                             |                  |        |                     |
| 11                                                                                    | 200                     | 4290                 | 6.8                    | 128.51 |                                             |                  |        |                     |
| 12                                                                                    | 200                     | 4290                 | 6.8                    | 117.88 |                                             |                  |        |                     |
| 14                                                                                    | 200                     | 4290                 | 6.8                    | 100.36 |                                             |                  |        |                     |
| 16                                                                                    | 200                     | 4290                 | 6.8                    | 86.53  |                                             |                  |        |                     |
| 17                                                                                    | 200                     | 4290                 | 6.8                    | 80.65  |                                             |                  |        |                     |
| 20                                                                                    | 200                     | 4290                 | 6.9                    | 70.50  |                                             |                  |        |                     |
| 21                                                                                    | 200                     | 4290                 | 6.9                    | 66.09  |                                             |                  |        |                     |
| 24                                                                                    | 200                     | 4290                 | 6.9                    | 58.32  |                                             |                  |        |                     |
| 26                                                                                    | 200                     | 4290                 | 7.5                    | 54.54  |                                             |                  |        |                     |
| 27                                                                                    | 200                     | 4290                 | 6.9                    | 51.70  |                                             |                  |        |                     |
| 30                                                                                    | 200                     | 4290                 | 7.6                    | 47.02  |                                             |                  |        |                     |
| 32                                                                                    | 200                     | 4290                 | 7.6                    | 43.83  |                                             |                  |        |                     |
| 37                                                                                    | 200                     | 4290                 | 7.7                    | 38.31  |                                             |                  |        |                     |
| 39                                                                                    | 200                     | 4290                 | 7.7                    | 35.91  |                                             |                  |        |                     |
| 44                                                                                    | 200                     | 4290                 | 7.7                    | 31.69  |                                             |                  |        |                     |
| 50                                                                                    | 200                     | 4060                 | 7.8                    | 28.09  |                                             |                  |        |                     |
| 59                                                                                    | 200                     | 3760                 | 7.8                    | 23.88  |                                             |                  |        |                     |
|  2 |                         |                      |                        |        |                                             |                  |        |                     |
| 59                                                                                    | 200                     | 3740                 | 6.1                    | 23.63  |                                             |                  |        |                     |
| 68                                                                                    | 200                     | 3500                 | 6.2                    | 20.57  |                                             |                  |        |                     |
| 73                                                                                    | 200                     | 3390                 | 6.2                    | 19.27  |                                             |                  |        |                     |
| 82                                                                                    | 200                     | 3180                 | 6.4                    | 17.03  |                                             |                  |        |                     |
| 89                                                                                    | 200                     | 3070                 | 6.4                    | 15.81  |                                             |                  |        |                     |
| 98                                                                                    | 200                     | 2910                 | 6.5                    | 14.33  |                                             |                  |        |                     |
| 109                                                                                   | 200                     | 2750                 | 6.6                    | 12.87  |                                             |                  |        |                     |
| 126                                                                                   | 190                     | 2620                 | 6.7                    | 11.08  |                                             |                  |        |                     |
| 134                                                                                   | 185                     | 2580                 | 6.8                    | 10.42  |                                             |                  |        |                     |
| 156                                                                                   | 175                     | 2460                 | 6.9                    | 8.97   |                                             |                  |        |                     |
| 175                                                                                   | 170                     | 2360                 | 7.4                    | 8.01   |                                             |                  |        |                     |
| 188                                                                                   | 145                     | 2350                 | 9.9                    | 7.44   |                                             |                  |        |                     |
| 208                                                                                   | 140                     | 2270                 | 10                     | 6.74   |                                             |                  |        |                     |
| 231                                                                                   | 135                     | 2190                 | 10.2                   | 6.05   |                                             |                  |        |                     |
| 269                                                                                   | 125                     | 2120                 | 10.5                   | 5.21   |                                             |                  |        |                     |
| 286                                                                                   | 120                     | 2100                 | 10.6                   | 4.90   |                                             |                  |        |                     |
| 332                                                                                   | 110                     | 2030                 | 10.9                   | 4.22   |                                             |                  |        |                     |
| 371                                                                                   | 105                     | 1970                 | 11.9                   | 3.77   |                                             |                  |        |                     |

21933170/DE – 11/2015

F37R17,  $n_e=1400$  1/min

200 Nm

| $n_a$<br>rpm                                                                                                                                                                | $M_{amax}$<br>Nm | $F_{Ra}$<br>N | $\varphi_{(R)}$<br>° | i    | DR63S<br>DR63M<br>DR63L<br>DRS71S<br>DRS71M | DRN80M |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------|---------------|----------------------|------|---------------------------------------------|--------|
|  3  3     |                  |               |                      |      |                                             |        |
| 0.17                                                                                                                                                                        | 200              | 4290          | -                    | 8193 |                                             |        |
| 0.20                                                                                                                                                                        | 200              | 4290          | -                    | 7064 |                                             |        |
| 0.21                                                                                                                                                                        | 200              | 4290          | -                    | 6585 |                                             |        |
| 0.24                                                                                                                                                                        | 200              | 4290          | -                    | 5756 |                                             |        |
| 0.28                                                                                                                                                                        | 200              | 4290          | -                    | 4963 |                                             |        |
| 0.32                                                                                                                                                                        | 200              | 4290          | -                    | 4434 |                                             |        |
| 0.36                                                                                                                                                                        | 200              | 4290          | -                    | 3875 |                                             |        |
| 0.41                                                                                                                                                                        | 200              | 4290          | -                    | 3392 |                                             |        |
| 0.47                                                                                                                                                                        | 200              | 4290          | -                    | 2965 |                                             |        |
| 0.54                                                                                                                                                                        | 200              | 4290          | -                    | 2587 |                                             |        |
| 0.61                                                                                                                                                                        | 200              | 4290          | -                    | 2284 |                                             |        |
| 0.70                                                                                                                                                                        | 200              | 4290          | -                    | 1997 |                                             |        |
| 0.80                                                                                                                                                                        | 200              | 4290          | -                    | 1742 |                                             |        |
| 0.91                                                                                                                                                                        | 200              | 4290          | -                    | 1545 |                                             |        |
|  2  3     |                  |               |                      |      |                                             |        |
| 0.73                                                                                                                                                                        | 200              | 4290          | -                    | 1929 |                                             |        |
| 0.83                                                                                                                                                                        | 200              | 4290          | -                    | 1679 |                                             |        |
| 0.90                                                                                                                                                                        | 200              | 4290          | -                    | 1550 |                                             |        |
| 1.0                                                                                                                                                                         | 200              | 4290          | -                    | 1356 |                                             |        |
| 1.2                                                                                                                                                                         | 200              | 4290          | -                    | 1180 |                                             |        |
| 1.3                                                                                                                                                                         | 200              | 4290          | -                    | 1044 |                                             |        |
| 1.5                                                                                                                                                                         | 200              | 4290          | -                    | 914  |                                             |        |
| 1.7                                                                                                                                                                         | 200              | 4290          | -                    | 808  |                                             |        |
| 2.0                                                                                                                                                                         | 200              | 4290          | -                    | 698  |                                             |        |
| 2.3                                                                                                                                                                         | 200              | 4290          | -                    | 616  |                                             |        |
| 2.6                                                                                                                                                                         | 200              | 4290          | -                    | 544  |                                             |        |
| 3.0                                                                                                                                                                         | 200              | 4290          | -                    | 466  |                                             |        |
| 3.4                                                                                                                                                                         | 200              | 4290          | -                    | 411  |                                             |        |
| 3.8                                                                                                                                                                         | 200              | 4290          | -                    | 364  |                                             |        |
|  3  2 |                  |               |                      |      |                                             |        |
| 1.0                                                                                                                                                                         | 200              | 4290          | -                    | 1370 |                                             |        |
| 1.2                                                                                                                                                                         | 200              | 4290          | -                    | 1198 |                                             |        |
| 1.3                                                                                                                                                                         | 200              | 4290          | -                    | 1047 |                                             |        |
| 1.5                                                                                                                                                                         | 200              | 4290          | -                    | 915  |                                             |        |
| 1.7                                                                                                                                                                         | 200              | 4290          | -                    | 807  |                                             |        |
| 2.0                                                                                                                                                                         | 200              | 4290          | -                    | 707  |                                             |        |
| 2.3                                                                                                                                                                         | 200              | 4290          | -                    | 617  |                                             |        |
| 2.6                                                                                                                                                                         | 200              | 4290          | -                    | 538  |                                             |        |
| 2.9                                                                                                                                                                         | 200              | 4290          | -                    | 477  |                                             |        |
| 3.4                                                                                                                                                                         | 200              | 4290          | -                    | 412  |                                             |        |
| 3.8                                                                                                                                                                         | 200              | 4290          | -                    | 365  |                                             |        |
| 4.3                                                                                                                                                                         | 200              | 4290          | -                    | 322  |                                             |        |
| 5.0                                                                                                                                                                         | 200              | 4290          | -                    | 278  |                                             |        |
| 5.8                                                                                                                                                                         | 200              | 4290          | -                    | 242  |                                             |        |
| 6.3                                                                                                                                                                         | 200              | 4290          | -                    | 221  |                                             |        |
| 7.2                                                                                                                                                                         | 200              | 4290          | -                    | 195  |                                             |        |
| 8.3                                                                                                                                                                         | 200              | 4290          | -                    | 168  |                                             |        |
| 9.5                                                                                                                                                                         | 200              | 4290          | -                    | 147  |                                             |        |

| F37R17, n <sub>e</sub> =1400 1/min                                                                                                                                      |                         |                      |                        |     | 200 Nm                                      |        |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------|----------------------|------------------------|-----|---------------------------------------------|--------|
| n <sub>a</sub><br>rpm                                                                                                                                                   | M <sub>amax</sub><br>Nm | F <sub>Ra</sub><br>N | Φ <sub>(/R)</sub><br>° | i   | DR63S<br>DR63M<br>DR63L<br>DRS71S<br>DRS71M | DRN80M |
| 11                                                                                                                                                                      | 200                     | 4290                 | -                      | 127 |                                             |        |
| 12                                                                                                                                                                      | 200                     | 4290                 | -                      | 121 |                                             |        |
| 13                                                                                                                                                                      | 200                     | 4290                 | -                      | 108 |                                             |        |
| 15                                                                                                                                                                      | 200                     | 4290                 | -                      | 91  |                                             |        |
|  2  2 |                         |                      |                        |     |                                             |        |
| 4.3                                                                                                                                                                     | 200                     | 4290                 | -                      | 326 |                                             |        |
| 4.9                                                                                                                                                                     | 200                     | 4290                 | -                      | 285 |                                             |        |
| 5.6                                                                                                                                                                     | 200                     | 4290                 | -                      | 250 |                                             |        |
| 6.4                                                                                                                                                                     | 200                     | 4290                 | -                      | 219 |                                             |        |
| 7.5                                                                                                                                                                     | 200                     | 4290                 | -                      | 186 |                                             |        |
| 8.4                                                                                                                                                                     | 200                     | 4290                 | -                      | 167 |                                             |        |
| 9.7                                                                                                                                                                     | 200                     | 4290                 | -                      | 145 |                                             |        |
| 11                                                                                                                                                                      | 200                     | 4290                 | -                      | 129 |                                             |        |
| 12                                                                                                                                                                      | 200                     | 4290                 | -                      | 118 |                                             |        |
| 14                                                                                                                                                                      | 200                     | 4290                 | -                      | 98  |                                             |        |
| 16                                                                                                                                                                      | 200                     | 4290                 | -                      | 87  |                                             |        |

| F47, n <sub>e</sub> =1400 1/min                                                       |                         |                      |                        |        | 400 Nm                                      |                  |        |                     |
|---------------------------------------------------------------------------------------|-------------------------|----------------------|------------------------|--------|---------------------------------------------|------------------|--------|---------------------|
| n <sub>a</sub><br>rpm                                                                 | M <sub>amax</sub><br>Nm | F <sub>Ra</sub><br>N | Φ <sub>(/R)</sub><br>° | i      | DR63S<br>DR63M<br>DR63L<br>DRS71S<br>DRS71M | DRN80M<br>DRN90S | DRN90L | DRN100LS<br>DRN100L |
|  3 |                         |                      |                        |        |                                             |                  |        |                     |
| 7.3                                                                                   | 400                     | 5920                 | 6.1                    | 190.76 |                                             |                  |        |                     |
| 8.0                                                                                   | 400                     | 5920                 | 6.2                    | 175.38 |                                             |                  |        |                     |
| 9.3                                                                                   | 400                     | 5920                 | 6.2                    | 150.06 |                                             |                  |        |                     |
| 11                                                                                    | 400                     | 5920                 | 6.2                    | 130.07 |                                             |                  |        |                     |
| 12                                                                                    | 400                     | 5920                 | 6.2                    | 121.57 |                                             |                  |        |                     |
| 13                                                                                    | 400                     | 5920                 | 6.2                    | 105.09 |                                             |                  |        |                     |
| 16                                                                                    | 400                     | 5920                 | 6.2                    | 89.29  |                                             |                  |        |                     |
| 18                                                                                    | 400                     | 5920                 | 6.2                    | 79.72  |                                             |                  |        |                     |
| 21                                                                                    | 400                     | 5920                 | 6.3                    | 68.09  |                                             |                  |        |                     |
| 21                                                                                    | 400                     | 5920                 | 6.7                    | 65.36  |                                             |                  |        |                     |
| 25                                                                                    | 400                     | 5920                 | 6.8                    | 56.49  |                                             |                  |        |                     |
| 29                                                                                    | 400                     | 5920                 | 6.8                    | 48.00* |                                             |                  |        |                     |
| 33                                                                                    | 400                     | 5920                 | 6.8                    | 42.86  |                                             |                  |        |                     |
| 38                                                                                    | 400                     | 5920                 | 6.9                    | 36.61  |                                             |                  |        |                     |
| 41                                                                                    | 400                     | 5920                 | 6.9                    | 34.29  |                                             |                  |        |                     |
| 48                                                                                    | 400                     | 5790                 | 7                      | 28.88  |                                             |                  |        |                     |
|  2 |                         |                      |                        |        |                                             |                  |        |                     |
| 45                                                                                    | 400                     | 5920                 | 5.7                    | 30.86  |                                             |                  |        |                     |
| 48                                                                                    | 400                     | 5830                 | 5.7                    | 29.32  |                                             |                  |        |                     |
| 54                                                                                    | 400                     | 5460                 | 5.8                    | 25.72  |                                             |                  |        |                     |
| 64                                                                                    | 400                     | 5030                 | 5.9                    | 21.82  |                                             |                  |        |                     |
| 71                                                                                    | 400                     | 4770                 | 5.9                    | 19.70  |                                             |                  |        |                     |
| 81                                                                                    | 400                     | 4450                 | 6                      | 17.33  |                                             |                  |        |                     |
| 86                                                                                    | 400                     | 4320                 | 6                      | 16.36  |                                             |                  |        |                     |
| 101                                                                                   | 400                     | 3950                 | 6.1                    | 13.93  |                                             |                  |        |                     |

21933170/DE – 11/2015

| F47, $n_e=1400$ 1/min |                  |               |                   |       |                                             | 400 Nm           |        |                     |
|-----------------------|------------------|---------------|-------------------|-------|---------------------------------------------|------------------|--------|---------------------|
| $n_a$<br>rpm          | $M_{amax}$<br>Nm | $F_{Ra}$<br>N | $\Phi_{(R)}$<br>° | $i$   | DR63S<br>DR63M<br>DR63L<br>DRS71S<br>DRS71M | DRN80M<br>DRN90S | DRN90L | DRN100LS<br>DRN100L |
| 111                   | 400              | 3740          | 6.4               | 12.66 |                                             |                  |        |                     |
| 128                   | 400              | 3440          | 6.5               | 10.97 |                                             |                  |        |                     |
| 156                   | 330              | 3250          | 8                 | 8.96  |                                             |                  |        |                     |
| 178                   | 380              | 2630          | 8.1               | 7.88  |                                             |                  |        |                     |
| 188                   | 380              | 2530          | 8.2               | 7.44* |                                             |                  |        |                     |
| 221                   | 350              | 2470          | 8.4               | 6.34  |                                             |                  |        |                     |
| 243                   | 340              | 2390          | 9                 | 5.76  |                                             |                  |        |                     |
| 281                   | 320              | 2310          | 9.2               | 4.99  |                                             |                  |        |                     |

| F47R17, n <sub>e</sub> =1400 1/min                                                                                                                                          |                         |                      |                        |       | 400 Nm                                      |        |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------|----------------------|------------------------|-------|---------------------------------------------|--------|
| n <sub>a</sub><br>rpm                                                                                                                                                       | M <sub>amax</sub><br>Nm | F <sub>Ra</sub><br>N | Φ <sub>(/R)</sub><br>' | i     | DR63S<br>DR63M<br>DR63L<br>DRS71S<br>DRS71M | DRN80M |
|  3  3     |                         |                      |                        |       |                                             |        |
| 0.11                                                                                                                                                                        | 400                     | 5920                 | -                      | 12251 |                                             |        |
| 0.13                                                                                                                                                                        | 400                     | 5920                 | -                      | 10619 |                                             |        |
| 0.14                                                                                                                                                                        | 400                     | 5920                 | -                      | 9846  |                                             |        |
| 0.16                                                                                                                                                                        | 400                     | 5920                 | -                      | 8534  |                                             |        |
| 0.19                                                                                                                                                                        | 400                     | 5920                 | -                      | 7460  |                                             |        |
| 0.21                                                                                                                                                                        | 400                     | 5920                 | -                      | 6536  |                                             |        |
| 0.24                                                                                                                                                                        | 400                     | 5920                 | -                      | 5746  |                                             |        |
| 0.28                                                                                                                                                                        | 400                     | 5920                 | -                      | 5022  |                                             |        |
| 0.32                                                                                                                                                                        | 400                     | 5920                 | -                      | 4401  |                                             |        |
| 0.36                                                                                                                                                                        | 400                     | 5920                 | -                      | 3883  |                                             |        |
| 0.41                                                                                                                                                                        | 400                     | 5920                 | -                      | 3443  |                                             |        |
| 0.47                                                                                                                                                                        | 400                     | 5920                 | -                      | 2976  |                                             |        |
| 0.53                                                                                                                                                                        | 400                     | 5920                 | -                      | 2629  |                                             |        |
| 0.61                                                                                                                                                                        | 400                     | 5920                 | -                      | 2304  |                                             |        |
| 0.69                                                                                                                                                                        | 400                     | 5920                 | -                      | 2033  |                                             |        |
|  2  3 |                         |                      |                        |       |                                             |        |
| 0.56                                                                                                                                                                        | 400                     | 5920                 | -                      | 2519  |                                             |        |
| 0.58                                                                                                                                                                        | 400                     | 5920                 | -                      | 2394  |                                             |        |
| 0.64                                                                                                                                                                        | 400                     | 5920                 | -                      | 2172  |                                             |        |
| 0.69                                                                                                                                                                        | 400                     | 5920                 | -                      | 2025  |                                             |        |
| 0.79                                                                                                                                                                        | 400                     | 5920                 | -                      | 1770  |                                             |        |
| 0.89                                                                                                                                                                        | 400                     | 5920                 | -                      | 1576  |                                             |        |
| 1.0                                                                                                                                                                         | 400                     | 5920                 | -                      | 1363  |                                             |        |
| 1.2                                                                                                                                                                         | 400                     | 5920                 | -                      | 1192  |                                             |        |
| 1.3                                                                                                                                                                         | 400                     | 5920                 | -                      | 1061  |                                             |        |
| 1.5                                                                                                                                                                         | 400                     | 5920                 | -                      | 931   |                                             |        |
| 1.7                                                                                                                                                                         | 400                     | 5920                 | -                      | 822   |                                             |        |
| 2.0                                                                                                                                                                         | 400                     | 5920                 | -                      | 706   |                                             |        |
| 2.3                                                                                                                                                                         | 400                     | 5920                 | -                      | 619   |                                             |        |
|  3  2 |                         |                      |                        |       |                                             |        |
| 0.78                                                                                                                                                                        | 400                     | 5920                 | -                      | 1785  |                                             |        |
| 0.89                                                                                                                                                                        | 400                     | 5920                 | -                      | 1578  |                                             |        |
| 1.0                                                                                                                                                                         | 400                     | 5920                 | -                      | 1364  |                                             |        |

| F47R17, n <sub>e</sub> =1400 1/min                                                                                                                                        |                         |                      |                        |      | 400 Nm                                      |        |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------|----------------------|------------------------|------|---------------------------------------------|--------|
| n <sub>a</sub><br>rpm                                                                                                                                                     | M <sub>amax</sub><br>Nm | F <sub>Ra</sub><br>N | Φ <sub>(/R)</sub><br>° | i    | DR63S<br>DR63M<br>DR63L<br>DRS71S<br>DRS71M | DRN80M |
| 1.2                                                                                                                                                                       | 400                     | 5920                 | -                      | 1203 |                                             |        |
| 1.3                                                                                                                                                                       | 400                     | 5920                 | -                      | 1049 |                                             |        |
| 1.5                                                                                                                                                                       | 400                     | 5920                 | -                      | 918  |                                             |        |
| 1.7                                                                                                                                                                       | 400                     | 5920                 | -                      | 809  |                                             |        |
| 2.0                                                                                                                                                                       | 400                     | 5920                 | -                      | 700  |                                             |        |
| 2.3                                                                                                                                                                       | 400                     | 5920                 | -                      | 622  |                                             |        |
| 2.6                                                                                                                                                                       | 400                     | 5920                 | -                      | 543  |                                             |        |
| 2.9                                                                                                                                                                       | 400                     | 5920                 | -                      | 475  |                                             |        |
| 3.3                                                                                                                                                                       | 400                     | 5920                 | -                      | 419  |                                             |        |
| 3.8                                                                                                                                                                       | 400                     | 5920                 | -                      | 370  |                                             |        |
| 4.3                                                                                                                                                                       | 400                     | 5920                 | -                      | 324  |                                             |        |
| 4.9                                                                                                                                                                       | 400                     | 5920                 | -                      | 288  |                                             |        |
| 5.6                                                                                                                                                                       | 400                     | 5920                 | -                      | 249  |                                             |        |
| 6.4                                                                                                                                                                       | 400                     | 5920                 | -                      | 218  |                                             |        |
| 7.3                                                                                                                                                                       | 400                     | 5920                 | -                      | 193  |                                             |        |
| 8.0                                                                                                                                                                       | 400                     | 5920                 | -                      | 175  |                                             |        |
| 9.5                                                                                                                                                                       | 400                     | 5920                 | -                      | 147  |                                             |        |
| 11                                                                                                                                                                        | 400                     | 5920                 | -                      | 130  |                                             |        |
|  2  2 |                         |                      |                        |      |                                             |        |
| 2.7                                                                                                                                                                       | 400                     | 5920                 | -                      | 524  |                                             |        |
| 2.9                                                                                                                                                                       | 400                     | 5920                 | -                      | 489  |                                             |        |
| 3.3                                                                                                                                                                       | 400                     | 5920                 | -                      | 427  |                                             |        |
| 3.7                                                                                                                                                                       | 400                     | 5920                 | -                      | 381  |                                             |        |
| 4.2                                                                                                                                                                       | 400                     | 5920                 | -                      | 334  |                                             |        |
| 4.7                                                                                                                                                                       | 400                     | 5920                 | -                      | 295  |                                             |        |
| 5.5                                                                                                                                                                       | 400                     | 5920                 | -                      | 253  |                                             |        |
| 6.5                                                                                                                                                                       | 400                     | 5920                 | -                      | 217  |                                             |        |
| 7.4                                                                                                                                                                       | 400                     | 5920                 | -                      | 190  |                                             |        |
| 7.9                                                                                                                                                                       | 400                     | 5920                 | -                      | 178  |                                             |        |
| 9.4                                                                                                                                                                       | 400                     | 5920                 | -                      | 149  |                                             |        |
| 11                                                                                                                                                                        | 400                     | 5920                 | -                      | 131  |                                             |        |

| F57, n <sub>e</sub> =1400 1/min                                                       |                         |                      |                        |        | 600 Nm                                      |                  |        |                     |         |                    |
|---------------------------------------------------------------------------------------|-------------------------|----------------------|------------------------|--------|---------------------------------------------|------------------|--------|---------------------|---------|--------------------|
| n <sub>a</sub><br>rpm                                                                 | M <sub>amax</sub><br>Nm | F <sub>Ra</sub><br>N | Φ <sub>(/R)</sub><br>° | i      | DR63S<br>DR63M<br>DR63L<br>DRS71S<br>DRS71M | DRN80M<br>DRN90S | DRN90L | DRN100LS<br>DRN100L | DRN112M | DRN132S<br>DRN132M |
|  3 |                         |                      |                        |        |                                             |                  |        |                     |         |                    |
| 7.0                                                                                   | 600                     | 9200                 | 6                      | 199.70 |                                             |                  |        |                     |         |                    |
| 7.6                                                                                   | 600                     | 9200                 | 6.1                    | 183.60 |                                             |                  |        |                     |         |                    |
| 8.9                                                                                   | 600                     | 9200                 | 6.1                    | 157.09 |                                             |                  |        |                     |         |                    |
| 10                                                                                    | 600                     | 9200                 | 6.1                    | 136.16 |                                             |                  |        |                     |         |                    |
| 11                                                                                    | 600                     | 9200                 | 6.1                    | 127.27 |                                             |                  |        |                     |         |                    |
| 13                                                                                    | 600                     | 9200                 | 6.1                    | 110.01 |                                             |                  |        |                     |         |                    |
| 15                                                                                    | 600                     | 9200                 | 6.1                    | 93.47  |                                             |                  |        |                     |         |                    |
| 17                                                                                    | 600                     | 9200                 | 6.1                    | 83.46  |                                             |                  |        |                     |         |                    |
| 19                                                                                    | 600                     | 9200                 | 6.5                    | 72.98  |                                             |                  |        |                     |         |                    |
| 21                                                                                    | 600                     | 9200                 | 6.5                    | 68.22  |                                             |                  |        |                     |         |                    |
| 24                                                                                    | 600                     | 9200                 | 6.5                    | 58.97  |                                             |                  |        |                     |         |                    |

21933170/DE – 11/2015

| F57, $n_e=1400$ 1/min                                                               |                  |               |                   |       |                                             |                  |        |                     |         | 600 Nm             |
|-------------------------------------------------------------------------------------|------------------|---------------|-------------------|-------|---------------------------------------------|------------------|--------|---------------------|---------|--------------------|
| $n_a$<br>rpm                                                                        | $M_{amax}$<br>Nm | $F_{Ra}$<br>N | $\Phi_{(R)}$<br>° | i     | DR63S<br>DR63M<br>DR63L<br>DRS71S<br>DRS71M | DRN80M<br>DRN90S | DRN90L | DRN100LS<br>DRN100L | DRN112M | DRN132S<br>DRN132M |
| 28                                                                                  | 600              | 9200          | 6.6               | 50.10 |                                             |                  |        |                     |         |                    |
| 31                                                                                  | 600              | 9160          | 6.6               | 44.73 |                                             |                  |        |                     |         |                    |
| 37                                                                                  | 600              | 8510          | 6.6               | 38.21 |                                             |                  |        |                     |         |                    |
| 39                                                                                  | 600              | 8250          | 6.6               | 35.79 |                                             |                  |        |                     |         |                    |
| 46                                                                                  | 590              | 7650          | 6.7               | 30.15 |                                             |                  |        |                     |         |                    |
|  2 |                  |               |                   |       |                                             |                  |        |                     |         |                    |
| 35                                                                                  | 290              | 10500         | 5.7               | 40.13 |                                             |                  |        |                     |         |                    |
| 41                                                                                  | 500              | 8670          | 5.7               | 34.24 |                                             |                  |        |                     |         |                    |
| 47                                                                                  | 545              | 7890          | 5.6               | 29.94 |                                             |                  |        |                     |         |                    |
| 49                                                                                  | 535              | 7760          | 5.7               | 28.45 |                                             |                  |        |                     |         |                    |
| 56                                                                                  | 575              | 7060          | 5.8               | 24.96 |                                             |                  |        |                     |         |                    |
| 66                                                                                  | 600              | 6350          | 5.8               | 21.17 |                                             |                  |        |                     |         |                    |
| 73                                                                                  | 600              | 6020          | 5.9               | 19.11 |                                             |                  |        |                     |         |                    |
| 83                                                                                  | 600              | 5620          | 5.9               | 16.81 |                                             |                  |        |                     |         |                    |
| 88                                                                                  | 600              | 5450          | 6                 | 15.88 |                                             |                  |        |                     |         |                    |
| 104                                                                                 | 600              | 4980          | 6.1               | 13.52 |                                             |                  |        |                     |         |                    |
| 114                                                                                 | 600              | 4710          | 6.3               | 12.29 |                                             |                  |        |                     |         |                    |
| 132                                                                                 | 600              | 4320          | 6.4               | 10.64 |                                             |                  |        |                     |         |                    |
| 150                                                                                 | 420              | 4760          | 7.6               | 9.31  |                                             |                  |        |                     |         |                    |
| 171                                                                                 | 420              | 4450          | 7.8               | 8.19  |                                             |                  |        |                     |         |                    |
| 181                                                                                 | 420              | 4310          | 7.8               | 7.73  |                                             |                  |        |                     |         |                    |
| 213                                                                                 | 420              | 3940          | 8                 | 6.58  |                                             |                  |        |                     |         |                    |
| 234                                                                                 | 420              | 3730          | 8.6               | 5.98  |                                             |                  |        |                     |         |                    |
| 270                                                                                 | 415              | 3460          | 8.8               | 5.18  |                                             |                  |        |                     |         |                    |

| F57R37, $n_e=1400$ 1/min                                                                                                                                                    |                  |               |                   |       |                                             |                  |        |                     |  | 600 Nm |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------|---------------|-------------------|-------|---------------------------------------------|------------------|--------|---------------------|--|--------|
| $n_a$<br>rpm                                                                                                                                                                | $M_{amax}$<br>Nm | $F_{Ra}$<br>N | $\Phi_{(R)}$<br>° | i     | DR63S<br>DR63M<br>DR63L<br>DRS71S<br>DRS71M | DRN80M<br>DRN90S | DRN90L | DRN100LS<br>DRN100L |  |        |
|  3  3 |                  |               |                   |       |                                             |                  |        |                     |  |        |
| 0.09                                                                                                                                                                        | 600              | 9200          | -                 | 14832 |                                             |                  |        |                     |  |        |
| 0.10                                                                                                                                                                        | 600              | 9200          | -                 | 13604 |                                             |                  |        |                     |  |        |
| 0.11                                                                                                                                                                        | 600              | 9200          | -                 | 12602 |                                             |                  |        |                     |  |        |
| 0.12                                                                                                                                                                        | 600              | 9200          | -                 | 11252 |                                             |                  |        |                     |  |        |
| 0.14                                                                                                                                                                        | 600              | 9200          | -                 | 9986  |                                             |                  |        |                     |  |        |
| 0.16                                                                                                                                                                        | 600              | 9200          | -                 | 8787  |                                             |                  |        |                     |  |        |
| 0.18                                                                                                                                                                        | 600              | 9200          | -                 | 7908  |                                             |                  |        |                     |  |        |
| 0.20                                                                                                                                                                        | 600              | 9200          | -                 | 6913  |                                             |                  |        |                     |  |        |
| 0.23                                                                                                                                                                        | 600              | 9200          | -                 | 6030  |                                             |                  |        |                     |  |        |
| 0.26                                                                                                                                                                        | 600              | 9200          | -                 | 5289  |                                             |                  |        |                     |  |        |
| 0.30                                                                                                                                                                        | 600              | 9200          | -                 | 4654  |                                             |                  |        |                     |  |        |
| 0.34                                                                                                                                                                        | 600              | 9200          | -                 | 4060  |                                             |                  |        |                     |  |        |
| 0.39                                                                                                                                                                        | 600              | 9200          | -                 | 3564  |                                             |                  |        |                     |  |        |
| 0.44                                                                                                                                                                        | 600              | 9200          | -                 | 3161  |                                             |                  |        |                     |  |        |
| 0.51                                                                                                                                                                        | 600              | 9200          | -                 | 2737  |                                             |                  |        |                     |  |        |
| 0.58                                                                                                                                                                        | 600              | 9200          | -                 | 2409  |                                             |                  |        |                     |  |        |
| 0.66                                                                                                                                                                        | 600              | 9200          | -                 | 2131  |                                             |                  |        |                     |  |        |
| 0.76                                                                                                                                                                        | 600              | 9200          | -                 | 1840  |                                             |                  |        |                     |  |        |



| F57R37, n <sub>e</sub> =1400 1/min                                                                                                                                          |                         |                      |                        |      | 600 Nm                                      |                  |        |                     |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------|----------------------|------------------------|------|---------------------------------------------|------------------|--------|---------------------|
| n <sub>a</sub><br>rpm                                                                                                                                                       | M <sub>amax</sub><br>Nm | F <sub>Ra</sub><br>N | φ <sub>(/R)</sub><br>° | i    | DR63S<br>DR63M<br>DR63L<br>DRS71S<br>DRS71M | DRN80M<br>DRN90S | DRN90L | DRN100LS<br>DRN100L |
| 0.86                                                                                                                                                                        | 600                     | 9200                 | -                      | 1623 |                                             |                  |        |                     |
| 0.97                                                                                                                                                                        | 600                     | 9200                 | -                      | 1439 |                                             |                  |        |                     |
| 1.1                                                                                                                                                                         | 600                     | 9200                 | -                      | 1238 |                                             |                  |        |                     |
|  2  3     |                         |                      |                        |      |                                             |                  |        |                     |
| 0.49                                                                                                                                                                        | 600                     | 9200                 | -                      | 2854 |                                             |                  |        |                     |
| 0.54                                                                                                                                                                        | 600                     | 9200                 | -                      | 2576 |                                             |                  |        |                     |
| 0.62                                                                                                                                                                        | 600                     | 9200                 | -                      | 2266 |                                             |                  |        |                     |
| 0.70                                                                                                                                                                        | 600                     | 9200                 | -                      | 2012 |                                             |                  |        |                     |
| 0.78                                                                                                                                                                        | 600                     | 9200                 | -                      | 1791 |                                             |                  |        |                     |
| 0.87                                                                                                                                                                        | 600                     | 9200                 | -                      | 1617 |                                             |                  |        |                     |
| 0.98                                                                                                                                                                        | 600                     | 9200                 | -                      | 1422 |                                             |                  |        |                     |
| 1.1                                                                                                                                                                         | 600                     | 9200                 | -                      | 1243 |                                             |                  |        |                     |
| 1.3                                                                                                                                                                         | 600                     | 9200                 | -                      | 1066 |                                             |                  |        |                     |
| 1.5                                                                                                                                                                         | 600                     | 9200                 | -                      | 949  |                                             |                  |        |                     |
| 1.6                                                                                                                                                                         | 600                     | 9200                 | -                      | 856  |                                             |                  |        |                     |
| 1.9                                                                                                                                                                         | 600                     | 9200                 | -                      | 749  |                                             |                  |        |                     |
| 2.1                                                                                                                                                                         | 600                     | 9200                 | -                      | 658  |                                             |                  |        |                     |
| 2.6                                                                                                                                                                         | 600                     | 9200                 | -                      | 549  |                                             |                  |        |                     |
| 2.9                                                                                                                                                                         | 600                     | 9200                 | -                      | 483  |                                             |                  |        |                     |
|  3  2 |                         |                      |                        |      |                                             |                  |        |                     |
| 1.3                                                                                                                                                                         | 600                     | 9200                 | -                      | 1106 |                                             |                  |        |                     |
| 1.4                                                                                                                                                                         | 600                     | 9200                 | -                      | 967  |                                             |                  |        |                     |
| 1.6                                                                                                                                                                         | 600                     | 9200                 | -                      | 851  |                                             |                  |        |                     |
| 1.9                                                                                                                                                                         | 600                     | 9200                 | -                      | 738  |                                             |                  |        |                     |
| 2.2                                                                                                                                                                         | 600                     | 9200                 | -                      | 646  |                                             |                  |        |                     |
| 2.5                                                                                                                                                                         | 600                     | 9200                 | -                      | 558  |                                             |                  |        |                     |
| 2.8                                                                                                                                                                         | 600                     | 9200                 | -                      | 506  |                                             |                  |        |                     |
| 3.1                                                                                                                                                                         | 600                     | 9200                 | -                      | 452  |                                             |                  |        |                     |
| 3.6                                                                                                                                                                         | 600                     | 9200                 | -                      | 386  |                                             |                  |        |                     |
| 4.1                                                                                                                                                                         | 600                     | 9200                 | -                      | 338  |                                             |                  |        |                     |
| 5.5                                                                                                                                                                         | 600                     | 9200                 | -                      | 255  |                                             |                  |        |                     |
| 7.0                                                                                                                                                                         | 600                     | 9200                 | -                      | 201  |                                             |                  |        |                     |
| 7.7                                                                                                                                                                         | 600                     | 9200                 | -                      | 181  |                                             |                  |        |                     |
| 9.0                                                                                                                                                                         | 600                     | 9200                 | -                      | 155  |                                             |                  |        |                     |
|  2  2 |                         |                      |                        |      |                                             |                  |        |                     |
| 3.3                                                                                                                                                                         | 600                     | 9200                 | -                      | 426  |                                             |                  |        |                     |
| 3.7                                                                                                                                                                         | 600                     | 9200                 | -                      | 382  |                                             |                  |        |                     |
| 4.2                                                                                                                                                                         | 600                     | 9200                 | -                      | 330  |                                             |                  |        |                     |
| 4.7                                                                                                                                                                         | 600                     | 9200                 | -                      | 298  |                                             |                  |        |                     |
| 5.3                                                                                                                                                                         | 600                     | 9200                 | -                      | 262  |                                             |                  |        |                     |
| 6.2                                                                                                                                                                         | 600                     | 9200                 | -                      | 226  |                                             |                  |        |                     |
| 7.0                                                                                                                                                                         | 600                     | 9200                 | -                      | 200  |                                             |                  |        |                     |
| 8.2                                                                                                                                                                         | 600                     | 9200                 | -                      | 170  |                                             |                  |        |                     |
| 9.2                                                                                                                                                                         | 600                     | 9200                 | -                      | 152  |                                             |                  |        |                     |
| 10                                                                                                                                                                          | 600                     | 9200                 | -                      | 134  |                                             |                  |        |                     |

21933170/DE – 11/2015

| F67, $n_e=1400$ 1/min                                                                 |                  |               |                   |        |                                             |                  |        |                     |         | 820 Nm             |
|---------------------------------------------------------------------------------------|------------------|---------------|-------------------|--------|---------------------------------------------|------------------|--------|---------------------|---------|--------------------|
| $n_a$<br>rpm                                                                          | $M_{amax}$<br>Nm | $F_{Ra}$<br>N | $\Phi_{(R)}$<br>° | i      | DR63S<br>DR63M<br>DR63L<br>DRS71S<br>DRS71M | DRN80M<br>DRN90S | DRN90L | DRN100LS<br>DRN100L | DRN112M | DRN132S<br>DRN132M |
|  3   |                  |               |                   |        |                                             |                  |        |                     |         |                    |
| 6.1                                                                                   | 820              | 10300         | 5.7               | 228.99 |                                             |                  |        |                     |         |                    |
| 7.2                                                                                   | 820              | 10300         | 5.8               | 195.39 |                                             |                  |        |                     |         |                    |
| 8.2                                                                                   | 820              | 10300         | 5.7               | 170.85 |                                             |                  |        |                     |         |                    |
| 8.6                                                                                   | 820              | 10300         | 5.7               | 162.31 |                                             |                  |        |                     |         |                    |
| 9.8                                                                                   | 820              | 10300         | 5.8               | 142.40 |                                             |                  |        |                     |         |                    |
| 12                                                                                    | 820              | 10300         | 5.8               | 120.79 |                                             |                  |        |                     |         |                    |
| 13                                                                                    | 820              | 10300         | 5.8               | 109.04 |                                             |                  |        |                     |         |                    |
| 15                                                                                    | 820              | 10300         | 5.8               | 95.94  |                                             |                  |        |                     |         |                    |
| 15                                                                                    | 820              | 10300         | 5.8               | 90.59  |                                             |                  |        |                     |         |                    |
| 18                                                                                    | 820              | 10300         | 6.3               | 79.76  |                                             |                  |        |                     |         |                    |
| 21                                                                                    | 820              | 10300         | 6.3               | 67.65  |                                             |                  |        |                     |         |                    |
| 23                                                                                    | 820              | 10300         | 6.3               | 61.07  |                                             |                  |        |                     |         |                    |
| 26                                                                                    | 820              | 10300         | 6.3               | 53.73  |                                             |                  |        |                     |         |                    |
| 28                                                                                    | 820              | 10300         | 6.3               | 50.74  |                                             |                  |        |                     |         |                    |
| 32                                                                                    | 820              | 10300         | 6.3               | 43.20  |                                             |                  |        |                     |         |                    |
| 36                                                                                    | 780              | 10700         | 6.4               | 39.26  |                                             |                  |        |                     |         |                    |
| 41                                                                                    | 740              | 11000         | 6.5               | 34.01  |                                             |                  |        |                     |         |                    |
|  2 |                  |               |                   |        |                                             |                  |        |                     |         |                    |
| 39                                                                                    | 820              | 10300         | 5.3               | 36.30  |                                             |                  |        |                     |         |                    |
| 44                                                                                    | 820              | 10300         | 5.4               | 32.08  |                                             |                  |        |                     |         |                    |
| 51                                                                                    | 820              | 10300         | 5.4               | 27.41  |                                             |                  |        |                     |         |                    |
| 56                                                                                    | 820              | 10300         | 5.4               | 25.13  |                                             |                  |        |                     |         |                    |
| 63                                                                                    | 820              | 10300         | 5.5               | 22.05  |                                             |                  |        |                     |         |                    |
| 67                                                                                    | 820              | 10300         | 5.5               | 20.90* |                                             |                  |        |                     |         |                    |
| 77                                                                                    | 820              | 10300         | 5.6               | 18.29  |                                             |                  |        |                     |         |                    |
| 85                                                                                    | 820              | 10300         | 5.8               | 16.48  |                                             |                  |        |                     |         |                    |
| 97                                                                                    | 820              | 10300         | 5.7               | 14.46  |                                             |                  |        |                     |         |                    |
| 110                                                                                   | 820              | 10300         | 5.8               | 12.76  |                                             |                  |        |                     |         |                    |
| 124                                                                                   | 820              | 10300         | 6                 | 11.31  |                                             |                  |        |                     |         |                    |
| 145                                                                                   | 820              | 10300         | 6.1               | 9.66   |                                             |                  |        |                     |         |                    |
| 154                                                                                   | 530              | 11400         | 8                 | 9.08   |                                             |                  |        |                     |         |                    |
| 163                                                                                   | 570              | 10900         | 8.1               | 8.60   |                                             |                  |        |                     |         |                    |
| 186                                                                                   | 610              | 10100         | 8.2               | 7.53   |                                             |                  |        |                     |         |                    |
| 206                                                                                   | 620              | 9660          | 8.7               | 6.78   |                                             |                  |        |                     |         |                    |
| 235                                                                                   | 610              | 9200          | 8.6               | 5.95   |                                             |                  |        |                     |         |                    |
| 267                                                                                   | 590              | 8850          | 8.8               | 5.25   |                                             |                  |        |                     |         |                    |
| 300                                                                                   | 560              | 8590          | 9.3               | 4.66   |                                             |                  |        |                     |         |                    |
| 353                                                                                   | 500              | 8390          | 9.6               | 3.97   |                                             |                  |        |                     |         |                    |

| F67R37, $n_e=1400$ 1/min                                                                                                                                                    |                  |               |                   |       |                                             |                  |        |                     |  | 820 Nm |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------|---------------|-------------------|-------|---------------------------------------------|------------------|--------|---------------------|--|--------|
| $n_a$<br>rpm                                                                                                                                                                | $M_{amax}$<br>Nm | $F_{Ra}$<br>N | $\Phi_{(R)}$<br>° | i     | DR63S<br>DR63M<br>DR63L<br>DRS71S<br>DRS71M | DRN80M<br>DRN90S | DRN90L | DRN100LS<br>DRN100L |  |        |
|  3  3 |                  |               |                   |       |                                             |                  |        |                     |  |        |
| 0.07                                                                                                                                                                        | 820              | 10300         | -                 | 19199 |                                             |                  |        |                     |  |        |
| 0.08                                                                                                                                                                        | 820              | 10300         | -                 | 17610 |                                             |                  |        |                     |  |        |

F67R37, n<sub>e</sub>=1400 1/min

820 Nm

| n <sub>a</sub><br>rpm                                                                                                                                                       | M <sub>amax</sub><br>Nm | F <sub>Ra</sub><br>N | Φ <sub>(/R)</sub><br>° | i     | DR63S<br>DR63M<br>DR63L<br>DRS71S<br>DRS71M | DRN80M<br>DRN90S | DRN90L | DRN100LS<br>DRN100L |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------|----------------------|------------------------|-------|---------------------------------------------|------------------|--------|---------------------|
| 0.09                                                                                                                                                                        | 820                     | 10300                | -                      | 14992 |                                             |                  |        |                     |
| 0.11                                                                                                                                                                        | 820                     | 10300                | -                      | 12926 |                                             |                  |        |                     |
| 0.12                                                                                                                                                                        | 820                     | 10300                | -                      | 11480 |                                             |                  |        |                     |
| 0.14                                                                                                                                                                        | 820                     | 10300                | -                      | 10220 |                                             |                  |        |                     |
| 0.16                                                                                                                                                                        | 820                     | 10300                | -                      | 8933  |                                             |                  |        |                     |
| 0.18                                                                                                                                                                        | 820                     | 10300                | -                      | 7940  |                                             |                  |        |                     |
| 0.20                                                                                                                                                                        | 820                     | 10300                | -                      | 7096  |                                             |                  |        |                     |
| 0.23                                                                                                                                                                        | 820                     | 10300                | -                      | 6080  |                                             |                  |        |                     |
| 0.26                                                                                                                                                                        | 820                     | 10300                | -                      | 5341  |                                             |                  |        |                     |
| 0.30                                                                                                                                                                        | 820                     | 10300                | -                      | 4690  |                                             |                  |        |                     |
| 0.34                                                                                                                                                                        | 820                     | 10300                | -                      | 4091  |                                             |                  |        |                     |
| 0.39                                                                                                                                                                        | 820                     | 10300                | -                      | 3574  |                                             |                  |        |                     |
| 0.45                                                                                                                                                                        | 820                     | 10300                | -                      | 3133  |                                             |                  |        |                     |
| 0.51                                                                                                                                                                        | 820                     | 10300                | -                      | 2756  |                                             |                  |        |                     |
| 0.57                                                                                                                                                                        | 820                     | 10300                | -                      | 2439  |                                             |                  |        |                     |
|  2  3     |                         |                      |                        |       |                                             |                  |        |                     |
| 0.41                                                                                                                                                                        | 820                     | 10300                | -                      | 3377  |                                             |                  |        |                     |
| 0.48                                                                                                                                                                        | 820                     | 10300                | -                      | 2912  |                                             |                  |        |                     |
| 0.52                                                                                                                                                                        | 820                     | 10300                | -                      | 2714  |                                             |                  |        |                     |
| 0.59                                                                                                                                                                        | 820                     | 10300                | -                      | 2372  |                                             |                  |        |                     |
| 0.66                                                                                                                                                                        | 820                     | 10300                | -                      | 2126  |                                             |                  |        |                     |
| 0.75                                                                                                                                                                        | 820                     | 10300                | -                      | 1859  |                                             |                  |        |                     |
| 0.86                                                                                                                                                                        | 820                     | 10300                | -                      | 1631  |                                             |                  |        |                     |
| 0.97                                                                                                                                                                        | 820                     | 10300                | -                      | 1437  |                                             |                  |        |                     |
| 1.1                                                                                                                                                                         | 820                     | 10300                | -                      | 1256  |                                             |                  |        |                     |
| 1.2                                                                                                                                                                         | 820                     | 10300                | -                      | 1126  |                                             |                  |        |                     |
| 1.4                                                                                                                                                                         | 820                     | 10300                | -                      | 984   |                                             |                  |        |                     |
| 1.6                                                                                                                                                                         | 820                     | 10300                | -                      | 864   |                                             |                  |        |                     |
| 1.9                                                                                                                                                                         | 820                     | 10300                | -                      | 722   |                                             |                  |        |                     |
| 2.2                                                                                                                                                                         | 820                     | 10300                | -                      | 634   |                                             |                  |        |                     |
| 2.6                                                                                                                                                                         | 820                     | 10300                | -                      | 539   |                                             |                  |        |                     |
|  3  2 |                         |                      |                        |       |                                             |                  |        |                     |
| 0.66                                                                                                                                                                        | 820                     | 10300                | -                      | 2106  |                                             |                  |        |                     |
| 0.74                                                                                                                                                                        | 820                     | 10300                | -                      | 1884  |                                             |                  |        |                     |
| 0.86                                                                                                                                                                        | 820                     | 10300                | -                      | 1635  |                                             |                  |        |                     |
| 0.98                                                                                                                                                                        | 820                     | 10300                | -                      | 1429  |                                             |                  |        |                     |
| 1.1                                                                                                                                                                         | 820                     | 10300                | -                      | 1271  |                                             |                  |        |                     |
| 1.3                                                                                                                                                                         | 820                     | 10300                | -                      | 1102  |                                             |                  |        |                     |
| 1.4                                                                                                                                                                         | 820                     | 10300                | -                      | 970   |                                             |                  |        |                     |
| 1.6                                                                                                                                                                         | 820                     | 10300                | -                      | 858   |                                             |                  |        |                     |
| 1.9                                                                                                                                                                         | 820                     | 10300                | -                      | 755   |                                             |                  |        |                     |
| 2.2                                                                                                                                                                         | 820                     | 10300                | -                      | 641   |                                             |                  |        |                     |
| 2.4                                                                                                                                                                         | 820                     | 10300                | -                      | 572   |                                             |                  |        |                     |
| 2.8                                                                                                                                                                         | 820                     | 10300                | -                      | 509   |                                             |                  |        |                     |
| 3.2                                                                                                                                                                         | 820                     | 10300                | -                      | 437   |                                             |                  |        |                     |
| 3.6                                                                                                                                                                         | 820                     | 10300                | -                      | 384   |                                             |                  |        |                     |
| 4.1                                                                                                                                                                         | 820                     | 10300                | -                      | 338   |                                             |                  |        |                     |
| 4.6                                                                                                                                                                         | 820                     | 10300                | -                      | 305   |                                             |                  |        |                     |
| 5.4                                                                                                                                                                         | 820                     | 10300                | -                      | 257   |                                             |                  |        |                     |

21933170/DE – 11/2015

**F67R37,  $n_e=1400$  1/min****820 Nm**

| $n_a$<br>rpm                                                                                                                                                            | $M_{amax}$<br>Nm | $F_{Ra}$<br>N | $\Phi_{(R)}$<br>° | i   | DR63S<br>DR63M<br>DR63L<br>DRS71S<br>DRS71M | DRN80M<br>DRN90S | DRN90L | DRN100LS<br>DRN100L |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------|---------------|-------------------|-----|---------------------------------------------|------------------|--------|---------------------|
| 6.1                                                                                                                                                                     | 820              | 10300         | -                 | 231 |                                             |                  |        |                     |
| 6.8                                                                                                                                                                     | 820              | 10300         | -                 | 205 |                                             |                  |        |                     |
| 8.0                                                                                                                                                                     | 820              | 10300         | -                 | 175 |                                             |                  |        |                     |
|  2  2 |                  |               |                   |     |                                             |                  |        |                     |
| 2.8                                                                                                                                                                     | 820              | 10300         | -                 | 500 |                                             |                  |        |                     |
| 3.1                                                                                                                                                                     | 820              | 10300         | -                 | 454 |                                             |                  |        |                     |
| 3.6                                                                                                                                                                     | 820              | 10300         | -                 | 392 |                                             |                  |        |                     |
| 4.2                                                                                                                                                                     | 820              | 10300         | -                 | 333 |                                             |                  |        |                     |
| 4.7                                                                                                                                                                     | 820              | 10300         | -                 | 297 |                                             |                  |        |                     |
| 5.4                                                                                                                                                                     | 820              | 10300         | -                 | 261 |                                             |                  |        |                     |
| 5.9                                                                                                                                                                     | 820              | 10300         | -                 | 238 |                                             |                  |        |                     |
| 7.0                                                                                                                                                                     | 820              | 10300         | -                 | 200 |                                             |                  |        |                     |
| 8.0                                                                                                                                                                     | 820              | 10300         | -                 | 176 |                                             |                  |        |                     |

**F77,  $n_e=1400$  1/min****1500 Nm**

| $n_a$<br>rpm                                                                          | $M_{amax}$<br>Nm | $F_{Ra}$<br>N | $\Phi_{(R)}$<br>° | i       | DR63S<br>DR63M<br>DR63L<br>DRS71S<br>DRS71M | DRN80M<br>DRN90S | DRN90L | DRN100LS<br>DRN100L | DRN112M | DRN132S<br>DRN132M | DRN132L<br>DRN160M<br>DRN160L |
|---------------------------------------------------------------------------------------|------------------|---------------|-------------------|---------|---------------------------------------------|------------------|--------|---------------------|---------|--------------------|-------------------------------|
|  3 |                  |               |                   |         |                                             |                  |        |                     |         |                    |                               |
| 5.0                                                                                   | 1500             | 15700         | 5.4               | 281.71  |                                             |                  |        |                     |         |                    |                               |
| 5.3                                                                                   | 1500             | 15700         | 5.4               | 262.93  |                                             |                  |        |                     |         |                    |                               |
| 6.2                                                                                   | 1500             | 15700         | 5.4               | 225.79  |                                             |                  |        |                     |         |                    |                               |
| 7.1                                                                                   | 1500             | 15700         | 5.4               | 198.31  |                                             |                  |        |                     |         |                    |                               |
| 7.4                                                                                   | 1500             | 15700         | 5.4               | 188.40  |                                             |                  |        |                     |         |                    |                               |
| 8.4                                                                                   | 1500             | 15700         | 5.5               | 166.47  |                                             |                  |        |                     |         |                    |                               |
| 9.8                                                                                   | 1500             | 15700         | 5.5               | 142.27  |                                             |                  |        |                     |         |                    |                               |
| 11                                                                                    | 1500             | 15700         | 5.5               | 130.42  |                                             |                  |        |                     |         |                    |                               |
| 12                                                                                    | 1500             | 15700         | 5.5               | 114.45  |                                             |                  |        |                     |         |                    |                               |
| 13                                                                                    | 1500             | 15700         | 5.5               | 108.46* |                                             |                  |        |                     |         |                    |                               |
| 15                                                                                    | 1500             | 15700         | 5.5               | 94.93   |                                             |                  |        |                     |         |                    |                               |
| 16                                                                                    | 1500             | 15700         | 5.5               | 85.52   |                                             |                  |        |                     |         |                    |                               |
| 19                                                                                    | 1500             | 15700         | 5.5               | 75.02   |                                             |                  |        |                     |         |                    |                               |
| 19                                                                                    | 1500             | 15700         | 5.9               | 72.50   |                                             |                  |        |                     |         |                    |                               |
| 21                                                                                    | 1500             | 15700         | 5.9               | 66.46   |                                             |                  |        |                     |         |                    |                               |
| 24                                                                                    | 1500             | 15700         | 6                 | 58.32   |                                             |                  |        |                     |         |                    |                               |
| 25                                                                                    | 1500             | 15700         | 6                 | 55.27   |                                             |                  |        |                     |         |                    |                               |
| 29                                                                                    | 1500             | 15700         | 6                 | 48.37   |                                             |                  |        |                     |         |                    |                               |
| 32                                                                                    | 1500             | 15700         | 6.1               | 43.58   |                                             |                  |        |                     |         |                    |                               |
| 37                                                                                    | 1500             | 15700         | 6                 | 38.23   |                                             |                  |        |                     |         |                    |                               |
| 41                                                                                    | 1500             | 15700         | 6.1               | 33.74   |                                             |                  |        |                     |         |                    |                               |
| 47                                                                                    | 1500             | 15700         | 6.1               | 29.91   |                                             |                  |        |                     |         |                    |                               |
| 55                                                                                    | 1450             | 16100         | 6.2               | 25.54   |                                             |                  |        |                     |         |                    |                               |
|  2 |                  |               |                   |         |                                             |                  |        |                     |         |                    |                               |
| 38                                                                                    | 1110             | 17900         | 4.9               | 36.58   |                                             |                  |        |                     |         |                    |                               |
| 44                                                                                    | 1380             | 16500         | 4.9               | 31.51   |                                             |                  |        |                     |         |                    |                               |
| 49                                                                                    | 1430             | 16200         | 4.9               | 28.75   |                                             |                  |        |                     |         |                    |                               |
| 55                                                                                    | 1500             | 15700         | 4.9               | 25.50*  |                                             |                  |        |                     |         |                    |                               |

| F77, n <sub>e</sub> =1400 1/min |                         |                      |                       |        |                                             |                  |        |                     |         | 1500 Nm            |                               |
|---------------------------------|-------------------------|----------------------|-----------------------|--------|---------------------------------------------|------------------|--------|---------------------|---------|--------------------|-------------------------------|
| n <sub>a</sub><br>rpm           | M <sub>amax</sub><br>Nm | F <sub>Ra</sub><br>N | Φ <sub>(R)</sub><br>° | i      | DR63S<br>DR63M<br>DR63L<br>DRS71S<br>DRS71M | DRN80M<br>DRN90S | DRN90L | DRN100LS<br>DRN100L | DRN112M | DRN132S<br>DRN132M | DRN132L<br>DRN160M<br>DRN160L |
| 65                              | 1500                    | 15700                | 5                     | 21.43  |                                             |                  |        |                     |         |                    |                               |
| 71                              | 1500                    | 15700                | 5.1                   | 19.70  |                                             |                  |        |                     |         |                    |                               |
| 80                              | 1500                    | 15700                | 5.2                   | 17.49  |                                             |                  |        |                     |         |                    |                               |
| 90                              | 1500                    | 15700                | 5.2                   | 15.64* |                                             |                  |        |                     |         |                    |                               |
| 100                             | 1500                    | 15700                | 5.4                   | 14.06  |                                             |                  |        |                     |         |                    |                               |
| 115                             | 1500                    | 14900                | 5.4                   | 12.20  |                                             |                  |        |                     |         |                    |                               |
| 128                             | 1500                    | 14200                | 5.5                   | 10.93  |                                             |                  |        |                     |         |                    |                               |
| 151                             | 1080                    | 13800                | 7.1                   | 9.30   |                                             |                  |        |                     |         |                    |                               |
| 169                             | 1080                    | 13100                | 7.1                   | 8.26   |                                             |                  |        |                     |         |                    |                               |
| 189                             | 1080                    | 12500                | 7.2                   | 7.39   |                                             |                  |        |                     |         |                    |                               |
| 211                             | 1080                    | 12000                | 7.5                   | 6.64   |                                             |                  |        |                     |         |                    |                               |
| 243                             | 1080                    | 11300                | 7.7                   | 5.76   |                                             |                  |        |                     |         |                    |                               |
| 271                             | 1080                    | 10700                | 7.8                   | 5.16   |                                             |                  |        |                     |         |                    |                               |
| 327                             | 1010                    | 10200                | 8.1                   | 4.28   |                                             |                  |        |                     |         |                    |                               |

| F77R37, n <sub>e</sub> =1400 1/min                                                                                                                                          |                         |                      |                       |       |                                             |                  |        |                     |  | 1500 Nm |  |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------|----------------------|-----------------------|-------|---------------------------------------------|------------------|--------|---------------------|--|---------|--|
| n <sub>a</sub><br>rpm                                                                                                                                                       | M <sub>amax</sub><br>Nm | F <sub>Ra</sub><br>N | Φ <sub>(R)</sub><br>° | i     | DR63S<br>DR63M<br>DR63L<br>DRS71S<br>DRS71M | DRN80M<br>DRN90S | DRN90L | DRN100LS<br>DRN100L |  |         |  |
|  3  3 |                         |                      |                       |       |                                             |                  |        |                     |  |         |  |
| 0.07                                                                                                                                                                        | 1500                    | 15700                | -                     | 19180 |                                             |                  |        |                     |  |         |  |
| 0.08                                                                                                                                                                        | 1500                    | 15700                | -                     | 17593 |                                             |                  |        |                     |  |         |  |
| 0.09                                                                                                                                                                        | 1500                    | 15700                | -                     | 16128 |                                             |                  |        |                     |  |         |  |
| 0.09                                                                                                                                                                        | 1500                    | 15700                | -                     | 14978 |                                             |                  |        |                     |  |         |  |
| 0.10                                                                                                                                                                        | 1500                    | 15700                | -                     | 13731 |                                             |                  |        |                     |  |         |  |
| 0.12                                                                                                                                                                        | 1500                    | 15700                | -                     | 12049 |                                             |                  |        |                     |  |         |  |
| 0.13                                                                                                                                                                        | 1500                    | 15700                | -                     | 11035 |                                             |                  |        |                     |  |         |  |
| 0.14                                                                                                                                                                        | 1500                    | 15700                | -                     | 9683  |                                             |                  |        |                     |  |         |  |
| 0.17                                                                                                                                                                        | 1500                    | 15700                | -                     | 8464  |                                             |                  |        |                     |  |         |  |
| 0.19                                                                                                                                                                        | 1500                    | 15700                | -                     | 7520  |                                             |                  |        |                     |  |         |  |
| 0.21                                                                                                                                                                        | 1500                    | 15700                | -                     | 6580  |                                             |                  |        |                     |  |         |  |
| 0.24                                                                                                                                                                        | 1500                    | 15700                | -                     | 5808  |                                             |                  |        |                     |  |         |  |
| 0.28                                                                                                                                                                        | 1500                    | 15700                | -                     | 5026  |                                             |                  |        |                     |  |         |  |
| 0.32                                                                                                                                                                        | 1500                    | 15700                | -                     | 4435  |                                             |                  |        |                     |  |         |  |
| 0.37                                                                                                                                                                        | 1500                    | 15700                | -                     | 3832  |                                             |                  |        |                     |  |         |  |
| 0.41                                                                                                                                                                        | 1500                    | 15700                | -                     | 3381  |                                             |                  |        |                     |  |         |  |
| 0.47                                                                                                                                                                        | 1500                    | 15700                | -                     | 2978  |                                             |                  |        |                     |  |         |  |
| 0.54                                                                                                                                                                        | 1500                    | 15700                | -                     | 2613  |                                             |                  |        |                     |  |         |  |
| 0.61                                                                                                                                                                        | 1500                    | 15700                | -                     | 2284  |                                             |                  |        |                     |  |         |  |
| 0.69                                                                                                                                                                        | 1500                    | 15700                | -                     | 2029  |                                             |                  |        |                     |  |         |  |
|  2  3 |                         |                      |                       |       |                                             |                  |        |                     |  |         |  |
| 0.28                                                                                                                                                                        | 1110                    | 17900                | -                     | 4931  |                                             |                  |        |                     |  |         |  |
| 0.31                                                                                                                                                                        | 1110                    | 17900                | -                     | 4523  |                                             |                  |        |                     |  |         |  |
| 0.36                                                                                                                                                                        | 1110                    | 17900                | -                     | 3851  |                                             |                  |        |                     |  |         |  |
| 0.42                                                                                                                                                                        | 1110                    | 17900                | -                     | 3320  |                                             |                  |        |                     |  |         |  |
| 0.45                                                                                                                                                                        | 1110                    | 17900                | -                     | 3095  |                                             |                  |        |                     |  |         |  |
| 0.52                                                                                                                                                                        | 1110                    | 17900                | -                     | 2705  |                                             |                  |        |                     |  |         |  |
| 0.55                                                                                                                                                                        | 1110                    | 17900                | -                     | 2536  |                                             |                  |        |                     |  |         |  |

21933170/DE – 11/2015

| F77R37, $n_e=1400$ 1/min                                                                                                                                                    |                  |               |                   |      | 1500 Nm                                     |                  |        |                     |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------|---------------|-------------------|------|---------------------------------------------|------------------|--------|---------------------|
| $n_a$<br>rpm                                                                                                                                                                | $M_{amax}$<br>Nm | $F_{Ra}$<br>N | $\Phi_{(R)}$<br>° | i    | DR63S<br>DR63M<br>DR63L<br>DRS71S<br>DRS71M | DRN80M<br>DRN90S | DRN90L | DRN100LS<br>DRN100L |
| 0.63                                                                                                                                                                        | 1110             | 17900         | -                 | 2238 |                                             |                  |        |                     |
| 0.69                                                                                                                                                                        | 1110             | 17900         | -                 | 2039 |                                             |                  |        |                     |
| 0.80                                                                                                                                                                        | 1110             | 17900         | -                 | 1759 |                                             |                  |        |                     |
| 0.85                                                                                                                                                                        | 1110             | 17900         | -                 | 1639 |                                             |                  |        |                     |
| 0.98                                                                                                                                                                        | 1110             | 17900         | -                 | 1433 |                                             |                  |        |                     |
| 1.0                                                                                                                                                                         | 1110             | 17900         | -                 | 1343 |                                             |                  |        |                     |
| 1.2                                                                                                                                                                         | 1110             | 17900         | -                 | 1185 |                                             |                  |        |                     |
| 1.3                                                                                                                                                                         | 1110             | 17900         | -                 | 1051 |                                             |                  |        |                     |
| 1.6                                                                                                                                                                         | 1110             | 17900         | -                 | 893  |                                             |                  |        |                     |
|  3  2     |                  |               |                   |      |                                             |                  |        |                     |
| 0.81                                                                                                                                                                        | 1500             | 15700         | -                 | 1728 |                                             |                  |        |                     |
| 0.91                                                                                                                                                                        | 1500             | 15700         | -                 | 1544 |                                             |                  |        |                     |
| 1.0                                                                                                                                                                         | 1500             | 15700         | -                 | 1354 |                                             |                  |        |                     |
| 1.2                                                                                                                                                                         | 1500             | 15700         | -                 | 1200 |                                             |                  |        |                     |
| 1.3                                                                                                                                                                         | 1500             | 15700         | -                 | 1053 |                                             |                  |        |                     |
| 1.5                                                                                                                                                                         | 1500             | 15700         | -                 | 910  |                                             |                  |        |                     |
| 1.7                                                                                                                                                                         | 1500             | 15700         | -                 | 810  |                                             |                  |        |                     |
| 2.0                                                                                                                                                                         | 1500             | 15700         | -                 | 710  |                                             |                  |        |                     |
| 2.3                                                                                                                                                                         | 1500             | 15700         | -                 | 615* |                                             |                  |        |                     |
| 2.6                                                                                                                                                                         | 1500             | 15700         | -                 | 538  |                                             |                  |        |                     |
| 2.9                                                                                                                                                                         | 1500             | 15700         | -                 | 480  |                                             |                  |        |                     |
| 3.4                                                                                                                                                                         | 1500             | 15700         | -                 | 413  |                                             |                  |        |                     |
| 3.8                                                                                                                                                                         | 1500             | 15700         | -                 | 367  |                                             |                  |        |                     |
| 4.3                                                                                                                                                                         | 1500             | 15700         | -                 | 323  |                                             |                  |        |                     |
| 5.0                                                                                                                                                                         | 1500             | 15700         | -                 | 280  |                                             |                  |        |                     |
| 5.7                                                                                                                                                                         | 1500             | 15700         | -                 | 247  |                                             |                  |        |                     |
| 6.3                                                                                                                                                                         | 1500             | 15700         | -                 | 221  |                                             |                  |        |                     |
| 7.0                                                                                                                                                                         | 1500             | 15700         | -                 | 199  |                                             |                  |        |                     |
|  2  2 |                  |               |                   |      |                                             |                  |        |                     |
| 1.7                                                                                                                                                                         | 1110             | 17900         | -                 | 815  |                                             |                  |        |                     |
| 2.0                                                                                                                                                                         | 1110             | 17900         | -                 | 706  |                                             |                  |        |                     |
| 2.1                                                                                                                                                                         | 1110             | 17900         | -                 | 660  |                                             |                  |        |                     |
| 2.5                                                                                                                                                                         | 1110             | 17900         | -                 | 571  |                                             |                  |        |                     |
| 2.9                                                                                                                                                                         | 1110             | 17900         | -                 | 485  |                                             |                  |        |                     |
| 3.2                                                                                                                                                                         | 1110             | 17900         | -                 | 433  |                                             |                  |        |                     |
| 3.8                                                                                                                                                                         | 1110             | 17900         | -                 | 370  |                                             |                  |        |                     |
| 4.0                                                                                                                                                                         | 1110             | 17900         | -                 | 346  |                                             |                  |        |                     |
| 4.8                                                                                                                                                                         | 1110             | 17900         | -                 | 292  |                                             |                  |        |                     |

| F87, $n_e=1400$ 1/min                                                                 |                  |               |                   |        | 3000 Nm |                  |        |                     |         |                    |                               |                    |         |
|---------------------------------------------------------------------------------------|------------------|---------------|-------------------|--------|---------|------------------|--------|---------------------|---------|--------------------|-------------------------------|--------------------|---------|
| $n_a$<br>rpm                                                                          | $M_{amax}$<br>Nm | $F_{Ra}$<br>N | $\Phi_{(R)}$<br>° | i      | DRS71M  | DRN80M<br>DRN90S | DRN90L | DRN100LS<br>DRN100L | DRN112M | DRN132S<br>DRN132M | DRN132L<br>DRN160M<br>DRN160L | DRN180M<br>DRN180L | DRN200L |
|  3 |                  |               |                   |        |         |                  |        |                     |         |                    |                               |                    |         |
| 5.2                                                                                   | 3000             | 19800         | 7                 | 270.68 |         |                  |        |                     |         |                    |                               |                    |         |
| 5.5                                                                                   | 3000             | 19800         | 7                 | 255.37 |         |                  |        |                     |         |                    |                               |                    |         |
| 6.1                                                                                   | 3000             | 19800         | 7                 | 228.93 |         |                  |        |                     |         |                    |                               |                    |         |
| 7.1                                                                                   | 3000             | 19800         | 7                 | 197.20 |         |                  |        |                     |         |                    |                               |                    |         |
| 7.8                                                                                   | 3000             | 19800         | 7                 | 179.97 |         |                  |        |                     |         |                    |                               |                    |         |

| F87, $n_e=1400$ 1/min                                                               |                  |               |                   |        |        |                  |        |                     |         | 3000 Nm            |                               |                    |         |
|-------------------------------------------------------------------------------------|------------------|---------------|-------------------|--------|--------|------------------|--------|---------------------|---------|--------------------|-------------------------------|--------------------|---------|
| $n_a$<br>rpm                                                                        | $M_{amax}$<br>Nm | $F_{Ra}$<br>N | $\Phi_{(R)}$<br>° | $i$    | DRS71M | DRN80M<br>DRN90S | DRN90L | DRN100LS<br>DRN100L | DRN112M | DRN132S<br>DRN132M | DRN132L<br>DRN160M<br>DRN160L | DRN180M<br>DRN180L | DRN200L |
| 8.8                                                                                 | 3000             | 19800         | 7                 | 159.61 |        |                  |        |                     |         |                    |                               |                    |         |
| 10                                                                                  | 3000             | 19800         | 7                 | 134.16 |        |                  |        |                     |         |                    |                               |                    |         |
| 11                                                                                  | 3000             | 19800         | 7                 | 123.29 |        |                  |        |                     |         |                    |                               |                    |         |
| 13                                                                                  | 3000             | 19800         | 7.1               | 109.49 |        |                  |        |                     |         |                    |                               |                    |         |
| 14                                                                                  | 3000             | 19800         | 7.1               | 97.89  |        |                  |        |                     |         |                    |                               |                    |         |
| 16                                                                                  | 3000             | 19800         | 7.1               | 88.01  |        |                  |        |                     |         |                    |                               |                    |         |
| 18                                                                                  | 3000             | 19800         | 7.1               | 76.39  |        |                  |        |                     |         |                    |                               |                    |         |
| 20                                                                                  | 3000             | 19600         | 7.1               | 68.40  |        |                  |        |                     |         |                    |                               |                    |         |
| 25                                                                                  | 3000             | 17700         | 7.1               | 56.75  |        |                  |        |                     |         |                    |                               |                    |         |
| 28                                                                                  | 2940             | 16800         | 7.5               | 50.36  |        |                  |        |                     |         |                    |                               |                    |         |
| 31                                                                                  | 2820             | 16200         | 7.5               | 45.28  |        |                  |        |                     |         |                    |                               |                    |         |
| 36                                                                                  | 2720             | 15400         | 7.5               | 39.30  |        |                  |        |                     |         |                    |                               |                    |         |
| 40                                                                                  | 2610             | 14900         | 7.6               | 35.19  |        |                  |        |                     |         |                    |                               |                    |         |
| 48                                                                                  | 2510             | 13800         | 7.6               | 29.20  |        |                  |        |                     |         |                    |                               |                    |         |
|  2 |                  |               |                   |        |        |                  |        |                     |         |                    |                               |                    |         |
| 41                                                                                  | 2610             | 14600         | 6.6               | 33.92  |        |                  |        |                     |         |                    |                               |                    |         |
| 49                                                                                  | 2450             | 13900         | 6.6               | 28.78  |        |                  |        |                     |         |                    |                               |                    |         |
| 53                                                                                  | 3000             | 11100         | 6.8               | 26.50  |        |                  |        |                     |         |                    |                               |                    |         |
| 59                                                                                  | 3000             | 10300         | 6.8               | 23.68  |        |                  |        |                     |         |                    |                               |                    |         |
| 66                                                                                  | 3000             | 9520          | 6.8               | 21.32* |        |                  |        |                     |         |                    |                               |                    |         |
| 73                                                                                  | 3000             | 8840          | 6.9               | 19.31  |        |                  |        |                     |         |                    |                               |                    |         |
| 82                                                                                  | 3000             | 8040          | 6.9               | 17.12  |        |                  |        |                     |         |                    |                               |                    |         |
| 90                                                                                  | 3000             | 7390          | 7                 | 15.48  |        |                  |        |                     |         |                    |                               |                    |         |
| 107                                                                                 | 3000             | 6370          | 7                 | 13.12* |        |                  |        |                     |         |                    |                               |                    |         |
| 122                                                                                 | 3000             | 5580          | 7.1               | 11.46  |        |                  |        |                     |         |                    |                               |                    |         |
| 146                                                                                 | 2880             | 5050          | 7.2               | 9.58   |        |                  |        |                     |         |                    |                               |                    |         |
| 169                                                                                 | 1530             | 8890          | 6.7               | 8.29   |        |                  |        |                     |         |                    |                               |                    |         |
| 190                                                                                 | 1530             | 8280          | 6.8               | 7.35   |        |                  |        |                     |         |                    |                               |                    |         |
| 211                                                                                 | 1530             | 7790          | 6.8               | 6.65   |        |                  |        |                     |         |                    |                               |                    |         |
| 249                                                                                 | 1530             | 7020          | 7                 | 5.63   |        |                  |        |                     |         |                    |                               |                    |         |
| 285                                                                                 | 1530             | 6430          | 7.1               | 4.92   |        |                  |        |                     |         |                    |                               |                    |         |
| 340                                                                                 | 1460             | 5980          | 7.4               | 4.12   |        |                  |        |                     |         |                    |                               |                    |         |

| F87R57, n <sub>e</sub> =1400 1/min                                                                                                                                          |                         |                      |                        |       |                                             |                  |        |                     |         | 3000 Nm            |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------|----------------------|------------------------|-------|---------------------------------------------|------------------|--------|---------------------|---------|--------------------|
| n <sub>a</sub><br>rpm                                                                                                                                                       | M <sub>amax</sub><br>Nm | F <sub>Ra</sub><br>N | Φ <sub>(/R)</sub><br>° | i     | DR63S<br>DR63M<br>DR63L<br>DRS71S<br>DRS71M | DRN80M<br>DRN90S | DRN90L | DRN100LS<br>DRN100L | DRN112M | DRN132S<br>DRN132M |
|  3  3 |                         |                      |                        |       |                                             |                  |        |                     |         |                    |
| 0.06                                                                                                                                                                        | 3000                    | 19800                | -                      | 23042 |                                             |                  |        |                     |         |                    |
| 0.07                                                                                                                                                                        | 3000                    | 19800                | -                      | 20462 |                                             |                  |        |                     |         |                    |
| 0.08                                                                                                                                                                        | 3000                    | 19800                | -                      | 18238 |                                             |                  |        |                     |         |                    |
| 0.09                                                                                                                                                                        | 3000                    | 19800                | -                      | 15877 |                                             |                  |        |                     |         |                    |
| 0.10                                                                                                                                                                        | 3000                    | 19800                | -                      | 14099 |                                             |                  |        |                     |         |                    |
| 0.11                                                                                                                                                                        | 3000                    | 19800                | -                      | 12205 |                                             |                  |        |                     |         |                    |
| 0.13                                                                                                                                                                        | 3000                    | 19800                | -                      | 10433 |                                             |                  |        |                     |         |                    |
| 0.15                                                                                                                                                                        | 3000                    | 19800                | -                      | 9381  |                                             |                  |        |                     |         |                    |
| 0.17                                                                                                                                                                        | 3000                    | 19800                | -                      | 8142  |                                             |                  |        |                     |         |                    |
| 0.20                                                                                                                                                                        | 3000                    | 19800                | -                      | 7100  |                                             |                  |        |                     |         |                    |
| 0.22                                                                                                                                                                        | 3000                    | 19800                | -                      | 6273  |                                             |                  |        |                     |         |                    |

21933170/DE – 11/2015

F87R57,  $n_e=1400$  1/min

3000 Nm

| $n_a$<br>rpm                                                                                                                                                                | $M_{amax}$<br>Nm | $F_{Ra}$<br>N | $\Phi_{(R)}$<br>° | $i$   | DR63S<br>DR63M<br>DR63L<br>DRS71S<br>DRS71M | DRN80M<br>DRN90S | DRN90L | DRN100LS<br>DRN100L | DRN112M | DRN132S<br>DRN132M |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------|---------------|-------------------|-------|---------------------------------------------|------------------|--------|---------------------|---------|--------------------|
| 0.25                                                                                                                                                                        | 3000             | 19800         | -                 | 5510  |                                             |                  |        |                     |         |                    |
| 0.28                                                                                                                                                                        | 3000             | 19800         | -                 | 4954  |                                             |                  |        |                     |         |                    |
| 0.33                                                                                                                                                                        | 3000             | 19800         | -                 | 4245  |                                             |                  |        |                     |         |                    |
| 0.38                                                                                                                                                                        | 3000             | 19800         | -                 | 3721  |                                             |                  |        |                     |         |                    |
|  2  3     |                  |               |                   |       |                                             |                  |        |                     |         |                    |
| 0.28                                                                                                                                                                        | 3000             | 19800         | -                 | 4952  |                                             |                  |        |                     |         |                    |
| 0.31                                                                                                                                                                        | 3000             | 19800         | -                 | 4562  |                                             |                  |        |                     |         |                    |
| 0.36                                                                                                                                                                        | 3000             | 19800         | -                 | 3919  |                                             |                  |        |                     |         |                    |
| 0.40                                                                                                                                                                        | 3000             | 19800         | -                 | 3503  |                                             |                  |        |                     |         |                    |
| 0.44                                                                                                                                                                        | 3000             | 19800         | -                 | 3196  |                                             |                  |        |                     |         |                    |
| 0.49                                                                                                                                                                        | 3000             | 19800         | -                 | 2857  |                                             |                  |        |                     |         |                    |
| 0.55                                                                                                                                                                        | 3000             | 19800         | -                 | 2524  |                                             |                  |        |                     |         |                    |
| 0.66                                                                                                                                                                        | 3000             | 19800         | -                 | 2134  |                                             |                  |        |                     |         |                    |
| 0.73                                                                                                                                                                        | 3000             | 19800         | -                 | 1913* |                                             |                  |        |                     |         |                    |
| 0.82                                                                                                                                                                        | 3000             | 19800         | -                 | 1717  |                                             |                  |        |                     |         |                    |
| 0.95                                                                                                                                                                        | 3000             | 19800         | -                 | 1476  |                                             |                  |        |                     |         |                    |
| 1.1                                                                                                                                                                         | 3000             | 19800         | -                 | 1278  |                                             |                  |        |                     |         |                    |
| 1.2                                                                                                                                                                         | 3000             | 19800         | -                 | 1142  |                                             |                  |        |                     |         |                    |
| 1.4                                                                                                                                                                         | 3000             | 19800         | -                 | 988   |                                             |                  |        |                     |         |                    |
| 1.6                                                                                                                                                                         | 3000             | 19800         | -                 | 883   |                                             |                  |        |                     |         |                    |
| 1.9                                                                                                                                                                         | 3000             | 19800         | -                 | 748   |                                             |                  |        |                     |         |                    |
|  3  2 |                  |               |                   |       |                                             |                  |        |                     |         |                    |
| 0.43                                                                                                                                                                        | 3000             | 19800         | -                 | 3244  |                                             |                  |        |                     |         |                    |
| 0.49                                                                                                                                                                        | 3000             | 19800         | -                 | 2881  |                                             |                  |        |                     |         |                    |
| 0.54                                                                                                                                                                        | 3000             | 19800         | -                 | 2576  |                                             |                  |        |                     |         |                    |
| 0.64                                                                                                                                                                        | 3000             | 19800         | -                 | 2199  |                                             |                  |        |                     |         |                    |
| 0.73                                                                                                                                                                        | 3000             | 19800         | -                 | 1930  |                                             |                  |        |                     |         |                    |
| 0.82                                                                                                                                                                        | 3000             | 19800         | -                 | 1709  |                                             |                  |        |                     |         |                    |
| 0.94                                                                                                                                                                        | 3000             | 19800         | -                 | 1493  |                                             |                  |        |                     |         |                    |
| 1.1                                                                                                                                                                         | 3000             | 19800         | -                 | 1300  |                                             |                  |        |                     |         |                    |
| 1.2                                                                                                                                                                         | 3000             | 19800         | -                 | 1148  |                                             |                  |        |                     |         |                    |
| 1.4                                                                                                                                                                         | 3000             | 19800         | -                 | 1010  |                                             |                  |        |                     |         |                    |
| 1.6                                                                                                                                                                         | 3000             | 19800         | -                 | 887   |                                             |                  |        |                     |         |                    |
| 1.8                                                                                                                                                                         | 3000             | 19800         | -                 | 780   |                                             |                  |        |                     |         |                    |
| 2.1                                                                                                                                                                         | 3000             | 19800         | -                 | 674   |                                             |                  |        |                     |         |                    |
| 2.3                                                                                                                                                                         | 3000             | 19800         | -                 | 609   |                                             |                  |        |                     |         |                    |
| 2.7                                                                                                                                                                         | 3000             | 19800         | -                 | 515   |                                             |                  |        |                     |         |                    |
| 3.1                                                                                                                                                                         | 3000             | 19800         | -                 | 452   |                                             |                  |        |                     |         |                    |
| 4.1                                                                                                                                                                         | 3000             | 19800         | -                 | 345   |                                             |                  |        |                     |         |                    |
| 4.7                                                                                                                                                                         | 3000             | 19800         | -                 | 300   |                                             |                  |        |                     |         |                    |
| 5.6                                                                                                                                                                         | 3000             | 19800         | -                 | 249   |                                             |                  |        |                     |         |                    |
|  2  2 |                  |               |                   |       |                                             |                  |        |                     |         |                    |
| 2.1                                                                                                                                                                         | 3000             | 19800         | -                 | 662   |                                             |                  |        |                     |         |                    |
| 2.4                                                                                                                                                                         | 3000             | 19800         | -                 | 592   |                                             |                  |        |                     |         |                    |
| 2.7                                                                                                                                                                         | 3000             | 19800         | -                 | 519   |                                             |                  |        |                     |         |                    |
| 3.0                                                                                                                                                                         | 3000             | 19800         | -                 | 468   |                                             |                  |        |                     |         |                    |
| 3.5                                                                                                                                                                         | 3000             | 19800         | -                 | 398   |                                             |                  |        |                     |         |                    |
| 4.0                                                                                                                                                                         | 3000             | 19800         | -                 | 350   |                                             |                  |        |                     |         |                    |
| 4.4                                                                                                                                                                         | 3000             | 19800         | -                 | 315*  |                                             |                  |        |                     |         |                    |



**F87R57, n<sub>e</sub>=1400 1/min**

**3000 Nm**

| n <sub>a</sub><br>rpm | M <sub>amax</sub><br>Nm | F <sub>Ra</sub><br>N | φ <sub>(/R)</sub><br>° | i   | DR63S<br>DR63M<br>DR63L<br>DRS71S<br>DRS71M | DRN80M<br>DRN90S | DRN90L | DRN100LS<br>DRN100L | DRN112M | DRN132S<br>DRN132M |
|-----------------------|-------------------------|----------------------|------------------------|-----|---------------------------------------------|------------------|--------|---------------------|---------|--------------------|
| 5.0                   | 3000                    | 19800                | -                      | 281 |                                             |                  |        |                     |         |                    |
| 5.8                   | 3000                    | 19800                | -                      | 240 |                                             |                  |        |                     |         |                    |
| 6.6                   | 3000                    | 19800                | -                      | 211 |                                             |                  |        |                     |         |                    |
| 7.3                   | 3000                    | 19800                | -                      | 193 |                                             |                  |        |                     |         |                    |

**F97, n<sub>e</sub>=1400 1/min**

**4300 Nm**

| n <sub>a</sub><br>rpm                                                                 | M <sub>amax</sub><br>Nm | F <sub>Ra</sub><br>N | φ <sub>(/R)</sub><br>° | i      | DRN80M<br>DRN90S | DRN90L | DRN100LS<br>DRN100L | DRN112M | DRN132S<br>DRN132M | DRN132L<br>DRN160M<br>DRN160L | DRN180M<br>DRN180L | DRN200L<br>DRN225S |
|---------------------------------------------------------------------------------------|-------------------------|----------------------|------------------------|--------|------------------|--------|---------------------|---------|--------------------|-------------------------------|--------------------|--------------------|
|  3   |                         |                      |                        |        |                  |        |                     |         |                    |                               |                    |                    |
| 5.1                                                                                   | 4300                    | 29900                | 6                      | 276.77 |                  |        |                     |         |                    |                               |                    |                    |
| 5.5                                                                                   | 4300                    | 29900                | 6                      | 253.41 |                  |        |                     |         |                    |                               |                    |                    |
| 6.3                                                                                   | 4300                    | 29900                | 6                      | 223.88 |                  |        |                     |         |                    |                               |                    |                    |
| 7.4                                                                                   | 4300                    | 29900                | 6                      | 189.92 |                  |        |                     |         |                    |                               |                    |                    |
| 8.0                                                                                   | 4300                    | 29900                | 6                      | 174.87 |                  |        |                     |         |                    |                               |                    |                    |
| 9.0                                                                                   | 4300                    | 29900                | 6                      | 156.30 |                  |        |                     |         |                    |                               |                    |                    |
| 9.9                                                                                   | 4300                    | 29900                | 6                      | 140.71 |                  |        |                     |         |                    |                               |                    |                    |
| 11                                                                                    | 4300                    | 29900                | 6                      | 127.42 |                  |        |                     |         |                    |                               |                    |                    |
| 12                                                                                    | 4300                    | 29900                | 6                      | 112.99 |                  |        |                     |         |                    |                               |                    |                    |
| 14                                                                                    | 4300                    | 29900                | 6                      | 102.16 |                  |        |                     |         |                    |                               |                    |                    |
| 14                                                                                    | 4300                    | 29900                | 6.2                    | 97.58  |                  |        |                     |         |                    |                               |                    |                    |
| 16                                                                                    | 4300                    | 29900                | 6.3                    | 89.85  |                  |        |                     |         |                    |                               |                    |                    |
| 16                                                                                    | 4300                    | 29900                | 6                      | 86.59  |                  |        |                     |         |                    |                               |                    |                    |
| 17                                                                                    | 4300                    | 29900                | 6.3                    | 80.31  |                  |        |                     |         |                    |                               |                    |                    |
| 19                                                                                    | 4300                    | 29900                | 6                      | 75.63  |                  |        |                     |         |                    |                               |                    |                    |
| 19                                                                                    | 4300                    | 29900                | 6.3                    | 72.29  |                  |        |                     |         |                    |                               |                    |                    |
| 21                                                                                    | 4300                    | 29000                | 6.3                    | 65.47  |                  |        |                     |         |                    |                               |                    |                    |
| 24                                                                                    | 4300                    | 27200                | 6.3                    | 58.06  |                  |        |                     |         |                    |                               |                    |                    |
| 27                                                                                    | 4300                    | 25800                | 6.3                    | 52.49  |                  |        |                     |         |                    |                               |                    |                    |
| 31                                                                                    | 4300                    | 23600                | 6.4                    | 44.49  |                  |        |                     |         |                    |                               |                    |                    |
| 36                                                                                    | 4300                    | 21900                | 6.4                    | 38.86  |                  |        |                     |         |                    |                               |                    |                    |
| 43                                                                                    | 4300                    | 19800                | 6.4                    | 32.50  |                  |        |                     |         |                    |                               |                    |                    |
|  2 |                         |                      |                        |        |                  |        |                     |         |                    |                               |                    |                    |
| 32                                                                                    | 3070                    | 27600                | 5.6                    | 43.28  |                  |        |                     |         |                    |                               |                    |                    |
| 38                                                                                    | 3070                    | 25500                | 5.6                    | 36.64  |                  |        |                     |         |                    |                               |                    |                    |
| 41                                                                                    | 4300                    | 20300                | 5.7                    | 33.91  |                  |        |                     |         |                    |                               |                    |                    |
| 46                                                                                    | 4300                    | 19000                | 5.8                    | 30.39  |                  |        |                     |         |                    |                               |                    |                    |
| 51                                                                                    | 4300                    | 17900                | 5.8                    | 27.44* |                  |        |                     |         |                    |                               |                    |                    |
| 56                                                                                    | 4300                    | 16800                | 5.8                    | 24.92  |                  |        |                     |         |                    |                               |                    |                    |
| 63                                                                                    | 4300                    | 15600                | 5.9                    | 22.11  |                  |        |                     |         |                    |                               |                    |                    |
| 70                                                                                    | 4300                    | 14600                | 5.8                    | 20.07  |                  |        |                     |         |                    |                               |                    |                    |
| 81                                                                                    | 4300                    | 13200                | 5.9                    | 17.25* |                  |        |                     |         |                    |                               |                    |                    |
| 93                                                                                    | 4300                    | 11900                | 5.9                    | 15.06  |                  |        |                     |         |                    |                               |                    |                    |
| 110                                                                                   | 4300                    | 10500                | 6                      | 12.77  |                  |        |                     |         |                    |                               |                    |                    |
| 125                                                                                   | 4100                    | 10000                | 6                      | 11.16  |                  |        |                     |         |                    |                               |                    |                    |
| 155                                                                                   | 2360                    | 13400                | 8.6                    | 9.06   |                  |        |                     |         |                    |                               |                    |                    |
| 170                                                                                   | 2360                    | 12600                | 8.5                    | 8.22   |                  |        |                     |         |                    |                               |                    |                    |
| 198                                                                                   | 2360                    | 11500                | 8.6                    | 7.07   |                  |        |                     |         |                    |                               |                    |                    |
| 227                                                                                   | 2250                    | 11100                | 8.7                    | 6.17   |                  |        |                     |         |                    |                               |                    |                    |

21933170/DE – 11/2015

| F97, $n_e=1400$ 1/min |                  |               |                   |      |                  |        |                     |         |                    | 4300 Nm                       |                    |                    |
|-----------------------|------------------|---------------|-------------------|------|------------------|--------|---------------------|---------|--------------------|-------------------------------|--------------------|--------------------|
| $n_a$<br>rpm          | $M_{amax}$<br>Nm | $F_{Ra}$<br>N | $\Phi_{(R)}$<br>° | $i$  | DRN80M<br>DRN90S | DRN90L | DRN100LS<br>DRN100L | DRN112M | DRN132S<br>DRN132M | DRN132L<br>DRN160M<br>DRN160L | DRN180M<br>DRN180L | DRN200L<br>DRN225S |
| 268                   | 2150             | 10400         | 8.8               | 5.23 |                  |        |                     |         |                    |                               |                    |                    |
| 306                   | 2050             | 9950          | 9                 | 4.57 |                  |        |                     |         |                    |                               |                    |                    |
| 362                   | 1800             | 9960          | 9                 | 3.87 |                  |        |                     |         |                    |                               |                    |                    |

| F97R57, n <sub>e</sub> =1400 1/min                                                                                                                                          |                         |                      |                        |        |                                             |                  |        |                     |         | 4300 Nm            |  |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------|----------------------|------------------------|--------|---------------------------------------------|------------------|--------|---------------------|---------|--------------------|--|
| n <sub>a</sub><br>rpm                                                                                                                                                       | M <sub>amax</sub><br>Nm | F <sub>Ra</sub><br>N | Φ <sub>(/R)</sub><br>' | i      | DR63S<br>DR63M<br>DR63L<br>DRS71S<br>DRS71M | DRN80M<br>DRN90S | DRN90L | DRN100LS<br>DRN100L | DRN112M | DRN132S<br>DRN132M |  |
|  3  3     |                         |                      |                        |        |                                             |                  |        |                     |         |                    |  |
| 0.05                                                                                                                                                                        | 4300                    | 29900                | -                      | 29211  |                                             |                  |        |                     |         |                    |  |
| 0.05                                                                                                                                                                        | 4300                    | 29900                | -                      | 26911  |                                             |                  |        |                     |         |                    |  |
| 0.06                                                                                                                                                                        | 4300                    | 29900                | -                      | 23814  |                                             |                  |        |                     |         |                    |  |
| 0.07                                                                                                                                                                        | 4300                    | 29900                | -                      | 20813  |                                             |                  |        |                     |         |                    |  |
| 0.08                                                                                                                                                                        | 4300                    | 29900                | -                      | 18119* |                                             |                  |        |                     |         |                    |  |
| 0.09                                                                                                                                                                        | 4300                    | 29900                | -                      | 15472  |                                             |                  |        |                     |         |                    |  |
| 0.10                                                                                                                                                                        | 4300                    | 29900                | -                      | 14022  |                                             |                  |        |                     |         |                    |  |
| 0.11                                                                                                                                                                        | 4300                    | 29900                | -                      | 12324  |                                             |                  |        |                     |         |                    |  |
| 0.13                                                                                                                                                                        | 4300                    | 29900                | -                      | 10838  |                                             |                  |        |                     |         |                    |  |
| 0.15                                                                                                                                                                        | 4300                    | 29900                | -                      | 9576   |                                             |                  |        |                     |         |                    |  |
| 0.17                                                                                                                                                                        | 4300                    | 29900                | -                      | 8318   |                                             |                  |        |                     |         |                    |  |
| 0.19                                                                                                                                                                        | 4300                    | 29900                | -                      | 7328   |                                             |                  |        |                     |         |                    |  |
| 0.22                                                                                                                                                                        | 4300                    | 29900                | -                      | 6469   |                                             |                  |        |                     |         |                    |  |
| 0.25                                                                                                                                                                        | 4300                    | 29900                | -                      | 5615   |                                             |                  |        |                     |         |                    |  |
| 0.28                                                                                                                                                                        | 4300                    | 29900                | -                      | 4961*  |                                             |                  |        |                     |         |                    |  |
| 0.32                                                                                                                                                                        | 4300                    | 29900                | -                      | 4333*  |                                             |                  |        |                     |         |                    |  |
|  2  3 |                         |                      |                        |        |                                             |                  |        |                     |         |                    |  |
| 0.22                                                                                                                                                                        | 4300                    | 29900                | -                      | 6338   |                                             |                  |        |                     |         |                    |  |
| 0.25                                                                                                                                                                        | 4300                    | 29900                | -                      | 5680   |                                             |                  |        |                     |         |                    |  |
| 0.28                                                                                                                                                                        | 4300                    | 29900                | -                      | 5016   |                                             |                  |        |                     |         |                    |  |
| 0.32                                                                                                                                                                        | 4300                    | 29900                | -                      | 4367   |                                             |                  |        |                     |         |                    |  |
| 0.36                                                                                                                                                                        | 4300                    | 29900                | -                      | 3914   |                                             |                  |        |                     |         |                    |  |
| 0.42                                                                                                                                                                        | 4300                    | 29900                | -                      | 3357   |                                             |                  |        |                     |         |                    |  |
| 0.47                                                                                                                                                                        | 4300                    | 29900                | -                      | 3009   |                                             |                  |        |                     |         |                    |  |
| 0.57                                                                                                                                                                        | 4300                    | 29900                | -                      | 2448   |                                             |                  |        |                     |         |                    |  |
| 0.64                                                                                                                                                                        | 4300                    | 29900                | -                      | 2199   |                                             |                  |        |                     |         |                    |  |
| 0.71                                                                                                                                                                        | 4300                    | 29900                | -                      | 1971   |                                             |                  |        |                     |         |                    |  |
| 0.80                                                                                                                                                                        | 4300                    | 29900                | -                      | 1741*  |                                             |                  |        |                     |         |                    |  |
| 0.95                                                                                                                                                                        | 4300                    | 29900                | -                      | 1468   |                                             |                  |        |                     |         |                    |  |
| 1.1                                                                                                                                                                         | 4300                    | 29900                | -                      | 1316   |                                             |                  |        |                     |         |                    |  |
| 1.2                                                                                                                                                                         | 4300                    | 29900                | -                      | 1189*  |                                             |                  |        |                     |         |                    |  |
| 1.4                                                                                                                                                                         | 4300                    | 29900                | -                      | 1023   |                                             |                  |        |                     |         |                    |  |
|  3  2 |                         |                      |                        |        |                                             |                  |        |                     |         |                    |  |
| 0.36                                                                                                                                                                        | 4300                    | 29900                | -                      | 3906   |                                             |                  |        |                     |         |                    |  |
| 0.42                                                                                                                                                                        | 4300                    | 29900                | -                      | 3352   |                                             |                  |        |                     |         |                    |  |
| 0.48                                                                                                                                                                        | 4300                    | 29900                | -                      | 2907   |                                             |                  |        |                     |         |                    |  |
| 0.55                                                                                                                                                                        | 4300                    | 29900                | -                      | 2553   |                                             |                  |        |                     |         |                    |  |
| 0.62                                                                                                                                                                        | 4300                    | 29900                | -                      | 2245   |                                             |                  |        |                     |         |                    |  |
| 0.71                                                                                                                                                                        | 4300                    | 29900                | -                      | 1970   |                                             |                  |        |                     |         |                    |  |
| 0.81                                                                                                                                                                        | 4300                    | 29900                | -                      | 1722   |                                             |                  |        |                     |         |                    |  |

**F97R57,  $n_e=1400$  1/min**

**4300 Nm**

| $n_a$<br>rpm | $M_{amax}$<br>Nm | $F_{Ra}$<br>N | $\Phi_{(R)}$<br>° | i     | DR63S<br>DR63M<br>DR63L<br>DRS71S<br>DRS71M | DRN80M<br>DRN90S | DRN90L | DRN100LS<br>DRN100L | DRN112M | DRN132S<br>DRN132M |
|--------------|------------------|---------------|-------------------|-------|---------------------------------------------|------------------|--------|---------------------|---------|--------------------|
| 0.92         | 4300             | 29900         | -                 | 1527  |                                             |                  |        |                     |         |                    |
| 1.1          | 4300             | 29900         | -                 | 1327  |                                             |                  |        |                     |         |                    |
| 1.2          | 4300             | 29900         | -                 | 1171* |                                             |                  |        |                     |         |                    |
| 1.4          | 4300             | 29900         | -                 | 1022  |                                             |                  |        |                     |         |                    |
| 1.6          | 4300             | 29900         | -                 | 898   |                                             |                  |        |                     |         |                    |
| 1.8          | 4300             | 29900         | -                 | 784   |                                             |                  |        |                     |         |                    |
| 2.0          | 4300             | 29900         | -                 | 690   |                                             |                  |        |                     |         |                    |
| 2.3          | 4300             | 29900         | -                 | 605   |                                             |                  |        |                     |         |                    |
| 2.6          | 4300             | 29900         | -                 | 529   |                                             |                  |        |                     |         |                    |
| 3.0          | 4300             | 29900         | -                 | 467   |                                             |                  |        |                     |         |                    |
| 3.4          | 4300             | 29900         | -                 | 406   |                                             |                  |        |                     |         |                    |
| 3.9          | 4300             | 29900         | -                 | 363   |                                             |                  |        |                     |         |                    |
| 4.9          | 4300             | 29900         | -                 | 285   |                                             |                  |        |                     |         |                    |
| 5.7          | 4300             | 29900         | -                 | 245   |                                             |                  |        |                     |         |                    |
| 6.7          | 4300             | 29900         | -                 | 208   |                                             |                  |        |                     |         |                    |
| 7.2          | 4300             | 29900         | -                 | 195   |                                             |                  |        |                     |         |                    |



|     |      |       |   |      |  |  |  |  |  |  |
|-----|------|-------|---|------|--|--|--|--|--|--|
| 1.6 | 4300 | 29900 | - | 892  |  |  |  |  |  |  |
| 1.8 | 4300 | 29900 | - | 760  |  |  |  |  |  |  |
| 2.1 | 4300 | 29900 | - | 667  |  |  |  |  |  |  |
| 2.5 | 4300 | 29900 | - | 569  |  |  |  |  |  |  |
| 2.7 | 4300 | 29900 | - | 510  |  |  |  |  |  |  |
| 3.0 | 4300 | 29900 | - | 473* |  |  |  |  |  |  |
| 3.5 | 4300 | 29900 | - | 403  |  |  |  |  |  |  |
| 3.9 | 4300 | 29900 | - | 361  |  |  |  |  |  |  |
| 4.4 | 4300 | 29900 | - | 317  |  |  |  |  |  |  |
| 5.1 | 4300 | 29900 | - | 275  |  |  |  |  |  |  |
| 5.8 | 4300 | 29900 | - | 242  |  |  |  |  |  |  |

**F107,  $n_e=1400$  1/min**

**7840 Nm**

| $n_a$<br>rpm | $M_{amax}$<br>Nm | $F_{Ra}$<br>N | $\Phi_{(R)}$<br>° | i | DRN100LS<br>DRN100L | DRN112M | DRN132S<br>DRN132M | DRN132L<br>DRN160M<br>DRN160L | DRN180M<br>DRN180L | DRN200L<br>DRN225S<br>DRN225M | DRN250M |
|--------------|------------------|---------------|-------------------|---|---------------------|---------|--------------------|-------------------------------|--------------------|-------------------------------|---------|
|--------------|------------------|---------------|-------------------|---|---------------------|---------|--------------------|-------------------------------|--------------------|-------------------------------|---------|



|     |      |       |     |         |  |  |  |  |  |  |  |
|-----|------|-------|-----|---------|--|--|--|--|--|--|--|
| 5.5 | 7680 | 49800 | 5.4 | 254.40* |  |  |  |  |  |  |  |
| 6.5 | 7680 | 49800 | 5.4 | 215.37  |  |  |  |  |  |  |  |
| 7.0 | 7680 | 49800 | 5.4 | 199.31  |  |  |  |  |  |  |  |
| 7.8 | 7680 | 49800 | 5.4 | 178.64  |  |  |  |  |  |  |  |
| 8.7 | 7680 | 49800 | 5.4 | 161.28* |  |  |  |  |  |  |  |
| 9.6 | 7680 | 49800 | 5.4 | 146.49  |  |  |  |  |  |  |  |
| 11  | 7680 | 49800 | 5.4 | 129.97  |  |  |  |  |  |  |  |
| 12  | 7680 | 49800 | 5.4 | 117.94  |  |  |  |  |  |  |  |
| 14  | 7680 | 49800 | 5.4 | 101.38* |  |  |  |  |  |  |  |
| 15  | 7680 | 49800 | 5.6 | 92.47*  |  |  |  |  |  |  |  |
| 16  | 7680 | 49800 | 5.4 | 88.49   |  |  |  |  |  |  |  |
| 17  | 7680 | 49800 | 5.7 | 83.99   |  |  |  |  |  |  |  |
| 19  | 7680 | 49800 | 5.7 | 74.52   |  |  |  |  |  |  |  |
| 21  | 7680 | 49800 | 5.7 | 67.62   |  |  |  |  |  |  |  |
| 24  | 7680 | 47800 | 5.7 | 58.12*  |  |  |  |  |  |  |  |

| F107, n <sub>e</sub> =1400 1/min                                                    |                         |                      |                       |        |                     |         |                    |                               |                    | 7840 Nm                       |         |
|-------------------------------------------------------------------------------------|-------------------------|----------------------|-----------------------|--------|---------------------|---------|--------------------|-------------------------------|--------------------|-------------------------------|---------|
| n <sub>a</sub><br>rpm                                                               | M <sub>amax</sub><br>Nm | F <sub>Ra</sub><br>N | Φ <sub>(R)</sub><br>° | i      | DRN100LS<br>DRN100L | DRN112M | DRN132S<br>DRN132M | DRN132L<br>DRN160M<br>DRN160L | DRN180M<br>DRN180L | DRN200L<br>DRN225S<br>DRN225M | DRN250M |
| 28                                                                                  | 7680                    | 45100                | 5.7                   | 50.73  |                     |         |                    |                               |                    |                               |         |
| 33                                                                                  | 7680                    | 42000                | 5.7                   | 43.03  |                     |         |                    |                               |                    |                               |         |
| 37                                                                                  | 7680                    | 39500                | 5.7                   | 37.61  |                     |         |                    |                               |                    |                               |         |
| 44                                                                                  | 7680                    | 36500                | 5.8                   | 31.80  |                     |         |                    |                               |                    |                               |         |
|  2 |                         |                      |                       |        |                     |         |                    |                               |                    |                               |         |
| 41                                                                                  | 7400                    | 38300                | 5.1                   | 33.79* |                     |         |                    |                               |                    |                               |         |
| 51                                                                                  | 7840                    | 33300                | 5.2                   | 27.57  |                     |         |                    |                               |                    |                               |         |
| 56                                                                                  | 7840                    | 31500                | 5.2                   | 25.14  |                     |         |                    |                               |                    |                               |         |
| 64                                                                                  | 7840                    | 28800                | 5.2                   | 21.76* |                     |         |                    |                               |                    |                               |         |
| 73                                                                                  | 7840                    | 26500                | 5.2                   | 19.20* |                     |         |                    |                               |                    |                               |         |
| 84                                                                                  | 7840                    | 23900                | 5.3                   | 16.58  |                     |         |                    |                               |                    |                               |         |
| 95                                                                                  | 7680                    | 22400                | 5.3                   | 14.67  |                     |         |                    |                               |                    |                               |         |
| 114                                                                                 | 7000                    | 22600                | 5.4                   | 12.33  |                     |         |                    |                               |                    |                               |         |
| 141                                                                                 | 6500                    | 21500                | 5.4                   | 9.96   |                     |         |                    |                               |                    |                               |         |
| 144                                                                                 | 4910                    | 23500                | 6.7                   | 9.69   |                     |         |                    |                               |                    |                               |         |
| 167                                                                                 | 4800                    | 22000                | 6.7                   | 8.37   |                     |         |                    |                               |                    |                               |         |
| 189                                                                                 | 4600                    | 21300                | 6.8                   | 7.40   |                     |         |                    |                               |                    |                               |         |
| 225                                                                                 | 4600                    | 19000                | 7                     | 6.22   |                     |         |                    |                               |                    |                               |         |
| 278                                                                                 | 4600                    | 16400                | 7                     | 5.03   |                     |         |                    |                               |                    |                               |         |

| F107R77, n <sub>e</sub> =1400 1/min                                                                                                                                         |                         |                      |                        |        | 7840 Nm                                     |                  |        |                     |         |                    |                               |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------|----------------------|------------------------|--------|---------------------------------------------|------------------|--------|---------------------|---------|--------------------|-------------------------------|
| n <sub>a</sub><br>rpm                                                                                                                                                       | M <sub>amax</sub><br>Nm | F <sub>Ra</sub><br>N | Φ <sub>(/R)</sub><br>° | i      | DR63S<br>DR63M<br>DR63L<br>DRS71S<br>DRS71M | DRN80M<br>DRN90S | DRN90L | DRN100LS<br>DRN100L | DRN112M | DRN132S<br>DRN132M | DRN132L<br>DRN160M<br>DRN160L |
|  3  3 |                         |                      |                        |        |                                             |                  |        |                     |         |                    |                               |
| 0.06                                                                                                                                                                        | 7680                    | 49800                | -                      | 25375* |                                             |                  |        |                     |         |                    |                               |
| 0.06                                                                                                                                                                        | 7680                    | 49800                | -                      | 21652  |                                             |                  |        |                     |         |                    |                               |
| 0.07                                                                                                                                                                        | 7680                    | 49800                | -                      | 18933  |                                             |                  |        |                     |         |                    |                               |
| 0.08                                                                                                                                                                        | 7680                    | 49800                | -                      | 16888  |                                             |                  |        |                     |         |                    |                               |
| 0.09                                                                                                                                                                        | 7680                    | 49800                | -                      | 14767  |                                             |                  |        |                     |         |                    |                               |
| 0.12                                                                                                                                                                        | 7680                    | 49800                | -                      | 11348* |                                             |                  |        |                     |         |                    |                               |
| 0.14                                                                                                                                                                        | 7680                    | 49800                | -                      | 10039  |                                             |                  |        |                     |         |                    |                               |
| 0.16                                                                                                                                                                        | 7680                    | 49800                | -                      | 8548   |                                             |                  |        |                     |         |                    |                               |
| 0.18                                                                                                                                                                        | 7680                    | 49800                | -                      | 7674   |                                             |                  |        |                     |         |                    |                               |
| 0.21                                                                                                                                                                        | 7680                    | 49800                | -                      | 6767   |                                             |                  |        |                     |         |                    |                               |
| 0.24                                                                                                                                                                        | 7680                    | 49800                | -                      | 5954   |                                             |                  |        |                     |         |                    |                               |
| 0.27                                                                                                                                                                        | 7680                    | 49800                | -                      | 5223   |                                             |                  |        |                     |         |                    |                               |
| 0.31                                                                                                                                                                        | 7680                    | 49800                | -                      | 4567   |                                             |                  |        |                     |         |                    |                               |
| 0.35                                                                                                                                                                        | 7680                    | 49800                | -                      | 3948   |                                             |                  |        |                     |         |                    |                               |
| 0.40                                                                                                                                                                        | 7680                    | 49800                | -                      | 3521   |                                             |                  |        |                     |         |                    |                               |
|  2  3 |                         |                      |                        |        |                                             |                  |        |                     |         |                    |                               |
| 0.26                                                                                                                                                                        | 7840                    | 49400                | -                      | 5383*  |                                             |                  |        |                     |         |                    |                               |
| 0.30                                                                                                                                                                        | 7840                    | 49400                | -                      | 4593   |                                             |                  |        |                     |         |                    |                               |
| 0.35                                                                                                                                                                        | 7840                    | 49400                | -                      | 4016   |                                             |                  |        |                     |         |                    |                               |
| 0.37                                                                                                                                                                        | 7840                    | 49400                | -                      | 3815   |                                             |                  |        |                     |         |                    |                               |
| 0.42                                                                                                                                                                        | 7840                    | 49400                | -                      | 3347   |                                             |                  |        |                     |         |                    |                               |
| 0.49                                                                                                                                                                        | 7840                    | 49400                | -                      | 2839   |                                             |                  |        |                     |         |                    |                               |
| 0.55                                                                                                                                                                        | 7840                    | 49400                | -                      | 2563*  |                                             |                  |        |                     |         |                    |                               |
| 0.62                                                                                                                                                                        | 7840                    | 49400                | -                      | 2255   |                                             |                  |        |                     |         |                    |                               |

| F107R77, n <sub>e</sub> =1400 1/min                                                                                                                                         |                         |                      |                        |      |                                             |                  |        |                     |         |                    | 7840 Nm                       |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------|----------------------|------------------------|------|---------------------------------------------|------------------|--------|---------------------|---------|--------------------|-------------------------------|
| n <sub>a</sub><br>rpm                                                                                                                                                       | M <sub>amax</sub><br>Nm | F <sub>Ra</sub><br>N | φ <sub>(/R)</sub><br>° | i    | DR63S<br>DR63M<br>DR63L<br>DRS71S<br>DRS71M | DRN80M<br>DRN90S | DRN90L | DRN100LS<br>DRN100L | DRN112M | DRN132S<br>DRN132M | DRN132L<br>DRN160M<br>DRN160L |
| 0.66                                                                                                                                                                        | 7840                    | 49400                | -                      | 2129 |                                             |                  |        |                     |         |                    |                               |
| 0.77                                                                                                                                                                        | 7840                    | 49400                | -                      | 1813 |                                             |                  |        |                     |         |                    |                               |
| 0.88                                                                                                                                                                        | 7840                    | 49400                | -                      | 1590 |                                             |                  |        |                     |         |                    |                               |
| 0.97                                                                                                                                                                        | 7840                    | 49400                | -                      | 1436 |                                             |                  |        |                     |         |                    |                               |
| 1.1                                                                                                                                                                         | 7840                    | 49400                | -                      | 1263 |                                             |                  |        |                     |         |                    |                               |
| 1.2                                                                                                                                                                         | 7840                    | 49400                | -                      | 1193 |                                             |                  |        |                     |         |                    |                               |
| 1.4                                                                                                                                                                         | 7840                    | 49400                | -                      | 1015 |                                             |                  |        |                     |         |                    |                               |
| 1.5                                                                                                                                                                         | 7840                    | 49400                | -                      | 923  |                                             |                  |        |                     |         |                    |                               |
| 1.8                                                                                                                                                                         | 7840                    | 49400                | -                      | 800  |                                             |                  |        |                     |         |                    |                               |
| 2.0                                                                                                                                                                         | 7840                    | 49400                | -                      | 696  |                                             |                  |        |                     |         |                    |                               |
|  3  2     |                         |                      |                        |      |                                             |                  |        |                     |         |                    |                               |
| 0.46                                                                                                                                                                        | 7680                    | 49800                | -                      | 3037 |                                             |                  |        |                     |         |                    |                               |
| 0.51                                                                                                                                                                        | 7680                    | 49800                | -                      | 2756 |                                             |                  |        |                     |         |                    |                               |
| 0.59                                                                                                                                                                        | 7680                    | 49800                | -                      | 2369 |                                             |                  |        |                     |         |                    |                               |
| 0.68                                                                                                                                                                        | 7680                    | 49800                | -                      | 2068 |                                             |                  |        |                     |         |                    |                               |
| 0.77                                                                                                                                                                        | 7680                    | 49800                | -                      | 1826 |                                             |                  |        |                     |         |                    |                               |
| 0.88                                                                                                                                                                        | 7680                    | 49800                | -                      | 1597 |                                             |                  |        |                     |         |                    |                               |
| 1.00                                                                                                                                                                        | 7680                    | 49800                | -                      | 1401 |                                             |                  |        |                     |         |                    |                               |
| 1.1                                                                                                                                                                         | 7680                    | 49800                | -                      | 1243 |                                             |                  |        |                     |         |                    |                               |
| 1.3                                                                                                                                                                         | 7680                    | 49800                | -                      | 1087 |                                             |                  |        |                     |         |                    |                               |
| 1.5                                                                                                                                                                         | 7680                    | 49800                | -                      | 950  |                                             |                  |        |                     |         |                    |                               |
| 1.7                                                                                                                                                                         | 7680                    | 49800                | -                      | 834  |                                             |                  |        |                     |         |                    |                               |
| 1.9                                                                                                                                                                         | 7680                    | 49800                | -                      | 736  |                                             |                  |        |                     |         |                    |                               |
| 2.2                                                                                                                                                                         | 7680                    | 49800                | -                      | 640  |                                             |                  |        |                     |         |                    |                               |
| 2.5                                                                                                                                                                         | 7680                    | 49800                | -                      | 560  |                                             |                  |        |                     |         |                    |                               |
| 2.9                                                                                                                                                                         | 7680                    | 49800                | -                      | 489  |                                             |                  |        |                     |         |                    |                               |
| 3.2                                                                                                                                                                         | 7680                    | 49800                | -                      | 436  |                                             |                  |        |                     |         |                    |                               |
| 3.8                                                                                                                                                                         | 7680                    | 49800                | -                      | 370  |                                             |                  |        |                     |         |                    |                               |
| 4.2                                                                                                                                                                         | 7680                    | 49800                | -                      | 333  |                                             |                  |        |                     |         |                    |                               |
| 4.8                                                                                                                                                                         | 7680                    | 49800                | -                      | 291  |                                             |                  |        |                     |         |                    |                               |
| 5.5                                                                                                                                                                         | 7680                    | 49800                | -                      | 255  |                                             |                  |        |                     |         |                    |                               |
| 6.2                                                                                                                                                                         | 7680                    | 49800                | -                      | 225* |                                             |                  |        |                     |         |                    |                               |
| 7.4                                                                                                                                                                         | 7680                    | 49800                | -                      | 190  |                                             |                  |        |                     |         |                    |                               |
|  2  2 |                         |                      |                        |      |                                             |                  |        |                     |         |                    |                               |
| 2.2                                                                                                                                                                         | 7840                    | 49400                | -                      | 644  |                                             |                  |        |                     |         |                    |                               |
| 2.4                                                                                                                                                                         | 7840                    | 49400                | -                      | 591  |                                             |                  |        |                     |         |                    |                               |
| 2.7                                                                                                                                                                         | 7840                    | 49400                | -                      | 518* |                                             |                  |        |                     |         |                    |                               |
| 2.9                                                                                                                                                                         | 7840                    | 49400                | -                      | 491  |                                             |                  |        |                     |         |                    |                               |
| 3.3                                                                                                                                                                         | 7840                    | 49400                | -                      | 430  |                                             |                  |        |                     |         |                    |                               |
| 3.6                                                                                                                                                                         | 7840                    | 49400                | -                      | 387  |                                             |                  |        |                     |         |                    |                               |
| 4.1                                                                                                                                                                         | 7840                    | 49400                | -                      | 340  |                                             |                  |        |                     |         |                    |                               |
| 4.7                                                                                                                                                                         | 7840                    | 49400                | -                      | 300  |                                             |                  |        |                     |         |                    |                               |
| 5.3                                                                                                                                                                         | 7840                    | 49400                | -                      | 266  |                                             |                  |        |                     |         |                    |                               |

21933170/DE – 11/2015

| F127, $n_e=1400$ 1/min                                                              |                  |               |                   |         | 12000 Nm           |                               |                    |                               |                               |
|-------------------------------------------------------------------------------------|------------------|---------------|-------------------|---------|--------------------|-------------------------------|--------------------|-------------------------------|-------------------------------|
| $n_a$<br>rpm                                                                        | $M_{amax}$<br>Nm | $F_{Ra}$<br>N | $\Phi_{(R)}$<br>° | $i$     | DRN132S<br>DRN132M | DRN132L<br>DRN160M<br>DRN160L | DRN180M<br>DRN180L | DRN200L<br>DRN225S<br>DRN225M | DRN250M<br>DRN280S<br>DRN280M |
|  3 |                  |               |                   |         |                    |                               |                    |                               |                               |
| 8.2                                                                                 | 12000            | 90000         | 4.9               | 170.83  |                    |                               |                    |                               |                               |
| 9.1                                                                                 | 12000            | 90000         | 4.9               | 153.67* |                    |                               |                    |                               |                               |
| 11                                                                                  | 12000            | 90000         | 4.9               | 125.37  |                    |                               |                    |                               |                               |
| 12                                                                                  | 12000            | 88000         | 4.9               | 114.34  |                    |                               |                    |                               |                               |
| 14                                                                                  | 12000            | 83000         | 4.9               | 98.95   |                    |                               |                    |                               |                               |
| 16                                                                                  | 12000            | 79000         | 4.9               | 87.31*  |                    |                               |                    |                               |                               |
| 19                                                                                  | 12000            | 74300         | 4.9               | 75.41*  |                    |                               |                    |                               |                               |
| 20                                                                                  | 12000            | 72100         | 5.2               | 70.07   |                    |                               |                    |                               |                               |
| 22                                                                                  | 12000            | 69400         | 5.2               | 63.91   |                    |                               |                    |                               |                               |
| 25                                                                                  | 12000            | 65200         | 5.2               | 55.31   |                    |                               |                    |                               |                               |
| 29                                                                                  | 12000            | 61300         | 5.2               | 48.80   |                    |                               |                    |                               |                               |
| 33                                                                                  | 12000            | 56800         | 5.2               | 42.15   |                    |                               |                    |                               |                               |
| 38                                                                                  | 12000            | 53200         | 5.2               | 37.28   |                    |                               |                    |                               |                               |
| 45                                                                                  | 12000            | 48300         | 5.3               | 31.33   |                    |                               |                    |                               |                               |
| 55                                                                                  | 12000            | 42400         | 5.3               | 25.30   |                    |                               |                    |                               |                               |
|  2 |                  |               |                   |         |                    |                               |                    |                               |                               |
| 52                                                                                  | 8500             | 55300         | 4.6               | 26.86   |                    |                               |                    |                               |                               |
| 57                                                                                  | 8500             | 53300         | 4.6               | 24.57   |                    |                               |                    |                               |                               |
| 65                                                                                  | 12000            | 38000         | 4.7               | 21.38   |                    |                               |                    |                               |                               |
| 74                                                                                  | 11000            | 38800         | 4.7               | 18.87   |                    |                               |                    |                               |                               |
| 86                                                                                  | 11000            | 35400         | 4.7               | 16.36   |                    |                               |                    |                               |                               |
| 96                                                                                  | 11000            | 32600         | 4.7               | 14.55   |                    |                               |                    |                               |                               |
| 112                                                                                 | 10000            | 33300         | 4.8               | 12.54   |                    |                               |                    |                               |                               |
| 137                                                                                 | 9500             | 30900         | 4.9               | 10.19   |                    |                               |                    |                               |                               |
| 158                                                                                 | 7000             | 36400         | 6.3               | 8.86    |                    |                               |                    |                               |                               |
| 178                                                                                 | 6000             | 37000         | 6.4               | 7.88    |                    |                               |                    |                               |                               |
| 206                                                                                 | 7000             | 32200         | 6.5               | 6.80    |                    |                               |                    |                               |                               |
| 254                                                                                 | 6000             | 31700         | 6.7               | 5.52    |                    |                               |                    |                               |                               |
| 299                                                                                 | 6000             | 29500         | 6.8               | 4.68    |                    |                               |                    |                               |                               |

| F127R77, $n_e=1400$ 1/min                                                                                                                                                   |                  |               |                   |        | 12000 Nm                                    |                  |        |                     |         |                    |                               |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------|---------------|-------------------|--------|---------------------------------------------|------------------|--------|---------------------|---------|--------------------|-------------------------------|
| $n_a$<br>rpm                                                                                                                                                                | $M_{amax}$<br>Nm | $F_{Ra}$<br>N | $\Phi_{(R)}$<br>° | $i$    | DR63S<br>DR63M<br>DR63L<br>DRS71S<br>DRS71M | DRN80M<br>DRN90S | DRN90L | DRN100LS<br>DRN100L | DRN112M | DRN132S<br>DRN132M | DRN132L<br>DRN160M<br>DRN160L |
|  3  3 |                  |               |                   |        |                                             |                  |        |                     |         |                    |                               |
| 0.06                                                                                                                                                                        | 12000            | 90000         | -                 | 24478* |                                             |                  |        |                     |         |                    |                               |
| 0.06                                                                                                                                                                        | 12000            | 90000         | -                 | 22323  |                                             |                  |        |                     |         |                    |                               |
| 0.07                                                                                                                                                                        | 12000            | 90000         | -                 | 19048  |                                             |                  |        |                     |         |                    |                               |
| 0.08                                                                                                                                                                        | 12000            | 90000         | -                 | 16656  |                                             |                  |        |                     |         |                    |                               |
| 0.10                                                                                                                                                                        | 12000            | 90000         | -                 | 14722* |                                             |                  |        |                     |         |                    |                               |
| 0.11                                                                                                                                                                        | 12000            | 90000         | -                 | 12912  |                                             |                  |        |                     |         |                    |                               |
| 0.12                                                                                                                                                                        | 12000            | 90000         | -                 | 11656* |                                             |                  |        |                     |         |                    |                               |
| 0.14                                                                                                                                                                        | 12000            | 90000         | -                 | 10191  |                                             |                  |        |                     |         |                    |                               |
| 0.16                                                                                                                                                                        | 12000            | 90000         | -                 | 8831   |                                             |                  |        |                     |         |                    |                               |
| 0.18                                                                                                                                                                        | 12000            | 90000         | -                 | 7643   |                                             |                  |        |                     |         |                    |                               |
| 0.21                                                                                                                                                                        | 12000            | 90000         | -                 | 6715   |                                             |                  |        |                     |         |                    |                               |
| 0.24                                                                                                                                                                        | 12000            | 90000         | -                 | 5925   |                                             |                  |        |                     |         |                    |                               |
| 0.27                                                                                                                                                                        | 12000            | 90000         | -                 | 5153   |                                             |                  |        |                     |         |                    |                               |

| F127R77, $n_e=1400$ 1/min                                                                                                                                               |                  |               |                   |       | 12000 Nm                                    |                  |        |                     |         |                    |                               |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------|---------------|-------------------|-------|---------------------------------------------|------------------|--------|---------------------|---------|--------------------|-------------------------------|
| $n_a$<br>rpm                                                                                                                                                            | $M_{amax}$<br>Nm | $F_{Ra}$<br>N | $\Phi_{(R)}$<br>° | $i$   | DR63S<br>DR63M<br>DR63L<br>DRS71S<br>DRS71M | DRN80M<br>DRN90S | DRN90L | DRN100LS<br>DRN100L | DRN112M | DRN132S<br>DRN132M | DRN132L<br>DRN160M<br>DRN160L |
| 0.31                                                                                                                                                                    | 12000            | 90000         | -                 | 4533  |                                             |                  |        |                     |         |                    |                               |
| 0.36                                                                                                                                                                    | 12000            | 90000         | -                 | 3926  |                                             |                  |        |                     |         |                    |                               |
| 0.41                                                                                                                                                                    | 12000            | 90000         | -                 | 3454  |                                             |                  |        |                     |         |                    |                               |
| 0.46                                                                                                                                                                    | 12000            | 90000         | -                 | 3031  |                                             |                  |        |                     |         |                    |                               |
|  3  2 |                  |               |                   |       |                                             |                  |        |                     |         |                    |                               |
| 0.52                                                                                                                                                                    | 12000            | 90000         | -                 | 2672  |                                             |                  |        |                     |         |                    |                               |
| 0.59                                                                                                                                                                    | 12000            | 90000         | -                 | 2357* |                                             |                  |        |                     |         |                    |                               |
| 0.69                                                                                                                                                                    | 12000            | 90000         | -                 | 2038  |                                             |                  |        |                     |         |                    |                               |
| 0.78                                                                                                                                                                    | 12000            | 90000         | -                 | 1784  |                                             |                  |        |                     |         |                    |                               |
| 0.87                                                                                                                                                                    | 12000            | 90000         | -                 | 1606  |                                             |                  |        |                     |         |                    |                               |
| 1.0                                                                                                                                                                     | 12000            | 90000         | -                 | 1390  |                                             |                  |        |                     |         |                    |                               |
| 1.1                                                                                                                                                                     | 12000            | 90000         | -                 | 1220  |                                             |                  |        |                     |         |                    |                               |
| 1.3                                                                                                                                                                     | 12000            | 90000         | -                 | 1077  |                                             |                  |        |                     |         |                    |                               |
| 1.5                                                                                                                                                                     | 12000            | 90000         | -                 | 930   |                                             |                  |        |                     |         |                    |                               |
| 1.7                                                                                                                                                                     | 12000            | 90000         | -                 | 820   |                                             |                  |        |                     |         |                    |                               |
| 1.9                                                                                                                                                                     | 12000            | 90000         | -                 | 727   |                                             |                  |        |                     |         |                    |                               |
| 2.2                                                                                                                                                                     | 12000            | 90000         | -                 | 648   |                                             |                  |        |                     |         |                    |                               |
| 2.6                                                                                                                                                                     | 12000            | 90000         | -                 | 549   |                                             |                  |        |                     |         |                    |                               |
| 2.8                                                                                                                                                                     | 12000            | 90000         | -                 | 495   |                                             |                  |        |                     |         |                    |                               |
| 3.3                                                                                                                                                                     | 12000            | 90000         | -                 | 428   |                                             |                  |        |                     |         |                    |                               |
| 3.7                                                                                                                                                                     | 12000            | 90000         | -                 | 376   |                                             |                  |        |                     |         |                    |                               |

| F127R87, $n_e=1400$ 1/min                                                                                                                                                   |                  |               |                   |     | 12000 Nm         |        |                     |         |                    |                               |                    |         |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------|---------------|-------------------|-----|------------------|--------|---------------------|---------|--------------------|-------------------------------|--------------------|---------|
| $n_a$<br>rpm                                                                                                                                                                | $M_{amax}$<br>Nm | $F_{Ra}$<br>N | $\Phi_{(R)}$<br>° | $i$ | DRN80M<br>DRN90S | DRN90L | DRN100LS<br>DRN100L | DRN112M | DRN132S<br>DRN132M | DRN132L<br>DRN160M<br>DRN160L | DRN180M<br>DRN180L | DRN200L |
|  3  2 |                  |               |                   |     |                  |        |                     |         |                    |                               |                    |         |
| 2.9                                                                                                                                                                         | 12000            | 90000         | -                 | 483 |                  |        |                     |         |                    |                               |                    |         |
| 3.3                                                                                                                                                                         | 12000            | 90000         | -                 | 418 |                  |        |                     |         |                    |                               |                    |         |
| 3.7                                                                                                                                                                         | 12000            | 90000         | -                 | 374 |                  |        |                     |         |                    |                               |                    |         |
| 4.5                                                                                                                                                                         | 12000            | 90000         | -                 | 312 |                  |        |                     |         |                    |                               |                    |         |
| 4.8                                                                                                                                                                         | 12000            | 90000         | -                 | 293 |                  |        |                     |         |                    |                               |                    |         |
| 5.4                                                                                                                                                                         | 12000            | 90000         | -                 | 259 |                  |        |                     |         |                    |                               |                    |         |
| 6.3                                                                                                                                                                         | 12000            | 90000         | -                 | 223 |                  |        |                     |         |                    |                               |                    |         |
| 7.1                                                                                                                                                                         | 12000            | 90000         | -                 | 198 |                  |        |                     |         |                    |                               |                    |         |
| 8.4                                                                                                                                                                         | 12000            | 90000         | -                 | 166 |                  |        |                     |         |                    |                               |                    |         |

| F157, $n_e=1400$ 1/min                                                                |                  |               |                   |         | 18000 Nm                      |                    |                               |                               |                    |                    |
|---------------------------------------------------------------------------------------|------------------|---------------|-------------------|---------|-------------------------------|--------------------|-------------------------------|-------------------------------|--------------------|--------------------|
| $n_a$<br>rpm                                                                          | $M_{amax}$<br>Nm | $F_{Ra}$<br>N | $\Phi_{(R)}$<br>° | $i$     | DRN132L<br>DRN160M<br>DRN160L | DRN180M<br>DRN180L | DRN200L<br>DRN225S<br>DRN225M | DRN250M<br>DRN280S<br>DRN280M | DRN315S<br>DRN315M | DRN315L<br>DRN315H |
|  3 |                  |               |                   |         |                               |                    |                               |                               |                    |                    |
| 5.2                                                                                   | 18000            | 100300        | 4.5               | 267.43  |                               |                    |                               |                               |                    |                    |
| 6.4                                                                                   | 18000            | 100300        | 4.5               | 217.62* |                               |                    |                               |                               |                    |                    |
| 7.9                                                                                   | 18000            | 100300        | 4.5               | 178.20* |                               |                    |                               |                               |                    |                    |
| 8.6                                                                                   | 18000            | 100300        | 4.5               | 162.96  |                               |                    |                               |                               |                    |                    |
| 9.9                                                                                   | 18000            | 100300        | 4.5               | 141.80* |                               |                    |                               |                               |                    |                    |
| 11                                                                                    | 18000            | 100300        | 4.5               | 125.14  |                               |                    |                               |                               |                    |                    |
| 13                                                                                    | 18000            | 100300        | 4.5               | 108.49  |                               |                    |                               |                               |                    |                    |


| F157, $n_e=1400$ 1/min                                                              |                  |               |                   |        |                               |                    |                               |                               |                    | 18000 Nm           |
|-------------------------------------------------------------------------------------|------------------|---------------|-------------------|--------|-------------------------------|--------------------|-------------------------------|-------------------------------|--------------------|--------------------|
| $n_a$<br>rpm                                                                        | $M_{amax}$<br>Nm | $F_{Ra}$<br>N | $\Phi_{(R)}$<br>° | $i$    | DRN132L<br>DRN160M<br>DRN160L | DRN180M<br>DRN180L | DRN200L<br>DRN225S<br>DRN225M | DRN250M<br>DRN280S<br>DRN280M | DRN315S<br>DRN315M | DRN315L<br>DRN315H |
| 15                                                                                  | 18000            | 100300        | 4.5               | 96.53* |                               |                    |                               |                               |                    |                    |
| 16                                                                                  | 18000            | 95800         | 4.8               | 85.80* |                               |                    |                               |                               |                    |                    |
| 18                                                                                  | 18000            | 92300         | 4.8               | 78.46  |                               |                    |                               |                               |                    |                    |
| 21                                                                                  | 18000            | 87000         | 4.8               | 68.28* |                               |                    |                               |                               |                    |                    |
| 23                                                                                  | 18000            | 82500         | 4.8               | 60.25  |                               |                    |                               |                               |                    |                    |
| 27                                                                                  | 18000            | 77500         | 4.8               | 52.24  |                               |                    |                               |                               |                    |                    |
| 30                                                                                  | 18000            | 73600         | 4.8               | 46.48* |                               |                    |                               |                               |                    |                    |
| 35                                                                                  | 18000            | 68900         | 4.9               | 40.06  |                               |                    |                               |                               |                    |                    |
| 43                                                                                  | 18000            | 62500         | 4.9               | 32.55  |                               |                    |                               |                               |                    |                    |
| 51                                                                                  | 18000            | 57800         | 4.9               | 27.60  |                               |                    |                               |                               |                    |                    |
|  2 |                  |               |                   |        |                               |                    |                               |                               |                    |                    |
| 26                                                                                  | 8000             | 98300         | 4.3               | 53.55  |                               |                    |                               |                               |                    |                    |
| 32                                                                                  | 10000            | 87800         | 4.3               | 43.94* |                               |                    |                               |                               |                    |                    |
| 39                                                                                  | 11000            | 79300         | 4.4               | 35.75* |                               |                    |                               |                               |                    |                    |
| 49                                                                                  | 17000            | 60800         | 4.4               | 28.60* |                               |                    |                               |                               |                    |                    |
| 55                                                                                  | 15000            | 61500         | 4.4               | 25.43  |                               |                    |                               |                               |                    |                    |
| 63                                                                                  | 18000            | 51800         | 4.4               | 22.16  |                               |                    |                               |                               |                    |                    |
| 71                                                                                  | 17000            | 50900         | 4.4               | 19.77  |                               |                    |                               |                               |                    |                    |
| 83                                                                                  | 18000            | 44900         | 4.5               | 16.85  |                               |                    |                               |                               |                    |                    |
| 100                                                                                 | 17000            | 42500         | 4.6               | 13.96  |                               |                    |                               |                               |                    |                    |
| 117                                                                                 | 16000            | 40900         | 4.6               | 11.92  |                               |                    |                               |                               |                    |                    |


| F157R97, n <sub>e</sub> =1400 1/min |                         |                      |                       |        |        |                  |        |                     |         | 18000 Nm           |                               |                    |                    |
|-------------------------------------|-------------------------|----------------------|-----------------------|--------|--------|------------------|--------|---------------------|---------|--------------------|-------------------------------|--------------------|--------------------|
| n <sub>a</sub><br>rpm               | M <sub>amax</sub><br>Nm | F <sub>Ra</sub><br>N | Φ <sub>(R)</sub><br>° | i      | DRS71M | DRN80M<br>DRN90S | DRN90L | DRN100LS<br>DRN100L | DRN112M | DRN132S<br>DRN132M | DRN132L<br>DRN160M<br>DRN160L | DRN180M<br>DRN180L | DRN200L<br>DRN225S |
| 3 3                                 |                         |                      |                       |        |        |                  |        |                     |         |                    |                               |                    |                    |
| 0.04                                | 18000                   | 100300               | -                     | 31434  |        |                  |        |                     |         |                    |                               |                    |                    |
| 0.05                                | 18000                   | 100300               | -                     | 26173  |        |                  |        |                     |         |                    |                               |                    |                    |
| 0.06                                | 18000                   | 100300               | -                     | 23464  |        |                  |        |                     |         |                    |                               |                    |                    |
| 0.07                                | 18000                   | 100300               | -                     | 20212  |        |                  |        |                     |         |                    |                               |                    |                    |
| 0.08                                | 18000                   | 100300               | -                     | 17984* |        |                  |        |                     |         |                    |                               |                    |                    |
| 0.09                                | 18000                   | 100300               | -                     | 16358  |        |                  |        |                     |         |                    |                               |                    |                    |
| 0.10                                | 18000                   | 100300               | -                     | 13751  |        |                  |        |                     |         |                    |                               |                    |                    |
| 0.11                                | 18000                   | 100300               | -                     | 12235  |        |                  |        |                     |         |                    |                               |                    |                    |
| 0.14                                | 18000                   | 100300               | -                     | 10033  |        |                  |        |                     |         |                    |                               |                    |                    |
| 0.16                                | 18000                   | 100300               | -                     | 9021   |        |                  |        |                     |         |                    |                               |                    |                    |
| 0.17                                | 18000                   | 100300               | -                     | 8026   |        |                  |        |                     |         |                    |                               |                    |                    |
| 0.20                                | 18000                   | 100300               | -                     | 7075   |        |                  |        |                     |         |                    |                               |                    |                    |
| 0.22                                | 18000                   | 100300               | -                     | 6295   |        |                  |        |                     |         |                    |                               |                    |                    |
| 0.26                                | 18000                   | 100300               | -                     | 5404   |        |                  |        |                     |         |                    |                               |                    |                    |
| 0.29                                | 18000                   | 100300               | -                     | 4831   |        |                  |        |                     |         |                    |                               |                    |                    |
| 0.34                                | 18000                   | 100300               | -                     | 4130*  |        |                  |        |                     |         |                    |                               |                    |                    |
| 0.39                                | 18000                   | 100300               | -                     | 3607   |        |                  |        |                     |         |                    |                               |                    |                    |
| 0.44                                | 18000                   | 100300               | -                     | 3210   |        |                  |        |                     |         |                    |                               |                    |                    |
| 0.50                                | 18000                   | 100300               | -                     | 2780   |        |                  |        |                     |         |                    |                               |                    |                    |
| 0.97                                | 18000                   | 100300               | -                     | 1441   |        |                  |        |                     |         |                    |                               |                    |                    |
| 3 2                                 |                         |                      |                       |        |        |                  |        |                     |         |                    |                               |                    |                    |
| 0.58                                | 18000                   | 100300               | -                     | 2427   |        |                  |        |                     |         |                    |                               |                    |                    |
| 0.64                                | 18000                   | 100300               | -                     | 2185   |        |                  |        |                     |         |                    |                               |                    |                    |




| F157R97, n <sub>e</sub> =1400 1/min |                         |                      |                        |       |        | 18000 Nm         |        |                     |         |                    |                               |                    |                    |
|-------------------------------------|-------------------------|----------------------|------------------------|-------|--------|------------------|--------|---------------------|---------|--------------------|-------------------------------|--------------------|--------------------|
| n <sub>a</sub><br>rpm               | M <sub>amax</sub><br>Nm | F <sub>Ra</sub><br>N | Φ <sub>(/R)</sub><br>° | i     | DRS71M | DRN80M<br>DRN90S | DRN90L | DRN100LS<br>DRN100L | DRN112M | DRN132S<br>DRN132M | DRN132L<br>DRN160M<br>DRN160L | DRN180M<br>DRN180L | DRN200L<br>DRN225S |
| 0.72                                | 18000                   | 100300               | -                      | 1944* |        |                  |        |                     |         |                    |                               |                    |                    |
| 0.84                                | 18000                   | 100300               | -                      | 1674  |        |                  |        |                     |         |                    |                               |                    |                    |
| 1.1                                 | 18000                   | 100300               | -                      | 1308  |        |                  |        |                     |         |                    |                               |                    |                    |
| 1.2                                 | 18000                   | 100300               | -                      | 1169  |        |                  |        |                     |         |                    |                               |                    |                    |
| 1.5                                 | 18000                   | 100300               | -                      | 953   |        |                  |        |                     |         |                    |                               |                    |                    |
| 1.7                                 | 18000                   | 100300               | -                      | 845   |        |                  |        |                     |         |                    |                               |                    |                    |
| 1.8                                 | 18000                   | 100300               | -                      | 764   |        |                  |        |                     |         |                    |                               |                    |                    |
| 2.1                                 | 18000                   | 100300               | -                      | 680   |        |                  |        |                     |         |                    |                               |                    |                    |
| 2.4                                 | 18000                   | 100300               | -                      | 576   |        |                  |        |                     |         |                    |                               |                    |                    |
| 2.8                                 | 18000                   | 100300               | -                      | 503   |        |                  |        |                     |         |                    |                               |                    |                    |
| 3.1                                 | 18000                   | 100300               | -                      | 446   |        |                  |        |                     |         |                    |                               |                    |                    |
| 4.0                                 | 18000                   | 100300               | -                      | 353   |        |                  |        |                     |         |                    |                               |                    |                    |
| 4.6                                 | 18000                   | 100300               | -                      | 302   |        |                  |        |                     |         |                    |                               |                    |                    |
| 5.1                                 | 18000                   | 100300               | -                      | 273   |        |                  |        |                     |         |                    |                               |                    |                    |
| 6.0                                 | 18000                   | 100300               | -                      | 232   |        |                  |        |                     |         |                    |                               |                    |                    |
| 6.9                                 | 18000                   | 100300               | -                      | 202   |        |                  |        |                     |         |                    |                               |                    |                    |
| 7.1                                 | 18000                   | 100300               | -                      | 197   |        |                  |        |                     |         |                    |                               |                    |                    |


## 9.3 Auswahltabellen F..DRN.. in kW

| P <sub>m</sub> = 0.12 kW |                      |       |                                    |                       |                                                                                    |        |    |      |         |                                                                                     |
|--------------------------|----------------------|-------|------------------------------------|-----------------------|------------------------------------------------------------------------------------|--------|----|------|---------|-------------------------------------------------------------------------------------|
| n <sub>a</sub><br>rpm    | M <sub>a</sub><br>Nm | i     | F <sub>Ra</sub> <sup>1)</sup><br>N | SEW<br>f <sub>B</sub> |  |        |    |      | m<br>kg |  |
| 0.06                     | 13900                | 22323 | 86700                              | 0.85                  | FA<br>FAF<br>F<br>FF                                                               | 127R77 | DR | 63S4 | 425     | 456                                                                                 |
| 0.07                     | 11800                | 19048 | 90000                              | 1.00                  |                                                                                    |        |    |      |         |                                                                                     |
| 0.08                     | 10300                | 16656 | 90000                              | 1.15                  |                                                                                    |        |    |      |         |                                                                                     |
| 0.09                     | 9180                 | 14722 | 90000                              | 1.30                  |                                                                                    |        |    |      |         |                                                                                     |
| 0.11                     | 7990                 | 12912 | 90000                              | 1.50                  |                                                                                    |        |    |      |         |                                                                                     |
| 0.12                     | 7040                 | 11656 | 90000                              | 1.70                  |                                                                                    |        |    |      |         |                                                                                     |
| 0.14                     | 6310                 | 10191 | 90000                              | 1.90                  |                                                                                    |        |    |      |         |                                                                                     |
| 0.09                     | 9200                 | 14767 | 45500                              | 0.85                  | FA<br>FAF<br>F<br>FF                                                               | 107R77 | DR | 63S4 | 275     | 456                                                                                 |
| 0.12                     | 7070                 | 11348 | 51400                              | 1.10                  |                                                                                    |        |    |      |         |                                                                                     |
| 0.14                     | 5740                 | 10039 | 54600                              | 1.35                  |                                                                                    |        |    |      |         |                                                                                     |
| 0.16                     | 4670                 | 8548  | 57000                              | 1.65                  |                                                                                    |        |    |      |         |                                                                                     |
| 0.18                     | 4750                 | 7674  | 56800                              | 1.60                  |                                                                                    |        |    |      |         |                                                                                     |
| 0.20                     | 4090                 | 6767  | 58200                              | 1.90                  |                                                                                    |        |    |      |         |                                                                                     |
| 0.23                     | 3460                 | 5954  | 59500                              | 2.2                   |                                                                                    |        |    |      |         |                                                                                     |
| 0.26                     | 2990                 | 5223  | 60400                              | 2.6                   |                                                                                    |        |    |      |         |                                                                                     |
| 0.30                     | 2840                 | 4567  | 60700                              | 2.7                   |                                                                                    |        |    |      |         |                                                                                     |
| 0.39                     | 2120                 | 3521  | 62000                              | 3.6                   |                                                                                    |        |    |      |         |                                                                                     |
| 0.21                     | 4140                 | 6469  | 30400                              | 1.05                  | FA<br>FAF<br>F<br>FF                                                               | 97R57  | DR | 63S4 | 185     | 456                                                                                 |
| 0.25                     | 3820                 | 5615  | 31300                              | 1.15                  |                                                                                    |        |    |      |         |                                                                                     |
| 0.28                     | 3320                 | 4961  | 32500                              | 1.30                  |                                                                                    |        |    |      |         |                                                                                     |
| 0.32                     | 2900                 | 4333  | 33500                              | 1.50                  |                                                                                    |        |    |      |         |                                                                                     |
| 0.35                     | 2690                 | 3906  | 34000                              | 1.60                  | FA<br>FAF<br>F<br>FF                                                               | 97R57  | DR | 63S4 | 180     | 456                                                                                 |
| 0.41                     | 2320                 | 3352  | 34800                              | 1.85                  |                                                                                    |        |    |      |         |                                                                                     |
| 0.47                     | 1910                 | 2907  | 35500                              | 2.2                   |                                                                                    |        |    |      |         |                                                                                     |
| 0.54                     | 1750                 | 2553  | 35800                              | 2.4                   |                                                                                    |        |    |      |         |                                                                                     |
| 0.33                     | 2760                 | 4245  | 23800                              | 1.10                  | FA<br>FAF<br>F<br>FF                                                               | 87R57  | DR | 63S4 | 120     | 456                                                                                 |
| 0.37                     | 2210                 | 3721  | 25800                              | 1.35                  |                                                                                    |        |    |      |         |                                                                                     |
| 0.43                     | 2240                 | 3244  | 25700                              | 1.35                  |                                                                                    |        |    |      |         |                                                                                     |
| 0.48                     | 1990                 | 2881  | 26500                              | 1.50                  |                                                                                    |        |    |      |         |                                                                                     |
| 0.54                     | 1780                 | 2576  | 27100                              | 1.70                  | FA<br>FAF<br>F<br>FF                                                               | 87R57  | DR | 63S4 | 115     | 456                                                                                 |
| 0.63                     | 1510                 | 2199  | 27800                              | 2.00                  |                                                                                    |        |    |      |         |                                                                                     |
| 0.72                     | 1300                 | 1930  | 28300                              | 2.3                   |                                                                                    |        |    |      |         |                                                                                     |
| 0.81                     | 1170                 | 1709  | 28600                              | 2.6                   |                                                                                    |        |    |      |         |                                                                                     |
| 0.92                     | 1030                 | 1493  | 28900                              | 2.9                   |                                                                                    |        |    |      |         |                                                                                     |
| 1.1                      | 820                  | 1300  | 29300                              | 3.7                   |                                                                                    |        |    |      |         |                                                                                     |
| 1.2                      | 745                  | 1148  | 29500                              | 4.0                   |                                                                                    |        |    |      |         |                                                                                     |
| 0.53                     | 1820                 | 2613  | 13000                              | 0.80                  | FA<br>FAF<br>F<br>FF                                                               | 77R37  | DR | 63S4 | 65      | 456                                                                                 |
| 0.60                     | 1570                 | 2284  | 15200                              | 0.95                  |                                                                                    |        |    |      |         |                                                                                     |
| 0.68                     | 1380                 | 2029  | 16400                              | 1.10                  |                                                                                    |        |    |      |         |                                                                                     |
| 0.80                     | 1180                 | 1728  | 17500                              | 1.25                  |                                                                                    |        |    |      |         |                                                                                     |
| 0.89                     | 1090                 | 1544  | 17900                              | 1.40                  | FA<br>FAF<br>F<br>FF                                                               | 77R37  | DR | 63S4 | 65      | 456                                                                                 |
| 1.0                      | 950                  | 1354  | 18500                              | 1.55                  |                                                                                    |        |    |      |         |                                                                                     |
| 1.2                      | 840                  | 1200  | 18800                              | 1.75                  |                                                                                    |        |    |      |         |                                                                                     |
| 1.3                      | 740                  | 1053  | 19100                              | 2.0                   |                                                                                    |        |    |      |         |                                                                                     |
| 1.5                      | 630                  | 910   | 19400                              | 2.4                   |                                                                                    |        |    |      |         |                                                                                     |
| 1.7                      | 525                  | 810   | 19600                              | 2.8                   |                                                                                    |        |    |      |         |                                                                                     |
| 1.9                      | 460                  | 710   | 19800                              | 3.2                   |                                                                                    |        |    |      |         |                                                                                     |
| 0.97                     | 960                  | 1429  | 7070                               | 0.85                  | FA<br>FAF<br>F<br>FF                                                               | 67R37  | DR | 63S4 | 43      | 456                                                                                 |
| 1.1                      | 860                  | 1271  | 9840                               | 0.95                  |                                                                                    |        |    |      |         |                                                                                     |
| 1.2                      | 725                  | 1102  | 11100                              | 1.15                  |                                                                                    |        |    |      |         |                                                                                     |
| 1.4                      | 635                  | 970   | 11700                              | 1.30                  |                                                                                    |        |    |      |         |                                                                                     |
| 1.6                      | 560                  | 858   | 12100                              | 1.45                  |                                                                                    |        |    |      |         |                                                                                     |
| 1.8                      | 490                  | 755   | 12400                              | 1.65                  |                                                                                    |        |    |      |         |                                                                                     |
| 2.2                      | 415                  | 641   | 12700                              | 1.95                  |                                                                                    |        |    |      |         |                                                                                     |
| 2.4                      | 390                  | 572   | 12800                              | 2.1                   |                                                                                    |        |    |      |         |                                                                                     |
| 2.7                      | 330                  | 509   | 13000                              | 2.5                   |                                                                                    |        |    |      |         |                                                                                     |
| 3.2                      | 285                  | 437   | 13000                              | 2.8                   |                                                                                    |        |    |      |         |                                                                                     |

| <b>P<sub>m</sub> = 0.12 kW</b>     |                                   |          |                                                |                                    |                                                                                    |       |    |      |                       |                                                                                     |
|------------------------------------|-----------------------------------|----------|------------------------------------------------|------------------------------------|------------------------------------------------------------------------------------|-------|----|------|-----------------------|-------------------------------------------------------------------------------------|
| <b>n<sub>a</sub></b><br><b>rpm</b> | <b>M<sub>a</sub></b><br><b>Nm</b> | <b>i</b> | <b>F<sub>Ra</sub><sup>1)</sup></b><br><b>N</b> | <b>SEW</b><br><b>f<sub>B</sub></b> |  |       |    |      | <b>m</b><br><b>kg</b> |  |
| 1.6                                | 610                               | 851      | 9100                                           | 1.00                               | FA<br>FAF<br>F<br>FF                                                               | 57R37 | DR | 63S4 | 39                    | 456                                                                                 |
| 1.9                                | 520                               | 738      | 9750                                           | 1.15                               |                                                                                    |       |    |      | 45                    | 456                                                                                 |
| 2.1                                | 455                               | 646      | 10200                                          | 1.30                               |                                                                                    |       |    |      | 39                    | 456                                                                                 |
| 2.5                                | 385                               | 558      | 10600                                          | 1.55                               |                                                                                    |       |    |      | 46                    | 456                                                                                 |
| 2.7                                | 345                               | 506      | 10900                                          | 1.75                               |                                                                                    |       |    |      |                       |                                                                                     |
| 3.0                                | 295                               | 452      | 11100                                          | 2.0                                |                                                                                    |       |    |      |                       |                                                                                     |
| 3.2                                | 310                               | 426      | 11100                                          | 1.95                               | FA<br>FAF<br>F<br>FF                                                               | 57R37 | DR | 63S4 | 38                    | 456                                                                                 |
| 3.6                                | 270                               | 382      | 11300                                          | 2.2                                |                                                                                    |       |    |      | 44                    | 456                                                                                 |
| 4.2                                | 230                               | 330      | 11500                                          | 2.6                                |                                                                                    |       |    |      | 39                    | 456                                                                                 |
| 4.6                                | 210                               | 298      | 11500                                          | 2.8                                |                                                                                    |       |    |      | 45                    | 456                                                                                 |
| 5.3                                | 185                               | 262      | 11500                                          | 3.2                                |                                                                                    |       |    |      |                       |                                                                                     |
| 2.5                                | 385                               | 543      | 6100                                           | 1.05                               | FA<br>FAF<br>F<br>FF                                                               | 47R17 | DR | 63S4 | 24                    | 456                                                                                 |
| 2.9                                | 330                               | 475      | 6740                                           | 1.20                               |                                                                                    |       |    |      | 26                    | 456                                                                                 |
| 3.3                                | 290                               | 419      | 7150                                           | 1.40                               |                                                                                    |       |    |      | 25                    | 456                                                                                 |
|                                    |                                   |          |                                                |                                    |                                                                                    |       |    |      | 28                    | 456                                                                                 |
| 2.6                                | 380                               | 524      | 6190                                           | 1.05                               | FA<br>FAF<br>F<br>FF                                                               | 47R17 | DR | 63S4 | 23                    | 456                                                                                 |
| 2.8                                | 350                               | 489      | 6530                                           | 1.15                               |                                                                                    |       |    |      | 26                    | 456                                                                                 |
| 3.2                                | 300                               | 427      | 7020                                           | 1.30                               |                                                                                    |       |    |      | 24                    | 456                                                                                 |
| 3.6                                | 265                               | 381      | 7310                                           | 1.50                               |                                                                                    |       |    |      | 27                    | 456                                                                                 |
| 4.1                                | 235                               | 334      | 7550                                           | 1.70                               |                                                                                    |       |    |      |                       |                                                                                     |
| 4.7                                | 205                               | 295      | 7740                                           | 1.95                               |                                                                                    |       |    |      |                       |                                                                                     |
| 5.4                                | 172                               | 253      | 7910                                           | 2.3                                |                                                                                    |       |    |      |                       |                                                                                     |
| 4.3                                | 215                               | 322      | 3990                                           | 0.90                               | FA<br>FAF<br>F<br>FF                                                               | 37R17 | DR | 63S4 | 19                    | 456                                                                                 |
| 5.0                                | 192                               | 278      | 4400                                           | 1.05                               |                                                                                    |       |    |      | 20                    | 456                                                                                 |
| 5.7                                | 162                               | 242      | 4750                                           | 1.25                               |                                                                                    |       |    |      | 19                    | 456                                                                                 |
| 6.2                                | 156                               | 221      | 4820                                           | 1.30                               |                                                                                    |       |    |      | 21                    | 456                                                                                 |
| 4.2                                | 235                               | 326      | 3710                                           | 0.85                               | FA<br>FAF<br>F<br>FF                                                               | 37R17 | DR | 63S4 | 19                    | 456                                                                                 |
| 4.8                                | 200                               | 285      | 4250                                           | 1.00                               |                                                                                    |       |    |      | 20                    | 456                                                                                 |
| 5.5                                | 177                               | 250      | 4590                                           | 1.15                               |                                                                                    |       |    |      | 19                    | 456                                                                                 |
| 6.3                                | 156                               | 219      | 4820                                           | 1.30                               |                                                                                    |       |    |      | 21                    | 456                                                                                 |
| 7.4                                | 132                               | 186      | 5040                                           | 1.50                               |                                                                                    |       |    |      |                       |                                                                                     |
| 8.3                                | 118                               | 167      | 5140                                           | 1.70                               |                                                                                    |       |    |      |                       |                                                                                     |
| 6.2                                | 155                               | 221      | 4500                                           | 0.85                               | FA<br>FAF<br>F<br>FF                                                               | 27R17 | DR | 63S4 | 13                    | 456                                                                                 |
| 8.0                                | 119                               | 172      | 4500                                           | 1.10                               |                                                                                    |       |    |      | 14                    | 456                                                                                 |
| 9.0                                | 104                               | 153      | 4500                                           | 1.25                               |                                                                                    |       |    |      | 13                    | 456                                                                                 |
| 11                                 | 87                                | 130      | 4500                                           | 1.50                               |                                                                                    |       |    |      | 14                    | 456                                                                                 |
| 6.5                                | 150                               | 211      | 4500                                           | 0.85                               | FA<br>FAF<br>F<br>FF                                                               | 27R17 | DR | 63S4 | 13                    | 456                                                                                 |
| 7.4                                | 131                               | 186      | 4500                                           | 1.00                               |                                                                                    |       |    |      | 13                    | 456                                                                                 |
| 9.7                                | 102                               | 142      | 4500                                           | 1.25                               |                                                                                    |       |    |      | 13                    | 456                                                                                 |
| 11                                 | 88                                | 124      | 4500                                           | 1.45                               |                                                                                    |       |    |      | 14                    | 456                                                                                 |
| 13                                 | 77                                | 109      | 4500                                           | 1.70                               |                                                                                    |       |    |      |                       |                                                                                     |
| 14                                 | 67                                | 96       | 4500                                           | 1.95                               |                                                                                    |       |    |      |                       |                                                                                     |
| 3.9                                | 290                               | 228.99   | 13000                                          | 2.8                                | FA<br>FAF<br>F<br>FF                                                               | 67    | DR | 63M6 | 32                    | 416                                                                                 |
| 4.6                                | 245                               | 195.39   | 13000                                          | 3.3                                |                                                                                    |       |    |      | 38                    | 415                                                                                 |
| 5.3                                | 215                               | 170.85   | 13000                                          | 3.8                                |                                                                                    |       |    |      | 35                    | 414                                                                                 |
| 5.6                                | 205                               | 162.31   | 13000                                          | 4.0                                |                                                                                    |       |    |      | 41                    | 415                                                                                 |
| 6.3                                | 181                               | 142.40   | 13000                                          | 4.5                                |                                                                                    |       |    |      |                       |                                                                                     |
| 4.5                                | 250                               | 199.70   | 11400                                          | 2.4                                | FA<br>FAF<br>F<br>FF                                                               | 57    | DR | 63M6 | 28                    | 410                                                                                 |
| 4.9                                | 230                               | 183.60   | 11500                                          | 2.6                                |                                                                                    |       |    |      | 34                    | 409                                                                                 |
| 5.7                                | 200                               | 157.09   | 11500                                          | 3.0                                |                                                                                    |       |    |      | 28                    | 408                                                                                 |
| 6.6                                | 173                               | 136.16   | 11500                                          | 3.5                                |                                                                                    |       |    |      | 35                    | 409                                                                                 |
| 7.1                                | 162                               | 127.27   | 11500                                          | 3.7                                |                                                                                    |       |    |      |                       |                                                                                     |
| 6.9                                | 166                               | 199.70   | 11500                                          | 3.6                                | FA<br>FAF<br>F<br>FF                                                               | 57    | DR | 63S4 | 28                    | 410                                                                                 |
| 7.5                                | 152                               | 183.60   | 11500                                          | 3.9                                |                                                                                    |       |    |      | 34                    | 409                                                                                 |
| 8.8                                | 130                               | 157.09   | 11500                                          | 4.6                                |                                                                                    |       |    |      | 28                    | 408                                                                                 |
| 10                                 | 113                               | 136.16   | 11500                                          | 5.3                                |                                                                                    |       |    |      | 35                    | 409                                                                                 |
|                                    |                                   |          |                                                |                                    |                                                                                    |       |    |      |                       |                                                                                     |
| 4.7                                | 240                               | 190.76   | 7510                                           | 1.65                               | FA<br>FAF<br>F<br>FF                                                               | 47    | DR | 63M6 | 21                    | 404                                                                                 |
| 5.1                                | 220                               | 175.38   | 7640                                           | 1.80                               |                                                                                    |       |    |      | 24                    | 403                                                                                 |
| 6.0                                | 191                               | 150.06   | 7820                                           | 2.1                                |                                                                                    |       |    |      | 22                    | 402                                                                                 |
| 6.9                                | 166                               | 130.07   | 7940                                           | 2.4                                |                                                                                    |       |    |      | 25                    | 403                                                                                 |
| 7.4                                | 155                               | 121.57   | 7990                                           | 2.6                                |                                                                                    |       |    |      |                       |                                                                                     |
| 8.6                                | 134                               | 105.09   | 8060                                           | 3.0                                |                                                                                    |       |    |      |                       |                                                                                     |
| 10                                 | 114                               | 89.29    | 8130                                           | 3.5                                |                                                                                    |       |    |      |                       |                                                                                     |
| 11                                 | 102                               | 79.72    | 8160                                           | 3.9                                |                                                                                    |       |    |      |                       |                                                                                     |


21933170/DE – 11/2015


| <b>P<sub>m</sub> = 0.12 kW</b>     |                                   |          |                                                |                                    |                                                                                    |    |    |      |                       |                                                                                     |
|------------------------------------|-----------------------------------|----------|------------------------------------------------|------------------------------------|------------------------------------------------------------------------------------|----|----|------|-----------------------|-------------------------------------------------------------------------------------|
| <b>n<sub>a</sub></b><br><b>rpm</b> | <b>M<sub>a</sub></b><br><b>Nm</b> | <b>i</b> | <b>F<sub>Ra</sub><sup>1)</sup></b><br><b>N</b> | <b>SEW</b><br><b>f<sub>B</sub></b> |  |    |    |      | <b>m</b><br><b>kg</b> |  |
| 7.2                                | 158                               | 190.76   | 7970                                           | 2.5                                | FA                                                                                 | 47 | DR | 63S4 | 21                    | 404                                                                                 |
| 7.9                                | 146                               | 175.38   | 8020                                           | 2.8                                | FAF                                                                                | 47 | DR | 63S4 | 24                    | 403                                                                                 |
| 9.2                                | 125                               | 150.06   | 8100                                           | 3.2                                | F                                                                                  | 47 | DR | 63S4 | 22                    | 402                                                                                 |
| 11                                 | 108                               | 130.07   | 8150                                           | 3.7                                | FF                                                                                 | 47 | DR | 63S4 | 25                    | 403                                                                                 |
| 7.0                                | 164                               | 128.51   | 4740                                           | 1.20                               | FA                                                                                 | 37 | DR | 63M6 | 16                    | 398                                                                                 |
| 7.6                                | 150                               | 117.88   | 4880                                           | 1.35                               | FAF                                                                                | 37 | DR | 63M6 | 18                    | 397                                                                                 |
| 9.0                                | 128                               | 100.36   | 5070                                           | 1.55                               | F                                                                                  | 37 | DR | 63M6 | 16                    | 396                                                                                 |
| 10                                 | 110                               | 86.53    | 5190                                           | 1.80                               | FF                                                                                 | 37 | DR | 63M6 | 18                    | 397                                                                                 |
| 11                                 | 103                               | 80.65    | 5240                                           | 1.95                               |                                                                                    |    |    |      |                       |                                                                                     |
| 11                                 | 107                               | 128.51   | 5220                                           | 1.85                               | FA                                                                                 | 37 | DR | 63S4 | 16                    | 398                                                                                 |
| 12                                 | 98                                | 117.88   | 5270                                           | 2.0                                | FAF                                                                                | 37 | DR | 63S4 | 18                    | 397                                                                                 |
| 14                                 | 83                                | 100.36   | 5340                                           | 2.4                                | F                                                                                  | 37 | DR | 63S4 | 16                    | 396                                                                                 |
| 16                                 | 72                                | 86.53    | 5400                                           | 2.8                                | FF                                                                                 | 37 | DR | 63S4 | 18                    | 397                                                                                 |
| 17                                 | 67                                | 80.65    | 5410                                           | 3.0                                |                                                                                    |    |    |      |                       |                                                                                     |
| 8.2                                | 140                               | 109.90   | 4500                                           | 0.95                               | FA                                                                                 | 27 | DR | 63M6 | 9.9                   | 393                                                                                 |
| 9.5                                | 121                               | 94.76    | 4500                                           | 1.10                               | FAF                                                                                | 27 | DR | 63M6 | 11                    | 392                                                                                 |
| 10                                 | 112                               | 88.32    | 4500                                           | 1.15                               | F                                                                                  | 27 | DR | 63M6 | 10                    | 391                                                                                 |
| 12                                 | 98                                | 77.21    | 4500                                           | 1.30                               | FF                                                                                 | 27 | DR | 63M6 | 11                    | 392                                                                                 |
| 9.8                                | 117                               | 140.74   | 4500                                           | 1.10                               |                                                                                    |    |    |      |                       |                                                                                     |
| 11                                 | 107                               | 129.09   | 4500                                           | 1.20                               |                                                                                    |    |    |      |                       |                                                                                     |
| 13                                 | 91                                | 109.90   | 4500                                           | 1.40                               |                                                                                    |    |    |      |                       |                                                                                     |
| 15                                 | 79                                | 94.76    | 4500                                           | 1.65                               |                                                                                    |    |    |      |                       |                                                                                     |
| 16                                 | 73                                | 88.32    | 4500                                           | 1.75                               |                                                                                    |    |    |      |                       |                                                                                     |
| 18                                 | 64                                | 77.21    | 4500                                           | 2.0                                | FA                                                                                 | 27 | DR | 63S4 | 9.9                   | 393                                                                                 |
| 19                                 | 60                                | 72.37    | 4500                                           | 2.2                                | FAF                                                                                | 27 | DR | 63S4 | 11                    | 392                                                                                 |
| 22                                 | 53                                | 63.86    | 4500                                           | 2.4                                | F                                                                                  | 27 | DR | 63S4 | 10                    | 391                                                                                 |
| 24                                 | 47                                | 56.62    | 4500                                           | 2.8                                | FF                                                                                 | 27 | DR | 63S4 | 11                    | 392                                                                                 |
| 28                                 | 42                                | 50.19    | 4500                                           | 3.1                                |                                                                                    |    |    |      |                       |                                                                                     |
| 30                                 | 39                                | 46.78    | 4500                                           | 3.4                                |                                                                                    |    |    |      |                       |                                                                                     |
| 34                                 | 34                                | 40.89    | 4500                                           | 3.8                                |                                                                                    |    |    |      |                       |                                                                                     |
| 36                                 | 32                                | 38.33    | 4430                                           | 4.1                                |                                                                                    |    |    |      |                       |                                                                                     |
| 41                                 | 28                                | 33.83    | 4270                                           | 4.6                                |                                                                                    |    |    |      |                       |                                                                                     |
| 47                                 | 24                                | 29.56    | 4100                                           | 5.3                                |                                                                                    |    |    |      |                       |                                                                                     |
| 51                                 | 23                                | 27.18    | 4000                                           | 5.8                                |                                                                                    |    |    |      |                       |                                                                                     |
| 59                                 | 19                                | 23.25    | 3820                                           | 6.7                                |                                                                                    |    |    |      |                       |                                                                                     |
| 68                                 | 17                                | 20.15    | 3650                                           | 7.8                                |                                                                                    |    |    |      |                       |                                                                                     |
| 73                                 | 16                                | 18.84    | 3580                                           | 8.3                                |                                                                                    |    |    |      |                       |                                                                                     |
| 85                                 | 14                                | 16.28    | 3420                                           | 9.6                                |                                                                                    |    |    |      |                       |                                                                                     |
| 100                                | 12                                | 13.84    | 3250                                           | 11                                 |                                                                                    |    |    |      |                       |                                                                                     |
| 112                                | 10                                | 12.35    | 3140                                           | 13                                 | FA                                                                                 | 27 | DR | 63S4 | 9.6                   | 393                                                                                 |
| 131                                | 8.8                               | 10.55    | 2990                                           | 15                                 | FAF                                                                                | 27 | DR | 63S4 | 10                    | 392                                                                                 |
| 140                                | 8.2                               | 9.88     | 2920                                           | 16                                 | F                                                                                  | 27 | DR | 63S4 | 10                    | 391                                                                                 |
| 147                                | 7.8                               | 9.40     | 2870                                           | 17                                 | FF                                                                                 | 27 | DR | 63S4 | 11                    | 392                                                                                 |
| 170                                | 6.7                               | 8.13     | 2740                                           | 18                                 |                                                                                    |    |    |      |                       |                                                                                     |
| 200                                | 5.7                               | 6.91     | 2600                                           | 20                                 |                                                                                    |    |    |      |                       |                                                                                     |
| 224                                | 5.1                               | 6.17     | 2510                                           | 21                                 |                                                                                    |    |    |      |                       |                                                                                     |
| 262                                | 4.4                               | 5.27     | 2390                                           | 23                                 |                                                                                    |    |    |      |                       |                                                                                     |
| 280                                | 4.1                               | 4.93     | 2340                                           | 23                                 |                                                                                    |    |    |      |                       |                                                                                     |
| 332                                | 3.5                               | 4.16     | 2210                                           | 25                                 |                                                                                    |    |    |      |                       |                                                                                     |


| <b>P<sub>m</sub> = 0.18 kW</b>     |                                   |          |                                                |                                    |                                                                                      |        |    |      |                       |                                                                                       |
|------------------------------------|-----------------------------------|----------|------------------------------------------------|------------------------------------|--------------------------------------------------------------------------------------|--------|----|------|-----------------------|---------------------------------------------------------------------------------------|
| <b>n<sub>a</sub></b><br><b>rpm</b> | <b>M<sub>a</sub></b><br><b>Nm</b> | <b>i</b> | <b>F<sub>Ra</sub><sup>1)</sup></b><br><b>N</b> | <b>SEW</b><br><b>f<sub>B</sub></b> |  |        |    |      | <b>m</b><br><b>kg</b> |  |
| 0.10                               | 13600                             | 12912    | 87200                                          | 0.90                               |                                                                                      |        |    |      |                       |                                                                                       |
| 0.11                               | 12100                             | 11656    | 90000                                          | 1.00                               | FA                                                                                   | 127R77 | DR | 63M4 | 425                   | 456                                                                                   |
| 0.13                               | 10700                             | 10191    | 90000                                          | 1.10                               | FAF                                                                                  | 127R77 | DR | 63M4 | 465                   | 456                                                                                   |
| 0.15                               | 8940                              | 8831     | 90000                                          | 1.35                               | F                                                                                    | 127R77 | DR | 63M4 | 460                   | 456                                                                                   |
| 0.17                               | 7740                              | 7643     | 90000                                          | 1.55                               | FF                                                                                   | 127R77 | DR | 63M4 | 510                   | 456                                                                                   |
| 0.20                               | 7130                              | 6715     | 90000                                          | 1.70                               |                                                                                      |        |    |      |                       |                                                                                       |

| P <sub>m</sub> = 0.18 kW |                      |      |                                    |                       |                                                                                    |        |    |      |         |                                                                                     |
|--------------------------|----------------------|------|------------------------------------|-----------------------|------------------------------------------------------------------------------------|--------|----|------|---------|-------------------------------------------------------------------------------------|
| n <sub>a</sub><br>rpm    | M <sub>a</sub><br>Nm | i    | F <sub>Ra</sub> <sup>1)</sup><br>N | SEW<br>f <sub>B</sub> |  |        |    |      | m<br>kg |  |
| 0.15                     | 8440                 | 8548 | 47700                              | 0.90                  | FA<br>FAF<br>F<br>FF                                                               | 107R77 | DR | 63M4 | 275     | 456                                                                                 |
| 0.17                     | 8130                 | 7674 | 48600                              | 0.95                  |                                                                                    |        |    |      |         |                                                                                     |
| 0.20                     | 7070                 | 6767 | 51400                              | 1.10                  |                                                                                    |        |    |      |         |                                                                                     |
| 0.22                     | 6080                 | 5954 | 53800                              | 1.25                  |                                                                                    |        |    |      |         |                                                                                     |
| 0.25                     | 5290                 | 5223 | 55700                              | 1.45                  |                                                                                    |        |    |      |         |                                                                                     |
| 0.29                     | 4850                 | 4567 | 56600                              | 1.60                  |                                                                                    |        |    |      |         |                                                                                     |
| 0.37                     | 3670                 | 3521 | 59100                              | 2.1                   | FA<br>FAF<br>F<br>FF                                                               | 107R77 | DR | 63M4 | 275     | 456                                                                                 |
| 0.43                     | 3250                 | 3037 | 59900                              | 2.4                   |                                                                                    |        |    |      |         |                                                                                     |
| 0.48                     | 2950                 | 2756 | 60500                              | 2.6                   |                                                                                    |        |    |      |         |                                                                                     |
| 0.56                     | 2540                 | 2369 | 61200                              | 3.0                   |                                                                                    |        |    |      |         |                                                                                     |
| 0.64                     | 2210                 | 2068 | 61800                              | 3.5                   |                                                                                    |        |    |      |         |                                                                                     |
| 0.30                     | 4800                 | 4333 | 22800                              | 0.90                  |                                                                                    |        |    |      |         |                                                                                     |
| 0.34                     | 4420                 | 3906 | 29500                              | 0.95                  |                                                                                    |        |    |      |         |                                                                                     |
| 0.39                     | 3800                 | 3352 | 31300                              | 1.15                  |                                                                                    |        |    |      |         |                                                                                     |
| 0.45                     | 3210                 | 2907 | 32800                              | 1.35                  |                                                                                    |        |    |      |         |                                                                                     |
| 0.52                     | 2890                 | 2553 | 33600                              | 1.50                  |                                                                                    |        |    |      |         |                                                                                     |
| 0.59                     | 2540                 | 2245 | 34300                              | 1.70                  |                                                                                    |        |    |      |         |                                                                                     |
| 0.67                     | 2210                 | 1970 | 35000                              | 1.95                  | FA<br>FAF<br>F<br>FF                                                               | 97R57  | DR | 63M4 | 180     | 456                                                                                 |
| 0.77                     | 1950                 | 1722 | 35500                              | 2.2                   |                                                                                    |        |    |      |         |                                                                                     |
| 0.86                     | 1730                 | 1527 | 35900                              | 2.5                   |                                                                                    |        |    |      |         |                                                                                     |
| 0.99                     | 1420                 | 1327 | 36400                              | 3.0                   |                                                                                    |        |    |      |         |                                                                                     |
| 1.1                      | 1330                 | 1171 | 36500                              | 3.2                   |                                                                                    |        |    |      |         |                                                                                     |
| 0.51                     | 2920                 | 2576 | 22300                              | 1.00                  |                                                                                    |        |    |      |         |                                                                                     |
| 0.60                     | 2490                 | 2199 | 24800                              | 1.20                  |                                                                                    |        |    |      |         |                                                                                     |
| 0.68                     | 2160                 | 1930 | 25900                              | 1.40                  |                                                                                    |        |    |      |         |                                                                                     |
| 0.77                     | 1930                 | 1709 | 26600                              | 1.55                  |                                                                                    |        |    |      |         |                                                                                     |
| 0.88                     | 1690                 | 1493 | 27300                              | 1.75                  |                                                                                    |        |    |      |         |                                                                                     |
| 1.0                      | 1390                 | 1300 | 28100                              | 2.1                   |                                                                                    |        |    |      |         |                                                                                     |
| 1.2                      | 1250                 | 1148 | 28400                              | 2.4                   |                                                                                    |        |    |      |         |                                                                                     |
| 1.3                      | 1080                 | 1010 | 28800                              | 2.8                   |                                                                                    |        |    |      |         |                                                                                     |
| 1.5                      | 970                  | 887  | 29000                              | 3.1                   | FA<br>FAF<br>F<br>FF                                                               | 77R37  | DR | 63M4 | 65      | 456                                                                                 |
| 1.7                      | 830                  | 780  | 29300                              | 3.6                   |                                                                                    |        |    |      |         |                                                                                     |
| 0.86                     | 1770                 | 1544 | 13500                              | 0.85                  |                                                                                    |        |    |      |         |                                                                                     |
| 0.98                     | 1550                 | 1354 | 15300                              | 0.95                  |                                                                                    |        |    |      |         |                                                                                     |
| 1.1                      | 1380                 | 1200 | 16500                              | 1.10                  |                                                                                    |        |    |      |         |                                                                                     |
| 1.2                      | 1210                 | 1053 | 17400                              | 1.25                  |                                                                                    |        |    |      |         |                                                                                     |
| 1.4                      | 1030                 | 910  | 18200                              | 1.45                  |                                                                                    |        |    |      |         |                                                                                     |
| 1.6                      | 880                  | 810  | 18700                              | 1.70                  |                                                                                    |        |    |      |         |                                                                                     |
| 1.9                      | 780                  | 710  | 19000                              | 1.90                  | FA<br>FAF<br>F<br>FF                                                               | 67R37  | DR | 63M4 | 43      | 456                                                                                 |
| 2.2                      | 690                  | 615  | 19300                              | 2.2                   |                                                                                    |        |    |      |         |                                                                                     |
| 1.5                      | 940                  | 858  | 8660                               | 0.85                  |                                                                                    |        |    |      |         |                                                                                     |
| 1.8                      | 820                  | 755  | 10200                              | 1.00                  |                                                                                    |        |    |      |         |                                                                                     |
| 2.1                      | 700                  | 641  | 11200                              | 1.15                  |                                                                                    |        |    |      |         |                                                                                     |
| 2.3                      | 645                  | 572  | 11600                              | 1.25                  |                                                                                    |        |    |      |         |                                                                                     |
| 2.6                      | 555                  | 509  | 12100                              | 1.45                  |                                                                                    |        |    |      |         |                                                                                     |
| 3.0                      | 480                  | 437  | 12500                              | 1.70                  |                                                                                    |        |    |      |         |                                                                                     |
| 3.4                      | 430                  | 384  | 12700                              | 1.90                  | FA<br>FAF<br>F<br>FF                                                               | 67R37  | DR | 63M4 | 42      | 456                                                                                 |
| 2.6                      | 575                  | 500  | 12000                              | 1.40                  |                                                                                    |        |    |      |         |                                                                                     |
| 2.9                      | 525                  | 454  | 12300                              | 1.55                  |                                                                                    |        |    |      |         |                                                                                     |
| 3.4                      | 450                  | 392  | 12600                              | 1.80                  |                                                                                    |        |    |      |         |                                                                                     |
| 4.0                      | 380                  | 333  | 12900                              | 2.2                   |                                                                                    |        |    |      |         |                                                                                     |
| 4.4                      | 335                  | 297  | 13000                              | 2.4                   |                                                                                    |        |    |      |         |                                                                                     |
| 5.1                      | 295                  | 261  | 13000                              | 2.8                   |                                                                                    |        |    |      |         |                                                                                     |
| 5.6                      | 260                  | 238  | 13000                              | 3.1                   |                                                                                    |        |    |      |         |                                                                                     |
| 6.6                      | 215                  | 200  | 13000                              | 3.7                   | FA<br>FAF<br>F<br>FF                                                               | 57R37  | DR | 63M4 | 39      | 456                                                                                 |
| 2.4                      | 635                  | 558  | 7570                               | 0.95                  |                                                                                    |        |    |      |         |                                                                                     |
| 2.6                      | 570                  | 506  | 9420                               | 1.05                  |                                                                                    |        |    |      |         |                                                                                     |
| 2.9                      | 495                  | 452  | 9930                               | 1.20                  |                                                                                    |        |    |      |         |                                                                                     |
| 3.4                      | 425                  | 386  | 10400                              | 1.40                  |                                                                                    |        |    |      |         |                                                                                     |
| 3.9                      | 370                  | 338  | 10700                              | 1.60                  | FA<br>FAF<br>F<br>FF                                                               | 57R37  | DR | 63M4 | 39      | 456                                                                                 |
| 2.6                      | 570                  | 506  | 9420                               | 1.05                  |                                                                                    |        |    |      |         |                                                                                     |
| 2.9                      | 495                  | 452  | 9930                               | 1.20                  |                                                                                    |        |    |      |         |                                                                                     |
| 3.4                      | 425                  | 386  | 10400                              | 1.40                  |                                                                                    |        |    |      |         |                                                                                     |
| 3.9                      | 370                  | 338  | 10700                              | 1.60                  |                                                                                    |        |    |      |         |                                                                                     |

21933170/DE – 11/2015


| P <sub>m</sub> = 0.18 kW |                      |        |                                    |                       |                                                                                    |       |    |      |         |                                                                                     |
|--------------------------|----------------------|--------|------------------------------------|-----------------------|------------------------------------------------------------------------------------|-------|----|------|---------|-------------------------------------------------------------------------------------|
| n <sub>a</sub><br>rpm    | M <sub>a</sub><br>Nm | i      | F <sub>Ra</sub> <sup>1)</sup><br>N | SEW<br>f <sub>B</sub> |  |       |    |      | m<br>kg |  |
| 3.1                      | 500                  | 426    | 9910                               | 1.20                  | FA<br>FAF<br>F<br>FF                                                               | 57R37 | DR | 63M4 | 38      | 456                                                                                 |
| 3.5                      | 445                  | 382    | 10300                              | 1.35                  |                                                                                    |       |    |      |         |                                                                                     |
| 4.0                      | 380                  | 330    | 10700                              | 1.55                  |                                                                                    |       |    |      |         |                                                                                     |
| 4.4                      | 340                  | 298    | 10900                              | 1.75                  |                                                                                    |       |    |      |         |                                                                                     |
| 5.0                      | 300                  | 262    | 11100                              | 2.00                  |                                                                                    |       |    |      |         |                                                                                     |
| 5.8                      | 255                  | 226    | 11400                              | 2.3                   |                                                                                    |       |    |      |         |                                                                                     |
| 6.6                      | 220                  | 200    | 11500                              | 2.7                   |                                                                                    |       |    |      |         |                                                                                     |
| 3.6                      | 410                  | 370    | 5210                               | 0.95                  | FA                                                                                 | 47R17 | DR | 63M4 | 24      | 456                                                                                 |
| 4.1                      | 375                  | 324    | 6250                               | 1.05                  | FAF                                                                                | 47R17 | DR | 63M4 | 26      | 456                                                                                 |
| 4.6                      | 325                  | 288    | 6810                               | 1.20                  | F                                                                                  | 47R17 | DR | 63M4 | 25      | 456                                                                                 |
| 5.3                      | 275                  | 249    | 7250                               | 1.45                  | FF                                                                                 | 47R17 | DR | 63M4 | 28      | 456                                                                                 |
| 4.0                      | 385                  | 334    | 6100                               | 1.05                  | FA<br>FAF<br>F<br>FF                                                               | 47R17 | DR | 63M4 | 23      | 456                                                                                 |
| 4.5                      | 335                  | 295    | 6680                               | 1.20                  |                                                                                    |       |    |      |         |                                                                                     |
| 5.2                      | 285                  | 253    | 7190                               | 1.40                  |                                                                                    |       |    |      |         |                                                                                     |
| 6.1                      | 250                  | 217    | 7430                               | 1.55                  |                                                                                    |       |    |      |         |                                                                                     |
| 7.0                      | 220                  | 190    | 7650                               | 1.80                  |                                                                                    |       |    |      |         |                                                                                     |
| 7.4                      | 205                  | 178    | 7740                               | 1.95                  |                                                                                    |       |    |      |         |                                                                                     |
| 7.1                      | 215                  | 186    | 4060                               | 0.95                  | FA                                                                                 | 37R17 | DR | 63M4 | 19      | 456                                                                                 |
| 7.9                      | 194                  | 167    | 4380                               | 1.05                  | FAF                                                                                | 37R17 | DR | 63M4 | 20      | 456                                                                                 |
| 9.1                      | 171                  | 145    | 4660                               | 1.15                  | F                                                                                  | 37R17 | DR | 63M4 | 19      | 456                                                                                 |
| 10                       | 151                  | 129    | 4870                               | 1.30                  | FF                                                                                 | 37R17 | DR | 63M4 | 21      | 456                                                                                 |
| 9.3                      | 166                  | 142    | 4500                               | 0.80                  | FA                                                                                 | 27R17 | DR | 63M4 | 13      | 456                                                                                 |
| 11                       | 144                  | 124    | 4500                               | 0.90                  | FAF                                                                                | 27R17 | DR | 63M4 | 13      | 456                                                                                 |
| 12                       | 126                  | 109    | 4500                               | 1.05                  | F                                                                                  | 27R17 | DR | 63M4 | 13      | 456                                                                                 |
| 14                       | 110                  | 96     | 4500                               | 1.20                  | FF                                                                                 | 27R17 | DR | 63M4 | 14      | 456                                                                                 |
| 3.1                      | 555                  | 281.71 | 19600                              | 2.7                   | FA                                                                                 | 77    | DR | 63L6 | 57      | 422                                                                                 |
| 3.3                      | 515                  | 262.93 | 19700                              | 2.9                   | FAF                                                                                | 77    | DR | 63L6 | 63      | 421                                                                                 |
| 3.8                      | 445                  | 225.79 | 19800                              | 3.4                   | F                                                                                  | 77    | DR | 63L6 | 60      | 420                                                                                 |
|                          |                      |        |                                    |                       | FF                                                                                 | 77    | DR | 63L6 | 71      | 421                                                                                 |
| 3.8                      | 450                  | 228.99 | 12600                              | 1.80                  | FA                                                                                 | 67    | DR | 63L6 | 33      | 416                                                                                 |
| 4.4                      | 385                  | 195.39 | 12900                              | 2.1                   | FAF                                                                                | 67    | DR | 63L6 | 39      | 415                                                                                 |
| 5.1                      | 335                  | 170.85 | 13000                              | 2.4                   | F                                                                                  | 67    | DR | 63L6 | 36      | 414                                                                                 |
|                          |                      |        |                                    |                       | FF                                                                                 | 67    | DR | 63L6 | 42      | 415                                                                                 |
| 5.8                      | 295                  | 228.99 | 13000                              | 2.8                   | FA                                                                                 | 67    | DR | 63M4 | 32      | 416                                                                                 |
| 6.8                      | 250                  | 195.39 | 13000                              | 3.2                   | FAF                                                                                | 67    | DR | 63M4 | 38      | 415                                                                                 |
| 7.7                      | 220                  | 170.85 | 13000                              | 3.7                   | F                                                                                  | 67    | DR | 63M4 | 35      | 414                                                                                 |
|                          |                      |        |                                    |                       | FF                                                                                 | 67    | DR | 63M4 | 41      | 415                                                                                 |
| 4.4                      | 390                  | 199.70 | 10600                              | 1.50                  | FA<br>FAF<br>F<br>FF                                                               | 57    | DR | 63L6 | 29      | 410                                                                                 |
| 4.7                      | 360                  | 183.60 | 10800                              | 1.65                  |                                                                                    |       |    |      |         |                                                                                     |
| 5.5                      | 310                  | 157.09 | 11100                              | 1.95                  |                                                                                    |       |    |      |         |                                                                                     |
| 6.4                      | 265                  | 136.16 | 11300                              | 2.2                   |                                                                                    |       |    |      |         |                                                                                     |
| 6.8                      | 250                  | 127.27 | 11400                              | 2.4                   |                                                                                    |       |    |      |         |                                                                                     |
| 7.9                      | 215                  | 110.01 | 11500                              | 2.8                   |                                                                                    |       |    |      |         |                                                                                     |
| 6.6                      | 260                  | 199.70 | 11300                              | 2.3                   | FA                                                                                 | 57    | DR | 63M4 | 28      | 410                                                                                 |
| 7.2                      | 235                  | 183.60 | 11500                              | 2.5                   | FAF                                                                                | 57    | DR | 63M4 | 34      | 409                                                                                 |
| 8.4                      | 200                  | 157.09 | 11500                              | 2.9                   | F                                                                                  | 57    | DR | 63M4 | 28      | 408                                                                                 |
| 9.7                      | 177                  | 136.16 | 11500                              | 3.4                   | FF                                                                                 | 57    | DR | 63M4 | 35      | 409                                                                                 |
| 10                       | 166                  | 127.27 | 11500                              | 3.6                   |                                                                                    |       |    |      |         |                                                                                     |
| 4.6                      | 375                  | 190.76 | 6240                               | 1.05                  | FA                                                                                 | 47    | DR | 63L6 | 22      | 404                                                                                 |
| 5.0                      | 345                  | 175.38 | 6600                               | 1.15                  | FAF                                                                                | 47    | DR | 63L6 | 24      | 403                                                                                 |
| 5.8                      | 295                  | 150.06 | 7090                               | 1.35                  | F                                                                                  | 47    | DR | 63L6 | 22      | 402                                                                                 |
| 6.7                      | 255                  | 130.07 | 7410                               | 1.55                  | FF                                                                                 | 47    | DR | 63L6 | 25      | 403                                                                                 |
| 7.2                      | 240                  | 121.57 | 7530                               | 1.65                  |                                                                                    |       |    |      |         |                                                                                     |
| 6.9                      | 245                  | 190.76 | 7470                               | 1.60                  | FA                                                                                 | 47    | DR | 63M4 | 21      | 404                                                                                 |
| 7.5                      | 225                  | 175.38 | 7600                               | 1.75                  | FAF                                                                                | 47    | DR | 63M4 | 24      | 403                                                                                 |
| 8.8                      | 195                  | 150.06 | 7800                               | 2.0                   | F                                                                                  | 47    | DR | 63M4 | 22      | 402                                                                                 |
| 10                       | 169                  | 130.07 | 7920                               | 2.4                   | FF                                                                                 | 47    | DR | 63M4 | 25      | 403                                                                                 |
| 11                       | 158                  | 121.57 | 7970                               | 2.5                   |                                                                                    |       |    |      |         |                                                                                     |
| 7.4                      | 230                  | 117.88 | 3750                               | 0.85                  | FA                                                                                 | 37    | DR | 63L6 | 17      | 398                                                                                 |
| 8.7                      | 198                  | 100.36 | 4320                               | 1.00                  | FAF                                                                                | 37    | DR | 63L6 | 18      | 397                                                                                 |
| 10                       | 171                  | 86.53  | 4660                               | 1.15                  | F                                                                                  | 37    | DR | 63L6 | 17      | 396                                                                                 |
| 11                       | 159                  | 80.65  | 4790                               | 1.25                  | FF                                                                                 | 37    | DR | 63L6 | 19      | 397                                                                                 |
| 12                       | 139                  | 70.50  | 4970                               | 1.45                  |                                                                                    |       |    |      |         |                                                                                     |

| P <sub>m</sub> = 0.18 kW |                      |        |                                    |                       |                                                                                    |    |    |      |         |                                                                                     |
|--------------------------|----------------------|--------|------------------------------------|-----------------------|------------------------------------------------------------------------------------|----|----|------|---------|-------------------------------------------------------------------------------------|
| n <sub>a</sub><br>rpm    | M <sub>a</sub><br>Nm | i      | F <sub>Ra</sub> <sup>1)</sup><br>N | SEW<br>f <sub>B</sub> |  |    |    |      | m<br>kg |  |
| 10                       | 167                  | 128.51 | 4700                               | 1.20                  |                                                                                    |    |    |      |         |                                                                                     |
| 11                       | 154                  | 117.88 | 4840                               | 1.30                  |                                                                                    |    |    |      |         |                                                                                     |
| 13                       | 131                  | 100.36 | 5040                               | 1.55                  |                                                                                    |    |    |      |         |                                                                                     |
| 15                       | 113                  | 86.53  | 5180                               | 1.75                  |                                                                                    |    |    |      |         |                                                                                     |
| 16                       | 105                  | 80.65  | 5230                               | 1.90                  |                                                                                    |    |    |      |         |                                                                                     |
| 19                       | 92                   | 70.50  | 5300                               | 2.2                   |                                                                                    |    |    |      |         |                                                                                     |
| 20                       | 86                   | 66.09  | 5330                               | 2.3                   |                                                                                    |    |    |      |         |                                                                                     |
| 23                       | 76                   | 58.32  | 5380                               | 2.6                   |                                                                                    |    |    |      |         |                                                                                     |
| 12                       | 143                  | 109.90 | 4500                               | 0.90                  |                                                                                    |    |    |      |         |                                                                                     |
| 14                       | 123                  | 94.76  | 4500                               | 1.05                  |                                                                                    |    |    |      |         |                                                                                     |
| 15                       | 115                  | 88.32  | 4500                               | 1.15                  |                                                                                    |    |    |      |         |                                                                                     |
| 17                       | 100                  | 77.21  | 4500                               | 1.30                  |                                                                                    |    |    |      |         |                                                                                     |
| 18                       | 94                   | 72.37  | 4500                               | 1.40                  |                                                                                    |    |    |      |         |                                                                                     |
| 21                       | 83                   | 63.86  | 4500                               | 1.55                  |                                                                                    |    |    |      |         |                                                                                     |
| 23                       | 74                   | 56.62  | 4500                               | 1.75                  |                                                                                    |    |    |      |         |                                                                                     |
| 26                       | 65                   | 50.19  | 4500                               | 2.00                  |                                                                                    |    |    |      |         |                                                                                     |
| 28                       | 61                   | 46.78  | 4500                               | 2.1                   |                                                                                    |    |    |      |         |                                                                                     |
| 32                       | 53                   | 40.89  | 4410                               | 2.4                   |                                                                                    |    |    |      |         |                                                                                     |
| 34                       | 50                   | 38.33  | 4340                               | 2.6                   |                                                                                    |    |    |      |         |                                                                                     |
| 39                       | 44                   | 33.83  | 4200                               | 3.0                   |                                                                                    |    |    |      |         |                                                                                     |
| 45                       | 38                   | 29.56  | 4040                               | 3.4                   |                                                                                    |    |    |      |         |                                                                                     |
| 49                       | 35                   | 27.18  | 3950                               | 3.7                   |                                                                                    |    |    |      |         |                                                                                     |
| 57                       | 30                   | 23.25  | 3780                               | 4.3                   |                                                                                    |    |    |      |         |                                                                                     |
| 65                       | 26                   | 20.15  | 3630                               | 5.0                   |                                                                                    |    |    |      |         |                                                                                     |
| 70                       | 24                   | 18.84  | 3560                               | 5.3                   |                                                                                    |    |    |      |         |                                                                                     |
| 81                       | 21                   | 16.28  | 3410                               | 6.1                   |                                                                                    |    |    |      |         |                                                                                     |
| 95                       | 18                   | 13.84  | 3240                               | 7.2                   |                                                                                    |    |    |      |         |                                                                                     |
| 107                      | 16                   | 12.35  | 3140                               | 8.1                   |                                                                                    |    |    |      |         |                                                                                     |
| 125                      | 14                   | 10.55  | 2990                               | 9.5                   |                                                                                    |    |    |      |         |                                                                                     |
| 134                      | 13                   | 9.88   | 2930                               | 10                    |                                                                                    |    |    |      |         |                                                                                     |
| 140                      | 12                   | 9.40   | 2870                               | 11                    |                                                                                    |    |    |      |         |                                                                                     |
| 162                      | 11                   | 8.13   | 2750                               | 12                    |                                                                                    |    |    |      |         |                                                                                     |
| 191                      | 9.0                  | 6.91   | 2610                               | 13                    |                                                                                    |    |    |      |         |                                                                                     |
| 214                      | 8.0                  | 6.17   | 2520                               | 14                    |                                                                                    |    |    |      |         |                                                                                     |
| 251                      | 6.9                  | 5.27   | 2400                               | 14                    |                                                                                    |    |    |      |         |                                                                                     |
| 268                      | 6.4                  | 4.93   | 2350                               | 15                    |                                                                                    |    |    |      |         |                                                                                     |
| 318                      | 5.4                  | 4.16   | 2230                               | 16                    |                                                                                    |    |    |      |         |                                                                                     |
| 335                      | 5.1                  | 8.13   | 2190                               | 24                    |                                                                                    |    |    |      |         |                                                                                     |
| 394                      | 4.4                  | 6.91   | 2080                               | 26                    |                                                                                    |    |    |      |         |                                                                                     |
| 441                      | 3.9                  | 6.17   | 2000                               | 28                    |                                                                                    |    |    |      |         |                                                                                     |
| 516                      | 3.3                  | 5.27   | 1910                               | 30                    |                                                                                    |    |    |      |         |                                                                                     |
| 551                      | 3.1                  | 4.93   | 1870                               | 31                    |                                                                                    |    |    |      |         |                                                                                     |
| 655                      | 2.6                  | 4.16   | 1770                               | 33                    |                                                                                    |    |    |      |         |                                                                                     |
|                          |                      |        |                                    |                       | FA                                                                                 | 27 | DR | 63S2 | 9.6     | 393                                                                                 |
|                          |                      |        |                                    |                       | FAF                                                                                | 27 | DR | 63S2 | 10      | 392                                                                                 |
|                          |                      |        |                                    |                       | F                                                                                  | 27 | DR | 63S2 | 10      | 391                                                                                 |
|                          |                      |        |                                    |                       | FF                                                                                 | 27 | DR | 63S2 | 11      | 392                                                                                 |


| P <sub>m</sub> = 0.25 kW |                      |      |                                    |                       |                                                                                      |        |    |      |         |                                                                                       |
|--------------------------|----------------------|------|------------------------------------|-----------------------|--------------------------------------------------------------------------------------|--------|----|------|---------|---------------------------------------------------------------------------------------|
| n <sub>a</sub><br>rpm    | M <sub>a</sub><br>Nm | i    | F <sub>Ra</sub> <sup>1)</sup><br>N | SEW<br>f <sub>B</sub> |  |        |    |      | m<br>kg |  |
| 0.15                     | 13300                | 8831 | 87900                              | 0.90                  |                                                                                      |        |    |      |         |                                                                                       |
| 0.17                     | 11500                | 7643 | 90000                              | 1.05                  | FA                                                                                   | 127R77 | DR | 63L4 | 425     | 456                                                                                   |
| 0.19                     | 10400                | 6715 | 90000                              | 1.15                  | FAF                                                                                  | 127R77 | DR | 63L4 | 465     | 456                                                                                   |
| 0.22                     | 9230                 | 5925 | 90000                              | 1.30                  | F                                                                                    | 127R77 | DR | 63L4 | 465     | 456                                                                                   |
| 0.25                     | 7940                 | 5153 | 90000                              | 1.50                  | FF                                                                                   | 127R77 | DR | 63L4 | 510     | 456                                                                                   |
| 0.29                     | 6890                 | 4533 | 90000                              | 1.75                  |                                                                                      |        |    |      |         |                                                                                       |
| 0.22                     | 9050                 | 5954 | 46000                              | 0.85                  | FA                                                                                   | 107R77 | DR | 63L4 | 275     | 456                                                                                   |
| 0.25                     | 7890                 | 5223 | 49300                              | 0.95                  | FAF                                                                                  | 107R77 | DR | 63L4 | 295     | 456                                                                                   |
| 0.28                     | 7120                 | 4567 | 51300                              | 1.10                  | F                                                                                    | 107R77 | DR | 63L4 | 290     | 456                                                                                   |
| 0.37                     | 5430                 | 3521 | 55300                              | 1.40                  | FF                                                                                   | 107R77 | DR | 63L4 | 320     | 456                                                                                   |
| 0.43                     | 4780                 | 3037 | 56800                              | 1.60                  |                                                                                      |        |    |      |         |                                                                                       |
| 0.47                     | 4340                 | 2756 | 57700                              | 1.75                  | FA                                                                                   | 107R77 | DR | 63L4 | 275     | 456                                                                                   |
| 0.55                     | 3730                 | 2369 | 59000                              | 2.1                   | FAF                                                                                  | 107R77 | DR | 63L4 | 295     | 456                                                                                   |
| 0.63                     | 3250                 | 2068 | 59900                              | 2.4                   | F                                                                                    | 107R77 | DR | 63L4 | 290     | 456                                                                                   |
| 0.81                     | 2490                 | 1597 | 61300                              | 3.1                   | FF                                                                                   | 107R77 | DR | 63L4 | 320     | 456                                                                                   |
| 0.93                     | 2150                 | 1401 | 61900                              | 3.6                   |                                                                                      |        |    |      |         |                                                                                       |


21933170/DE – 11/2015





| P <sub>m</sub> = 0.25 kW |                      |      |                                    |                       |                                                                                    |       |    |      |         |                                                                                     |    |       |    |      |    |
|--------------------------|----------------------|------|------------------------------------|-----------------------|------------------------------------------------------------------------------------|-------|----|------|---------|-------------------------------------------------------------------------------------|----|-------|----|------|----|
| n <sub>a</sub><br>rpm    | M <sub>a</sub><br>Nm | i    | F <sub>Ra</sub> <sup>1)</sup><br>N | SEW<br>f <sub>B</sub> |  |       |    |      | m<br>kg |  |    |       |    |      |    |
| 0.45                     | 4670                 | 2907 | 27500                              | 0.90                  | FA<br>FAF<br>F<br>FF                                                               | 97R57 | DR | 63L4 | 185     | 456                                                                                 |    |       |    |      |    |
| 0.51                     | 4180                 | 2553 | 30300                              | 1.05                  |                                                                                    |       |    |      |         |                                                                                     |    |       |    |      |    |
| 0.58                     | 3670                 | 2245 | 31600                              | 1.15                  |                                                                                    |       |    |      |         |                                                                                     |    |       |    |      |    |
| 0.66                     | 3200                 | 1970 | 32800                              | 1.35                  |                                                                                    |       |    |      |         |                                                                                     |    |       |    |      |    |
| 0.75                     | 2820                 | 1722 | 33700                              | 1.50                  |                                                                                    |       |    |      |         |                                                                                     |    |       |    |      |    |
| 0.85                     | 2500                 | 1527 | 34400                              | 1.70                  |                                                                                    |       |    |      |         |                                                                                     |    |       |    |      |    |
| 0.98                     | 2090                 | 1327 | 35200                              | 2.0                   |                                                                                    |       |    |      |         |                                                                                     |    |       |    |      |    |
| 1.1                      | 1910                 | 1171 | 35500                              | 2.2                   |                                                                                    |       |    |      |         |                                                                                     |    |       |    |      |    |
| 1.3                      | 1670                 | 1022 | 36000                              | 2.6                   |                                                                                    |       |    |      |         |                                                                                     |    |       |    |      |    |
| 0.67                     | 3130                 | 1930 | 13500                              | 0.95                  | FA<br>FAF<br>F<br>FF                                                               | 87R57 | DR | 63L4 | 120     | 456                                                                                 |    |       |    |      |    |
| 0.76                     | 2790                 | 1709 | 23700                              | 1.05                  |                                                                                    |       |    |      |         |                                                                                     |    |       |    |      |    |
| 0.87                     | 2440                 | 1493 | 25000                              | 1.25                  |                                                                                    |       |    |      |         |                                                                                     |    |       |    |      |    |
| 1.0                      | 2050                 | 1300 | 26300                              | 1.45                  |                                                                                    |       |    |      |         |                                                                                     |    |       |    |      |    |
| 1.1                      | 1830                 | 1148 | 26900                              | 1.65                  |                                                                                    |       |    |      |         |                                                                                     |    |       |    |      |    |
| 1.3                      | 1590                 | 1010 | 27600                              | 1.90                  |                                                                                    |       |    |      |         |                                                                                     |    |       |    |      |    |
| 1.5                      | 1410                 | 887  | 28000                              | 2.1                   |                                                                                    |       |    |      |         |                                                                                     |    |       |    |      |    |
| 1.7                      | 1230                 | 780  | 28500                              | 2.4                   |                                                                                    |       |    |      |         |                                                                                     |    |       |    |      |    |
| 1.9                      | 1040                 | 674  | 28900                              | 2.9                   |                                                                                    |       |    |      |         |                                                                                     |    |       |    |      |    |
| 1.2                      | 1740                 | 1053 | 13900                              | 0.85                  | FA<br>FAF<br>F<br>FF                                                               | 77R37 | DR | 63L4 | 66      | 456                                                                                 |    |       |    |      |    |
| 1.4                      | 1490                 | 910  | 15700                              | 1.00                  |                                                                                    |       |    |      |         |                                                                                     |    |       |    |      |    |
| 1.6                      | 1290                 | 810  | 16900                              | 1.15                  |                                                                                    |       |    |      |         |                                                                                     |    |       |    |      |    |
| 1.8                      | 1130                 | 710  | 17700                              | 1.30                  |                                                                                    |       |    |      |         |                                                                                     |    |       |    |      |    |
| 2.1                      | 1000                 | 615  | 18300                              | 1.50                  |                                                                                    |       |    |      |         |                                                                                     |    |       |    |      |    |
| 2.4                      | 870                  | 538  | 18700                              | 1.70                  |                                                                                    |       |    |      |         |                                                                                     |    |       |    |      |    |
| 2.7                      | 775                  | 480  | 19000                              | 1.95                  |                                                                                    |       |    |      |         |                                                                                     |    |       |    |      |    |
| 3.2                      | 660                  | 413  | 19400                              | 2.3                   |                                                                                    |       |    |      |         |                                                                                     |    |       |    |      |    |
| 2.3                      | 930                  | 572  | 9150                               | 0.90                  | FA                                                                                 | 67R37 | DR | 63L4 | 44      | 456                                                                                 |    |       |    |      |    |
| 2.6                      | 810                  | 509  | 10400                              | 1.00                  | FAF                                                                                | 67R37 | DR | 63L4 | 50      | 456                                                                                 |    |       |    |      |    |
| 3.0                      | 700                  | 437  | 11200                              | 1.15                  | F                                                                                  | 67R37 | DR | 63L4 | 46      | 456                                                                                 |    |       |    |      |    |
|                          |                      |      |                                    |                       | FF                                                                                 | 67R37 | DR | 63L4 | 53      | 456                                                                                 |    |       |    |      |    |
| 2.6                      | 830                  | 500  | 10200                              | 1.00                  | FA<br>FAF<br>F<br>FF                                                               | 67R37 | DR | 63L4 | 42      | 456                                                                                 |    |       |    |      |    |
| 2.9                      | 755                  | 454  | 10800                              | 1.10                  |                                                                                    |       |    |      |         |                                                                                     |    |       |    |      |    |
| 3.3                      | 650                  | 392  | 11600                              | 1.25                  |                                                                                    |       |    |      |         |                                                                                     |    |       |    |      |    |
| 3.9                      | 550                  | 333  | 12200                              | 1.50                  |                                                                                    |       |    |      |         |                                                                                     |    |       |    |      |    |
| 4.4                      | 485                  | 297  | 12500                              | 1.70                  |                                                                                    |       |    |      |         |                                                                                     |    |       |    |      |    |
| 5.0                      | 425                  | 261  | 12700                              | 1.90                  |                                                                                    |       |    |      |         |                                                                                     |    |       |    |      |    |
| 5.5                      | 385                  | 238  | 12900                              | 2.1                   |                                                                                    |       |    |      |         |                                                                                     |    |       |    |      |    |
|                          |                      |      |                                    |                       |                                                                                    |       |    |      |         |                                                                                     |    |       |    |      |    |
| 3.4                      | 620                  | 386  | 8830                               | 0.95                  | FA                                                                                 | 57R37 | DR | 63L4 | 40      | 456                                                                                 |    |       |    |      |    |
| 3.8                      | 540                  | 338  | 9640                               | 1.10                  | FAF                                                                                | 57R37 | DR | 63L4 | 45      | 456                                                                                 |    |       |    |      |    |
| 5.1                      | 405                  | 255  | 10500                              | 1.45                  | F                                                                                  | 57R37 | DR | 63L4 | 40      | 456                                                                                 |    |       |    |      |    |
|                          |                      |      |                                    |                       | FF                                                                                 | 57R37 | DR | 63L4 | 46      | 456                                                                                 |    |       |    |      |    |
| 3.4                      | 635                  | 382  | 7390                               | 0.95                  | FA<br>FAF<br>F<br>FF                                                               | 57R37 | DR | 63L4 | 39      | 456                                                                                 |    |       |    |      |    |
| 3.9                      | 550                  | 330  | 9570                               | 1.10                  |                                                                                    |       |    |      |         |                                                                                     |    |       |    |      |    |
| 4.4                      | 495                  | 298  | 9950                               | 1.20                  |                                                                                    |       |    |      |         |                                                                                     |    |       |    |      |    |
| 5.0                      | 435                  | 262  | 10300                              | 1.35                  |                                                                                    |       |    |      |         |                                                                                     |    |       |    |      |    |
| 5.8                      | 370                  | 226  | 10700                              | 1.60                  |                                                                                    |       |    |      |         |                                                                                     |    |       |    |      |    |
| 6.5                      | 320                  | 200  | 11000                              | 1.85                  |                                                                                    |       |    |      |         |                                                                                     |    |       |    |      |    |
| 7.6                      | 275                  | 170  | 11300                              | 2.2                   |                                                                                    |       |    |      |         |                                                                                     |    |       |    |      |    |
|                          |                      |      |                                    |                       |                                                                                    |       |    |      |         |                                                                                     |    |       |    |      |    |
| 5.2                      | 400                  | 249  | 5880                               | 1.00                  | FA                                                                                 | 47R17 | DR | 63L4 | 24      | 456                                                                                 |    |       |    |      |    |
| 6.0                      | 355                  | 218  | 6470                               | 1.10                  | FAF                                                                                | 47R17 | DR | 63L4 | 27      | 456                                                                                 |    |       |    |      |    |
| 6.7                      | 315                  | 193  | 6920                               | 1.25                  | F                                                                                  | 47R17 | DR | 63L4 | 25      | 456                                                                                 |    |       |    |      |    |
| 7.4                      | 285                  | 175  | 7180                               | 1.40                  | FF                                                                                 | 47R17 | DR | 63L4 | 28      | 456                                                                                 |    |       |    |      |    |
| 5.1                      | 410                  | 253  | 4980                               | 0.95                  | FA<br>FAF<br>F<br>FF                                                               | 47R17 | DR | 63L4 | 24      | 456                                                                                 |    |       |    |      |    |
| 6.0                      | 365                  | 217  | 6380                               | 1.10                  |                                                                                    |       |    |      |         |                                                                                     |    |       |    |      |    |
| 6.8                      | 315                  | 190  | 6900                               | 1.25                  |                                                                                    |       |    |      |         |                                                                                     |    |       |    |      |    |
| 7.3                      | 295                  | 178  | 7090                               | 1.35                  |                                                                                    |       |    |      |         |                                                                                     |    |       |    |      |    |
| 8.7                      | 245                  | 149  | 7480                               | 1.60                  |                                                                                    |       |    |      |         |                                                                                     |    |       |    |      |    |
| 9.9                      | 215                  | 131  | 7670                               | 1.85                  |                                                                                    |       |    |      |         |                                                                                     |    |       |    |      |    |
|                          |                      |      |                                    |                       |                                                                                    |       |    |      |         |                                                                                     |    |       |    |      |    |
| 8.9                      | 245                  | 145  | 3420                               | 0.80                  |                                                                                    |       |    |      |         |                                                                                     | FA | 37R17 | DR | 63L4 | 20 |
| 10                       | 215                  | 129  | 4040                               | 0.90                  | FAF                                                                                | 37R17 | DR | 63L4 | 21      | 456                                                                                 |    |       |    |      |    |
| 11                       | 198                  | 118  | 4320                               | 1.00                  | F                                                                                  | 37R17 | DR | 63L4 | 20      | 456                                                                                 |    |       |    |      |    |
| 13                       | 164                  | 98   | 4740                               | 1.20                  | FF                                                                                 | 37R17 | DR | 63L4 | 20      | 456                                                                                 |    |       |    |      |    |
| 15                       | 144                  | 87   | 4940                               | 1.40                  |                                                                                    |       |    |      | 22      | 456                                                                                 |    |       |    |      |    |





| <b>P<sub>m</sub> = 0.25 kW</b>     |                                   |          |                                                |                                    |                                                                                    |    |     |      |                       |                                                                                     |
|------------------------------------|-----------------------------------|----------|------------------------------------------------|------------------------------------|------------------------------------------------------------------------------------|----|-----|------|-----------------------|-------------------------------------------------------------------------------------|
| <b>n<sub>a</sub></b><br><b>rpm</b> | <b>M<sub>a</sub></b><br><b>Nm</b> | <b>i</b> | <b>F<sub>Ra</sub><sup>1)</sup></b><br><b>N</b> | <b>SEW</b><br><b>f<sub>B</sub></b> |  |    |     |      | <b>m</b><br><b>kg</b> |  |
| 3.2                                | 750                               | 281.71   | 19100                                          | 2.0                                | FA                                                                                 | 77 | DRS | 71S6 | 58                    | 422                                                                                 |
| 3.4                                | 700                               | 262.93   | 19300                                          | 2.1                                | FAF                                                                                | 77 | DRS | 71S6 | 65                    | 421                                                                                 |
| 4.0                                | 600                               | 225.79   | 19500                                          | 2.5                                | F                                                                                  | 77 | DRS | 71S6 | 62                    | 420                                                                                 |
| 4.5                                | 525                               | 198.31   | 19600                                          | 2.8                                | FF                                                                                 | 77 | DRS | 71S6 | 73                    | 421                                                                                 |
| 4.8                                | 500                               | 188.40   | 19700                                          | 3.0                                |                                                                                    |    |     |      |                       |                                                                                     |
| 3.9                                | 610                               | 228.99   | 11800                                          | 1.35                               | FA                                                                                 | 67 | DRS | 71S6 | 34                    | 416                                                                                 |
| 4.6                                | 520                               | 195.39   | 12300                                          | 1.55                               | FAF                                                                                | 67 | DRS | 71S6 | 41                    | 415                                                                                 |
| 5.2                                | 455                               | 170.85   | 12600                                          | 1.80                               | F                                                                                  | 67 | DRS | 71S6 | 37                    | 414                                                                                 |
| 5.5                                | 430                               | 162.31   | 12700                                          | 1.90                               | FF                                                                                 | 67 | DRS | 71S6 | 43                    | 415                                                                                 |
| 6.3                                | 375                               | 142.40   | 12900                                          | 2.2                                |                                                                                    |    |     |      |                       |                                                                                     |
| 5.7                                | 420                               | 228.99   | 12700                                          | 1.95                               | FA                                                                                 | 67 | DR  | 63L4 | 33                    | 416                                                                                 |
| 6.6                                | 355                               | 195.39   | 13000                                          | 2.3                                | FAF                                                                                | 67 | DR  | 63L4 | 39                    | 415                                                                                 |
| 7.6                                | 310                               | 170.85   | 13000                                          | 2.6                                | F                                                                                  | 67 | DR  | 63L4 | 36                    | 414                                                                                 |
| 8.0                                | 295                               | 162.31   | 13000                                          | 2.8                                | FF                                                                                 | 67 | DR  | 63L4 | 42                    | 415                                                                                 |
| 9.1                                | 260                               | 142.40   | 13000                                          | 3.1                                |                                                                                    |    |     |      |                       |                                                                                     |
| 4.5                                | 530                               | 199.70   | 9700                                           | 1.15                               | FA                                                                                 | 57 | DRS | 71S6 | 31                    | 410                                                                                 |
| 4.9                                | 485                               | 183.60   | 9990                                           | 1.25                               | FAF                                                                                | 57 | DRS | 71S6 | 36                    | 409                                                                                 |
| 5.7                                | 415                               | 157.09   | 10500                                          | 1.45                               | F                                                                                  | 57 | DRS | 71S6 | 31                    | 408                                                                                 |
| 6.6                                | 360                               | 136.16   | 10800                                          | 1.65                               | FF                                                                                 | 57 | DRS | 71S6 | 37                    | 409                                                                                 |
| 7.0                                | 335                               | 127.27   | 10900                                          | 1.75                               |                                                                                    |    |     |      |                       |                                                                                     |
| 8.1                                | 290                               | 110.01   | 11200                                          | 2.0                                |                                                                                    |    |     |      |                       |                                                                                     |
| 6.5                                | 365                               | 199.70   | 10800                                          | 1.65                               | FA                                                                                 | 57 | DR  | 63L4 | 29                    | 410                                                                                 |
| 7.1                                | 335                               | 183.60   | 10900                                          | 1.80                               | FAF                                                                                | 57 | DR  | 63L4 | 34                    | 409                                                                                 |
| 8.3                                | 285                               | 157.09   | 11200                                          | 2.1                                | F                                                                                  | 57 | DR  | 63L4 | 29                    | 408                                                                                 |
| 9.6                                | 250                               | 136.16   | 11400                                          | 2.4                                | FF                                                                                 | 57 | DR  | 63L4 | 35                    | 409                                                                                 |
| 10                                 | 230                               | 127.27   | 11500                                          | 2.6                                |                                                                                    |    |     |      |                       |                                                                                     |
| 12                                 | 200                               | 110.01   | 11500                                          | 3.0                                |                                                                                    |    |     |      |                       |                                                                                     |
| 6.0                                | 400                               | 150.06   | 5920                                           | 1.00                               | FA                                                                                 | 47 | DRS | 71S6 | 24                    | 404                                                                                 |
| 6.9                                | 345                               | 130.07   | 6590                                           | 1.15                               | FAF                                                                                | 47 | DRS | 71S6 | 26                    | 403                                                                                 |
| 7.4                                | 320                               | 121.57   | 6830                                           | 1.25                               | F                                                                                  | 47 | DRS | 71S6 | 24                    | 402                                                                                 |
| 8.5                                | 280                               | 105.09   | 7230                                           | 1.45                               | FF                                                                                 | 47 | DRS | 71S6 | 27                    | 403                                                                                 |
| 6.8                                | 350                               | 190.76   | 6550                                           | 1.15                               | FA                                                                                 | 47 | DR  | 63L4 | 22                    | 404                                                                                 |
| 7.4                                | 320                               | 175.38   | 6850                                           | 1.25                               | FAF                                                                                | 47 | DR  | 63L4 | 24                    | 403                                                                                 |
| 8.7                                | 275                               | 150.06   | 7270                                           | 1.45                               | F                                                                                  | 47 | DR  | 63L4 | 22                    | 402                                                                                 |
| 10.0                               | 235                               | 130.07   | 7540                                           | 1.65                               | FF                                                                                 | 47 | DR  | 63L4 | 25                    | 403                                                                                 |
| 11                                 | 220                               | 121.57   | 7640                                           | 1.80                               |                                                                                    |    |     |      |                       |                                                                                     |
| 12                                 | 193                               | 105.09   | 7810                                           | 2.1                                |                                                                                    |    |     |      |                       |                                                                                     |
| 15                                 | 164                               | 89.29    | 7950                                           | 2.4                                |                                                                                    |    |     |      |                       |                                                                                     |
| 10                                 | 235                               | 128.51   | 3690                                           | 0.85                               |                                                                                    |    |     |      |                       |                                                                                     |
| 11                                 | 215                               | 117.88   | 4040                                           | 0.90                               |                                                                                    |    |     |      |                       |                                                                                     |
| 13                                 | 184                               | 100.36   | 4500                                           | 1.10                               |                                                                                    |    |     |      |                       |                                                                                     |
| 15                                 | 159                               | 86.53    | 4790                                           | 1.25                               |                                                                                    |    |     |      |                       |                                                                                     |
| 16                                 | 148                               | 80.65    | 4900                                           | 1.35                               |                                                                                    |    |     |      |                       |                                                                                     |
| 18                                 | 130                               | 70.50    | 5060                                           | 1.55                               | FA                                                                                 | 37 | DR  | 63L4 | 17                    | 398                                                                                 |
| 20                                 | 121                               | 66.09    | 5120                                           | 1.65                               | FAF                                                                                | 37 | DR  | 63L4 | 18                    | 397                                                                                 |
| 22                                 | 107                               | 58.32    | 5210                                           | 1.85                               | F                                                                                  | 37 | DR  | 63L4 | 17                    | 396                                                                                 |
| 24                                 | 100                               | 54.54    | 5260                                           | 2.0                                | FF                                                                                 | 37 | DR  | 63L4 | 19                    | 397                                                                                 |
| 25                                 | 95                                | 51.70    | 5280                                           | 2.1                                |                                                                                    |    |     |      |                       |                                                                                     |
| 28                                 | 86                                | 47.02    | 5330                                           | 2.3                                |                                                                                    |    |     |      |                       |                                                                                     |
| 30                                 | 80                                | 43.83    | 5360                                           | 2.5                                |                                                                                    |    |     |      |                       |                                                                                     |
| 34                                 | 70                                | 38.31    | 5400                                           | 2.8                                |                                                                                    |    |     |      |                       |                                                                                     |
| 36                                 | 66                                | 35.91    | 5420                                           | 3.0                                |                                                                                    |    |     |      |                       |                                                                                     |
| 41                                 | 58                                | 31.69    | 5440                                           | 3.4                                |                                                                                    |    |     |      |                       |                                                                                     |
| 17                                 | 142                               | 77.21    | 4500                                           | 0.90                               | FA                                                                                 | 27 | DR  | 63L4 | 11                    | 393                                                                                 |
| 18                                 | 133                               | 72.37    | 4500                                           | 1.00                               | FAF                                                                                | 27 | DR  | 63L4 | 11                    | 392                                                                                 |
| 20                                 | 117                               | 63.86    | 4500                                           | 1.10                               | F                                                                                  | 27 | DR  | 63L4 | 11                    | 391                                                                                 |
| 23                                 | 104                               | 56.62    | 4500                                           | 1.25                               | FF                                                                                 | 27 | DR  | 63L4 | 12                    | 392                                                                                 |
| 26                                 | 92                                | 50.19    | 4440                                           | 1.40                               |                                                                                    |    |     |      |                       |                                                                                     |
| 28                                 | 86                                | 46.78    | 4370                                           | 1.50                               |                                                                                    |    |     |      |                       |                                                                                     |
| 32                                 | 75                                | 40.89    | 4240                                           | 1.75                               |                                                                                    |    |     |      |                       |                                                                                     |
| 34                                 | 70                                | 38.33    | 4180                                           | 1.85                               |                                                                                    |    |     |      |                       |                                                                                     |
| 38                                 | 62                                | 33.83    | 4060                                           | 2.1                                |                                                                                    |    |     |      |                       |                                                                                     |

| P <sub>m</sub> = 0.25 kW |                      |       |                                    |                       |                                                                                    |    |    |      |         |                                                                                     |
|--------------------------|----------------------|-------|------------------------------------|-----------------------|------------------------------------------------------------------------------------|----|----|------|---------|-------------------------------------------------------------------------------------|
| n <sub>a</sub><br>rpm    | M <sub>a</sub><br>Nm | i     | F <sub>Ra</sub> <sup>1)</sup><br>N | SEW<br>f <sub>B</sub> |  |    |    |      | m<br>kg |  |
| 44                       | 54                   | 29.56 | 3920                               | 2.4                   |                                                                                    |    |    |      |         |                                                                                     |
| 48                       | 50                   | 27.18 | 3840                               | 2.6                   |                                                                                    |    |    |      |         |                                                                                     |
| 56                       | 43                   | 23.25 | 3690                               | 3.0                   |                                                                                    |    |    |      |         |                                                                                     |
| 64                       | 37                   | 20.15 | 3550                               | 3.5                   |                                                                                    |    |    |      |         |                                                                                     |
| 69                       | 35                   | 18.84 | 3480                               | 3.8                   |                                                                                    |    |    |      |         |                                                                                     |
| 80                       | 30                   | 16.28 | 3350                               | 4.4                   |                                                                                    |    |    |      |         |                                                                                     |
| 94                       | 25                   | 13.84 | 3200                               | 5.1                   |                                                                                    |    |    |      |         |                                                                                     |
| 105                      | 23                   | 12.35 | 3090                               | 5.7                   |                                                                                    |    |    |      |         |                                                                                     |
| 123                      | 19                   | 10.55 | 2950                               | 6.7                   |                                                                                    |    |    |      |         |                                                                                     |
| 132                      | 18                   | 9.88  | 2900                               | 7.2                   |                                                                                    |    |    |      |         |                                                                                     |
| 138                      | 17                   | 9.40  | 2840                               | 7.5                   | FA                                                                                 | 27 | DR | 63L4 | 10      | 393                                                                                 |
| 160                      | 15                   | 8.13  | 2720                               | 8.3                   | FAF                                                                                | 27 | DR | 63L4 | 11      | 392                                                                                 |
| 188                      | 13                   | 6.91  | 2590                               | 9.0                   | F                                                                                  | 27 | DR | 63L4 | 11      | 391                                                                                 |
| 211                      | 11                   | 6.17  | 2500                               | 9.6                   | FF                                                                                 | 27 | DR | 63L4 | 12      | 392                                                                                 |
| 247                      | 9.7                  | 5.27  | 2380                               | 10                    |                                                                                    |    |    |      |         |                                                                                     |
| 264                      | 9.1                  | 4.93  | 2340                               | 11                    |                                                                                    |    |    |      |         |                                                                                     |
| 313                      | 7.6                  | 4.16  | 2220                               | 11                    |                                                                                    |    |    |      |         |                                                                                     |
| 327                      | 7.3                  | 8.13  | 2180                               | 17                    | FA                                                                                 | 27 | DR | 63M2 | 9.6     | 393                                                                                 |
| 385                      | 6.2                  | 6.91  | 2080                               | 18                    | FAF                                                                                | 27 | DR | 63M2 | 10      | 392                                                                                 |
| 431                      | 5.5                  | 6.17  | 2000                               | 20                    | F                                                                                  | 27 | DR | 63M2 | 10      | 391                                                                                 |
| 505                      | 4.7                  | 5.27  | 1910                               | 21                    | FF                                                                                 | 27 | DR | 63M2 | 11      | 392                                                                                 |
| 539                      | 4.4                  | 4.93  | 1870                               | 22                    |                                                                                    |    |    |      |         |                                                                                     |
| 640                      | 3.7                  | 4.16  | 1770                               | 24                    |                                                                                    |    |    |      |         |                                                                                     |


| P <sub>m</sub> = 0.37 kW |                      |      |                                    |                       |                                                                                      |        |     |      |         |                                                                                       |
|--------------------------|----------------------|------|------------------------------------|-----------------------|--------------------------------------------------------------------------------------|--------|-----|------|---------|---------------------------------------------------------------------------------------|
| n <sub>a</sub><br>rpm    | M <sub>a</sub><br>Nm | i    | F <sub>Ra</sub> <sup>1)</sup><br>N | SEW<br>f <sub>B</sub> |  |        |     |      | m<br>kg |  |
| 0.21                     | 14900                | 6715 | 84600                              | 0.80                  | FA<br>FAF<br>F<br>FF                                                                 | 127R77 | DRS | 71S4 | 430     | 456                                                                                   |
| 0.23                     | 13200                | 5925 | 88100                              | 0.90                  |                                                                                      | 127R77 | DRS | 71S4 | 465     | 456                                                                                   |
| 0.27                     | 11400                | 5153 | 90000                              | 1.05                  |                                                                                      | 127R77 | DRS | 71S4 | 465     | 456                                                                                   |
| 0.30                     | 9930                 | 4533 | 90000                              | 1.20                  |                                                                                      | 127R77 | DRS | 71S4 | 510     | 456                                                                                   |
| 0.35                     | 8690                 | 3926 | 90000                              | 1.40                  |                                                                                      |        |     |      |         |                                                                                       |
| 0.40                     | 7560                 | 3454 | 90000                              | 1.60                  |                                                                                      |        |     |      |         |                                                                                       |
| 0.46                     | 6610                 | 3031 | 90000                              | 1.80                  |                                                                                      |        |     |      |         |                                                                                       |
| 0.45                     | 6850                 | 3037 | 52000                              | 1.10                  | FA<br>FAF<br>F<br>FF                                                                 | 107R77 | DRS | 71S4 | 275     | 456                                                                                   |
| 0.50                     | 6210                 | 2756 | 53500                              | 1.25                  |                                                                                      | 107R77 | DRS | 71S4 | 295     | 456                                                                                   |
| 0.58                     | 5340                 | 2369 | 55500                              | 1.45                  |                                                                                      | 107R77 | DRS | 71S4 | 290     | 456                                                                                   |
| 0.67                     | 4660                 | 2068 | 57000                              | 1.65                  |                                                                                      | 107R77 | DRS | 71S4 | 320     | 456                                                                                   |
| 0.86                     | 3570                 | 1597 | 59300                              | 2.2                   |                                                                                      |        |     |      |         |                                                                                       |
| 0.70                     | 4540                 | 1970 | 29200                              | 0.95                  | FA<br>FAF<br>F<br>FF                                                                 | 97R57  | DRS | 71S4 | 185     | 456                                                                                   |
| 0.80                     | 3990                 | 1722 | 30800                              | 1.10                  |                                                                                      | 97R57  | DRS | 71S4 | 205     | 456                                                                                   |
| 0.90                     | 3540                 | 1527 | 32000                              | 1.20                  |                                                                                      | 97R57  | DRS | 71S4 | 190     | 456                                                                                   |
| 1.0                      | 2990                 | 1327 | 33300                              | 1.45                  |                                                                                      | 97R57  | DRS | 71S4 | 225     | 456                                                                                   |
| 1.2                      | 2710                 | 1171 | 33900                              | 1.60                  |                                                                                      |        |     |      |         |                                                                                       |
| 1.4                      | 2370                 | 1022 | 34700                              | 1.80                  |                                                                                      |        |     |      |         |                                                                                       |
| 1.5                      | 2000                 | 898  | 35400                              | 2.1                   |                                                                                      |        |     |      |         |                                                                                       |
| 1.1                      | 2930                 | 1300 | 22000                              | 1.00                  | FA<br>FAF<br>F<br>FF                                                                 | 87R57  | DRS | 71S4 | 120     | 456                                                                                   |
| 1.2                      | 2610                 | 1148 | 24400                              | 1.15                  |                                                                                      | 87R57  | DRS | 71S4 | 130     | 456                                                                                   |
| 1.4                      | 2280                 | 1010 | 25600                              | 1.30                  |                                                                                      | 87R57  | DRS | 71S4 | 125     | 456                                                                                   |
| 1.6                      | 2010                 | 887  | 26400                              | 1.50                  |                                                                                      | 87R57  | DRS | 71S4 | 140     | 456                                                                                   |
| 1.8                      | 1760                 | 780  | 27100                              | 1.70                  |                                                                                      |        |     |      |         |                                                                                       |
| 2.0                      | 1500                 | 674  | 27800                              | 2.00                  |                                                                                      |        |     |      |         |                                                                                       |
| 2.3                      | 1370                 | 609  | 28100                              | 2.2                   |                                                                                      |        |     |      |         |                                                                                       |
| 2.7                      | 1150                 | 515  | 28600                              | 2.6                   |                                                                                      |        |     |      |         |                                                                                       |
| 3.0                      | 1020                 | 452  | 28900                              | 2.9                   |                                                                                      |        |     |      |         |                                                                                       |
| 1.7                      | 1840                 | 810  | 11300                              | 0.80                  | FA<br>FAF<br>F<br>FF                                                                 | 77R37  | DRS | 71S4 | 68      | 456                                                                                   |
| 1.9                      | 1620                 | 710  | 14900                              | 0.95                  |                                                                                      | 77R37  | DRS | 71S4 | 74      | 456                                                                                   |
| 2.2                      | 1420                 | 615  | 16200                              | 1.05                  |                                                                                      | 77R37  | DRS | 71S4 | 72      | 456                                                                                   |
| 2.6                      | 1240                 | 538  | 17200                              | 1.20                  |                                                                                      | 77R37  | DRS | 71S4 | 82      | 456                                                                                   |
| 2.9                      | 1100                 | 480  | 17900                              | 1.35                  |                                                                                      |        |     |      |         |                                                                                       |
| 3.4                      | 940                  | 413  | 18500                              | 1.60                  |                                                                                      |        |     |      |         |                                                                                       |
| 3.8                      | 840                  | 367  | 18900                              | 1.80                  |                                                                                      |        |     |      |         |                                                                                       |
| 4.3                      | 750                  | 323  | 19100                              | 2.0                   |                                                                                      |        |     |      |         |                                                                                       |


| <b>P<sub>m</sub> = 0.37 kW</b>     |                                   |          |                                                |                                    |                                                                                    |       |     |      |                       |                                                                                     |
|------------------------------------|-----------------------------------|----------|------------------------------------------------|------------------------------------|------------------------------------------------------------------------------------|-------|-----|------|-----------------------|-------------------------------------------------------------------------------------|
| <b>n<sub>a</sub></b><br><b>rpm</b> | <b>M<sub>a</sub></b><br><b>Nm</b> | <b>i</b> | <b>F<sub>Ra</sub><sup>1)</sup></b><br><b>N</b> | <b>SEW</b><br><b>f<sub>B</sub></b> |  |       |     |      | <b>m</b><br><b>kg</b> |  |
| 3.6                                | 880                               | 384      | 9670                                           | 0.95                               | FA                                                                                 | 67R37 | DRS | 71S4 | 46                    | 456                                                                                 |
| 4.1                                | 785                               | 338      | 10600                                          | 1.05                               | FAF                                                                                | 67R37 | DRS | 71S4 | 52                    | 456                                                                                 |
| 4.5                                | 700                               | 305      | 11200                                          | 1.15                               | F                                                                                  | 67R37 | DRS | 71S4 | 48                    | 456                                                                                 |
| 5.4                                | 590                               | 257      | 11900                                          | 1.40                               | FF                                                                                 | 67R37 | DRS | 71S4 | 55                    | 456                                                                                 |
| 6.0                                | 520                               | 231      | 12300                                          | 1.55                               |                                                                                    |       |     |      |                       |                                                                                     |
| 5.4                                | 580                               | 255      | 9330                                           | 1.05                               | FA                                                                                 | 57R37 | DRS | 71S4 | 42                    | 456                                                                                 |
| 6.9                                | 455                               | 201      | 10200                                          | 1.30                               | FAF                                                                                | 57R37 | DRS | 71S4 | 47                    | 456                                                                                 |
| 7.6                                | 410                               | 181      | 10500                                          | 1.45                               | F                                                                                  | 57R37 | DRS | 71S4 | 42                    | 456                                                                                 |
|                                    |                                   |          |                                                |                                    | FF                                                                                 | 57R37 | DRS | 71S4 | 48                    | 456                                                                                 |
| 5.3                                | 615                               | 262      | 9070                                           | 0.95                               | FA                                                                                 | 57R37 | DRS | 71S4 | 41                    | 456                                                                                 |
| 6.1                                | 525                               | 226      | 9740                                           | 1.15                               | FAF                                                                                | 57R37 | DRS | 71S4 | 47                    | 456                                                                                 |
| 6.9                                | 460                               | 200      | 10200                                          | 1.30                               | F                                                                                  | 57R37 | DRS | 71S4 | 41                    | 456                                                                                 |
| 8.1                                | 390                               | 170      | 10600                                          | 1.50                               | FF                                                                                 | 57R37 | DRS | 71S4 | 48                    | 456                                                                                 |
| 9.0                                | 345                               | 152      | 10900                                          | 1.70                               |                                                                                    |       |     |      |                       |                                                                                     |
| 10                                 | 305                               | 134      | 11100                                          | 1.95                               |                                                                                    |       |     |      |                       |                                                                                     |
| 7.9                                | 400                               | 175      | 5860                                           | 1.00                               | FA                                                                                 | 47R17 | DRS | 71S4 | 26                    | 456                                                                                 |
| 9.4                                | 340                               | 147      | 6660                                           | 1.15                               | FAF                                                                                | 47R17 | DRS | 71S4 | 29                    | 456                                                                                 |
| 11                                 | 300                               | 130      | 7050                                           | 1.35                               | F                                                                                  | 47R17 | DRS | 71S4 | 27                    | 456                                                                                 |
|                                    |                                   |          |                                                |                                    | FF                                                                                 | 47R17 | DRS | 71S4 | 30                    | 456                                                                                 |
| 3.3                                | 1050                              | 270.68   | 28900                                          | 2.8                                | FA                                                                                 | 87    | DRS | 71M6 | 99                    | 428                                                                                 |
| 3.5                                | 990                               | 255.37   | 29000                                          | 3.0                                | FAF                                                                                | 87    | DRS | 71M6 | 110                   | 427                                                                                 |
| 4.0                                | 890                               | 228.93   | 29200                                          | 3.4                                | F                                                                                  | 87    | DRS | 71M6 | 105                   | 426                                                                                 |
|                                    |                                   |          |                                                |                                    | FF                                                                                 | 87    | DRS | 71M6 | 120                   | 427                                                                                 |
| 4.0                                | 880                               | 225.79   | 18700                                          | 1.70                               | FA                                                                                 | 77    | DRS | 71M6 | 60                    | 422                                                                                 |
| 4.6                                | 770                               | 198.31   | 19100                                          | 1.95                               | FAF                                                                                | 77    | DRS | 71M6 | 66                    | 421                                                                                 |
| 4.8                                | 735                               | 188.40   | 19200                                          | 2.0                                | F                                                                                  | 77    | DRS | 71M6 | 64                    | 420                                                                                 |
| 5.4                                | 645                               | 166.47   | 19400                                          | 2.3                                | FF                                                                                 | 77    | DRS | 71M6 | 74                    | 421                                                                                 |
| 6.4                                | 555                               | 142.27   | 19600                                          | 2.7                                |                                                                                    |       |     |      |                       |                                                                                     |
| 4.9                                | 720                               | 281.71   | 19200                                          | 2.1                                | FA                                                                                 | 77    | DRS | 71S4 | 58                    | 422                                                                                 |
| 5.2                                | 670                               | 262.93   | 19300                                          | 2.2                                | FAF                                                                                | 77    | DRS | 71S4 | 65                    | 421                                                                                 |
| 6.1                                | 575                               | 225.79   | 19500                                          | 2.6                                | F                                                                                  | 77    | DRS | 71S4 | 62                    | 420                                                                                 |
| 7.0                                | 505                               | 198.31   | 19700                                          | 3.0                                | FF                                                                                 | 77    | DRS | 71S4 | 73                    | 421                                                                                 |
| 4.6                                | 760                               | 195.39   | 10800                                          | 1.05                               | FA                                                                                 | 67    | DRS | 71M6 | 36                    | 416                                                                                 |
| 5.3                                | 665                               | 170.85   | 11500                                          | 1.25                               | FAF                                                                                | 67    | DRS | 71M6 | 42                    | 415                                                                                 |
| 5.6                                | 630                               | 162.31   | 11700                                          | 1.30                               | F                                                                                  | 67    | DRS | 71M6 | 39                    | 414                                                                                 |
| 6.4                                | 555                               | 142.40   | 12100                                          | 1.45                               | FF                                                                                 | 67    | DRS | 71M6 | 45                    | 415                                                                                 |
| 7.5                                | 470                               | 120.79   | 12500                                          | 1.75                               |                                                                                    |       |     |      |                       |                                                                                     |
| 6.0                                | 585                               | 228.99   | 12000                                          | 1.40                               | FA                                                                                 | 67    | DRS | 71S4 | 34                    | 416                                                                                 |
| 7.1                                | 500                               | 195.39   | 12400                                          | 1.65                               | FAF                                                                                | 67    | DRS | 71S4 | 41                    | 415                                                                                 |
| 8.1                                | 435                               | 170.85   | 12700                                          | 1.85                               | F                                                                                  | 67    | DRS | 71S4 | 37                    | 414                                                                                 |
| 8.5                                | 415                               | 162.31   | 12800                                          | 1.95                               | FF                                                                                 | 67    | DRS | 71S4 | 43                    | 415                                                                                 |
| 9.7                                | 360                               | 142.40   | 12900                                          | 2.2                                |                                                                                    |       |     |      |                       |                                                                                     |
| 11                                 | 305                               | 120.79   | 13000                                          | 2.6                                |                                                                                    |       |     |      |                       |                                                                                     |
| 5.8                                | 610                               | 157.09   | 9100                                           | 1.00                               | FA                                                                                 | 57    | DRS | 71M6 | 32                    | 410                                                                                 |
| 6.6                                | 530                               | 136.16   | 9700                                           | 1.15                               | FAF                                                                                | 57    | DRS | 71M6 | 37                    | 409                                                                                 |
| 7.1                                | 495                               | 127.27   | 9940                                           | 1.20                               | F                                                                                  | 57    | DRS | 71M6 | 32                    | 408                                                                                 |
| 8.2                                | 425                               | 110.01   | 10400                                          | 1.40                               | FF                                                                                 | 57    | DRS | 71M6 | 38                    | 409                                                                                 |
| 6.9                                | 510                               | 199.70   | 9850                                           | 1.15                               |                                                                                    |       |     |      |                       |                                                                                     |
| 7.5                                | 470                               | 183.60   | 10100                                          | 1.30                               |                                                                                    |       |     |      |                       |                                                                                     |
| 8.8                                | 400                               | 157.09   | 10600                                          | 1.50                               | FA                                                                                 | 57    | DRS | 71S4 | 31                    | 410                                                                                 |
| 10                                 | 345                               | 136.16   | 10900                                          | 1.70                               | FAF                                                                                | 57    | DRS | 71S4 | 36                    | 409                                                                                 |
| 11                                 | 325                               | 127.27   | 11000                                          | 1.85                               | F                                                                                  | 57    | DRS | 71S4 | 31                    | 408                                                                                 |
| 13                                 | 280                               | 110.01   | 11200                                          | 2.1                                | FF                                                                                 | 57    | DRS | 71S4 | 37                    | 409                                                                                 |
| 15                                 | 235                               | 93.47    | 11500                                          | 2.5                                |                                                                                    |       |     |      |                       |                                                                                     |
| 17                                 | 210                               | 83.46    | 11500                                          | 2.8                                |                                                                                    |       |     |      |                       |                                                                                     |
| 9.2                                | 380                               | 150.06   | 6140                                           | 1.05                               | FA                                                                                 | 47    | DRS | 71S4 | 24                    | 404                                                                                 |
| 11                                 | 330                               | 130.07   | 6740                                           | 1.20                               | FAF                                                                                | 47    | DRS | 71S4 | 26                    | 403                                                                                 |
| 13                                 | 265                               | 105.09   | 7320                                           | 1.50                               | F                                                                                  | 47    | DRS | 71S4 | 24                    | 402                                                                                 |
| 15                                 | 225                               | 89.29    | 7600                                           | 1.75                               | FF                                                                                 | 47    | DRS | 71S4 | 27                    | 403                                                                                 |
| 17                                 | 200                               | 79.72    | 7750                                           | 1.95                               |                                                                                    |       |     |      |                       |                                                                                     |
| 20                                 | 174                               | 68.09    | 7900                                           | 2.3                                |                                                                                    |       |     |      |                       |                                                                                     |
| 21                                 | 167                               | 65.36    | 7930                                           | 2.4                                |                                                                                    |       |     |      |                       |                                                                                     |

| P <sub>m</sub> = 0.37 kW |                      |       |                                    |                       |                                                                                    |    |     |      |         |                                                                                     |
|--------------------------|----------------------|-------|------------------------------------|-----------------------|------------------------------------------------------------------------------------|----|-----|------|---------|-------------------------------------------------------------------------------------|
| n <sub>a</sub><br>rpm    | M <sub>a</sub><br>Nm | i     | F <sub>Ra</sub> <sup>1)</sup><br>N | SEW<br>f <sub>B</sub> |  |    |     |      | m<br>kg |  |
| 16                       | 220                  | 86.53 | 3960                               | 0.90                  |                                                                                    |    |     |      |         |                                                                                     |
| 17                       | 205                  | 80.65 | 4200                               | 0.95                  |                                                                                    |    |     |      |         |                                                                                     |
| 20                       | 180                  | 70.50 | 4550                               | 1.10                  |                                                                                    |    |     |      |         |                                                                                     |
| 21                       | 169                  | 66.09 | 4680                               | 1.20                  |                                                                                    |    |     |      |         |                                                                                     |
| 24                       | 149                  | 58.32 | 4880                               | 1.35                  |                                                                                    |    |     |      |         |                                                                                     |
| 25                       | 140                  | 54.54 | 4970                               | 1.45                  |                                                                                    |    |     |      |         |                                                                                     |
| 27                       | 132                  | 51.70 | 5030                               | 1.50                  |                                                                                    |    |     |      |         |                                                                                     |
| 29                       | 120                  | 47.02 | 5120                               | 1.65                  |                                                                                    |    |     |      |         |                                                                                     |
| 31                       | 112                  | 43.83 | 5180                               | 1.80                  |                                                                                    |    |     |      |         |                                                                                     |
| 36                       | 98                   | 38.31 | 5270                               | 2.0                   |                                                                                    |    |     |      |         |                                                                                     |
| 38                       | 92                   | 35.91 | 5300                               | 2.2                   |                                                                                    |    |     |      |         |                                                                                     |
| 44                       | 81                   | 31.69 | 5300                               | 2.5                   |                                                                                    |    |     |      |         |                                                                                     |
| 49                       | 72                   | 28.09 | 5140                               | 2.8                   |                                                                                    |    |     |      |         |                                                                                     |
| 58                       | 61                   | 23.88 | 4930                               | 3.3                   |                                                                                    |    |     |      |         |                                                                                     |
| 24                       | 145                  | 56.62 | 4080                               | 0.90                  | FA                                                                                 | 27 | DRS | 71S4 | 13      | 393                                                                                 |
| 28                       | 128                  | 50.19 | 4010                               | 1.00                  | FAF                                                                                | 27 | DRS | 71S4 | 13      | 392                                                                                 |
| 30                       | 120                  | 46.78 | 3970                               | 1.10                  | F                                                                                  | 27 | DRS | 71S4 | 13      | 391                                                                                 |
| 34                       | 105                  | 40.89 | 3880                               | 1.25                  | FF                                                                                 | 27 | DRS | 71S4 | 14      | 392                                                                                 |
| 36                       | 98                   | 38.33 | 3840                               | 1.35                  |                                                                                    |    |     |      |         |                                                                                     |
| 41                       | 87                   | 33.83 | 3750                               | 1.50                  |                                                                                    |    |     |      |         |                                                                                     |
| 47                       | 76                   | 29.56 | 3650                               | 1.70                  |                                                                                    |    |     |      |         |                                                                                     |
| 51                       | 70                   | 27.18 | 3580                               | 1.85                  |                                                                                    |    |     |      |         |                                                                                     |
| 59                       | 60                   | 23.25 | 3460                               | 2.2                   |                                                                                    |    |     |      |         |                                                                                     |
| 68                       | 52                   | 20.15 | 3340                               | 2.5                   |                                                                                    |    |     |      |         |                                                                                     |
| 73                       | 48                   | 18.84 | 3290                               | 2.7                   |                                                                                    |    |     |      |         |                                                                                     |
| 85                       | 42                   | 16.28 | 3170                               | 3.1                   |                                                                                    |    |     |      |         |                                                                                     |
| 100                      | 35                   | 13.84 | 3040                               | 3.7                   |                                                                                    |    |     |      |         |                                                                                     |
| 112                      | 32                   | 12.35 | 2950                               | 4.1                   |                                                                                    |    |     |      |         |                                                                                     |
| 131                      | 27                   | 10.55 | 2820                               | 4.8                   |                                                                                    |    |     |      |         |                                                                                     |
| 140                      | 25                   | 9.88  | 2770                               | 5.1                   |                                                                                    |    |     |      |         |                                                                                     |
| 147                      | 24                   | 9.40  | 2710                               | 5.4                   |                                                                                    |    |     |      |         |                                                                                     |
| 170                      | 21                   | 8.13  | 2600                               | 5.9                   |                                                                                    |    |     |      |         |                                                                                     |
| 200                      | 18                   | 6.91  | 2490                               | 6.4                   |                                                                                    |    |     |      |         |                                                                                     |
| 224                      | 16                   | 6.17  | 2410                               | 6.9                   |                                                                                    |    |     |      |         |                                                                                     |
| 262                      | 14                   | 5.27  | 2300                               | 7.4                   |                                                                                    |    |     |      |         |                                                                                     |
| 280                      | 13                   | 4.93  | 2250                               | 7.6                   |                                                                                    |    |     |      |         |                                                                                     |
| 332                      | 11                   | 4.16  | 2140                               | 8.2                   |                                                                                    |    |     |      |         |                                                                                     |
| 326                      | 11                   | 8.13  | 2150                               | 11                    | FA                                                                                 | 27 | DR  | 63L2 | 10      | 393                                                                                 |
| 384                      | 9.2                  | 6.91  | 2050                               | 12                    | FAF                                                                                | 27 | DR  | 63L2 | 11      | 392                                                                                 |
| 430                      | 8.2                  | 6.17  | 1980                               | 13                    | F                                                                                  | 27 | DR  | 63L2 | 11      | 391                                                                                 |
| 503                      | 7.0                  | 5.27  | 1890                               | 14                    | FF                                                                                 | 27 | DR  | 63L2 | 12      | 392                                                                                 |
| 537                      | 6.6                  | 4.93  | 1850                               | 15                    |                                                                                    |    |     |      |         |                                                                                     |
| 638                      | 5.5                  | 4.16  | 1750                               | 16                    |                                                                                    |    |     |      |         |                                                                                     |


| P <sub>m</sub> = 0.55 kW |                      |      |                                    |                       |                                                                                      |        |     |      |         |                                                                                       |
|--------------------------|----------------------|------|------------------------------------|-----------------------|--------------------------------------------------------------------------------------|--------|-----|------|---------|---------------------------------------------------------------------------------------|
| n <sub>a</sub><br>rpm    | M <sub>a</sub><br>Nm | i    | F <sub>Ra</sub> <sup>1)</sup><br>N | SEW<br>f <sub>B</sub> |  |        |     |      | m<br>kg |  |
| 0.22                     | 20500                | 6295 | 91800                              | 0.90                  | FA                                                                                   | 157R97 | DRS | 71M4 | 770     | 456                                                                                   |
| 0.25                     | 17100                | 5404 | 102700                             | 1.05                  | FAF                                                                                  | 157R97 | DRS | 71M4 | 830     | 456                                                                                   |
| 0.49                     | 8820                 | 2780 | 118800                             | 2.0                   | F                                                                                    | 157R97 | DRS | 71M4 | 790     | 456                                                                                   |
|                          |                      |      |                                    |                       | FF                                                                                   | 157R97 | DRS | 71M4 | 900     | 456                                                                                   |
| 0.56                     | 7790                 | 2427 | 120000                             | 2.3                   | FA                                                                                   | 157R97 | DRS | 71M4 | 760     | 456                                                                                   |
| 0.81                     | 5530                 | 1674 | 120000                             | 3.2                   | FAF                                                                                  | 157R97 | DRS | 71M4 | 820     | 456                                                                                   |
| 1.0                      | 4270                 | 1308 | 120000                             | 4.2                   | F                                                                                    | 157R97 | DRS | 71M4 | 790     | 456                                                                                   |
| 1.2                      | 3750                 | 1169 | 120000                             | 4.8                   | FF                                                                                   | 157R97 | DRS | 71M4 | 890     | 456                                                                                   |
| 0.35                     | 13400                | 3926 | 87700                              | 0.90                  | FA                                                                                   | 127R77 | DRS | 71M4 | 430     | 456                                                                                   |
| 0.39                     | 11700                | 3454 | 90000                              | 1.00                  | FAF                                                                                  | 127R77 | DRS | 71M4 | 465     | 456                                                                                   |
| 0.45                     | 10200                | 3031 | 90000                              | 1.15                  | F                                                                                    | 127R77 | DRS | 71M4 | 465     | 456                                                                                   |
|                          |                      |      |                                    |                       | FF                                                                                   | 127R77 | DRS | 71M4 | 510     | 456                                                                                   |

**P<sub>m</sub> = 0.55 kW**


| n <sub>a</sub><br>rpm | M <sub>a</sub><br>Nm | i       | F <sub>Ra</sub> <sup>1)</sup><br>N | SEW<br>f <sub>B</sub> |  |        |     |      | m<br>kg |  |
|-----------------------|----------------------|---------|------------------------------------|-----------------------|------------------------------------------------------------------------------------|--------|-----|------|---------|-------------------------------------------------------------------------------------|
| 0.57                  | 8240                 | 2369    | 48300                              | 0.95                  |                                                                                    |        |     |      |         |                                                                                     |
| 0.66                  | 7200                 | 2068    | 51100                              | 1.05                  |                                                                                    |        |     |      |         |                                                                                     |
| 0.74                  | 6190                 | 1826    | 53600                              | 1.25                  |                                                                                    |        |     |      |         |                                                                                     |
| 0.85                  | 5530                 | 1597    | 55100                              | 1.40                  | FA                                                                                 | 107R77 | DRS | 71M4 | 275     | 456                                                                                 |
| 0.97                  | 4820                 | 1401    | 56700                              | 1.60                  | FAF                                                                                | 107R77 | DRS | 71M4 | 300     | 456                                                                                 |
| 1.1                   | 4210                 | 1243    | 58000                              | 1.80                  | F                                                                                  | 107R77 | DRS | 71M4 | 295     | 456                                                                                 |
| 1.2                   | 3760                 | 1087    | 58900                              | 2.0                   | FF                                                                                 | 107R77 | DRS | 71M4 | 320     | 456                                                                                 |
| 1.4                   | 3220                 | 950     | 60000                              | 2.4                   |                                                                                    |        |     |      |         |                                                                                     |
| 1.6                   | 2800                 | 834     | 60800                              | 2.7                   |                                                                                    |        |     |      |         |                                                                                     |
| 2.1                   | 2180                 | 640     | 61900                              | 3.5                   |                                                                                    |        |     |      |         |                                                                                     |
| 1.0                   | 4620                 | 1327    | 28900                              | 0.95                  |                                                                                    |        |     |      |         |                                                                                     |
| 1.2                   | 4150                 | 1171    | 30300                              | 1.05                  |                                                                                    |        |     |      |         |                                                                                     |
| 1.3                   | 3620                 | 1022    | 31800                              | 1.20                  |                                                                                    |        |     |      |         |                                                                                     |
| 1.5                   | 3100                 | 898     | 33100                              | 1.40                  | FA                                                                                 | 97R57  | DRS | 71M4 | 185     | 456                                                                                 |
| 1.7                   | 2740                 | 784     | 33900                              | 1.55                  | FAF                                                                                | 97R57  | DRS | 71M4 | 210     | 456                                                                                 |
| 2.0                   | 2380                 | 690     | 34600                              | 1.80                  | F                                                                                  | 97R57  | DRS | 71M4 | 195     | 456                                                                                 |
| 2.2                   | 2100                 | 605     | 35200                              | 2.0                   | FF                                                                                 | 97R57  | DRS | 71M4 | 225     | 456                                                                                 |
| 2.6                   | 1820                 | 529     | 35700                              | 2.4                   |                                                                                    |        |     |      |         |                                                                                     |
| 2.9                   | 1610                 | 467     | 36100                              | 2.7                   |                                                                                    |        |     |      |         |                                                                                     |
| 3.4                   | 1380                 | 406     | 36500                              | 3.1                   |                                                                                    |        |     |      |         |                                                                                     |
| 3.7                   | 1240                 | 363     | 36700                              | 3.5                   |                                                                                    |        |     |      |         |                                                                                     |
| 1.5                   | 3100                 | 887     | 15200                              | 0.95                  |                                                                                    |        |     |      |         |                                                                                     |
| 1.7                   | 2710                 | 780     | 24000                              | 1.10                  | FA                                                                                 | 87R57  | DRS | 71M4 | 120     | 456                                                                                 |
| 2.0                   | 2330                 | 674     | 25400                              | 1.30                  | FAF                                                                                | 87R57  | DRS | 71M4 | 135     | 456                                                                                 |
| 2.2                   | 2120                 | 609     | 26100                              | 1.40                  | F                                                                                  | 87R57  | DRS | 71M4 | 125     | 456                                                                                 |
| 2.6                   | 1790                 | 515     | 27000                              | 1.70                  | FF                                                                                 | 87R57  | DRS | 71M4 | 140     | 456                                                                                 |
| 3.0                   | 1570                 | 452     | 27600                              | 1.90                  |                                                                                    |        |     |      |         |                                                                                     |
| 3.9                   | 1180                 | 345     | 28600                              | 2.5                   |                                                                                    |        |     |      |         |                                                                                     |
| 2.8                   | 1690                 | 480     | 14300                              | 0.90                  | FA                                                                                 | 77R37  | DRS | 71M4 | 69      | 456                                                                                 |
| 3.3                   | 1440                 | 413     | 16100                              | 1.05                  | FAF                                                                                | 77R37  | DRS | 71M4 | 76      | 456                                                                                 |
| 3.7                   | 1290                 | 367     | 17000                              | 1.15                  | F                                                                                  | 77R37  | DRS | 71M4 | 73      | 456                                                                                 |
| 4.2                   | 1140                 | 323     | 17700                              | 1.30                  | FF                                                                                 | 77R37  | DRS | 71M4 | 83      | 456                                                                                 |
| 5.3                   | 900                  | 257     | 9470                               | 0.90                  | FA                                                                                 | 67R37  | DRS | 71M4 | 47      | 456                                                                                 |
| 5.9                   | 800                  | 231     | 10400                              | 1.00                  | FAF                                                                                | 67R37  | DRS | 71M4 | 53      | 456                                                                                 |
| 6.6                   | 720                  | 205     | 11100                              | 1.15                  | F                                                                                  | 67R37  | DRS | 71M4 | 50      | 456                                                                                 |
| 7.8                   | 610                  | 175     | 11800                              | 1.35                  | FF                                                                                 | 67R37  | DRS | 71M4 | 56      | 456                                                                                 |
| 3.4                   | 1550                 | 270.68  | 27700                              | 1.95                  | FA                                                                                 | 87     | DRS | 80S6 | 100     | 428                                                                                 |
| 3.6                   | 1460                 | 255.37  | 27900                              | 2.0                   | FAF                                                                                | 87     | DRS | 80S6 | 115     | 427                                                                                 |
| 4.0                   | 1310                 | 228.93  | 28300                              | 2.3                   | F                                                                                  | 87     | DRS | 80S6 | 105     | 426                                                                                 |
| 4.6                   | 1130                 | 197.20  | 28700                              | 2.6                   | FF                                                                                 | 87     | DRS | 80S6 | 120     | 427                                                                                 |
| 5.1                   | 1030                 | 179.97  | 28900                              | 2.9                   |                                                                                    |        |     |      |         |                                                                                     |
| 4.0                   | 1290                 | 225.79  | 17000                              | 1.15                  | FA                                                                                 | 77     | DRS | 80S6 | 62      | 422                                                                                 |
| 4.6                   | 1130                 | 198.31  | 17700                              | 1.30                  | FAF                                                                                | 77     | DRS | 80S6 | 69      | 421                                                                                 |
| 4.9                   | 1080                 | 188.40  | 18000                              | 1.40                  | F                                                                                  | 77     | DRS | 80S6 | 66      | 420                                                                                 |
|                       |                      |         |                                    |                       | FF                                                                                 | 77     | DRS | 80S6 | 77      | 421                                                                                 |
| 5.5                   | 950                  | 166.47  | 18500                              | 1.55                  | FA                                                                                 | 77     | DRS | 80S6 | 62      | 422                                                                                 |
| 6.4                   | 810                  | 142.27  | 18900                              | 1.85                  | FAF                                                                                | 77     | DRS | 80S6 | 69      | 421                                                                                 |
| 7.0                   | 745                  | 130.42  | 19100                              | 2.0                   | F                                                                                  | 77     | DRS | 80S6 | 66      | 420                                                                                 |
|                       |                      |         |                                    |                       | FF                                                                                 | 77     | DRS | 80S6 | 77      | 421                                                                                 |
| 6.0                   | 870                  | 225.79  | 18800                              | 1.70                  |                                                                                    |        |     |      |         |                                                                                     |
| 6.9                   | 765                  | 198.31  | 19100                              | 1.95                  |                                                                                    |        |     |      |         |                                                                                     |
| 7.2                   | 725                  | 188.40  | 19200                              | 2.1                   | FA                                                                                 | 77     | DRS | 71M4 | 60      | 422                                                                                 |
| 8.2                   | 640                  | 166.47  | 19400                              | 2.3                   | FAF                                                                                | 77     | DRS | 71M4 | 66      | 421                                                                                 |
| 9.6                   | 545                  | 142.27  | 19600                              | 2.7                   | F                                                                                  | 77     | DRS | 71M4 | 64      | 420                                                                                 |
| 10                    | 500                  | 130.42  | 19700                              | 3.0                   | FF                                                                                 | 77     | DRS | 71M4 | 74      | 421                                                                                 |
| 12                    | 440                  | 114.45  | 19800                              | 3.4                   |                                                                                    |        |     |      |         |                                                                                     |
| 13                    | 415                  | 108.46* | 19800                              | 3.6                   |                                                                                    |        |     |      |         |                                                                                     |
| 14                    | 365                  | 94.93   | 19900                              | 4.1                   |                                                                                    |        |     |      |         |                                                                                     |

| P <sub>m</sub> = 0.55 kW |                      |        |                                    |                       |                                                                                    |  |  |  |         |                                                                                     |
|--------------------------|----------------------|--------|------------------------------------|-----------------------|------------------------------------------------------------------------------------|--|--|--|---------|-------------------------------------------------------------------------------------|
| n <sub>a</sub><br>rpm    | M <sub>a</sub><br>Nm | i      | F <sub>Ra</sub> <sup>1)</sup><br>N | SEW<br>f <sub>B</sub> |  |  |  |  | m<br>kg |  |
| 7.0                      | 750                  | 195.39 | 10900                              | 1.10                  |                                                                                    |  |  |  |         |                                                                                     |
| 8.0                      | 655                  | 170.85 | 11500                              | 1.25                  |                                                                                    |  |  |  |         |                                                                                     |
| 8.4                      | 625                  | 162.31 | 11700                              | 1.30                  |                                                                                    |  |  |  |         |                                                                                     |
| 9.6                      | 545                  | 142.40 | 12200                              | 1.50                  |                                                                                    |  |  |  |         |                                                                                     |
| 11                       | 465                  | 120.79 | 12600                              | 1.75                  |                                                                                    |  |  |  |         |                                                                                     |
| 12                       | 420                  | 109.04 | 12700                              | 1.95                  |                                                                                    |  |  |  |         |                                                                                     |
| 14                       | 370                  | 95.94  | 12900                              | 2.2                   |                                                                                    |  |  |  |         |                                                                                     |
| 15                       | 345                  | 90.59  | 13000                              | 2.3                   |                                                                                    |  |  |  |         |                                                                                     |
| 17                       | 305                  | 79.76  | 13000                              | 2.7                   |                                                                                    |  |  |  |         |                                                                                     |
| 8.7                      | 605                  | 157.09 | 9150                               | 1.00                  |                                                                                    |  |  |  |         |                                                                                     |
| 10.0                     | 525                  | 136.16 | 9740                               | 1.15                  |                                                                                    |  |  |  |         |                                                                                     |
| 11                       | 490                  | 127.27 | 9980                               | 1.20                  |                                                                                    |  |  |  |         |                                                                                     |
| 12                       | 420                  | 110.01 | 10400                              | 1.40                  |                                                                                    |  |  |  |         |                                                                                     |
| 15                       | 360                  | 93.47  | 10800                              | 1.65                  |                                                                                    |  |  |  |         |                                                                                     |
| 16                       | 320                  | 83.46  | 11000                              | 1.85                  |                                                                                    |  |  |  |         |                                                                                     |
| 19                       | 280                  | 72.98  | 11200                              | 2.1                   |                                                                                    |  |  |  |         |                                                                                     |
| 20                       | 260                  | 68.22  | 11300                              | 2.3                   |                                                                                    |  |  |  |         |                                                                                     |
| 23                       | 225                  | 58.97  | 11500                              | 2.6                   |                                                                                    |  |  |  |         |                                                                                     |
| 13                       | 405                  | 105.09 | 5840                               | 1.00                  |                                                                                    |  |  |  |         |                                                                                     |
| 15                       | 340                  | 89.29  | 6620                               | 1.15                  |                                                                                    |  |  |  |         |                                                                                     |
| 17                       | 305                  | 79.72  | 6990                               | 1.30                  |                                                                                    |  |  |  |         |                                                                                     |
| 20                       | 260                  | 68.09  | 7360                               | 1.50                  |                                                                                    |  |  |  |         |                                                                                     |
| 21                       | 250                  | 65.36  | 7440                               | 1.60                  |                                                                                    |  |  |  |         |                                                                                     |
| 24                       | 215                  | 56.49  | 7670                               | 1.85                  |                                                                                    |  |  |  |         |                                                                                     |
| 28                       | 185                  | 48.00* | 7850                               | 2.2                   |                                                                                    |  |  |  |         |                                                                                     |
| 32                       | 166                  | 42.86  | 7940                               | 2.4                   |                                                                                    |  |  |  |         |                                                                                     |
| 23                       | 225                  | 58.32  | 3890                               | 0.90                  |                                                                                    |  |  |  |         |                                                                                     |
| 25                       | 210                  | 54.54  | 4140                               | 0.95                  |                                                                                    |  |  |  |         |                                                                                     |
| 26                       | 200                  | 51.70  | 4300                               | 1.00                  |                                                                                    |  |  |  |         |                                                                                     |
| 29                       | 182                  | 47.02  | 4540                               | 1.10                  |                                                                                    |  |  |  |         |                                                                                     |
| 31                       | 169                  | 43.83  | 4680                               | 1.20                  |                                                                                    |  |  |  |         |                                                                                     |
| 36                       | 148                  | 38.31  | 4900                               | 1.35                  |                                                                                    |  |  |  |         |                                                                                     |
| 38                       | 139                  | 35.91  | 4980                               | 1.45                  |                                                                                    |  |  |  |         |                                                                                     |
| 43                       | 122                  | 31.69  | 4990                               | 1.65                  |                                                                                    |  |  |  |         |                                                                                     |
| 48                       | 108                  | 28.09  | 4870                               | 1.85                  |                                                                                    |  |  |  |         |                                                                                     |
| 57                       | 92                   | 23.88  | 4700                               | 2.2                   |                                                                                    |  |  |  |         |                                                                                     |
| 58                       | 91                   | 23.63  | 4690                               | 2.2                   |                                                                                    |  |  |  |         |                                                                                     |
| 66                       | 79                   | 20.57  | 4540                               | 2.5                   |                                                                                    |  |  |  |         |                                                                                     |
| 71                       | 74                   | 19.27  | 4470                               | 2.7                   |                                                                                    |  |  |  |         |                                                                                     |
| 80                       | 66                   | 17.03  | 4340                               | 3.0                   |                                                                                    |  |  |  |         |                                                                                     |
| 95                       | 55                   | 14.33  | 4150                               | 3.6                   |                                                                                    |  |  |  |         |                                                                                     |
| 36                       | 144                  | 77.21  | 3410                               | 0.90                  |                                                                                    |  |  |  |         |                                                                                     |
| 39                       | 135                  | 72.37  | 3390                               | 0.95                  |                                                                                    |  |  |  |         |                                                                                     |
| 44                       | 119                  | 63.86  | 3350                               | 1.10                  |                                                                                    |  |  |  |         |                                                                                     |
| 50                       | 106                  | 56.62  | 3290                               | 1.25                  |                                                                                    |  |  |  |         |                                                                                     |
| 56                       | 94                   | 50.19  | 3230                               | 1.40                  |                                                                                    |  |  |  |         |                                                                                     |
| 58                       | 90                   | 23.25  | 3210                               | 1.45                  |                                                                                    |  |  |  |         |                                                                                     |
| 67                       | 78                   | 20.15  | 3130                               | 1.65                  |                                                                                    |  |  |  |         |                                                                                     |
| 72                       | 73                   | 18.84  | 3090                               | 1.80                  |                                                                                    |  |  |  |         |                                                                                     |
| 84                       | 63                   | 16.28  | 3000                               | 2.1                   |                                                                                    |  |  |  |         |                                                                                     |
| 98                       | 53                   | 13.84  | 2900                               | 2.4                   |                                                                                    |  |  |  |         |                                                                                     |
| 110                      | 48                   | 12.35  | 2820                               | 2.7                   |                                                                                    |  |  |  |         |                                                                                     |
| 129                      | 41                   | 10.55  | 2720                               | 3.2                   |                                                                                    |  |  |  |         |                                                                                     |
| 138                      | 38                   | 9.88   | 2670                               | 3.4                   |                                                                                    |  |  |  |         |                                                                                     |
| 145                      | 36                   | 9.40   | 2610                               | 3.6                   |                                                                                    |  |  |  |         |                                                                                     |
| 167                      | 31                   | 8.13   | 2510                               | 3.9                   |                                                                                    |  |  |  |         |                                                                                     |
| 197                      | 27                   | 6.91   | 2410                               | 4.3                   |                                                                                    |  |  |  |         |                                                                                     |
| 221                      | 24                   | 6.17   | 2340                               | 4.6                   |                                                                                    |  |  |  |         |                                                                                     |
| 258                      | 20                   | 5.27   | 2240                               | 4.9                   |                                                                                    |  |  |  |         |                                                                                     |
| 276                      | 19                   | 4.93   | 2200                               | 5.0                   |                                                                                    |  |  |  |         |                                                                                     |
| 327                      | 16                   | 4.16   | 2100                               | 5.4                   |                                                                                    |  |  |  |         |                                                                                     |

**P<sub>m</sub> = 0.55 kW**


| n <sub>a</sub><br>rpm | M <sub>a</sub><br>Nm | i    | F <sub>Ra</sub> <sup>1)</sup><br>N | SEW<br>f <sub>B</sub> |  |    |     |      | m<br>kg |  |
|-----------------------|----------------------|------|------------------------------------|-----------------------|------------------------------------------------------------------------------------|----|-----|------|---------|-------------------------------------------------------------------------------------|
| 346                   | 15                   | 8.13 | 2070                               | 8.1                   |                                                                                    |    |     |      |         |                                                                                     |
| 407                   | 13                   | 6.91 | 1970                               | 8.8                   | FA                                                                                 | 27 | DRS | 71M2 | 13      | 393                                                                                 |
| 456                   | 12                   | 6.17 | 1910                               | 9.5                   | FAF                                                                                | 27 | DRS | 71M2 | 14      | 392                                                                                 |
| 533                   | 9.8                  | 5.27 | 1820                               | 10                    | F                                                                                  | 27 | DRS | 71M2 | 14      | 391                                                                                 |
| 570                   | 9.2                  | 4.93 | 1790                               | 10                    | FF                                                                                 | 27 | DRS | 71M2 | 15      | 392                                                                                 |
| 676                   | 7.8                  | 4.16 | 1700                               | 11                    |                                                                                    |    |     |      |         |                                                                                     |

**P<sub>m</sub> = 0.75 kW**


| n <sub>a</sub><br>rpm | M <sub>a</sub><br>Nm | i      | F <sub>Ra</sub> <sup>1)</sup><br>N | SEW<br>f <sub>B</sub> |  |        |     |      | m<br>kg |  |
|-----------------------|----------------------|--------|------------------------------------|-----------------------|------------------------------------------------------------------------------------|--------|-----|------|---------|-------------------------------------------------------------------------------------|
| 0.52                  | 11600                | 2780   | 114700                             | 1.55                  | FA                                                                                 | 157R97 | DRN | 80M4 | 770     | 456                                                                                 |
|                       |                      |        |                                    |                       | FAF                                                                                | 157R97 | DRN | 80M4 | 830     | 456                                                                                 |
|                       |                      |        |                                    |                       | F                                                                                  | 157R97 | DRN | 80M4 | 790     | 456                                                                                 |
|                       |                      |        |                                    |                       | FF                                                                                 | 157R97 | DRN | 80M4 | 900     | 456                                                                                 |
| 0.59                  | 10300                | 2427   | 116800                             | 1.75                  | FA                                                                                 | 157R97 | DRN | 80M4 | 770     | 456                                                                                 |
| 0.86                  | 7280                 | 1674   | 120000                             | 2.5                   | FAF                                                                                | 157R97 | DRN | 80M4 | 830     | 456                                                                                 |
| 1.1                   | 5620                 | 1308   | 120000                             | 3.2                   | F                                                                                  | 157R97 | DRN | 80M4 | 790     | 456                                                                                 |
| 1.2                   | 4960                 | 1169   | 120000                             | 3.6                   | FF                                                                                 | 157R97 | DRN | 80M4 | 900     | 456                                                                                 |
| 0.48                  | 13400                | 3031   | 87700                              | 0.90                  | FA                                                                                 | 127R77 | DRN | 80M4 | 435     | 456                                                                                 |
|                       |                      |        |                                    |                       | FAF                                                                                | 127R77 | DRN | 80M4 | 470     | 456                                                                                 |
|                       |                      |        |                                    |                       | F                                                                                  | 127R77 | DRN | 80M4 | 470     | 456                                                                                 |
|                       |                      |        |                                    |                       | FF                                                                                 | 127R77 | DRN | 80M4 | 520     | 456                                                                                 |
| 0.54                  | 12000                | 2672   | 90000                              | 1.00                  | FA                                                                                 | 127R77 | DRN | 80M4 | 435     | 456                                                                                 |
| 0.61                  | 10500                | 2357   | 90000                              | 1.15                  | FAF                                                                                | 127R77 | DRN | 80M4 | 470     | 456                                                                                 |
| 0.71                  | 9120                 | 2038   | 90000                              | 1.30                  | F                                                                                  | 127R77 | DRN | 80M4 | 470     | 456                                                                                 |
| 0.81                  | 7940                 | 1784   | 90000                              | 1.50                  | FF                                                                                 | 127R77 | DRN | 80M4 | 510     | 456                                                                                 |
| 0.90                  | 7120                 | 1606   | 90000                              | 1.70                  |                                                                                    |        |     |      |         |                                                                                     |
| 0.79                  | 8090                 | 1826   | 48700                              | 0.95                  |                                                                                    |        |     |      |         |                                                                                     |
| 0.90                  | 7200                 | 1597   | 51100                              | 1.05                  |                                                                                    |        |     |      |         |                                                                                     |
| 1.0                   | 6280                 | 1401   | 53300                              | 1.20                  |                                                                                    |        |     |      |         |                                                                                     |
| 1.2                   | 5510                 | 1243   | 55200                              | 1.40                  | FA                                                                                 | 107R77 | DRN | 80M4 | 280     | 456                                                                                 |
| 1.3                   | 4900                 | 1087   | 56500                              | 1.55                  | FAF                                                                                | 107R77 | DRN | 80M4 | 305     | 456                                                                                 |
| 1.5                   | 4210                 | 950    | 58000                              | 1.80                  | F                                                                                  | 107R77 | DRN | 80M4 | 300     | 456                                                                                 |
| 1.7                   | 3670                 | 834    | 59100                              | 2.1                   | FF                                                                                 | 107R77 | DRN | 80M4 | 325     | 456                                                                                 |
| 2.2                   | 2850                 | 640    | 60700                              | 2.7                   |                                                                                    |        |     |      |         |                                                                                     |
| 3.3                   | 1940                 | 436    | 62300                              | 4.0                   |                                                                                    |        |     |      |         |                                                                                     |
| 1.4                   | 4690                 | 1022   | 26900                              | 0.90                  |                                                                                    |        |     |      |         |                                                                                     |
| 1.6                   | 4040                 | 898    | 30600                              | 1.05                  |                                                                                    |        |     |      |         |                                                                                     |
| 1.8                   | 3560                 | 784    | 31900                              | 1.20                  |                                                                                    |        |     |      |         |                                                                                     |
| 2.1                   | 3100                 | 690    | 33100                              | 1.40                  | FA                                                                                 | 97R57  | DRN | 80M4 | 190     | 456                                                                                 |
| 2.4                   | 2730                 | 605    | 33900                              | 1.55                  | FAF                                                                                | 97R57  | DRN | 80M4 | 215     | 456                                                                                 |
| 2.7                   | 2370                 | 529    | 34700                              | 1.80                  | F                                                                                  | 97R57  | DRN | 80M4 | 200     | 456                                                                                 |
| 3.1                   | 2090                 | 467    | 35200                              | 2.0                   | FF                                                                                 | 97R57  | DRN | 80M4 | 230     | 456                                                                                 |
| 3.6                   | 1800                 | 406    | 35700                              | 2.4                   |                                                                                    |        |     |      |         |                                                                                     |
| 4.0                   | 1620                 | 363    | 36100                              | 2.6                   |                                                                                    |        |     |      |         |                                                                                     |
| 2.1                   | 3030                 | 674    | 18400                              | 1.00                  | FA                                                                                 | 87R57  | DRN | 80M4 | 125     | 456                                                                                 |
| 2.4                   | 2750                 | 609    | 23900                              | 1.10                  | FAF                                                                                | 87R57  | DRN | 80M4 | 140     | 456                                                                                 |
| 2.8                   | 2320                 | 515    | 25400                              | 1.30                  | F                                                                                  | 87R57  | DRN | 80M4 | 130     | 456                                                                                 |
| 3.2                   | 2040                 | 452    | 26300                              | 1.45                  | FF                                                                                 | 87R57  | DRN | 80M4 | 145     | 456                                                                                 |
| 4.2                   | 1540                 | 345    | 27700                              | 1.95                  |                                                                                    |        |     |      |         |                                                                                     |
| 3.9                   | 1670                 | 367    | 14400                              | 0.90                  | FA                                                                                 | 77R37  | DRN | 80M4 | 74      | 456                                                                                 |
| 4.5                   | 1480                 | 323    | 15800                              | 1.00                  | FAF                                                                                | 77R37  | DRN | 80M4 | 80      | 456                                                                                 |
| 5.2                   | 1270                 | 280    | 17000                              | 1.15                  | F                                                                                  | 77R37  | DRN | 80M4 | 77      | 456                                                                                 |
|                       |                      |        |                                    |                       | FF                                                                                 | 77R37  | DRN | 80M4 | 88      | 456                                                                                 |
| 5.3                   | 1340                 | 270.68 | 28200                              | 2.2                   | FA                                                                                 | 87     | DRN | 80M4 | 105     | 428                                                                                 |
| 5.6                   | 1270                 | 255.37 | 28400                              | 2.4                   | FAF                                                                                | 87     | DRN | 80M4 | 115     | 427                                                                                 |
| 6.3                   | 1130                 | 228.93 | 28700                              | 2.6                   | F                                                                                  | 87     | DRN | 80M4 | 110     | 426                                                                                 |
|                       |                      |        |                                    |                       | FF                                                                                 | 87     | DRN | 80M4 | 125     | 427                                                                                 |
| 6.4                   | 1120                 | 225.79 | 17800                              | 1.35                  | FA                                                                                 | 77     | DRN | 80M4 | 65      | 422                                                                                 |
| 7.3                   | 980                  | 198.31 | 18400                              | 1.50                  | FAF                                                                                | 77     | DRN | 80M4 | 71      | 421                                                                                 |
| 7.6                   | 930                  | 188.40 | 18500                              | 1.60                  | F                                                                                  | 77     | DRN | 80M4 | 68      | 420                                                                                 |
|                       |                      |        |                                    |                       | FF                                                                                 | 77     | DRN | 80M4 | 79      | 421                                                                                 |

21933170/DE – 11/2015




| <b>P<sub>m</sub> = 0.75 kW</b>     |                                   |          |                                                |                                    |                                                                                    |           |            |             |                       |                                                                                     |
|------------------------------------|-----------------------------------|----------|------------------------------------------------|------------------------------------|------------------------------------------------------------------------------------|-----------|------------|-------------|-----------------------|-------------------------------------------------------------------------------------|
| <b>n<sub>a</sub></b><br><b>rpm</b> | <b>M<sub>a</sub></b><br><b>Nm</b> | <b>i</b> | <b>F<sub>Ra</sub><sup>1)</sup></b><br><b>N</b> | <b>SEW</b><br><b>f<sub>B</sub></b> |  |           |            |             | <b>m</b><br><b>kg</b> |  |
| <b>8.6</b>                         | 820                               | 166.47   | 18900                                          | 1.80                               | <b>FA</b>                                                                          | <b>77</b> | <b>DRN</b> | <b>80M4</b> | 65                    | 422                                                                                 |
| <b>10</b>                          | 705                               | 142.27   | 19200                                          | 2.1                                | <b>FAF</b>                                                                         | <b>77</b> | <b>DRN</b> | <b>80M4</b> | 71                    | 421                                                                                 |
| <b>11</b>                          | 645                               | 130.42   | 19400                                          | 2.3                                | <b>F</b>                                                                           | <b>77</b> | <b>DRN</b> | <b>80M4</b> | 68                    | 420                                                                                 |
| <b>13</b>                          | 565                               | 114.45   | 19600                                          | 2.6                                | <b>FF</b>                                                                          | <b>77</b> | <b>DRN</b> | <b>80M4</b> | 79                    | 421                                                                                 |
| <b>13</b>                          | 535                               | 108.46*  | 19600                                          | 2.8                                |                                                                                    |           |            |             |                       |                                                                                     |
| <b>8.4</b>                         | 840                               | 170.85   | 10000                                          | 0.95                               | <b>FA</b>                                                                          | <b>67</b> | <b>DRN</b> | <b>80M4</b> | 41                    | 416                                                                                 |
| <b>8.9</b>                         | 800                               | 162.31   | 10400                                          | 1.00                               | <b>FAF</b>                                                                         | <b>67</b> | <b>DRN</b> | <b>80M4</b> | 47                    | 415                                                                                 |
| <b>10</b>                          | 705                               | 142.40   | 11200                                          | 1.15                               | <b>F</b>                                                                           | <b>67</b> | <b>DRN</b> | <b>80M4</b> | 43                    | 414                                                                                 |
| <b>12</b>                          | 600                               | 120.79   | 11900                                          | 1.35                               | <b>FF</b>                                                                          | <b>67</b> | <b>DRN</b> | <b>80M4</b> | 49                    | 415                                                                                 |
| <b>13</b>                          | 540                               | 109.04   | 12200                                          | 1.50                               |                                                                                    |           |            |             |                       |                                                                                     |
| <b>15</b>                          | 475                               | 95.94    | 12500                                          | 1.70                               | <b>FA</b>                                                                          | <b>67</b> | <b>DRN</b> | <b>80M4</b> | 41                    | 416                                                                                 |
| <b>16</b>                          | 450                               | 90.59    | 12600                                          | 1.80                               | <b>FAF</b>                                                                         | <b>67</b> | <b>DRN</b> | <b>80M4</b> | 47                    | 415                                                                                 |
| <b>18</b>                          | 395                               | 79.76    | 12800                                          | 2.1                                | <b>F</b>                                                                           | <b>67</b> | <b>DRN</b> | <b>80M4</b> | 43                    | 414                                                                                 |
| <b>21</b>                          | 335                               | 67.65    | 13000                                          | 2.4                                | <b>FF</b>                                                                          | <b>67</b> | <b>DRN</b> | <b>80M4</b> | 49                    | 415                                                                                 |
| <b>24</b>                          | 300                               | 61.07    | 13000                                          | 2.7                                |                                                                                    |           |            |             |                       |                                                                                     |
| <b>11</b>                          | 630                               | 127.27   | 7950                                           | 0.95                               |                                                                                    |           |            |             |                       |                                                                                     |
| <b>13</b>                          | 545                               | 110.01   | 9590                                           | 1.10                               | <b>FA</b>                                                                          | <b>57</b> | <b>DRN</b> | <b>80M4</b> | 37                    | 410                                                                                 |
| <b>15</b>                          | 460                               | 93.47    | 10200                                          | 1.30                               | <b>FAF</b>                                                                         | <b>57</b> | <b>DRN</b> | <b>80M4</b> | 42                    | 409                                                                                 |
| <b>17</b>                          | 415                               | 83.46    | 10500                                          | 1.45                               | <b>F</b>                                                                           | <b>57</b> | <b>DRN</b> | <b>80M4</b> | 37                    | 408                                                                                 |
| <b>20</b>                          | 360                               | 72.98    | 10800                                          | 1.65                               | <b>FF</b>                                                                          | <b>57</b> | <b>DRN</b> | <b>80M4</b> | 43                    | 409                                                                                 |
| <b>21</b>                          | 335                               | 68.22    | 10900                                          | 1.75                               |                                                                                    |           |            |             |                       |                                                                                     |
| <b>24</b>                          | 290                               | 58.97    | 11200                                          | 2.0                                |                                                                                    |           |            |             |                       |                                                                                     |
| <b>29</b>                          | 245                               | 50.10    | 11400                                          | 2.4                                |                                                                                    |           |            |             |                       |                                                                                     |
| <b>32</b>                          | 220                               | 44.73    | 11300                                          | 2.7                                |                                                                                    |           |            |             |                       |                                                                                     |
| <b>18</b>                          | 395                               | 79.72    | 5970                                           | 1.00                               | <b>FA</b>                                                                          | <b>47</b> | <b>DRN</b> | <b>80M4</b> | 29                    | 404                                                                                 |
| <b>21</b>                          | 335                               | 68.09    | 6680                                           | 1.20                               | <b>FAF</b>                                                                         | <b>47</b> | <b>DRN</b> | <b>80M4</b> | 32                    | 403                                                                                 |
| <b>22</b>                          | 325                               | 65.36    | 6820                                           | 1.25                               | <b>F</b>                                                                           | <b>47</b> | <b>DRN</b> | <b>80M4</b> | 30                    | 402                                                                                 |
|                                    |                                   |          |                                                |                                    | <b>FF</b>                                                                          | <b>47</b> | <b>DRN</b> | <b>80M4</b> | 33                    | 403                                                                                 |
| <b>25</b>                          | 280                               | 56.49    | 7220                                           | 1.40                               |                                                                                    |           |            |             |                       |                                                                                     |
| <b>30</b>                          | 235                               | 48.00*   | 7540                                           | 1.70                               | <b>FA</b>                                                                          | <b>47</b> | <b>DRN</b> | <b>80M4</b> | 29                    | 404                                                                                 |
| <b>34</b>                          | 210                               | 42.86    | 7700                                           | 1.90                               | <b>FAF</b>                                                                         | <b>47</b> | <b>DRN</b> | <b>80M4</b> | 32                    | 403                                                                                 |
| <b>39</b>                          | 182                               | 36.61    | 7860                                           | 2.2                                | <b>F</b>                                                                           | <b>47</b> | <b>DRN</b> | <b>80M4</b> | 30                    | 402                                                                                 |
| <b>42</b>                          | 171                               | 34.29    | 7770                                           | 2.4                                | <b>FF</b>                                                                          | <b>47</b> | <b>DRN</b> | <b>80M4</b> | 33                    | 403                                                                                 |
| <b>50</b>                          | 144                               | 28.88    | 7460                                           | 2.8                                |                                                                                    |           |            |             |                       |                                                                                     |
| <b>31</b>                          | 230                               | 47.02    | 3730                                           | 0.85                               |                                                                                    |           |            |             |                       |                                                                                     |
| <b>33</b>                          | 215                               | 43.83    | 4020                                           | 0.90                               | <b>FA</b>                                                                          | <b>37</b> | <b>DRN</b> | <b>80M4</b> | 24                    | 398                                                                                 |
| <b>38</b>                          | 191                               | 38.31    | 4420                                           | 1.05                               | <b>FAF</b>                                                                         | <b>37</b> | <b>DRN</b> | <b>80M4</b> | 26                    | 397                                                                                 |
| <b>40</b>                          | 179                               | 35.91    | 4570                                           | 1.10                               | <b>F</b>                                                                           | <b>37</b> | <b>DRN</b> | <b>80M4</b> | 25                    | 396                                                                                 |
| <b>45</b>                          | 158                               | 31.69    | 4590                                           | 1.25                               | <b>FF</b>                                                                          | <b>37</b> | <b>DRN</b> | <b>80M4</b> | 27                    | 397                                                                                 |
| <b>51</b>                          | 140                               | 28.09    | 4500                                           | 1.45                               |                                                                                    |           |            |             |                       |                                                                                     |
| <b>61</b>                          | 118                               | 23.63    | 4370                                           | 1.70                               |                                                                                    |           |            |             |                       |                                                                                     |
| <b>70</b>                          | 102                               | 20.57    | 4250                                           | 1.95                               | <b>FA</b>                                                                          | <b>37</b> | <b>DRN</b> | <b>80M4</b> | 24                    | 398                                                                                 |
| <b>75</b>                          | 96                                | 19.27    | 4200                                           | 2.1                                | <b>FAF</b>                                                                         | <b>37</b> | <b>DRN</b> | <b>80M4</b> | 26                    | 397                                                                                 |
| <b>85</b>                          | 85                                | 17.03    | 4090                                           | 2.4                                | <b>F</b>                                                                           | <b>37</b> | <b>DRN</b> | <b>80M4</b> | 25                    | 396                                                                                 |
| <b>100</b>                         | 71                                | 14.33    | 3930                                           | 2.8                                | <b>FF</b>                                                                          | <b>37</b> | <b>DRN</b> | <b>80M4</b> | 27                    | 397                                                                                 |
| <b>112</b>                         | 64                                | 12.87    | 3830                                           | 3.1                                |                                                                                    |           |            |             |                       |                                                                                     |
| <b>62</b>                          | 116                               | 23.25    | 2900                                           | 1.10                               |                                                                                    |           |            |             |                       |                                                                                     |
| <b>71</b>                          | 100                               | 20.15    | 2860                                           | 1.30                               |                                                                                    |           |            |             |                       |                                                                                     |
| <b>76</b>                          | 94                                | 18.84    | 2830                                           | 1.40                               |                                                                                    |           |            |             |                       |                                                                                     |
| <b>88</b>                          | 81                                | 16.28    | 2770                                           | 1.60                               |                                                                                    |           |            |             |                       |                                                                                     |
| <b>104</b>                         | 69                                | 13.84    | 2700                                           | 1.90                               |                                                                                    |           |            |             |                       |                                                                                     |
| <b>117</b>                         | 61                                | 12.35    | 2640                                           | 2.1                                | <b>FA</b>                                                                          | <b>27</b> | <b>DRN</b> | <b>80M4</b> | 18                    | 393                                                                                 |
| <b>136</b>                         | 52                                | 10.55    | 2560                                           | 2.5                                | <b>FAF</b>                                                                         | <b>27</b> | <b>DRN</b> | <b>80M4</b> | 19                    | 392                                                                                 |
| <b>146</b>                         | 49                                | 9.88     | 2520                                           | 2.6                                | <b>F</b>                                                                           | <b>27</b> | <b>DRN</b> | <b>80M4</b> | 19                    | 391                                                                                 |
| <b>153</b>                         | 47                                | 9.40     | 2450                                           | 2.8                                | <b>FF</b>                                                                          | <b>27</b> | <b>DRN</b> | <b>80M4</b> | 19                    | 392                                                                                 |
| <b>177</b>                         | 40                                | 8.13     | 2370                                           | 3.0                                |                                                                                    |           |            |             |                       |                                                                                     |
| <b>208</b>                         | 34                                | 6.91     | 2280                                           | 3.3                                |                                                                                    |           |            |             |                       |                                                                                     |
| <b>234</b>                         | 31                                | 6.17     | 2220                                           | 3.6                                |                                                                                    |           |            |             |                       |                                                                                     |
| <b>273</b>                         | 26                                | 5.27     | 2140                                           | 3.8                                |                                                                                    |           |            |             |                       |                                                                                     |
| <b>292</b>                         | 25                                | 4.93     | 2100                                           | 3.9                                |                                                                                    |           |            |             |                       |                                                                                     |
| <b>346</b>                         | 21                                | 4.16     | 2010                                           | 4.2                                |                                                                                    |           |            |             |                       |                                                                                     |




| <b>P<sub>m</sub> = 1.1 kW</b>      |                                   |          |                                                |                                    |                                                                                      |               |            |             |                       |                                                                                     |
|------------------------------------|-----------------------------------|----------|------------------------------------------------|------------------------------------|--------------------------------------------------------------------------------------|---------------|------------|-------------|-----------------------|-------------------------------------------------------------------------------------|
| <b>n<sub>a</sub></b><br><b>rpm</b> | <b>M<sub>a</sub></b><br><b>Nm</b> | <b>i</b> | <b>F<sub>Ra</sub><sup>1)</sup></b><br><b>N</b> | <b>SEW</b><br><b>f<sub>B</sub></b> |    |               |            |             | <b>m</b><br><b>kg</b> |  |
| <b>0.52</b>                        | 17400                             | 2780     | 101800                                         | 1.05                               | <b>FA</b>                                                                            | <b>157R97</b> | <b>DRN</b> | <b>90S4</b> | 780                   | 456                                                                                 |
|                                    |                                   |          |                                                |                                    | <b>FAF</b>                                                                           | <b>157R97</b> | <b>DRN</b> | <b>90S4</b> | 840                   | 456                                                                                 |
|                                    |                                   |          |                                                |                                    | <b>F</b>                                                                             | <b>157R97</b> | <b>DRN</b> | <b>90S4</b> | 800                   | 456                                                                                 |
|                                    |                                   |          |                                                |                                    | <b>FF</b>                                                                            | <b>157R97</b> | <b>DRN</b> | <b>90S4</b> | 900                   | 456                                                                                 |
| <b>0.60</b>                        | 15400                             | 2427     | 107100                                         | 1.15                               |    | <b>157R97</b> | <b>DRN</b> | <b>90S4</b> | 770                   | 456                                                                                 |
| <b>0.67</b>                        | 13700                             | 2185     | 110800                                         | 1.30                               |                                                                                      |               |            |             |                       |                                                                                     |
| <b>0.75</b>                        | 12200                             | 1944     | 113700                                         | 1.45                               |                                                                                      |               |            |             |                       |                                                                                     |
| <b>0.87</b>                        | 10800                             | 1674     | 116000                                         | 1.65                               |                                                                                      |               |            |             |                       |                                                                                     |
| <b>1.1</b>                         | 8380                              | 1308     | 119300                                         | 2.2                                |                                                                                      |               |            |             |                       |                                                                                     |
| <b>1.2</b>                         | 7420                              | 1169     | 120000                                         | 2.4                                |                                                                                      |               |            |             |                       |                                                                                     |
| <b>1.5</b>                         | 5930                              | 953      | 120000                                         | 3.0                                |                                                                                      |               |            |             |                       |                                                                                     |
| <b>1.7</b>                         | 5180                              | 845      | 120000                                         | 3.5                                |                                                                                      |               |            |             |                       |                                                                                     |
| <b>3.3</b>                         | 2740                              | 446      | 120000                                         | 6.6                                |                                                                                      |               |            |             |                       |                                                                                     |
| <b>4.8</b>                         | 1850                              | 302      | 120000                                         | 9.7                                |                                                                                      |               |            |             |                       |                                                                                     |
| <b>0.71</b>                        | 13400                             | 2038     | 87700                                          | 0.90                               | <b>FA</b>                                                                            | <b>127R77</b> | <b>DRN</b> | <b>90S4</b> | 440                   | 456                                                                                 |
| <b>0.82</b>                        | 11700                             | 1784     | 90000                                          | 1.00                               | <b>FAF</b>                                                                           | <b>127R77</b> | <b>DRN</b> | <b>90S4</b> | 475                   | 456                                                                                 |
| <b>0.91</b>                        | 10500                             | 1606     | 90000                                          | 1.15                               | <b>F</b>                                                                             | <b>127R77</b> | <b>DRN</b> | <b>90S4</b> | 475                   | 456                                                                                 |
| <b>1.0</b>                         | 9100                              | 1390     | 90000                                          | 1.30                               | <b>FF</b>                                                                            | <b>127R77</b> | <b>DRN</b> | <b>90S4</b> | 520                   | 456                                                                                 |
| <b>1.2</b>                         | 7950                              | 1220     | 90000                                          | 1.50                               |    | <b>107R77</b> | <b>DRN</b> | <b>90S4</b> | 285                   | 456                                                                                 |
| <b>1.4</b>                         | 7070                              | 1077     | 90000                                          | 1.70                               |                                                                                      |               |            |             |                       |                                                                                     |
| <b>1.2</b>                         | 8140                              | 1243     | 48600                                          | 0.95                               |                                                                                      |               |            |             |                       |                                                                                     |
| <b>1.3</b>                         | 7200                              | 1087     | 51100                                          | 1.05                               |                                                                                      |               |            |             |                       |                                                                                     |
| <b>1.5</b>                         | 6220                              | 950      | 53500                                          | 1.25                               |                                                                                      |               |            |             |                       |                                                                                     |
| <b>1.8</b>                         | 5430                              | 834      | 55300                                          | 1.40                               |                                                                                      |               |            |             |                       |                                                                                     |
| <b>2.0</b>                         | 4770                              | 736      | 56800                                          | 1.60                               |                                                                                      |               |            |             |                       |                                                                                     |
| <b>2.3</b>                         | 4200                              | 640      | 58000                                          | 1.85                               |                                                                                      |               |            |             |                       |                                                                                     |
| <b>2.1</b>                         | 4560                              | 690      | 29100                                          | 0.95                               | <b>FA</b>                                                                            | <b>97R57</b>  | <b>DRN</b> | <b>90S4</b> | 195                   | 456                                                                                 |
| <b>2.4</b>                         | 4010                              | 605      | 30700                                          | 1.05                               | <b>FAF</b>                                                                           | <b>97R57</b>  | <b>DRN</b> | <b>90S4</b> | 220                   | 456                                                                                 |
| <b>2.8</b>                         | 3490                              | 529      | 32100                                          | 1.25                               | <b>F</b>                                                                             | <b>97R57</b>  | <b>DRN</b> | <b>90S4</b> | 205                   | 456                                                                                 |
| <b>3.1</b>                         | 3080                              | 467      | 33100                                          | 1.40                               | <b>FF</b>                                                                            | <b>97R57</b>  | <b>DRN</b> | <b>90S4</b> | 240                   | 456                                                                                 |
| <b>3.6</b>                         | 2660                              | 406      | 34100                                          | 1.60                               |  | <b>87R57</b>  | <b>DRN</b> | <b>90S4</b> | 130                   | 456                                                                                 |
| <b>4.0</b>                         | 2390                              | 363      | 34600                                          | 1.80                               |                                                                                      |               |            |             |                       |                                                                                     |
| <b>3.2</b>                         | 3000                              | 452      | 19600                                          | 1.00                               |                                                                                      |               |            |             |                       |                                                                                     |
| <b>4.2</b>                         | 2270                              | 345      | 25600                                          | 1.30                               |                                                                                      |               |            |             |                       |                                                                                     |
| <b>4.8</b>                         | 1960                              | 300      | 26500                                          | 1.50                               |                                                                                      |               |            |             |                       |                                                                                     |
| <b>5.8</b>                         | 1630                              | 249      | 27500                                          | 1.85                               |                                                                                      |               |            |             |                       |                                                                                     |
| <b>5.3</b>                         | 1990                              | 276.77   | 35400                                          | 2.2                                |                                                                                      |               |            |             |                       |                                                                                     |
| <b>5.7</b>                         | 1820                              | 253.41   | 35700                                          | 2.4                                |                                                                                      |               |            |             |                       |                                                                                     |
| <b>6.5</b>                         | 1610                              | 223.88   | 36100                                          | 2.7                                |                                                                                      |               |            |             |                       |                                                                                     |
| <b>5.4</b>                         | 1950                              | 270.68   | 26600                                          | 1.55                               | <b>FA</b>                                                                            | <b>87</b>     | <b>DRN</b> | <b>90S4</b> | 110                   | 428                                                                                 |
| <b>5.7</b>                         | 1840                              | 255.37   | 26900                                          | 1.65                               | <b>FAF</b>                                                                           | <b>87</b>     | <b>DRN</b> | <b>90S4</b> | 120                   | 427                                                                                 |
| <b>6.4</b>                         | 1650                              | 228.93   | 27400                                          | 1.80                               | <b>F</b>                                                                             | <b>87</b>     | <b>DRN</b> | <b>90S4</b> | 115                   | 426                                                                                 |
| <b>7.4</b>                         | 1420                              | 197.20   | 28000                                          | 2.1                                | <b>FF</b>                                                                            | <b>87</b>     | <b>DRN</b> | <b>90S4</b> | 130                   | 427                                                                                 |
| <b>8.1</b>                         | 1290                              | 179.97   | 28300                                          | 2.3                                | <b>FA</b>                                                                            | <b>87</b>     | <b>DRN</b> | <b>90S4</b> | 110                   | 428                                                                                 |
| <b>9.1</b>                         | 1150                              | 159.61   | 28600                                          | 2.6                                | <b>FAF</b>                                                                           | <b>87</b>     | <b>DRN</b> | <b>90S4</b> | 120                   | 427                                                                                 |
| <b>11</b>                          | 960                               | 134.16   | 29000                                          | 3.1                                | <b>F</b>                                                                             | <b>87</b>     | <b>DRN</b> | <b>90S4</b> | 115                   | 426                                                                                 |
| <b>12</b>                          | 890                               | 123.29   | 29200                                          | 3.4                                | <b>FF</b>                                                                            | <b>87</b>     | <b>DRN</b> | <b>90S4</b> | 130                   | 427                                                                                 |
| <b>7.3</b>                         | 1430                              | 198.31   | 16200                                          | 1.05                               | <b>FA</b>                                                                            | <b>77</b>     | <b>DRN</b> | <b>90S4</b> | 69                    | 422                                                                                 |
| <b>7.7</b>                         | 1360                              | 188.40   | 16600                                          | 1.10                               | <b>FAF</b>                                                                           | <b>77</b>     | <b>DRN</b> | <b>90S4</b> | 76                    | 421                                                                                 |
| <b>8.7</b>                         | 1200                              | 166.47   | 17400                                          | 1.25                               | <b>F</b>                                                                             | <b>77</b>     | <b>DRN</b> | <b>90S4</b> | 73                    | 420                                                                                 |
| <b>10</b>                          | 1020                              | 142.27   | 18200                                          | 1.45                               | <b>FF</b>                                                                            | <b>77</b>     | <b>DRN</b> | <b>90S4</b> | 84                    | 421                                                                                 |
| <b>11</b>                          | 940                               | 130.42   | 18500                                          | 1.60                               |  | <b>77</b>     | <b>DRN</b> | <b>90S4</b> | 69                    | 422                                                                                 |
| <b>13</b>                          | 820                               | 114.45   | 18900                                          | 1.80                               |                                                                                      |               |            |             |                       |                                                                                     |
| <b>13</b>                          | 780                               | 108.46*  | 19000                                          | 1.90                               |                                                                                      |               |            |             |                       |                                                                                     |
| <b>15</b>                          | 685                               | 94.93    | 19300                                          | 2.2                                |                                                                                      |               |            |             |                       |                                                                                     |
| <b>17</b>                          | 615                               | 85.52    | 19500                                          | 2.4                                |                                                                                      |               |            |             |                       |                                                                                     |
| <b>19</b>                          | 540                               | 75.02    | 19600                                          | 2.8                                |                                                                                      |               |            |             |                       |                                                                                     |
| <b>12</b>                          | 870                               | 120.79   | 9820                                           | 0.95                               | <b>FA</b>                                                                            | <b>67</b>     | <b>DRN</b> | <b>90S4</b> | 47                    | 416                                                                                 |
|                                    |                                   |          |                                                |                                    | <b>FAF</b>                                                                           | <b>67</b>     | <b>DRN</b> | <b>90S4</b> | 53                    | 415                                                                                 |
|                                    |                                   |          |                                                |                                    | <b>F</b>                                                                             | <b>67</b>     | <b>DRN</b> | <b>90S4</b> | 50                    | 414                                                                                 |
|                                    |                                   |          |                                                |                                    | <b>FF</b>                                                                            | <b>67</b>     | <b>DRN</b> | <b>90S4</b> | 56                    | 415                                                                                 |


21933170/DE – 11/2015


| P <sub>m</sub> = 1.1 kW |                      |        |                                    |                       |                                                                                    |                      |                          |                              |                      |                                                                                     |
|-------------------------|----------------------|--------|------------------------------------|-----------------------|------------------------------------------------------------------------------------|----------------------|--------------------------|------------------------------|----------------------|-------------------------------------------------------------------------------------|
| n <sub>a</sub><br>rpm   | M <sub>a</sub><br>Nm | i      | F <sub>Ra</sub> <sup>1)</sup><br>N | SEW<br>f <sub>B</sub> |  |                      |                          |                              | m<br>kg              |  |
| 13                      | 785                  | 109.04 | 10600                              | 1.05                  | FA<br>FAF<br>F<br>FF                                                               | 67<br>67<br>67<br>67 | DRN<br>DRN<br>DRN<br>DRN | 90S4<br>90S4<br>90S4<br>90S4 | 47<br>53<br>50<br>56 | 416<br>415<br>414<br>415                                                            |
| 15                      | 690                  | 95.94  | 11300                              | 1.20                  |                                                                                    |                      |                          |                              |                      |                                                                                     |
| 16                      | 650                  | 90.59  | 11600                              | 1.25                  |                                                                                    |                      |                          |                              |                      |                                                                                     |
| 18                      | 575                  | 79.76  | 12000                              | 1.40                  |                                                                                    |                      |                          |                              |                      |                                                                                     |
| 22                      | 485                  | 67.65  | 12500                              | 1.70                  |                                                                                    |                      |                          |                              |                      |                                                                                     |
| 24                      | 440                  | 61.07  | 12700                              | 1.85                  |                                                                                    |                      |                          |                              |                      |                                                                                     |
| 27                      | 385                  | 53.73  | 12900                              | 2.1                   |                                                                                    |                      |                          |                              |                      |                                                                                     |
| 29                      | 365                  | 50.74  | 12900                              | 2.2                   |                                                                                    |                      |                          |                              |                      |                                                                                     |
| 34                      | 310                  | 43.20  | 13000                              | 2.6                   |                                                                                    |                      |                          |                              |                      |                                                                                     |
| 37                      | 280                  | 39.26  | 13000                              | 2.8                   |                                                                                    |                      |                          |                              |                      |                                                                                     |
| 43                      | 245                  | 34.01  | 13000                              | 3.0                   |                                                                                    |                      |                          |                              |                      |                                                                                     |
| 17                      | 600                  | 83.46  | 9180                               | 1.00                  | FA<br>FAF<br>F<br>FF                                                               | 57<br>57<br>57<br>57 | DRN<br>DRN<br>DRN<br>DRN | 90S4<br>90S4<br>90S4<br>90S4 | 43<br>48<br>43<br>50 | 410<br>409<br>408<br>409                                                            |
| 20                      | 525                  | 72.98  | 9740                               | 1.15                  |                                                                                    |                      |                          |                              |                      |                                                                                     |
| 21                      | 490                  | 68.22  | 9980                               | 1.20                  |                                                                                    |                      |                          |                              |                      |                                                                                     |
| 25                      | 425                  | 58.97  | 10400                              | 1.40                  |                                                                                    |                      |                          |                              |                      |                                                                                     |
| 29                      | 360                  | 50.10  | 10800                              | 1.65                  |                                                                                    |                      |                          |                              |                      |                                                                                     |
| 33                      | 320                  | 44.73  | 10600                              | 1.85                  |                                                                                    |                      |                          |                              |                      |                                                                                     |
| 38                      | 275                  | 38.21  | 10300                              | 2.2                   |                                                                                    |                      |                          |                              |                      |                                                                                     |
| 41                      | 255                  | 35.79  | 10100                              | 2.3                   |                                                                                    |                      |                          |                              |                      |                                                                                     |
| 48                      | 215                  | 30.15  | 9720                               | 2.7                   |                                                                                    |                      |                          |                              |                      |                                                                                     |
| 26                      | 405                  | 56.49  | 5680                               | 1.00                  | FA<br>FAF<br>F<br>FF                                                               | 47<br>47<br>47<br>47 | DRN<br>DRN<br>DRN<br>DRN | 90S4<br>90S4<br>90S4<br>90S4 | 35<br>38<br>36<br>39 | 404<br>403<br>402<br>403                                                            |
| 30                      | 345                  | 48.00* | 6600                               | 1.15                  |                                                                                    |                      |                          |                              |                      |                                                                                     |
| 34                      | 305                  | 42.86  | 6970                               | 1.30                  |                                                                                    |                      |                          |                              |                      |                                                                                     |
| 40                      | 260                  | 36.61  | 7300                               | 1.50                  |                                                                                    |                      |                          |                              |                      |                                                                                     |
| 42                      | 245                  | 34.29  | 7210                               | 1.60                  | FA<br>FAF<br>F<br>FF                                                               | 47<br>47<br>47<br>47 | DRN<br>DRN<br>DRN<br>DRN | 90S4<br>90S4<br>90S4<br>90S4 | 35<br>38<br>36<br>39 | 404<br>403<br>402<br>403                                                            |
| 50                      | 205                  | 28.88  | 6990                               | 1.90                  |                                                                                    |                      |                          |                              |                      |                                                                                     |
| 47                      | 220                  | 30.86  | 7080                               | 1.80                  |                                                                                    |                      |                          |                              |                      |                                                                                     |
| 50                      | 210                  | 29.32  | 7010                               | 1.90                  |                                                                                    |                      |                          |                              |                      |                                                                                     |
| 57                      | 186                  | 25.72  | 6820                               | 2.2                   | FA<br>FAF<br>F<br>FF                                                               | 47<br>47<br>47<br>47 | DRN<br>DRN<br>DRN<br>DRN | 90S4<br>90S4<br>90S4<br>90S4 | 34<br>37<br>35<br>38 | 404<br>403<br>402<br>403                                                            |
| 67                      | 158                  | 21.82  | 6580                               | 2.5                   |                                                                                    |                      |                          |                              |                      |                                                                                     |
| 74                      | 142                  | 19.70  | 6430                               | 2.8                   |                                                                                    |                      |                          |                              |                      |                                                                                     |
| 46                      | 225                  | 31.69  | 3830                               | 0.85                  |                                                                                    |                      |                          |                              |                      |                                                                                     |
| 52                      | 200                  | 28.09  | 3960                               | 1.00                  | FA<br>FAF<br>F<br>FF                                                               | 37<br>37<br>37<br>37 | DRN<br>DRN<br>DRN<br>DRN | 90S4<br>90S4<br>90S4<br>90S4 | 30<br>32<br>31<br>33 | 398<br>397<br>396<br>397                                                            |
| 61                      | 172                  | 23.88  | 3920                               | 1.15                  |                                                                                    |                      |                          |                              |                      |                                                                                     |
| 71                      | 149                  | 20.57  | 3860                               | 1.35                  |                                                                                    |                      |                          |                              |                      |                                                                                     |
| 76                      | 139                  | 19.27  | 3820                               | 1.45                  |                                                                                    |                      |                          |                              |                      |                                                                                     |
| 85                      | 123                  | 17.03  | 3760                               | 1.65                  | FA<br>FAF<br>F<br>FF                                                               | 37<br>37<br>37<br>37 | DRN<br>DRN<br>DRN<br>DRN | 90S4<br>90S4<br>90S4<br>90S4 | 30<br>32<br>31<br>32 | 398<br>397<br>396<br>397                                                            |
| 102                     | 103                  | 14.33  | 3650                               | 1.95                  |                                                                                    |                      |                          |                              |                      |                                                                                     |
| 113                     | 93                   | 12.87  | 3580                               | 2.2                   |                                                                                    |                      |                          |                              |                      |                                                                                     |
| 131                     | 80                   | 11.08  | 3470                               | 2.4                   |                                                                                    |                      |                          |                              |                      |                                                                                     |
| 140                     | 75                   | 10.42  | 3430                               | 2.5                   |                                                                                    |                      |                          |                              |                      |                                                                                     |
| 162                     | 65                   | 8.97   | 3320                               | 2.7                   |                                                                                    |                      |                          |                              |                      |                                                                                     |
| 72                      | 146                  | 20.15  | 2440                               | 0.90                  | FA<br>FAF<br>F<br>FF                                                               | 27<br>27<br>27<br>27 | DRN<br>DRN<br>DRN<br>DRN | 90S4<br>90S4<br>90S4<br>90S4 | 24<br>25<br>24<br>25 | 393<br>392<br>391<br>392                                                            |
| 77                      | 136                  | 18.84  | 2440                               | 0.95                  |                                                                                    |                      |                          |                              |                      |                                                                                     |
| 89                      | 118                  | 16.28  | 2440                               | 1.10                  |                                                                                    |                      |                          |                              |                      |                                                                                     |
| 105                     | 100                  | 13.84  | 2410                               | 1.30                  |                                                                                    |                      |                          |                              |                      |                                                                                     |
| 118                     | 89                   | 12.35  | 2380                               | 1.45                  |                                                                                    |                      |                          |                              |                      |                                                                                     |
| 138                     | 76                   | 10.55  | 2330                               | 1.70                  |                                                                                    |                      |                          |                              |                      |                                                                                     |
| 147                     | 71                   | 9.88   | 2310                               | 1.80                  |                                                                                    |                      |                          |                              |                      |                                                                                     |
| 155                     | 68                   | 9.40   | 2230                               | 1.90                  |                                                                                    |                      |                          |                              |                      |                                                                                     |
| 179                     | 59                   | 8.13   | 2180                               | 2.1                   |                                                                                    |                      |                          |                              |                      |                                                                                     |
| 211                     | 50                   | 6.91   | 2120                               | 2.3                   |                                                                                    |                      |                          |                              |                      |                                                                                     |
| 236                     | 45                   | 6.17   | 2080                               | 2.4                   |                                                                                    |                      |                          |                              |                      |                                                                                     |
| 276                     | 38                   | 5.27   | 2010                               | 2.6                   |                                                                                    |                      |                          |                              |                      |                                                                                     |
| 295                     | 36                   | 4.93   | 1990                               | 2.7                   |                                                                                    |                      |                          |                              |                      |                                                                                     |
| 350                     | 30                   | 4.16   | 1910                               | 2.9                   |                                                                                    |                      |                          |                              |                      |                                                                                     |

**P<sub>m</sub> = 1.5 kW**


| n <sub>a</sub><br>rpm | M <sub>a</sub><br>Nm | i       | F <sub>Ra</sub> <sup>1)</sup><br>N | SEW<br>f <sub>B</sub> |  |        |     |      | m<br>kg |  |
|-----------------------|----------------------|---------|------------------------------------|-----------------------|------------------------------------------------------------------------------------|--------|-----|------|---------|-------------------------------------------------------------------------------------|
| 0.60                  | 21300                | 2427    | 88800                              | 0.85                  |                                                                                    |        |     |      |         |                                                                                     |
| 0.67                  | 19000                | 2185    | 96900                              | 0.95                  |                                                                                    |        |     |      |         |                                                                                     |
| 0.75                  | 16900                | 1944    | 103200                             | 1.05                  |                                                                                    |        |     |      |         |                                                                                     |
| 0.87                  | 14800                | 1674    | 108300                             | 1.20                  | FA                                                                                 | 157R97 | DRN | 90L4 | 780     | 456                                                                                 |
| 1.1                   | 11500                | 1308    | 114900                             | 1.55                  | FAF                                                                                | 157R97 | DRN | 90L4 | 840     | 456                                                                                 |
| 1.2                   | 10200                | 1169    | 116900                             | 1.75                  | F                                                                                  | 157R97 | DRN | 90L4 | 800     | 456                                                                                 |
| 1.5                   | 8250                 | 953     | 119500                             | 2.2                   | FF                                                                                 | 157R97 | DRN | 90L4 | 900     | 456                                                                                 |
| 1.7                   | 7240                 | 845     | 120000                             | 2.5                   |                                                                                    |        |     |      |         |                                                                                     |
| 3.3                   | 3820                 | 446     | 120000                             | 4.7                   |                                                                                    |        |     |      |         |                                                                                     |
| 4.8                   | 2590                 | 302     | 120000                             | 7.0                   |                                                                                    |        |     |      |         |                                                                                     |
| 0.91                  | 14400                | 1606    | 85700                              | 0.85                  |                                                                                    |        |     |      |         |                                                                                     |
| 1.0                   | 12400                | 1390    | 89500                              | 0.95                  |                                                                                    |        |     |      |         |                                                                                     |
| 1.2                   | 10900                | 1220    | 90000                              | 1.10                  | FA                                                                                 | 127R77 | DRN | 90L4 | 440     | 456                                                                                 |
| 1.4                   | 9690                 | 1077    | 90000                              | 1.25                  | FAF                                                                                | 127R77 | DRN | 90L4 | 480     | 456                                                                                 |
| 1.6                   | 8320                 | 930     | 90000                              | 1.45                  | F                                                                                  | 127R77 | DRN | 90L4 | 480     | 456                                                                                 |
| 1.8                   | 7310                 | 820     | 90000                              | 1.65                  | FF                                                                                 | 127R77 | DRN | 90L4 | 520     | 456                                                                                 |
| 2.0                   | 6460                 | 727     | 90000                              | 1.85                  |                                                                                    |        |     |      |         |                                                                                     |
| 2.2                   | 5830                 | 648     | 90000                              | 2.1                   |                                                                                    |        |     |      |         |                                                                                     |
| 1.5                   | 8530                 | 950     | 47500                              | 0.90                  |                                                                                    |        |     |      |         |                                                                                     |
| 1.8                   | 7460                 | 834     | 50400                              | 1.05                  |                                                                                    |        |     |      |         |                                                                                     |
| 2.0                   | 6560                 | 736     | 52700                              | 1.15                  | FA                                                                                 | 107R77 | DRN | 90L4 | 290     | 456                                                                                 |
| 2.3                   | 5760                 | 640     | 54600                              | 1.35                  | FAF                                                                                | 107R77 | DRN | 90L4 | 310     | 456                                                                                 |
| 2.6                   | 4980                 | 560     | 56300                              | 1.55                  | F                                                                                  | 107R77 | DRN | 90L4 | 305     | 456                                                                                 |
| 3.0                   | 4350                 | 489     | 57700                              | 1.75                  | FF                                                                                 | 107R77 | DRN | 90L4 | 335     | 456                                                                                 |
| 3.4                   | 3920                 | 436     | 58600                              | 1.95                  |                                                                                    |        |     |      |         |                                                                                     |
| 4.0                   | 3320                 | 370     | 59800                              | 2.3                   |                                                                                    |        |     |      |         |                                                                                     |
| 2.8                   | 4780                 | 529     | 23800                              | 0.90                  | FA                                                                                 | 97R57  | DRN | 90L4 | 200     | 456                                                                                 |
| 3.1                   | 4220                 | 467     | 30100                              | 1.00                  | FAF                                                                                | 97R57  | DRN | 90L4 | 220     | 456                                                                                 |
| 3.6                   | 3650                 | 406     | 31700                              | 1.20                  | F                                                                                  | 97R57  | DRN | 90L4 | 210     | 456                                                                                 |
| 4.0                   | 3270                 | 363     | 32700                              | 1.30                  | FF                                                                                 | 97R57  | DRN | 90L4 | 240     | 456                                                                                 |
| 4.9                   | 2700                 | 300     | 24100                              | 1.10                  | FA                                                                                 | 87R57  | DRN | 90L4 | 135     | 456                                                                                 |
| 5.9                   | 2240                 | 249     | 25700                              | 1.35                  | FAF                                                                                | 87R57  | DRN | 90L4 | 150     | 456                                                                                 |
|                       |                      |         |                                    |                       | F                                                                                  | 87R57  | DRN | 90L4 | 140     | 456                                                                                 |
|                       |                      |         |                                    |                       | FF                                                                                 | 87R57  | DRN | 90L4 | 155     | 456                                                                                 |
| 5.3                   | 2710                 | 276.77  | 34000                              | 1.60                  | FA                                                                                 | 97     | DRN | 90L4 | 175     | 434                                                                                 |
| 5.8                   | 2480                 | 253.41  | 34400                              | 1.75                  | FAF                                                                                | 97     | DRN | 90L4 | 200     | 433                                                                                 |
| 6.5                   | 2190                 | 223.88  | 35000                              | 1.95                  | F                                                                                  | 97     | DRN | 90L4 | 185     | 432                                                                                 |
| 7.7                   | 1860                 | 189.92  | 35600                              | 2.3                   | FF                                                                                 | 97     | DRN | 90L4 | 215     | 433                                                                                 |
| 8.4                   | 1710                 | 174.87  | 35900                              | 2.5                   |                                                                                    |        |     |      |         |                                                                                     |
| 5.4                   | 2650                 | 270.68  | 24300                              | 1.15                  | FA                                                                                 | 87     | DRN | 90L4 | 110     | 428                                                                                 |
| 5.7                   | 2500                 | 255.37  | 24800                              | 1.20                  | FAF                                                                                | 87     | DRN | 90L4 | 125     | 427                                                                                 |
| 6.4                   | 2240                 | 228.93  | 25700                              | 1.35                  | F                                                                                  | 87     | DRN | 90L4 | 120     | 426                                                                                 |
| 7.4                   | 1930                 | 197.20  | 26600                              | 1.55                  | FF                                                                                 | 87     | DRN | 90L4 | 135     | 427                                                                                 |
| 8.1                   | 1760                 | 179.97  | 27100                              | 1.70                  | FA                                                                                 | 87     | DRN | 90L4 | 110     | 428                                                                                 |
| 9.2                   | 1560                 | 159.61  | 27700                              | 1.90                  | FAF                                                                                | 87     | DRN | 90L4 | 125     | 427                                                                                 |
| 11                    | 1310                 | 134.16  | 28300                              | 2.3                   | F                                                                                  | 87     | DRN | 90L4 | 120     | 426                                                                                 |
| 13                    | 1070                 | 109.49  | 28800                              | 2.8                   | FF                                                                                 | 87     | DRN | 90L4 | 135     | 427                                                                                 |
| 15                    | 950                  | 97.89   | 29100                              | 3.1                   |                                                                                    |        |     |      |         |                                                                                     |
| 8.8                   | 1630                 | 166.47  | 14800                              | 0.90                  | FA                                                                                 | 77     | DRN | 90L4 | 73      | 422                                                                                 |
| 10                    | 1390                 | 142.27  | 16400                              | 1.10                  | FAF                                                                                | 77     | DRN | 90L4 | 79      | 421                                                                                 |
| 11                    | 1270                 | 130.42  | 17000                              | 1.15                  | F                                                                                  | 77     | DRN | 90L4 | 76      | 420                                                                                 |
| 13                    | 1120                 | 114.45  | 17800                              | 1.35                  | FF                                                                                 | 77     | DRN | 90L4 | 87      | 421                                                                                 |
| 13                    | 1060                 | 108.46* | 18100                              | 1.40                  |                                                                                    |        |     |      |         |                                                                                     |
| 15                    | 930                  | 94.93   | 18600                              | 1.60                  |                                                                                    |        |     |      |         |                                                                                     |
| 17                    | 830                  | 85.52   | 18900                              | 1.80                  |                                                                                    |        |     |      |         |                                                                                     |
| 19                    | 735                  | 75.02   | 19200                              | 2.0                   | FA                                                                                 | 77     | DRN | 90L4 | 73      | 422                                                                                 |
| 20                    | 710                  | 72.50   | 19200                              | 2.1                   | FAF                                                                                | 77     | DRN | 90L4 | 79      | 421                                                                                 |
| 22                    | 650                  | 66.46   | 19400                              | 2.3                   | F                                                                                  | 77     | DRN | 90L4 | 76      | 420                                                                                 |
| 25                    | 570                  | 58.32   | 19600                              | 2.6                   | FF                                                                                 | 77     | DRN | 90L4 | 87      | 421                                                                                 |
| 26                    | 540                  | 55.27   | 19600                              | 2.8                   |                                                                                    |        |     |      |         |                                                                                     |
| 30                    | 470                  | 48.37   | 19700                              | 3.2                   |                                                                                    |        |     |      |         |                                                                                     |
| 34                    | 425                  | 43.58   | 19800                              | 3.5                   |                                                                                    |        |     |      |         |                                                                                     |
| 38                    | 370                  | 38.23   | 19900                              | 4.0                   |                                                                                    |        |     |      |         |                                                                                     |


21933170/DE – 11/2015

| <b>P<sub>m</sub> = 1.5 kW</b>      |                                   |          |                                                |                                    |                                                                                    |           |            |             |                       |                                                                                     |
|------------------------------------|-----------------------------------|----------|------------------------------------------------|------------------------------------|------------------------------------------------------------------------------------|-----------|------------|-------------|-----------------------|-------------------------------------------------------------------------------------|
| <b>n<sub>a</sub></b><br><b>rpm</b> | <b>M<sub>a</sub></b><br><b>Nm</b> | <b>i</b> | <b>F<sub>Ra</sub><sup>1)</sup></b><br><b>N</b> | <b>SEW</b><br><b>f<sub>B</sub></b> |  |           |            |             | <b>m</b><br><b>kg</b> |  |
| <b>40</b>                          | 355                               | 36.58    | 19900                                          | 3.1                                | <b>FA</b>                                                                          | <b>77</b> | <b>DRN</b> | <b>90L4</b> | 71                    | 422                                                                                 |
| <b>46</b>                          | 305                               | 31.51    | 20000                                          | 4.5                                | <b>FAF</b>                                                                         | <b>77</b> | <b>DRN</b> | <b>90L4</b> | 78                    | 421                                                                                 |
|                                    |                                   |          |                                                |                                    | <b>F</b>                                                                           | <b>77</b> | <b>DRN</b> | <b>90L4</b> | 75                    | 420                                                                                 |
|                                    |                                   |          |                                                |                                    | <b>FF</b>                                                                          | <b>77</b> | <b>DRN</b> | <b>90L4</b> | 86                    | 421                                                                                 |
| <b>16</b>                          | 880                               | 90.59    | 9650                                           | 0.90                               |                                                                                    |           |            |             |                       |                                                                                     |
| <b>18</b>                          | 780                               | 79.76    | 10600                                          | 1.05                               |                                                                                    |           |            |             |                       |                                                                                     |
| <b>22</b>                          | 660                               | 67.65    | 11500                                          | 1.25                               | <b>FA</b>                                                                          | <b>67</b> | <b>DRN</b> | <b>90L4</b> | 50                    | 416                                                                                 |
| <b>24</b>                          | 595                               | 61.07    | 11900                                          | 1.35                               | <b>FAF</b>                                                                         | <b>67</b> | <b>DRN</b> | <b>90L4</b> | 56                    | 415                                                                                 |
| <b>27</b>                          | 525                               | 53.73    | 12300                                          | 1.55                               | <b>F</b>                                                                           | <b>67</b> | <b>DRN</b> | <b>90L4</b> | 53                    | 414                                                                                 |
| <b>29</b>                          | 495                               | 50.74    | 12400                                          | 1.65                               | <b>FF</b>                                                                          | <b>67</b> | <b>DRN</b> | <b>90L4</b> | 59                    | 415                                                                                 |
| <b>34</b>                          | 420                               | 43.20    | 12700                                          | 1.95                               |                                                                                    |           |            |             |                       |                                                                                     |
| <b>37</b>                          | 380                               | 39.26    | 12900                                          | 2.0                                |                                                                                    |           |            |             |                       |                                                                                     |
| <b>40</b>                          | 355                               | 36.30    | 13000                                          | 2.3                                | <b>FA</b>                                                                          | <b>67</b> | <b>DRN</b> | <b>90L4</b> | 49                    | 416                                                                                 |
| <b>46</b>                          | 310                               | 32.08    | 13000                                          | 2.6                                | <b>FAF</b>                                                                         | <b>67</b> | <b>DRN</b> | <b>90L4</b> | 55                    | 415                                                                                 |
| <b>53</b>                          | 265                               | 27.41    | 13000                                          | 3.0                                | <b>F</b>                                                                           | <b>67</b> | <b>DRN</b> | <b>90L4</b> | 52                    | 414                                                                                 |
| <b>58</b>                          | 245                               | 25.13    | 13000                                          | 3.3                                | <b>FF</b>                                                                          | <b>67</b> | <b>DRN</b> | <b>90L4</b> | 58                    | 415                                                                                 |
| <b>25</b>                          | 575                               | 58.97    | 9370                                           | 1.05                               |                                                                                    |           |            |             |                       |                                                                                     |
| <b>29</b>                          | 490                               | 50.10    | 9980                                           | 1.20                               | <b>FA</b>                                                                          | <b>57</b> | <b>DRN</b> | <b>90L4</b> | 46                    | 410                                                                                 |
| <b>33</b>                          | 435                               | 44.73    | 9940                                           | 1.35                               | <b>FAF</b>                                                                         | <b>57</b> | <b>DRN</b> | <b>90L4</b> | 52                    | 409                                                                                 |
| <b>38</b>                          | 370                               | 38.21    | 9680                                           | 1.60                               | <b>F</b>                                                                           | <b>57</b> | <b>DRN</b> | <b>90L4</b> | 46                    | 408                                                                                 |
| <b>41</b>                          | 350                               | 35.79    | 9560                                           | 1.70                               | <b>FF</b>                                                                          | <b>57</b> | <b>DRN</b> | <b>90L4</b> | 53                    | 409                                                                                 |
| <b>48</b>                          | 295                               | 30.15    | 9240                                           | 2.0                                |                                                                                    |           |            |             |                       |                                                                                     |
| <b>40</b>                          | 355                               | 36.61    | 6460                                           | 1.10                               | <b>FA</b>                                                                          | <b>47</b> | <b>DRN</b> | <b>90L4</b> | 38                    | 404                                                                                 |
| <b>43</b>                          | 335                               | 34.29    | 6600                                           | 1.20                               | <b>FAF</b>                                                                         | <b>47</b> | <b>DRN</b> | <b>90L4</b> | 41                    | 403                                                                                 |
| <b>51</b>                          | 280                               | 28.88    | 6460                                           | 1.40                               | <b>F</b>                                                                           | <b>47</b> | <b>DRN</b> | <b>90L4</b> | 39                    | 402                                                                                 |
|                                    |                                   |          |                                                |                                    | <b>FF</b>                                                                          | <b>47</b> | <b>DRN</b> | <b>90L4</b> | 42                    | 403                                                                                 |
| <b>47</b>                          | 300                               | 30.86    | 6520                                           | 1.30                               |                                                                                    |           |            |             |                       |                                                                                     |
| <b>50</b>                          | 285                               | 29.32    | 6480                                           | 1.40                               |                                                                                    |           |            |             |                       |                                                                                     |
| <b>57</b>                          | 250                               | 25.72    | 6360                                           | 1.60                               | <b>FA</b>                                                                          | <b>47</b> | <b>DRN</b> | <b>90L4</b> | 38                    | 404                                                                                 |
| <b>67</b>                          | 210                               | 21.82    | 6190                                           | 1.85                               | <b>FAF</b>                                                                         | <b>47</b> | <b>DRN</b> | <b>90L4</b> | 40                    | 403                                                                                 |
| <b>74</b>                          | 193                               | 19.70    | 6070                                           | 2.1                                | <b>F</b>                                                                           | <b>47</b> | <b>DRN</b> | <b>90L4</b> | 38                    | 402                                                                                 |
| <b>84</b>                          | 170                               | 17.33    | 5920                                           | 2.4                                | <b>FF</b>                                                                          | <b>47</b> | <b>DRN</b> | <b>90L4</b> | 42                    | 403                                                                                 |
| <b>89</b>                          | 160                               | 16.36    | 5850                                           | 2.5                                |                                                                                    |           |            |             |                       |                                                                                     |
| <b>105</b>                         | 137                               | 13.93    | 5650                                           | 2.9                                |                                                                                    |           |            |             |                       |                                                                                     |
| <b>71</b>                          | 200                               | 20.57    | 3410                                           | 1.00                               |                                                                                    |           |            |             |                       |                                                                                     |
| <b>76</b>                          | 189                               | 19.27    | 3410                                           | 1.05                               |                                                                                    |           |            |             |                       |                                                                                     |
| <b>86</b>                          | 167                               | 17.03    | 3390                                           | 1.20                               | <b>FA</b>                                                                          | <b>37</b> | <b>DRN</b> | <b>90L4</b> | 33                    | 398                                                                                 |
| <b>102</b>                         | 141                               | 14.33    | 3340                                           | 1.40                               | <b>FAF</b>                                                                         | <b>37</b> | <b>DRN</b> | <b>90L4</b> | 35                    | 397                                                                                 |
| <b>114</b>                         | 126                               | 12.87    | 3300                                           | 1.60                               | <b>F</b>                                                                           | <b>37</b> | <b>DRN</b> | <b>90L4</b> | 34                    | 396                                                                                 |
| <b>132</b>                         | 109                               | 11.08    | 3230                                           | 1.75                               | <b>FF</b>                                                                          | <b>37</b> | <b>DRN</b> | <b>90L4</b> | 36                    | 397                                                                                 |
| <b>140</b>                         | 102                               | 10.42    | 3200                                           | 1.80                               |                                                                                    |           |            |             |                       |                                                                                     |
| <b>163</b>                         | 88                                | 8.97     | 3120                                           | 2.00                               |                                                                                    |           |            |             |                       |                                                                                     |
| <b>182</b>                         | 79                                | 8.01     | 3060                                           | 2.2                                |                                                                                    |           |            |             |                       |                                                                                     |
| <b>106</b>                         | 136                               | 13.84    | 2090                                           | 0.95                               |                                                                                    |           |            |             |                       |                                                                                     |
| <b>118</b>                         | 121                               | 12.35    | 2090                                           | 1.05                               |                                                                                    |           |            |             |                       |                                                                                     |
| <b>138</b>                         | 103                               | 10.55    | 2090                                           | 1.25                               |                                                                                    |           |            |             |                       |                                                                                     |
| <b>148</b>                         | 97                                | 9.88     | 2080                                           | 1.35                               | <b>FA</b>                                                                          | <b>27</b> | <b>DRN</b> | <b>90L4</b> | 27                    | 393                                                                                 |
| <b>155</b>                         | 92                                | 9.40     | 1990                                           | 1.40                               | <b>FAF</b>                                                                         | <b>27</b> | <b>DRN</b> | <b>90L4</b> | 28                    | 392                                                                                 |
| <b>180</b>                         | 80                                | 8.13     | 1970                                           | 1.55                               | <b>F</b>                                                                           | <b>27</b> | <b>DRN</b> | <b>90L4</b> | 28                    | 391                                                                                 |
| <b>212</b>                         | 68                                | 6.91     | 1940                                           | 1.70                               | <b>FF</b>                                                                          | <b>27</b> | <b>DRN</b> | <b>90L4</b> | 28                    | 392                                                                                 |
| <b>237</b>                         | 60                                | 6.17     | 1920                                           | 1.80                               |                                                                                    |           |            |             |                       |                                                                                     |
| <b>277</b>                         | 52                                | 5.27     | 1880                                           | 1.95                               |                                                                                    |           |            |             |                       |                                                                                     |
| <b>296</b>                         | 48                                | 4.93     | 1860                                           | 2.00                               |                                                                                    |           |            |             |                       |                                                                                     |
| <b>352</b>                         | 41                                | 4.16     | 1800                                           | 2.1                                |                                                                                    |           |            |             |                       |                                                                                     |

| <b>P<sub>m</sub> = 2.2 kW</b>      |                                   |          |                                                |                                    |                                                                                      |               |            |               |                       |                                                                                       |
|------------------------------------|-----------------------------------|----------|------------------------------------------------|------------------------------------|--------------------------------------------------------------------------------------|---------------|------------|---------------|-----------------------|---------------------------------------------------------------------------------------|
| <b>n<sub>a</sub></b><br><b>rpm</b> | <b>M<sub>a</sub></b><br><b>Nm</b> | <b>i</b> | <b>F<sub>Ra</sub><sup>1)</sup></b><br><b>N</b> | <b>SEW</b><br><b>f<sub>B</sub></b> |  |               |            |               | <b>m</b><br><b>kg</b> |  |
| <b>1.0</b>                         | 18100                             | 1441     | 99800                                          | 1.00                               | <b>FA</b>                                                                            | <b>157R97</b> | <b>DRN</b> | <b>100LS4</b> | 780                   | 456                                                                                   |
|                                    |                                   |          |                                                |                                    | <b>FAF</b>                                                                           | <b>157R97</b> | <b>DRN</b> | <b>100LS4</b> | 840                   | 456                                                                                   |
|                                    |                                   |          |                                                |                                    | <b>F</b>                                                                             | <b>157R97</b> | <b>DRN</b> | <b>100LS4</b> | 810                   | 456                                                                                   |
|                                    |                                   |          |                                                |                                    | <b>FF</b>                                                                            | <b>157R97</b> | <b>DRN</b> | <b>100LS4</b> | 910                   | 456                                                                                   |


**P<sub>m</sub> = 2.2 kW**


| n <sub>a</sub><br>rpm | M <sub>a</sub><br>Nm | i       | F <sub>Ra</sub> <sup>1)</sup><br>N | SEW<br>f <sub>B</sub> |  |        |     |        | m<br>kg |  |
|-----------------------|----------------------|---------|------------------------------------|-----------------------|------------------------------------------------------------------------------------|--------|-----|--------|---------|-------------------------------------------------------------------------------------|
| 1.1                   | 17300                | 1308    | 102200                             | 1.05                  | FA<br>FAF<br>F<br>FF                                                               | 157R97 | DRN | 100LS4 | 780     | 456                                                                                 |
| 1.2                   | 15400                | 1169    | 107100                             | 1.15                  |                                                                                    |        |     |        |         |                                                                                     |
| 1.5                   | 12400                | 953     | 113300                             | 1.45                  |                                                                                    |        |     |        |         |                                                                                     |
| 1.7                   | 10900                | 845     | 115800                             | 1.65                  |                                                                                    |        |     |        |         |                                                                                     |
| 1.9                   | 9850                 | 764     | 117500                             | 1.85                  |                                                                                    |        |     |        |         |                                                                                     |
| 2.1                   | 8760                 | 680     | 118900                             | 2.0                   |                                                                                    |        |     |        |         |                                                                                     |
| 2.5                   | 7350                 | 576     | 120000                             | 2.4                   |                                                                                    |        |     |        |         |                                                                                     |
| 3.2                   | 5790                 | 446     | 120000                             | 3.1                   |                                                                                    |        |     |        |         |                                                                                     |
| 4.8                   | 3920                 | 302     | 120000                             | 4.6                   |                                                                                    |        |     |        |         |                                                                                     |
| 5.3                   | 3520                 | 273     | 120000                             | 5.1                   |                                                                                    |        |     |        |         |                                                                                     |
| 6.3                   | 2950                 | 232     | 120000                             | 6.1                   | FA<br>FAF<br>F<br>FF                                                               | 127R77 | DRN | 100LS4 | 445     | 456                                                                                 |
| 7.4                   | 2500                 | 197     | 120000                             | 7.2                   |                                                                                    |        |     |        |         |                                                                                     |
| 1.4                   | 14400                | 1077    | 85700                              | 0.85                  |                                                                                    |        |     |        |         |                                                                                     |
| 1.6                   | 12400                | 930     | 89600                              | 0.95                  |                                                                                    |        |     |        |         |                                                                                     |
| 1.8                   | 10900                | 820     | 90000                              | 1.10                  |                                                                                    |        |     |        |         |                                                                                     |
| 2.0                   | 9670                 | 727     | 90000                              | 1.25                  |                                                                                    |        |     |        |         |                                                                                     |
| 2.2                   | 8680                 | 648     | 90000                              | 1.40                  |                                                                                    |        |     |        |         |                                                                                     |
| 2.6                   | 7360                 | 549     | 90000                              | 1.65                  |                                                                                    |        |     |        |         |                                                                                     |
| 2.9                   | 6620                 | 495     | 90000                              | 1.80                  |                                                                                    |        |     |        |         |                                                                                     |
| 3.4                   | 5730                 | 428     | 90000                              | 2.1                   |                                                                                    |        |     |        |         |                                                                                     |
| 2.3                   | 8580                 | 640     | 47300                              | 0.90                  | FA<br>FAF<br>F<br>FF                                                               | 107R77 | DRN | 100LS4 | 295     | 456                                                                                 |
| 2.6                   | 7450                 | 560     | 50400                              | 1.05                  |                                                                                    |        |     |        |         |                                                                                     |
| 3.0                   | 6500                 | 489     | 52800                              | 1.20                  |                                                                                    |        |     |        |         |                                                                                     |
| 3.3                   | 5840                 | 436     | 54400                              | 1.30                  |                                                                                    |        |     |        |         |                                                                                     |
| 3.9                   | 4950                 | 370     | 56400                              | 1.55                  |                                                                                    |        |     |        |         |                                                                                     |
| 4.4                   | 4460                 | 333     | 57500                              | 1.70                  |                                                                                    |        |     |        |         |                                                                                     |
| 5.1                   | 3830                 | 285     | 31200                              | 1.10                  |                                                                                    |        |     |        |         |                                                                                     |
| 5.9                   | 3290                 | 245     | 32600                              | 1.30                  |                                                                                    |        |     |        |         |                                                                                     |
| 5.7                   | 3680                 | 254.40* | 59100                              | 2.1                   |                                                                                    |        |     |        |         |                                                                                     |
| 6.7                   | 3120                 | 215.37  | 60200                              | 2.5                   |                                                                                    |        |     |        |         |                                                                                     |
| 7.3                   | 2880                 | 199.31  | 60600                              | 2.7                   | FA<br>FAF<br>F<br>FF                                                               | 107    | DRN | 100LS4 | 255     | 440                                                                                 |
| 8.1                   | 2580                 | 178.64  | 61100                              | 3.0                   |                                                                                    |        |     |        |         |                                                                                     |
| 5.2                   | 4010                 | 276.77  | 30700                              | 1.05                  |                                                                                    |        |     |        |         |                                                                                     |
| 5.7                   | 3670                 | 253.41  | 31700                              | 1.15                  |                                                                                    |        |     |        |         |                                                                                     |
| 6.5                   | 3240                 | 223.88  | 32700                              | 1.35                  |                                                                                    |        |     |        |         |                                                                                     |
| 7.6                   | 2750                 | 189.92  | 33900                              | 1.55                  |                                                                                    |        |     |        |         |                                                                                     |
| 8.3                   | 2530                 | 174.87  | 34300                              | 1.70                  |                                                                                    |        |     |        |         |                                                                                     |
| 9.3                   | 2260                 | 156.30  | 34900                              | 1.90                  |                                                                                    |        |     |        |         |                                                                                     |
| 10                    | 2030                 | 140.71  | 35300                              | 2.1                   |                                                                                    |        |     |        |         |                                                                                     |
| 11                    | 1840                 | 127.42  | 35700                              | 2.3                   |                                                                                    |        |     |        |         |                                                                                     |
| 7.4                   | 2850                 | 197.20  | 23500                              | 1.05                  | FA<br>FAF<br>F<br>FF                                                               | 87     | DRN | 100LS4 | 115     | 428                                                                                 |
| 8.1                   | 2600                 | 179.97  | 24400                              | 1.15                  |                                                                                    |        |     |        |         |                                                                                     |
| 9.1                   | 2310                 | 159.61  | 25500                              | 1.30                  |                                                                                    |        |     |        |         |                                                                                     |
| 11                    | 1940                 | 134.16  | 26600                              | 1.55                  |                                                                                    |        |     |        |         |                                                                                     |
| 12                    | 1780                 | 123.29  | 27100                              | 1.70                  |                                                                                    |        |     |        |         |                                                                                     |
| 13                    | 1580                 | 109.49  | 27600                              | 1.90                  |                                                                                    |        |     |        |         |                                                                                     |
| 15                    | 1410                 | 97.89   | 28000                              | 2.1                   |                                                                                    |        |     |        |         |                                                                                     |
| 16                    | 1270                 | 88.01   | 28400                              | 2.4                   |                                                                                    |        |     |        |         |                                                                                     |
| 19                    | 1100                 | 76.39   | 27700                              | 2.7                   |                                                                                    |        |     |        |         |                                                                                     |
| 21                    | 990                  | 68.40   | 27000                              | 3.0                   |                                                                                    |        |     |        |         |                                                                                     |
| 26                    | 820                  | 56.75   | 25700                              | 3.6                   | FA<br>FAF<br>F<br>FF                                                               | 77     | DRN | 100LS4 | 77      | 422                                                                                 |
| 29                    | 725                  | 50.36   | 25000                              | 4.0                   |                                                                                    |        |     |        |         |                                                                                     |
| 32                    | 655                  | 45.28   | 24300                              | 4.3                   |                                                                                    |        |     |        |         |                                                                                     |
| 13                    | 1650                 | 114.45  | 14600                              | 0.90                  |                                                                                    |        |     |        |         |                                                                                     |
| 13                    | 1570                 | 108.46* | 15200                              | 0.95                  |                                                                                    |        |     |        |         |                                                                                     |
| 15                    | 1370                 | 94.93   | 16500                              | 1.10                  |                                                                                    |        |     |        |         |                                                                                     |
| 17                    | 1230                 | 85.52   | 17200                              | 1.20                  |                                                                                    |        |     |        |         |                                                                                     |
| 19                    | 1080                 | 75.02   | 18000                              | 1.40                  |                                                                                    |        |     |        |         |                                                                                     |
| 22                    | 960                  | 66.46   | 18400                              | 1.55                  |                                                                                    |        |     |        |         |                                                                                     |
| 25                    | 840                  | 58.32   | 18800                              | 1.80                  |                                                                                    |        |     |        |         |                                                                                     |
| 26                    | 800                  | 55.27   | 19000                              | 1.85                  | FA<br>FAF<br>F<br>FF                                                               | 77     | DRN | 100LS4 | 83      | 421                                                                                 |
| 30                    | 700                  | 48.37   | 19300                              | 2.1                   |                                                                                    |        |     |        |         |                                                                                     |
| 33                    | 630                  | 43.58   | 19400                              | 2.4                   |                                                                                    |        |     |        |         |                                                                                     |
|                       |                      |         |                                    |                       |                                                                                    |        |     |        |         |                                                                                     |


| <b>P<sub>m</sub> = 2.2 kW</b>      |                                   |          |                                                |                                    |                                                                                    |    |     |        |                       |                                                                                     |
|------------------------------------|-----------------------------------|----------|------------------------------------------------|------------------------------------|------------------------------------------------------------------------------------|----|-----|--------|-----------------------|-------------------------------------------------------------------------------------|
| <b>n<sub>a</sub></b><br><b>rpm</b> | <b>M<sub>a</sub></b><br><b>Nm</b> | <b>i</b> | <b>F<sub>Ra</sub><sup>1)</sup></b><br><b>N</b> | <b>SEW</b><br><b>f<sub>B</sub></b> |  |    |     |        | <b>m</b><br><b>kg</b> |  |
| 40                                 | 525                               | 36.58    | 19600                                          | 2.1                                | FA                                                                                 | 77 | DRN | 100LS4 | 75                    | 422                                                                                 |
| 46                                 | 455                               | 31.51    | 19800                                          | 3.0                                | FAF                                                                                | 77 | DRN | 100LS4 | 82                    | 421                                                                                 |
| 50                                 | 415                               | 28.75    | 19800                                          | 3.4                                | F                                                                                  | 77 | DRN | 100LS4 | 79                    | 420                                                                                 |
| 57                                 | 365                               | 25.50*   | 19900                                          | 4.1                                | FF                                                                                 | 77 | DRN | 100LS4 | 90                    | 421                                                                                 |
| 24                                 | 880                               | 61.07    | 9680                                           | 0.95                               | FA<br>FAF<br>F<br>FF                                                               | 67 | DRN | 100LS4 | 54                    | 416                                                                                 |
| 27                                 | 775                               | 53.73    | 10700                                          | 1.05                               |                                                                                    |    |     |        |                       |                                                                                     |
| 29                                 | 735                               | 50.74    | 11000                                          | 1.10                               |                                                                                    |    |     |        |                       |                                                                                     |
| 34                                 | 625                               | 43.20    | 11700                                          | 1.30                               |                                                                                    |    |     |        |                       |                                                                                     |
| 37                                 | 565                               | 39.26    | 12100                                          | 1.35                               |                                                                                    |    |     |        |                       |                                                                                     |
| 43                                 | 490                               | 34.01    | 12400                                          | 1.50                               | FA<br>FAF<br>F<br>FF                                                               | 67 | DRN | 100LS4 | 53                    | 416                                                                                 |
| 45                                 | 460                               | 32.08    | 12600                                          | 1.75                               |                                                                                    |    |     |        |                       |                                                                                     |
| 53                                 | 395                               | 27.41    | 12800                                          | 2.1                                |                                                                                    |    |     |        |                       |                                                                                     |
| 58                                 | 360                               | 25.13    | 12900                                          | 2.2                                |                                                                                    |    |     |        |                       |                                                                                     |
| 66                                 | 315                               | 22.05    | 13000                                          | 2.6                                |                                                                                    |    |     |        |                       |                                                                                     |
| 69                                 | 300                               | 20.90*   | 13000                                          | 2.7                                | FA<br>FAF<br>F<br>FF                                                               | 67 | DRN | 100LS4 | 55                    | 414                                                                                 |
| 79                                 | 265                               | 18.29    | 13000                                          | 3.1                                |                                                                                    |    |     |        |                       |                                                                                     |
| 32                                 | 645                               | 44.73    | 6640                                           | 0.95                               |                                                                                    |    |     |        |                       |                                                                                     |
| 38                                 | 550                               | 38.21    | 8640                                           | 1.10                               |                                                                                    |    |     |        |                       |                                                                                     |
| 41                                 | 515                               | 35.79    | 8590                                           | 1.15                               |                                                                                    |    |     |        |                       |                                                                                     |
| 48                                 | 435                               | 30.15    | 8430                                           | 1.35                               | FA<br>FAF<br>F<br>FF                                                               | 57 | DRN | 100LS4 | 50                    | 410                                                                                 |
| 58                                 | 360                               | 24.96    | 8200                                           | 1.60                               |                                                                                    |    |     |        |                       |                                                                                     |
| 68                                 | 305                               | 21.17    | 7980                                           | 1.95                               |                                                                                    |    |     |        |                       |                                                                                     |
| 76                                 | 275                               | 19.11    | 7820                                           | 2.2                                |                                                                                    |    |     |        |                       |                                                                                     |
| 86                                 | 240                               | 16.81    | 7630                                           | 2.5                                |                                                                                    |    |     |        |                       |                                                                                     |
| 91                                 | 230                               | 15.88    | 7540                                           | 2.6                                | FA<br>FAF<br>F<br>FF                                                               | 57 | DRN | 100LS4 | 55                    | 409                                                                                 |
| 56                                 | 370                               | 25.72    | 5560                                           | 1.05                               |                                                                                    |    |     |        |                       |                                                                                     |
| 66                                 | 315                               | 21.82    | 5510                                           | 1.25                               |                                                                                    |    |     |        |                       |                                                                                     |
| 74                                 | 285                               | 19.70    | 5460                                           | 1.40                               |                                                                                    |    |     |        |                       |                                                                                     |
| 84                                 | 250                               | 17.33    | 5390                                           | 1.60                               |                                                                                    |    |     |        |                       |                                                                                     |
| 89                                 | 235                               | 16.36    | 5350                                           | 1.70                               | FA<br>FAF<br>F<br>FF                                                               | 47 | DRN | 100LS4 | 42                    | 404                                                                                 |
| 104                                | 200                               | 13.93    | 5220                                           | 2.00                               |                                                                                    |    |     |        |                       |                                                                                     |
| 115                                | 183                               | 12.66    | 5140                                           | 2.2                                |                                                                                    |    |     |        |                       |                                                                                     |
| 132                                | 159                               | 10.97    | 5010                                           | 2.5                                |                                                                                    |    |     |        |                       |                                                                                     |
| 162                                | 130                               | 8.96     | 4710                                           | 2.5                                |                                                                                    |    |     |        |                       |                                                                                     |
| 101                                | 205                               | 14.33    | 2800                                           | 0.95                               | FA<br>FAF<br>F<br>FF                                                               | 37 | DRN | 100LS4 | 37                    | 398                                                                                 |
| 113                                | 186                               | 12.87    | 2810                                           | 1.05                               |                                                                                    |    |     |        |                       |                                                                                     |
| 131                                | 161                               | 11.08    | 2820                                           | 1.20                               |                                                                                    |    |     |        |                       |                                                                                     |
| 139                                | 151                               | 10.42    | 2810                                           | 1.25                               |                                                                                    |    |     |        |                       |                                                                                     |
| 162                                | 130                               | 8.97     | 2790                                           | 1.35                               |                                                                                    |    |     |        |                       |                                                                                     |
| 181                                | 116                               | 8.01     | 2760                                           | 1.45                               | FA<br>FAF<br>F<br>FF                                                               | 37 | DRN | 100LS4 | 39                    | 397                                                                                 |
| 215                                | 98                                | 6.74     | 2620                                           | 1.45                               |                                                                                    |    |     |        |                       |                                                                                     |
| 240                                | 88                                | 6.05     | 2580                                           | 1.55                               |                                                                                    |    |     |        |                       |                                                                                     |
| 278                                | 76                                | 5.21     | 2530                                           | 1.65                               |                                                                                    |    |     |        |                       |                                                                                     |
| 296                                | 71                                | 4.90     | 2510                                           | 1.70                               |                                                                                    |    |     |        |                       |                                                                                     |
| 344                                | 61                                | 4.22     | 2440                                           | 1.80                               | FA<br>FAF<br>F<br>FF                                                               | 37 | DRN | 100LS4 | 38                    | 396                                                                                 |
| 385                                | 55                                | 3.77     | 2390                                           | 1.90                               |                                                                                    |    |     |        |                       |                                                                                     |

| <b>P<sub>m</sub> = 3.0 kW</b>      |                                   |          |                                                |                                    |                                                                                      |        |     |       |                       |                                                                                       |
|------------------------------------|-----------------------------------|----------|------------------------------------------------|------------------------------------|--------------------------------------------------------------------------------------|--------|-----|-------|-----------------------|---------------------------------------------------------------------------------------|
| <b>n<sub>a</sub></b><br><b>rpm</b> | <b>M<sub>a</sub></b><br><b>Nm</b> | <b>i</b> | <b>F<sub>Ra</sub><sup>1)</sup></b><br><b>N</b> | <b>SEW</b><br><b>f<sub>B</sub></b> |  |        |     |       | <b>m</b><br><b>kg</b> |  |
| 1.2                                | 21100                             | 1169     | 89600                                          | 0.85                               | FA<br>FAF<br>F<br>FF                                                                 | 157R97 | DRN | 100L4 | 790                   | 456                                                                                   |
| 1.5                                | 17100                             | 953      | 102800                                         | 1.05                               |                                                                                      |        |     |       |                       |                                                                                       |
| 1.7                                | 15000                             | 845      | 107900                                         | 1.20                               |                                                                                      |        |     |       |                       |                                                                                       |
| 1.9                                | 13500                             | 764      | 111100                                         | 1.30                               |                                                                                      |        |     |       |                       |                                                                                       |
| 2.1                                | 12000                             | 680      | 114000                                         | 1.50                               |                                                                                      |        |     |       |                       |                                                                                       |
| 2.5                                | 10100                             | 576      | 117000                                         | 1.75                               |                                                                                      |        |     |       |                       |                                                                                       |
| 3.3                                | 7970                              | 446      | 119800                                         | 2.3                                |                                                                                      |        |     |       |                       |                                                                                       |
| 4.8                                | 5390                              | 302      | 120000                                         | 3.3                                |                                                                                      |        |     |       |                       |                                                                                       |
| 5.3                                | 4850                              | 273      | 120000                                         | 3.7                                | FA<br>FAF<br>F<br>FF                                                                 | 157R97 | DRN | 100L4 | 850                   | 456                                                                                   |
| 6.3                                | 4080                              | 232      | 120000                                         | 4.4                                |                                                                                      |        |     |       |                       |                                                                                       |
| 7.4                                | 3460                              | 197      | 120000                                         | 5.2                                |                                                                                      |        |     |       |                       |                                                                                       |





| P <sub>m</sub> = 3.0 kW |                      |         |                                    |                       |                                                                                    |        |     |       |         |                                                                                     |
|-------------------------|----------------------|---------|------------------------------------|-----------------------|------------------------------------------------------------------------------------|--------|-----|-------|---------|-------------------------------------------------------------------------------------|
| n <sub>a</sub><br>rpm   | M <sub>a</sub><br>Nm | i       | F <sub>Ra</sub> <sup>1)</sup><br>N | SEW<br>f <sub>B</sub> |  |        |     |       | m<br>kg |  |
| 2.0                     | 13200                | 727     | 88100                              | 0.90                  | FA                                                                                 | 127R77 | DRN | 100L4 | 455     | 456                                                                                 |
| 2.2                     | 11800                | 648     | 90000                              | 1.00                  | FAF                                                                                | 127R77 | DRN | 100L4 | 490     | 456                                                                                 |
| 2.6                     | 10000                | 549     | 90000                              | 1.20                  | F                                                                                  | 127R77 | DRN | 100L4 | 490     | 456                                                                                 |
| 2.9                     | 9040                 | 495     | 90000                              | 1.35                  | FF                                                                                 | 127R77 | DRN | 100L4 | 530     | 456                                                                                 |
| 3.3                     | 7970                 | 436     | 49000                              | 0.95                  | FA                                                                                 | 107R77 | DRN | 100L4 | 300     | 456                                                                                 |
| 3.9                     | 6760                 | 370     | 52200                              | 1.15                  | FAF                                                                                | 107R77 | DRN | 100L4 | 325     | 456                                                                                 |
| 4.4                     | 6080                 | 333     | 53800                              | 1.25                  | F                                                                                  | 107R77 | DRN | 100L4 | 320     | 456                                                                                 |
| 5.0                     | 5320                 | 291     | 55600                              | 1.45                  | FF                                                                                 | 107R77 | DRN | 100L4 | 345     | 456                                                                                 |
| 5.7                     | 5000                 | 254.40* | 56300                              | 1.55                  | FA                                                                                 | 107    | DRN | 100L4 | 265     | 440                                                                                 |
| 6.8                     | 4230                 | 215.37  | 57900                              | 1.80                  | FAF                                                                                | 107    | DRN | 100L4 | 285     | 439                                                                                 |
| 7.3                     | 3920                 | 199.31  | 58600                              | 1.95                  | F                                                                                  | 107    | DRN | 100L4 | 280     | 438                                                                                 |
| 8.2                     | 3510                 | 178.64  | 59400                              | 2.2                   | FF                                                                                 | 107    | DRN | 100L4 | 305     | 439                                                                                 |
| 9.0                     | 3170                 | 161.28* | 60100                              | 2.4                   |                                                                                    |        |     |       |         |                                                                                     |
| 6.5                     | 4400                 | 223.88  | 29600                              | 1.00                  | FA                                                                                 | 97     | DRN | 100L4 | 190     | 434                                                                                 |
| 7.7                     | 3730                 | 189.92  | 31500                              | 1.15                  | FAF                                                                                | 97     | DRN | 100L4 | 210     | 433                                                                                 |
| 8.3                     | 3440                 | 174.87  | 32300                              | 1.25                  | F                                                                                  | 97     | DRN | 100L4 | 195     | 432                                                                                 |
|                         |                      |         |                                    |                       | FF                                                                                 | 97     | DRN | 100L4 | 230     | 433                                                                                 |
| 9.3                     | 3070                 | 156.30  | 33100                              | 1.40                  |                                                                                    |        |     |       |         |                                                                                     |
| 10                      | 2760                 | 140.71  | 33800                              | 1.55                  | FA                                                                                 | 97     | DRN | 100L4 | 190     | 434                                                                                 |
| 11                      | 2500                 | 127.42  | 34400                              | 1.70                  | FAF                                                                                | 97     | DRN | 100L4 | 210     | 433                                                                                 |
| 13                      | 2220                 | 112.99  | 35000                              | 1.95                  | F                                                                                  | 97     | DRN | 100L4 | 195     | 432                                                                                 |
| 14                      | 2010                 | 102.16  | 35400                              | 2.1                   | FF                                                                                 | 97     | DRN | 100L4 | 230     | 433                                                                                 |
| 16                      | 1760                 | 89.85   | 35800                              | 2.4                   |                                                                                    |        |     |       |         |                                                                                     |
| 11                      | 2630                 | 134.16  | 24300                              | 1.15                  | FA                                                                                 | 87     | DRN | 100L4 | 125     | 428                                                                                 |
| 12                      | 2420                 | 123.29  | 25100                              | 1.25                  | FAF                                                                                | 87     | DRN | 100L4 | 135     | 427                                                                                 |
| 13                      | 2150                 | 109.49  | 26000                              | 1.40                  | F                                                                                  | 87     | DRN | 100L4 | 130     | 426                                                                                 |
|                         |                      |         |                                    |                       | FF                                                                                 | 87     | DRN | 100L4 | 145     | 427                                                                                 |
| 15                      | 1920                 | 97.89   | 26700                              | 1.55                  |                                                                                    |        |     |       |         |                                                                                     |
| 17                      | 1730                 | 88.01   | 26700                              | 1.75                  | FA                                                                                 | 87     | DRN | 100L4 | 125     | 428                                                                                 |
| 19                      | 1500                 | 76.39   | 26100                              | 2.0                   | FAF                                                                                | 87     | DRN | 100L4 | 135     | 427                                                                                 |
| 21                      | 1340                 | 68.40   | 25500                              | 2.2                   | F                                                                                  | 87     | DRN | 100L4 | 130     | 426                                                                                 |
| 26                      | 1110                 | 56.75   | 24600                              | 2.7                   | FF                                                                                 | 87     | DRN | 100L4 | 145     | 427                                                                                 |
| 29                      | 990                  | 50.36   | 23900                              | 3.0                   |                                                                                    |        |     |       |         |                                                                                     |
| 17                      | 1680                 | 85.52   | 14400                              | 0.90                  | FA                                                                                 | 77     | DRN | 100L4 | 84      | 422                                                                                 |
| 19                      | 1470                 | 75.02   | 15900                              | 1.00                  | FAF                                                                                | 77     | DRN | 100L4 | 91      | 421                                                                                 |
| 22                      | 1300                 | 66.46   | 16900                              | 1.15                  | F                                                                                  | 77     | DRN | 100L4 | 88      | 420                                                                                 |
|                         |                      |         |                                    |                       | FF                                                                                 | 77     | DRN | 100L4 | 98      | 421                                                                                 |
| 25                      | 1140                 | 58.32   | 17700                              | 1.30                  |                                                                                    |        |     |       |         |                                                                                     |
| 26                      | 1080                 | 55.27   | 18000                              | 1.40                  | FA                                                                                 | 77     | DRN | 100L4 | 84      | 422                                                                                 |
| 30                      | 950                  | 48.37   | 18500                              | 1.60                  | FAF                                                                                | 77     | DRN | 100L4 | 91      | 421                                                                                 |
| 33                      | 850                  | 43.58   | 18800                              | 1.75                  | F                                                                                  | 77     | DRN | 100L4 | 88      | 420                                                                                 |
| 38                      | 750                  | 38.23   | 19100                              | 2.00                  | FF                                                                                 | 77     | DRN | 100L4 | 98      | 421                                                                                 |
| 40                      | 715                  | 36.58   | 19200                              | 1.55                  |                                                                                    |        |     |       |         |                                                                                     |
| 46                      | 615                  | 31.51   | 19500                              | 2.2                   | FA                                                                                 | 77     | DRN | 100L4 | 83      | 422                                                                                 |
| 51                      | 565                  | 28.75   | 19600                              | 2.5                   | FAF                                                                                | 77     | DRN | 100L4 | 89      | 421                                                                                 |
| 57                      | 500                  | 25.50*  | 19700                              | 3.0                   | F                                                                                  | 77     | DRN | 100L4 | 86      | 420                                                                                 |
| 68                      | 420                  | 21.43   | 19800                              | 3.6                   | FF                                                                                 | 77     | DRN | 100L4 | 97      | 421                                                                                 |
| 34                      | 840                  | 43.20   | 10000                              | 0.95                  | FA                                                                                 | 67     | DRN | 100L4 | 61      | 416                                                                                 |
| 37                      | 770                  | 39.26   | 10700                              | 1.00                  | FAF                                                                                | 67     | DRN | 100L4 | 67      | 415                                                                                 |
| 43                      | 665                  | 34.01   | 11500                              | 1.10                  | F                                                                                  | 67     | DRN | 100L4 | 64      | 414                                                                                 |
|                         |                      |         |                                    |                       | FF                                                                                 | 67     | DRN | 100L4 | 70      | 415                                                                                 |
| 45                      | 630                  | 32.08   | 11700                              | 1.30                  |                                                                                    |        |     |       |         |                                                                                     |
| 53                      | 535                  | 27.41   | 12200                              | 1.50                  |                                                                                    |        |     |       |         |                                                                                     |
| 58                      | 490                  | 25.13   | 12400                              | 1.65                  | FA                                                                                 | 67     | DRN | 100L4 | 60      | 416                                                                                 |
| 66                      | 430                  | 22.05   | 12700                              | 1.90                  | FAF                                                                                | 67     | DRN | 100L4 | 66      | 415                                                                                 |
| 70                      | 410                  | 20.90*  | 12800                              | 2.00                  | F                                                                                  | 67     | DRN | 100L4 | 63      | 414                                                                                 |
| 80                      | 355                  | 18.29   | 12900                              | 2.3                   | FF                                                                                 | 67     | DRN | 100L4 | 69      | 415                                                                                 |
| 88                      | 320                  | 16.48   | 13000                              | 2.5                   |                                                                                    |        |     |       |         |                                                                                     |
| 101                     | 280                  | 14.46   | 13000                              | 2.9                   |                                                                                    |        |     |       |         |                                                                                     |

| P <sub>m</sub> = 3.0 kW |                      |       |                                    |                       |                                                                                    |    |     |       |         |                                                                                     |
|-------------------------|----------------------|-------|------------------------------------|-----------------------|------------------------------------------------------------------------------------|----|-----|-------|---------|-------------------------------------------------------------------------------------|
| n <sub>a</sub><br>rpm   | M <sub>a</sub><br>Nm | i     | F <sub>Ra</sub> <sup>1)</sup><br>N | SEW<br>f <sub>B</sub> |  |    |     |       | m<br>kg |  |
| 58                      | 490                  | 24.96 | 7420                               | 1.15                  | FA                                                                                 | 57 | DRN | 100L4 | 56      | 410                                                                                 |
| 69                      | 415                  | 21.17 | 7310                               | 1.45                  |                                                                                    |    |     |       |         |                                                                                     |
| 76                      | 375                  | 19.11 | 7220                               | 1.60                  |                                                                                    |    |     |       |         |                                                                                     |
| 87                      | 330                  | 16.81 | 7100                               | 1.80                  |                                                                                    |    |     |       |         |                                                                                     |
| 92                      | 310                  | 15.88 | 7040                               | 1.90                  |                                                                                    |    |     |       |         |                                                                                     |
| 108                     | 265                  | 13.52 | 6850                               | 2.3                   |                                                                                    |    |     |       |         |                                                                                     |
| 119                     | 240                  | 12.29 | 6730                               | 2.5                   | FAF                                                                                | 57 | DRN | 100L4 | 62      | 409                                                                                 |
| 137                     | 205                  | 10.64 | 6540                               | 2.9                   |                                                                                    |    |     |       |         |                                                                                     |
| 74                      | 385                  | 19.70 | 4760                               | 1.05                  |                                                                                    |    |     |       |         |                                                                                     |
| 84                      | 340                  | 17.33 | 4760                               | 1.15                  |                                                                                    |    |     |       |         |                                                                                     |
| 89                      | 320                  | 16.36 | 4760                               | 1.25                  |                                                                                    |    |     |       |         |                                                                                     |
| 104                     | 270                  | 13.93 | 4720                               | 1.45                  |                                                                                    |    |     |       |         |                                                                                     |
| 115                     | 245                  | 12.66 | 4690                               | 1.60                  | F                                                                                  | 47 | DRN | 100L4 | 50      | 402                                                                                 |
| 133                     | 215                  | 10.97 | 4620                               | 1.85                  |                                                                                    |    |     |       |         |                                                                                     |
| 163                     | 176                  | 8.96  | 4350                               | 1.85                  |                                                                                    |    |     |       |         |                                                                                     |
| 131                     | 215                  | 11.08 | 2340                               | 0.85                  |                                                                                    |    |     |       |         |                                                                                     |
| 140                     | 205                  | 10.42 | 2360                               | 0.90                  |                                                                                    |    |     |       |         |                                                                                     |
| 162                     | 176                  | 8.97  | 2400                               | 1.00                  |                                                                                    |    |     |       |         |                                                                                     |
| 182                     | 158                  | 8.01  | 2410                               | 1.10                  | FF                                                                                 | 37 | DRN | 100L4 | 44      | 398                                                                                 |
| 216                     | 133                  | 6.74  | 2290                               | 1.05                  |                                                                                    |    |     |       |         |                                                                                     |
| 241                     | 119                  | 6.05  | 2290                               | 1.15                  |                                                                                    |    |     |       |         |                                                                                     |
| 279                     | 103                  | 5.21  | 2280                               | 1.20                  |                                                                                    |    |     |       |         |                                                                                     |
| 297                     | 96                   | 4.90  | 2270                               | 1.25                  |                                                                                    |    |     |       |         |                                                                                     |
| 345                     | 83                   | 4.22  | 2240                               | 1.35                  |                                                                                    |    |     |       |         |                                                                                     |
| 386                     | 74                   | 3.77  | 2210                               | 1.40                  |                                                                                    |    |     |       |         |                                                                                     |


| P <sub>m</sub> = 4.0 kW |                      |         |                                    |                       |                                                                                      |        |     |       |         |                                                                                       |
|-------------------------|----------------------|---------|------------------------------------|-----------------------|--------------------------------------------------------------------------------------|--------|-----|-------|---------|---------------------------------------------------------------------------------------|
| n <sub>a</sub><br>rpm   | M <sub>a</sub><br>Nm | i       | F <sub>Ra</sub> <sup>1)</sup><br>N | SEW<br>f <sub>B</sub> |  |        |     |       | m<br>kg |  |
| 1.7                     | 20100                | 845     | 93100                              | 0.90                  | FA<br>FAF<br>F<br>FF                                                                 | 157R97 | DRN | 112M4 | 800     | 456                                                                                   |
| 1.9                     | 18100                | 764     | 99700                              | 1.00                  |                                                                                      |        |     |       |         |                                                                                       |
| 2.2                     | 16100                | 680     | 105200                             | 1.10                  |                                                                                      |        |     |       |         |                                                                                       |
| 2.5                     | 13600                | 576     | 111000                             | 1.30                  |                                                                                      |        |     |       |         |                                                                                       |
| 3.3                     | 10600                | 446     | 116300                             | 1.70                  |                                                                                      |        |     |       |         |                                                                                       |
| 4.8                     | 7220                 | 302     | 120000                             | 2.5                   |                                                                                      |        |     |       |         |                                                                                       |
| 5.4                     | 6500                 | 273     | 120000                             | 2.8                   |                                                                                      |        |     |       |         |                                                                                       |
| 6.3                     | 5480                 | 232     | 120000                             | 3.3                   |                                                                                      |        |     |       |         |                                                                                       |
| 7.4                     | 4650                 | 197     | 120000                             | 3.9                   |                                                                                      |        |     |       |         |                                                                                       |
| 2.7                     | 13300                | 549     | 87800                              | 0.90                  | FA                                                                                   | 127R77 | DRN | 112M4 | 460     | 456                                                                                   |
| 3.0                     | 12000                | 495     | 90000                              | 1.00                  | FAF                                                                                  | 127R77 | DRN | 112M4 | 500     | 456                                                                                   |
| 3.4                     | 10400                | 428     | 90000                              | 1.15                  | F                                                                                    | 127R77 | DRN | 112M4 | 500     | 456                                                                                   |
| 3.9                     | 9120                 | 376     | 90000                              | 1.30                  | FF                                                                                   | 127R77 | DRN | 112M4 | 540     | 456                                                                                   |
| 4.4                     | 8090                 | 333     | 48700                              | 0.95                  | FA                                                                                   | 107R77 | DRN | 112M4 | 310     | 456                                                                                   |
| 5.0                     | 7070                 | 291     | 51400                              | 1.10                  | FAF                                                                                  | 107R77 | DRN | 112M4 | 330     | 456                                                                                   |
| 5.7                     | 6200                 | 255     | 53500                              | 1.25                  | F                                                                                    | 107R77 | DRN | 112M4 | 325     | 456                                                                                   |
|                         |                      |         |                                    |                       | FF                                                                                   | 107R77 | DRN | 112M4 | 355     | 456                                                                                   |
| 5.8                     | 6630                 | 254.40* | 52500                              | 1.15                  | FA<br>FAF<br>F<br>FF                                                                 | 107    | DRN | 112M4 | 270     | 440                                                                                   |
| 6.8                     | 5610                 | 215.37  | 54900                              | 1.35                  |                                                                                      |        |     |       |         |                                                                                       |
| 7.4                     | 5200                 | 199.31  | 55900                              | 1.50                  |                                                                                      |        |     |       |         |                                                                                       |
| 8.2                     | 4660                 | 178.64  | 57000                              | 1.65                  |                                                                                      |        |     |       |         |                                                                                       |
| 9.1                     | 4200                 | 161.28* | 58000                              | 1.85                  |                                                                                      |        |     |       |         |                                                                                       |
| 10.0                    | 3820                 | 146.49  | 58800                              | 2.0                   |                                                                                      |        |     |       |         |                                                                                       |
| 11                      | 3390                 | 129.97  | 59600                              | 2.3                   |                                                                                      |        |     |       |         |                                                                                       |
| 12                      | 3070                 | 117.94  | 60200                              | 2.5                   |                                                                                      |        |     |       |         |                                                                                       |
| 14                      | 2640                 | 101.38* | 61000                              | 2.9                   |                                                                                      |        |     |       |         |                                                                                       |
| 8.4                     | 4560                 | 174.87  | 29100                              | 0.95                  | FA                                                                                   | 97     | DRN | 112M4 | 195     | 434                                                                                   |
| 9.4                     | 4070                 | 156.30  | 30500                              | 1.05                  | FAF                                                                                  | 97     | DRN | 112M4 | 220     | 433                                                                                   |
| 10                      | 3670                 | 140.71  | 31700                              | 1.15                  | F                                                                                    | 97     | DRN | 112M4 | 205     | 432                                                                                   |
| 11                      | 3320                 | 127.42  | 32500                              | 1.30                  | FF                                                                                   | 97     | DRN | 112M4 | 235     | 433                                                                                   |




| P <sub>m</sub> = 4.0 kW |                      |        |                                    |                       |                                                                                    |    |     |       |         |                                                                                     |
|-------------------------|----------------------|--------|------------------------------------|-----------------------|------------------------------------------------------------------------------------|----|-----|-------|---------|-------------------------------------------------------------------------------------|
| n <sub>a</sub><br>rpm   | M <sub>a</sub><br>Nm | i      | F <sub>Ra</sub> <sup>1)</sup><br>N | SEW<br>f <sub>B</sub> |  |    |     |       | m<br>kg |  |
| 13                      | 2940                 | 112.99 | 33400                              | 1.45                  | FA<br>FAF<br>F<br>FF                                                               | 97 | DRN | 112M4 | 195     | 434                                                                                 |
| 14                      | 2660                 | 102.16 | 34100                              | 1.60                  |                                                                                    |    |     |       |         |                                                                                     |
| 15                      | 2540                 | 97.58  | 34300                              | 1.70                  |                                                                                    |    |     |       |         |                                                                                     |
| 16                      | 2340                 | 89.85  | 34700                              | 1.85                  |                                                                                    |    |     |       |         |                                                                                     |
| 18                      | 2090                 | 80.31  | 35200                              | 2.0                   |                                                                                    |    |     |       |         |                                                                                     |
| 20                      | 1880                 | 72.29  | 35600                              | 2.3                   |                                                                                    |    |     |       |         |                                                                                     |
| 22                      | 1700                 | 65.47  | 35900                              | 2.5                   |                                                                                    |    |     |       |         |                                                                                     |
| 13                      | 2850                 | 109.49 | 23500                              | 1.05                  | FA                                                                                 | 87 | DRN | 112M4 | 135     | 428                                                                                 |
| 15                      | 2550                 | 97.89  | 24600                              | 1.15                  | FAF                                                                                | 87 | DRN | 112M4 | 145     | 427                                                                                 |
| 17                      | 2290                 | 88.01  | 24500                              | 1.30                  | F                                                                                  | 87 | DRN | 112M4 | 140     | 426                                                                                 |
|                         |                      |        |                                    |                       | FF                                                                                 | 87 | DRN | 112M4 | 155     | 427                                                                                 |
| 19                      | 1990                 | 76.39  | 24100                              | 1.50                  | FA                                                                                 | 87 | DRN | 112M4 | 135     | 428                                                                                 |
| 21                      | 1780                 | 68.40  | 23800                              | 1.70                  | FAF                                                                                | 87 | DRN | 112M4 | 145     | 427                                                                                 |
| 26                      | 1480                 | 56.75  | 23100                              | 2.0                   | F                                                                                  | 87 | DRN | 112M4 | 140     | 426                                                                                 |
| 29                      | 1310                 | 50.36  | 22600                              | 2.2                   | FF                                                                                 | 87 | DRN | 112M4 | 155     | 427                                                                                 |
| 32                      | 1180                 | 45.28  | 22200                              | 2.4                   |                                                                                    |    |     |       |         |                                                                                     |
| 22                      | 1730                 | 66.46  | 13900                              | 0.85                  | FA                                                                                 | 77 | DRN | 112M4 | 93      | 422                                                                                 |
| 25                      | 1520                 | 58.32  | 15600                              | 1.00                  | FAF                                                                                | 77 | DRN | 112M4 | 100     | 421                                                                                 |
| 26                      | 1440                 | 55.27  | 16100                              | 1.05                  | F                                                                                  | 77 | DRN | 112M4 | 97      | 420                                                                                 |
| 30                      | 1260                 | 48.37  | 17100                              | 1.20                  | FF                                                                                 | 77 | DRN | 112M4 | 110     | 421                                                                                 |
| 34                      | 1130                 | 43.58  | 17700                              | 1.30                  | FA                                                                                 | 77 | DRN | 112M4 | 93      | 422                                                                                 |
| 38                      | 990                  | 38.23  | 18300                              | 1.50                  | FAF                                                                                | 77 | DRN | 112M4 | 100     | 421                                                                                 |
| 43                      | 880                  | 33.74  | 18700                              | 1.70                  | F                                                                                  | 77 | DRN | 112M4 | 97      | 420                                                                                 |
| 49                      | 780                  | 29.91  | 19000                              | 1.90                  | FF                                                                                 | 77 | DRN | 112M4 | 110     | 421                                                                                 |
| 57                      | 665                  | 25.54  | 19300                              | 2.2                   |                                                                                    |    |     |       |         |                                                                                     |
| 46                      | 820                  | 31.51  | 18900                              | 1.70                  | FA                                                                                 | 77 | DRN | 112M4 | 92      | 422                                                                                 |
| 51                      | 750                  | 28.75  | 19100                              | 1.90                  | FAF                                                                                | 77 | DRN | 112M4 | 98      | 421                                                                                 |
| 57                      | 665                  | 25.50* | 19300                              | 2.2                   | F                                                                                  | 77 | DRN | 112M4 | 96      | 420                                                                                 |
| 68                      | 555                  | 21.43  | 19600                              | 2.7                   | FF                                                                                 | 77 | DRN | 112M4 | 105     | 421                                                                                 |
| 74                      | 510                  | 19.70  | 19700                              | 2.9                   |                                                                                    |    |     |       |         |                                                                                     |
| 53                      | 715                  | 27.41  | 11200                              | 1.15                  | FA<br>FAF<br>F<br>FF                                                               | 67 | DRN | 112M4 | 69      | 416                                                                                 |
| 58                      | 655                  | 25.13  | 11600                              | 1.25                  |                                                                                    |    |     |       |         |                                                                                     |
| 66                      | 575                  | 22.05  | 12000                              | 1.45                  |                                                                                    |    |     |       |         |                                                                                     |
| 70                      | 545                  | 20.90* | 12200                              | 1.50                  |                                                                                    |    |     |       |         |                                                                                     |
| 80                      | 475                  | 18.29  | 12500                              | 1.70                  |                                                                                    |    |     |       |         |                                                                                     |
| 89                      | 425                  | 16.48  | 12700                              | 1.90                  |                                                                                    |    |     |       |         |                                                                                     |
| 101                     | 375                  | 14.46  | 12900                              | 2.2                   |                                                                                    |    |     |       |         |                                                                                     |
| 115                     | 330                  | 12.76  | 13000                              | 2.5                   |                                                                                    |    |     |       |         |                                                                                     |
| 129                     | 295                  | 11.31  | 13000                              | 2.8                   |                                                                                    |    |     |       |         |                                                                                     |
| 152                     | 250                  | 9.66   | 13000                              | 3.2                   |                                                                                    |    |     |       |         |                                                                                     |
| 161                     | 235                  | 9.08   | 12900                              | 2.2                   |                                                                                    |    |     |       |         |                                                                                     |
| 170                     | 220                  | 8.60   | 12700                              | 2.5                   |                                                                                    |    |     |       |         |                                                                                     |
| 194                     | 196                  | 7.53   | 12300                              | 3.1                   |                                                                                    |    |     |       |         |                                                                                     |
| 216                     | 177                  | 6.78   | 12000                              | 3.5                   |                                                                                    |    |     |       |         |                                                                                     |
| 246                     | 155                  | 5.95   | 11600                              | 3.9                   |                                                                                    |    |     |       |         |                                                                                     |
| 279                     | 137                  | 5.25   | 11300                              | 4.3                   |                                                                                    |    |     |       |         |                                                                                     |
| 314                     | 121                  | 4.66   | 10900                              | 4.6                   |                                                                                    |    |     |       |         |                                                                                     |
| 368                     | 104                  | 3.97   | 10500                              | 4.8                   |                                                                                    |    |     |       |         |                                                                                     |
| 69                      | 550                  | 21.17  | 6490                               | 1.10                  | FA<br>FAF<br>F<br>FF                                                               | 57 | DRN | 112M4 | 66      | 410                                                                                 |
| 77                      | 495                  | 19.11  | 6480                               | 1.20                  |                                                                                    |    |     |       |         |                                                                                     |
| 87                      | 435                  | 16.81  | 6440                               | 1.35                  |                                                                                    |    |     |       |         |                                                                                     |
| 92                      | 410                  | 15.88  | 6420                               | 1.45                  |                                                                                    |    |     |       |         |                                                                                     |
| 108                     | 350                  | 13.52  | 6320                               | 1.70                  |                                                                                    |    |     |       |         |                                                                                     |
| 119                     | 320                  | 12.29  | 6240                               | 1.85                  |                                                                                    |    |     |       |         |                                                                                     |
| 138                     | 275                  | 10.64  | 6120                               | 2.2                   |                                                                                    |    |     |       |         |                                                                                     |
| 157                     | 240                  | 9.31   | 5820                               | 1.75                  |                                                                                    |    |     |       |         |                                                                                     |
| 179                     | 210                  | 8.19   | 5700                               | 1.95                  |                                                                                    |    |     |       |         |                                                                                     |
| 189                     | 200                  | 7.73   | 5650                               | 2.1                   |                                                                                    |    |     |       |         |                                                                                     |
| 222                     | 172                  | 6.58   | 5480                               | 2.4                   |                                                                                    |    |     |       |         |                                                                                     |
| 245                     | 156                  | 5.98   | 5380                               | 2.7                   |                                                                                    |    |     |       |         |                                                                                     |
| 282                     | 135                  | 5.18   | 5220                               | 3.1                   |                                                                                    |    |     |       |         |                                                                                     |


| P <sub>m</sub> = 5.5 kW |                      |         |                                    |                       |                                                                                    |        |     |       |         |                                                                                     |
|-------------------------|----------------------|---------|------------------------------------|-----------------------|------------------------------------------------------------------------------------|--------|-----|-------|---------|-------------------------------------------------------------------------------------|
| n <sub>a</sub><br>rpm   | M <sub>a</sub><br>Nm | i       | F <sub>Ra</sub> <sup>1)</sup><br>N | SEW<br>f <sub>B</sub> |  |        |     |       | m<br>kg |  |
| 2.5                     | 18900                | 576     | 97200                              | 0.95                  | FA<br>FAF<br>F<br>FF                                                               | 157R97 | DRN | 132S4 | 810     | 456                                                                                 |
| 2.9                     | 16500                | 503     | 104400                             | 1.10                  |                                                                                    |        |     |       |         |                                                                                     |
| 3.3                     | 14800                | 446     | 108500                             | 1.20                  |                                                                                    |        |     |       |         |                                                                                     |
| 4.2                     | 11500                | 353     | 114900                             | 1.55                  |                                                                                    |        |     |       |         |                                                                                     |
| 4.8                     | 10000                | 302     | 117200                             | 1.80                  |                                                                                    |        |     |       |         |                                                                                     |
| 5.4                     | 9040                 | 273     | 118500                             | 2.00                  |                                                                                    |        |     |       |         |                                                                                     |
| 6.3                     | 7630                 | 232     | 120000                             | 2.4                   |                                                                                    |        |     |       |         |                                                                                     |
| 7.2                     | 6630                 | 202     | 120000                             | 2.7                   |                                                                                    |        |     |       |         |                                                                                     |
| 7.4                     | 6470                 | 197     | 120000                             | 2.8                   |                                                                                    |        |     |       |         |                                                                                     |
| 3.5                     | 13900                | 418     | 86700                              | 0.85                  | FA<br>FAF<br>F<br>FF                                                               | 127R87 | DRN | 132S4 | 495     | 456                                                                                 |
| 3.9                     | 12400                | 374     | 89600                              | 0.95                  |                                                                                    |        |     |       |         |                                                                                     |
| 4.7                     | 10300                | 312     | 90000                              | 1.15                  |                                                                                    |        |     |       |         |                                                                                     |
| 5.0                     | 9730                 | 293     | 90000                              | 1.25                  |                                                                                    |        |     |       |         |                                                                                     |
| 5.6                     | 8590                 | 259     | 90000                              | 1.40                  |                                                                                    |        |     |       |         |                                                                                     |
| 6.5                     | 7410                 | 223     | 90000                              | 1.60                  |                                                                                    |        |     |       |         |                                                                                     |
| 3.4                     | 14300                | 428     | 85800                              | 0.85                  | FA                                                                                 | 127R77 | DRN | 132S4 | 475     | 456                                                                                 |
|                         |                      |         |                                    |                       | FAF                                                                                | 127R77 | DRN | 132S4 | 510     | 456                                                                                 |
|                         |                      |         |                                    |                       | F                                                                                  | 127R77 | DRN | 132S4 | 510     | 456                                                                                 |
|                         |                      |         |                                    |                       | FF                                                                                 | 127R77 | DRN | 132S4 | 550     | 456                                                                                 |
| 6.8                     | 7740                 | 215.37  | 49600                              | 1.00                  | FA                                                                                 | 107    | DRN | 132S4 | 285     | 440                                                                                 |
| 7.3                     | 7160                 | 199.31  | 51200                              | 1.05                  | FAF                                                                                | 107    | DRN | 132S4 | 305     | 439                                                                                 |
| 8.2                     | 6420                 | 178.64  | 53000                              | 1.20                  | F                                                                                  | 107    | DRN | 132S4 | 300     | 438                                                                                 |
| 9.1                     | 5790                 | 161.28* | 54500                              | 1.30                  | FF                                                                                 | 107    | DRN | 132S4 | 325     | 439                                                                                 |
| 10.0                    | 5260                 | 146.49  | 55700                              | 1.45                  | FA<br>FAF<br>F<br>FF                                                               | 107    | DRN | 132S4 | 285     | 440                                                                                 |
| 11                      | 4670                 | 129.97  | 57000                              | 1.65                  |                                                                                    |        |     |       |         |                                                                                     |
| 12                      | 4230                 | 117.94  | 57900                              | 1.80                  |                                                                                    |        |     |       |         |                                                                                     |
| 14                      | 3640                 | 101.38* | 59100                              | 2.1                   |                                                                                    |        |     |       |         |                                                                                     |
| 16                      | 3320                 | 92.47*  | 59800                              | 2.3                   |                                                                                    |        |     |       |         |                                                                                     |
| 17                      | 3180                 | 88.49   | 60000                              | 2.4                   |                                                                                    |        |     |       |         |                                                                                     |
| 17                      | 3010                 | 83.99   | 60400                              | 2.5                   |                                                                                    |        |     |       |         |                                                                                     |
| 11                      | 4580                 | 127.42  | 29000                              | 0.95                  | FA                                                                                 | 97     | DRN | 132S4 | 210     | 434                                                                                 |
| 13                      | 4060                 | 112.99  | 30600                              | 1.05                  | FAF                                                                                | 97     | DRN | 132S4 | 230     | 433                                                                                 |
| 14                      | 3670                 | 102.16  | 31700                              | 1.15                  | F                                                                                  | 97     | DRN | 132S4 | 215     | 432                                                                                 |
|                         |                      |         |                                    |                       | FF                                                                                 | 97     | DRN | 132S4 | 250     | 433                                                                                 |
| 15                      | 3500                 | 97.58   | 32100                              | 1.25                  | FA<br>FAF<br>F<br>FF                                                               | 97     | DRN | 132S4 | 210     | 434                                                                                 |
| 16                      | 3220                 | 89.85   | 32800                              | 1.35                  |                                                                                    |        |     |       |         |                                                                                     |
| 17                      | 3110                 | 86.59   | 33100                              | 1.40                  |                                                                                    |        |     |       |         |                                                                                     |
| 18                      | 2880                 | 80.31   | 33600                              | 1.50                  |                                                                                    |        |     |       |         |                                                                                     |
| 19                      | 2710                 | 75.63   | 33900                              | 1.60                  |                                                                                    |        |     |       |         |                                                                                     |
| 20                      | 2590                 | 72.29   | 34200                              | 1.65                  |                                                                                    |        |     |       |         |                                                                                     |
| 22                      | 2350                 | 65.47   | 34700                              | 1.85                  |                                                                                    |        |     |       |         |                                                                                     |
| 25                      | 2080                 | 58.06   | 34400                              | 2.1                   |                                                                                    |        |     |       |         |                                                                                     |
| 28                      | 1880                 | 52.49   | 33700                              | 2.3                   |                                                                                    |        |     |       |         |                                                                                     |
| 17                      | 3160                 | 88.01   | 11900                              | 0.95                  | FA                                                                                 | 87     | DRN | 132S4 | 145     | 428                                                                                 |
| 19                      | 2740                 | 76.39   | 21200                              | 1.10                  | FAF                                                                                | 87     | DRN | 132S4 | 155     | 427                                                                                 |
| 21                      | 2450                 | 68.40   | 21200                              | 1.20                  | F                                                                                  | 87     | DRN | 132S4 | 150     | 426                                                                                 |
| 26                      | 2040                 | 56.75   | 21000                              | 1.45                  | FF                                                                                 | 87     | DRN | 132S4 | 165     | 427                                                                                 |
| 29                      | 1810                 | 50.36   | 20700                              | 1.60                  | FA<br>FAF<br>F<br>FF                                                               | 87     | DRN | 132S4 | 145     | 428                                                                                 |
| 32                      | 1620                 | 45.28   | 20500                              | 1.75                  |                                                                                    |        |     |       |         |                                                                                     |
| 37                      | 1410                 | 39.30   | 20100                              | 1.95                  |                                                                                    |        |     |       |         |                                                                                     |
| 42                      | 1260                 | 35.19   | 19700                              | 2.1                   |                                                                                    |        |     |       |         |                                                                                     |
| 50                      | 1040                 | 29.20   | 19100                              | 2.4                   |                                                                                    |        |     |       |         |                                                                                     |
| 43                      | 1210                 | 33.92   | 19600                              | 2.1                   | FA                                                                                 | 87     | DRN | 132S4 | 140     | 428                                                                                 |
| 51                      | 1030                 | 28.78   | 19000                              | 2.4                   | FAF                                                                                | 87     | DRN | 132S4 | 155     | 427                                                                                 |
| 55                      | 950                  | 26.50   | 18700                              | 3.2                   | F                                                                                  | 87     | DRN | 132S4 | 145     | 426                                                                                 |
| 62                      | 850                  | 23.68   | 18300                              | 3.5                   | FF                                                                                 | 87     | DRN | 132S4 | 160     | 427                                                                                 |
| 30                      | 1730                 | 48.37   | 13900                              | 0.85                  | FA<br>FAF<br>F<br>FF                                                               | 77     | DRN | 132S4 | 105     | 422                                                                                 |
| 34                      | 1560                 | 43.58   | 15300                              | 0.95                  |                                                                                    |        |     |       |         |                                                                                     |
| 38                      | 1370                 | 38.23   | 16500                              | 1.10                  |                                                                                    |        |     |       |         |                                                                                     |
| 43                      | 1210                 | 33.74   | 17400                              | 1.25                  |                                                                                    |        |     |       |         |                                                                                     |
| 49                      | 1070                 | 29.91   | 18000                              | 1.40                  |                                                                                    |        |     |       |         |                                                                                     |
| 57                      | 910                  | 25.54   | 18600                              | 1.60                  |                                                                                    |        |     |       |         |                                                                                     |


**P<sub>m</sub> = 5.5 kW**

| n <sub>a</sub><br>rpm | M <sub>a</sub><br>Nm | i      | F <sub>Ra</sub> <sup>1)</sup><br>N | SEW<br>f <sub>B</sub> |  |    |     |       | m<br>kg |  |
|-----------------------|----------------------|--------|------------------------------------|-----------------------|------------------------------------------------------------------------------------|----|-----|-------|---------|-------------------------------------------------------------------------------------|
| 57                    | 910                  | 25.50* | 18600                              | 1.65                  | FA<br>FAF<br>F<br>FF                                                               | 77 | DRN | 132S4 | 105     | 422                                                                                 |
| 68                    | 770                  | 21.43  | 19100                              | 1.95                  |                                                                                    |    |     |       |         |                                                                                     |
| 74                    | 705                  | 19.70  | 19200                              | 2.1                   |                                                                                    |    |     |       |         |                                                                                     |
| 84                    | 625                  | 17.49  | 19400                              | 2.4                   |                                                                                    |    |     |       |         |                                                                                     |
| 93                    | 560                  | 15.64* | 19600                              | 2.7                   |                                                                                    |    |     |       |         |                                                                                     |
| 104                   | 505                  | 14.06  | 19200                              | 3.0                   |                                                                                    |    |     |       |         |                                                                                     |
| 120                   | 435                  | 12.20  | 18500                              | 3.4                   | FA<br>FAF<br>F<br>FF                                                               | 67 | DRN | 132S4 | 81      | 416                                                                                 |
| 66                    | 790                  | 22.05  | 10500                              | 1.05                  |                                                                                    |    |     |       |         |                                                                                     |
| 70                    | 750                  | 20.90* | 10900                              | 1.10                  |                                                                                    |    |     |       |         |                                                                                     |
| 80                    | 655                  | 18.29  | 11600                              | 1.25                  |                                                                                    |    |     |       |         |                                                                                     |
| 89                    | 590                  | 16.48  | 11900                              | 1.40                  |                                                                                    |    |     |       |         |                                                                                     |
| 101                   | 515                  | 14.46  | 12300                              | 1.60                  |                                                                                    |    |     |       |         |                                                                                     |
| 115                   | 455                  | 12.76  | 12600                              | 1.80                  |                                                                                    |    |     |       |         |                                                                                     |
| 129                   | 405                  | 11.31  | 12800                              | 2.0                   |                                                                                    |    |     |       |         |                                                                                     |
| 151                   | 345                  | 9.66   | 12900                              | 2.4                   |                                                                                    |    |     |       |         |                                                                                     |
| 161                   | 325                  | 9.08   | 12400                              | 1.60                  |                                                                                    |    |     |       |         |                                                                                     |
| 170                   | 305                  | 8.60   | 12200                              | 1.85                  |                                                                                    |    |     |       |         |                                                                                     |
| 194                   | 270                  | 7.53   | 11900                              | 2.2                   |                                                                                    |    |     |       |         |                                                                                     |
| 215                   | 240                  | 6.78   | 11600                              | 2.5                   |                                                                                    |    |     |       |         |                                                                                     |
| 246                   | 210                  | 5.95   | 11300                              | 2.8                   |                                                                                    |    |     |       |         |                                                                                     |
| 278                   | 189                  | 5.25   | 11000                              | 3.1                   |                                                                                    |    |     |       |         |                                                                                     |
| 314                   | 167                  | 4.66   | 10700                              | 3.4                   |                                                                                    |    |     |       |         |                                                                                     |
| 368                   | 143                  | 3.97   | 10300                              | 3.5                   |                                                                                    |    |     |       |         |                                                                                     |
| 87                    | 600                  | 16.81  | 5460                               | 1.00                  | FA<br>FAF<br>F<br>FF                                                               | 57 | DRN | 132S4 | 77      | 410                                                                                 |
| 92                    | 570                  | 15.88  | 5490                               | 1.05                  |                                                                                    |    |     |       |         |                                                                                     |
| 108                   | 485                  | 13.52  | 5530                               | 1.25                  |                                                                                    |    |     |       |         |                                                                                     |
| 119                   | 440                  | 12.29  | 5530                               | 1.35                  |                                                                                    |    |     |       |         |                                                                                     |
| 137                   | 380                  | 10.64  | 5500                               | 1.55                  |                                                                                    |    |     |       |         |                                                                                     |
| 178                   | 290                  | 8.19   | 5180                               | 1.45                  |                                                                                    |    |     |       |         |                                                                                     |
| 189                   | 275                  | 7.73   | 5150                               | 1.50                  |                                                                                    |    |     |       |         |                                                                                     |
| 222                   | 235                  | 6.58   | 5060                               | 1.75                  |                                                                                    |    |     |       |         |                                                                                     |
| 244                   | 215                  | 5.98   | 4990                               | 1.95                  |                                                                                    |    |     |       |         |                                                                                     |
| 282                   | 186                  | 5.18   | 4880                               | 2.2                   |                                                                                    |    |     |       |         |                                                                                     |


**P<sub>m</sub> = 7.5 kW**

| n <sub>a</sub><br>rpm | M <sub>a</sub><br>Nm | i       | F <sub>Ra</sub> <sup>1)</sup><br>N | SEW<br>f <sub>B</sub> |  |        |     |       | m<br>kg |  |
|-----------------------|----------------------|---------|------------------------------------|-----------------------|--------------------------------------------------------------------------------------|--------|-----|-------|---------|---------------------------------------------------------------------------------------|
| 3.3                   | 20200                | 446     | 93100                              | 0.90                  | FA<br>FAF<br>F<br>FF                                                                 | 157R97 | DRN | 132M4 | 830     | 456                                                                                   |
| 4.2                   | 15800                | 353     | 106200                             | 1.15                  |                                                                                      |        |     |       |         |                                                                                       |
| 4.9                   | 13600                | 302     | 111000                             | 1.30                  |                                                                                      |        |     |       |         |                                                                                       |
| 5.4                   | 12300                | 273     | 113500                             | 1.45                  |                                                                                      |        |     |       |         |                                                                                       |
| 6.3                   | 10400                | 232     | 116600                             | 1.75                  |                                                                                      |        |     |       |         |                                                                                       |
| 7.3                   | 9080                 | 202     | 118500                             | 2.00                  |                                                                                      |        |     |       |         |                                                                                       |
| 7.5                   | 8840                 | 197     | 118800                             | 2.0                   | FA<br>FAF<br>F<br>FF                                                                 | 127R87 | DRN | 132M4 | 510     | 456                                                                                   |
| 4.7                   | 14100                | 312     | 86300                              | 0.85                  |                                                                                      |        |     |       |         |                                                                                       |
| 5.0                   | 13200                | 293     | 88000                              | 0.90                  |                                                                                      |        |     |       |         |                                                                                       |
| 5.7                   | 11700                | 259     | 90000                              | 1.00                  |                                                                                      |        |     |       |         |                                                                                       |
| 6.6                   | 10100                | 223     | 90000                              | 1.20                  |                                                                                      |        |     |       |         |                                                                                       |
| 7.4                   | 8950                 | 198     | 90000                              | 1.35                  |                                                                                      |        |     |       |         |                                                                                       |
| 8.6                   | 8330                 | 170.83  | 90000                              | 1.45                  | FA<br>FAF<br>F<br>FF                                                                 | 127    | DRN | 132M4 | 445     | 446                                                                                   |
| 9.6                   | 7490                 | 153.67* | 90000                              | 1.60                  |                                                                                      |        |     |       |         |                                                                                       |
| 12                    | 6110                 | 125.37  | 90000                              | 1.95                  |                                                                                      |        |     |       |         |                                                                                       |
| 8.2                   | 8710                 | 178.64  | 47000                              | 0.90                  |                                                                                      |        |     |       |         |                                                                                       |
| 9.1                   | 7860                 | 161.28* | 49300                              | 1.00                  | FA<br>FAF<br>F<br>FF                                                                 | 107    | DRN | 132M4 | 300     | 440                                                                                   |
| 10                    | 7140                 | 146.49  | 51200                              | 1.05                  |                                                                                      |        |     |       |         |                                                                                       |
| 11                    | 6340                 | 129.97  | 53200                              | 1.20                  |                                                                                      |        |     |       |         |                                                                                       |
| 12                    | 5750                 | 117.94  | 54600                              | 1.35                  |                                                                                      |        |     |       |         |                                                                                       |
| 14                    | 4940                 | 101.38* | 56400                              | 1.55                  |                                                                                      |        |     |       |         |                                                                                       |
| 16                    | 4510                 | 92.47*  | 57400                              | 1.70                  |                                                                                      |        |     |       |         |                                                                                       |
| 17                    | 4310                 | 88.49   | 57800                              | 1.80                  | FA<br>FAF<br>F<br>FF                                                                 | 107    | DRN | 132M4 | 320     | 439                                                                                   |
| 17                    | 4090                 | 83.99   | 58200                              | 1.85                  |                                                                                      |        |     |       |         |                                                                                       |
| 20                    | 3630                 | 74.52   | 59200                              | 2.1                   |                                                                                      |        |     |       |         |                                                                                       |
| 22                    | 3290                 | 67.62   | 59800                              | 2.3                   |                                                                                      |        |     |       |         |                                                                                       |


| <b>P<sub>m</sub> = 7.5 kW</b>      |                                   |          |                                                |                                    |                                                                                    |    |     |       |                          |                                                                                     |
|------------------------------------|-----------------------------------|----------|------------------------------------------------|------------------------------------|------------------------------------------------------------------------------------|----|-----|-------|--------------------------|-------------------------------------------------------------------------------------|
| <b>n<sub>a</sub></b><br><b>rpm</b> | <b>M<sub>a</sub></b><br><b>Nm</b> | <b>i</b> | <b>F<sub>Ra</sub><sup>1)</sup></b><br><b>N</b> | <b>SEW</b><br><b>f<sub>B</sub></b> |  |    |     |       | <b>m</b><br><b>kg</b>    |  |
| 15                                 | 4760                              | 97.58    | 24600                                          | 0.90                               | FA<br>FAF<br>F<br>FF                                                               | 97 | DRN | 132M4 | 225<br>245<br>235<br>265 | 434<br>433<br>432<br>433                                                            |
| 16                                 | 4380                              | 89.85    | 29600                                          | 1.00                               |                                                                                    |    |     |       |                          |                                                                                     |
| 17                                 | 4220                              | 86.59    | 30100                                          | 1.00                               |                                                                                    |    |     |       |                          |                                                                                     |
| 18                                 | 3910                              | 80.31    | 31000                                          | 1.10                               |                                                                                    |    |     |       |                          |                                                                                     |
| 19                                 | 3680                              | 75.63    | 31600                                          | 1.15                               |                                                                                    |    |     |       |                          |                                                                                     |
| 20                                 | 3520                              | 72.29    | 32000                                          | 1.20                               | FA<br>FAF<br>F<br>FF                                                               | 97 | DRN | 132M4 | 225<br>245<br>235<br>265 | 434<br>433<br>432<br>433                                                            |
| 22                                 | 3190                              | 65.47    | 32200                                          | 1.35                               |                                                                                    |    |     |       |                          |                                                                                     |
| 25                                 | 2830                              | 58.06    | 31700                                          | 1.50                               |                                                                                    |    |     |       |                          |                                                                                     |
| 28                                 | 2560                              | 52.49    | 31300                                          | 1.70                               |                                                                                    |    |     |       |                          |                                                                                     |
| 33                                 | 2170                              | 44.49    | 30500                                          | 2.00                               |                                                                                    |    |     |       |                          |                                                                                     |
| 38                                 | 1890                              | 38.86    | 29800                                          | 2.3                                | FA<br>FAF<br>F<br>FF                                                               | 97 | DRN | 132M4 | 220<br>240<br>225<br>260 | 434<br>433<br>432<br>433                                                            |
| 45                                 | 1580                              | 32.50    | 28800                                          | 2.7                                |                                                                                    |    |     |       |                          |                                                                                     |
| 34                                 | 2110                              | 43.28    | 30400                                          | 1.45                               |                                                                                    |    |     |       |                          |                                                                                     |
| 40                                 | 1780                              | 36.64    | 29500                                          | 1.70                               |                                                                                    |    |     |       |                          |                                                                                     |
| 43                                 | 1650                              | 33.91    | 29000                                          | 2.6                                |                                                                                    |    |     |       |                          |                                                                                     |
| 48                                 | 1480                              | 30.39    | 28400                                          | 2.9                                | FA<br>FAF<br>F<br>FF                                                               | 87 | DRN | 132M4 | 160<br>175<br>165<br>185 | 428<br>427<br>426<br>427                                                            |
| 26                                 | 2760                              | 56.75    | 18100                                          | 1.10                               |                                                                                    |    |     |       |                          |                                                                                     |
| 29                                 | 2450                              | 50.36    | 18200                                          | 1.20                               |                                                                                    |    |     |       |                          |                                                                                     |
| 32                                 | 2200                              | 45.28    | 18200                                          | 1.30                               |                                                                                    |    |     |       |                          |                                                                                     |
| 37                                 | 1910                              | 39.30    | 18100                                          | 1.40                               |                                                                                    |    |     |       |                          |                                                                                     |
| 42                                 | 1710                              | 35.19    | 17900                                          | 1.50                               | FA<br>FAF<br>F<br>FF                                                               | 87 | DRN | 132M4 | 160<br>170<br>165<br>180 | 428<br>427<br>426<br>427                                                            |
| 50                                 | 1420                              | 29.20    | 17600                                          | 1.75                               |                                                                                    |    |     |       |                          |                                                                                     |
| 51                                 | 1400                              | 28.78    | 17500                                          | 1.75                               |                                                                                    |    |     |       |                          |                                                                                     |
| 55                                 | 1290                              | 26.50    | 17400                                          | 2.3                                |                                                                                    |    |     |       |                          |                                                                                     |
| 62                                 | 1150                              | 23.68    | 17100                                          | 2.6                                |                                                                                    |    |     |       |                          |                                                                                     |
| 69                                 | 1040                              | 21.32*   | 16800                                          | 2.9                                | FA<br>FAF<br>F<br>FF                                                               | 77 | DRN | 132M4 | 125<br>130<br>125<br>135 | 422<br>421<br>420<br>421                                                            |
| 76                                 | 940                               | 19.31    | 16500                                          | 3.2                                |                                                                                    |    |     |       |                          |                                                                                     |
| 86                                 | 830                               | 17.12    | 16100                                          | 3.6                                |                                                                                    |    |     |       |                          |                                                                                     |
| 95                                 | 755                               | 15.48    | 15800                                          | 4.0                                |                                                                                    |    |     |       |                          |                                                                                     |
| 44                                 | 1640                              | 33.74    | 14700                                          | 0.90                               | FA<br>FAF<br>F<br>FF                                                               | 77 | DRN | 132M4 | 120<br>130<br>125<br>135 | 422<br>421<br>420<br>421                                                            |
| 49                                 | 1450                              | 29.91    | 16000                                          | 1.05                               |                                                                                    |    |     |       |                          |                                                                                     |
| 57                                 | 1240                              | 25.54    | 17200                                          | 1.15                               |                                                                                    |    |     |       |                          |                                                                                     |
| 58                                 | 1240                              | 25.50*   | 17200                                          | 1.20                               |                                                                                    |    |     |       |                          |                                                                                     |
| 68                                 | 1040                              | 21.43    | 18100                                          | 1.45                               | FA<br>FAF<br>F<br>FF                                                               | 77 | DRN | 132M4 | 120<br>130<br>125<br>135 | 422<br>421<br>420<br>421                                                            |
| 75                                 | 960                               | 19.70    | 18500                                          | 1.55                               |                                                                                    |    |     |       |                          |                                                                                     |
| 84                                 | 850                               | 17.49    | 18800                                          | 1.75                               |                                                                                    |    |     |       |                          |                                                                                     |
| 94                                 | 760                               | 15.64*   | 18900                                          | 1.95                               |                                                                                    |    |     |       |                          |                                                                                     |
| 104                                | 685                               | 14.06    | 18500                                          | 2.2                                |                                                                                    |    |     |       |                          |                                                                                     |
| 120                                | 595                               | 12.20    | 17900                                          | 2.5                                |                                                                                    |    |     |       |                          |                                                                                     |
| 134                                | 530                               | 10.93    | 17500                                          | 2.8                                |                                                                                    |    |     |       |                          |                                                                                     |
| 158                                | 450                               | 9.30     | 16400                                          | 2.4                                |                                                                                    |    |     |       |                          |                                                                                     |
| 178                                | 400                               | 8.26     | 16000                                          | 2.7                                |                                                                                    |    |     |       |                          |                                                                                     |
| 199                                | 360                               | 7.39     | 15600                                          | 3.0                                |                                                                                    |    |     |       |                          |                                                                                     |
| 221                                | 320                               | 6.64     | 15300                                          | 3.3                                |                                                                                    |    |     |       |                          |                                                                                     |
| 255                                | 280                               | 5.76     | 14800                                          | 3.8                                | FA<br>FAF<br>F<br>FF                                                               | 77 | DRN | 132M4 | 520<br>560<br>560<br>600 | 456<br>456<br>456<br>456                                                            |
| 284                                | 250                               | 5.16     | 14400                                          | 4.3                                |                                                                                    |    |     |       |                          |                                                                                     |
| 343                                | 205                               | 4.28     | 13700                                          | 4.8                                |                                                                                    |    |     |       |                          |                                                                                     |

| <b>P<sub>m</sub> = 9.2 kW</b>      |                                   |          |                                                |                                    |                                                                                      |        |     |       |                          |                                                                                       |
|------------------------------------|-----------------------------------|----------|------------------------------------------------|------------------------------------|--------------------------------------------------------------------------------------|--------|-----|-------|--------------------------|---------------------------------------------------------------------------------------|
| <b>n<sub>a</sub></b><br><b>rpm</b> | <b>M<sub>a</sub></b><br><b>Nm</b> | <b>i</b> | <b>F<sub>Ra</sub><sup>1)</sup></b><br><b>N</b> | <b>SEW</b><br><b>f<sub>B</sub></b> |  |        |     |       | <b>m</b><br><b>kg</b>    |  |
| 4.2                                | 19400                             | 353      | 95600                                          | 0.90                               | FA<br>FAF<br>F<br>FF                                                                 | 157R97 | DRN | 132L4 | 840<br>890<br>860<br>960 | 456<br>456<br>456<br>456                                                              |
| 4.9                                | 16800                             | 302      | 103600                                         | 1.05                               |                                                                                      |        |     |       |                          |                                                                                       |
| 5.4                                | 15100                             | 273      | 107700                                         | 1.20                               |                                                                                      |        |     |       |                          |                                                                                       |
| 6.4                                | 12800                             | 232      | 112600                                         | 1.40                               |                                                                                      |        |     |       |                          |                                                                                       |
| 7.3                                | 11100                             | 202      | 115500                                         | 1.60                               |                                                                                      |        |     |       |                          |                                                                                       |
| 7.5                                | 10800                             | 197      | 116000                                         | 1.65                               | FA<br>FAF<br>F<br>FF                                                                 | 127R87 | DRN | 132L4 | 520<br>560<br>560<br>600 | 456<br>456<br>456<br>456                                                              |
| 5.7                                | 14300                             | 259      | 85800                                          | 0.85                               |                                                                                      |        |     |       |                          |                                                                                       |
| 6.6                                | 12400                             | 223      | 89600                                          | 0.95                               |                                                                                      |        |     |       |                          |                                                                                       |
| 7.4                                | 10900                             | 198      | 90000                                          | 1.10                               |                                                                                      |        |     |       |                          |                                                                                       |


**P<sub>m</sub> = 9.2 kW**

| n <sub>a</sub><br>rpm | M <sub>a</sub><br>Nm | i       | F <sub>Ra</sub> <sup>1)</sup><br>N | SEW<br>f <sub>B</sub> |  |     |     |       | m<br>kg |  |
|-----------------------|----------------------|---------|------------------------------------|-----------------------|------------------------------------------------------------------------------------|-----|-----|-------|---------|-------------------------------------------------------------------------------------|
| 8.6                   | 10200                | 170.83  | 90000                              | 1.20                  | FA                                                                                 | 127 | DRN | 132L4 | 455     | 446                                                                                 |
| 9.6                   | 9180                 | 153.67* | 90000                              | 1.30                  | FAF                                                                                | 127 | DRN | 132L4 | 490     | 445                                                                                 |
| 12                    | 7490                 | 125.37  | 90000                              | 1.60                  | F                                                                                  | 127 | DRN | 132L4 | 490     | 444                                                                                 |
| 13                    | 6830                 | 114.34  | 90000                              | 1.75                  | FF                                                                                 | 127 | DRN | 132L4 | 540     | 445                                                                                 |
| 15                    | 5910                 | 98.95   | 90000                              | 2.0                   |                                                                                    |     |     |       |         |                                                                                     |
| 10                    | 8750                 | 146.49  | 46800                              | 0.90                  | FA                                                                                 | 107 | DRN | 132L4 | 310     | 440                                                                                 |
| 11                    | 7760                 | 129.97  | 49600                              | 1.00                  | FAF                                                                                | 107 | DRN | 132L4 | 330     | 439                                                                                 |
| 12                    | 7040                 | 117.94  | 51500                              | 1.10                  | F                                                                                  | 107 | DRN | 132L4 | 325     | 438                                                                                 |
| 14                    | 6050                 | 101.38* | 53900                              | 1.25                  | FF                                                                                 | 107 | DRN | 132L4 | 355     | 439                                                                                 |
| 16                    | 5520                 | 92.47*  | 55100                              | 1.40                  |                                                                                    |     |     |       |         |                                                                                     |
| 18                    | 5010                 | 83.99   | 56300                              | 1.55                  | FA                                                                                 | 107 | DRN | 132L4 | 310     | 440                                                                                 |
| 20                    | 4450                 | 74.52   | 57500                              | 1.70                  | FAF                                                                                | 107 | DRN | 132L4 | 330     | 439                                                                                 |
| 22                    | 4040                 | 67.62   | 58300                              | 1.90                  | F                                                                                  | 107 | DRN | 132L4 | 325     | 438                                                                                 |
| 25                    | 3470                 | 58.12*  | 58000                              | 2.2                   | FF                                                                                 | 107 | DRN | 132L4 | 355     | 439                                                                                 |
| 29                    | 3030                 | 50.73   | 56500                              | 2.5                   |                                                                                    |     |     |       |         |                                                                                     |
| 18                    | 4790                 | 80.31   | 23100                              | 0.90                  | FA                                                                                 | 97  | DRN | 132L4 | 235     | 434                                                                                 |
| 19                    | 4520                 | 75.63   | 29200                              | 0.95                  | FAF                                                                                | 97  | DRN | 132L4 | 255     | 433                                                                                 |
| 20                    | 4320                 | 72.29   | 29600                              | 1.00                  | F                                                                                  | 97  | DRN | 132L4 | 240     | 432                                                                                 |
| 22                    | 3910                 | 65.47   | 29600                              | 1.10                  | FF                                                                                 | 97  | DRN | 132L4 | 275     | 433                                                                                 |
| 25                    | 3460                 | 58.06   | 29500                              | 1.25                  |                                                                                    |     |     |       |         |                                                                                     |
| 28                    | 3130                 | 52.49   | 29300                              | 1.35                  | FA                                                                                 | 97  | DRN | 132L4 | 235     | 434                                                                                 |
| 33                    | 2650                 | 44.49   | 28800                              | 1.60                  | FAF                                                                                | 97  | DRN | 132L4 | 255     | 433                                                                                 |
| 38                    | 2320                 | 38.86   | 28300                              | 1.85                  | F                                                                                  | 97  | DRN | 132L4 | 240     | 432                                                                                 |
| 45                    | 1940                 | 32.50   | 27500                              | 2.2                   | FF                                                                                 | 97  | DRN | 132L4 | 275     | 433                                                                                 |
| 43                    | 2020                 | 33.91   | 27700                              | 2.1                   | FA                                                                                 | 97  | DRN | 132L4 | 230     | 434                                                                                 |
| 48                    | 1810                 | 30.39   | 27200                              | 2.4                   | FAF                                                                                | 97  | DRN | 132L4 | 250     | 433                                                                                 |
| 54                    | 1630                 | 27.44*  | 26700                              | 2.6                   | F                                                                                  | 97  | DRN | 132L4 | 235     | 432                                                                                 |
| 59                    | 1480                 | 24.92   | 26200                              | 2.9                   | FF                                                                                 | 97  | DRN | 132L4 | 270     | 433                                                                                 |
| 29                    | 3000                 | 50.36   | 16000                              | 1.00                  | FA                                                                                 | 87  | DRN | 132L4 | 170     | 428                                                                                 |
| 32                    | 2700                 | 45.28   | 16300                              | 1.05                  | FAF                                                                                | 87  | DRN | 132L4 | 185     | 427                                                                                 |
| 37                    | 2340                 | 39.30   | 16400                              | 1.15                  | F                                                                                  | 87  | DRN | 132L4 | 175     | 426                                                                                 |
| 42                    | 2100                 | 35.19   | 16400                              | 1.25                  | FF                                                                                 | 87  | DRN | 132L4 | 190     | 427                                                                                 |
| 50                    | 1740                 | 29.20   | 16300                              | 1.45                  |                                                                                    |     |     |       |         |                                                                                     |
| 55                    | 1580                 | 26.50   | 16200                              | 1.90                  |                                                                                    |     |     |       |         |                                                                                     |
| 62                    | 1410                 | 23.68   | 16000                              | 2.1                   | FA                                                                                 | 87  | DRN | 132L4 | 165     | 428                                                                                 |
| 69                    | 1270                 | 21.32*  | 15900                              | 2.4                   | FAF                                                                                | 87  | DRN | 132L4 | 180     | 427                                                                                 |
| 76                    | 1150                 | 19.31   | 15600                              | 2.6                   | F                                                                                  | 87  | DRN | 132L4 | 175     | 426                                                                                 |
| 86                    | 1020                 | 17.12   | 15400                              | 2.9                   | FF                                                                                 | 87  | DRN | 132L4 | 190     | 427                                                                                 |
| 95                    | 920                  | 15.48   | 15100                              | 3.2                   |                                                                                    |     |     |       |         |                                                                                     |
| 112                   | 780                  | 13.12*  | 14600                              | 3.8                   |                                                                                    |     |     |       |         |                                                                                     |
| 75                    | 1170                 | 19.70   | 17600                              | 1.25                  |                                                                                    |     |     |       |         |                                                                                     |
| 84                    | 1040                 | 17.49   | 18100                              | 1.45                  |                                                                                    |     |     |       |         |                                                                                     |
| 94                    | 930                  | 15.64*  | 18200                              | 1.60                  |                                                                                    |     |     |       |         |                                                                                     |
| 105                   | 840                  | 14.06   | 17900                              | 1.80                  |                                                                                    |     |     |       |         |                                                                                     |
| 120                   | 725                  | 12.20   | 17400                              | 2.1                   | FA                                                                                 | 77  | DRN | 132L4 | 130     | 422                                                                                 |
| 135                   | 650                  | 10.93   | 17100                              | 2.3                   | FAF                                                                                | 77  | DRN | 132L4 | 135     | 421                                                                                 |
| 158                   | 555                  | 9.30    | 15900                              | 1.95                  | F                                                                                  | 77  | DRN | 132L4 | 135     | 420                                                                                 |
| 178                   | 490                  | 8.26    | 15600                              | 2.2                   | FF                                                                                 | 77  | DRN | 132L4 | 145     | 421                                                                                 |
| 199                   | 440                  | 7.39    | 15200                              | 2.4                   |                                                                                    |     |     |       |         |                                                                                     |
| 221                   | 395                  | 6.64    | 14900                              | 2.7                   |                                                                                    |     |     |       |         |                                                                                     |
| 255                   | 340                  | 5.76    | 14500                              | 3.1                   |                                                                                    |     |     |       |         |                                                                                     |
| 285                   | 305                  | 5.16    | 14100                              | 3.5                   |                                                                                    |     |     |       |         |                                                                                     |
| 343                   | 255                  | 4.28    | 13500                              | 4.0                   |                                                                                    |     |     |       |         |                                                                                     |

**P<sub>m</sub> = 11.0 kW**


| n <sub>a</sub><br>rpm | M <sub>a</sub><br>Nm | i   | F <sub>Ra</sub> <sup>1)</sup><br>N | SEW<br>f <sub>B</sub> |  |        |     |       | m<br>kg |  |
|-----------------------|----------------------|-----|------------------------------------|-----------------------|--------------------------------------------------------------------------------------|--------|-----|-------|---------|---------------------------------------------------------------------------------------|
| 4.9                   | 20000                | 302 | 93500                              | 0.90                  | FA                                                                                   | 157R97 | DRN | 160M4 | 870     | 456                                                                                   |
| 5.4                   | 18100                | 273 | 99800                              | 1.00                  | FAF                                                                                  | 157R97 | DRN | 160M4 | 930     | 456                                                                                   |
| 6.4                   | 15300                | 232 | 107300                             | 1.15                  | F                                                                                    | 157R97 | DRN | 160M4 | 890     | 456                                                                                   |
| 7.3                   | 13300                | 202 | 111600                             | 1.35                  | FF                                                                                   | 157R97 | DRN | 160M4 | 1000    | 456                                                                                   |
| 7.5                   | 13000                | 197 | 112300                             | 1.40                  |                                                                                      |        |     |       |         |                                                                                       |

21933170/DE – 11/2015


| <b>P<sub>m</sub> = 11.0 kW</b>     |                                   |          |                                                |                                    |                                                                                    |        |     |       |                       |                                                                                     |
|------------------------------------|-----------------------------------|----------|------------------------------------------------|------------------------------------|------------------------------------------------------------------------------------|--------|-----|-------|-----------------------|-------------------------------------------------------------------------------------|
| <b>n<sub>a</sub></b><br><b>rpm</b> | <b>M<sub>a</sub></b><br><b>Nm</b> | <b>i</b> | <b>F<sub>Ra</sub><sup>1)</sup></b><br><b>N</b> | <b>SEW</b><br><b>f<sub>B</sub></b> |  |        |     |       | <b>m</b><br><b>kg</b> |  |
| 6.6                                | 14800                             | 223      | 84800                                          | 0.80                               | FA                                                                                 | 127R87 | DRN | 160M4 | 550                   | 456                                                                                 |
| 7.5                                | 13100                             | 198      | 88300                                          | 0.90                               | FAF                                                                                | 127R87 | DRN | 160M4 | 590                   | 456                                                                                 |
| 8.9                                | 11000                             | 166      | 90000                                          | 1.10                               | F                                                                                  | 127R87 | DRN | 160M4 | 590                   | 456                                                                                 |
|                                    |                                   |          |                                                |                                    | FF                                                                                 | 127R87 | DRN | 160M4 | 630                   | 456                                                                                 |
| 5.5                                | 19000                             | 267.43   | 96900                                          | 0.95                               | FA<br>FAF<br>F<br>FF                                                               | 157    | DRN | 160M4 | 740                   | 452                                                                                 |
| 6.8                                | 15500                             | 217.62*  | 106900                                         | 1.15                               |                                                                                    |        |     |       |                       |                                                                                     |
| 8.3                                | 12700                             | 178.20*  | 112800                                         | 1.40                               |                                                                                    |        |     |       |                       |                                                                                     |
| 9.0                                | 11600                             | 162.96   | 114800                                         | 1.55                               |                                                                                    |        |     |       |                       |                                                                                     |
| 10                                 | 10100                             | 141.80*  | 117100                                         | 1.80                               |                                                                                    |        |     |       |                       |                                                                                     |
| 12                                 | 8920                              | 125.14   | 118700                                         | 2.0                                |                                                                                    |        |     |       |                       |                                                                                     |
| 14                                 | 7730                              | 108.49   | 120000                                         | 2.3                                |                                                                                    |        |     |       |                       |                                                                                     |
| 15                                 | 6880                              | 96.53*   | 120000                                         | 2.6                                |                                                                                    |        |     |       |                       |                                                                                     |
| 17                                 | 6110                              | 85.80*   | 117500                                         | 2.9                                |                                                                                    |        |     |       |                       |                                                                                     |
| 19                                 | 5590                              | 78.46    | 115100                                         | 3.2                                | FA<br>FAF<br>F<br>FF                                                               | 127    | DRN | 160M4 | 485                   | 446                                                                                 |
| 22                                 | 4860                              | 68.28*   | 111400                                         | 3.7                                |                                                                                    |        |     |       |                       |                                                                                     |
| 8.6                                | 12100                             | 170.83   | 90000                                          | 1.00                               |                                                                                    |        |     |       |                       |                                                                                     |
| 9.6                                | 10900                             | 153.67*  | 90000                                          | 1.10                               |                                                                                    |        |     |       |                       |                                                                                     |
| 12                                 | 8940                              | 125.37   | 90000                                          | 1.35                               |                                                                                    |        |     |       |                       |                                                                                     |
| 13                                 | 8150                              | 114.34   | 90000                                          | 1.45                               |                                                                                    |        |     |       |                       |                                                                                     |
| 15                                 | 7050                              | 98.95    | 90000                                          | 1.70                               |                                                                                    |        |     |       |                       |                                                                                     |
| 17                                 | 6220                              | 87.31*   | 90000                                          | 1.95                               |                                                                                    |        |     |       |                       |                                                                                     |
| 20                                 | 5370                              | 75.41*   | 88300                                          | 2.2                                |                                                                                    |        |     |       |                       |                                                                                     |
| 12                                 | 8410                              | 117.94   | 47800                                          | 0.90                               | FA<br>FAF<br>F<br>FF                                                               | 107    | DRN | 160M4 | 340                   | 440                                                                                 |
| 15                                 | 7220                              | 101.38*  | 51000                                          | 1.05                               |                                                                                    |        |     |       |                       |                                                                                     |
| 16                                 | 6590                              | 92.47*   | 52600                                          | 1.15                               |                                                                                    |        |     |       |                       |                                                                                     |
| 18                                 | 5980                              | 83.99    | 54100                                          | 1.30                               |                                                                                    |        |     |       |                       |                                                                                     |
| 20                                 | 5310                              | 74.52    | 55600                                          | 1.45                               |                                                                                    |        |     |       |                       |                                                                                     |
| 22                                 | 4820                              | 67.62    | 56700                                          | 1.60                               |                                                                                    |        |     |       |                       |                                                                                     |
| 25                                 | 4140                              | 58.12*   | 56200                                          | 1.85                               |                                                                                    |        |     |       |                       |                                                                                     |
| 29                                 | 3610                              | 50.73    | 54900                                          | 2.1                                |                                                                                    |        |     |       |                       |                                                                                     |
| 34                                 | 3060                              | 43.03    | 53300                                          | 2.5                                |                                                                                    |        |     |       |                       |                                                                                     |
| 44                                 | 2400                              | 33.79*   | 50700                                          | 3.1                                | FA<br>FAF<br>F<br>FF                                                               | 97     | DRN | 160M4 | 265                   | 434                                                                                 |
| 53                                 | 1960                              | 27.57    | 48500                                          | 4.0                                |                                                                                    |        |     |       |                       |                                                                                     |
| 59                                 | 1790                              | 25.14    | 47500                                          | 4.4                                |                                                                                    |        |     |       |                       |                                                                                     |
| 22                                 | 4660                              | 65.47    | 26900                                          | 0.90                               |                                                                                    |        |     |       |                       |                                                                                     |
| 25                                 | 4140                              | 58.06    | 27100                                          | 1.05                               |                                                                                    |        |     |       |                       |                                                                                     |
| 28                                 | 3740                              | 52.49    | 27100                                          | 1.15                               |                                                                                    |        |     |       |                       |                                                                                     |
| 33                                 | 3170                              | 44.49    | 26900                                          | 1.35                               |                                                                                    |        |     |       |                       |                                                                                     |
| 38                                 | 2770                              | 38.86    | 26700                                          | 1.55                               |                                                                                    |        |     |       |                       |                                                                                     |
| 45                                 | 2310                              | 32.50    | 26200                                          | 1.85                               |                                                                                    |        |     |       |                       |                                                                                     |
| 43                                 | 2410                              | 33.91    | 26300                                          | 1.80                               | FA<br>FAF<br>F<br>FF                                                               | 87     | DRN | 160M4 | 200                   | 428                                                                                 |
| 48                                 | 2160                              | 30.39    | 25900                                          | 2.00                               |                                                                                    |        |     |       |                       |                                                                                     |
| 54                                 | 1950                              | 27.44*   | 25500                                          | 2.2                                |                                                                                    |        |     |       |                       |                                                                                     |
| 59                                 | 1770                              | 24.92    | 25200                                          | 2.4                                |                                                                                    |        |     |       |                       |                                                                                     |
| 67                                 | 1570                              | 22.11    | 24600                                          | 2.7                                |                                                                                    |        |     |       |                       |                                                                                     |
| 37                                 | 2800                              | 39.30    | 14600                                          | 0.95                               |                                                                                    |        |     |       |                       |                                                                                     |
| 42                                 | 2500                              | 35.19    | 14800                                          | 1.05                               |                                                                                    |        |     |       |                       |                                                                                     |
| 50                                 | 2080                              | 29.20    | 15000                                          | 1.20                               |                                                                                    |        |     |       |                       |                                                                                     |
| 56                                 | 1880                              | 26.50    | 15000                                          | 1.60                               | FA<br>FAF<br>F<br>FF                                                               | 87     | DRN | 160M4 | 210                   | 427                                                                                 |
| 62                                 | 1680                              | 23.68    | 15000                                          | 1.80                               |                                                                                    |        |     |       |                       |                                                                                     |
| 69                                 | 1520                              | 21.32*   | 14900                                          | 1.95                               |                                                                                    |        |     |       |                       |                                                                                     |
| 76                                 | 1370                              | 19.31    | 14800                                          | 2.2                                |                                                                                    |        |     |       |                       |                                                                                     |
| 86                                 | 1220                              | 17.12    | 14600                                          | 2.5                                |                                                                                    |        |     |       |                       |                                                                                     |
| 95                                 | 1100                              | 15.48    | 14400                                          | 2.7                                |                                                                                    |        |     |       |                       |                                                                                     |
| 112                                | 930                               | 13.12*   | 14000                                          | 3.2                                |                                                                                    |        |     |       |                       |                                                                                     |




**P<sub>m</sub> = 11.0 kW**

| n <sub>a</sub><br>rpm | M <sub>a</sub><br>Nm | i      | F <sub>Ra</sub> <sup>1)</sup><br>N | SEW<br>f <sub>B</sub> |  |    |     |       | m<br>kg |  |
|-----------------------|----------------------|--------|------------------------------------|-----------------------|------------------------------------------------------------------------------------|----|-----|-------|---------|-------------------------------------------------------------------------------------|
| 75                    | 1400                 | 19.70  | 16300                              | 1.05                  |                                                                                    |    |     |       |         |                                                                                     |
| 84                    | 1240                 | 17.49  | 17200                              | 1.20                  |                                                                                    |    |     |       |         |                                                                                     |
| 94                    | 1110                 | 15.64* | 17600                              | 1.35                  |                                                                                    |    |     |       |         |                                                                                     |
| 105                   | 1000                 | 14.06  | 17300                              | 1.50                  |                                                                                    |    |     |       |         |                                                                                     |
| 121                   | 870                  | 12.20  | 16900                              | 1.70                  |                                                                                    |    |     |       |         |                                                                                     |
| 135                   | 775                  | 10.93  | 16600                              | 1.90                  | FA                                                                                 | 77 | DRN | 160M4 | 160     | 422                                                                                 |
| 158                   | 660                  | 9.30   | 15400                              | 1.65                  | FAF                                                                                | 77 | DRN | 160M4 | 170     | 421                                                                                 |
| 178                   | 585                  | 8.26   | 15100                              | 1.85                  | F                                                                                  | 77 | DRN | 160M4 | 165     | 420                                                                                 |
| 199                   | 525                  | 7.39   | 14800                              | 2.0                   | FF                                                                                 | 77 | DRN | 160M4 | 175     | 421                                                                                 |
| 222                   | 470                  | 6.64   | 14500                              | 2.3                   |                                                                                    |    |     |       |         |                                                                                     |
| 256                   | 410                  | 5.76   | 14100                              | 2.6                   |                                                                                    |    |     |       |         |                                                                                     |
| 285                   | 365                  | 5.16   | 13800                              | 2.9                   |                                                                                    |    |     |       |         |                                                                                     |
| 344                   | 305                  | 4.28   | 13300                              | 3.3                   |                                                                                    |    |     |       |         |                                                                                     |


**P<sub>m</sub> = 15.0 kW**


| n <sub>a</sub><br>rpm | M <sub>a</sub><br>Nm | i       | F <sub>Ra</sub> <sup>1)</sup><br>N | SEW<br>f <sub>B</sub> |  |        |     |       | m<br>kg |  |
|-----------------------|----------------------|---------|------------------------------------|-----------------------|------------------------------------------------------------------------------------|--------|-----|-------|---------|-------------------------------------------------------------------------------------|
| 6.4                   | 20900                | 232     | 90200                              | 0.85                  | FA                                                                                 | 157R97 | DRN | 160L4 | 880     | 456                                                                                 |
| 7.3                   | 18200                | 202     | 99400                              | 1.00                  | FAF                                                                                | 157R97 | DRN | 160L4 | 940     | 456                                                                                 |
| 7.5                   | 17700                | 197     | 100900                             | 1.00                  | F                                                                                  | 157R97 | DRN | 160L4 | 900     | 456                                                                                 |
|                       |                      |         |                                    |                       | FF                                                                                 | 157R97 | DRN | 160L4 | 1010    | 456                                                                                 |
| 6.8                   | 21100                | 217.62* | 89600                              | 0.85                  |                                                                                    |        |     |       |         |                                                                                     |
| 8.3                   | 17300                | 178.20* | 102200                             | 1.05                  |                                                                                    |        |     |       |         |                                                                                     |
| 9.0                   | 15800                | 162.96  | 106100                             | 1.15                  |                                                                                    |        |     |       |         |                                                                                     |
| 10                    | 13700                | 141.80* | 110800                             | 1.30                  |                                                                                    |        |     |       |         |                                                                                     |
| 12                    | 12100                | 125.14  | 113800                             | 1.50                  | FA                                                                                 | 157    | DRN | 160L4 | 760     | 452                                                                                 |
| 14                    | 10500                | 108.49  | 116500                             | 1.70                  | FAF                                                                                | 157    | DRN | 160L4 | 810     | 451                                                                                 |
| 15                    | 9380                 | 96.53*  | 115600                             | 1.90                  | F                                                                                  | 157    | DRN | 160L4 | 780     | 450                                                                                 |
| 17                    | 8330                 | 85.80*  | 113000                             | 2.2                   | FF                                                                                 | 157    | DRN | 160L4 | 880     | 451                                                                                 |
| 19                    | 7620                 | 78.46   | 111000                             | 2.4                   |                                                                                    |        |     |       |         |                                                                                     |
| 22                    | 6630                 | 68.28*  | 107800                             | 2.7                   |                                                                                    |        |     |       |         |                                                                                     |
| 24                    | 5850                 | 60.25   | 104900                             | 3.1                   |                                                                                    |        |     |       |         |                                                                                     |
| 12                    | 12100                | 125.37  | 88900                              | 1.00                  | FA                                                                                 | 127    | DRN | 160L4 | 500     | 446                                                                                 |
| 13                    | 11100                | 114.34  | 88300                              | 1.10                  | FAF                                                                                | 127    | DRN | 160L4 | 540     | 445                                                                                 |
| 15                    | 9610                 | 98.95   | 86900                              | 1.25                  | F                                                                                  | 127    | DRN | 160L4 | 540     | 444                                                                                 |
| 17                    | 8480                 | 87.31*  | 85500                              | 1.40                  | FF                                                                                 | 127    | DRN | 160L4 | 580     | 445                                                                                 |
| 20                    | 7320                 | 75.41*  | 83700                              | 1.65                  |                                                                                    |        |     |       |         |                                                                                     |
| 21                    | 6800                 | 70.07   | 82700                              | 1.75                  |                                                                                    |        |     |       |         |                                                                                     |
| 16                    | 8980                 | 92.47*  | 46200                              | 0.85                  | FA                                                                                 | 107    | DRN | 160L4 | 360     | 440                                                                                 |
| 17                    | 8590                 | 88.49   | 47300                              | 0.90                  | FAF                                                                                | 107    | DRN | 160L4 | 380     | 439                                                                                 |
| 18                    | 8160                 | 83.99   | 48500                              | 0.95                  | F                                                                                  | 107    | DRN | 160L4 | 375     | 438                                                                                 |
| 20                    | 7240                 | 74.52   | 51000                              | 1.05                  | FF                                                                                 | 107    | DRN | 160L4 | 400     | 439                                                                                 |
| 22                    | 6570                 | 67.62   | 52700                              | 1.15                  |                                                                                    |        |     |       |         |                                                                                     |
| 25                    | 5640                 | 58.12*  | 52200                              | 1.35                  | FA                                                                                 | 107    | DRN | 160L4 | 360     | 440                                                                                 |
| 29                    | 4930                 | 50.73   | 51400                              | 1.55                  | FAF                                                                                | 107    | DRN | 160L4 | 380     | 439                                                                                 |
| 34                    | 4180                 | 43.03   | 50300                              | 1.85                  | F                                                                                  | 107    | DRN | 160L4 | 375     | 438                                                                                 |
| 39                    | 3650                 | 37.61   | 49300                              | 2.1                   | FF                                                                                 | 107    | DRN | 160L4 | 400     | 439                                                                                 |
| 46                    | 3090                 | 31.80   | 47900                              | 2.5                   |                                                                                    |        |     |       |         |                                                                                     |
| 44                    | 3280                 | 33.79*  | 48400                              | 2.2                   | FA                                                                                 | 107    | DRN | 160L4 | 350     | 440                                                                                 |
| 53                    | 2670                 | 27.57   | 46600                              | 2.9                   | FAF                                                                                | 107    | DRN | 160L4 | 370     | 439                                                                                 |
| 59                    | 2440                 | 25.14   | 45800                              | 3.2                   | F                                                                                  | 107    | DRN | 160L4 | 365     | 438                                                                                 |
| 68                    | 2110                 | 21.76*  | 44400                              | 3.7                   | FF                                                                                 | 107    | DRN | 160L4 | 390     | 439                                                                                 |
| 33                    | 4320                 | 44.49   | 22900                              | 1.00                  | FA                                                                                 | 97     | DRN | 160L4 | 285     | 434                                                                                 |
| 38                    | 3770                 | 38.86   | 23100                              | 1.15                  | FAF                                                                                | 97     | DRN | 160L4 | 305     | 433                                                                                 |
| 45                    | 3150                 | 32.50   | 23200                              | 1.35                  | F                                                                                  | 97     | DRN | 160L4 | 290     | 432                                                                                 |
|                       |                      |         |                                    |                       | FF                                                                                 | 97     | DRN | 160L4 | 325     | 433                                                                                 |

| P <sub>m</sub> = 15.0 kW |                      |        |                                    |                       |                                                                                    |    |     |       |         |                                                                                     |
|--------------------------|----------------------|--------|------------------------------------|-----------------------|------------------------------------------------------------------------------------|----|-----|-------|---------|-------------------------------------------------------------------------------------|
| n <sub>a</sub><br>rpm    | M <sub>a</sub><br>Nm | i      | F <sub>Ra</sub> <sup>1)</sup><br>N | SEW<br>f <sub>B</sub> |  |    |     |       | m<br>kg |  |
| 43                       | 3290                 | 33.91  | 23200                              | 1.30                  | FA<br>FAF<br>F<br>FF                                                               | 97 | DRN | 160L4 | 275     | 434                                                                                 |
| 48                       | 2950                 | 30.39  | 23200                              | 1.45                  |                                                                                    |    |     |       |         |                                                                                     |
| 54                       | 2660                 | 27.44* | 23000                              | 1.60                  |                                                                                    |    |     |       |         |                                                                                     |
| 59                       | 2420                 | 24.92  | 22900                              | 1.80                  |                                                                                    |    |     |       |         |                                                                                     |
| 67                       | 2140                 | 22.11  | 22600                              | 2.0                   |                                                                                    |    |     |       |         |                                                                                     |
| 73                       | 1950                 | 20.07  | 22400                              | 2.2                   |                                                                                    |    |     |       |         |                                                                                     |
| 85                       | 1670                 | 17.25* | 21900                              | 2.6                   |                                                                                    |    |     |       |         |                                                                                     |
| 98                       | 1460                 | 15.06  | 21400                              | 2.9                   |                                                                                    |    |     |       |         |                                                                                     |
| 115                      | 1240                 | 12.77  | 20800                              | 3.5                   | FA<br>FAF<br>F<br>FF                                                               | 87 | DRN | 160L4 | 215     | 428                                                                                 |
| 132                      | 1080                 | 11.16  | 20200                              | 3.8                   |                                                                                    |    |     |       |         |                                                                                     |
| 56                       | 2570                 | 26.50  | 12400                              | 1.15                  |                                                                                    |    |     |       |         |                                                                                     |
| 62                       | 2300                 | 23.68  | 12600                              | 1.30                  |                                                                                    |    |     |       |         |                                                                                     |
| 69                       | 2070                 | 21.32* | 12800                              | 1.45                  |                                                                                    |    |     |       |         |                                                                                     |
| 76                       | 1870                 | 19.31  | 12800                              | 1.60                  |                                                                                    |    |     |       |         |                                                                                     |
| 86                       | 1660                 | 17.12  | 12900                              | 1.80                  |                                                                                    |    |     |       |         |                                                                                     |
| 95                       | 1500                 | 15.48  | 12800                              | 2.00                  |                                                                                    |    |     |       |         |                                                                                     |
| 112                      | 1270                 | 13.12* | 12700                              | 2.4                   |                                                                                    |    |     |       |         |                                                                                     |
| 129                      | 1110                 | 11.46  | 12600                              | 2.7                   |                                                                                    |    |     |       |         |                                                                                     |
| 154                      | 930                  | 9.58   | 12300                              | 3.1                   |                                                                                    |    |     |       |         |                                                                                     |
| 178                      | 800                  | 8.29   | 11700                              | 1.90                  |                                                                                    |    |     |       |         |                                                                                     |
| 200                      | 710                  | 7.35   | 11500                              | 2.1                   |                                                                                    |    |     |       |         |                                                                                     |
| 222                      | 645                  | 6.65   | 11300                              | 2.4                   |                                                                                    |    |     |       |         |                                                                                     |
| 262                      | 545                  | 5.63   | 11000                              | 2.8                   |                                                                                    |    |     |       |         |                                                                                     |
| 300                      | 475                  | 4.92   | 10700                              | 3.2                   |                                                                                    |    |     |       |         |                                                                                     |
| 358                      | 395                  | 4.12   | 10300                              | 3.6                   |                                                                                    |    |     |       |         |                                                                                     |


| P <sub>m</sub> = 18.5 kW |                      |         |                                    |                       |                                                                                      |                          |                          |                                  |                          |                                                                                       |
|--------------------------|----------------------|---------|------------------------------------|-----------------------|--------------------------------------------------------------------------------------|--------------------------|--------------------------|----------------------------------|--------------------------|---------------------------------------------------------------------------------------|
| n <sub>a</sub><br>rpm    | M <sub>a</sub><br>Nm | i       | F <sub>Ra</sub> <sup>1)</sup><br>N | SEW<br>f <sub>B</sub> |  |                          |                          |                                  | m<br>kg                  |  |
| 7.3                      | 22500                | 202     | 74900                              | 0.80                  | FA                                                                                   | 157R97                   | DRN                      | 180M4                            | 910                      | 456                                                                                   |
| 7.5                      | 21900                | 197     | 86400                              | 0.80                  | FAF                                                                                  | 157R97                   | DRN                      | 180M4                            | 960                      | 456                                                                                   |
|                          |                      |         |                                    |                       | F                                                                                    | 157R97                   | DRN                      | 180M4                            | 930                      | 456                                                                                   |
|                          |                      |         |                                    |                       | FF                                                                                   | 157R97                   | DRN                      | 180M4                            | 1030                     | 456                                                                                   |
| 8.3                      | 21200                | 178.20* | 89000                              | 0.85                  | FA<br>FAF<br>F<br>FF                                                                 | 157<br>157<br>157<br>157 | DRN<br>DRN<br>DRN<br>DRN | 180M4<br>180M4<br>180M4<br>180M4 | 780<br>840<br>800<br>910 | 452<br>451<br>450<br>451                                                              |
| 9.1                      | 19400                | 162.96  | 95600                              | 0.90                  |                                                                                      |                          |                          |                                  |                          |                                                                                       |
| 10                       | 16900                | 141.80* | 103200                             | 1.05                  |                                                                                      |                          |                          |                                  |                          |                                                                                       |
| 12                       | 14900                | 125.14  | 108200                             | 1.20                  |                                                                                      |                          |                          |                                  |                          |                                                                                       |
| 14                       | 12900                | 108.49  | 112400                             | 1.40                  |                                                                                      |                          |                          |                                  |                          |                                                                                       |
| 15                       | 11500                | 96.53*  | 111200                             | 1.55                  |                                                                                      |                          |                          |                                  |                          |                                                                                       |
| 17                       | 10200                | 85.80*  | 109100                             | 1.75                  |                                                                                      |                          |                          |                                  |                          |                                                                                       |
| 19                       | 9370                 | 78.46   | 107400                             | 1.90                  |                                                                                      |                          |                          |                                  |                          |                                                                                       |
| 22                       | 8160                 | 68.28*  | 104700                             | 2.2                   |                                                                                      |                          |                          |                                  |                          |                                                                                       |
| 25                       | 7200                 | 60.25   | 102100                             | 2.5                   |                                                                                      |                          |                          |                                  |                          |                                                                                       |
| 28                       | 6240                 | 52.24   | 99200                              | 2.9                   |                                                                                      |                          |                          |                                  |                          |                                                                                       |
| 13                       | 13600                | 114.34  | 82200                              | 0.90                  | FA<br>FAF<br>F<br>FF                                                                 | 127<br>127<br>127<br>127 | DRN<br>DRN<br>DRN<br>DRN | 180M4<br>180M4<br>180M4<br>180M4 | 520<br>560<br>560<br>600 | 446<br>445<br>444<br>445                                                              |
| 15                       | 11800                | 98.95   | 81600                              | 1.00                  |                                                                                      |                          |                          |                                  |                          |                                                                                       |
| 17                       | 10400                | 87.31*  | 80900                              | 1.15                  |                                                                                      |                          |                          |                                  |                          |                                                                                       |
| 20                       | 9010                 | 75.41*  | 79700                              | 1.35                  |                                                                                      |                          |                          |                                  |                          |                                                                                       |
| 21                       | 8370                 | 70.07   | 79000                              | 1.45                  |                                                                                      |                          |                          |                                  |                          |                                                                                       |
| 23                       | 7630                 | 63.91   | 78000                              | 1.55                  |                                                                                      |                          |                          |                                  |                          |                                                                                       |
| 27                       | 6610                 | 55.31   | 76300                              | 1.80                  |                                                                                      |                          |                          |                                  |                          |                                                                                       |
| 30                       | 5830                 | 48.80   | 74800                              | 2.1                   |                                                                                      |                          |                          |                                  |                          |                                                                                       |
| 20                       | 8900                 | 74.52   | 46400                              | 0.85                  | FA                                                                                   | 107                      | DRN                      | 180M4                            | 380                      | 440                                                                                   |
| 22                       | 8080                 | 67.62   | 48700                              | 0.95                  | FAF                                                                                  | 107                      | DRN                      | 180M4                            | 400                      | 439                                                                                   |
| 25                       | 6940                 | 58.12*  | 48700                              | 1.10                  | F                                                                                    | 107                      | DRN                      | 180M4                            | 395                      | 438                                                                                   |
| 29                       | 6060                 | 50.73   | 48400                              | 1.25                  | FF                                                                                   | 107                      | DRN                      | 180M4                            | 425                      | 439                                                                                   |
| 34                       | 5140                 | 43.03   | 47700                              | 1.50                  | FA                                                                                   | 107                      | DRN                      | 180M4                            | 380                      | 440                                                                                   |
| 39                       | 4490                 | 37.61   | 47000                              | 1.70                  | FAF                                                                                  | 107                      | DRN                      | 180M4                            | 400                      | 439                                                                                   |
| 46                       | 3800                 | 31.80   | 45900                              | 2.0                   | F                                                                                    | 107                      | DRN                      | 180M4                            | 395                      | 438                                                                                   |
|                          |                      |         |                                    |                       | FF                                                                                   | 107                      | DRN                      | 180M4                            | 425                      | 439                                                                                   |
| 44                       | 4030                 | 33.79*  | 46300                              | 1.85                  | FA                                                                                   | 107                      | DRN                      | 180M4                            | 370                      | 440                                                                                   |
| 54                       | 3290                 | 27.57   | 44900                              | 2.4                   | FAF                                                                                  | 107                      | DRN                      | 180M4                            | 390                      | 439                                                                                   |
| 59                       | 3000                 | 25.14   | 44200                              | 2.6                   | F                                                                                    | 107                      | DRN                      | 180M4                            | 385                      | 438                                                                                   |
| 68                       | 2600                 | 21.76*  | 43100                              | 3.0                   | FF                                                                                   | 107                      | DRN                      | 180M4                            | 415                      | 439                                                                                   |




| <b>P<sub>m</sub> = 18.5 kW</b>     |                                   |          |                                                |                                    |                                                                                    |           |            |              |                       |                                                                                     |
|------------------------------------|-----------------------------------|----------|------------------------------------------------|------------------------------------|------------------------------------------------------------------------------------|-----------|------------|--------------|-----------------------|-------------------------------------------------------------------------------------|
| <b>n<sub>a</sub></b><br><b>rpm</b> | <b>M<sub>a</sub></b><br><b>Nm</b> | <b>i</b> | <b>F<sub>Ra</sub><sup>1)</sup></b><br><b>N</b> | <b>SEW</b><br><b>f<sub>B</sub></b> |  |           |            |              | <b>m</b><br><b>kg</b> |  |
| <b>38</b>                          | 4640                              | 38.86    | 20100                                          | 0.95                               | <b>FA</b>                                                                          | <b>97</b> | <b>DRN</b> | <b>180M4</b> | 305                   | 434                                                                                 |
| <b>45</b>                          | 3880                              | 32.50    | 20600                                          | 1.10                               | <b>FAF</b>                                                                         | <b>97</b> | <b>DRN</b> | <b>180M4</b> | 325                   | 433                                                                                 |
|                                    |                                   |          |                                                |                                    | <b>F</b>                                                                           | <b>97</b> | <b>DRN</b> | <b>180M4</b> | 310                   | 432                                                                                 |
|                                    |                                   |          |                                                |                                    | <b>FF</b>                                                                          | <b>97</b> | <b>DRN</b> | <b>180M4</b> | 345                   | 433                                                                                 |
| <b>54</b>                          | 3270                              | 27.44*   | 20900                                          | 1.30                               |                                                                                    |           |            |              |                       |                                                                                     |
| <b>59</b>                          | 2970                              | 24.92    | 20900                                          | 1.45                               |                                                                                    |           |            |              |                       |                                                                                     |
| <b>67</b>                          | 2640                              | 22.11    | 20900                                          | 1.65                               | <b>FA</b>                                                                          | <b>97</b> | <b>DRN</b> | <b>180M4</b> | 300                   | 434                                                                                 |
| <b>74</b>                          | 2390                              | 20.07    | 20800                                          | 1.80                               | <b>FAF</b>                                                                         | <b>97</b> | <b>DRN</b> | <b>180M4</b> | 320                   | 433                                                                                 |
| <b>86</b>                          | 2060                              | 17.25*   | 20500                                          | 2.1                                | <b>F</b>                                                                           | <b>97</b> | <b>DRN</b> | <b>180M4</b> | 305                   | 432                                                                                 |
| <b>98</b>                          | 1790                              | 15.06    | 20200                                          | 2.4                                | <b>FF</b>                                                                          | <b>97</b> | <b>DRN</b> | <b>180M4</b> | 340                   | 433                                                                                 |
| <b>116</b>                         | 1520                              | 12.77    | 19700                                          | 2.8                                |                                                                                    |           |            |              |                       |                                                                                     |
| <b>132</b>                         | 1330                              | 11.16    | 19300                                          | 3.1                                |                                                                                    |           |            |              |                       |                                                                                     |
| <b>69</b>                          | 2540                              | 21.32*   | 10900                                          | 1.20                               |                                                                                    |           |            |              |                       |                                                                                     |
| <b>77</b>                          | 2300                              | 19.31    | 11100                                          | 1.30                               |                                                                                    |           |            |              |                       |                                                                                     |
| <b>86</b>                          | 2040                              | 17.12    | 11400                                          | 1.45                               |                                                                                    |           |            |              |                       |                                                                                     |
| <b>95</b>                          | 1850                              | 15.48    | 11500                                          | 1.60                               |                                                                                    |           |            |              |                       |                                                                                     |
| <b>113</b>                         | 1560                              | 13.12*   | 11600                                          | 1.90                               | <b>FA</b>                                                                          | <b>87</b> | <b>DRN</b> | <b>180M4</b> | 235                   | 428                                                                                 |
| <b>129</b>                         | 1360                              | 11.46    | 11600                                          | 2.2                                | <b>FAF</b>                                                                         | <b>87</b> | <b>DRN</b> | <b>180M4</b> | 250                   | 427                                                                                 |
| <b>154</b>                         | 1140                              | 9.58     | 11500                                          | 2.5                                | <b>F</b>                                                                           | <b>87</b> | <b>DRN</b> | <b>180M4</b> | 245                   | 426                                                                                 |
| <b>178</b>                         | 990                               | 8.29     | 10900                                          | 1.55                               | <b>FF</b>                                                                          | <b>87</b> | <b>DRN</b> | <b>180M4</b> | 260                   | 427                                                                                 |
| <b>201</b>                         | 870                               | 7.35     | 10800                                          | 1.75                               |                                                                                    |           |            |              |                       |                                                                                     |
| <b>222</b>                         | 790                               | 6.65     | 10700                                          | 1.95                               |                                                                                    |           |            |              |                       |                                                                                     |
| <b>262</b>                         | 670                               | 5.63     | 10400                                          | 2.3                                |                                                                                    |           |            |              |                       |                                                                                     |
| <b>300</b>                         | 585                               | 4.92     | 10200                                          | 2.6                                |                                                                                    |           |            |              |                       |                                                                                     |
| <b>359</b>                         | 490                               | 4.12     | 9890                                           | 3.0                                |                                                                                    |           |            |              |                       |                                                                                     |

| <b>P<sub>m</sub> = 22 kW</b>       |                                   |          |                                                |                                    |                                                                                      |            |            |              |                       |                                                                                       |
|------------------------------------|-----------------------------------|----------|------------------------------------------------|------------------------------------|--------------------------------------------------------------------------------------|------------|------------|--------------|-----------------------|---------------------------------------------------------------------------------------|
| <b>n<sub>a</sub></b><br><b>rpm</b> | <b>M<sub>a</sub></b><br><b>Nm</b> | <b>i</b> | <b>F<sub>Ra</sub><sup>1)</sup></b><br><b>N</b> | <b>SEW</b><br><b>f<sub>B</sub></b> |  |            |            |              | <b>m</b><br><b>kg</b> |  |
| <b>10</b>                          | 20100                             | 141.80*  | 93200                                          | 0.90                               |                                                                                      |            |            |              |                       |                                                                                       |
| <b>12</b>                          | 17700                             | 125.14   | 100900                                         | 1.00                               |                                                                                      |            |            |              |                       |                                                                                       |
| <b>14</b>                          | 15400                             | 108.49   | 107100                                         | 1.15                               |                                                                                      |            |            |              |                       |                                                                                       |
| <b>15</b>                          | 13700                             | 96.53*   | 106800                                         | 1.30                               |                                                                                      |            |            |              |                       |                                                                                       |
| <b>17</b>                          | 12200                             | 85.80*   | 105200                                         | 1.45                               | <b>FA</b>                                                                            | <b>157</b> | <b>DRN</b> | <b>180L4</b> | 790                   | 452                                                                                   |
| <b>19</b>                          | 11100                             | 78.46    | 103900                                         | 1.60                               | <b>FAF</b>                                                                           | <b>157</b> | <b>DRN</b> | <b>180L4</b> | 850                   | 451                                                                                   |
| <b>22</b>                          | 9710                              | 68.28*   | 101600                                         | 1.85                               | <b>F</b>                                                                             | <b>157</b> | <b>DRN</b> | <b>180L4</b> | 820                   | 450                                                                                   |
| <b>25</b>                          | 8570                              | 60.25    | 99400                                          | 2.1                                | <b>FF</b>                                                                            | <b>157</b> | <b>DRN</b> | <b>180L4</b> | 920                   | 451                                                                                   |
| <b>28</b>                          | 7420                              | 52.24    | 96800                                          | 2.4                                |                                                                                      |            |            |              |                       |                                                                                       |
| <b>32</b>                          | 6610                              | 46.48*   | 94600                                          | 2.7                                |                                                                                      |            |            |              |                       |                                                                                       |
| <b>37</b>                          | 5690                              | 40.06    | 91700                                          | 3.2                                |                                                                                      |            |            |              |                       |                                                                                       |
| <b>45</b>                          | 4620                              | 32.55    | 87600                                          | 3.9                                |                                                                                      |            |            |              |                       |                                                                                       |
| <b>15</b>                          | 14000                             | 98.95    | 76400                                          | 0.85                               |                                                                                      |            |            |              |                       |                                                                                       |
| <b>17</b>                          | 12400                             | 87.31*   | 76300                                          | 0.95                               |                                                                                      |            |            |              |                       |                                                                                       |
| <b>20</b>                          | 10700                             | 75.41*   | 75700                                          | 1.10                               | <b>FA</b>                                                                            | <b>127</b> | <b>DRN</b> | <b>180L4</b> | 540                   | 446                                                                                   |
| <b>21</b>                          | 9960                              | 70.07    | 75300                                          | 1.20                               | <b>FAF</b>                                                                           | <b>127</b> | <b>DRN</b> | <b>180L4</b> | 580                   | 445                                                                                   |
| <b>23</b>                          | 9080                              | 63.91    | 74600                                          | 1.30                               | <b>F</b>                                                                             | <b>127</b> | <b>DRN</b> | <b>180L4</b> | 580                   | 444                                                                                   |
| <b>27</b>                          | 7860                              | 55.31    | 73400                                          | 1.55                               | <b>FF</b>                                                                            | <b>127</b> | <b>DRN</b> | <b>180L4</b> | 620                   | 445                                                                                   |
| <b>30</b>                          | 6940                              | 48.80    | 72200                                          | 1.75                               |                                                                                      |            |            |              |                       |                                                                                       |
| <b>35</b>                          | 5990                              | 42.15    | 70600                                          | 2.0                                |                                                                                      |            |            |              |                       |                                                                                       |
| <b>25</b>                          | 8260                              | 58.12*   | 45200                                          | 0.95                               | <b>FA</b>                                                                            | <b>107</b> | <b>DRN</b> | <b>180L4</b> | 395                   | 440                                                                                   |
| <b>29</b>                          | 7210                              | 50.73    | 45300                                          | 1.05                               | <b>FAF</b>                                                                           | <b>107</b> | <b>DRN</b> | <b>180L4</b> | 415                   | 439                                                                                   |
| <b>34</b>                          | 6120                              | 43.03    | 45100                                          | 1.25                               | <b>F</b>                                                                             | <b>107</b> | <b>DRN</b> | <b>180L4</b> | 410                   | 438                                                                                   |
|                                    |                                   |          |                                                |                                    | <b>FF</b>                                                                            | <b>107</b> | <b>DRN</b> | <b>180L4</b> | 440                   | 439                                                                                   |
| <b>39</b>                          | 5340                              | 37.61    | 44700                                          | 1.45                               | <b>FA</b>                                                                            | <b>107</b> | <b>DRN</b> | <b>180L4</b> | 395                   | 440                                                                                   |
| <b>46</b>                          | 4520                              | 31.80    | 44000                                          | 1.70                               | <b>FAF</b>                                                                           | <b>107</b> | <b>DRN</b> | <b>180L4</b> | 415                   | 439                                                                                   |
|                                    |                                   |          |                                                |                                    | <b>F</b>                                                                             | <b>107</b> | <b>DRN</b> | <b>180L4</b> | 410                   | 438                                                                                   |
|                                    |                                   |          |                                                |                                    | <b>FF</b>                                                                            | <b>107</b> | <b>DRN</b> | <b>180L4</b> | 440                   | 439                                                                                   |
| <b>44</b>                          | 4800                              | 33.79*   | 44300                                          | 1.55                               | <b>FA</b>                                                                            | <b>107</b> | <b>DRN</b> | <b>180L4</b> | 385                   | 440                                                                                   |
| <b>54</b>                          | 3920                              | 27.57    | 43300                                          | 2.0                                | <b>FAF</b>                                                                           | <b>107</b> | <b>DRN</b> | <b>180L4</b> | 405                   | 439                                                                                   |
| <b>59</b>                          | 3570                              | 25.14    | 42700                                          | 2.2                                | <b>F</b>                                                                             | <b>107</b> | <b>DRN</b> | <b>180L4</b> | 400                   | 438                                                                                   |
| <b>68</b>                          | 3090                              | 21.76*   | 41800                                          | 2.5                                | <b>FF</b>                                                                            | <b>107</b> | <b>DRN</b> | <b>180L4</b> | 430                   | 439                                                                                   |
| <b>77</b>                          | 2730                              | 19.20*   | 40900                                          | 2.9                                |                                                                                      |            |            |              |                       |                                                                                       |


**P<sub>m</sub> = 22 kW**

| n <sub>a</sub><br>rpm | M <sub>a</sub><br>Nm | i      | F <sub>Ra</sub> <sup>1)</sup><br>N | SEW<br>f <sub>B</sub> |  |    |     |       | m<br>kg |  |
|-----------------------|----------------------|--------|------------------------------------|-----------------------|------------------------------------------------------------------------------------|----|-----|-------|---------|-------------------------------------------------------------------------------------|
| 54                    | 3900                 | 27.44* | 18700                              | 1.10                  | FA<br>FAF<br>F<br>FF                                                               | 97 | DRN | 180L4 | 315     | 434                                                                                 |
| 59                    | 3540                 | 24.92  | 18900                              | 1.20                  |                                                                                    |    |     |       |         |                                                                                     |
| 67                    | 3140                 | 22.11  | 19100                              | 1.35                  |                                                                                    |    |     |       |         |                                                                                     |
| 74                    | 2850                 | 20.07  | 19200                              | 1.50                  |                                                                                    |    |     |       |         |                                                                                     |
| 86                    | 2450                 | 17.25* | 19100                              | 1.75                  |                                                                                    |    |     |       |         |                                                                                     |
| 98                    | 2140                 | 15.06  | 19000                              | 2.0                   |                                                                                    |    |     |       |         |                                                                                     |
| 116                   | 1810                 | 12.77  | 18700                              | 2.4                   | FA<br>FAF<br>F<br>FF                                                               | 87 | DRN | 180L4 | 255     | 428                                                                                 |
| 132                   | 1580                 | 11.16  | 18400                              | 2.6                   |                                                                                    |    |     |       |         |                                                                                     |
| 69                    | 3030                 | 21.32* | 9030                               | 1.00                  |                                                                                    |    |     |       |         |                                                                                     |
| 76                    | 2740                 | 19.31  | 9460                               | 1.10                  |                                                                                    |    |     |       |         |                                                                                     |
| 86                    | 2430                 | 17.12  | 9870                               | 1.25                  |                                                                                    |    |     |       |         |                                                                                     |
| 95                    | 2200                 | 15.48  | 10100                              | 1.35                  |                                                                                    |    |     |       |         |                                                                                     |
| 113                   | 1860                 | 13.12* | 10400                              | 1.60                  |                                                                                    |    |     |       |         |                                                                                     |
| 129                   | 1620                 | 11.46  | 10600                              | 1.85                  |                                                                                    |    |     |       |         |                                                                                     |
| 154                   | 1360                 | 9.58   | 10600                              | 2.1                   |                                                                                    |    |     |       |         |                                                                                     |
| 178                   | 1170                 | 8.29   | 10100                              | 1.30                  |                                                                                    |    |     |       |         |                                                                                     |
| 201                   | 1040                 | 7.35   | 10100                              | 1.45                  |                                                                                    |    |     |       |         |                                                                                     |
| 222                   | 940                  | 6.65   | 10000                              | 1.60                  |                                                                                    |    |     |       |         |                                                                                     |
| 262                   | 800                  | 5.63   | 9890                               | 1.90                  |                                                                                    |    |     |       |         |                                                                                     |
| 300                   | 695                  | 4.92   | 9740                               | 2.2                   |                                                                                    |    |     |       |         |                                                                                     |
| 359                   | 585                  | 4.12   | 9490                               | 2.5                   |                                                                                    |    |     |       |         |                                                                                     |


**P<sub>m</sub> = 30 kW**


| n <sub>a</sub><br>rpm | M <sub>a</sub><br>Nm | i      | F <sub>Ra</sub> <sup>1)</sup><br>N | SEW<br>f <sub>B</sub> |  |     |     |       | m<br>kg |  |
|-----------------------|----------------------|--------|------------------------------------|-----------------------|-------------------------------------------------------------------------------------|-----|-----|-------|---------|-------------------------------------------------------------------------------------|
| 14                    | 21000                | 108.49 | 90100                              | 0.85                  | FA<br>FAF<br>F<br>FF                                                                | 157 | DRN | 200L4 | 900     | 452                                                                                 |
| 15                    | 18600                | 96.53* | 96900                              | 0.95                  |                                                                                     |     |     |       |         |                                                                                     |
| 17                    | 16600                | 85.80* | 96400                              | 1.10                  |                                                                                     |     |     |       |         |                                                                                     |
| 19                    | 15100                | 78.46  | 95800                              | 1.20                  |                                                                                     |     |     |       |         |                                                                                     |
| 22                    | 13200                | 68.28* | 94500                              | 1.35                  |                                                                                     |     |     |       |         |                                                                                     |
| 25                    | 11600                | 60.25  | 93200                              | 1.55                  |                                                                                     |     |     |       |         |                                                                                     |
| 28                    | 10100                | 52.24  | 91400                              | 1.80                  |                                                                                     |     |     |       |         |                                                                                     |
| 32                    | 8990                 | 46.48* | 89800                              | 2.0                   | FA<br>FAF<br>F<br>FF                                                                | 127 | DRN | 200L4 | 640     | 446                                                                                 |
| 37                    | 7750                 | 40.06  | 87600                              | 2.3                   |                                                                                     |     |     |       |         |                                                                                     |
| 20                    | 14500                | 75.41* | 64600                              | 0.80                  |                                                                                     |     |     |       |         |                                                                                     |
| 21                    | 13500                | 70.07  | 65700                              | 0.90                  |                                                                                     |     |     |       |         |                                                                                     |
| 23                    | 12300                | 63.91  | 66800                              | 0.95                  |                                                                                     |     |     |       |         |                                                                                     |
| 27                    | 10700                | 55.31  | 66700                              | 1.10                  |                                                                                     |     |     |       |         |                                                                                     |
| 30                    | 9440                 | 48.80  | 66300                              | 1.25                  |                                                                                     |     |     |       |         |                                                                                     |
| 35                    | 8150                 | 42.15  | 65500                              | 1.45                  |                                                                                     |     |     |       |         |                                                                                     |
| 40                    | 7210                 | 37.28  | 64600                              | 1.65                  |                                                                                     |     |     |       |         |                                                                                     |
| 47                    | 6060                 | 31.33  | 63200                              | 2.00                  |                                                                                     |     |     |       |         |                                                                                     |
| 58                    | 4890                 | 25.30  | 61100                              | 2.4                   |                                                                                     |     |     |       |         |                                                                                     |
| 55                    | 5200                 | 26.86  | 61700                              | 1.65                  |                                                                                     |     |     |       |         |                                                                                     |
| 60                    | 4750                 | 24.57  | 60800                              | 1.80                  |                                                                                     |     |     |       |         |                                                                                     |
| 69                    | 4130                 | 21.38  | 59300                              | 2.9                   |                                                                                     |     |     |       |         |                                                                                     |
| 78                    | 3650                 | 18.87  | 57900                              | 3.0                   |                                                                                     |     |     |       |         |                                                                                     |
| 34                    | 8320                 | 43.03  | 39200                              | 0.90                  |                                                                                     |     |     |       |         |                                                                                     |
| 39                    | 7280                 | 37.61  | 39600                              | 1.05                  |                                                                                     |     |     |       |         |                                                                                     |
| 47                    | 6150                 | 31.80  | 39700                              | 1.25                  |                                                                                     |     |     |       |         |                                                                                     |
| 54                    | 5330                 | 27.57  | 39500                              | 1.45                  |                                                                                     |     |     |       |         |                                                                                     |
| 59                    | 4860                 | 25.14  | 39300                              | 1.60                  |                                                                                     |     |     |       |         |                                                                                     |
| 68                    | 4210                 | 21.76* | 38800                              | 1.85                  |                                                                                     |     |     |       |         |                                                                                     |
| 77                    | 3710                 | 19.20* | 38300                              | 2.1                   |                                                                                     |     |     |       |         |                                                                                     |
| 89                    | 3200                 | 16.58  | 37500                              | 2.4                   |                                                                                     |     |     |       |         |                                                                                     |
| 101                   | 2830                 | 14.67  | 36900                              | 2.7                   |                                                                                     |     |     |       |         |                                                                                     |
| 120                   | 2380                 | 12.33  | 35800                              | 2.9                   |                                                                                     |     |     |       |         |                                                                                     |
| 149                   | 1920                 | 9.96   | 34400                              | 3.4                   |                                                                                     |     |     |       |         |                                                                                     |


**P<sub>m</sub> = 30 kW**

| n <sub>a</sub><br>rpm | M <sub>a</sub><br>Nm | i      | F <sub>Ra</sub> <sup>1)</sup><br>N | SEW<br>f <sub>B</sub> |  |    |     |       | m<br>kg |  |
|-----------------------|----------------------|--------|------------------------------------|-----------------------|------------------------------------------------------------------------------------|----|-----|-------|---------|-------------------------------------------------------------------------------------|
| 67                    | 4280                 | 22.11  | 15100                              | 1.00                  |                                                                                    |    |     |       |         |                                                                                     |
| 74                    | 3880                 | 20.07  | 15500                              | 1.10                  |                                                                                    |    |     |       |         |                                                                                     |
| 86                    | 3330                 | 17.25* | 16000                              | 1.30                  |                                                                                    |    |     |       |         |                                                                                     |
| 98                    | 2910                 | 15.06  | 16300                              | 1.50                  |                                                                                    |    |     |       |         |                                                                                     |
| 116                   | 2470                 | 12.77  | 16400                              | 1.75                  | FA                                                                                 | 97 | DRN | 200L4 | 425     | 434                                                                                 |
| 133                   | 2160                 | 11.16  | 16400                              | 1.90                  | FAF                                                                                | 97 | DRN | 200L4 | 445     | 433                                                                                 |
| 163                   | 1750                 | 9.06   | 15400                              | 1.35                  | F                                                                                  | 97 | DRN | 200L4 | 430     | 432                                                                                 |
| 180                   | 1590                 | 8.22   | 15300                              | 1.50                  | FF                                                                                 | 97 | DRN | 200L4 | 465     | 433                                                                                 |
| 209                   | 1360                 | 7.07   | 15100                              | 1.70                  |                                                                                    |    |     |       |         |                                                                                     |
| 240                   | 1190                 | 6.17   | 14900                              | 1.90                  |                                                                                    |    |     |       |         |                                                                                     |
| 283                   | 1010                 | 5.23   | 14600                              | 2.1                   |                                                                                    |    |     |       |         |                                                                                     |
| 324                   | 880                  | 4.57   | 14300                              | 2.3                   |                                                                                    |    |     |       |         |                                                                                     |


**P<sub>m</sub> = 37 kW**

| n <sub>a</sub><br>rpm | M <sub>a</sub><br>Nm | i      | F <sub>Ra</sub> <sup>1)</sup><br>N | SEW<br>f <sub>B</sub> |  |     |     |       | m<br>kg |  |
|-----------------------|----------------------|--------|------------------------------------|-----------------------|------------------------------------------------------------------------------------|-----|-----|-------|---------|-------------------------------------------------------------------------------------|
| 17                    | 20400                | 85.80* | 88600                              | 0.90                  |                                                                                    |     |     |       |         |                                                                                     |
| 19                    | 18700                | 78.46  | 88700                              | 0.95                  |                                                                                    |     |     |       |         |                                                                                     |
| 22                    | 16200                | 68.28* | 88400                              | 1.10                  | FA                                                                                 | 157 | DRN | 225S4 | 930     | 452                                                                                 |
| 25                    | 14300                | 60.25  | 87800                              | 1.25                  | FAF                                                                                | 157 | DRN | 225S4 | 990     | 451                                                                                 |
| 28                    | 12400                | 52.24  | 86700                              | 1.45                  | F                                                                                  | 157 | DRN | 225S4 | 950     | 450                                                                                 |
| 32                    | 11000                | 46.48* | 85600                              | 1.60                  | FF                                                                                 | 157 | DRN | 225S4 | 1060    | 451                                                                                 |
| 37                    | 9550                 | 40.06  | 83900                              | 1.90                  |                                                                                    |     |     |       |         |                                                                                     |
| 46                    | 7750                 | 32.55  | 81300                              | 2.3                   |                                                                                    |     |     |       |         |                                                                                     |
| 54                    | 6580                 | 27.60  | 79000                              | 2.7                   |                                                                                    |     |     |       |         |                                                                                     |
| 27                    | 13100                | 55.31  | 59200                              | 0.90                  |                                                                                    |     |     |       |         |                                                                                     |
| 30                    | 11600                | 48.80  | 60800                              | 1.05                  | FA                                                                                 | 127 | DRN | 225S4 | 680     | 446                                                                                 |
| 35                    | 10000                | 42.15  | 61100                              | 1.20                  | FAF                                                                                | 127 | DRN | 225S4 | 720     | 445                                                                                 |
| 40                    | 8880                 | 37.28  | 60700                              | 1.35                  | F                                                                                  | 127 | DRN | 225S4 | 720     | 444                                                                                 |
| 47                    | 7460                 | 31.33  | 59900                              | 1.60                  | FF                                                                                 | 127 | DRN | 225S4 | 760     | 445                                                                                 |
| 59                    | 6030                 | 25.30  | 58400                              | 2.00                  |                                                                                    |     |     |       |         |                                                                                     |
| 55                    | 6400                 | 26.86  | 58900                              | 1.35                  |                                                                                    |     |     |       |         |                                                                                     |
| 60                    | 5850                 | 24.57  | 58200                              | 1.45                  |                                                                                    |     |     |       |         |                                                                                     |
| 69                    | 5090                 | 21.38  | 57000                              | 2.4                   |                                                                                    |     |     |       |         |                                                                                     |
| 79                    | 4490                 | 18.87  | 55900                              | 2.4                   | FA                                                                                 | 127 | DRN | 225S4 | 670     | 446                                                                                 |
| 91                    | 3890                 | 16.36  | 54500                              | 2.8                   | FAF                                                                                | 127 | DRN | 225S4 | 710     | 445                                                                                 |
| 102                   | 3460                 | 14.55  | 53300                              | 3.2                   | F                                                                                  | 127 | DRN | 225S4 | 700     | 444                                                                                 |
| 118                   | 2990                 | 12.54  | 51800                              | 3.3                   | FF                                                                                 | 127 | DRN | 225S4 | 750     | 445                                                                                 |
| 145                   | 2420                 | 10.19  | 49500                              | 3.9                   |                                                                                    |     |     |       |         |                                                                                     |
| 167                   | 2110                 | 8.86   | 47700                              | 3.3                   |                                                                                    |     |     |       |         |                                                                                     |
| 188                   | 1870                 | 7.88   | 46400                              | 3.2                   |                                                                                    |     |     |       |         |                                                                                     |
| 54                    | 6570                 | 27.57  | 36200                              | 1.20                  |                                                                                    |     |     |       |         |                                                                                     |
| 59                    | 5990                 | 25.14  | 36300                              | 1.30                  |                                                                                    |     |     |       |         |                                                                                     |
| 68                    | 5180                 | 21.76* | 36200                              | 1.50                  |                                                                                    |     |     |       |         |                                                                                     |
| 77                    | 4570                 | 19.20* | 36000                              | 1.70                  |                                                                                    |     |     |       |         |                                                                                     |
| 89                    | 3950                 | 16.58  | 35600                              | 2.00                  | FA                                                                                 | 107 | DRN | 225S4 | 530     | 440                                                                                 |
| 101                   | 3490                 | 14.67  | 35100                              | 2.2                   | FAF                                                                                | 107 | DRN | 225S4 | 550     | 439                                                                                 |
| 120                   | 2930                 | 12.33  | 34300                              | 2.4                   | F                                                                                  | 107 | DRN | 225S4 | 540     | 438                                                                                 |
| 149                   | 2370                 | 9.96   | 33200                              | 2.7                   | FF                                                                                 | 107 | DRN | 225S4 | 570     | 439                                                                                 |
| 153                   | 2310                 | 9.69   | 32400                              | 2.1                   |                                                                                    |     |     |       |         |                                                                                     |
| 177                   | 1990                 | 8.37   | 31600                              | 2.4                   |                                                                                    |     |     |       |         |                                                                                     |
| 200                   | 1760                 | 7.40   | 31000                              | 2.6                   |                                                                                    |     |     |       |         |                                                                                     |
| 238                   | 1480                 | 6.22   | 30000                              | 3.1                   |                                                                                    |     |     |       |         |                                                                                     |

| P <sub>m</sub> = 45 kW |                      |        |                                    |                       |                                                                                    |     |     |       |         |                                                                                     |
|------------------------|----------------------|--------|------------------------------------|-----------------------|------------------------------------------------------------------------------------|-----|-----|-------|---------|-------------------------------------------------------------------------------------|
| n <sub>a</sub><br>rpm  | M <sub>a</sub><br>Nm | i      | F <sub>Ra</sub> <sup>1)</sup><br>N | SEW<br>f <sub>B</sub> |  |     |     |       | m<br>kg |  |
| 22                     | 19700                | 68.28* | 81400                              | 0.90                  | FA<br>FAF<br>F<br>FF                                                               | 157 | DRN | 225M4 | 930     | 452                                                                                 |
| 25                     | 17400                | 60.25  | 81600                              | 1.05                  |                                                                                    |     |     |       |         |                                                                                     |
| 28                     | 15100                | 52.24  | 81300                              | 1.20                  |                                                                                    |     |     |       |         |                                                                                     |
| 32                     | 13400                | 46.48* | 80800                              | 1.35                  |                                                                                    |     |     |       |         |                                                                                     |
| 37                     | 11600                | 40.06  | 79800                              | 1.55                  |                                                                                    |     |     |       |         |                                                                                     |
| 46                     | 9430                 | 32.55  | 78000                              | 1.90                  |                                                                                    |     |     |       |         |                                                                                     |
| 54                     | 8000                 | 27.60  | 76100                              | 2.2                   |                                                                                    |     |     |       |         |                                                                                     |
| 30                     | 14100                | 48.80  | 51600                              | 0.85                  | FA<br>FAF<br>F<br>FF                                                               | 127 | DRN | 225M4 | 680     | 446                                                                                 |
| 35                     | 12200                | 42.15  | 54300                              | 1.00                  |                                                                                    |     |     |       |         |                                                                                     |
| 40                     | 10800                | 37.28  | 55800                              | 1.10                  |                                                                                    |     |     |       |         |                                                                                     |
| 47                     | 9080                 | 31.33  | 56100                              | 1.30                  |                                                                                    |     |     |       |         |                                                                                     |
| 59                     | 7330                 | 25.30  | 55400                              | 1.65                  |                                                                                    |     |     |       |         |                                                                                     |
| 55                     | 7780                 | 26.86  | 55600                              | 1.10                  | FA<br>FAF<br>F<br>FF                                                               | 127 | DRN | 225M4 | 670     | 446                                                                                 |
| 60                     | 7120                 | 24.57  | 55200                              | 1.20                  |                                                                                    |     |     |       |         |                                                                                     |
| 69                     | 6190                 | 21.38  | 54500                              | 1.95                  |                                                                                    |     |     |       |         |                                                                                     |
| 79                     | 5470                 | 18.87  | 53600                              | 2.0                   |                                                                                    |     |     |       |         |                                                                                     |
| 91                     | 4740                 | 16.36  | 52500                              | 2.3                   |                                                                                    |     |     |       |         |                                                                                     |
| 102                    | 4210                 | 14.55  | 51600                              | 2.6                   |                                                                                    |     |     |       |         |                                                                                     |
| 118                    | 3630                 | 12.54  | 50300                              | 2.8                   |                                                                                    |     |     |       |         |                                                                                     |
| 145                    | 2950                 | 10.19  | 48300                              | 3.2                   |                                                                                    |     |     |       |         |                                                                                     |
| 167                    | 2560                 | 8.86   | 46500                              | 2.7                   |                                                                                    |     |     |       |         |                                                                                     |
| 188                    | 2280                 | 7.88   | 45400                              | 2.6                   |                                                                                    |     |     |       |         |                                                                                     |
| 218                    | 1970                 | 6.80   | 44000                              | 3.6                   |                                                                                    |     |     |       |         |                                                                                     |
| 268                    | 1600                 | 5.52   | 41900                              | 3.8                   |                                                                                    |     |     |       |         |                                                                                     |
| 54                     | 7990                 | 27.57  | 31500                              | 1.00                  | FA<br>FAF<br>F<br>FF                                                               | 107 | DRN | 225M4 | 530     | 440                                                                                 |
| 59                     | 7290                 | 25.14  | 32600                              | 1.10                  |                                                                                    |     |     |       |         |                                                                                     |
| 68                     | 6300                 | 21.76* | 33200                              | 1.25                  |                                                                                    |     |     |       |         |                                                                                     |
| 77                     | 5560                 | 19.20* | 33300                              | 1.40                  |                                                                                    |     |     |       |         |                                                                                     |
| 89                     | 4800                 | 16.58  | 33300                              | 1.65                  |                                                                                    |     |     |       |         |                                                                                     |
| 101                    | 4250                 | 14.67  | 33100                              | 1.80                  |                                                                                    |     |     |       |         |                                                                                     |
| 120                    | 3570                 | 12.33  | 32600                              | 1.95                  |                                                                                    |     |     |       |         |                                                                                     |
| 149                    | 2880                 | 9.96   | 31900                              | 2.2                   |                                                                                    |     |     |       |         |                                                                                     |
| 153                    | 2810                 | 9.69   | 30900                              | 1.75                  |                                                                                    |     |     |       |         |                                                                                     |
| 177                    | 2420                 | 8.37   | 30400                              | 2.00                  |                                                                                    |     |     |       |         |                                                                                     |
| 200                    | 2140                 | 7.40   | 29800                              | 2.1                   |                                                                                    |     |     |       |         |                                                                                     |
| 238                    | 1800                 | 6.22   | 29000                              | 2.6                   |                                                                                    |     |     |       |         |                                                                                     |

| P <sub>m</sub> = 55 kW |                      |        |                                    |                       |                                                                                      |     |     |       |         |                                                                                       |
|------------------------|----------------------|--------|------------------------------------|-----------------------|--------------------------------------------------------------------------------------|-----|-----|-------|---------|---------------------------------------------------------------------------------------|
| n <sub>a</sub><br>rpm  | M <sub>a</sub><br>Nm | i      | F <sub>Ra</sub> <sup>1)</sup><br>N | SEW<br>f <sub>B</sub> |  |     |     |       | m<br>kg |  |
| 25                     | 21300                | 60.25  | 73800                              | 0.85                  | FA<br>FAF<br>F<br>FF                                                                 | 157 | DRN | 250M4 | 1080    | 452                                                                                   |
| 28                     | 18500                | 52.24  | 74600                              | 0.95                  |                                                                                      |     |     |       |         |                                                                                       |
| 32                     | 16400                | 46.48* | 74800                              | 1.10                  |                                                                                      |     |     |       |         |                                                                                       |
| 37                     | 14100                | 40.06  | 74700                              | 1.25                  |                                                                                      |     |     |       |         |                                                                                       |
| 46                     | 11500                | 32.55  | 73800                              | 1.55                  |                                                                                      |     |     |       |         |                                                                                       |
| 54                     | 9780                 | 27.60  | 72600                              | 1.85                  |                                                                                      |     |     |       |         |                                                                                       |
| 52                     | 10100                | 28.60* | 72900                              | 1.70                  | FA<br>FAF<br>F<br>FF                                                                 | 157 | DRN | 250M4 | 1080    | 452                                                                                   |
| 58                     | 9010                 | 25.43  | 71900                              | 1.65                  |                                                                                      |     |     |       |         |                                                                                       |
| 67                     | 7850                 | 22.16  | 70600                              | 2.3                   |                                                                                      |     |     |       |         |                                                                                       |
| 75                     | 7000                 | 19.77  | 69400                              | 2.4                   |                                                                                      |     |     |       |         |                                                                                       |
| 88                     | 5970                 | 16.85  | 67500                              | 3.0                   |                                                                                      |     |     |       |         |                                                                                       |
| 40                     | 13200                | 37.28  | 47000                              | 0.90                  | FA<br>FAF<br>F<br>FF                                                                 | 127 | DRN | 250M4 | 830     | 446                                                                                   |
| 47                     | 11100                | 31.33  | 50000                              | 1.10                  |                                                                                      |     |     |       |         |                                                                                       |
| 59                     | 8960                 | 25.30  | 51600                              | 1.35                  |                                                                                      |     |     |       |         |                                                                                       |
|                        |                      |        |                                    |                       |                                                                                      |     |     |       |         |                                                                                       |


**P<sub>m</sub> = 55 kW**

| n <sub>a</sub><br>rpm | M <sub>a</sub><br>Nm | i     | F <sub>Ra</sub> <sup>1)</sup><br>N | SEW<br>f <sub>B</sub> |  |     |     |       | m<br>kg |  |
|-----------------------|----------------------|-------|------------------------------------|-----------------------|------------------------------------------------------------------------------------|-----|-----|-------|---------|-------------------------------------------------------------------------------------|
| 69                    | 7570                 | 21.38 | 51300                              | 1.60                  |                                                                                    |     |     |       |         |                                                                                     |
| 79                    | 6680                 | 18.87 | 50800                              | 1.65                  |                                                                                    |     |     |       |         |                                                                                     |
| 91                    | 5790                 | 16.36 | 50100                              | 1.90                  |                                                                                    |     |     |       |         |                                                                                     |
| 102                   | 5150                 | 14.55 | 49400                              | 2.1                   |                                                                                    |     |     |       |         |                                                                                     |
| 118                   | 4440                 | 12.54 | 48400                              | 2.2                   | FA                                                                                 | 127 | DRN | 250M4 | 820     | 446                                                                                 |
| 145                   | 3610                 | 10.19 | 46800                              | 2.6                   | FAF                                                                                | 127 | DRN | 250M4 | 850     | 445                                                                                 |
| 167                   | 3140                 | 8.86  | 45100                              | 2.2                   | F                                                                                  | 127 | DRN | 250M4 | 850     | 444                                                                                 |
| 188                   | 2790                 | 7.88  | 44100                              | 2.2                   | FF                                                                                 | 127 | DRN | 250M4 | 900     | 445                                                                                 |
| 218                   | 2400                 | 6.80  | 42900                              | 2.9                   |                                                                                    |     |     |       |         |                                                                                     |
| 268                   | 1950                 | 5.52  | 41000                              | 3.1                   |                                                                                    |     |     |       |         |                                                                                     |
| 317                   | 1650                 | 4.68  | 39600                              | 3.6                   |                                                                                    |     |     |       |         |                                                                                     |

**P<sub>m</sub> = 75 kW**


| n <sub>a</sub><br>rpm | M <sub>a</sub><br>Nm | i      | F <sub>Ra</sub> <sup>1)</sup><br>N | SEW<br>f <sub>B</sub> |  |     |     |       | m<br>kg |  |
|-----------------------|----------------------|--------|------------------------------------|-----------------------|------------------------------------------------------------------------------------|-----|-----|-------|---------|-------------------------------------------------------------------------------------|
| 32                    | 22400                | 46.48* | 62900                              | 0.80                  | FA                                                                                 | 157 | DRN | 280S4 | 1130    | 452                                                                                 |
| 37                    | 19300                | 40.06  | 64400                              | 0.95                  | FAF                                                                                | 157 | DRN | 280S4 | 1190    | 451                                                                                 |
| 46                    | 15700                | 32.55  | 65400                              | 1.15                  | F                                                                                  | 157 | DRN | 280S4 | 1150    | 450                                                                                 |
| 54                    | 13300                | 27.60  | 65500                              | 1.35                  | FF                                                                                 | 157 | DRN | 280S4 | 1260    | 451                                                                                 |
| 52                    | 13800                | 28.60* | 65500                              | 1.25                  |                                                                                    |     |     |       |         |                                                                                     |
| 58                    | 12200                | 25.43  | 65400                              | 1.20                  | FA                                                                                 | 157 | DRN | 280S4 | 1130    | 452                                                                                 |
| 67                    | 10700                | 22.16  | 64900                              | 1.70                  | FAF                                                                                | 157 | DRN | 280S4 | 1190    | 451                                                                                 |
| 75                    | 9550                 | 19.77  | 64300                              | 1.80                  | F                                                                                  | 157 | DRN | 280S4 | 1150    | 450                                                                                 |
| 88                    | 8140                 | 16.85  | 63200                              | 2.2                   | FF                                                                                 | 157 | DRN | 280S4 | 1260    | 451                                                                                 |
| 106                   | 6740                 | 13.96  | 61600                              | 2.5                   |                                                                                    |     |     |       |         |                                                                                     |
| 124                   | 5750                 | 11.92  | 60100                              | 2.8                   |                                                                                    |     |     |       |         |                                                                                     |
| 59                    | 12200                | 25.30  | 40000                              | 1.00                  | FA                                                                                 | 127 | DRN | 280S4 | 880     | 446                                                                                 |
|                       |                      |        |                                    |                       | FAF                                                                                | 127 | DRN | 280S4 | 920     | 445                                                                                 |
|                       |                      |        |                                    |                       | F                                                                                  | 127 | DRN | 280S4 | 910     | 444                                                                                 |
|                       |                      |        |                                    |                       | FF                                                                                 | 127 | DRN | 280S4 | 960     | 445                                                                                 |
| 69                    | 10300                | 21.38  | 43000                              | 1.15                  |                                                                                    |     |     |       |         |                                                                                     |
| 79                    | 9110                 | 18.87  | 44400                              | 1.20                  |                                                                                    |     |     |       |         |                                                                                     |
| 91                    | 7900                 | 16.36  | 45200                              | 1.40                  |                                                                                    |     |     |       |         |                                                                                     |
| 102                   | 7030                 | 14.55  | 45000                              | 1.55                  | FA                                                                                 | 127 | DRN | 280S4 | 870     | 446                                                                                 |
| 118                   | 6060                 | 12.54  | 44600                              | 1.65                  | FAF                                                                                | 127 | DRN | 280S4 | 900     | 445                                                                                 |
| 145                   | 4920                 | 10.19  | 43700                              | 1.95                  | F                                                                                  | 127 | DRN | 280S4 | 900     | 444                                                                                 |
| 167                   | 4280                 | 8.86   | 42200                              | 1.65                  | FF                                                                                 | 127 | DRN | 280S4 | 950     | 445                                                                                 |
| 188                   | 3800                 | 7.88   | 41600                              | 1.55                  |                                                                                    |     |     |       |         |                                                                                     |
| 218                   | 3280                 | 6.80   | 40700                              | 2.1                   |                                                                                    |     |     |       |         |                                                                                     |
| 268                   | 2660                 | 5.52   | 39300                              | 2.2                   |                                                                                    |     |     |       |         |                                                                                     |
| 317                   | 2260                 | 4.68   | 38100                              | 2.6                   |                                                                                    |     |     |       |         |                                                                                     |


**P<sub>m</sub> = 90 kW**


| n <sub>a</sub><br>rpm | M <sub>a</sub><br>Nm | i     | F <sub>Ra</sub> <sup>1)</sup><br>N | SEW<br>f <sub>B</sub> |  |     |     |       | m<br>kg |  |
|-----------------------|----------------------|-------|------------------------------------|-----------------------|--------------------------------------------------------------------------------------|-----|-----|-------|---------|---------------------------------------------------------------------------------------|
| 46                    | 18800                | 32.55 | 59100                              | 0.95                  | FA                                                                                   | 157 | DRN | 280M4 | 1250    | 452                                                                                   |
| 54                    | 16000                | 27.60 | 60200                              | 1.10                  | FAF                                                                                  | 157 | DRN | 280M4 | 1310    | 451                                                                                   |
|                       |                      |       |                                    |                       | F                                                                                    | 157 | DRN | 280M4 | 1270    | 450                                                                                   |
|                       |                      |       |                                    |                       | FF                                                                                   | 157 | DRN | 280M4 | 1380    | 451                                                                                   |
| 67                    | 12800                | 22.16 | 60600                              | 1.40                  | FA                                                                                   | 157 | DRN | 280M4 | 1240    | 452                                                                                   |
| 75                    | 11400                | 19.77 | 60500                              | 1.50                  | FAF                                                                                  | 157 | DRN | 280M4 | 1300    | 451                                                                                   |
| 88                    | 9770                 | 16.85 | 59900                              | 1.85                  | F                                                                                    | 157 | DRN | 280M4 | 1260    | 450                                                                                   |
| 106                   | 8100                 | 13.96 | 58900                              | 2.1                   | FF                                                                                   | 157 | DRN | 280M4 | 1370    | 451                                                                                   |
| 124                   | 6910                 | 11.92 | 57800                              | 2.3                   |                                                                                      |     |     |       |         |                                                                                       |
| 59                    | 14600                | 25.30 | 29600                              | 0.80                  | FA                                                                                   | 127 | DRN | 280M4 | 990     | 446                                                                                   |
|                       |                      |       |                                    |                       | FAF                                                                                  | 127 | DRN | 280M4 | 1030    | 445                                                                                   |
|                       |                      |       |                                    |                       | F                                                                                    | 127 | DRN | 280M4 | 1030    | 444                                                                                   |
|                       |                      |       |                                    |                       | FF                                                                                   | 127 | DRN | 280M4 | 1070    | 445                                                                                   |


# 9 Flachgetriebemotoren


Auswahltabellen F..DRN.. in kW

| P <sub>m</sub> = 90 kW |                      |       |                                    |                       |                                                                                    |     |     |       |         |                                                                                     |
|------------------------|----------------------|-------|------------------------------------|-----------------------|------------------------------------------------------------------------------------|-----|-----|-------|---------|-------------------------------------------------------------------------------------|
| n <sub>a</sub><br>rpm  | M <sub>a</sub><br>Nm | i     | F <sub>Ra</sub> <sup>1)</sup><br>N | SEW<br>f <sub>B</sub> |  |     |     |       | m<br>kg |  |
| 91                     | 9490                 | 16.36 | 39900                              | 1.15                  | <div>FA</div> <div>FAF</div> <div>F</div> <div>FF</div>                            | 127 | DRN | 280M4 | 980     | 446                                                                                 |
| 102                    | 8440                 | 14.55 | 41100                              | 1.30                  |                                                                                    |     |     |       |         |                                                                                     |
| 118                    | 7270                 | 12.54 | 41800                              | 1.35                  |                                                                                    |     |     |       |         |                                                                                     |
| 145                    | 5910                 | 10.19 | 41400                              | 1.60                  |                                                                                    |     |     |       |         |                                                                                     |
| 167                    | 5140                 | 8.86  | 40100                              | 1.35                  |                                                                                    |     |     |       |         |                                                                                     |
| 188                    | 4570                 | 7.88  | 39700                              | 1.30                  |                                                                                    |     |     |       |         |                                                                                     |
| 218                    | 3940                 | 6.80  | 39000                              | 1.80                  |                                                                                    |     |     |       |         |                                                                                     |
| 268                    | 3200                 | 5.52  | 37900                              | 1.85                  |                                                                                    |     |     |       |         |                                                                                     |
| 316                    | 2710                 | 4.68  | 36900                              | 2.2                   |                                                                                    |     |     |       |         |                                                                                     |

| P <sub>m</sub> = 110 kW |                      |       |                                    |                       |                                                                                    |     |     |              |         |                                                                                     |
|-------------------------|----------------------|-------|------------------------------------|-----------------------|------------------------------------------------------------------------------------|-----|-----|--------------|---------|-------------------------------------------------------------------------------------|
| n <sub>a</sub><br>rpm   | M <sub>a</sub><br>Nm | i     | F <sub>Ra</sub> <sup>1)</sup><br>N | SEW<br>f <sub>B</sub> |  |     |     |              | m<br>kg |  |
| 54                      | 19400                | 27.60 | 53100                              | 0.90                  | FA                                                                                 | 157 | DRN | 315S4        | 1490    | 452                                                                                 |
|                         |                      |       |                                    |                       | FAF                                                                                | 157 | DRN | 315S4        | 1550    | 451                                                                                 |
|                         |                      |       |                                    |                       | F                                                                                  | 157 | DRN | 315S4        | 1510    | 450                                                                                 |
|                         |                      |       |                                    |                       | FF                                                                                 | 157 | DRN | 315S4        | 1620    | 451                                                                                 |
| 67                      | 15600                | 22.16 | 54900                              | 1.15                  | FA                                                                                 | 157 | DRN | 315S4/ERF/NS | 1490    | 452                                                                                 |
|                         |                      |       |                                    |                       | FAF                                                                                | 157 | DRN | 315S4/ERF/NS | 1550    | 451                                                                                 |
|                         |                      |       |                                    |                       | F                                                                                  | 157 | DRN | 315S4/ERF/NS | 1510    | 450                                                                                 |
|                         |                      |       |                                    |                       | FF                                                                                 | 157 | DRN | 315S4/ERF/NS | 1610    | 451                                                                                 |
| 75                      | 13900                | 19.77 | 55400                              | 1.20                  | FA                                                                                 | 157 | DRN | 315S4        | 1490    | 452                                                                                 |
| 88                      | 11800                | 16.85 | 55600                              | 1.50                  | FAF                                                                                | 157 | DRN | 315S4        | 1550    | 451                                                                                 |
| 107                     | 9850                 | 13.96 | 55300                              | 1.70                  | F                                                                                  | 157 | DRN | 315S4        | 1510    | 450                                                                                 |
| 125                     | 8410                 | 11.92 | 54700                              | 1.90                  | FF                                                                                 | 157 | DRN | 315S4        | 1610    | 451                                                                                 |


| P <sub>m</sub> = 132 kW |                      |       |                                    |                       |                                                                                      |     |     |              |         |                                                                                       |
|-------------------------|----------------------|-------|------------------------------------|-----------------------|--------------------------------------------------------------------------------------|-----|-----|--------------|---------|---------------------------------------------------------------------------------------|
| n <sub>a</sub><br>rpm   | M <sub>a</sub><br>Nm | i     | F <sub>Ra</sub> <sup>1)</sup><br>N | SEW<br>f <sub>B</sub> |  |     |     |              | m<br>kg |  |
| 67<br>75                | 18700                | 22.16 | 48700                              | 0.95                  | FA                                                                                   | 157 | DRN | 315M4/ERF/NS | 1510    | 452                                                                                   |
|                         | 16700                | 19.77 | 49800                              | 1.00                  | FAF                                                                                  | 157 | DRN | 315M4/ERF/NS | 1570    | 451                                                                                   |
|                         |                      |       |                                    |                       | F                                                                                    | 157 | DRN | 315M4/ERF/NS | 1530    | 450                                                                                   |
|                         |                      |       |                                    |                       | FF                                                                                   | 157 | DRN | 315M4/ERF/NS | 1630    | 451                                                                                   |
| 88<br>107<br>125        | 14200                | 16.85 | 50900                              | 1.25                  | FA                                                                                   | 157 | DRN | 315M4        | 1510    | 452                                                                                   |
|                         | 11800                | 13.96 | 51400                              | 1.45                  | FAF                                                                                  | 157 | DRN | 315M4        | 1570    | 451                                                                                   |
|                         | 10000                | 11.92 | 51400                              | 1.60                  | F                                                                                    | 157 | DRN | 315M4        | 1530    | 450                                                                                   |
|                         |                      |       |                                    |                       | FF                                                                                   | 157 | DRN | 315M4        | 1630    | 451                                                                                   |


| P <sub>m</sub> = 160 kW |                      |       |                                    |                       |                                                                                      |     |     |       |         |                                                                                       |
|-------------------------|----------------------|-------|------------------------------------|-----------------------|--------------------------------------------------------------------------------------|-----|-----|-------|---------|---------------------------------------------------------------------------------------|
| n <sub>a</sub><br>rpm   | M <sub>a</sub><br>Nm | i     | F <sub>Ra</sub> <sup>1)</sup><br>N | SEW<br>f <sub>B</sub> |  |     |     |       | m<br>kg |  |
| 88                      | 17300                | 16.85 | 44800                              | 1.05                  | FA                                                                                   | 157 | DRN | 315L4 | 1640    | 452                                                                                   |
| 106                     | 14300                | 13.96 | 46400                              | 1.20                  | FAF                                                                                  | 157 | DRN | 315L4 | 1700    | 451                                                                                   |
|                         |                      |       |                                    |                       | F                                                                                    | 157 | DRN | 315L4 | 1660    | 450                                                                                   |
| 125                     | 12200                | 11.92 | 47100                              | 1.30                  | FF                                                                                   | 157 | DRN | 315L4 | 1770    | 451                                                                                   |


| P <sub>m</sub> = 200 kW |                      |       |                                    |                       |                                                                                      |     |     |              |         |                                                                                       |
|-------------------------|----------------------|-------|------------------------------------|-----------------------|--------------------------------------------------------------------------------------|-----|-----|--------------|---------|---------------------------------------------------------------------------------------|
| n <sub>a</sub><br>rpm   | M <sub>a</sub><br>Nm | i     | F <sub>Ra</sub> <sup>1)</sup><br>N | SEW<br>f <sub>B</sub> |  |     |     |              | m<br>kg |  |
| 88                      | 21600                | 16.85 | 36200                              | 0.85                  | FA                                                                                   | 157 | DRN | 315H4/ERF/NS | 1760    | 452                                                                                   |
|                         |                      |       |                                    |                       | FAF                                                                                  | 157 | DRN | 315H4/ERF/NS | 1820    | 451                                                                                   |
|                         |                      |       |                                    |                       | F                                                                                    | 157 | DRN | 315H4/ERF/NS | 1780    | 450                                                                                   |
|                         |                      |       |                                    |                       | FF                                                                                   | 157 | DRN | 315H4/ERF/NS | 1880    | 451                                                                                   |
| 107                     | 17900                | 13.96 | 39200                              | 0.95                  | FA                                                                                   | 157 | DRN | 315H4        | 1760    | 452                                                                                   |
|                         |                      |       |                                    |                       | FAF                                                                                  | 157 | DRN | 315H4        | 1820    | 451                                                                                   |
|                         |                      |       |                                    |                       | F                                                                                    | 157 | DRN | 315H4        | 1780    | 450                                                                                   |
|                         |                      |       |                                    |                       | FF                                                                                   | 157 | DRN | 315H4        | 1880    | 451                                                                                   |
| 125                     | 15200                | 11.92 | 41000                              | 1.05                  |                                                                                      |     |     |              |         |                                                                                       |


21933170/DE – 11/2015

## 9.4 Auswahltabellen für niedrige Abtriebsdrehzahlen F..R..DRN.. in Nm


| <b>M<sub>a max</sub> = 130 Nm</b> |          |                                         |                                                                                    |  |  |  |                                                                                                    |
|-----------------------------------|----------|-----------------------------------------|------------------------------------------------------------------------------------|--|--|--|----------------------------------------------------------------------------------------------------|
| <b>n<sub>a</sub></b><br>rpm       | <b>i</b> | <b>F<sub>Ra</sub><sup>1)</sup></b><br>N |  |  |  |  | <b>m</b><br>kg  |
| 0.15                              | 8972     | 4500                                    |                                                                                    |  |  |  |                                                                                                    |
| 0.18                              | 7736     | 4500                                    |                                                                                    |  |  |  |                                                                                                    |
| 0.19                              | 7211     | 4500                                    |                                                                                    |  |  |  |                                                                                                    |
| 0.22                              | 6303     | 4500                                    |                                                                                    |  |  |  |                                                                                                    |
| 0.25                              | 5435     | 4500                                    |                                                                                    |  |  |  |                                                                                                    |
| 0.28                              | 4855     | 4500                                    |                                                                                    |  |  |  |                                                                                                    |
| 0.33                              | 4243     | 4500                                    |                                                                                    |  |  |  |                                                                                                    |
| 0.37                              | 3715     | 4500                                    |                                                                                    |  |  |  |                                                                                                    |
| 0.43                              | 3247     | 4500                                    |                                                                                    |  |  |  |                                                                                                    |
| 0.48                              | 2878     | 4500                                    |                                                                                    |  |  |  |                                                                                                    |
| 0.55                              | 2515     | 4500                                    |                                                                                    |  |  |  |                                                                                                    |
| 0.62                              | 2217     | 4500                                    |                                                                                    |  |  |  |                                                                                                    |
| 0.73                              | 1898     | 4500                                    |                                                                                    |  |  |  |                                                                                                    |
| 0.84                              | 1645     | 4500                                    |                                                                                    |  |  |  |                                                                                                    |
| 0.90                              | 1525     | 4500                                    |                                                                                    |  |  |  |                                                                                                    |
| 1.0                               | 1322     | 4500                                    |                                                                                    |  |  |  |                                                                                                    |
| 1.2                               | 1146     | 4500                                    |                                                                                    |  |  |  |                                                                                                    |
| 1.4                               | 1013     | 4500                                    |                                                                                    |  |  |  |                                                                                                    |
| 1.6                               | 890      | 4500                                    |                                                                                    |  |  |  |                                                                                                    |
| 1.8                               | 778      | 4500                                    |                                                                                    |  |  |  |                                                                                                    |
| 2.0                               | 682      | 4500                                    |                                                                                    |  |  |  |                                                                                                    |
| 2.3                               | 602      | 4500                                    |                                                                                    |  |  |  |                                                                                                    |
| 2.6                               | 520      | 4500                                    |                                                                                    |  |  |  |                                                                                                    |
| 3.0                               | 458      | 4500                                    |                                                                                    |  |  |  |                                                                                                    |
| 3.5                               | 397      | 4500                                    |                                                                                    |  |  |  |                                                                                                    |
| 4.0                               | 342      | 4500                                    |                                                                                    |  |  |  |                                                                                                    |
| 4.6                               | 302      | 4500                                    |                                                                                    |  |  |  |                                                                                                    |
| 5.2                               | 266      | 4500                                    |                                                                                    |  |  |  |                                                                                                    |
| 5.8                               | 236      | 4500                                    |                                                                                    |  |  |  |                                                                                                    |
| 6.5                               | 211      | 4500                                    |                                                                                    |  |  |  |                                                                                                    |
| 7.4                               | 186      | 4500                                    |                                                                                    |  |  |  |                                                                                                    |
| 9.3                               | 142      | 4500                                    |                                                                                    |  |  |  |                                                                                                    |
| 11                                | 124      | 4500                                    |                                                                                    |  |  |  |                                                                                                    |
| 12                                | 109      | 4500                                    |                                                                                    |  |  |  |                                                                                                    |
| 14                                | 96       | 4500                                    |                                                                                    |  |  |  |                                                                                                    |


| <b>M<sub>a max</sub> = 200 Nm</b> |          |                                         |                                                                                      |  |  |  |                                                                                                      |
|-----------------------------------|----------|-----------------------------------------|--------------------------------------------------------------------------------------|--|--|--|------------------------------------------------------------------------------------------------------|
| <b>n<sub>a</sub></b><br>rpm       | <b>i</b> | <b>F<sub>Ra</sub><sup>1)</sup></b><br>N |  |  |  |  | <b>m</b><br>kg  |
| 0.17                              | 8193     | 4290                                    |                                                                                      |  |  |  |                                                                                                      |
| 0.20                              | 7064     | 4290                                    |                                                                                      |  |  |  |                                                                                                      |
| 0.21                              | 6585     | 4290                                    |                                                                                      |  |  |  |                                                                                                      |
| 0.24                              | 5756     | 4290                                    |                                                                                      |  |  |  |                                                                                                      |
| 0.28                              | 4963     | 4290                                    |                                                                                      |  |  |  |                                                                                                      |
| 0.31                              | 4434     | 4290                                    |                                                                                      |  |  |  |                                                                                                      |
| 0.36                              | 3875     | 4290                                    |                                                                                      |  |  |  |                                                                                                      |
| 0.41                              | 3392     | 4290                                    |                                                                                      |  |  |  |                                                                                                      |
| 0.47                              | 2965     | 4290                                    |                                                                                      |  |  |  |                                                                                                      |
| 0.53                              | 2587     | 4290                                    |                                                                                      |  |  |  |                                                                                                      |
| 0.60                              | 2284     | 4290                                    |                                                                                      |  |  |  |                                                                                                      |
| 0.69                              | 1997     | 4290                                    |                                                                                      |  |  |  |                                                                                                      |
| 0.17                              | 8193     | 4290                                    |                                                                                      |  |  |  |                                                                                                      |
| 0.20                              | 7064     | 4290                                    |                                                                                      |  |  |  |                                                                                                      |
| 0.21                              | 6585     | 4290                                    |                                                                                      |  |  |  |                                                                                                      |
| 0.24                              | 5756     | 4290                                    |                                                                                      |  |  |  |                                                                                                      |
| 0.28                              | 4963     | 4290                                    |                                                                                      |  |  |  |                                                                                                      |
| 0.31                              | 4434     | 4290                                    |                                                                                      |  |  |  |                                                                                                      |
| 0.36                              | 3875     | 4290                                    |                                                                                      |  |  |  |                                                                                                      |
| 0.41                              | 3392     | 4290                                    |                                                                                      |  |  |  |                                                                                                      |
| 0.47                              | 2965     | 4290                                    |                                                                                      |  |  |  |                                                                                                      |
| 0.53                              | 2587     | 4290                                    |                                                                                      |  |  |  |                                                                                                      |
| 0.60                              | 2284     | 4290                                    |                                                                                      |  |  |  |                                                                                                      |
| 0.69                              | 1997     | 4290                                    |                                                                                      |  |  |  |                                                                                                      |

| <b>M<sub>a max</sub> = 200 Nm</b>  |          |                                                |                                                                                    |       |    |      |                       |                                                                                     |
|------------------------------------|----------|------------------------------------------------|------------------------------------------------------------------------------------|-------|----|------|-----------------------|-------------------------------------------------------------------------------------|
| <b>n<sub>a</sub></b><br><b>rpm</b> | <b>i</b> | <b>F<sub>Ra</sub><sup>1)</sup></b><br><b>N</b> |  |       |    |      | <b>m</b><br><b>kg</b> |  |
| 0.72                               | 1929     | 4290                                           | FA<br>FAF<br>F<br>FF                                                               | 37R17 | DR | 63S4 | 19                    | 456                                                                                 |
| 0.82                               | 1679     | 4290                                           |                                                                                    |       |    |      |                       |                                                                                     |
| 0.89                               | 1550     | 4290                                           |                                                                                    |       |    |      |                       |                                                                                     |
| 1.0                                | 1356     | 4290                                           |                                                                                    |       |    |      |                       |                                                                                     |
| 1.2                                | 1180     | 4290                                           |                                                                                    |       |    |      |                       |                                                                                     |
| 1.3                                | 1044     | 4290                                           |                                                                                    |       |    |      |                       |                                                                                     |
| 1.5                                | 914      | 4290                                           |                                                                                    |       |    |      |                       |                                                                                     |
| 1.7                                | 808      | 4290                                           |                                                                                    |       |    |      |                       |                                                                                     |
| 2.0                                | 698      | 4290                                           |                                                                                    |       |    |      |                       |                                                                                     |
| 2.2                                | 616      | 4290                                           |                                                                                    |       |    |      |                       |                                                                                     |
| 2.5                                | 544      | 4290                                           |                                                                                    |       |    |      |                       |                                                                                     |
| 3.0                                | 466      | 4290                                           |                                                                                    |       |    |      |                       |                                                                                     |
| 3.4                                | 411      | 4290                                           |                                                                                    |       |    |      |                       |                                                                                     |
| 3.8                                | 364      | 4290                                           |                                                                                    |       |    |      |                       |                                                                                     |
| 4.2                                | 326      | 4290                                           | FA                                                                                 | 37R17 | DR | 63S4 | 19                    | 456                                                                                 |
| 4.8                                | 285      | 4290                                           | FAF                                                                                | 37R17 | DR | 63S4 | 20                    | 456                                                                                 |
|                                    |          |                                                | F                                                                                  | 37R17 | DR | 63S4 | 19                    | 456                                                                                 |
|                                    |          |                                                | FF                                                                                 | 37R17 | DR | 63S4 | 21                    | 456                                                                                 |
| 5.3                                | 250      | 4290                                           | FA                                                                                 | 37R17 | DR | 63M4 | 19                    | 456                                                                                 |
| 6.0                                | 219      | 4290                                           | FAF                                                                                | 37R17 | DR | 63M4 | 20                    | 456                                                                                 |
| 7.1                                | 186      | 4290                                           | F                                                                                  | 37R17 | DR | 63M4 | 19                    | 456                                                                                 |
|                                    |          |                                                | FF                                                                                 | 37R17 | DR | 63M4 | 21                    | 456                                                                                 |
| 7.8                                | 167      | 4290                                           | FA                                                                                 | 37R17 | DR | 63L4 | 20                    | 456                                                                                 |
| 8.9                                | 145      | 4290                                           | FAF                                                                                | 37R17 | DR | 63L4 | 21                    | 456                                                                                 |
| 10                                 | 129      | 4290                                           | F                                                                                  | 37R17 | DR | 63L4 | 20                    | 456                                                                                 |
|                                    |          |                                                | FF                                                                                 | 37R17 | DR | 63L4 | 22                    | 456                                                                                 |


| <b>M<sub>a max</sub> = 400 Nm</b>  |          |                                                |                                                                                      |       |    |      |                       |                                                                                       |
|------------------------------------|----------|------------------------------------------------|--------------------------------------------------------------------------------------|-------|----|------|-----------------------|---------------------------------------------------------------------------------------|
| <b>n<sub>a</sub></b><br><b>rpm</b> | <b>i</b> | <b>F<sub>Ra</sub><sup>1)</sup></b><br><b>N</b> |  |       |    |      | <b>m</b><br><b>kg</b> |  |
| 0.11                               | 12251    | 5920                                           | FA<br>FAF<br>F<br>FF                                                                 | 47R17 | DR | 63S4 | 24                    | 456                                                                                   |
| 0.13                               | 10619    | 5920                                           |                                                                                      |       |    |      |                       |                                                                                       |
| 0.14                               | 9846     | 5920                                           |                                                                                      |       |    |      |                       |                                                                                       |
| 0.16                               | 8534     | 5920                                           |                                                                                      |       |    |      |                       |                                                                                       |
| 0.19                               | 7460     | 5920                                           |                                                                                      |       |    |      |                       |                                                                                       |
| 0.21                               | 6536     | 5920                                           |                                                                                      |       |    |      |                       |                                                                                       |
| 0.24                               | 5746     | 5920                                           |                                                                                      |       |    |      |                       |                                                                                       |
| 0.27                               | 5022     | 5920                                           |                                                                                      |       |    |      |                       |                                                                                       |
| 0.31                               | 4401     | 5920                                           |                                                                                      |       |    |      |                       |                                                                                       |
| 0.36                               | 3883     | 5920                                           |                                                                                      |       |    |      |                       |                                                                                       |
| 0.40                               | 3443     | 5920                                           |                                                                                      |       |    |      |                       |                                                                                       |
| 0.46                               | 2976     | 5920                                           |                                                                                      |       |    |      |                       |                                                                                       |
| 0.52                               | 2629     | 5920                                           |                                                                                      |       |    |      |                       |                                                                                       |
| 0.55                               | 2519     | 5920                                           |                                                                                      |       |    |      |                       |                                                                                       |
| 0.58                               | 2394     | 5920                                           |                                                                                      |       |    |      |                       |                                                                                       |
| 0.64                               | 2172     | 5920                                           |                                                                                      |       |    |      |                       |                                                                                       |
| 0.68                               | 2025     | 5920                                           |                                                                                      |       |    |      |                       |                                                                                       |
| 0.78                               | 1770     | 5920                                           | FA                                                                                   | 47R17 | DR | 63S4 | 23                    | 456                                                                                   |
| 0.88                               | 1576     | 5920                                           | FAF                                                                                  | 47R17 | DR | 63S4 | 26                    | 456                                                                                   |
| 1.0                                | 1363     | 5920                                           | F                                                                                    | 47R17 | DR | 63S4 | 24                    | 456                                                                                   |
| 1.2                                | 1192     | 5920                                           | FF                                                                                   | 47R17 | DR | 63S4 | 27                    | 456                                                                                   |
| 1.3                                | 1061     | 5920                                           | FA<br>FAF<br>F<br>FF                                                                 | 47R17 | DR | 63M4 | 23                    | 456                                                                                   |
| 1.5                                | 931      | 5920                                           |                                                                                      |       |    |      |                       |                                                                                       |
| 1.7                                | 822      | 5920                                           |                                                                                      |       |    |      |                       |                                                                                       |
| 2.0                                | 706      | 5920                                           |                                                                                      |       |    |      |                       |                                                                                       |
| 2.2                                | 619      | 5920                                           |                                                                                      |       |    |      |                       |                                                                                       |
| 2.5                                | 524      | 5920                                           |                                                                                      |       |    |      |                       |                                                                                       |
| 2.7                                | 489      | 5920                                           |                                                                                      |       |    |      |                       |                                                                                       |
| 3.1                                | 427      | 5920                                           |                                                                                      |       |    |      |                       |                                                                                       |
| 3.5                                | 381      | 5920                                           |                                                                                      |       |    |      |                       |                                                                                       |
| 3.9                                | 334      | 5920                                           | FA                                                                                   | 47R17 | DR | 63L4 | 24                    | 456                                                                                   |
| 4.4                                | 295      | 5920                                           | FAF                                                                                  | 47R17 | DR | 63L4 | 26                    | 456                                                                                   |
| 5.1                                | 253      | 5920                                           | F                                                                                    | 47R17 | DR | 63L4 | 25                    | 456                                                                                   |
|                                    |          |                                                | FF                                                                                   | 47R17 | DR | 63L4 | 28                    | 456                                                                                   |





| <b>M<sub>a max</sub> = 400 Nm</b>  |          |                                                |                                                                                    |              |            |             |                       |                                                                                     |
|------------------------------------|----------|------------------------------------------------|------------------------------------------------------------------------------------|--------------|------------|-------------|-----------------------|-------------------------------------------------------------------------------------|
| <b>n<sub>a</sub></b><br><b>rpm</b> | <b>i</b> | <b>F<sub>Ra</sub><sup>1)</sup></b><br><b>N</b> |  |              |            |             | <b>m</b><br><b>kg</b> |  |
| <b>6.4</b>                         | 217      | 5920                                           | <b>FA</b>                                                                          | <b>47R17</b> | <b>DRS</b> | <b>71S4</b> | 26                    | 456                                                                                 |
| <b>7.3</b>                         | 190      | 5920                                           | <b>FAF</b>                                                                         | <b>47R17</b> | <b>DRS</b> | <b>71S4</b> | 28                    | 456                                                                                 |
| <b>7.8</b>                         | 178      | 5920                                           | <b>F</b>                                                                           | <b>47R17</b> | <b>DRS</b> | <b>71S4</b> | 26                    | 456                                                                                 |
|                                    |          |                                                | <b>FF</b>                                                                          | <b>47R17</b> | <b>DRS</b> | <b>71S4</b> | 30                    | 456                                                                                 |
| <b>9.1</b>                         | 149      | 5920                                           | <b>FA</b>                                                                          | <b>47R17</b> | <b>DRS</b> | <b>71M4</b> | 27                    | 456                                                                                 |
|                                    |          |                                                | <b>FAF</b>                                                                         | <b>47R17</b> | <b>DRS</b> | <b>71M4</b> | 30                    | 456                                                                                 |
| <b>10</b>                          | 131      | 5920                                           | <b>F</b>                                                                           | <b>47R17</b> | <b>DRS</b> | <b>71M4</b> | 28                    | 456                                                                                 |
|                                    |          |                                                | <b>FF</b>                                                                          | <b>47R17</b> | <b>DRS</b> | <b>71M4</b> | 31                    | 456                                                                                 |


| <b>M<sub>a max</sub> = 600 Nm</b>  |          |                                                |                                                                                    |              |            |             |                       |                                                                                     |
|------------------------------------|----------|------------------------------------------------|------------------------------------------------------------------------------------|--------------|------------|-------------|-----------------------|-------------------------------------------------------------------------------------|
| <b>n<sub>a</sub></b><br><b>rpm</b> | <b>i</b> | <b>F<sub>Ra</sub><sup>1)</sup></b><br><b>N</b> |  |              |            |             | <b>m</b><br><b>kg</b> |  |
| <b>0.09</b>                        | 14832    | 9200                                           |                                                                                    |              |            |             |                       |                                                                                     |
| <b>0.10</b>                        | 13604    | 9200                                           |                                                                                    |              |            |             |                       |                                                                                     |
| <b>0.11</b>                        | 12602    | 9200                                           |                                                                                    |              |            |             |                       |                                                                                     |
| <b>0.12</b>                        | 11252    | 9200                                           |                                                                                    |              |            |             |                       |                                                                                     |
| <b>0.14</b>                        | 9986     | 9200                                           |                                                                                    |              |            |             |                       |                                                                                     |
| <b>0.16</b>                        | 8787     | 9200                                           | <b>FA</b>                                                                          | <b>57R37</b> | <b>DR</b>  | <b>63S4</b> | 39                    | 456                                                                                 |
| <b>0.17</b>                        | 7908     | 9200                                           | <b>FAF</b>                                                                         | <b>57R37</b> | <b>DR</b>  | <b>63S4</b> | 45                    | 456                                                                                 |
| <b>0.20</b>                        | 6913     | 9200                                           | <b>F</b>                                                                           | <b>57R37</b> | <b>DR</b>  | <b>63S4</b> | 39                    | 456                                                                                 |
| <b>0.23</b>                        | 6030     | 9200                                           | <b>FF</b>                                                                          | <b>57R37</b> | <b>DR</b>  | <b>63S4</b> | 46                    | 456                                                                                 |
| <b>0.26</b>                        | 5289     | 9200                                           |                                                                                    |              |            |             |                       |                                                                                     |
| <b>0.30</b>                        | 4654     | 9200                                           |                                                                                    |              |            |             |                       |                                                                                     |
| <b>0.34</b>                        | 4060     | 9200                                           |                                                                                    |              |            |             |                       |                                                                                     |
| <b>0.39</b>                        | 3564     | 9200                                           |                                                                                    |              |            |             |                       |                                                                                     |
| <b>0.44</b>                        | 3161     | 9200                                           |                                                                                    |              |            |             |                       |                                                                                     |
| <b>0.48</b>                        | 2854     | 9200                                           |                                                                                    |              |            |             |                       |                                                                                     |
| <b>0.54</b>                        | 2576     | 9200                                           |                                                                                    |              |            |             |                       |                                                                                     |
| <b>0.61</b>                        | 2266     | 9200                                           |                                                                                    |              |            |             |                       |                                                                                     |
| <b>0.69</b>                        | 2012     | 9200                                           |                                                                                    |              |            |             |                       |                                                                                     |
| <b>0.77</b>                        | 1791     | 9200                                           | <b>FA</b>                                                                          | <b>57R37</b> | <b>DR</b>  | <b>63S4</b> | 39                    | 456                                                                                 |
| <b>0.85</b>                        | 1617     | 9200                                           | <b>FAF</b>                                                                         | <b>57R37</b> | <b>DR</b>  | <b>63S4</b> | 44                    | 456                                                                                 |
| <b>0.97</b>                        | 1422     | 9200                                           | <b>F</b>                                                                           | <b>57R37</b> | <b>DR</b>  | <b>63S4</b> | 39                    | 456                                                                                 |
| <b>1.1</b>                         | 1243     | 9200                                           | <b>FF</b>                                                                          | <b>57R37</b> | <b>DR</b>  | <b>63S4</b> | 45                    | 456                                                                                 |
| <b>1.3</b>                         | 1066     | 9200                                           |                                                                                    |              |            |             |                       |                                                                                     |
| <b>1.4</b>                         | 949      | 9200                                           |                                                                                    |              |            |             |                       |                                                                                     |
| <b>1.6</b>                         | 856      | 9200                                           |                                                                                    |              |            |             |                       |                                                                                     |
| <b>1.8</b>                         | 749      | 9200                                           | <b>FA</b>                                                                          | <b>57R37</b> | <b>DR</b>  | <b>63M4</b> | 39                    | 456                                                                                 |
| <b>2.0</b>                         | 658      | 9200                                           | <b>FAF</b>                                                                         | <b>57R37</b> | <b>DR</b>  | <b>63M4</b> | 44                    | 456                                                                                 |
| <b>2.4</b>                         | 549      | 9200                                           | <b>F</b>                                                                           | <b>57R37</b> | <b>DR</b>  | <b>63M4</b> | 39                    | 456                                                                                 |
|                                    |          |                                                | <b>FF</b>                                                                          | <b>57R37</b> | <b>DR</b>  | <b>63M4</b> | 45                    | 456                                                                                 |
| <b>2.7</b>                         | 483      | 9200                                           | <b>FA</b>                                                                          | <b>57R37</b> | <b>DR</b>  | <b>63L4</b> | 39                    | 456                                                                                 |
|                                    |          |                                                | <b>FAF</b>                                                                         | <b>57R37</b> | <b>DR</b>  | <b>63L4</b> | 45                    | 456                                                                                 |
|                                    |          |                                                | <b>F</b>                                                                           | <b>57R37</b> | <b>DR</b>  | <b>63L4</b> | 40                    | 456                                                                                 |
|                                    |          |                                                | <b>FF</b>                                                                          | <b>57R37</b> | <b>DR</b>  | <b>63L4</b> | 46                    | 456                                                                                 |
| <b>3.0</b>                         | 426      | 9200                                           | <b>FA</b>                                                                          | <b>57R37</b> | <b>DR</b>  | <b>63L4</b> | 39                    | 456                                                                                 |
| <b>3.4</b>                         | 382      | 9200                                           | <b>FAF</b>                                                                         | <b>57R37</b> | <b>DR</b>  | <b>63L4</b> | 45                    | 456                                                                                 |
|                                    |          |                                                | <b>F</b>                                                                           | <b>57R37</b> | <b>DR</b>  | <b>63L4</b> | 39                    | 456                                                                                 |
|                                    |          |                                                | <b>FF</b>                                                                          | <b>57R37</b> | <b>DR</b>  | <b>63L4</b> | 46                    | 456                                                                                 |
| <b>4.2</b>                         | 330      | 9200                                           | <b>FA</b>                                                                          | <b>57R37</b> | <b>DRS</b> | <b>71S4</b> | 41                    | 456                                                                                 |
| <b>4.6</b>                         | 298      | 9200                                           | <b>FAF</b>                                                                         | <b>57R37</b> | <b>DRS</b> | <b>71S4</b> | 47                    | 456                                                                                 |
| <b>5.3</b>                         | 262      | 9200                                           | <b>F</b>                                                                           | <b>57R37</b> | <b>DRS</b> | <b>71S4</b> | 41                    | 456                                                                                 |
|                                    |          |                                                | <b>FF</b>                                                                          | <b>57R37</b> | <b>DRS</b> | <b>71S4</b> | 48                    | 456                                                                                 |
| <b>6.0</b>                         | 226      | 9200                                           | <b>FA</b>                                                                          | <b>57R37</b> | <b>DRS</b> | <b>71M4</b> | 42                    | 456                                                                                 |
| <b>6.8</b>                         | 200      | 9200                                           | <b>FAF</b>                                                                         | <b>57R37</b> | <b>DRS</b> | <b>71M4</b> | 48                    | 456                                                                                 |
| <b>8.0</b>                         | 170      | 9200                                           | <b>F</b>                                                                           | <b>57R37</b> | <b>DRS</b> | <b>71M4</b> | 42                    | 456                                                                                 |
|                                    |          |                                                | <b>FF</b>                                                                          | <b>57R37</b> | <b>DRS</b> | <b>71M4</b> | 49                    | 456                                                                                 |
| <b>9.4</b>                         | 152      | 9200                                           | <b>FA</b>                                                                          | <b>57R37</b> | <b>DRN</b> | <b>80M4</b> | 47                    | 456                                                                                 |
| <b>11</b>                          | 134      | 9200                                           | <b>FAF</b>                                                                         | <b>57R37</b> | <b>DRN</b> | <b>80M4</b> | 52                    | 456                                                                                 |
|                                    |          |                                                | <b>F</b>                                                                           | <b>57R37</b> | <b>DRN</b> | <b>80M4</b> | 47                    | 456                                                                                 |
|                                    |          |                                                | <b>FF</b>                                                                          | <b>57R37</b> | <b>DRN</b> | <b>80M4</b> | 54                    | 456                                                                                 |


21933170/DE – 11/2015


| M <sub>a max</sub> = 820 Nm |       |                                    |                                                                                    |       |     |      |         |                                                                                     |
|-----------------------------|-------|------------------------------------|------------------------------------------------------------------------------------|-------|-----|------|---------|-------------------------------------------------------------------------------------|
| n <sub>a</sub><br>rpm       | i     | F <sub>Ra</sub> <sup>1)</sup><br>N |  |       |     |      | m<br>kg |  |
| 0.07                        | 19199 | 10300                              |                                                                                    |       |     |      |         |                                                                                     |
| 0.08                        | 17610 | 10300                              |                                                                                    |       |     |      |         |                                                                                     |
| 0.09                        | 14992 | 10300                              |                                                                                    |       |     |      |         |                                                                                     |
| 0.11                        | 12926 | 10300                              |                                                                                    |       |     |      |         |                                                                                     |
| 0.12                        | 11480 | 10300                              |                                                                                    |       |     |      |         |                                                                                     |
| 0.14                        | 10220 | 10300                              |                                                                                    |       |     |      |         |                                                                                     |
| 0.15                        | 8933  | 10300                              |                                                                                    |       |     |      |         |                                                                                     |
| 0.17                        | 7940  | 10300                              |                                                                                    |       |     |      |         |                                                                                     |
| 0.19                        | 7096  | 10300                              |                                                                                    |       |     |      |         |                                                                                     |
| 0.23                        | 6080  | 10300                              |                                                                                    |       |     |      |         |                                                                                     |
| 0.26                        | 5341  | 10300                              |                                                                                    |       |     |      |         |                                                                                     |
| 0.29                        | 4690  | 10300                              |                                                                                    |       |     |      |         |                                                                                     |
| 0.34                        | 4091  | 10300                              |                                                                                    |       |     |      |         |                                                                                     |
| 0.39                        | 3574  | 10300                              |                                                                                    |       |     |      |         |                                                                                     |
| 0.44                        | 3133  | 10300                              |                                                                                    |       |     |      |         |                                                                                     |
| 0.50                        | 2756  | 10300                              |                                                                                    |       |     |      |         |                                                                                     |
| 0.57                        | 2439  | 10300                              |                                                                                    |       |     |      |         |                                                                                     |
| 0.41                        | 3377  | 10300                              |                                                                                    |       |     |      |         |                                                                                     |
| 0.47                        | 2912  | 10300                              |                                                                                    |       |     |      |         |                                                                                     |
| 0.51                        | 2714  | 10300                              |                                                                                    |       |     |      |         |                                                                                     |
| 0.58                        | 2372  | 10300                              |                                                                                    |       |     |      |         |                                                                                     |
| 0.65                        | 2126  | 10300                              |                                                                                    |       |     |      |         |                                                                                     |
| 0.85                        | 1631  | 10300                              |                                                                                    |       |     |      |         |                                                                                     |
| 0.96                        | 1437  | 10300                              |                                                                                    |       |     |      |         |                                                                                     |
| 1.1                         | 1256  | 10300                              |                                                                                    |       |     |      |         |                                                                                     |
| 1.2                         | 1126  | 10300                              | FA                                                                                 | 67R37 | DR  | 63M4 | 42      | 456                                                                                 |
| 1.3                         | 984   | 10300                              | FAF                                                                                | 67R37 | DR  | 63M4 | 48      | 456                                                                                 |
| 1.5                         | 864   | 10300                              | F                                                                                  | 67R37 | DR  | 63M4 | 45      | 456                                                                                 |
|                             |       |                                    | FF                                                                                 | 67R37 | DR  | 63M4 | 51      | 456                                                                                 |
| 1.8                         | 722   | 10300                              | FA                                                                                 | 67R37 | DR  | 63L4 | 43      | 456                                                                                 |
| 2.0                         | 634   | 10300                              | FAF                                                                                | 67R37 | DR  | 63L4 | 49      | 456                                                                                 |
| 2.4                         | 539   | 10300                              | F                                                                                  | 67R37 | DR  | 63L4 | 46      | 456                                                                                 |
|                             |       |                                    | FF                                                                                 | 67R37 | DR  | 63L4 | 52      | 456                                                                                 |
| 0.73                        | 1884  | 10300                              | FA                                                                                 | 67R37 | DR  | 63S4 | 43      | 456                                                                                 |
|                             |       |                                    | FAF                                                                                | 67R37 | DR  | 63S4 | 49      | 456                                                                                 |
|                             |       |                                    | F                                                                                  | 67R37 | DR  | 63S4 | 46      | 456                                                                                 |
|                             |       |                                    | FF                                                                                 | 67R37 | DR  | 63S4 | 52      | 456                                                                                 |
| 2.6                         | 500   | 10300                              | FA                                                                                 | 67R37 | DR  | 63L4 | 42      | 456                                                                                 |
|                             |       |                                    | FAF                                                                                | 67R37 | DR  | 63L4 | 49      | 456                                                                                 |
|                             |       |                                    | F                                                                                  | 67R37 | DR  | 63L4 | 45      | 456                                                                                 |
|                             |       |                                    | FF                                                                                 | 67R37 | DR  | 63L4 | 51      | 456                                                                                 |
| 3.0                         | 454   | 10300                              | FA                                                                                 | 67R37 | DRS | 71S4 | 44      | 456                                                                                 |
| 3.5                         | 392   | 10300                              | FAF                                                                                | 67R37 | DRS | 71S4 | 51      | 456                                                                                 |
|                             |       |                                    | F                                                                                  | 67R37 | DRS | 71S4 | 47      | 456                                                                                 |
|                             |       |                                    | FF                                                                                 | 67R37 | DRS | 71S4 | 53      | 456                                                                                 |
| 4.1                         | 333   | 10300                              | FA                                                                                 | 67R37 | DRS | 71M4 | 46      | 456                                                                                 |
| 4.6                         | 297   | 10300                              | FAF                                                                                | 67R37 | DRS | 71M4 | 52      | 456                                                                                 |
| 5.2                         | 261   | 10300                              | F                                                                                  | 67R37 | DRS | 71M4 | 48      | 456                                                                                 |
| 5.7                         | 238   | 10300                              | FF                                                                                 | 67R37 | DRS | 71M4 | 54      | 456                                                                                 |
| 7.2                         | 200   | 10300                              | FA                                                                                 | 67R37 | DRN | 80M4 | 50      | 456                                                                                 |
|                             |       |                                    | FAF                                                                                | 67R37 | DRN | 80M4 | 57      | 456                                                                                 |
|                             |       |                                    | F                                                                                  | 67R37 | DRN | 80M4 | 53      | 456                                                                                 |
|                             |       |                                    | FF                                                                                 | 67R37 | DRN | 80M4 | 59      | 456                                                                                 |


| M <sub>a max</sub> = 1500 Nm |       |                                    |                                                                                    |       |     |      |         |                                                                                     |
|------------------------------|-------|------------------------------------|------------------------------------------------------------------------------------|-------|-----|------|---------|-------------------------------------------------------------------------------------|
| n <sub>a</sub><br>rpm        | i     | F <sub>Ra</sub> <sup>1)</sup><br>N |  |       |     |      | m<br>kg |  |
| 0.07                         | 19180 | 15700                              |                                                                                    |       |     |      |         |                                                                                     |
| 0.08                         | 17593 | 15700                              |                                                                                    |       |     |      |         |                                                                                     |
| 0.09                         | 16128 | 15700                              |                                                                                    |       |     |      |         |                                                                                     |
| 0.09                         | 14978 | 15700                              |                                                                                    |       |     |      |         |                                                                                     |
| 0.10                         | 13731 | 15700                              |                                                                                    |       |     |      |         |                                                                                     |
| 0.11                         | 12049 | 15700                              |                                                                                    |       |     |      |         |                                                                                     |
| 0.13                         | 11035 | 15700                              |                                                                                    |       |     |      |         |                                                                                     |
| 0.14                         | 9683  | 15700                              |                                                                                    |       |     |      |         |                                                                                     |
| 0.16                         | 8464  | 15700                              |                                                                                    |       |     |      |         |                                                                                     |
| 0.18                         | 7520  | 15700                              |                                                                                    |       |     |      |         |                                                                                     |
| 0.21                         | 6580  | 15700                              |                                                                                    |       |     |      |         |                                                                                     |
| 0.24                         | 5808  | 15700                              |                                                                                    |       |     |      |         |                                                                                     |
| 0.27                         | 5026  | 15700                              |                                                                                    |       |     |      |         |                                                                                     |
| 0.31                         | 4435  | 15700                              |                                                                                    |       |     |      |         |                                                                                     |
| 0.36                         | 3832  | 15700                              |                                                                                    |       |     |      |         |                                                                                     |
| 0.46                         | 2978  | 15700                              |                                                                                    |       |     |      |         |                                                                                     |
| 0.53                         | 2613  | 15700                              |                                                                                    |       |     |      |         |                                                                                     |
| 0.60                         | 2284  | 15700                              |                                                                                    |       |     |      |         |                                                                                     |
| 0.65                         | 2029  | 15700                              | FA                                                                                 | 77R37 | DR  | 63M4 | 65      | 456                                                                                 |
|                              |       |                                    | FAF                                                                                | 77R37 | DR  | 63M4 | 72      | 456                                                                                 |
|                              |       |                                    | F                                                                                  | 77R37 | DR  | 63M4 | 69      | 456                                                                                 |
|                              |       |                                    | FF                                                                                 | 77R37 | DR  | 63M4 | 80      | 456                                                                                 |
| 0.76                         | 1728  | 15700                              | FA                                                                                 | 77R37 | DR  | 63M4 | 65      | 456                                                                                 |
|                              |       |                                    | FAF                                                                                | 77R37 | DR  | 63M4 | 72      | 456                                                                                 |
|                              |       |                                    | F                                                                                  | 77R37 | DR  | 63M4 | 69      | 456                                                                                 |
|                              |       |                                    | FF                                                                                 | 77R37 | DR  | 63M4 | 80      | 456                                                                                 |
| 0.86                         | 1544  | 15700                              | FA                                                                                 | 77R37 | DR  | 63M4 | 65      | 456                                                                                 |
|                              |       |                                    | FAF                                                                                | 77R37 | DR  | 63M4 | 72      | 456                                                                                 |
|                              |       |                                    | F                                                                                  | 77R37 | DR  | 63M4 | 69      | 456                                                                                 |
|                              |       |                                    | FF                                                                                 | 77R37 | DR  | 63M4 | 80      | 456                                                                                 |
| 0.98                         | 1354  | 15700                              | FA                                                                                 | 77R37 | DR  | 63M4 | 65      | 456                                                                                 |
|                              |       |                                    | FAF                                                                                | 77R37 | DR  | 63M4 | 72      | 456                                                                                 |
|                              |       |                                    | F                                                                                  | 77R37 | DR  | 63M4 | 69      | 456                                                                                 |
|                              |       |                                    | FF                                                                                 | 77R37 | DR  | 63M4 | 80      | 456                                                                                 |
| 1.1                          | 1200  | 15700                              | FA                                                                                 | 77R37 | DR  | 63L4 | 66      | 456                                                                                 |
|                              |       |                                    | FAF                                                                                | 77R37 | DR  | 63L4 | 72      | 456                                                                                 |
|                              |       |                                    | F                                                                                  | 77R37 | DR  | 63L4 | 70      | 456                                                                                 |
|                              |       |                                    | FF                                                                                 | 77R37 | DR  | 63L4 | 80      | 456                                                                                 |
| 1.2                          | 1053  | 15700                              | FA                                                                                 | 77R37 | DR  | 63L4 | 66      | 456                                                                                 |
|                              |       |                                    | FAF                                                                                | 77R37 | DR  | 63L4 | 72      | 456                                                                                 |
|                              |       |                                    | F                                                                                  | 77R37 | DR  | 63L4 | 70      | 456                                                                                 |
|                              |       |                                    | FF                                                                                 | 77R37 | DR  | 63L4 | 80      | 456                                                                                 |
| 1.5                          | 910   | 15700                              | FA                                                                                 | 77R37 | DRS | 71S4 | 68      | 456                                                                                 |
|                              |       |                                    | FAF                                                                                | 77R37 | DRS | 71S4 | 74      | 456                                                                                 |
|                              |       |                                    | F                                                                                  | 77R37 | DRS | 71S4 | 72      | 456                                                                                 |
|                              |       |                                    | FF                                                                                 | 77R37 | DRS | 71S4 | 82      | 456                                                                                 |
| 1.7                          | 810   | 15700                              | FA                                                                                 | 77R37 | DRS | 71S4 | 68      | 456                                                                                 |
|                              |       |                                    | FAF                                                                                | 77R37 | DRS | 71S4 | 74      | 456                                                                                 |
|                              |       |                                    | F                                                                                  | 77R37 | DRS | 71S4 | 72      | 456                                                                                 |
|                              |       |                                    | FF                                                                                 | 77R37 | DRS | 71S4 | 82      | 456                                                                                 |
| 1.9                          | 710   | 15700                              | FA                                                                                 | 77R37 | DRS | 71S4 | 68      | 456                                                                                 |
|                              |       |                                    | FAF                                                                                | 77R37 | DRS | 71S4 | 74      | 456                                                                                 |
|                              |       |                                    | F                                                                                  | 77R37 | DRS | 71S4 | 72      | 456                                                                                 |
|                              |       |                                    | FF                                                                                 | 77R37 | DRS | 71S4 | 82      | 456                                                                                 |
| 2.2                          | 615   | 15700                              | FA                                                                                 | 77R37 | DRS | 71M4 | 69      | 456                                                                                 |
|                              |       |                                    | FAF                                                                                | 77R37 | DRS | 71M4 | 76      | 456                                                                                 |
|                              |       |                                    | F                                                                                  | 77R37 | DRS | 71M4 | 73      | 456                                                                                 |
|                              |       |                                    | FF                                                                                 | 77R37 | DRS | 71M4 | 83      | 456                                                                                 |
| 2.5                          | 538   | 15700                              | FA                                                                                 | 77R37 | DRS | 71M4 | 69      | 456                                                                                 |
|                              |       |                                    | FAF                                                                                | 77R37 | DRS | 71M4 | 76      | 456                                                                                 |
|                              |       |                                    | F                                                                                  | 77R37 | DRS | 71M4 | 73      | 456                                                                                 |
|                              |       |                                    | FF                                                                                 | 77R37 | DRS | 71M4 | 83      | 456                                                                                 |
| 2.8                          | 480   | 15700                              | FA                                                                                 | 77R37 | DRS | 71M4 | 69      | 456                                                                                 |
|                              |       |                                    | FAF                                                                                | 77R37 | DRS | 71M4 | 76      | 456                                                                                 |
|                              |       |                                    | F                                                                                  | 77R37 | DRS | 71M4 | 73      | 456                                                                                 |
|                              |       |                                    | FF                                                                                 | 77R37 | DRS | 71M4 | 83      | 456                                                                                 |
| 3.5                          | 413   | 15700                              | FA                                                                                 | 77R37 | DRN | 80M4 | 74      | 456                                                                                 |
|                              |       |                                    | FAF                                                                                | 77R37 | DRN | 80M4 | 80      | 456                                                                                 |
|                              |       |                                    | F                                                                                  | 77R37 | DRN | 80M4 | 77      | 456                                                                                 |
|                              |       |                                    | FF                                                                                 | 77R37 | DRN | 80M4 | 88      | 456                                                                                 |
| 3.9                          | 367   | 15700                              | FA                                                                                 | 77R37 | DRN | 80M4 | 74      | 456                                                                                 |
|                              |       |                                    | FAF                                                                                | 77R37 | DRN | 80M4 | 80      | 456                                                                                 |
|                              |       |                                    | F                                                                                  | 77R37 | DRN | 80M4 | 77      | 456                                                                                 |
|                              |       |                                    | FF                                                                                 | 77R37 | DRN | 80M4 | 88      | 456                                                                                 |
| 4.5                          | 323   | 15700                              | FA                                                                                 | 77R37 | DRN | 90S4 | 80      | 456                                                                                 |
|                              |       |                                    | FAF                                                                                | 77R37 | DRN | 90S4 | 86      | 456                                                                                 |
|                              |       |                                    | F                                                                                  | 77R37 | DRN | 90S4 | 83      | 456                                                                                 |
|                              |       |                                    | FF                                                                                 | 77R37 | DRN | 90S4 | 94      | 456                                                                                 |


| M <sub>a max</sub> = 3000 Nm |       |                                    |                                                                                      |  |  |  |         |                                                                                       |
|------------------------------|-------|------------------------------------|--------------------------------------------------------------------------------------|--|--|--|---------|---------------------------------------------------------------------------------------|
| n <sub>a</sub><br>rpm        | i     | F <sub>Ra</sub> <sup>1)</sup><br>N |  |  |  |  | m<br>kg |  |
| 0.06                         | 23042 | 19800                              |                                                                                      |  |  |  |         |                                                                                       |
| 0.07                         | 20462 | 19800                              |                                                                                      |  |  |  |         |                                                                                       |
| 0.08                         | 18238 | 19800                              |                                                                                      |  |  |  |         |                                                                                       |
| 0.09                         | 15877 | 19800                              |                                                                                      |  |  |  |         |                                                                                       |
| 0.10                         | 14099 | 19800                              |                                                                                      |  |  |  |         |                                                                                       |
| 0.11                         | 12205 | 19800                              |                                                                                      |  |  |  |         |                                                                                       |
| 0.13                         | 10433 | 19800                              |                                                                                      |  |  |  |         |                                                                                       |
| 0.15                         | 9381  | 19800                              |                                                                                      |  |  |  |         |                                                                                       |
| 0.17                         | 8142  | 19800                              |                                                                                      |  |  |  |         |                                                                                       |
| 0.19                         | 7100  | 19800                              |                                                                                      |  |  |  |         |                                                                                       |
| 0.22                         | 6273  | 19800                              |                                                                                      |  |  |  |         |                                                                                       |
| 0.25                         | 5510  | 19800                              |                                                                                      |  |  |  |         |                                                                                       |
| 0.28                         | 4954  | 19800                              |                                                                                      |  |  |  |         |                                                                                       |


| <b>M<sub>a max</sub> = 3000 Nm</b>                   |          |                                         |                                                                                    |              |            |             |                |                                                                                     |
|------------------------------------------------------|----------|-----------------------------------------|------------------------------------------------------------------------------------|--------------|------------|-------------|----------------|-------------------------------------------------------------------------------------|
| <b>n<sub>a</sub></b><br>rpm                          | <b>i</b> | <b>F<sub>Ra</sub><sup>1)</sup></b><br>N |  |              |            |             | <b>m</b><br>kg |  |
| <b>0.31</b><br><b>0.35</b>                           | 4245     | 19800                                   | <b>FA</b>                                                                          | <b>87R57</b> | <b>DR</b>  | <b>63M4</b> | 120            | 456                                                                                 |
|                                                      | 3721     | 19800                                   | <b>FAF</b>                                                                         | <b>87R57</b> | <b>DR</b>  | <b>63M4</b> | 130            | 456                                                                                 |
|                                                      |          |                                         | <b>F</b>                                                                           | <b>87R57</b> | <b>DR</b>  | <b>63M4</b> | 125            | 456                                                                                 |
|                                                      |          |                                         | <b>FF</b>                                                                          | <b>87R57</b> | <b>DR</b>  | <b>63M4</b> | 140            | 456                                                                                 |
| <b>0.41</b><br><b>0.46</b>                           | 3244     | 19800                                   | <b>FA</b>                                                                          | <b>87R57</b> | <b>DR</b>  | <b>63M4</b> | 115            | 456                                                                                 |
|                                                      | 2881     | 19800                                   | <b>FAF</b>                                                                         | <b>87R57</b> | <b>DR</b>  | <b>63M4</b> | 130            | 456                                                                                 |
|                                                      |          |                                         | <b>F</b>                                                                           | <b>87R57</b> | <b>DR</b>  | <b>63M4</b> | 125            | 456                                                                                 |
|                                                      |          |                                         | <b>FF</b>                                                                          | <b>87R57</b> | <b>DR</b>  | <b>63M4</b> | 140            | 456                                                                                 |
| <b>0.50</b><br><b>0.59</b><br><b>0.67</b>            | 2576     | 19800                                   | <b>FA</b>                                                                          | <b>87R57</b> | <b>DR</b>  | <b>63L4</b> | 120            | 456                                                                                 |
|                                                      | 2199     | 19800                                   | <b>FAF</b>                                                                         | <b>87R57</b> | <b>DR</b>  | <b>63L4</b> | 130            | 456                                                                                 |
|                                                      | 1930     | 19800                                   | <b>F</b>                                                                           | <b>87R57</b> | <b>DR</b>  | <b>63L4</b> | 125            | 456                                                                                 |
|                                                      |          |                                         | <b>FF</b>                                                                          | <b>87R57</b> | <b>DR</b>  | <b>63L4</b> | 140            | 456                                                                                 |
| <b>0.81</b><br><b>0.92</b>                           | 1709     | 19800                                   | <b>FA</b>                                                                          | <b>87R57</b> | <b>DRS</b> | <b>71S4</b> | 120            | 456                                                                                 |
|                                                      | 1493     | 19800                                   | <b>FAF</b>                                                                         | <b>87R57</b> | <b>DRS</b> | <b>71S4</b> | 130            | 456                                                                                 |
|                                                      |          |                                         | <b>F</b>                                                                           | <b>87R57</b> | <b>DRS</b> | <b>71S4</b> | 125            | 456                                                                                 |
|                                                      |          |                                         | <b>FF</b>                                                                          | <b>87R57</b> | <b>DRS</b> | <b>71S4</b> | 140            | 456                                                                                 |
| <b>1.0</b><br><b>1.2</b><br><b>1.4</b><br><b>1.5</b> | 1300     | 19800                                   | <b>FA</b>                                                                          | <b>87R57</b> | <b>DRS</b> | <b>71M4</b> | 120            | 456                                                                                 |
|                                                      | 1148     | 19800                                   | <b>FAF</b>                                                                         | <b>87R57</b> | <b>DRS</b> | <b>71M4</b> | 135            | 456                                                                                 |
|                                                      | 1010     | 19800                                   | <b>F</b>                                                                           | <b>87R57</b> | <b>DRS</b> | <b>71M4</b> | 125            | 456                                                                                 |
|                                                      | 887      | 19800                                   | <b>FF</b>                                                                          | <b>87R57</b> | <b>DRS</b> | <b>71M4</b> | 140            | 456                                                                                 |
| <b>1.8</b><br><b>2.1</b>                             | 780      | 19800                                   | <b>FA</b>                                                                          | <b>87R57</b> | <b>DRN</b> | <b>80M4</b> | 125            | 456                                                                                 |
|                                                      | 674      | 19800                                   | <b>FAF</b>                                                                         | <b>87R57</b> | <b>DRN</b> | <b>80M4</b> | 140            | 456                                                                                 |
|                                                      |          |                                         | <b>F</b>                                                                           | <b>87R57</b> | <b>DRN</b> | <b>80M4</b> | 130            | 456                                                                                 |
|                                                      |          |                                         | <b>FF</b>                                                                          | <b>87R57</b> | <b>DRN</b> | <b>80M4</b> | 145            | 456                                                                                 |
| <b>2.4</b><br><b>2.8</b><br><b>3.2</b>               | 609      | 19800                                   | <b>FA</b>                                                                          | <b>87R57</b> | <b>DRN</b> | <b>90S4</b> | 130            | 456                                                                                 |
|                                                      | 515      | 19800                                   | <b>FAF</b>                                                                         | <b>87R57</b> | <b>DRN</b> | <b>90S4</b> | 145            | 456                                                                                 |
|                                                      | 452      | 19800                                   | <b>F</b>                                                                           | <b>87R57</b> | <b>DRN</b> | <b>90S4</b> | 140            | 456                                                                                 |
|                                                      |          |                                         | <b>FF</b>                                                                          | <b>87R57</b> | <b>DRN</b> | <b>90S4</b> | 155            | 456                                                                                 |
| <b>4.2</b>                                           | 345      | 19800                                   | <b>FA</b>                                                                          | <b>87R57</b> | <b>DRN</b> | <b>90L4</b> | 135            | 456                                                                                 |
|                                                      |          |                                         | <b>FAF</b>                                                                         | <b>87R57</b> | <b>DRN</b> | <b>90L4</b> | 150            | 456                                                                                 |
|                                                      |          |                                         | <b>F</b>                                                                           | <b>87R57</b> | <b>DRN</b> | <b>90L4</b> | 140            | 456                                                                                 |
|                                                      |          |                                         | <b>FF</b>                                                                          | <b>87R57</b> | <b>DRN</b> | <b>90L4</b> | 155            | 456                                                                                 |


| <b>M<sub>a max</sub> = 4300 Nm</b>        |          |                                         |                                                                                      |              |            |             |                |                                                                                       |
|-------------------------------------------|----------|-----------------------------------------|--------------------------------------------------------------------------------------|--------------|------------|-------------|----------------|---------------------------------------------------------------------------------------|
| <b>n<sub>a</sub></b><br>rpm               | <b>i</b> | <b>F<sub>Ra</sub><sup>1)</sup></b><br>N |  |              |            |             | <b>m</b><br>kg |  |
| <b>0.07</b>                               | 20813    | 29900                                   | <b>FA</b><br><b>FAF</b><br><b>F</b><br><b>FF</b>                                     | <b>97R57</b> | <b>DR</b>  | <b>63S4</b> | 185            | 456                                                                                   |
| <b>0.08</b>                               | 18119    | 29900                                   |                                                                                      | <b>97R57</b> | <b>DR</b>  | <b>63S4</b> | 205            | 456                                                                                   |
| <b>0.09</b>                               | 15472    | 29900                                   |                                                                                      | <b>97R57</b> | <b>DR</b>  | <b>63S4</b> | 190            | 456                                                                                   |
| <b>0.10</b>                               | 14022    | 29900                                   |                                                                                      | <b>97R57</b> | <b>DR</b>  | <b>63S4</b> | 225            | 456                                                                                   |
| <b>0.11</b>                               | 12324    | 29900                                   |                                                                                      | <b>97R57</b> | <b>DR</b>  | <b>63S4</b> |                |                                                                                       |
| <b>0.13</b>                               | 10838    | 29900                                   |                                                                                      | <b>97R57</b> | <b>DR</b>  | <b>63S4</b> |                |                                                                                       |
| <b>0.14</b>                               | 9576     | 29900                                   |                                                                                      | <b>97R57</b> | <b>DR</b>  | <b>63S4</b> |                |                                                                                       |
| <b>0.17</b>                               | 8318     | 29900                                   |                                                                                      | <b>97R57</b> | <b>DR</b>  | <b>63S4</b> |                |                                                                                       |
| <b>0.19</b>                               | 7328     | 29900                                   |                                                                                      | <b>97R57</b> | <b>DR</b>  | <b>63S4</b> |                |                                                                                       |
| <b>0.20</b>                               | 6469     | 29900                                   | <b>FA</b>                                                                            | <b>97R57</b> | <b>DR</b>  | <b>63M4</b> | 185            | 456                                                                                   |
| <b>0.24</b>                               | 5615     | 29900                                   | <b>FAF</b>                                                                           | <b>97R57</b> | <b>DR</b>  | <b>63M4</b> | 205            | 456                                                                                   |
| <b>0.27</b>                               | 4961     | 29900                                   | <b>F</b>                                                                             | <b>97R57</b> | <b>DR</b>  | <b>63M4</b> | 190            | 456                                                                                   |
| <b>0.30</b>                               | 4333     | 29900                                   | <b>FF</b>                                                                            | <b>97R57</b> | <b>DR</b>  | <b>63M4</b> | 225            | 456                                                                                   |
| <b>0.34</b>                               | 3906     | 29900                                   | <b>FA</b>                                                                            | <b>97R57</b> | <b>DR</b>  | <b>63M4</b> | 185            | 456                                                                                   |
|                                           |          |                                         | <b>FAF</b>                                                                           | <b>97R57</b> | <b>DR</b>  | <b>63M4</b> | 205            | 456                                                                                   |
|                                           |          |                                         | <b>F</b>                                                                             | <b>97R57</b> | <b>DR</b>  | <b>63M4</b> | 190            | 456                                                                                   |
|                                           |          |                                         | <b>FF</b>                                                                            | <b>97R57</b> | <b>DR</b>  | <b>63M4</b> | 225            | 456                                                                                   |
| <b>0.39</b><br><b>0.45</b>                | 3352     | 29900                                   | <b>FA</b>                                                                            | <b>97R57</b> | <b>DR</b>  | <b>63L4</b> | 185            | 456                                                                                   |
|                                           | 2907     | 29900                                   | <b>FAF</b>                                                                           | <b>97R57</b> | <b>DR</b>  | <b>63L4</b> | 205            | 456                                                                                   |
|                                           |          |                                         | <b>F</b>                                                                             | <b>97R57</b> | <b>DR</b>  | <b>63L4</b> | 190            | 456                                                                                   |
|                                           |          |                                         | <b>FF</b>                                                                            | <b>97R57</b> | <b>DR</b>  | <b>63L4</b> | 225            | 456                                                                                   |
| <b>0.54</b><br><b>0.61</b><br><b>0.70</b> | 2553     | 29900                                   | <b>FA</b>                                                                            | <b>97R57</b> | <b>DRS</b> | <b>71S4</b> | 185            | 456                                                                                   |
|                                           | 2245     | 29900                                   | <b>FAF</b>                                                                           | <b>97R57</b> | <b>DRS</b> | <b>71S4</b> | 205            | 456                                                                                   |
|                                           | 1970     | 29900                                   | <b>F</b>                                                                             | <b>97R57</b> | <b>DRS</b> | <b>71S4</b> | 190            | 456                                                                                   |
|                                           |          |                                         | <b>FF</b>                                                                            | <b>97R57</b> | <b>DRS</b> | <b>71S4</b> | 225            | 456                                                                                   |


| <b>M<sub>a max</sub> = 4300 Nm</b> |          |                                         |                                                                                    |       |     |        |                |                                                                                     |
|------------------------------------|----------|-----------------------------------------|------------------------------------------------------------------------------------|-------|-----|--------|----------------|-------------------------------------------------------------------------------------|
| <b>n<sub>a</sub></b><br>rpm        | <b>i</b> | <b>F<sub>Ra</sub><sup>1)</sup></b><br>N |  |       |     |        | <b>m</b><br>kg |  |
| 0.79                               | 1722     | 29900                                   | FA                                                                                 | 97R57 | DRS | 71M4   | 185            | 456                                                                                 |
| 0.89                               | 1527     | 29900                                   | FAF                                                                                | 97R57 | DRS | 71M4   | 210            | 456                                                                                 |
| 1.0                                | 1327     | 29900                                   | F                                                                                  | 97R57 | DRS | 71M4   | 195            | 456                                                                                 |
|                                    |          |                                         | FF                                                                                 | 97R57 | DRS | 71M4   | 225            | 456                                                                                 |
| 1.2                                | 1171     | 29900                                   | FA                                                                                 | 97R57 | DRN | 80M4   | 190            | 456                                                                                 |
| 1.4                                | 1022     | 29900                                   | FAF                                                                                | 97R57 | DRN | 80M4   | 215            | 456                                                                                 |
|                                    |          |                                         | F                                                                                  | 97R57 | DRN | 80M4   | 200            | 456                                                                                 |
|                                    |          |                                         | FF                                                                                 | 97R57 | DRN | 80M4   | 230            | 456                                                                                 |
| 1.6                                | 898      | 29900                                   | FA                                                                                 | 97R57 | DRN | 90S4   | 195            | 456                                                                                 |
| 1.8                                | 784      | 29900                                   | FAF                                                                                | 97R57 | DRN | 90S4   | 220            | 456                                                                                 |
| 2.1                                | 690      | 29900                                   | F                                                                                  | 97R57 | DRN | 90S4   | 205            | 456                                                                                 |
|                                    |          |                                         | FF                                                                                 | 97R57 | DRN | 90S4   | 240            | 456                                                                                 |
| 2.4                                | 605      | 29900                                   | FA                                                                                 | 97R57 | DRN | 90L4   | 200            | 456                                                                                 |
| 2.8                                | 529      | 29900                                   | FAF                                                                                | 97R57 | DRN | 90L4   | 220            | 456                                                                                 |
|                                    |          |                                         | F                                                                                  | 97R57 | DRN | 90L4   | 210            | 456                                                                                 |
|                                    |          |                                         | FF                                                                                 | 97R57 | DRN | 90L4   | 240            | 456                                                                                 |
| 3.1                                | 467      | 29900                                   | FA                                                                                 | 97R57 | DRN | 100LS4 | 205            | 456                                                                                 |
| 3.6                                | 406      | 29900                                   | FAF                                                                                | 97R57 | DRN | 100LS4 | 225            | 456                                                                                 |
| 4.0                                | 363      | 29900                                   | F                                                                                  | 97R57 | DRN | 100LS4 | 210            | 456                                                                                 |
|                                    |          |                                         | FF                                                                                 | 97R57 | DRN | 100LS4 | 245            | 456                                                                                 |
| 5.1                                | 285      | 29900                                   | FA                                                                                 | 97R57 | DRN | 100L4  | 210            | 456                                                                                 |
| 6.0                                | 245      | 29900                                   | FAF                                                                                | 97R57 | DRN | 100L4  | 235            | 456                                                                                 |
|                                    |          |                                         | F                                                                                  | 97R57 | DRN | 100L4  | 220            | 456                                                                                 |
|                                    |          |                                         | FF                                                                                 | 97R57 | DRN | 100L4  | 250            | 456                                                                                 |

| <b>M<sub>a max</sub> = 7680 Nm</b> |          |                                         |                                                                                      |        |     |      |                |                                                                                       |
|------------------------------------|----------|-----------------------------------------|--------------------------------------------------------------------------------------|--------|-----|------|----------------|---------------------------------------------------------------------------------------|
| <b>n<sub>a</sub></b><br>rpm        | <b>i</b> | <b>F<sub>Ra</sub><sup>1)</sup></b><br>N |  |        |     |      | <b>m</b><br>kg |  |
| 0.05                               | 25375    | 49800                                   | FA                                                                                   | 107R77 | DR  | 63S4 | 275            | 456                                                                                   |
| 0.06                               | 21652    | 49800                                   | FAF                                                                                  | 107R77 | DR  | 63S4 | 295            | 456                                                                                   |
| 0.07                               | 18933    | 49800                                   | F                                                                                    | 107R77 | DR  | 63S4 | 290            | 456                                                                                   |
| 0.08                               | 16888    | 49800                                   | FF                                                                                   | 107R77 | DR  | 63S4 | 320            | 456                                                                                   |
| 0.09                               | 14767    | 49800                                   |                                                                                      |        |     |      |                |                                                                                       |
| 0.12                               | 11348    | 49800                                   | FA                                                                                   | 107R77 | DR  | 63M4 | 275            | 456                                                                                   |
| 0.13                               | 10039    | 49800                                   | FAF                                                                                  | 107R77 | DR  | 63M4 | 295            | 456                                                                                   |
| 0.15                               | 8548     | 49800                                   | F                                                                                    | 107R77 | DR  | 63M4 | 290            | 456                                                                                   |
| 0.17                               | 7674     | 49800                                   | FF                                                                                   | 107R77 | DR  | 63M4 | 320            | 456                                                                                   |
| 0.19                               | 6767     | 49800                                   | FA                                                                                   | 107R77 | DR  | 63L4 | 275            | 456                                                                                   |
| 0.22                               | 5954     | 49800                                   | FAF                                                                                  | 107R77 | DR  | 63L4 | 295            | 456                                                                                   |
| 0.25                               | 5223     | 49800                                   | F                                                                                    | 107R77 | DR  | 63L4 | 290            | 456                                                                                   |
|                                    |          |                                         | FF                                                                                   | 107R77 | DR  | 63L4 | 320            | 456                                                                                   |
| 0.30                               | 4567     | 49800                                   | FA                                                                                   | 107R77 | DRS | 71S4 | 275            | 456                                                                                   |
| 0.39                               | 3521     | 49800                                   | FAF                                                                                  | 107R77 | DRS | 71S4 | 300            | 456                                                                                   |
|                                    |          |                                         | F                                                                                    | 107R77 | DRS | 71S4 | 295            | 456                                                                                   |
|                                    |          |                                         | FF                                                                                   | 107R77 | DRS | 71S4 | 320            | 456                                                                                   |
| 0.45                               | 3037     | 49800                                   | FA                                                                                   | 107R77 | DRS | 71M4 | 275            | 456                                                                                   |
| 0.49                               | 2756     | 49800                                   | FAF                                                                                  | 107R77 | DRS | 71M4 | 300            | 456                                                                                   |
| 0.57                               | 2369     | 49800                                   | F                                                                                    | 107R77 | DRS | 71M4 | 295            | 456                                                                                   |
|                                    |          |                                         | FF                                                                                   | 107R77 | DRS | 71M4 | 320            | 456                                                                                   |
| 0.70                               | 2068     | 49800                                   | FA                                                                                   | 107R77 | DRN | 80M4 | 280            | 456                                                                                   |
| 0.79                               | 1826     | 49800                                   | FAF                                                                                  | 107R77 | DRN | 80M4 | 305            | 456                                                                                   |
|                                    |          |                                         | F                                                                                    | 107R77 | DRN | 80M4 | 300            | 456                                                                                   |
|                                    |          |                                         | FF                                                                                   | 107R77 | DRN | 80M4 | 325            | 456                                                                                   |
| 0.91                               | 1597     | 49800                                   | FA                                                                                   | 107R77 | DRN | 90S4 | 285            | 456                                                                                   |
| 1.0                                | 1401     | 49800                                   | FAF                                                                                  | 107R77 | DRN | 90S4 | 310            | 456                                                                                   |
| 1.2                                | 1243     | 49800                                   | F                                                                                    | 107R77 | DRN | 90S4 | 305            | 456                                                                                   |
|                                    |          |                                         | FF                                                                                   | 107R77 | DRN | 90S4 | 330            | 456                                                                                   |
| 1.3                                | 1087     | 49800                                   | FA                                                                                   | 107R77 | DRN | 90L4 | 290            | 456                                                                                   |
| 1.5                                | 950      | 49800                                   | FAF                                                                                  | 107R77 | DRN | 90L4 | 310            | 456                                                                                   |
|                                    |          |                                         | F                                                                                    | 107R77 | DRN | 90L4 | 305            | 456                                                                                   |
|                                    |          |                                         | FF                                                                                   | 107R77 | DRN | 90L4 | 335            | 456                                                                                   |


| <b>M<sub>a max</sub> = 7680 Nm</b> |          |                                         |                                                                                    |        |     |        |                |                                                                                     |
|------------------------------------|----------|-----------------------------------------|------------------------------------------------------------------------------------|--------|-----|--------|----------------|-------------------------------------------------------------------------------------|
| <b>n<sub>a</sub></b><br>rpm        | <b>i</b> | <b>F<sub>Ra</sub><sup>1)</sup></b><br>N |  |        |     |        | <b>m</b><br>kg |  |
| 1.7                                | 834      | 49800                                   | FA                                                                                 | 107R77 | DRN | 100LS4 | 295            | 456                                                                                 |
| 2.0                                | 736      | 49800                                   | FAF                                                                                | 107R77 | DRN | 100LS4 | 315            | 456                                                                                 |
| 2.3                                | 640      | 49800                                   | F                                                                                  | 107R77 | DRN | 100LS4 | 310            | 456                                                                                 |
|                                    |          |                                         | FF                                                                                 | 107R77 | DRN | 100LS4 | 340            | 456                                                                                 |
| 2.6                                | 560      | 49800                                   | FA                                                                                 | 107R77 | DRN | 100L4  | 300            | 456                                                                                 |
| 3.0                                | 489      | 49800                                   | FAF                                                                                | 107R77 | DRN | 100L4  | 325            | 456                                                                                 |
| 3.3                                | 436      | 49800                                   | F                                                                                  | 107R77 | DRN | 100L4  | 320            | 456                                                                                 |
|                                    |          |                                         | FF                                                                                 | 107R77 | DRN | 100L4  | 345            | 456                                                                                 |
| 4.0                                | 370      | 49800                                   | FA                                                                                 | 107R77 | DRN | 112M4  | 310            | 456                                                                                 |
| 4.4                                | 333      | 49800                                   | FAF                                                                                | 107R77 | DRN | 112M4  | 330            | 456                                                                                 |
|                                    |          |                                         | F                                                                                  | 107R77 | DRN | 112M4  | 325            | 456                                                                                 |
|                                    |          |                                         | FF                                                                                 | 107R77 | DRN | 112M4  | 355            | 456                                                                                 |

| <b>M<sub>a max</sub> = 12000 Nm</b> |          |                                         |                                                                                    |        |     |        |                |                                                                                     |
|-------------------------------------|----------|-----------------------------------------|------------------------------------------------------------------------------------|--------|-----|--------|----------------|-------------------------------------------------------------------------------------|
| <b>n<sub>a</sub></b><br>rpm         | <b>i</b> | <b>F<sub>Ra</sub><sup>1)</sup></b><br>N |  |        |     |        | <b>m</b><br>kg |  |
| 0.06                                | 24478    | 90000                                   | FA                                                                                 | 127R77 | DR  | 63S4   | 425            | 456                                                                                 |
| 0.06                                | 22323    | 90000                                   | FAF                                                                                | 127R77 | DR  | 63S4   | 465            | 456                                                                                 |
|                                     |          |                                         | F                                                                                  | 127R77 | DR  | 63S4   | 460            | 456                                                                                 |
|                                     |          |                                         | FF                                                                                 | 127R77 | DR  | 63S4   | 510            | 456                                                                                 |
| 0.07                                | 19048    | 90000                                   | FA                                                                                 | 127R77 | DR  | 63M4   | 425            | 456                                                                                 |
| 0.08                                | 16656    | 90000                                   | FAF                                                                                | 127R77 | DR  | 63M4   | 465            | 456                                                                                 |
| 0.09                                | 14722    | 90000                                   | F                                                                                  | 127R77 | DR  | 63M4   | 460            | 456                                                                                 |
| 0.10                                | 12912    | 90000                                   | FF                                                                                 | 127R77 | DR  | 63M4   | 510            | 456                                                                                 |
| 0.11                                | 11656    | 90000                                   |                                                                                    |        |     |        |                |                                                                                     |
| 0.13                                | 10191    | 90000                                   | FA                                                                                 | 127R77 | DR  | 63L4   | 425            | 456                                                                                 |
| 0.15                                | 8831     | 90000                                   | FAF                                                                                | 127R77 | DR  | 63L4   | 465            | 456                                                                                 |
|                                     |          |                                         | F                                                                                  | 127R77 | DR  | 63L4   | 465            | 456                                                                                 |
|                                     |          |                                         | FF                                                                                 | 127R77 | DR  | 63L4   | 510            | 456                                                                                 |
| 0.18                                | 7643     | 90000                                   | FA                                                                                 | 127R77 | DRS | 71S4   | 430            | 456                                                                                 |
| 0.21                                | 6715     | 90000                                   | FAF                                                                                | 127R77 | DRS | 71S4   | 465            | 456                                                                                 |
| 0.23                                | 5925     | 90000                                   | F                                                                                  | 127R77 | DRS | 71S4   | 465            | 456                                                                                 |
|                                     |          |                                         | FF                                                                                 | 127R77 | DRS | 71S4   | 510            | 456                                                                                 |
| 0.26                                | 5153     | 90000                                   | FA                                                                                 | 127R77 | DRS | 71M4   | 430            | 456                                                                                 |
| 0.30                                | 4533     | 90000                                   | FAF                                                                                | 127R77 | DRS | 71M4   | 465            | 456                                                                                 |
| 0.35                                | 3926     | 90000                                   | F                                                                                  | 127R77 | DRS | 71M4   | 465            | 456                                                                                 |
|                                     |          |                                         | FF                                                                                 | 127R77 | DRS | 71M4   | 510            | 456                                                                                 |
| 0.42                                | 3454     | 90000                                   | FA                                                                                 | 127R77 | DRN | 80M4   | 435            | 456                                                                                 |
| 0.48                                | 3031     | 90000                                   | FAF                                                                                | 127R77 | DRN | 80M4   | 470            | 456                                                                                 |
|                                     |          |                                         | F                                                                                  | 127R77 | DRN | 80M4   | 470            | 456                                                                                 |
|                                     |          |                                         | FF                                                                                 | 127R77 | DRN | 80M4   | 520            | 456                                                                                 |
| 0.54                                | 2672     | 90000                                   | FA                                                                                 | 127R77 | DRN | 80M4   | 435            | 456                                                                                 |
|                                     |          |                                         | FAF                                                                                | 127R77 | DRN | 80M4   | 470            | 456                                                                                 |
|                                     |          |                                         | F                                                                                  | 127R77 | DRN | 80M4   | 470            | 456                                                                                 |
|                                     |          |                                         | FF                                                                                 | 127R77 | DRN | 80M4   | 510            | 456                                                                                 |
| 0.62                                | 2357     | 90000                                   | FA                                                                                 | 127R77 | DRN | 90S4   | 440            | 456                                                                                 |
| 0.71                                | 2038     | 90000                                   | FAF                                                                                | 127R77 | DRN | 90S4   | 475            | 456                                                                                 |
|                                     |          |                                         | F                                                                                  | 127R77 | DRN | 90S4   | 475            | 456                                                                                 |
|                                     |          |                                         | FF                                                                                 | 127R77 | DRN | 90S4   | 520            | 456                                                                                 |
| 0.82                                | 1784     | 90000                                   | FA                                                                                 | 127R77 | DRN | 90L4   | 440            | 456                                                                                 |
| 0.91                                | 1606     | 90000                                   | FAF                                                                                | 127R77 | DRN | 90L4   | 480            | 456                                                                                 |
| 1.0                                 | 1390     | 90000                                   | F                                                                                  | 127R77 | DRN | 90L4   | 480            | 456                                                                                 |
|                                     |          |                                         | FF                                                                                 | 127R77 | DRN | 90L4   | 520            | 456                                                                                 |
| 1.2                                 | 1220     | 90000                                   | FA                                                                                 | 127R77 | DRN | 100LS4 | 445            | 456                                                                                 |
| 1.4                                 | 1077     | 90000                                   | FAF                                                                                | 127R77 | DRN | 100LS4 | 485            | 456                                                                                 |
| 1.6                                 | 930      | 90000                                   | F                                                                                  | 127R77 | DRN | 100LS4 | 480            | 456                                                                                 |
|                                     |          |                                         | FF                                                                                 | 127R77 | DRN | 100LS4 | 530            | 456                                                                                 |
| 1.8                                 | 820      | 90000                                   | FA                                                                                 | 127R77 | DRN | 100L4  | 455            | 456                                                                                 |
| 2.0                                 | 727      | 90000                                   | FAF                                                                                | 127R77 | DRN | 100L4  | 490            | 456                                                                                 |
|                                     |          |                                         | F                                                                                  | 127R77 | DRN | 100L4  | 490            | 456                                                                                 |
|                                     |          |                                         | FF                                                                                 | 127R77 | DRN | 100L4  | 530            | 456                                                                                 |

| <b>M<sub>a max</sub> = 12000 Nm</b> |     |                                    |                                                                                    |        |     |       |         |                                                                                     |
|-------------------------------------|-----|------------------------------------|------------------------------------------------------------------------------------|--------|-----|-------|---------|-------------------------------------------------------------------------------------|
| n <sub>a</sub><br>rpm               | i   | F <sub>Ra</sub> <sup>1)</sup><br>N |  |        |     |       | m<br>kg |  |
| 2.3                                 | 648 | 90000                              | FA                                                                                 | 127R77 | DRN | 112M4 | 460     | 456                                                                                 |
| 2.7                                 | 549 | 90000                              | FAF                                                                                | 127R77 | DRN | 112M4 | 500     | 456                                                                                 |
| 3.0                                 | 495 | 90000                              | F                                                                                  | 127R77 | DRN | 112M4 | 500     | 456                                                                                 |
|                                     |     |                                    | FF                                                                                 | 127R77 | DRN | 112M4 | 540     | 456                                                                                 |
| 3.4                                 | 428 | 90000                              | FA                                                                                 | 127R77 | DRN | 132S4 | 475     | 456                                                                                 |
|                                     |     |                                    | FAF                                                                                | 127R77 | DRN | 132S4 | 510     | 456                                                                                 |
| 3.9                                 | 376 | 90000                              | F                                                                                  | 127R77 | DRN | 132S4 | 510     | 456                                                                                 |
|                                     |     |                                    | FF                                                                                 | 127R77 | DRN | 132S4 | 550     | 456                                                                                 |
| 3.0                                 | 483 | 90000                              | FA                                                                                 | 127R87 | DRN | 132S4 | 495     | 456                                                                                 |
| 3.5                                 | 418 | 90000                              | FAF                                                                                | 127R87 | DRN | 132S4 | 530     | 456                                                                                 |
| 3.9                                 | 374 | 90000                              | F                                                                                  | 127R87 | DRN | 132S4 | 530     | 456                                                                                 |
|                                     |     |                                    | FF                                                                                 | 127R87 | DRN | 132S4 | 570     | 456                                                                                 |
| 4.7                                 | 312 | 90000                              | FA                                                                                 | 127R87 | DRN | 132M4 | 510     | 456                                                                                 |
|                                     |     |                                    | FAF                                                                                | 127R87 | DRN | 132M4 | 550     | 456                                                                                 |
| 5.0                                 | 293 | 90000                              | F                                                                                  | 127R87 | DRN | 132M4 | 550     | 456                                                                                 |
|                                     |     |                                    | FF                                                                                 | 127R87 | DRN | 132M4 | 590     | 456                                                                                 |
| 5.7                                 | 259 | 90000                              | FA                                                                                 | 127R87 | DRN | 132L4 | 520     | 456                                                                                 |
|                                     |     |                                    | FAF                                                                                | 127R87 | DRN | 132L4 | 560     | 456                                                                                 |
| 6.6                                 | 223 | 90000                              | F                                                                                  | 127R87 | DRN | 132L4 | 560     | 456                                                                                 |
|                                     |     |                                    | FF                                                                                 | 127R87 | DRN | 132L4 | 600     | 456                                                                                 |
| 7.5                                 | 198 | 90000                              | FA                                                                                 | 127R87 | DRN | 160M4 | 550     | 456                                                                                 |
|                                     |     |                                    | FAF                                                                                | 127R87 | DRN | 160M4 | 590     | 456                                                                                 |
|                                     |     |                                    | F                                                                                  | 127R87 | DRN | 160M4 | 590     | 456                                                                                 |
|                                     |     |                                    | FF                                                                                 | 127R87 | DRN | 160M4 | 630     | 456                                                                                 |

| <b>M<sub>a max</sub> = 18000 Nm</b> |       |                                    |                                                                                      |        |     |        |         |                                                                                       |
|-------------------------------------|-------|------------------------------------|--------------------------------------------------------------------------------------|--------|-----|--------|---------|---------------------------------------------------------------------------------------|
| n <sub>a</sub><br>rpm               | i     | F <sub>Ra</sub> <sup>1)</sup><br>N |  |        |     |        | m<br>kg |  |
| 0.04                                | 31434 | 100300                             |                                                                                      |        |     |        |         |                                                                                       |
| 0.05                                | 26173 | 100300                             |                                                                                      |        |     |        |         |                                                                                       |
| 0.06                                | 23464 | 100300                             | FA                                                                                   | 157R97 | DRS | 71M4   | 770     | 456                                                                                   |
| 0.07                                | 20212 | 100300                             | FAF                                                                                  | 157R97 | DRS | 71M4   | 830     | 456                                                                                   |
| 0.08                                | 17984 | 100300                             | F                                                                                    | 157R97 | DRS | 71M4   | 790     | 456                                                                                   |
| 0.08                                | 16358 | 100300                             | FF                                                                                   | 157R97 | DRS | 71M4   | 900     | 456                                                                                   |
| 0.10                                | 13751 | 100300                             |                                                                                      |        |     |        |         |                                                                                       |
| 0.11                                | 12235 | 100300                             |                                                                                      |        |     |        |         |                                                                                       |
| 0.14                                | 10033 | 100300                             | FA                                                                                   | 157R97 | DRN | 80M4   | 770     | 456                                                                                   |
| 0.16                                | 9021  | 100300                             | FAF                                                                                  | 157R97 | DRN | 80M4   | 830     | 456                                                                                   |
| 0.18                                | 8026  | 100300                             | F                                                                                    | 157R97 | DRN | 80M4   | 790     | 456                                                                                   |
|                                     |       |                                    | FF                                                                                   | 157R97 | DRN | 80M4   | 900     | 456                                                                                   |
| 0.19                                | 7075  | 100300                             | FA                                                                                   | 157R97 | DRS | 71M4   | 770     | 456                                                                                   |
|                                     |       |                                    | FAF                                                                                  | 157R97 | DRS | 71M4   | 830     | 456                                                                                   |
| 0.22                                | 6295  | 100300                             | F                                                                                    | 157R97 | DRS | 71M4   | 790     | 456                                                                                   |
|                                     |       |                                    | FF                                                                                   | 157R97 | DRS | 71M4   | 900     | 456                                                                                   |
| 0.27                                | 5404  | 100300                             | FA                                                                                   | 157R97 | DRN | 80M4   | 770     | 456                                                                                   |
|                                     |       |                                    | FAF                                                                                  | 157R97 | DRN | 80M4   | 830     | 456                                                                                   |
| 0.30                                | 4831  | 100300                             | F                                                                                    | 157R97 | DRN | 80M4   | 790     | 456                                                                                   |
|                                     |       |                                    | FF                                                                                   | 157R97 | DRN | 80M4   | 900     | 456                                                                                   |
| 0.35                                | 4130  | 100300                             | FA                                                                                   | 157R97 | DRN | 90S4   | 780     | 456                                                                                   |
|                                     |       |                                    | FAF                                                                                  | 157R97 | DRN | 90S4   | 840     | 456                                                                                   |
|                                     |       |                                    | F                                                                                    | 157R97 | DRN | 90S4   | 800     | 456                                                                                   |
|                                     |       |                                    | FF                                                                                   | 157R97 | DRN | 90S4   | 900     | 456                                                                                   |
| 0.40                                | 3607  | 100300                             | FA                                                                                   | 157R97 | DRN | 100LS4 | 780     | 456                                                                                   |
|                                     |       |                                    | FAF                                                                                  | 157R97 | DRN | 100LS4 | 840     | 456                                                                                   |
| 0.45                                | 3210  | 100300                             | F                                                                                    | 157R97 | DRN | 100LS4 | 810     | 456                                                                                   |
|                                     |       |                                    | FF                                                                                   | 157R97 | DRN | 100LS4 | 910     | 456                                                                                   |
| 0.53                                | 2780  | 100300                             | FA                                                                                   | 157R97 | DRN | 90L4   | 780     | 456                                                                                   |
|                                     |       |                                    | FAF                                                                                  | 157R97 | DRN | 90L4   | 840     | 456                                                                                   |
|                                     |       |                                    | F                                                                                    | 157R97 | DRN | 90L4   | 800     | 456                                                                                   |
|                                     |       |                                    | FF                                                                                   | 157R97 | DRN | 90L4   | 910     | 456                                                                                   |





| <b>M<sub>a max</sub> = 18000 Nm</b>    |          |                                                |                                                                                    |               |            |               |                       |                                                                                     |
|----------------------------------------|----------|------------------------------------------------|------------------------------------------------------------------------------------|---------------|------------|---------------|-----------------------|-------------------------------------------------------------------------------------|
| <b>n<sub>a</sub></b><br><b>rpm</b>     | <b>i</b> | <b>F<sub>Ra</sub><sup>1)</sup></b><br><b>N</b> |  |               |            |               | <b>m</b><br><b>kg</b> |  |
| <b>1.0</b>                             | 1441     | 100300                                         | <b>FA</b>                                                                          | <b>157R97</b> | <b>DRN</b> | <b>100LS4</b> | 780                   | 456                                                                                 |
|                                        |          |                                                | <b>FAF</b>                                                                         | <b>157R97</b> | <b>DRN</b> | <b>100LS4</b> | 840                   | 456                                                                                 |
|                                        |          |                                                | <b>F</b>                                                                           | <b>157R97</b> | <b>DRN</b> | <b>100LS4</b> | 810                   | 456                                                                                 |
|                                        |          |                                                | <b>FF</b>                                                                          | <b>157R97</b> | <b>DRN</b> | <b>100LS4</b> | 910                   | 456                                                                                 |
| <b>0.60</b><br><b>0.67</b>             | 2427     | 100300                                         | <b>FA</b>                                                                          | <b>157R97</b> | <b>DRN</b> | <b>90L4</b>   | 780                   | 456                                                                                 |
|                                        | 2185     | 100300                                         | <b>FAF</b>                                                                         | <b>157R97</b> | <b>DRN</b> | <b>90L4</b>   | 840                   | 456                                                                                 |
|                                        |          |                                                | <b>F</b>                                                                           | <b>157R97</b> | <b>DRN</b> | <b>90L4</b>   | 800                   | 456                                                                                 |
|                                        |          |                                                | <b>FF</b>                                                                          | <b>157R97</b> | <b>DRN</b> | <b>90L4</b>   | 900                   | 456                                                                                 |
| <b>0.75</b><br><b>0.87</b>             | 1944     | 100300                                         | <b>FA</b>                                                                          | <b>157R97</b> | <b>DRN</b> | <b>100LS4</b> | 780                   | 456                                                                                 |
|                                        | 1674     | 100300                                         | <b>FAF</b>                                                                         | <b>157R97</b> | <b>DRN</b> | <b>100LS4</b> | 840                   | 456                                                                                 |
|                                        |          |                                                | <b>F</b>                                                                           | <b>157R97</b> | <b>DRN</b> | <b>100LS4</b> | 800                   | 456                                                                                 |
|                                        |          |                                                | <b>FF</b>                                                                          | <b>157R97</b> | <b>DRN</b> | <b>100LS4</b> | 910                   | 456                                                                                 |
| <b>1.1</b><br><b>1.2</b>               | 1308     | 100300                                         | <b>FA</b>                                                                          | <b>157R97</b> | <b>DRN</b> | <b>100L4</b>  | 790                   | 456                                                                                 |
|                                        | 1169     | 100300                                         | <b>FAF</b>                                                                         | <b>157R97</b> | <b>DRN</b> | <b>100L4</b>  | 850                   | 456                                                                                 |
|                                        |          |                                                | <b>F</b>                                                                           | <b>157R97</b> | <b>DRN</b> | <b>100L4</b>  | 810                   | 456                                                                                 |
|                                        |          |                                                | <b>FF</b>                                                                          | <b>157R97</b> | <b>DRN</b> | <b>100L4</b>  | 920                   | 456                                                                                 |
| <b>1.5</b><br><b>1.7</b><br><b>1.9</b> | 953      | 100300                                         | <b>FA</b>                                                                          | <b>157R97</b> | <b>DRN</b> | <b>112M4</b>  | 800                   | 456                                                                                 |
|                                        | 845      | 100300                                         | <b>FAF</b>                                                                         | <b>157R97</b> | <b>DRN</b> | <b>112M4</b>  | 860                   | 456                                                                                 |
|                                        | 764      | 100300                                         | <b>F</b>                                                                           | <b>157R97</b> | <b>DRN</b> | <b>112M4</b>  | 820                   | 456                                                                                 |
|                                        |          |                                                | <b>FF</b>                                                                          | <b>157R97</b> | <b>DRN</b> | <b>112M4</b>  | 920                   | 456                                                                                 |
| <b>2.2</b><br><b>2.5</b>               | 680      | 100300                                         | <b>FA</b>                                                                          | <b>157R97</b> | <b>DRN</b> | <b>132S4</b>  | 810                   | 456                                                                                 |
|                                        | 576      | 100300                                         | <b>FAF</b>                                                                         | <b>157R97</b> | <b>DRN</b> | <b>132S4</b>  | 870                   | 456                                                                                 |
|                                        |          |                                                | <b>F</b>                                                                           | <b>157R97</b> | <b>DRN</b> | <b>132S4</b>  | 830                   | 456                                                                                 |
|                                        |          |                                                | <b>FF</b>                                                                          | <b>157R97</b> | <b>DRN</b> | <b>132S4</b>  | 940                   | 456                                                                                 |
| <b>2.9</b><br><b>3.3</b>               | 503      | 100300                                         | <b>FA</b>                                                                          | <b>157R97</b> | <b>DRN</b> | <b>132M4</b>  | 830                   | 456                                                                                 |
|                                        | 446      | 100300                                         | <b>FAF</b>                                                                         | <b>157R97</b> | <b>DRN</b> | <b>132M4</b>  | 890                   | 456                                                                                 |
|                                        |          |                                                | <b>F</b>                                                                           | <b>157R97</b> | <b>DRN</b> | <b>132M4</b>  | 850                   | 456                                                                                 |
|                                        |          |                                                | <b>FF</b>                                                                          | <b>157R97</b> | <b>DRN</b> | <b>132M4</b>  | 950                   | 456                                                                                 |
| <b>4.2</b>                             | 353      | 100300                                         | <b>FA</b>                                                                          | <b>157R97</b> | <b>DRN</b> | <b>132L4</b>  | 840                   | 456                                                                                 |
|                                        |          |                                                | <b>FAF</b>                                                                         | <b>157R97</b> | <b>DRN</b> | <b>132L4</b>  | 890                   | 456                                                                                 |
|                                        |          |                                                | <b>F</b>                                                                           | <b>157R97</b> | <b>DRN</b> | <b>132L4</b>  | 860                   | 456                                                                                 |
|                                        |          |                                                | <b>FF</b>                                                                          | <b>157R97</b> | <b>DRN</b> | <b>132L4</b>  | 960                   | 456                                                                                 |
| <b>4.9</b><br><b>5.4</b>               | 302      | 100300                                         | <b>FA</b>                                                                          | <b>157R97</b> | <b>DRN</b> | <b>160M4</b>  | 870                   | 456                                                                                 |
|                                        | 273      | 100300                                         | <b>FAF</b>                                                                         | <b>157R97</b> | <b>DRN</b> | <b>160M4</b>  | 930                   | 456                                                                                 |
|                                        |          |                                                | <b>F</b>                                                                           | <b>157R97</b> | <b>DRN</b> | <b>160M4</b>  | 890                   | 456                                                                                 |
|                                        |          |                                                | <b>FF</b>                                                                          | <b>157R97</b> | <b>DRN</b> | <b>160M4</b>  | 1000                  | 456                                                                                 |
| <b>6.4</b><br><b>7.3</b>               | 232      | 100300                                         | <b>FA</b>                                                                          | <b>157R97</b> | <b>DRN</b> | <b>160L4</b>  | 880                   | 456                                                                                 |
|                                        | 202      | 100300                                         | <b>FAF</b>                                                                         | <b>157R97</b> | <b>DRN</b> | <b>160L4</b>  | 940                   | 456                                                                                 |
|                                        |          |                                                | <b>F</b>                                                                           | <b>157R97</b> | <b>DRN</b> | <b>160L4</b>  | 900                   | 456                                                                                 |
|                                        |          |                                                | <b>FF</b>                                                                          | <b>157R97</b> | <b>DRN</b> | <b>160L4</b>  | 1010                  | 456                                                                                 |
| <b>7.5</b>                             | 197      | 100300                                         | <b>FA</b>                                                                          | <b>157R97</b> | <b>DRN</b> | <b>180M4</b>  | 910                   | 456                                                                                 |
|                                        |          |                                                | <b>FAF</b>                                                                         | <b>157R97</b> | <b>DRN</b> | <b>180M4</b>  | 960                   | 456                                                                                 |
|                                        |          |                                                | <b>F</b>                                                                           | <b>157R97</b> | <b>DRN</b> | <b>180M4</b>  | 930                   | 456                                                                                 |
|                                        |          |                                                | <b>FF</b>                                                                          | <b>157R97</b> | <b>DRN</b> | <b>180M4</b>  | 1030                  | 456                                                                                 |




9.5 Maßblätter F..DRN.. in mm

42 020 00 14


**F27..**




**FA27B..**



**FH27B..**  
max. DR71..



**FV27B..**






21933170/DE – 11/2015

| (→ 155) | DR63.. | DR71S | DR71M | DRN80M | DRN90S | DRN90L |  |  |
|---------|--------|-------|-------|--------|--------|--------|--|--|
| AC      | 132    | 139   | 139   | 156    | 179    | 179    |  |  |
| AD      | 105    | 119   | 119   | 128    | 140    | 140    |  |  |
| ADS     | 105    | 129   | 129   | 139    | 150    | 150    |  |  |
| L       | 337    | 348   | 373   | 428    | 429    | 461    |  |  |
| LS      | 392    | 416   | 441   | 509    | 523    | 555    |  |  |
| LB      | 191    | 202   | 227   | 282    | 283    | 315    |  |  |
| LBS     | 246    | 270   | 295   | 363    | 377    | 409    |  |  |



**FA27..**







42 022 00 14



**FA27..**









**FH27..**  
max. DR71..

**FV27..**



| (→ 155) | DR63.. | DR71S | DR71M | DRN80M | DRN90S | DRN90L |  |  |
|---------|--------|-------|-------|--------|--------|--------|--|--|
| AC      | 132    | 139   | 139   | 156    | 179    | 179    |  |  |
| AD      | 105    | 119   | 119   | 128    | 140    | 140    |  |  |
| ADS     | 105    | 129   | 129   | 139    | 150    | 150    |  |  |
| L       | 286    | 297   | 322   | 377    | 378    | 410    |  |  |
| LS      | 341    | 365   | 390   | 458    | 472    | 504    |  |  |
| LB      | 191    | 202   | 227   | 282    | 283    | 315    |  |  |
| LBS     | 246    | 270   | 295   | 363    | 377    | 409    |  |  |

42 023 00 14


**FAZ27..****FAZ27..****FHZ27..**  
max. DR71..**FVZ27..**

| (→ 155) | DR63.. | DR71S | DR71M | DRN80M | DRN90S | DRN90L |  |  |
|---------|--------|-------|-------|--------|--------|--------|--|--|
| AC      | 132    | 139   | 139   | 156    | 179    | 179    |  |  |
| AD      | 105    | 119   | 119   | 128    | 140    | 140    |  |  |
| ADS     | 105    | 129   | 129   | 139    | 150    | 150    |  |  |
| L       | 286    | 297   | 322   | 377    | 378    | 410    |  |  |
| LS      | 341    | 365   | 390   | 458    | 472    | 504    |  |  |
| LB      | 191    | 202   | 227   | 282    | 283    | 315    |  |  |
| LBS     | 246    | 270   | 295   | 363    | 377    | 409    |  |  |




42 024 00 14


**F37..**




**FA37B..**



**FH37B..**




**FV37B..**



| (→ 155) | DR63.. | DR71S | DR71M | DRN80M | DRN90S | DRN90L | DRN100LS | DRN100L |
|---------|--------|-------|-------|--------|--------|--------|----------|---------|
| AC      | 132    | 139   | 139   | 156    | 179    | 179    | 197      | 197     |
| AD      | 105    | 119   | 119   | 128    | 140    | 140    | 157      | 157     |
| ADS     | 105    | 129   | 129   | 139    | 150    | 150    | 158      | 158     |
| L       | 351    | 362   | 387   | 442    | 443    | 475    | 474      | 524     |
| LS      | 406    | 430   | 455   | 523    | 537    | 569    | 568      | 618     |
| LB      | 191    | 202   | 227   | 282    | 283    | 315    | 314      | 364     |
| LBS     | 246    | 270   | 295   | 363    | 377    | 409    | 408      | 458     |

## 9










**FZ37..**




42 072 00 15




| (  155) | DR63.. | DR71S | DR71M | DRN80M | DRN90S | DRN90L | DRN100LS | DRN100L |
|--------------------------------------------------------------------------------------------|--------|-------|-------|--------|--------|--------|----------|---------|
| AC                                                                                         | 132    | 139   | 139   | 156    | 179    | 179    | 197      | 197     |
| AD                                                                                         | 105    | 119   | 119   | 128    | 140    | 140    | 157      | 157     |
| ADS                                                                                        | 105    | 129   | 129   | 139    | 150    | 150    | 158      | 158     |
| L                                                                                          | 360    | 371   | 396   | 451    | 452    | 484    | 483      | 533     |
| LS                                                                                         | 415    | 439   | 464   | 532    | 546    | 578    | 577      | 627     |
| LB                                                                                         | 191    | 202   | 227   | 282    | 283    | 315    | 314      | 364     |
| LBS                                                                                        | 246    | 270   | 295   | 363    | 377    | 409    | 408      | 458     |




**F47..**

402


## 9

21933170/DE – 11/2015


## FA47..




42 031 00 14




## FA47..



## FH47..





## FV47..



| (→ 155) | DR63.. | DR71S | DR71M | DRN80M | DRN90S | DRN90L | DRN100LS | DRN100L |
|---------|--------|-------|-------|--------|--------|--------|----------|---------|
| AC      | 132    | 139   | 139   | 156    | 179    | 179    | 197      | 197     |
| AD      | 105    | 119   | 119   | 128    | 140    | 140    | 157      | 157     |
| ADS     | 105    | 129   | 129   | 139    | 150    | 150    | 158      | 158     |
| L       | 324    | 335   | 360   | 415    | 416    | 448    | 447      | 497     |
| LS      | 379    | 403   | 428   | 496    | 510    | 542    | 541      | 591     |
| LB      | 191    | 202   | 227   | 282    | 283    | 315    | 314      | 364     |
| LBS     | 246    | 270   | 295   | 363    | 377    | 409    | 408      | 458     |

**FAZ47..**




42 032 00 14



**FAZ47..**

**FHZ47..**


**FVZ47..**



| (→ 155) | DR63.. | DR71S | DR71M | DRN80M | DRN90S | DRN90L | DRN100LS | DRN100L |
|---------|--------|-------|-------|--------|--------|--------|----------|---------|
| AC      | 132    | 139   | 139   | 156    | 179    | 179    | 197      | 197     |
| AD      | 105    | 119   | 119   | 128    | 140    | 140    | 157      | 157     |
| ADS     | 105    | 129   | 129   | 139    | 150    | 150    | 158      | 158     |
| L       | 335    | 346   | 371   | 426    | 427    | 459    | 458      | 508     |
| LS      | 390    | 414   | 439   | 507    | 521    | 553    | 552      | 602     |
| LB      | 191    | 202   | 227   | 282    | 283    | 315    | 314      | 364     |
| LBS     | 246    | 270   | 295   | 363    | 377    | 409    | 408      | 458     |

## FZ47..

42 073 00 15








| (→ 155) | DR63.. | DR71S | DR71M | DRN80M | DRN90S | DRN90L | DRN100LS | DRN100L |
|---------|--------|-------|-------|--------|--------|--------|----------|---------|
| AC      | 132    | 139   | 139   | 156    | 179    | 179    | 197      | 197     |
| AD      | 105    | 119   | 119   | 128    | 140    | 140    | 157      | 157     |
| ADS     | 105    | 129   | 129   | 139    | 150    | 150    | 158      | 158     |
| L       | 392    | 403   | 428   | 483    | 484    | 516    | 515      | 565     |
| LS      | 447    | 471   | 496   | 564    | 578    | 610    | 609      | 659     |
| LB      | 191    | 202   | 227   | 282    | 283    | 315    | 314      | 364     |
| LBS     | 246    | 270   | 295   | 363    | 377    | 409    | 408      | 458     |



**FT47..**

42 033 00 14




9

21933170/DE – 11/2015


| (→ 155) | DR63.. | DR71S | DR71M |  |  |  |  |
|---------|--------|-------|-------|--|--|--|--|
| AC      | 132    | 139   | 139   |  |  |  |  |
| AD      | 105    | 119   | 119   |  |  |  |  |
| ADS     | 105    | 129   | 129   |  |  |  |  |
| L       | 343    | 354   | 379   |  |  |  |  |
| LS      | 398    | 422   | 447   |  |  |  |  |
| LB      | 191    | 202   | 227   |  |  |  |  |
| LBS     | 246    | 270   | 295   |  |  |  |  |

42 034 00 14


**F57..**




**FA57B..**



**FH57B..**  
**max. DRN100L**





**FV57B..**



| (→ 155) | DR63.. | DR71S | DR71M | DRN80M | DRN90S | DRN90L | DRN100LS | DRN100L | DRN112M | DRN132S |
|---------|--------|-------|-------|--------|--------|--------|----------|---------|---------|---------|
| AC      | 132    | 139   | 139   | 156    | 179    | 179    | 197      | 197     | 221     | 221     |
| AD      | 105    | 119   | 119   | 128    | 140    | 140    | 157      | 157     | 170     | 170     |
| ADS     | 105    | 129   | 129   | 139    | 150    | 150    | 158      | 158     | 172     | 172     |
| L       | 406    | 417   | 442   | 496    | 498    | 530    | 526      | 576     | 607     | 661     |
| LS      | 461    | 485   | 510   | 577    | 591    | 623    | 620      | 670     | 719     | 773     |
| LB      | 185    | 196   | 221   | 275    | 277    | 309    | 305      | 355     | 386     | 440     |
| LBS     | 240    | 264   | 289   | 356    | 370    | 402    | 399      | 449     | 498     | 552     |

## 9



| (→ 155) | DR63.. | DR71S | DR71M | DRN80M | DRN90S | DRN90L | DRN100LS | DRN100L | DRN112M | DRN132S |
|---------|--------|-------|-------|--------|--------|--------|----------|---------|---------|---------|
| AC      | 132    | 139   | 139   | 156    | 179    | 179    | 197      | 197     | 221     | 221     |
| AD      | 105    | 119   | 119   | 128    | 140    | 140    | 157      | 157     | 170     | 170     |
| ADS     | 105    | 129   | 129   | 139    | 150    | 150    | 158      | 158     | 172     | 172     |
| L       | 428    | 439   | 464   | 518    | 520    | 552    | 548      | 598     | 629     | 683     |
| LS      | 483    | 507   | 532   | 599    | 613    | 645    | 642      | 692     | 741     | 795     |
| LB      | 185    | 196   | 221   | 275    | 277    | 309    | 305      | 355     | 386     | 440     |
| LBS     | 240    | 264   | 289   | 356    | 370    | 402    | 399      | 449     | 498     | 552     |



| (→ 155) | DR63.. | DR71S | DR71M | DRN80M | DRN90S | DRN90L | DRN100LS | DRN100L | DRN112M | DRN132S |
|---------|--------|-------|-------|--------|--------|--------|----------|---------|---------|---------|
| AC      | 132    | 139   | 139   | 156    | 179    | 179    | 197      | 197     | 221     | 221     |
| AD      | 105    | 119   | 119   | 128    | 140    | 140    | 157      | 157     | 170     | 170     |
| ADS     | 105    | 129   | 129   | 139    | 150    | 150    | 158      | 158     | 172     | 172     |
| L       | 335    | 346   | 371   | 425    | 427    | 459    | 455      | 505     | 536     | 590     |
| LS      | 390    | 414   | 439   | 506    | 520    | 552    | 549      | 599     | 648     | 702     |
| LB      | 185    | 196   | 221   | 275    | 277    | 309    | 305      | 355     | 386     | 440     |
| LBS     | 240    | 264   | 289   | 356    | 370    | 402    | 399      | 449     | 498     | 552     |

**FAZ57..**




42 037 00 14



**FAZ57..**

**FHZ57..**  
max. DRN100L


**FVZ57..**



| (→ 155) | DR63.. | DR71S | DR71M | DRN80M | DRN90S | DRN90L | DRN100LS | DRN100L | DRN112M | DRN132S |
|---------|--------|-------|-------|--------|--------|--------|----------|---------|---------|---------|
| AC      | 132    | 139   | 139   | 156    | 179    | 179    | 197      | 197     | 221     | 221     |
| AD      | 105    | 119   | 119   | 128    | 140    | 140    | 157      | 157     | 170     | 170     |
| ADS     | 105    | 129   | 129   | 139    | 150    | 150    | 158      | 158     | 172     | 172     |
| L       | 347    | 358   | 383   | 437    | 439    | 471    | 467      | 517     | 548     | 602     |
| LS      | 402    | 426   | 451   | 518    | 532    | 564    | 561      | 611     | 660     | 714     |
| LB      | 185    | 196   | 221   | 275    | 277    | 309    | 305      | 355     | 386     | 440     |
| LBS     | 240    | 264   | 289   | 356    | 370    | 402    | 399      | 449     | 498     | 552     |

**FZ57..**





42 074 00 15



| (→ 155) | DR63.. | DR71S | DR71M | DRN80M | DRN90S | DRN90L | DRN100LS | DRN100L | DRN112M | DRN132S |
|---------|--------|-------|-------|--------|--------|--------|----------|---------|---------|---------|
| AC      | 132    | 139   | 139   | 156    | 179    | 179    | 197      | 197     | 221     | 221     |
| AD      | 105    | 119   | 119   | 128    | 140    | 140    | 157      | 157     | 170     | 170     |
| ADS     | 105    | 129   | 129   | 139    | 150    | 150    | 158      | 158     | 172     | 172     |
| L       | 413    | 424   | 449   | 504    | 505    | 537    | 534      | 584     | 615     | 669     |
| LS      | 468    | 492   | 517   | 585    | 599    | 631    | 627      | 677     | 727     | 781     |
| LB      | 185    | 196   | 221   | 275    | 277    | 309    | 305      | 355     | 386     | 440     |
| LBS     | 240    | 264   | 289   | 356    | 370    | 402    | 399      | 449     | 498     | 552     |



42 039 00 14


**F67..****FA67B..****FH67B..**  
max. DR132S**FV67B..**

| (→ 155) | DR63.. | DR71S | DR71M | DRN80M | DRN90S | DRN90L | DRN100LS | DRN100L | DRN112M | DRN132S |
|---------|--------|-------|-------|--------|--------|--------|----------|---------|---------|---------|
| AC      | 132    | 139   | 139   | 156    | 179    | 179    | 197      | 197     | 221     | 221     |
| AD      | 105    | 119   | 119   | 128    | 140    | 140    | 157      | 157     | 170     | 170     |
| ADS     | 105    | 129   | 129   | 139    | 150    | 150    | 158      | 158     | 172     | 172     |
| L       | 427    | 438   | 463   | 517    | 519    | 551    | 547      | 597     | 628     | 682     |
| LS      | 482    | 506   | 531   | 598    | 612    | 644    | 641      | 691     | 740     | 794     |
| LB      | 185    | 196   | 221   | 275    | 277    | 309    | 305      | 355     | 386     | 440     |
| LBS     | 240    | 264   | 289   | 356    | 370    | 402    | 399      | 449     | 498     | 552     |



# FF67..


42 040 00 14




# FAF67..

# FHF67.. max. DR132S





# FVF67..



| (→ 155) | DR63.. | DR71S | DR71M | DRN80M | DRN90S | DRN90L | DRN100LS | DRN100L | DRN112M | DRN132S |
|---------|--------|-------|-------|--------|--------|--------|----------|---------|---------|---------|
| AC      | 132    | 139   | 139   | 156    | 179    | 179    | 197      | 197     | 221     | 221     |
| AD      | 105    | 119   | 119   | 128    | 140    | 140    | 157      | 157     | 170     | 170     |
| ADS     | 105    | 129   | 129   | 139    | 150    | 150    | 158      | 158     | 172     | 172     |
| L       | 449    | 460   | 485   | 539    | 541    | 573    | 569      | 619     | 650     | 704     |
| LS      | 504    | 528   | 553   | 620    | 634    | 666    | 663      | 713     | 762     | 816     |
| LB      | 185    | 196   | 221   | 275    | 277    | 309    | 305      | 355     | 386     | 440     |
| LBS     | 240    | 264   | 289   | 356    | 370    | 402    | 399      | 449     | 498     | 552     |

**FA67..**


42 041 00 14

**FA67..****FH67..**  
max. DR132S**FV67..**

| (→ 155) | DR63.. | DR71S | DR71M | DRN80M | DRN90S | DRN90L | DRN100LS | DRN100L | DRN112M | DRN132S |
|---------|--------|-------|-------|--------|--------|--------|----------|---------|---------|---------|
| AC      | 132    | 139   | 139   | 156    | 179    | 179    | 197      | 197     | 221     | 221     |
| AD      | 105    | 119   | 119   | 128    | 140    | 140    | 157      | 157     | 170     | 170     |
| ADS     | 105    | 129   | 129   | 139    | 150    | 150    | 158      | 158     | 172     | 172     |
| L       | 346    | 357   | 382   | 436    | 438    | 470    | 466      | 516     | 547     | 601     |
| LS      | 401    | 425   | 450   | 517    | 531    | 563    | 560      | 610     | 659     | 713     |
| LB      | 185    | 196   | 221   | 275    | 277    | 309    | 305      | 355     | 386     | 440     |
| LBS     | 240    | 264   | 289   | 356    | 370    | 402    | 399      | 449     | 498     | 552     |

**FAZ67..**


42 042 00 14



**FAZ67..**

**FHZ67..**  
max. DR132S


**FVZ67..**



| (→ 155) | DR63.. | DR71S | DR71M | DRN80M | DRN90S | DRN90L | DRN100LS | DRN100L | DRN112M | DRN132S |
|---------|--------|-------|-------|--------|--------|--------|----------|---------|---------|---------|
| AC      | 132    | 139   | 139   | 156    | 179    | 179    | 197      | 197     | 221     | 221     |
| AD      | 105    | 119   | 119   | 128    | 140    | 140    | 157      | 157     | 170     | 170     |
| ADS     | 105    | 129   | 129   | 139    | 150    | 150    | 158      | 158     | 172     | 172     |
| L       | 358    | 369   | 394   | 448    | 450    | 482    | 478      | 528     | 559     | 613     |
| LS      | 413    | 437   | 462   | 529    | 543    | 575    | 572      | 622     | 671     | 725     |
| LB      | 185    | 196   | 221   | 275    | 277    | 309    | 305      | 355     | 386     | 440     |
| LBS     | 240    | 264   | 289   | 356    | 370    | 402    | 399      | 449     | 498     | 552     |


## FZ67..

42 075 00 15



| (→ 155) | DR63.. | DR71S | DR71M | DRN80M | DRN90S | DRN90L | DRN100LS | DRN100L | DRN112M | DRN132S |
|---------|--------|-------|-------|--------|--------|--------|----------|---------|---------|---------|
| AC      | 132    | 139   | 139   | 156    | 179    | 179    | 197      | 197     | 221     | 221     |
| AD      | 105    | 119   | 119   | 128    | 140    | 140    | 157      | 157     | 170     | 170     |
| ADS     | 105    | 129   | 129   | 139    | 150    | 150    | 158      | 158     | 172     | 172     |
| L       | 434    | 445   | 470   | 525    | 526    | 558    | 555      | 605     | 636     | 690     |
| LS      | 489    | 513   | 538   | 606    | 620    | 652    | 648      | 698     | 748     | 802     |
| LB      | 185    | 196   | 221   | 275    | 277    | 309    | 305      | 355     | 386     | 440     |
| LBS     | 240    | 264   | 289   | 356    | 370    | 402    | 399      | 449     | 498     | 552     |

## 9




**SEW**  
**EURODRIVE**


21933170/DE – 11/2015

42 044 00 14


**F77..**




**FA77B..**



**FH77B..**  
**max. DRN132L**




**FV77B..**



| (→ 155) | DRN80M | DRN90S | DRN90L | DRN100LS | DRN100L | DRN112M | DRN132S | DRN132M | DRN132L | DRN160M |
|---------|--------|--------|--------|----------|---------|---------|---------|---------|---------|---------|
| AC      | 156    | 179    | 179    | 197      | 197     | 221     | 221     | 261     | 261     | 314     |
| AD      | 128    | 140    | 140    | 157      | 157     | 170     | 170     | 228     | 228     | 253     |
| ADS     | 139    | 150    | 150    | 158      | 158     | 172     | 172     | 228     | 228     | 253     |
| L       | 562    | 564    | 596    | 592      | 642     | 673     | 723     | 741     | 767     | 833     |
| LS      | 643    | 657    | 689    | 686      | 736     | 785     | 835     | 879     | 904     | 1022    |
| LB      | 268    | 270    | 302    | 298      | 348     | 379     | 429     | 447     | 473     | 539     |
| LBS     | 349    | 363    | 395    | 392      | 442     | 491     | 541     | 585     | 610     | 728     |

**FF77..**


42 045 00 14




**FAF77..**

**FHF77..**  
max. DRN132L


**FVF77..**



| (→ 155) | DRN80M | DRN90S | DRN90L | DRN100LS | DRN100L | DRN112M | DRN132S | DRN132M | DRN132L | DRN160M |
|---------|--------|--------|--------|----------|---------|---------|---------|---------|---------|---------|
| AC      | 156    | 179    | 179    | 197      | 197     | 221     | 221     | 261     | 261     | 314     |
| AD      | 128    | 140    | 140    | 157      | 157     | 170     | 170     | 228     | 228     | 253     |
| ADS     | 139    | 150    | 150    | 158      | 158     | 172     | 172     | 228     | 228     | 253     |
| L       | 598    | 600    | 632    | 628      | 678     | 709     | 759     | 777     | 803     | 869     |
| LS      | 679    | 693    | 725    | 722      | 772     | 821     | 871     | 915     | 940     | 1058    |
| LB      | 268    | 270    | 302    | 298      | 348     | 379     | 429     | 447     | 473     | 539     |
| LBS     | 349    | 363    | 395    | 392      | 442     | 491     | 541     | 585     | 610     | 728     |



## FV77..




| (→ 155) | DRN80M | DRN90S | DRN90L | DRN100LS | DRN100L | DRN112M | DRN132S | DRN132M | DRN132L | DRN160M |
|---------|--------|--------|--------|----------|---------|---------|---------|---------|---------|---------|
| AC      | 156    | 179    | 179    | 197      | 197     | 221     | 221     | 261     | 261     | 314     |
| AD      | 128    | 140    | 140    | 157      | 157     | 170     | 170     | 228     | 228     | 253     |
| ADS     | 139    | 150    | 150    | 158      | 158     | 172     | 172     | 228     | 228     | 253     |
| L       | 461    | 463    | 495    | 491      | 541     | 572     | 622     | 640     | 666     | 732     |
| LS      | 542    | 556    | 588    | 585      | 635     | 684     | 734     | 778     | 803     | 921     |
| LB      | 268    | 270    | 302    | 298      | 348     | 379     | 429     | 447     | 473     | 539     |
| LBS     | 349    | 363    | 395    | 392      | 442     | 491     | 541     | 585     | 610     | 728     |



**FAZ77..**


42 047 00 14



**FAZ77..**

**FHZ77..**  
max. DRN132L


**FVZ77..**



| (→ 155) | DRN80M | DRN90S | DRN90L | DRN100LS | DRN100L | DRN112M | DRN132S | DRN132M | DRN132L | DRN160M |
|---------|--------|--------|--------|----------|---------|---------|---------|---------|---------|---------|
| AC      | 156    | 179    | 179    | 197      | 197     | 221     | 221     | 261     | 261     | 314     |
| AD      | 128    | 140    | 140    | 157      | 157     | 170     | 170     | 228     | 228     | 253     |
| ADS     | 139    | 150    | 150    | 158      | 158     | 172     | 172     | 228     | 228     | 253     |
| L       | 474    | 476    | 508    | 504      | 554     | 585     | 635     | 653     | 679     | 745     |
| LS      | 555    | 569    | 601    | 598      | 648     | 697     | 747     | 791     | 816     | 934     |
| LB      | 268    | 270    | 302    | 298      | 348     | 379     | 429     | 447     | 473     | 539     |
| LBS     | 349    | 363    | 395    | 392      | 442     | 491     | 541     | 585     | 610     | 728     |

**FZ77..**



42 076 00 15





| (→ 155) | DRN80M | DRN90S | DRN90L | DRN100LS | DRN100L | DRN112M | DRN132S | DRN132M | DRN132L | DRN160M |
|---------|--------|--------|--------|----------|---------|---------|---------|---------|---------|---------|
| AC      | 156    | 179    | 179    | 197      | 197     | 221     | 221     | 261     | 261     | 314     |
| AD      | 128    | 140    | 140    | 157      | 157     | 170     | 170     | 228     | 228     | 253     |
| ADS     | 139    | 150    | 150    | 158      | 158     | 172     | 172     | 228     | 228     | 253     |
| L       | 571    | 572    | 604    | 601      | 651     | 682     | 732     | 750     | 775     | 842     |
| LS      | 652    | 666    | 698    | 694      | 744     | 794     | 844     | 887     | 912     | 1031    |
| LB      | 268    | 270    | 302    | 298      | 348     | 379     | 429     | 447     | 473     | 539     |
| LBS     | 349    | 363    | 395    | 392      | 442     | 491     | 541     | 585     | 610     | 728     |



42 049 00 14

**F87..****FA87B..****FH87B..**


FH87B/R.. → 6.3

**FV87B..**

| (→ 155) | DRN90L | DRN100LS | DRN100L | DRN112M | DRN132S | DRN132M | DRN132L | DRN160M | DRN160L | DRN180.. |
|---------|--------|----------|---------|---------|---------|---------|---------|---------|---------|----------|
| AC      | 179    | 197      | 197     | 221     | 221     | 261     | 261     | 314     | 314     | 357      |
| AD      | 140    | 157      | 157     | 170     | 170     | 228     | 228     | 253     | 253     | 268      |
| ADS     | 150    | 158      | 158     | 172     | 172     | 228     | 228     | 253     | 253     | 268      |
| L       | 641    | 637      | 687     | 718     | 768     | 786     | 812     | 878     | 878     | 901      |
| LS      | 734    | 731      | 781     | 830     | 880     | 924     | 949     | 1067    | 1067    | 1090     |
| LB      | 297    | 293      | 343     | 374     | 424     | 442     | 468     | 534     | 534     | 557      |
| LBS     | 390    | 387      | 437     | 486     | 536     | 580     | 605     | 723     | 723     | 746      |

# FF87..


42 050 00 14



# FAF87..


# FHF87.. FHF87/R.. → 6.3

# FVF87..







21933170/DE – 11/2015

| (→ 155) | DRN90L | DRN100LS | DRN100L | DRN112M | DRN132S | DRN132M | DRN132L | DRN160M | DRN160L | DRN180.. |
|---------|--------|----------|---------|---------|---------|---------|---------|---------|---------|----------|
| AC      | 179    | 197      | 197     | 221     | 221     | 261     | 261     | 314     | 314     | 357      |
| AD      | 140    | 157      | 157     | 170     | 170     | 228     | 228     | 253     | 253     | 268      |
| ADS     | 150    | 158      | 158     | 172     | 172     | 228     | 228     | 253     | 253     | 268      |
| L       | 671    | 667      | 717     | 748     | 798     | 816     | 842     | 908     | 908     | 931      |
| LS      | 764    | 761      | 811     | 860     | 910     | 954     | 979     | 1097    | 1097    | 1120     |
| LB      | 297    | 293      | 343     | 374     | 424     | 442     | 468     | 534     | 534     | 557      |
| LBS     | 390    | 387      | 437     | 486     | 536     | 580     | 605     | 723     | 723     | 746      |

**FA87..**



42 051 00 14

**FA87..****FH87..**  
**FH87/R..****FV87..**

| (→ 155) | DRN90L | DRN100LS | DRN100L | DRN112M | DRN132S | DRN132M | DRN132L | DRN160M | DRN160L | DRN180.. |
|---------|--------|----------|---------|---------|---------|---------|---------|---------|---------|----------|
| AC      | 179    | 197      | 197     | 221     | 221     | 261     | 261     | 314     | 314     | 357      |
| AD      | 140    | 157      | 157     | 170     | 170     | 228     | 228     | 253     | 253     | 268      |
| ADS     | 150    | 158      | 158     | 172     | 172     | 228     | 228     | 253     | 253     | 268      |
| L       | 521    | 517      | 567     | 598     | 648     | 666     | 692     | 758     | 758     | 781      |
| LS      | 614    | 611      | 661     | 710     | 760     | 804     | 829     | 947     | 947     | 970      |
| LB      | 297    | 293      | 343     | 374     | 424     | 442     | 468     | 534     | 534     | 557      |
| LBS     | 390    | 387      | 437     | 486     | 536     | 580     | 605     | 723     | 723     | 746      |

# FAZ87..




42 052 00 14



# FAZ87..

# FHZ87.. FHZ87/R.. → 6.3

# FVZ87..




21933170/DE – 11/2015

| (→ 155) | DRN90L | DRN100LS | DRN100L | DRN112M | DRN132S | DRN132M | DRN132L | DRN160M | DRN160L | DRN180.. |
|---------|--------|----------|---------|---------|---------|---------|---------|---------|---------|----------|
| AC      | 179    | 197      | 197     | 221     | 221     | 261     | 261     | 314     | 314     | 357      |
| AD      | 140    | 157      | 157     | 170     | 170     | 228     | 228     | 253     | 253     | 268      |
| ADS     | 150    | 158      | 158     | 172     | 172     | 228     | 228     | 253     | 253     | 268      |
| L       | 536    | 532      | 582     | 613     | 663     | 681     | 707     | 773     | 773     | 796      |
| LS      | 629    | 626      | 676     | 725     | 775     | 819     | 844     | 962     | 962     | 985      |
| LB      | 297    | 293      | 343     | 374     | 424     | 442     | 468     | 534     | 534     | 557      |
| LBS     | 390    | 387      | 437     | 486     | 536     | 580     | 605     | 723     | 723     | 746      |

**FZ87..**

**42 077 00 15**








| (→ 155) | DRN90L | DRN100LS | DRN100L | DRN112M | DRN132S | DRN132M | DRN132L | DRN160M | DRN160L | DRN180.. |
|---------|--------|----------|---------|---------|---------|---------|---------|---------|---------|----------|
| AC      | 179    | 197      | 197     | 221     | 221     | 261     | 261     | 314     | 314     | 357      |
| AD      | 140    | 157      | 157     | 170     | 170     | 228     | 228     | 253     | 253     | 268      |
| ADS     | 150    | 158      | 158     | 172     | 172     | 228     | 228     | 253     | 253     | 268      |
| L       | 652    | 648      | 698     | 729     | 779     | 797     | 823     | 889     | 889     | 912      |
| LS      | 745    | 742      | 792     | 841     | 891     | 935     | 960     | 1078    | 1078    | 1101     |
| LB      | 297    | 293      | 343     | 374     | 424     | 442     | 468     | 534     | 534     | 557      |
| LBS     | 390    | 387      | 437     | 486     | 536     | 580     | 605     | 723     | 723     | 746      |



FT87..

42 053 00 14





9



21933170/DE – 11/2015

| (→ 155) | DRN90L | DRN100LS | DRN100L | DRN112M | DRN132S | DRN132M | DRN132L | DRN160M | DRN160L | DRN180.. |
|---------|--------|----------|---------|---------|---------|---------|---------|---------|---------|----------|
| AC      | 179    | 197      | 197     | 221     | 221     | 261     | 261     | 314     | 314     | 357      |
| AD      | 140    | 157      | 157     | 170     | 170     | 228     | 228     | 253     | 253     | 268      |
| ADS     | 150    | 158      | 158     | 172     | 172     | 228     | 228     | 253     | 253     | 268      |
| L       | 547    | 543      | 593     | 624     | 674     | 692     | 718     | 784     | 784     | 807      |
| LS      | 640    | 637      | 687     | 736     | 786     | 830     | 855     | 973     | 973     | 996      |
| LB      | 297    | 293      | 343     | 374     | 424     | 442     | 468     | 534     | 534     | 557      |
| LBS     | 390    | 387      | 437     | 486     | 536     | 580     | 605     | 723     | 723     | 746      |

42 054 00 14

**F97..****FA97B..****FH97B..**


FH97B/R.. → 6.3

**FV97B..**

| (→ 155) | DRN100LS | DRN100L | DRN112M | DRN132S | DRN132M | DRN132L | DRN160M | DRN160L | DRN180.. | DRN200L |
|---------|----------|---------|---------|---------|---------|---------|---------|---------|----------|---------|
| AC      | 197      | 197     | 221     | 221     | 261     | 261     | 314     | 314     | 357      | 394     |
| AD      | 157      | 157     | 170     | 170     | 228     | 228     | 253     | 253     | 268      | 283     |
| ADS     | 158      | 158     | 172     | 172     | 228     | 228     | 253     | 253     | 268      | 283     |
| L       | 704      | 754     | 785     | 835     | 853     | 879     | 945     | 945     | 968      | 1078    |
| LS      | 798      | 848     | 897     | 947     | 991     | 1016    | 1134    | 1134    | 1157     | 1283    |
| LB      | 288      | 338     | 369     | 419     | 437     | 463     | 529     | 529     | 552      | 662     |
| LBS     | 382      | 432     | 481     | 531     | 575     | 600     | 718     | 718     | 741      | 867     |

# FF97..


42 055 00 14




# FAF97..

# FHF97.. FHF97/R.. → 6.3





# FVF97..



| (→ 155) | DRN100LS | DRN100L | DRN112M | DRN132S | DRN132M | DRN132L | DRN160M | DRN160L | DRN180.. | DRN200L |
|---------|----------|---------|---------|---------|---------|---------|---------|---------|----------|---------|
| AC      | 197      | 197     | 221     | 221     | 261     | 261     | 314     | 314     | 357      | 394     |
| AD      | 157      | 157     | 170     | 170     | 228     | 228     | 253     | 253     | 268      | 283     |
| ADS     | 158      | 158     | 172     | 172     | 228     | 228     | 253     | 253     | 268      | 283     |
| L       | 744      | 794     | 825     | 875     | 893     | 919     | 985     | 985     | 1008     | 1118    |
| LS      | 838      | 888     | 937     | 987     | 1031    | 1056    | 1174    | 1174    | 1197     | 1323    |
| LB      | 288      | 338     | 369     | 419     | 437     | 463     | 529     | 529     | 552      | 662     |
| LBS     | 382      | 432     | 481     | 531     | 575     | 600     | 718     | 718     | 741      | 867     |

**FA97..**



42 056 00 14

**FA97..****FH97..**  
**FH97/R..****FV97..**

| (→ 155) | DRN100LS | DRN100L | DRN112M | DRN132S | DRN132M | DRN132L | DRN160M | DRN160L | DRN180.. | DRN200L |
|---------|----------|---------|---------|---------|---------|---------|---------|---------|----------|---------|
| AC      | 197      | 197     | 221     | 221     | 261     | 261     | 314     | 314     | 357      | 394     |
| AD      | 157      | 157     | 170     | 170     | 228     | 228     | 253     | 253     | 268      | 283     |
| ADS     | 158      | 158     | 172     | 172     | 228     | 228     | 253     | 253     | 268      | 283     |
| L       | 562      | 612     | 643     | 693     | 711     | 737     | 803     | 803     | 826      | 936     |
| LS      | 656      | 706     | 755     | 805     | 849     | 874     | 992     | 992     | 1015     | 1141    |
| LB      | 288      | 338     | 369     | 419     | 437     | 463     | 529     | 529     | 552      | 662     |
| LBS     | 382      | 432     | 481     | 531     | 575     | 600     | 718     | 718     | 741      | 867     |

# FAZ97..




42 057 00 14



# FAZ97..

# FHZ97.. FHZ97/R.. → 6.3

# FVZ97..




21933170/DE – 11/2015

| (→ 155) | DRN100LS | DRN100L | DRN112M | DRN132S | DRN132M | DRN132L | DRN160M | DRN160L | DRN180.. | DRN200L |
|---------|----------|---------|---------|---------|---------|---------|---------|---------|----------|---------|
| AC      | 197      | 197     | 221     | 221     | 261     | 261     | 314     | 314     | 357      | 394     |
| AD      | 157      | 157     | 170     | 170     | 228     | 228     | 253     | 253     | 268      | 283     |
| ADS     | 158      | 158     | 172     | 172     | 228     | 228     | 253     | 253     | 268      | 283     |
| L       | 580      | 630     | 661     | 711     | 729     | 755     | 821     | 821     | 844      | 954     |
| LS      | 674      | 724     | 773     | 823     | 867     | 892     | 1010    | 1010    | 1033     | 1159    |
| LB      | 288      | 338     | 369     | 419     | 437     | 463     | 529     | 529     | 552      | 662     |
| LBS     | 382      | 432     | 481     | 531     | 575     | 600     | 718     | 718     | 741      | 867     |

## FZ97..






42 078 00 15



| (→ 155) | DRN100LS | DRN100L | DRN112M | DRN132S | DRN132M | DRN132L | DRN160M | DRN160L | DRN180.. | DRN200L |
|---------|----------|---------|---------|---------|---------|---------|---------|---------|----------|---------|
| AC      | 197      | 197     | 221     | 221     | 261     | 261     | 314     | 314     | 357      | 394     |
| AD      | 157      | 157     | 170     | 170     | 228     | 228     | 253     | 253     | 268      | 283     |
| ADS     | 158      | 158     | 172     | 172     | 228     | 228     | 253     | 253     | 268      | 283     |
| L       | 716      | 766     | 797     | 847     | 865     | 891     | 957     | 957     | 980      | 1090    |
| LS      | 810      | 860     | 909     | 959     | 1003    | 1028    | 1146    | 1146    | 1169     | 1295    |
| LB      | 288      | 338     | 369     | 419     | 437     | 463     | 529     | 529     | 552      | 662     |
| LBS     | 382      | 432     | 481     | 531     | 575     | 600     | 718     | 718     | 741      | 867     |

**FT97..**

42 058 00 14




9


21933170/DE – 11/2015

| (→ 155) | DRN90L | DRN100LS | DRN100L | DRN112M | DRN132S | DRN132M | DRN132L | DRN160M | DRN160L | DRN180.. |
|---------|--------|----------|---------|---------|---------|---------|---------|---------|---------|----------|
| AC      | 179    | 197      | 197     | 221     | 221     | 261     | 261     | 314     | 314     | 357      |
| AD      | 140    | 157      | 157     | 170     | 170     | 228     | 228     | 253     | 253     | 268      |
| ADS     | 150    | 158      | 158     | 172     | 172     | 228     | 228     | 253     | 253     | 268      |
| L       | 592    | 588      | 638     | 669     | 719     | 737     | 763     | 829     | 829     | 852      |
| LS      | 685    | 682      | 732     | 781     | 831     | 875     | 900     | 1018    | 1018    | 1041     |
| LB      | 292    | 288      | 338     | 369     | 419     | 437     | 463     | 529     | 529     | 552      |
| LBS     | 385    | 382      | 432     | 481     | 531     | 575     | 600     | 718     | 718     | 741      |


**F107..**



**FH107B..**



**FV107B..**


21933170/DE – 11/2015




## 9

| (→ 155)    | DRN100L | DRN112M | DRN132S | DRN132M | DRN132L | DRN160M | DRN160L | DRN180.. | DRN200L | DRN225.. |
|------------|---------|---------|---------|---------|---------|---------|---------|----------|---------|----------|
| <b>AC</b>  | 197     | 221     | 221     | 261     | 261     | 314     | 314     | 357      | 394     | 434      |
| <b>AD</b>  | 157     | 170     | 170     | 228     | 228     | 253     | 253     | 268      | 283     | 305      |
| <b>ADS</b> | 158     | 172     | 172     | 228     | 228     | 253     | 253     | 268      | 283     | 305      |
| <b>L</b>   | 855     | 886     | 936     | 954     | 980     | 1046    | 1046    | 1069     | 1179    | 1153     |
| <b>LS</b>  | 949     | 998     | 1048    | 1092    | 1117    | 1235    | 1235    | 1258     | 1384    | 1358     |
| <b>LB</b>  | 332     | 363     | 413     | 431     | 457     | 523     | 523     | 546      | 656     | 630      |
| <b>LBS</b> | 426     | 475     | 525     | 569     | 594     | 712     | 712     | 735      | 861     | 835      |


## FA107..




42 061 00 14




## FA107..



## FH107..





## FV107..



| (→ 155) | DRN100L | DRN112M | DRN132S | DRN132M | DRN132L | DRN160M | DRN160L | DRN180.. | DRN200L | DRN225.. |
|---------|---------|---------|---------|---------|---------|---------|---------|----------|---------|----------|
| AC      | 197     | 221     | 221     | 261     | 261     | 314     | 314     | 357      | 394     | 434      |
| AD      | 157     | 170     | 170     | 228     | 228     | 253     | 253     | 268      | 283     | 305      |
| ADS     | 158     | 172     | 172     | 228     | 228     | 253     | 253     | 268      | 283     | 305      |
| L       | 644     | 675     | 725     | 743     | 769     | 835     | 835     | 858      | 968     | 942      |
| LS      | 738     | 787     | 837     | 881     | 906     | 1024    | 1024    | 1047     | 1173    | 1147     |
| LB      | 332     | 363     | 413     | 431     | 457     | 523     | 523     | 546      | 656     | 630      |
| LBS     | 426     | 475     | 525     | 569     | 594     | 712     | 712     | 735      | 861     | 835      |

# FAZ107..




42 062 00 14



# FAZ107..

# FHZ107..


# FVZ107..



| (→ 155) | DRN100L | DRN112M | DRN132S | DRN132M | DRN132L | DRN160M | DRN160L | DRN180.. | DRN200L | DRN225.. |
|---------|---------|---------|---------|---------|---------|---------|---------|----------|---------|----------|
| AC      | 197     | 221     | 221     | 261     | 261     | 314     | 314     | 357      | 394     | 434      |
| AD      | 157     | 170     | 170     | 228     | 228     | 253     | 253     | 268      | 283     | 305      |
| ADS     | 158     | 172     | 172     | 228     | 228     | 253     | 253     | 268      | 283     | 305      |
| L       | 644     | 675     | 725     | 743     | 769     | 835     | 835     | 858      | 968     | 942      |
| LS      | 738     | 787     | 837     | 881     | 906     | 1024    | 1024    | 1047     | 1173    | 1147     |
| LB      | 332     | 363     | 413     | 431     | 457     | 523     | 523     | 546      | 656     | 630      |
| LBS     | 426     | 475     | 525     | 569     | 594     | 712     | 712     | 735      | 861     | 835      |

## FZ107..






42 079 00 15



| (→ 155) | DRN100L | DRN112M | DRN132S | DRN132M | DRN132L | DRN160M | DRN160L | DRN180.. | DRN200L | DRN225.. |
|---------|---------|---------|---------|---------|---------|---------|---------|----------|---------|----------|
| AC      | 197     | 221     | 221     | 261     | 261     | 314     | 314     | 357      | 394     | 434      |
| AD      | 157     | 170     | 170     | 228     | 228     | 253     | 253     | 268      | 283     | 305      |
| ADS     | 158     | 172     | 172     | 228     | 228     | 253     | 253     | 268      | 283     | 305      |
| L       | 814     | 845     | 895     | 913     | 939     | 1005    | 1005    | 1028     | 1138    | 1112     |
| LS      | 908     | 957     | 1007    | 1051    | 1076    | 1194    | 1194    | 1217     | 1343    | 1317     |
| LB      | 332     | 363     | 413     | 431     | 457     | 523     | 523     | 546      | 656     | 630      |
| LBS     | 426     | 475     | 525     | 569     | 594     | 712     | 712     | 735      | 861     | 835      |

**FT107..**

42 063 00 14






9

21933170/DE – 11/2015



| (→ 155) | DRN100L | DRN112M | DRN132S | DRN132M | DRN132L | DRN160M | DRN160L | DRN180.. | DRN200L | DRN225.. |
|---------|---------|---------|---------|---------|---------|---------|---------|----------|---------|----------|
| AC      | 197     | 221     | 221     | 261     | 261     | 314     | 314     | 357      | 394     | 434      |
| AD      | 157     | 170     | 170     | 228     | 228     | 253     | 253     | 268      | 283     | 305      |
| ADS     | 158     | 172     | 172     | 228     | 228     | 253     | 253     | 268      | 283     | 305      |
| L       | 670     | 701     | 751     | 769     | 795     | 861     | 861     | 884      | 994     | 968      |
| LS      | 764     | 813     | 863     | 907     | 932     | 1050    | 1050    | 1073     | 1199    | 1173     |
| LB      | 332     | 363     | 413     | 431     | 457     | 523     | 523     | 546      | 656     | 630      |
| LBS     | 426     | 475     | 525     | 569     | 594     | 712     | 712     | 735      | 861     | 835      |

**F127..**

42 064 00 14

**FA127B..****FH127B..**


| (→ 155) | DRN132M | DRN132L | DRN160M | DRN160L | DRN180.. | DRN200L | DRN225.. | DRN250M | DRN280S | DRN280M |
|---------|---------|---------|---------|---------|----------|---------|----------|---------|---------|---------|
| AC      | 261     | 261     | 314     | 314     | 357      | 394     | 434      | 495     | 495     | 495     |
| AD      | 228     | 228     | 253     | 253     | 268      | 283     | 305      | 394     | 394     | 394     |
| ADS     | 228     | 228     | 253     | 253     | 268      | 283     | 305      | 394     | 394     | 394     |
| L       | 1001    | 1027    | 1093    | 1093    | 1116     | 1226    | 1200     | 1337    | 1337    | 1432    |
| LS      | 1139    | 1164    | 1282    | 1282    | 1305     | 1431    | 1405     | 1577    | 1577    | 1672    |
| LB      | 416     | 442     | 508     | 508     | 531      | 641     | 615      | 752     | 752     | 847     |
| LBS     | 554     | 579     | 697     | 697     | 720      | 846     | 820      | 992     | 992     | 1087    |




| (→ 155) | DRN132M | DRN132L | DRN160M | DRN160L | DRN180.. | DRN200L | DRN225.. | DRN250M | DRN280S | DRN280M |
|---------|---------|---------|---------|---------|----------|---------|----------|---------|---------|---------|
| AC      | 261     | 261     | 314     | 314     | 357      | 394     | 434      | 495     | 495     | 495     |
| AD      | 228     | 228     | 253     | 253     | 268      | 283     | 305      | 394     | 394     | 394     |
| ADS     | 228     | 228     | 253     | 253     | 268      | 283     | 305      | 394     | 394     | 394     |
| L       | 1050    | 1076    | 1142    | 1142    | 1165     | 1275    | 1249     | 1386    | 1386    | 1481    |
| LS      | 1188    | 1213    | 1331    | 1331    | 1354     | 1480    | 1454     | 1626    | 1626    | 1721    |
| LB      | 416     | 442     | 508     | 508     | 531      | 641     | 615      | 752     | 752     | 847     |
| LBS     | 554     | 579     | 697     | 697     | 720      | 846     | 820      | 992     | 992     | 1087    |

## FA127..


42 066 00 14



## FA127..



## FH127..




| (→ 155) | DRN132M | DRN132L | DRN160M | DRN160L | DRN180.. | DRN200L | DRN225.. | DRN250M | DRN280S | DRN280M |
|---------|---------|---------|---------|---------|----------|---------|----------|---------|---------|---------|
| AC      | 261     | 261     | 314     | 314     | 357      | 394     | 434      | 495     | 495     | 495     |
| AD      | 228     | 228     | 253     | 253     | 268      | 283     | 305      | 394     | 394     | 394     |
| ADS     | 228     | 228     | 253     | 253     | 268      | 283     | 305      | 394     | 394     | 394     |
| L       | 789     | 815     | 881     | 881     | 904      | 1014    | 988      | 1125    | 1125    | 1220    |
| LS      | 927     | 952     | 1070    | 1070    | 1093     | 1219    | 1193     | 1365    | 1365    | 1460    |
| LB      | 416     | 442     | 508     | 508     | 531      | 641     | 615      | 752     | 752     | 847     |
| LBS     | 554     | 579     | 697     | 697     | 720      | 846     | 820      | 992     | 992     | 1087    |





**FAZ127..**

42 067 00 14



**FAZ127..**


**FHZ127..**



| (→ 155) | DRN132M | DRN132L | DRN160M | DRN160L | DRN180.. | DRN200L | DRN225.. | DRN250M | DRN280S | DRN280M |
|---------|---------|---------|---------|---------|----------|---------|----------|---------|---------|---------|
| AC      | 261     | 261     | 314     | 314     | 357      | 394     | 434      | 495     | 495     | 495     |
| AD      | 228     | 228     | 253     | 253     | 268      | 283     | 305      | 394     | 394     | 394     |
| ADS     | 228     | 228     | 253     | 253     | 268      | 283     | 305      | 394     | 394     | 394     |
| L       | 794     | 819     | 886     | 886     | 909      | 1018    | 993      | 1130    | 1130    | 1225    |
| LS      | 931     | 956     | 1075    | 1075    | 1098     | 1223    | 1198     | 1370    | 1370    | 1465    |
| LB      | 416     | 442     | 508     | 508     | 531      | 641     | 615      | 752     | 752     | 847     |
| LBS     | 554     | 579     | 697     | 697     | 720      | 846     | 820      | 992     | 992     | 1087    |

## FZ127..


42 080 00 15



| (→ 155) | DRN132M | DRN132L | DRN160M | DRN160L | DRN180.. | DRN200L | DRN225.. | DRN250M | DRN280S | DRN280M |
|---------|---------|---------|---------|---------|----------|---------|----------|---------|---------|---------|
| AC      | 261     | 261     | 314     | 314     | 357      | 394     | 434      | 495     | 495     | 495     |
| AD      | 228     | 228     | 253     | 253     | 268      | 283     | 305      | 394     | 394     | 394     |
| ADS     | 228     | 228     | 253     | 253     | 268      | 283     | 305      | 394     | 394     | 394     |
| L       | 999     | 1024    | 1091    | 1091    | 1114     | 1223    | 1198     | 1335    | 1335    | 1430    |
| LS      | 1136    | 1161    | 1280    | 1280    | 1303     | 1428    | 1403     | 1575    | 1575    | 1670    |
| LB      | 416     | 442     | 508     | 508     | 531      | 641     | 615      | 752     | 752     | 847     |
| LBS     | 554     | 579     | 697     | 697     | 720      | 846     | 820      | 992     | 992     | 1087    |

FT127..

42 068 00 14






| (→ 155) | DRN132M | DRN132L | DRN160M | DRN160L | DRN180.. | DRN200L | DRN225.. | DRN250M | DRN280S | DRN280M |
|---------|---------|---------|---------|---------|----------|---------|----------|---------|---------|---------|
| AC      | 261     | 261     | 314     | 314     | 357      | 394     | 434      | 495     | 495     | 495     |
| AD      | 228     | 228     | 253     | 253     | 268      | 283     | 305      | 394     | 394     | 394     |
| ADS     | 228     | 228     | 253     | 253     | 268      | 283     | 305      | 394     | 394     | 394     |
| L       | 820     | 846     | 912     | 912     | 935      | 1045    | 1019     | 1156    | 1156    | 1251    |
| LS      | 958     | 983     | 1101    | 1101    | 1124     | 1250    | 1224     | 1396    | 1396    | 1491    |
| LB      | 416     | 442     | 508     | 508     | 531      | 641     | 615      | 752     | 752     | 847     |
| LBS     | 554     | 579     | 697     | 697     | 720      | 846     | 820      | 992     | 992     | 1087    |

21933170/DE – 11/2015




**F157..**

42 069 00 14

**FA157B..****FH157B..**

| (→ 155) | DRN160L | DRN180.. | DRN200L | DRN225.. | DRN250M | DRN280S | DRN280M | DRN315S-M | DRN315ME-H |
|---------|---------|----------|---------|----------|---------|---------|---------|-----------|------------|
| AC      | 314     | 357      | 394     | 434      | 495     | 495     | 495     | 624       | 624        |
| AD      | 253     | 268      | 283     | 305      | 394     | 394     | 394     | 506       | 506        |
| ADS     | 253     | 268      | 283     | 305      | 394     | 394     | 394     | 506       | 506        |
| L       | 1162    | 1185     | 1295    | 1269     | 1406    | 1406    | 1501    | 1603      | 1733       |
| LS      | 1351    | 1374     | 1500    | 1474     | 1646    | 1646    | 1741    | 1854      | 1984       |
| LB      | 500     | 523      | 633     | 607      | 744     | 744     | 839     | 941       | 1071       |
| LBS     | 689     | 712      | 838     | 812      | 984     | 984     | 1079    | 1192      | 1322       |


42 070 00 14




| (→ 155) | DRN160L | DRN180.. | DRN200L | DRN225.. | DRN250M | DRN280S | DRN280M | DRN315S-M | DRN315ME-H |
|---------|---------|----------|---------|----------|---------|---------|---------|-----------|------------|
| AC      | 314     | 357      | 394     | 434      | 495     | 495     | 495     | 624       | 624        |
| AD      | 253     | 268      | 283     | 305      | 394     | 394     | 394     | 506       | 506        |
| ADS     | 253     | 268      | 283     | 305      | 394     | 394     | 394     | 506       | 506        |
| L       | 1225    | 1248     | 1358    | 1332     | 1469    | 1469    | 1564    | 1666      | 1796       |
| LS      | 1414    | 1437     | 1563    | 1537     | 1709    | 1709    | 1804    | 1917      | 2047       |
| LB      | 500     | 523      | 633     | 607      | 744     | 744     | 839     | 941       | 1071       |
| LBS     | 689     | 712      | 838     | 812      | 984     | 984     | 1079    | 1192      | 1322       |

## FA157..


42 071 00 14



## FA157..




## FH157..



| (→ 155) | DRN160L | DRN180.. | DRN200L | DRN225.. | DRN250M | DRN280S | DRN280M | DRN315S-M | DRN315ME-H |
|---------|---------|----------|---------|----------|---------|---------|---------|-----------|------------|
| AC      | 314     | 357      | 394     | 434      | 495     | 495     | 495     | 624       | 624        |
| AD      | 253     | 268      | 283     | 305      | 394     | 394     | 394     | 506       | 506        |
| ADS     | 253     | 268      | 283     | 305      | 394     | 394     | 394     | 506       | 506        |
| L       | 955     | 978      | 1088    | 1062     | 1199    | 1199    | 1294    | 1396      | 1526       |
| LS      | 1144    | 1167     | 1293    | 1267     | 1439    | 1439    | 1534    | 1647      | 1777       |
| LB      | 500     | 523      | 633     | 607      | 744     | 744     | 839     | 941       | 1071       |
| LBS     | 689     | 712      | 838     | 812      | 984     | 984     | 1079    | 1192      | 1322       |



**FAZ157..**

42 072 00 14



**FAZ157..**


**FHZ157..**



| (→ 155) | DRN160L | DRN180.. | DRN200L | DRN225.. | DRN250M | DRN280S | DRN280M | DRN315S-M | DRN315ME-H |
|---------|---------|----------|---------|----------|---------|---------|---------|-----------|------------|
| AC      | 314     | 357      | 394     | 434      | 495     | 495     | 495     | 624       | 624        |
| AD      | 253     | 268      | 283     | 305      | 394     | 394     | 394     | 506       | 506        |
| ADS     | 253     | 268      | 283     | 305      | 394     | 394     | 394     | 506       | 506        |
| L       | 955     | 978      | 1088    | 1062     | 1199    | 1199    | 1294    | 1396      | 1526       |
| LS      | 1144    | 1167     | 1293    | 1267     | 1439    | 1439    | 1534    | 1647      | 1777       |
| LB      | 500     | 523      | 633     | 607      | 744     | 744     | 839     | 941       | 1071       |
| LBS     | 689     | 712      | 838     | 812      | 984     | 984     | 1079    | 1192      | 1322       |

**FZ157..**

42 081 00 15




| (→ 155) | DRN160L | DRN180.. | DRN200L | DRN225.. | DRN250M | DRN280S | DRN280M | DRN315S-M | DRN315ME-H |
|---------|---------|----------|---------|----------|---------|---------|---------|-----------|------------|
| AC      | 314     | 357      | 394     | 434      | 495     | 495     | 495     | 624       | 624        |
| AD      | 253     | 268      | 283     | 305      | 394     | 394     | 394     | 506       | 506        |
| ADS     | 253     | 268      | 283     | 305      | 394     | 394     | 394     | 506       | 506        |
| L       | 1165    | 1188     | 1298    | 1272     | 1409    | 1409    | 1504    | 1606      | 1736       |
| LS      | 1354    | 1377     | 1503    | 1477     | 1649    | 1649    | 1744    | 1857      | 1987       |
| LB      | 500     | 523      | 633     | 607      | 744     | 744     | 839     | 941       | 1071       |
| LBS     | 689     | 712      | 838     | 812      | 984     | 984     | 1079    | 1192      | 1322       |




FT157..

42 073 00 14



| (→ 155) | DRN160L | DRN180.. | DRN200L | DRN225.. | DRN250M | DRN280S | DRN280M | DRN315S-M | DRN315ME-H |
|---------|---------|----------|---------|----------|---------|---------|---------|-----------|------------|
| AC      | 314     | 357      | 394     | 434      | 495     | 495     | 495     | 624       | 624        |
| AD      | 253     | 268      | 283     | 305      | 394     | 394     | 394     | 506       | 506        |
| ADS     | 253     | 268      | 283     | 305      | 394     | 394     | 394     | 506       | 506        |
| L       | 993     | 1016     | 1126    | 1100     | 1237    | 1237    | 1332    | 1434      | 1564       |
| LS      | 1182    | 1205     | 1331    | 1305     | 1477    | 1477    | 1572    | 1685      | 1815       |
| LB      | 500     | 523      | 633     | 607      | 744     | 744     | 839     | 941       | 1071       |
| LBS     | 689     | 712      | 838     | 812      | 984     | 984     | 1079    | 1192      | 1322       |

42 121 00 06



| (→ D 155) |          | AC  | L   | LS  | LB  | LBS |
|-----------|----------|-----|-----|-----|-----|-----|
| F..27R17  | DR63..   | 132 | 324 | 379 | 149 | 204 |
| F..37R17  | DR63..   | 132 | 324 | 379 | 149 | 204 |
|           | DR71S    | 139 | 335 | 403 | 160 | 228 |
| F..47R17  | DR63..   | 132 | 324 | 379 | 149 | 204 |
|           | DR71S    | 139 | 335 | 403 | 160 | 228 |
|           | DR71M    | 139 | 360 | 428 | 185 | 253 |
| F..57R37  | DR63..   | 132 | 356 | 411 | 191 | 246 |
|           | DR71S    | 139 | 367 | 434 | 202 | 269 |
|           | DR71M    | 139 | 392 | 459 | 227 | 294 |
|           | DRN80M   | 156 | 446 | 527 | 281 | 362 |
| F..67R37  | DR63..   | 132 | 356 | 411 | 191 | 246 |
|           | DR71S    | 139 | 367 | 434 | 202 | 269 |
|           | DR71M    | 139 | 392 | 459 | 227 | 294 |
|           | DRN80M   | 156 | 446 | 527 | 281 | 362 |
|           | DRN90S   | 179 | 448 | 541 | 283 | 376 |
| F..77R37  | DR63..   | 132 | 348 | 403 | 191 | 246 |
|           | DR71S    | 139 | 359 | 426 | 202 | 269 |
|           | DR71M    | 139 | 384 | 451 | 227 | 294 |
|           | DRN80M   | 156 | 438 | 519 | 281 | 362 |
|           | DRN90S   | 179 | 440 | 533 | 283 | 376 |
|           | DRN90L   | 179 | 472 | 565 | 315 | 408 |
| F..87R57  | DR63..   | 132 | 412 | 467 | 185 | 240 |
|           | DR71S    | 139 | 423 | 491 | 196 | 264 |
|           | DR71M    | 139 | 448 | 516 | 221 | 289 |
|           | DRN80M   | 156 | 502 | 583 | 275 | 356 |
|           | DRN90S   | 179 | 504 | 597 | 277 | 370 |
|           | DRN90L   | 179 | 536 | 629 | 309 | 402 |
|           | DRN100LS | 197 | 533 | 626 | 305 | 398 |
|           | DRN100L  | 197 | 583 | 676 | 355 | 448 |
| F..97R57  | DR63..   | 132 | 407 | 462 | 185 | 240 |
|           | DR71S    | 139 | 418 | 486 | 196 | 264 |
|           | DR71M    | 139 | 443 | 511 | 221 | 289 |
|           | DRN80M   | 156 | 497 | 578 | 275 | 356 |
|           | DRN90S   | 179 | 499 | 592 | 277 | 370 |
|           | DRN90L   | 179 | 531 | 624 | 309 | 402 |
|           | DRN100LS | 197 | 528 | 621 | 305 | 398 |
|           | DRN100L  | 197 | 578 | 671 | 355 | 448 |
|           | DRN112M  | 221 | 608 | 720 | 386 | 498 |

| (→ D 155) |          | AC  | L   | LS   | LB  | LBS |
|-----------|----------|-----|-----|------|-----|-----|
| F..107R77 | DR63..   | 132 | 425 | 480  | 178 | 233 |
|           | DR71S    | 139 | 436 | 504  | 189 | 257 |
|           | DR71M    | 139 | 461 | 529  | 214 | 282 |
|           | DRN80M   | 156 | 515 | 596  | 268 | 349 |
|           | DRN90S   | 179 | 517 | 610  | 270 | 363 |
|           | DRN90L   | 179 | 549 | 642  | 302 | 395 |
|           | DRN100LS | 197 | 545 | 638  | 298 | 391 |
|           | DRN100L  | 197 | 595 | 688  | 348 | 441 |
|           | DRN112M  | 221 | 626 | 738  | 379 | 491 |
|           | DRN132S  | 221 | 676 | 788  | 429 | 541 |
|           | DRN132M  | 261 | 692 | 831  | 445 | 584 |
|           | DRN132L  | 261 | 745 | 884  | 465 | 604 |
| F..127R77 | DR63..   | 132 | 410 | 465  | 178 | 233 |
|           | DR71S    | 139 | 421 | 489  | 189 | 257 |
|           | DR71M    | 139 | 446 | 514  | 214 | 282 |
|           | DRN80M   | 156 | 500 | 581  | 268 | 349 |
|           | DRN90S   | 179 | 502 | 595  | 270 | 363 |
|           | DRN90L   | 179 | 534 | 627  | 302 | 395 |
|           | DRN100LS | 197 | 530 | 623  | 298 | 391 |
|           | DRN100L  | 197 | 580 | 673  | 348 | 441 |
|           | DRN112M  | 221 | 611 | 723  | 379 | 491 |
|           | DRN132S  | 221 | 661 | 773  | 429 | 541 |
| F..127R87 | DRN132S  | 221 | 704 | 816  | 424 | 536 |
|           | DRN132M  | 261 | 720 | 859  | 440 | 579 |
|           | DRN132L  | 261 | 745 | 884  | 465 | 604 |
|           | DRN160M  | 314 | 814 | 1003 | 534 | 723 |
|           | DRN160L  | 314 | 814 | 1003 | 534 | 723 |
| F..157R97 | DR71M    | 139 | 529 | 597  | 204 | 272 |
|           | DRN80M   | 156 | 583 | 664  | 258 | 339 |
|           | DRN90S   | 179 | 585 | 678  | 260 | 353 |
|           | DRN90L   | 179 | 617 | 710  | 292 | 385 |
|           | DRN100LS | 197 | 613 | 706  | 288 | 381 |
|           | DRN100L  | 197 | 663 | 756  | 338 | 431 |
|           | DRN112M  | 221 | 694 | 806  | 369 | 481 |
|           | DRN132S  | 221 | 744 | 856  | 419 | 531 |
|           | DRN132M  | 261 | 760 | 899  | 435 | 574 |
|           | DRN132L  | 261 | 785 | 924  | 460 | 599 |
|           | DRN160M  | 314 | 854 | 1043 | 529 | 718 |
|           | DRN160L  | 314 | 854 | 1043 | 529 | 718 |
|           | DRN180M  | 357 | 879 | 1068 | 554 | 743 |

21933170/DE – 11/2015