

10 Kegelradgetriebemotoren



10.1 Geometrisch mögliche Kombinationen K..DRU..J (IE4)

K19, $n_e=1400 \text{ min}^{-1}$					80 Nm		
n_a min^{-1}	M_{amax} Nm	F_{Ra} N	$\varphi_{(R)}$ °	i	DRU71SJ_FU	DRU71SJ DRU71MJ_FU DRU80SJ_FU	DRU71MJ DRU80SJ DRU80MJ_FU
 2							
24	70	4330	-	58.68			
26	70	4330	-	53.88			
28	70	4330	-	49.69			
31	69	4340	-	44.48			
34	67	4350	-	40.63			
41	64	4370	-	34.29			
44	80	4260	-	31.74			
48	61	4200	-	29.29			
48	80	4120	-	29.14			
52	60	4090	-	27.16			
52	80	3990	-	26.88			
58	80	3820	-	24.06			
64	80	3680	-	21.98			
75	80	3430	-	18.55			
88	80	3210	-	15.84			
95	80	3110	-	14.69			
110	80	2930	-	12.70			
118	79	2850	-	11.84			
136	76	2720	-	10.32			
146	63	2910	-	9.58			
173	80	2590	-	8.09			
203	80	2420	-	6.91			
218	80	2340	-	6.41			
253	80	2200	-	5.54			
271	80	2140	-	5.16			
311	80	2010	-	4.50			

K29, n _e =1400 min ⁻¹					130 Nm			
n _a min ⁻¹	M _{amax} Nm	F _{Ra} N	φ _(/R) °	i	DRU71SJ_FU	DRU71SJ DRU71MJ_FU DRU80SJ_FU	DRU71MJ DRU80SJ DRU80MJ_FU	DRU90MJ DRU90MJ_FU DRU90LJ_FU
 2								
19	130	4980	-	71.93				
21	130	4980	-	66.25				
23	130	4980	-	61.28				
26	130	4980	-	54.89				
28	130	4980	-	50.35				
33	128	4790	-	42.87				
36	130	4720	-	38.90				
38	122	4560	-	36.96				
39	130	4560	-	35.83				
42	130	4410	-	33.15				
46	115	4250	-	30.11				
47	130	4210	-	29.69				
51	130	4060	-	27.23				

K29, $n_e=1400 \text{ min}^{-1}$					130 Nm			
n_a min^{-1}	M_{amax} Nm	F_{Ra} N	$\Phi_{(R)}$ °	i	DRU71SJ_FU	DRU71SJ DRU71MJ_FU DRU80SJ_FU	DRU71MJ DRU80SJ DRU80MJ_FU	DRU90MJ DRU90MJ_FU DRU90LJ_FU
56	109	3980	-	24.91				
60	130	3790	-	23.19				
63	105	3820	-	22.08				
70	130	3550	-	19.99				
86	130	3240	-	16.29				
104	130	2970	-	13.47				
117	130	2810	-	11.94				
141	110	3000	-	9.90				
153	130	2470	-	9.17				
164	122	2740	-	8.53				
187	123	2300	-	7.48				
201	112	2580	-	6.95				
243	112	2370	-	5.75				
275	110	2260	-	5.10				
357	126	1910	-	3.92				
439	110	1830	-	3.19				

K37, $n_e=1400 \text{ min}^{-1}$					200 Nm			
n_a min^{-1}	M_{amax} Nm	F_{Ra} N	$\Phi_{(R)}$ °	i	DRU71SJ_FU	DRU71SJ DRU71MJ_FU DRU80SJ_FU	DRU71MJ DRU80SJ DRU80MJ_FU	DRU90MJ DRU90MJ_FU DRU90LJ_FU
 3								
13	200	5640	6.8	106.38				
14	200	5640	6.8	97.81				
17	200	5640	6.9	83.69				
19	200	5520	6.9	72.54				
21	200	5360	6.9	67.80				
24	200	5020	6.9	58.60				
28	200	4660	7	49.79				
31	200	4420	7	44.46				
37	200	4100	7	37.97				
39	200	3970	7.1	35.57				
47	200	3650	7.1	29.96				
49	200	3580	8.1	28.83				
56	200	3330	8.1	24.99				
60	195	3260	8.2	23.36				
69	185	3110	8.3	20.19				
82	180	2900	8.4	17.15				
91	175	2780	8.5	15.31				
107	165	2650	8.6	13.08				
115	160	2600	11.9	12.14				
133	160	2410	12.2	10.49				
157	160	2200	12.4	8.91				
176	155	2110	12.5	7.96				
206	150	1980	12.8	6.80				
220	145	1950	12.9	6.37				
261	140	1810	13.2	5.36				
352	125	1660	13	3.98				

K37R17, $n_e=1400 \text{ min}^{-1}$					200 Nm	
n_a min^{-1}	M_{amax} Nm	F_{Ra} N	$\Phi_{(R)}$ °	i	DRU71SJ_FU	DRU71MJ_FU DRU80SJ_FU
 3 3						
0.20	200	5640	-	6832		
0.24	200	5640	-	5922		
0.25	200	5640	-	5491		
0.29	200	5640	-	4759		
0.34	200	5640	-	4160		
0.38	200	5640	-	3645		
0.44	200	5640	-	3205		
0.50	200	5640	-	2801		
0.57	200	5640	-	2454		
0.65	200	5640	-	2166		
0.74	200	5640	-	1891		
0.84	200	5640	-	1660		
0.95	200	5640	-	1466		
1.1	200	5640	-	1288		
1.2	200	5640	-	1136		
 3 2						
1.4	200	5640	-	996		
1.6	200	5640	-	876		
1.8	200	5640	-	761		
2.1	200	5640	-	671		
2.4	200	5640	-	585		
2.7	200	5640	-	512		
3.1	200	5640	-	451		
3.5	200	5640	-	396		
4.0	200	5640	-	346		
4.6	200	5640	-	304		
5.2	200	5640	-	267		
6.0	200	5640	-	234		
6.8	200	5640	-	205		
7.7	200	5640	-	181		
8.8	200	5640	-	160		
10	200	5640	-	136		
11	200	5640	-	127		
13	200	5640	-	110		
15	200	5640	-	96		

K39, $n_e=1400 \text{ min}^{-1}$					300 Nm				
n_a min^{-1}	M_{amax} Nm	F_{Ra} N	$\Phi_{(R)}$ °	i	DRU71SJ_FU	DRU71SJ DRU71MJ_FU DRU80SJ_FU	DRU71MJ DRU80SJ DRU80MJ_FU	DRU80MJ DRU90MJ DRU90MJ_FU DRU90LJ_FU	DRU90LJ DRU100MJ_FU
 2									
24	300	7500	-	58.24					
28	300	7440	-	49.69					
32	300	7000	-	43.45					
34	300	6840	-	41.28					
39	300	6440	-	36.22					
46	300	5960	-	30.72					
50	300	5670	-	27.73					
57	300	5330	-	24.40					

K39, $n_e=1400 \text{ min}^{-1}$					300 Nm				
n_a min^{-1}	M_{amax} Nm	F_{Ra} N	$\Phi_{(R)}$ °	i	DRU71SJ_FU	DRU71SJ DRU71MJ_FU DRU80SJ_FU	DRU71MJ DRU80SJ DRU80MJ_FU	DRU80MJ DRU90MJ DRU90MJ_FU DRU90LJ_FU	DRU90LJ DRU100MJ_FU
61	300	5180	-	23.04					
71	295	4820	-	19.62					
79	290	4630	-	17.83					
91	280	4380	-	15.44					
104	270	4160	-	13.44					
110	250	4930	-	12.73					
116	255	4790	-	12.09					
132	285	4360	-	10.61					
156	300	3950	-	9.00					
172	300	3760	-	8.12					
196	300	3530	-	7.15					
207	300	3430	-	6.75					
243	275	3300	-	5.75					
268	260	3240	-	5.22					
310	240	3130	-	4.52					
355	215	3070	-	3.94					
498	170	2870	-	2.81					

K39R17, n _e =1400 min ⁻¹					300 Nm				
n _a min ⁻¹	M _{amax} Nm	F _{Ra} N	Φ _(/R) °	i	DRU71SJ_FU		DRU71MJ_FU DRU80SJ_FU		
 2  3									
0.35	300	7500	-	4057					
0.42	300	7500	-	3370					
0.48	300	7500	-	2906					
0.56	300	7500	-	2508					
0.59	300	7500	-	2367					
0.65	300	7500	-	2162					
0.74	300	7500	-	1881					
0.79	300	7500	-	1762					
0.86	300	7500	-	1622					
0.94	300	7500	-	1494					
1.1	300	7500	-	1321					
1.2	300	7500	-	1169					
1.3	300	7500	-	1093					
 2  2									
1.5	300	7500	-	956					
1.7	300	7500	-	814					
2.0	300	7500	-	711					
2.3	300	7500	-	605					
2.8	300	7500	-	504					
3.1	300	7500	-	454					
3.5	300	7500	-	399					
3.8	300	7500	-	365					
4.5	300	7500	-	312					
4.7	300	7500	-	299					
5.5	300	7500	-	254					
6.0	300	7500	-	234					
6.7	300	7500	-	210					

19391609/DE – 06/2017

K39R17, $n_e=1400 \text{ min}^{-1}$					300 Nm	
n_a min^{-1}	M_{amax} Nm	F_{Ra} N	$\varphi_{(R)}$ °	i	DRU71SJ_FU	DRU71MJ_FU DRU80SJ_FU
7.4	300	7500	-	189		
8.0	300	7500	-	174		
9.0	300	7500	-	156		
9.9	300	7500	-	142		
12	300	7500	-	117		
19	295	7500	-	75		

K47, $n_e=1400 \text{ min}^{-1}$					400 Nm				
n_a min^{-1}	M_{amax} Nm	F_{Ra} N	$\varphi_{(R)}$ °	i	DRU71SJ_FU	DRU71SJ DRU71MJ_FU DRU80SJ_FU	DRU71MJ DRU80SJ DRU80MJ_FU	DRU80MJ DRU90MJ DRU90MJ_FU DRU90LJ_FU	DRU90LJ DRU100MJ_FU
 3									
11	400	5920	6.4	131.87*					
12	400	5920	6.4	121.48*					
13	400	5920	6.4	104.37					
15	400	5920	6.4	90.86					
16	400	5920	6.4	85.12*					
19	400	5920	6.5	75.20*					
20	400	5920	6.5	69.84					
22	400	5920	6.5	63.30*					
25	400	5920	6.5	56.83					
29	400	5920	6.6	48.95*					
30	400	5920	6.6	46.03*					
35	400	5920	6.6	39.61					
40	400	5920	6.7	35.39					
45	400	5700	7.5	31.30					
48	400	5520	7.5	29.32					
54	400	5170	7.6	25.91					
58	400	4970	7.7	24.06					
64	400	4710	7.7	21.81					
72	400	4440	7.7	19.58					
83	380	4220	7.8	16.86					
88	380	4080	7.9	15.86					
103	360	3890	8	13.65					
115	350	3720	8.3	12.19					
119	280	4060	10.5	11.77					
133	280	3830	10.6	10.56					
154	280	3540	10.7	9.10					
164	270	3500	10.8	8.56					
190	250	3380	11	7.36					
213	240	3270	11.5	6.58					
241	230	3140	11.8	5.81					
302	205	2980	12	4.64					

K47R37, $n_e=1400 \text{ min}^{-1}$					400 Nm				
n_a min^{-1}	M_{amax} Nm	F_{Ra} N	$\varphi_{(R)}$ °	i	DRU71SJ_FU	DRU71SJ DRU71MJ_FU DRU80SJ_FU	DRU71MJ DRU80SJ DRU80MJ_FU	DRU90MJ DRU90MJ_FU DRU90LJ_FU	DRU90LJ DRU100MJ_FU
 3  3									
0.14	400	5920	-	10138					
0.16	400	5920	-	8534					

K47R37, $n_e=1400 \text{ min}^{-1}$					400 Nm				
n_a min^{-1}	M_{amax} Nm	F_{Ra} N	$\Phi_{(R)}$ °	i	DRU71SJ_FU	DRU71SJ DRU71MJ_FU DRU80SJ_FU	DRU71MJ DRU80SJ DRU80MJ_FU	DRU90MJ DRU90MJ_FU DRU90LJ_FU	DRU90LJ DRU100MJ_FU
0.18	400	5920	-	7662					
0.21	400	5920	-	6826					
0.23	400	5920	-	5983					
0.27	400	5920	-	5159					
0.30	400	5920	-	4601*					
0.36	400	5920	-	3940					
0.40	400	5920	-	3477					
0.46	400	5920	-	3043					
0.51	400	5920	-	2733					
0.59	400	5920	-	2354					
0.68	400	5920	-	2063					
0.77	400	5920	-	1819					
0.88	400	5920	-	1586					
1.0	400	5920	-	1388					
 3  2									
1.1	400	5920	-	1222					
1.3	400	5920	-	1097					
1.5	400	5920	-	945					
1.7	400	5920	-	831*					
1.9	400	5920	-	718*					
2.2	400	5920	-	639					
2.5	400	5920	-	552					
2.8	400	5920	-	495					
3.3	400	5920	-	426					
3.7	400	5920	-	375					
4.3	400	5920	-	327					
4.8	400	5920	-	289					
5.5	400	5920	-	256					
6.2	400	5920	-	225					
7.1	400	5920	-	198					
8.2	400	5920	-	171					
9.2	400	5920	-	153					
11	400	5920	-	131					
12	400	5920	-	112					
14	400	5920	-	99					
15	400	5920	-	94					

K49, n _e =1400 min ⁻¹					500 Nm					
n _a min ⁻¹	M _{amax} Nm	F _{Ra} N	Φ _(/R) °	i	DRU71SJ_FU	DRU71SJ DRU71MJ_FU DRU80SJ_FU	DRU71MJ DRU80SJ DRU80MJ_FU	DRU80MJ DRU90MJ DRU90MJ_FU DRU90LJ_FU	DRU90LJ DRU100MJ_FU	DRU100MJ DRU100LJ DRU100LJ_FU
 2										
19	475	9000	-	75.20						
20	445	9000	-	70.19						
23	500	9000	-	60.27						
26	500	8590	-	52.94						
28	500	8380	-	50.29						
32	500	7900	-	44.44						
37	500	7310	-	37.98						
40	500	7000	-	34.81						

K49, $n_e=1400 \text{ min}^{-1}$						500 Nm				
n_a min^{-1}	M_{amax} Nm	F_{Ra} N	$\varphi_{(R)}$ °	i	DRU71SJ_FU	DRU71SJ DRU71MJ_FU DRU80SJ_FU	DRU71MJ DRU80SJ DRU80MJ_FU	DRU80MJ DRU90MJ DRU90MJ_FU DRU90LJ_FU	DRU90LJ DRU100MJ_FU	DRU100MJ DRU100LJ DRU100LJ_FU
46	500	6550	-	30.55						
48	500	6370	-	28.95						
55	500	5940	-	25.34						
61	500	5610	-	22.83						
70	500	5220	-	20.03						
79	500	4860	-	17.67						
89	490	4590	-	15.67						
105	470	4320	-	13.38						
123	495	5000	-	11.37						
134	480	4860	-	10.42						
153	500	4460	-	9.14						
162	500	4340	-	8.66						
185	500	4050	-	7.58						
205	500	3840	-	6.83						
234	500	3570	-	5.99						
265	485	3400	-	5.29						
299	465	3270	-	4.69						
350	440	3110	-	4.00						

K49R37, $n_e=1400 \text{ min}^{-1}$						500 Nm				
n_a min^{-1}	M_{amax} Nm	F_{Ra} N	$\varphi_{(R)}$ °	i	DRU71SJ_FU	DRU71SJ DRU71MJ_FU DRU80SJ_FU	DRU71MJ DRU80SJ DRU80MJ_FU	DRU90MJ DRU90MJ_FU DRU90LJ_FU	DRU90LJ DRU100MJ_FU	
 2  3										
0.20	500	9000	-	7137						
0.23	500	9000	-	5991						
0.27	500	9000	-	5120						
0.35	500	9000	-	4034						
0.39	500	9000	-	3580						
0.45	500	9000	-	3081						
0.50	500	9000	-	2773						
0.55	500	9000	-	2545						
0.59	500	9000	-	2372						
0.66	500	9000	-	2118						
0.72	500	9000	-	1941						
0.80	500	9000	-	1741						
0.86	500	9000	-	1632						
0.92	500	9000	-	1521						
1.1	500	9000	-	1228						
1.4	500	9000	-	1000						
 2  2										
0.98	500	9000	-	1424						
1.1	500	9000	-	1309						
1.2	500	9000	-	1120						
1.5	500	9000	-	908						
1.7	500	9000	-	802						
2.0	500	9000	-	701						
2.2	500	9000	-	645						
2.4	500	9000	-	595						
2.6	500	9000	-	543						

K49R37, $n_e=1400 \text{ min}^{-1}$ **500 Nm**

n_a min^{-1}	M_{amax} Nm	F_{Ra} N	$\Phi_{(R)}$ °	i	DRU71SJ_FU	DRU71SJ DRU71MJ_FU DRU80SJ_FU	DRU71MJ DRU80SJ DRU80MJ_FU	DRU90MJ DRU90MJ_FU DRU90LJ_FU	DRU90LJ DRU100MJ_FU
2.8	500	9000	-	501					
3.1	500	9000	-	449					
3.5	500	9000	-	401					
3.9	500	9000	-	360					
4.2	500	9000	-	330					
4.7	500	9000	-	300					
5.1	500	9000	-	274					
5.8	500	9000	-	243					
6.5	500	9000	-	217					
7.3	500	9000	-	193					
8.0	500	9000	-	176					
9.2	500	9000	-	152					
11	500	9000	-	125					
14	500	9000	-	99					

K57, $n_e=1400 \text{ min}^{-1}$ **600 Nm**

n_a min^{-1}	M_{amax} Nm	F_{Ra} N	$\Phi_{(R)}$ °	i	DRU71SJ_FU	DRU71SJ DRU71MJ_FU DRU80SJ_FU	DRU71MJ DRU80SJ DRU80MJ_FU	DRU80MJ DRU90MJ DRU90MJ_FU DRU90LJ_FU	DRU90LJ DRU100MJ_FU
 3									
9.6	600	7630	5.9	145.14*					
11	600	7630	5.9	123.85					
13	600	7630	5.9	108.29					
14	600	7630	5.9	102.88*					
16	600	7630	5.9	90.26*					
18	600	7630	5.9	76.56*					
20	600	7630	6	69.12					
23	600	7630	6	60.81*					
24	600	7630	6	57.42*					
29	600	7630	6	48.89					
32	600	7630	6.1	44.43					
36	600	7630	6.1	38.49					
39	600	7630	6.8	35.70					
46	600	7300	6.9	30.28					
51	600	6930	6.9	27.34					
58	600	6480	6.9	24.05					
62	600	6280	6.9	22.71					
72	575	5910	7	19.34					
80	555	5740	7.2	17.57					
92	535	5430	7.3	15.22					
106	510	5190	7.4	13.25					
117	415	5150	9.4	11.92					
124	415	4990	9.5	11.26					
146	405	4650	9.6	9.59					
161	390	4520	10	8.71					
185	365	4360	10.2	7.55					
213	345	4180	10.4	6.57					
299	300	3800	11	4.69					

K57R37, $n_e=1400 \text{ min}^{-1}$					600 Nm				
n_a min^{-1}	M_{amax} Nm	F_{Ra} N	$\Phi_{(R)}$ °	i	DRU71SJ_FU	DRU71SJ DRU71MJ_FU DRU80SJ_FU	DRU71MJ DRU80SJ DRU80MJ_FU	DRU90MJ DRU90MJ_FU DRU90LJ_FU	DRU90LJ DRU100MJ_FU
 3 3									
0.12	600	7630	-	12169					
0.13	600	7630	-	11162*					
0.15	600	7630	-	9503					
0.16	600	7630	-	8547					
0.19	600	7630	-	7277					
0.22	600	7630	-	6478*					
0.25	600	7630	-	5662*					
0.28	600	7630	-	5033					
0.32	600	7630	-	4340					
0.36	600	7630	-	3854					
0.41	600	7630	-	3390					
0.48	600	7630	-	2924					
0.54	600	7630	-	2593					
0.62	600	7630	-	2249					
0.70	600	7630	-	1986					
 3 2									
0.80	600	7630	-	1743					
0.91	600	7630	-	1539					
1.0	600	7630	-	1354					
1.2	600	7630	-	1174					
1.4	600	7630	-	1036*					
1.5	600	7630	-	906*					
1.7	600	7630	-	806					
2.0	600	7630	-	699					
2.3	600	7630	-	615					
2.6	600	7630	-	544*					
3.0	600	7630	-	473					
3.3	600	7630	-	421					
3.9	600	7630	-	362					
4.4	600	7630	-	319					
5.0	600	7630	-	280					
5.7	600	7630	-	246					
6.5	600	7630	-	215					
7.3	600	7630	-	192					
8.4	600	7630	-	166					
9.7	600	7630	-	145					
11	600	7630	-	129					
13	600	7630	-	111					
14	600	7630	-	97					

K67, $n_e=1400 \text{ min}^{-1}$					820 Nm				
n_a min^{-1}	M_{amax} Nm	F_{Ra} N	$\Phi_{(R)}$ °	i	DRU71SJ_FU	DRU71SJ DRU71MJ_FU DRU80SJ_FU	DRU71MJ DRU80SJ DRU80MJ_FU	DRU80MJ DRU90MJ DRU90MJ_FU DRU90LJ_FU	DRU90LJ DRU100MJ_FU
 3									
9.7	820	10300	6.2	144.79*					
11	820	10300	6.2	123.54					
13	820	10300	6.1	108.03					

K67, $n_e=1400 \text{ min}^{-1}$						820 Nm			
n_a min^{-1}	M_{amax} Nm	F_{Ra} N	$\Phi_{(R)}$ °	i	DRU71SJ_FU	DRU71SJ DRU71MJ_FU DRU80SJ_FU	DRU71MJ DRU80SJ DRU80MJ_FU	DRU80MJ DRU90MJ DRU90MJ_FU DRU90LJ_FU	DRU90LJ DRU100MJ_FU
14	820	10300	6.1	102.62					
16	820	10300	6.2	90.04					
18	820	10300	6.2	76.37					
20	820	10300	6.2	68.95					
23	820	10300	6.2	60.66					
24	820	10300	6.2	57.28					
29	820	10300	6.3	48.77					
32	820	10300	6.3	44.32					
36	800	10500	6.4	38.39					
39	820	10300	7.1	35.62					
46	820	10300	7.1	30.22					
51	820	10300	7.1	27.28					
58	800	10500	7.2	24.00					
62	780	10700	7.2	22.66					
73	760	10800	7.3	19.30					
80	740	11000	7.5	17.54					
92	700	11300	7.5	15.19					
106	670	11500	7.6	13.22					
112	530	12300	8.6	12.48					
132	500	11800	8.8	10.63					
145	480	11500	9.1	9.66					
167	440	11100	9.3	8.37					
192	420	10700	9.4	7.28					
269	350	9860	10	5.20					

K67R37, $n_e=1400 \text{ min}^{-1}$						820 Nm			
n_a min^{-1}	M_{amax} Nm	F_{Ra} N	$\Phi_{(R)}$ °	i	DRU71SJ_FU	DRU71SJ DRU71MJ_FU DRU80SJ_FU	DRU71MJ DRU80SJ DRU80MJ_FU	DRU90MJ DRU90MJ_FU DRU90LJ_FU	DRU90LJ DRU100MJ_FU
 3  3									
0.12	820	10300	-	12139					
0.13	820	10300	-	11134					
0.15	820	10300	-	9479					
0.17	820	10300	-	8173					
0.19	820	10300	-	7259					
0.22	820	10300	-	6462					
0.25	820	10300	-	5648					
0.29	820	10300	-	4846					
0.32	820	10300	-	4329					
0.37	820	10300	-	3750					
0.42	820	10300	-	3315					
0.48	820	10300	-	2917					
0.55	820	10300	-	2532					
0.62	820	10300	-	2244					
0.71	820	10300	-	1981					
 3  2									
0.81	820	10300	-	1739					
0.91	820	10300	-	1535					
1.0	820	10300	-	1351					
1.2	820	10300	-	1171					

K67R37, $n_e=1400 \text{ min}^{-1}$						820 Nm			
n_a min^{-1}	M_{amax} Nm	F_{Ra} N	$\Phi_{(R)}$ °	i	DRU71SJ_FU	DRU71SJ DRU71MJ_FU DRU80SJ_FU	DRU71MJ DRU80SJ DRU80MJ_FU	DRU90MJ DRU90MJ_FU DRU90LJ_FU	DRU90LJ DRU100MJ_FU
1.4	820	10300	-	1034					
1.6	820	10300	-	903					
1.8	820	10300	-	793					
2.0	820	10300	-	697					
2.3	820	10300	-	613					
2.6	820	10300	-	542					
3.0	820	10300	-	471					
3.3	820	10300	-	420					
3.9	820	10300	-	361					
4.3	820	10300	-	323					
5.0	820	10300	-	279					
5.7	820	10300	-	246					
6.5	820	10300	-	217					
7.3	820	10300	-	191					
8.4	820	10300	-	166					
9.7	820	10300	-	144					
11	820	10300	-	122					

K77, n _e =1400 min ⁻¹					1550 Nm					
n _a min ⁻¹	M _{amax} Nm	F _{Ra} N	Φ _(/R) °	i	DRU71SJ_FU	DRU71SJ DRU71MJ_FU DRU80SJ_FU	DRU71MJ DRU80SJ DRU80MJ_FU	DRU80MJ DRU90MJ DRU90MJ_FU DRU90LJ_FU	DRU90LJ DRU100MJ_FU	DRU100MJ DRU100LJ DRU100LJ_FU
 3										
7.3	1450	16100	5.4	192.18						
7.8	1450	16100	5.4	179.37						
9.1	1550	15400	5.4	154.02						
10	1550	15400	5.4	135.28						
11	1550	15400	5.4	128.52						
12	1550	15400	5.4	113.56						
14	1550	15400	5.4	97.05						
16	1550	15400	5.4	88.97						
18	1550	15400	5.4	78.07						
19	1550	15400	5.4	73.99						
22	1550	15400	5.5	64.75						
24	1550	15400	5.5	58.34						
27	1550	15400	5.5	51.18						
31	1550	15400	5.5	45.16						
35	1550	15400	5.6	40.04						
36	1500	15700	6	38.39						
40	1550	15400	6	35.20						
45	1550	15400	6.1	30.89						
48	1550	15400	6.1	29.27						
55	1550	15400	6.1	25.62						
61	1550	15400	6.3	23.08						
69	1500	15700	6.3	20.25						
78	1450	16100	6.3	17.87						
88	1400	15500	6.4	15.84						
104	1340	14800	6.5	13.52						
113	1000	15100	7.9	12.36						
129	990	14400	7.8	10.84						

K77, $n_e=1400 \text{ min}^{-1}$						1550 Nm				
n_a min^{-1}	M_{amax} Nm	F_{Ra} N	$\varphi_{(R)}$ °	i	DRU71SJ_FU	DRU71SJ DRU71MJ_FU DRU80SJ_FU	DRU71MJ DRU80SJ DRU80MJ_FU	DRU80MJ DRU90MJ DRU90MJ_FU DRU90LJ_FU	DRU90LJ DRU100MJ_FU	DRU100MJ DRU100LJ DRU100LJ_FU
146	940	13900	7.9	9.56						
165	890	13500	8.2	8.48						
193	820	13100	8.3	7.24						

K77R37, $n_e=1400 \text{ min}^{-1}$						1550 Nm				
n_a min^{-1}	M_{amax} Nm	F_{Ra} N	$\varphi_{(R)}$ °	i	DRU71SJ_FU	DRU71SJ DRU71MJ_FU DRU80SJ_FU	DRU71MJ DRU80SJ DRU80MJ_FU	DRU90MJ DRU90MJ_FU DRU90LJ_FU	DRU90LJ DRU100MJ_FU	
 3  3										
0.09	1550	15400	-	15310						
0.10	1550	15400	-	14043						
0.12	1550	15400	-	11955						
0.14	1550	15400	-	10217						
0.16	1550	15400	-	8809						
0.19	1550	15400	-	7528						
0.21	1550	15400	-	6606						
0.24	1550	15400	-	5774						
0.28	1550	15400	-	5089						
0.31	1550	15400	-	4489						
0.35	1550	15400	-	3961						
0.40	1550	15400	-	3485						
0.48	1550	15400	-	2901						
0.52	1550	15400	-	2717						
0.59	1550	15400	-	2370						
 3  2										
0.68	1550	15400	-	2050						
0.79	1550	15400	-	1772						
0.92	1550	15400	-	1514						
1.0	1550	15400	-	1388						
1.1	1550	15400	-	1218						
1.3	1550	15400	-	1053						
1.5	1550	15400	-	924						
1.7	1550	15400	-	815						
2.0	1550	15400	-	709						
2.3	1550	15400	-	622						
2.5	1550	15400	-	552						
2.9	1550	15400	-	485						
3.3	1550	15400	-	428						
3.8	1550	15400	-	367						
4.3	1550	15400	-	328						
4.8	1550	15400	-	290						
5.6	1550	15400	-	252						
6.3	1550	15400	-	221						
7.2	1550	15400	-	195						
8.0	1550	15400	-	175						
9.1	1550	15400	-	154						

K87, $n_e=1400 \text{ min}^{-1}$					2700 Nm				
n_a min^{-1}	M_{amax} Nm	F_{Ra} N	$\Phi_{(R)}$ °	i	DRU71MJ_FU DRU80SJ_FU	DRU71MJ DRU80SJ DRU80MJ_FU	DRU80MJ DRU90MJ DRU90MJ_FU DRU90LJ_FU	DRU90LJ DRU100MJ_FU	DRU100MJ DRU100LJ DRU100LJ_FU
 3									
7.1	2700	27300	5.3	197.37					
8.0	2700	27300	5.3	174.19					
8.5	2700	27300	5.3	164.34*					
9.5	2700	27300	5.4	147.32*					
11	2700	27300	5.4	126.91*					
12	2700	27300	5.4	115.82					
14	2700	27300	5.4	102.71*					
16	2700	27300	5.4	86.34					
18	2700	27300	5.4	79.34					
20	2700	27300	5.4	70.46					
22	2700	26200	5.4	63.00*					
25	2700	25000	5.5	56.64					
28	2700	23500	5.5	49.16					
32	2600	22800	5.5	44.02					
38	2500	21400	5.5	36.52*					
45	2700	19200	6.1	31.39					
50	2600	18500	6.1	27.88					
56	2500	18000	6.1	24.92					
62	2300	17900	6.2	22.41					
72	2300	16800	6.3	19.45					
80	2200	16300	6.3	17.42					
88	1800	16000	6.5	16.00					
97	2100	15300	6.4	14.45					
111	2000	14800	6.5	12.56					
125	1500	14900	6.7	11.17					
140	1500	14200	6.8	10.00					
169	1400	13500	7	8.29					
194	1300	13200	7.1	7.21					

K87R57, $n_e=1400 \text{ min}^{-1}$					2700 Nm				
n_a min^{-1}	M_{amax} Nm	F_{Ra} N	$\Phi_{(R)}$ °	i	DRU71SJ_FU	DRU71SJ DRU71MJ_FU DRU80SJ_FU	DRU71MJ DRU80SJ DRU80MJ_FU	DRU80MJ DRU90MJ DRU90MJ_FU DRU90LJ_FU	DRU90LJ DRU100MJ_FU
 3  3									
0.09	2700	27300	-	14829					
0.11	2700	27300	-	13168					
0.12	2700	27300	-	11737					
0.14	2700	27300	-	10217					
0.15	2700	27300	-	9073					
0.18	2700	27300	-	7854					
0.20	2700	27300	-	6832					
0.24	2700	27300	-	5930					
0.27	2700	27300	-	5240					
0.31	2700	27300	-	4562					
0.35	2700	27300	-	4037					
0.39	2700	27300	-	3609					
0.45	2700	27300	-	3107					
0.51	2700	27300	-	2728					

K87R57, $n_e=1400 \text{ min}^{-1}$					2700 Nm				
n_a min^{-1}	M_{amax} Nm	F_{Ra} N	$\Phi_{(R)}$ °	i	DRU71SJ_FU	DRU71SJ DRU71MJ_FU DRU80SJ_FU	DRU71MJ DRU80SJ DRU80MJ_FU	DRU80MJ DRU90MJ DRU90MJ_FU DRU90LJ_FU	DRU90LJ DRU100MJ_FU
0.59	2700	27300	-	2371					
 3  2									
0.67	2700	27300	-	2088					
0.76	2700	27300	-	1854					
0.84	2700	27300	-	1657					
0.99	2700	27300	-	1415					
1.1	2700	27300	-	1229					
1.3	2700	27300	-	1078					
1.5	2700	27300	-	951					
1.7	2700	27300	-	837					
1.9	2700	27300	-	726					
2.2	2700	27300	-	638					
2.5	2700	27300	-	562*					
3.0	2700	27300	-	474*					
3.3	2700	27300	-	426					
3.8	2700	27300	-	373					
4.2	2700	27300	-	330					
4.8	2700	27300	-	294					
5.6	2700	27300	-	250					
5.9	2700	27300	-	236					
7.0	2700	27300	-	201					
7.7	2700	27300	-	183					
8.8	2700	27300	-	159					
9.9	2600	27400	-	141					

K97, $n_e=1400 \text{ min}^{-1}$					4300 Nm				
n_a min^{-1}	M_{amax} Nm	F_{Ra} N	$\Phi_{(R)}$ °	i	DRU71MJ_FU DRU80SJ_FU	DRU71MJ DRU80SJ DRU80MJ_FU	DRU80MJ DRU90MJ DRU90MJ_FU DRU90LJ_FU	DRU90LJ DRU100MJ_FU	DRU100MJ DRU100LJ DRU100LJ_FU
 3									
8.0	4300	40000	6.8	176.05*					
9.1	4300	40000	6.8	153.21*					
10.0	4300	40000	6.8	140.28					
11	4300	40000	6.8	123.93*					
13	4300	40000	6.8	105.13					
14	4300	40000	6.8	96.80					
16	4300	38800	6.8	86.52					
18	4300	37100	6.8	77.89*					
20	4300	35600	6.9	70.54					
22	4300	33800	6.9	62.55					
25	4300	32300	6.9	56.55					
29	4300	30000	6.9	47.93*					
33	4300	28300	6.9	41.87					
37	4300	27100	7.4	38.30					
41	4300	25700	7.5	34.23					
45	4300	24500	7.5	30.82					
50	4300	23300	7.5	27.91					
57	4300	22000	7.6	24.75					
63	4300	20900	7.6	22.37					


K97, $n_e=1400 \text{ min}^{-1}$										4300 Nm
n_a min^{-1}	M_{amax} Nm	F_{Ra} N	$\varphi_{(R)}$ °	i	DRU71MJ_FU DRU80SJ_FU	DRU71MJ DRU80SJ DRU80MJ_FU	DRU80MJ DRU90MJ DRU90MJ_FU DRU90LJ_FU	DRU90LJ DRU100MJ_FU	DRU100MJ DRU100LJ DRU100LJ_FU	
74	4300	19100	7.6	18.96						
85	4300	17800	7.7	16.56						
101	4300	16100	7.7	13.85						
117	3890	16200	7.8	11.99						
134	2870	16400	9.7	10.41						
161	2660	15800	9.8	8.71						
186	2400	15700	10	7.54						


K97R57, $n_e=1400 \text{ min}^{-1}$										4300 Nm
n_a min^{-1}	M_{amax} Nm	F_{Ra} N	$\varphi_{(R)}$ °	i	DRU71SJ_FU	DRU71SJ DRU71MJ_FU DRU80SJ_FU	DRU71MJ DRU80SJ DRU80MJ_FU	DRU80MJ DRU90MJ DRU90MJ_FU DRU90LJ_FU	DRU90LJ DRU100MJ_FU	
 3 										
0.08	4300	40000	-	18091						
0.08	4300	40000	-	16666						
0.09	4300	40000	-	14897						
0.11	4300	40000	-	13182						
0.12	4300	40000	-	11677						
0.14	4300	40000	-	10317						
0.15	4300	40000	-	9083						
0.17	4300	40000	-	8054						
0.20	4300	40000	-	6970						
0.23	4300	40000	-	6027						
0.26	4300	40000	-	5391						
0.30	4300	40000	-	4669						
0.34	4300	40000	-	4082						
0.39	4300	40000	-	3583						
0.45	4300	40000	-	3108*						
0.51	4300	40000	-	2757						
 3 										
0.58	4300	40000	-	2419						
0.66	4300	40000	-	2123						
0.75	4300	40000	-	1856						
0.86	4300	40000	-	1625						
0.98	4300	40000	-	1430						
1.1	4300	40000	-	1261						
1.3	4300	40000	-	1102						
1.5	4300	40000	-	957						
1.6	4300	40000	-	855						
1.9	4300	40000	-	743						
2.1	4300	40000	-	652*						
2.4	4300	40000	-	573						
2.8	4300	40000	-	504						
3.2	4300	40000	-	437						
3.7	4300	40000	-	382*						
4.1	4300	40000	-	342*						
4.6	4300	40000	-	305						
5.4	4300	40000	-	258						


K97R57, $n_e=1400 \text{ min}^{-1}$					4300 Nm				
n_a min^{-1}	M_{amax} Nm	F_{Ra} N	$\phi_{(R)}$ °	i	DRU71SJ_FU	DRU71SJ DRU71MJ_FU DRU80SJ_FU	DRU71MJ DRU80SJ DRU80MJ_FU	DRU80MJ DRU90MJ DRU90MJ_FU DRU90LJ_FU	DRU90LJ DRU100MJ_FU
6.0	4300	40000	-	232					
7.0	4300	40000	-	199					

10.2 Auswahltabellen K..DRU...J (IE4), 50 Hz


P_m = 0.18 kW										
n_a min ⁻¹ 50Hz	n_a min ⁻¹ 10-50Hz	M_a Nm	i	$F_{Ra}^{1)}$ N	SEW f_B					m kg 
-	2.1 - 10	166	144.79*	13000	4.9	K	67	DRU	71SJ4	36 606
						KF	67	DRU	71SJ4	42 607
						KA	67	DRU	71SJ4	34 608
						KAF	67	DRU	71SJ4	39 607
-	2.1 - 10	166	145.14*	9740	3.6	K	57	DRU	71SJ4	31 600
12	2.4 - 12	142	123.85	9810	4.2	KF	57	DRU	71SJ4	35 601
14	2.8 - 14	124	108.29	9860	4.8	KA	57	DRU	71SJ4	29 602
						KAF	57	DRU	71SJ4	34 601
-	2.3 - 11	151	131.87*	8000	2.6	K	47	DRU	71SJ4	25 590
-	2.5 - 12	139	121.48*	8050	2.9					
14	2.9 - 14	120	104.37	8110	3.3					
17	3.3 - 17	104	90.86	8160	3.8					
18	3.5 - 18	98	85.12*	8170	4.1					
20	4.0 - 20	86	75.20*	8200	4.6	KAF	47	DRU	71SJ4	27 591
-	2.8 - 14	122	106.38	6320	1.65	K	37	DRU	71SJ4	19 580
-	3.1 - 15	112	97.81	6380	1.80					
18	3.6 - 18	96	83.69	6460	2.1					
21	4.1 - 21	83	72.54	6420	2.4					
22	4.4 - 22	78	67.80	6310	2.6					
26	5.1 - 26	67	58.60	6070	3.0					
30	6.0 - 30	57	49.79	5810	3.5					
34	6.7 - 34	51	44.46	5630	3.9					
40	7.9 - 40	44	37.97	5390	4.6					
42	8.4 - 42	41	35.57	5290	4.9					
-	5.5 - 27	57	54.89	5300	2.3	K	29	DRU	71SJ4	12 573
-	6.0 - 30	52	50.35	5320	2.5					
35	7.0 - 35	45	42.87	5350	2.9					
41	8.1 - 41	38	36.96	5260	3.2					
50	10.0 - 50	31	30.11	4960	3.7					
-	6.7 - 34	46	44.48	4470	1.50	K	19	DRU	71SJ4	11 567
-	7.4 - 37	42	40.63	4500	1.60					
44	8.7 - 44	36	34.29	4500	1.80					
51	10 - 51	31	29.29	4460	2.0					
55	11 - 55	28	27.16	4370	2.1					
-	12 - 62	26	24.06	4270	3.1					
-	14 - 68	23	21.98	4160	3.4					
81	16 - 81	20	18.55	3950	4.0					
95	19 - 95	17	15.84	3770	4.8					
102	20 - 102	16	14.69	3680	5.1					
118	24 - 118	14	12.70	3520	5.9					
127	25 - 127	13	11.84	3450	6.3					
145	29 - 145	11	10.32	3310	6.9					
-	31 - 157	10	9.58	3250	6.0					
185	37 - 185	8.8	8.09	3080	9.1					

P_m = 0.25 kW										
n_a min ⁻¹ 50Hz	n_a min ⁻¹ 10-50Hz	M_a Nm	i	$F_{Ra}^{1)}$ N	SEW f_B					m kg 
-	1.6 - 7.8	305	192.18	20000	4.7	K	77	DRU	71SJ4	63 612
						KF	77	DRU	71SJ4	71 613
						KA	77	DRU	71SJ4	55 614
						KAF	77	DRU	71SJ4	63 613
-	2.1 - 10	230	144.79*	13000	3.6	K	67	DRU	71SJ4	36 606
12	2.4 - 12	197	123.54	13000	4.2	KF	67	DRU	71SJ4	42 607
14	2.8 - 14	172	108.03	13000	4.8	KA	67	DRU	71SJ4	34 608
						KAF	67	DRU	71SJ4	39 607

P_m = 0.25 kW											
n_a min⁻¹ 50Hz	n_a min⁻¹ 10-50Hz	M_a Nm	i	F_{Ra}¹⁾ N	SEW f_B					m kg	
-	2.1 - 10	230	145.14*	9530	2.6	K	57	DRU	71SJ4	31	600
12	2.4 - 12	197	123.85	9640	3.0						
14	2.8 - 14	172	108.29	9720	3.5						
15	2.9 - 15	164	102.88*	9740	3.7						
17	3.3 - 17	144	90.26*	9800	4.2						
20	3.9 - 20	122	76.56*	9860	4.9						
-	4.0 - 20	120	75.20	9000	4.0	K	49	DRU	71SJ4	37	596
-	4.3 - 21	112	70.19	9000	4.0						
-	2.3 - 11	205	131.87*	7720	1.90	K	47	DRU	71SJ4	25	590
-	2.5 - 12	193	121.48*	7810	2.1						
14	2.9 - 14	166	104.37	7940	2.4						
17	3.3 - 17	145	90.86	8030	2.8						
18	3.5 - 18	136	85.12*	8060	3.0						
20	4.0 - 20	120	75.20*	8110	3.3						
21	4.3 - 21	111	69.84	8140	3.6						
24	4.7 - 24	101	63.30*	8170	4.0						
26	5.3 - 26	90	56.83	8190	4.4						
-	5.2 - 26	93	58.24	7500	3.2	K	39	DRU	71SJ4	24	586
30	6.0 - 30	79	49.69	7500	3.8						
-	2.8 - 14	169	106.38	5960	1.20	K	37	DRU	71SJ4	19	580
-	3.1 - 15	156	97.81	6070	1.30						
18	3.6 - 18	133	83.69	6240	1.50						
21	4.1 - 21	115	72.54	6120	1.75						
22	4.4 - 22	108	67.80	6030	1.85						
26	5.1 - 26	93	58.60	5830	2.1						
30	6.0 - 30	79	49.79	5610	2.5						
34	6.7 - 34	71	44.46	5450	2.8						
40	7.9 - 40	60	37.97	5230	3.3						
42	8.4 - 42	57	35.57	5140	3.5						
50	10 - 50	48	29.96	4910	4.2						
52	10 - 52	46	28.83	4860	4.4						
-	5.5 - 27	79	54.89	5220	1.65	K	29	DRU	71SJ4	12	573
-	6.0 - 30	73	50.35	5240	1.80						
35	7.0 - 35	62	42.87	5280	2.1						
41	8.1 - 41	53	36.96	5110	2.3						
50	10.0 - 50	44	30.11	4840	2.6						
-	10 - 51	44	29.69	4860	3.0						
-	11 - 55	40	27.23	4740	3.2						
60	12 - 60	36	24.91	4590	3.0						
65	13 - 65	34	23.19	4530	3.8						
68	14 - 68	32	22.08	4440	3.3						
-	6.7 - 34	64	44.48	4370	1.05	K	19	DRU	71SJ4	11	567
-	7.4 - 37	59	40.63	4400	1.15						
44	8.7 - 44	50	34.29	4460	1.30						
51	10 - 51	42	29.29	4320	1.45						
55	11 - 55	39	27.16	4240	1.55						
-	12 - 62	36	24.06	4170	2.2						
-	14 - 68	32	21.98	4060	2.5						
81	16 - 81	27	18.55	3870	2.9						
95	19 - 95	23	15.84	3700	3.4						
102	20 - 102	22	14.69	3620	3.7						
118	24 - 118	19	12.70	3470	4.3						
127	25 - 127	18	11.84	3400	4.5						
145	29 - 145	15	10.32	3260	5.0						
-	31 - 157	14	9.58	3220	4.3						
185	37 - 185	12	8.09	3050	6.5						
217	43 - 217	10	6.91	2910	7.7						
234	47 - 234	9.7	6.41	2840	8.3						
271	54 - 271	8.4	5.54	2710	9.6						


P _m = 0.37 kW											
n _a min ⁻¹ 50Hz	n _a min ⁻¹ 10-50Hz	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
-	1.9 - 9.7	360	154.02	19900	4.3	K	77	DRU	71MJ4	63	612
11	2.2 - 11	315	135.28	20000	4.9	KF	77	DRU	71MJ4	71	613
						KA	77	DRU	71MJ4	55	614
						KAF	77	DRU	71MJ4	63	613
-	2.4 - 12	290	123.54	13000	2.8	K	67	DRU	71MJ4	36	606
14	2.8 - 14	250	108.03	13000	3.2	KF	67	DRU	71MJ4	42	607
15	2.9 - 15	240	102.62	13000	3.4	KA	67	DRU	71MJ4	34	608
17	3.3 - 17	210	90.04	13000	3.9	KAF	67	DRU	71MJ4	39	607
20	3.9 - 20	180	76.37	13000	4.6						
-	2.4 - 12	290	123.85	9320	2.1						
14	2.8 - 14	255	108.29	9450	2.4						
15	2.9 - 15	240	102.88*	9490	2.5	K	57	DRU	71MJ4	31	600
17	3.3 - 17	210	90.26*	9590	2.8	KF	57	DRU	71MJ4	35	601
20	3.9 - 20	180	76.56*	9690	3.3	KA	57	DRU	71MJ4	29	602
22	4.3 - 22	163	69.12	9750	3.7	KAF	57	DRU	71MJ4	34	601
25	4.9 - 25	143	60.81*	9800	4.2						
26	5.2 - 26	135	57.42*	9830	4.4						
-	5.0 - 25	142	60.27	9000	3.5	K	49	DRU	71MJ4	37	596
						KF	49	DRU	71MJ4	39	597
						KA	49	DRU	71MJ4	35	598
						KAF	49	DRU	71MJ4	39	597
-	2.9 - 14	245	104.37	7490	1.65						
17	3.3 - 17	210	90.86	7690	1.85						
18	3.5 - 18	200	85.12*	7770	2.0						
20	4.0 - 20	177	75.20*	7890	2.3						
21	4.3 - 21	164	69.84	7940	2.4	K	47	DRU	71MJ4	25	590
24	4.7 - 24	149	63.30*	8010	2.7	KF	47	DRU	71MJ4	28	591
26	5.3 - 26	134	56.83	8060	3.0	KA	47	DRU	71MJ4	24	592
31	6.1 - 31	115	48.95*	8120	3.5	KAF	47	DRU	71MJ4	27	591
33	6.5 - 33	108	46.03*	8140	3.7						
38	7.6 - 38	93	39.61	8180	4.3						
42	8.5 - 42	83	35.39	8210	4.8						
-	6.0 - 30	117	49.69	7500	2.6	K	39	DRU	71MJ4	24	586
35	6.9 - 35	102	43.45	7500	2.9	KF	39	DRU	71MJ4	25	587
36	7.3 - 36	97	41.28	7500	3.1	KA	39	DRU	71MJ4	23	588
41	8.3 - 41	85	36.22	7500	3.5	KAF	39	DRU	71MJ4	24	587
-	3.6 - 18	197	83.69	5670	1.00						
21	4.1 - 21	171	72.54	5620	1.15						
22	4.4 - 22	160	67.80	5560	1.25						
26	5.1 - 26	138	58.60	5430	1.45						
30	6.0 - 30	117	49.79	5260	1.70						
34	6.7 - 34	105	44.46	5140	1.90						
40	7.9 - 40	89	37.97	4970	2.2	K	37	DRU	71MJ4	19	580
42	8.4 - 42	84	35.57	4900	2.4	KF	37	DRU	71MJ4	21	581
50	10 - 50	71	29.96	4700	2.8	KA	37	DRU	71MJ4	18	582
-	10 - 52	68	28.83	4660	3.0	KAF	37	DRU	71MJ4	20	581
60	12 - 60	59	24.99	4490	3.4						
64	13 - 64	55	23.36	4420	3.5						
74	15 - 74	48	20.19	4250	3.9						
87	17 - 87	40	17.15	4070	4.5						
98	20 - 98	36	15.31	3940	4.8						
-	7.0 - 35	92	42.87	5020	1.40						
41	8.1 - 41	79	36.96	4860	1.55						
50	10.0 - 50	64	30.11	4630	1.80	K	29	DRU	71MJ4	12	573
60	12 - 60	53	24.91	4420	2.0	KF	29	DRU	71MJ4	14	577
-	13 - 65	51	23.19	4380	2.6	KA	29	DRU	71MJ4	12	579
68	14 - 68	47	22.08	4280	2.2	KAF	29	DRU	71MJ4	13	577
75	15 - 75	44	19.99	4210	3.0						
92	18 - 92	36	16.29	3980	3.6						

P_m = 0.37 kW

n _a min ⁻¹ 50Hz	n _a min ⁻¹ 10-50Hz	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
-	8.7 - 44	73	34.29	4190	0.85						
51	10 - 51	63	29.29	4060	0.95						
55	11 - 55	58	27.16	4000	1.05						
-	16 - 81	41	18.55	3740	1.95						
95	19 - 95	35	15.84	3590	2.3						
102	20 - 102	32	14.69	3520	2.5						
118	24 - 118	28	12.70	3380	2.9	K	19	DRU	71MJ4	11	567
127	25 - 127	26	11.84	3310	3.0	KF	19	DRU	71MJ4	11	570
145	29 - 145	23	10.32	3190	3.4	KA	19	DRU	71MJ4	11	572
-	37 - 185	18	8.09	3010	4.4	KAF	19	DRU	71MJ4	11	570
217	43 - 217	15	6.91	2870	5.2						
234	47 - 234	14	6.41	2800	5.6						
271	54 - 271	12	5.54	2680	6.5						
291	58 - 291	12	5.16	2620	6.9						
333	67 - 333	10	4.50	2510	8.0						


10


P_m = 0.55 kW


n _a min ⁻¹ 50Hz	n _a min ⁻¹ 10-50Hz	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
-	1.5 - 7.6	690	197.37	28900	3.9	K	87	DRU	80SJ4	105	618
8.6	1.7 - 8.6	605	174.19	29000	4.4	KF	87	DRU	80SJ4	110	619
9.1	1.8 - 9.1	575	164.34*	29000	4.7	KA	87	DRU	80SJ4	91	620
						KAF	87	DRU	80SJ4	105	619
-	1.9 - 9.7	535	154.02	19600	2.9						
11	2.2 - 11	470	135.28	19700	3.3	K	77	DRU	80SJ4	66	612
12	2.3 - 12	450	128.52	19800	3.4	KF	77	DRU	80SJ4	74	613
13	2.6 - 13	395	113.56	19900	3.9	KA	77	DRU	80SJ4	58	614
15	3.1 - 15	335	97.05	19900	4.6	KAF	77	DRU	80SJ4	66	613
17	3.4 - 17	310	88.97	20000	5.0						
-	2.4 - 12	430	123.54	12700	1.90						
14	2.8 - 14	375	108.03	12900	2.2						
15	2.9 - 15	355	102.62	12900	2.3						
17	3.3 - 17	315	90.04	13000	2.6	K	67	DRU	80SJ4	41	606
20	3.9 - 20	265	76.37	13000	3.1	KF	67	DRU	80SJ4	47	607
22	4.4 - 22	240	68.95	13000	3.4	KA	67	DRU	80SJ4	39	608
25	4.9 - 25	210	60.66	13000	3.9	KAF	67	DRU	80SJ4	44	607
26	5.2 - 26	200	57.28	13000	4.1						
31	6.2 - 31	171	48.77	13000	4.8						
-	2.4 - 12	430	123.85	8730	1.40						
14	2.8 - 14	375	108.29	8970	1.60						
15	2.9 - 15	360	102.88*	9050	1.65						
17	3.3 - 17	315	90.26*	9220	1.90						
20	3.9 - 20	265	76.56*	9400	2.2	K	57	DRU	80SJ4	35	600
22	4.3 - 22	240	69.12	9490	2.5	KF	57	DRU	80SJ4	40	601
25	4.9 - 25	210	60.81*	9590	2.8	KA	57	DRU	80SJ4	33	602
26	5.2 - 26	200	57.42*	9630	3.0	KAF	57	DRU	80SJ4	39	601
31	6.1 - 31	171	48.89	9720	3.5						
34	6.8 - 34	156	44.43	9770	3.9						
39	7.8 - 39	135	38.49	9830	4.5						
42	8.4 - 42	125	35.70	9860	4.8						
-	5.0 - 25	210	60.27	9000	2.4						
28	5.7 - 28	185	52.94	9000	2.7	K	49	DRU	80SJ4	40	596
30	6.0 - 30	176	50.29	9000	2.8	KF	49	DRU	80SJ4	42	597
34	6.8 - 34	156	44.44	9000	3.2	KA	49	DRU	80SJ4	38	598
40	7.9 - 40	133	37.98	9000	3.8	KAF	49	DRU	80SJ4	43	597


P_m = 0.55 kW											
n_a min⁻¹ 50Hz	n_a min⁻¹ 10-50Hz	M_a Nm	i	F_{Ra}¹⁾ N	SEW f_B					m kg	
-	2.9 - 14	365	104.37	6380	1.10						
17	3.3 - 17	315	90.86	6890	1.25						
18	3.5 - 18	295	85.12*	7080	1.35						
20	4.0 - 20	260	75.20*	7360	1.50						
21	4.3 - 21	240	69.84	7500	1.65						
24	4.7 - 24	220	63.30*	7650	1.80						
26	5.3 - 26	199	56.83	7780	2.0	K	47	DRU	80SJ4	30	590
31	6.1 - 31	171	48.95*	7910	2.3	KF	47	DRU	80SJ4	33	591
33	6.5 - 33	161	46.03*	7960	2.5	KA	47	DRU	80SJ4	29	592
38	7.6 - 38	139	39.61	8050	2.9	KAF	47	DRU	80SJ4	32	591
42	8.5 - 42	124	35.39	7960	3.2						
48	9.6 - 48	110	31.30	7720	3.6						
51	10 - 51	103	29.32	7580	3.9						
58	12 - 58	91	25.91	7340	4.4						
62	12 - 62	84	24.06	7190	4.8						
-	6.0 - 30	174	49.69	7500	1.70						
35	6.9 - 35	152	43.45	7500	1.95						
36	7.3 - 36	145	41.28	7500	2.1	K	39	DRU	80SJ4	28	586
41	8.3 - 41	127	36.22	7500	2.4	KF	39	DRU	80SJ4	30	587
49	9.8 - 49	108	30.72	7420	2.8	KA	39	DRU	80SJ4	27	588
54	11 - 54	97	27.73	7230	3.1	KAF	39	DRU	80SJ4	29	587
61	12 - 61	85	24.40	6990	3.5						
65	13 - 65	81	23.04	6890	3.7						
30	6.0 - 30	174	49.79	4740	1.15						
34	6.7 - 34	156	44.46	4680	1.30						
40	7.9 - 40	133	37.97	4570	1.50						
42	8.4 - 42	124	35.57	4520	1.60						
50	10 - 50	105	29.96	4390	1.90						
-	10 - 52	101	28.83	4360	2.0	K	37	DRU	80SJ4	22	580
60	12 - 60	88	24.99	4230	2.3	KF	37	DRU	80SJ4	24	581
64	13 - 64	82	23.36	4170	2.4	KA	37	DRU	80SJ4	22	582
74	15 - 74	71	20.19	4040	2.6	KAF	37	DRU	80SJ4	23	581
87	17 - 87	60	17.15	3890	3.0						
98	20 - 98	54	15.31	3780	3.3						
115	23 - 115	46	13.08	3640	3.6						
124	25 - 124	42	12.14	3570	3.8						
143	29 - 143	37	10.49	3430	4.4						
-	7.0 - 35	136	42.87	4570	0.95						
41	8.1 - 41	118	36.96	4470	1.05						
50	10.0 - 50	96	30.11	4320	1.20						
60	12 - 60	79	24.91	4160	1.35	K	29	DRU	80SJ4	16	573
-	13 - 65	75	23.19	4160	1.70	KF	29	DRU	80SJ4	17	577
68	14 - 68	70	22.08	4060	1.50	KA	29	DRU	80SJ4	15	579
75	15 - 75	65	19.99	4020	2.0	KAF	29	DRU	80SJ4	17	577
92	18 - 92	53	16.29	3820	2.5						
111	22 - 111	44	13.47	3640	3.0						
126	25 - 126	39	11.94	3530	3.4						
-	30 - 152	33	9.90	3420	3.4						
-	16 - 81	60	18.55	3540	1.35						
95	19 - 95	52	15.84	3410	1.55						
102	20 - 102	48	14.69	3360	1.65						
118	24 - 118	41	12.70	3240	1.95						
127	25 - 127	38	11.84	3180	2.0	K	19	DRU	80SJ4	14	567
145	29 - 145	34	10.32	3070	2.3	KF	19	DRU	80SJ4	15	570
-	37 - 185	27	8.09	2940	3.0	KA	19	DRU	80SJ4	14	572
217	43 - 217	23	6.91	2810	3.5	KAF	19	DRU	80SJ4	14	570
234	47 - 234	21	6.41	2750	3.8						
271	54 - 271	18	5.54	2630	4.3						
291	58 - 291	17	5.16	2580	4.7						
333	67 - 333	15	4.50	2470	5.3						


P_m = 0.75 kW											
n_a min⁻¹ 50Hz	n_a min⁻¹ 10-50Hz	M_a Nm	i	F_{Ra}¹⁾ N	SEW f_B					m kg	
-	1.7 - 8.6	830	174.19	28900	3.2	K	87	DRU	80MJ4	105	618
-	1.8 - 9.1	780	164.34*	28900	3.4					115	619
10	2.0 - 10	700	147.32*	28900	3.8					94	620
12	2.4 - 12	605	126.91*	29000	4.5					105	619
13	2.6 - 13	550	115.82	29000	4.9						
-	2.2 - 11	645	135.28	19400	2.4	K	77	DRU	80MJ4	68	612
-	2.3 - 12	610	128.52	19500	2.5					77	613
13	2.6 - 13	540	113.56	19600	2.9					61	614
15	3.1 - 15	460	97.05	19800	3.3					69	613
17	3.4 - 17	420	88.97	19800	3.6						
19	3.8 - 19	370	78.07	19900	4.2	KAF	77	DRU	80MJ4		
20	4.1 - 20	350	73.99	19900	4.4						
-	2.8 - 14	515	108.03	12300	1.60						
-	2.9 - 15	490	102.62	12500	1.65						
17	3.3 - 17	425	90.04	12700	1.90						
20	3.9 - 20	360	76.37	12900	2.2	K	67	DRU	80MJ4	44	606
22	4.4 - 22	325	68.95	13000	2.5					50	607
25	4.9 - 25	285	60.66	13000	2.8					41	608
26	5.2 - 26	270	57.28	13000	3.0					47	607
31	6.2 - 31	230	48.77	13000	3.5						
34	6.8 - 34	210	44.32	13000	3.9	KAF	67	DRU	80MJ4		
39	7.8 - 39	183	38.39	13000	4.4						
42	8.4 - 42	170	35.62	13000	4.8						
-	2.8 - 14	515	108.29	8290	1.15						
-	2.9 - 15	490	102.88*	8460	1.20	K	57	DRU	80MJ4	38	600
17	3.3 - 17	430	90.26*	8740	1.40					43	601
20	3.9 - 20	365	76.56*	9030	1.65					36	602
22	4.3 - 22	330	69.12	9170	1.80					42	601
25	4.9 - 25	290	60.81*	9320	2.1						
26	5.2 - 26	270	57.42*	9380	2.2	KAF	57	DRU	80MJ4		
31	6.1 - 31	230	48.89	9520	2.6						
34	6.8 - 34	210	44.43	9590	2.8						
39	7.8 - 39	184	38.49	9680	3.3						
42	8.4 - 42	170	35.70	9720	3.5						
50	9.9 - 50	145	30.28	9800	4.2	K	49	DRU	80MJ4	43	596
55	11 - 55	130	27.34	9760	4.6					45	597
-	5.7 - 28	250	52.94	9000	2.0					40	598
-	6.0 - 30	240	50.29	9000	2.1					45	597
34	6.8 - 34	210	44.44	9000	2.4					45	597
40	7.9 - 40	181	37.98	9000	2.8	KAF	49	DRU	80MJ4		
43	8.6 - 43	166	34.81	9000	3.0						
49	9.8 - 49	146	30.55	8870	3.4						
52	10 - 52	138	28.95	8750	3.6						
20	4.0 - 20	355	75.20*	6450	1.10	K	47	DRU	80MJ4	32	590
-	4.3 - 21	330	69.84	6740	1.20					35	591
24	4.7 - 24	300	63.30*	7040	1.30					31	592
26	5.3 - 26	270	56.83	7300	1.45					34	591
31	6.1 - 31	230	48.95*	7570	1.70						
33	6.5 - 33	215	46.03*	7660	1.80	KAF	47	DRU	80MJ4		
38	7.6 - 38	189	39.61	7810	2.1						
42	8.5 - 42	169	35.39	7620	2.4						
-	9.6 - 48	149	31.30	7410	2.7						
-	10 - 51	140	29.32	7300	2.9						
58	12 - 58	124	25.91	7090	3.2	K	47	DRU	80MJ4		
-	12 - 62	115	24.06	6960	3.5						
69	14 - 69	104	21.81	6790	3.8						
77	15 - 77	94	19.58	6600	4.3						
89	18 - 89	80	16.86	6340	4.7						
127	25 - 127	56	11.77	5720	5.0						

P _m = 0.75 kW											
n_a min ⁻¹ 50Hz	n_a min ⁻¹ 10-50Hz	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
-	6.9 - 35	205	43.45	7500	1.45	K KF KA KAF	39	DRU	80MJ4	31	586
-	7.3 - 36	197	41.28	7500	1.50						
41	8.3 - 41	173	36.22	7330	1.75						
49	9.8 - 49	147	30.72	7080	2.0						
54	11 - 54	132	27.73	6930	2.3						
61	12 - 61	116	24.40	6720	2.6						
65	13 - 65	110	23.04	6640	2.7						
76	15 - 76	94	19.62	6380	3.1						
84	17 - 84	85	17.83	6230	3.4						
97	19 - 97	74	15.44	6000	3.8						
-	7.9 - 40	181	37.97	4130	1.10	K KF KA KAF	37	DRU	80MJ4	24	580
-	8.4 - 42	170	35.57	4110	1.20						
-	10 - 50	143	29.96	4040	1.40						
-	12 - 60	119	24.99	3940	1.70						
-	13 - 64	112	23.36	3900	1.75						
-	15 - 74	96	20.19	3810	1.90						
-	17 - 87	82	17.15	3690	2.2						
-	20 - 98	73	15.31	3610	2.4						
-	23 - 115	62	13.08	3480	2.6						
-	25 - 124	58	12.14	3430	2.8						
-	29 - 143	50	10.49	3310	3.2						
-	34 - 168	43	8.91	3180	3.8						
-	38 - 188	38	7.96	3090	4.1						
-	44 - 221	32	6.80	2960	4.6						
-	47 - 236	30	6.37	2910	4.8						
-	10.0 - 50	131	30.11	3970	0.90	K KF KA KAF	29	DRU	80MJ4	18	573
-	12 - 60	108	24.91	3870	1.00						
-	14 - 68	96	22.08	3800	1.10						
-	15 - 75	89	19.99	3810	1.45						
-	18 - 92	72	16.29	3650	1.80						
-	22 - 111	60	13.47	3500	2.2						
-	25 - 126	53	11.94	3400	2.5						
-	33 - 164	41	9.17	3190	3.2						
-	35 - 176	39	8.53	3210	3.2						
-	40 - 201	33	7.48	3020	3.7						
-	43 - 216	31	6.95	3030	3.6						
-	19 - 95	70	15.84	3220	1.15	K KF KA KAF	19	DRU	80MJ4	17	567
-	20 - 102	65	14.69	3180	1.25						
-	24 - 118	56	12.70	3080	1.40						
-	25 - 127	52	11.84	3040	1.50						
-	29 - 145	46	10.32	2950	1.65						
-	43 - 217	31	6.91	2740	2.6						
-	47 - 234	29	6.41	2680	2.8						
-	54 - 271	25	5.54	2580	3.2						
-	58 - 291	23	5.16	2530	3.4						
-	67 - 333	20	4.50	2430	3.9						


P _m = 1.1 kW											
n _a min ⁻¹ 50Hz	n _a min ⁻¹ 10-50Hz	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
8.5	1.7 - 8.5	1230	176.05*	40000	3.5	K	97	DRU	90MJ4	170	624
9.8	2.0 - 9.8	1070	153.21*	40000	4.0	KF	97	DRU	90MJ4	190	625
11	2.1 - 11	980	140.28	40000	4.4	KA	97	DRU	90MJ4	150	626
12	2.4 - 12	860	123.93*	40000	5.0	KAF	97	DRU	90MJ4	175	625
10	2.0 - 10	1030	147.32*	28800	2.6						
12	2.4 - 12	880	126.91*	28800	3.0	K	87	DRU	90MJ4	110	618
13	2.6 - 13	810	115.82	28900	3.3	KF	87	DRU	90MJ4	120	619
15	2.9 - 15	715	102.71*	28900	3.8	KA	87	DRU	90MJ4	97	620
17	3.5 - 17	600	86.34	29000	4.5	KAF	87	DRU	90MJ4	110	619
19	3.8 - 19	555	79.34	29000	4.9						


P _m = 1.1 kW											
n _a min ⁻¹ 50Hz	n _a min ⁻¹ 10-50Hz	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
13	2.6 - 13	795	113.56	19000	1.95	K KF KA KAF	77	DRU	90MJ4	72	612
15	3.1 - 15	675	97.05	19300	2.3						
17	3.4 - 17	620	88.97	19400	2.5						
19	3.8 - 19	545	78.07	19600	2.8						
20	4.1 - 20	515	73.99	19700	3.0						
23	4.6 - 23	450	64.75	19800	3.4						
26	5.1 - 26	405	58.34	19800	3.8						
29	5.9 - 29	355	51.18	19900	4.3						
33	6.6 - 33	315	45.16	20000	4.9						
17	3.3 - 17	630	90.04	11700	1.30	K KF KA KAF	67	DRU	90MJ4	48	606
20	3.9 - 20	530	76.37	12200	1.55						
22	4.4 - 22	480	68.95	12500	1.70						
25	4.9 - 25	420	60.66	12700	1.95						
26	5.2 - 26	400	57.28	12800	2.0						
31	6.2 - 31	340	48.77	13000	2.4						
34	6.8 - 34	310	44.32	13000	2.6						
39	7.8 - 39	265	38.39	13000	3.0						
42	8.4 - 42	245	35.62	13000	3.3						
50	9.9 - 50	210	30.22	13000	3.9						
55	11 - 55	191	27.28	13000	4.3						
63	13 - 63	168	24.00	13000	4.8						
66	13 - 66	159	22.66	13000	4.9						
20	3.9 - 20	535	76.56*	8140	1.10	K KF KA KAF	57	DRU	90MJ4	42	600
22	4.3 - 22	480	69.12	8500	1.25						
25	4.9 - 25	425	60.81*	8770	1.40						
26	5.2 - 26	400	57.42*	8870	1.50						
31	6.1 - 31	340	48.89	9120	1.75						
34	6.8 - 34	310	44.43	9240	1.95						
39	7.8 - 39	265	38.49	9400	2.2						
42	8.4 - 42	250	35.70	9470	2.4						
50	9.9 - 50	210	30.28	9590	2.8						
55	11 - 55	191	27.34	9360	3.1						
62	12 - 62	168	24.05	9060	3.6						
66	13 - 66	159	22.71	8930	3.8						
78	16 - 78	135	19.34	8570	4.2						
85	17 - 85	123	17.57	8350	4.5						
126	25 - 126	84	11.92	7430	5.0						
34	6.8 - 34	310	44.44	9000	1.60	K KF KA KAF	49	DRU	90MJ4	47	596
40	7.9 - 40	265	37.98	8750	1.90						
43	8.6 - 43	240	34.81	8600	2.0						
49	9.8 - 49	210	30.55	8380	2.3						
52	10 - 52	200	28.95	8280	2.5						
59	12 - 59	177	25.34	8040	2.8						
66	13 - 66	160	22.83	7850	3.1						
75	15 - 75	140	20.03	7610	3.6						
26	5.3 - 26	395	56.83	5950	1.00	K KF KA KAF	47	DRU	90MJ4	36	590
31	6.1 - 31	340	48.95*	6640	1.15						
33	6.5 - 33	320	46.03*	6850	1.25						
38	7.6 - 38	275	39.61	7140	1.45						
42	8.5 - 42	245	35.39	7020	1.60						
58	12 - 58	181	25.91	6650	2.2						
69	14 - 69	153	21.81	6420	2.6						
77	15 - 77	137	19.58	6270	2.9						
89	18 - 89	118	16.86	6060	3.2						
95	19 - 95	111	15.86	5970	3.4						
110	22 - 110	96	13.65	5760	3.8						
123	25 - 123	85	12.19	5590	4.1						
127	25 - 127	82	11.77	5510	3.4						
142	28 - 142	74	10.56	5360	3.8						
165	33 - 165	64	9.10	5150	4.4						
175	35 - 175	60	8.56	5070	4.5						
204	41 - 204	52	7.36	4860	4.8						

P _m = 1.1 kW											
n _a min ⁻¹ 50Hz	n _a min ⁻¹ 10-50Hz	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B						
41	8.3 - 41	250	36.22	6630	1.20						
49	9.8 - 49	215	30.72	6490	1.40						
54	11 - 54	194	27.73	6390	1.55						
61	12 - 61	171	24.40	6260	1.75						
65	13 - 65	161	23.04	6190	1.85						
76	15 - 76	137	19.62	6000	2.1						
84	17 - 84	125	17.83	5890	2.3						
97	19 - 97	108	15.44	5700	2.6						
112	22 - 112	94	13.44	5520	2.9						
141	28 - 141	74	10.61	5430	3.8						
74	15 - 74	141	20.19	3400	1.30						
87	17 - 87	120	17.15	3340	1.50						
98	20 - 98	107	15.31	3300	1.65						
115	23 - 115	92	13.08	3220	1.80						
143	29 - 143	74	10.49	3100	2.2						
168	34 - 168	62	8.91	3000	2.6						
188	38 - 188	56	7.96	2930	2.8						
221	44 - 221	48	6.80	2830	3.1						
236	47 - 236	45	6.37	2780	3.2						
280	56 - 280	38	5.36	2670	3.7						
377	75 - 377	28	3.98	2470	4.5						
92	18 - 92	106	16.29	3350	1.25						
111	22 - 111	88	13.47	3250	1.50						
126	25 - 126	78	11.94	3180	1.65						
164	33 - 164	60	9.17	3020	2.2						
201	40 - 201	49	7.48	2880	2.5						
216	43 - 216	46	6.95	2930	2.4						
261	52 - 261	38	5.75	2790	2.9						
294	59 - 294	34	5.10	2700	3.2						

P _m = 1.5 kW													
n _a min ⁻¹ 50Hz	n _a min ⁻¹ 10-50Hz	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B							m kg	
-	1.7 - 8.5	1680	176.05*	40000	2.6	K KF KA KAF	97 97 97 97	DRU DRU DRU DRU	90LJ4 90LJ4 90LJ4 90LJ4	170 190 150 175	624 625 626 625		
9.8	2.0 - 9.8	1460	153.21*	40000	2.9								
11	2.1 - 11	1330	140.28	40000	3.2								
12	2.4 - 12	1180	123.93*	40000	3.6								
14	2.9 - 14	1000	105.13	40000	4.3								
16	3.1 - 16	920	96.80	40000	4.7								
-	2.0 - 10	1400	147.32*	28500	1.90	K KF KA KAF	87 87 87 87	DRU DRU DRU DRU	90LJ4 90LJ4 90LJ4 90LJ4	110 120 100 115	618 619 620 619		
12	2.4 - 12	1210	126.91*	28700	2.2								
13	2.6 - 13	1100	115.82	28700	2.4								
15	2.9 - 15	980	102.71*	28800	2.8								
17	3.5 - 17	820	86.34	28900	3.3								
19	3.8 - 19	755	79.34	28900	3.6								
21	4.3 - 21	670	70.46	28900	4.0								
24	4.8 - 24	600	63.00*	29000	4.5								
26	5.3 - 26	540	56.64	29000	5.0								
-	2.6 - 13	1080	113.56	18000	1.45	K KF KA KAF	77 77 77 77	DRU DRU DRU DRU	90LJ4 90LJ4 90LJ4 90LJ4	75 83 68 76	612 613 614 613		
15	3.1 - 15	920	97.05	18600	1.65								
17	3.4 - 17	840	88.97	18800	1.80								
19	3.8 - 19	745	78.07	19100	2.1								
20	4.1 - 20	705	73.99	19200	2.2								
23	4.6 - 23	615	64.75	19500	2.5								
26	5.1 - 26	555	58.34	19600	2.8								
29	5.9 - 29	485	51.18	19700	3.2								
33	6.6 - 33	430	45.16	19800	3.6								
37	7.5 - 37	380	40.04	19900	4.0								
39	7.8 - 39	365	38.39	19900	4.1								
43	8.5 - 43	335	35.20	19900	4.6								


P_m = 1.5 kW

n _a min ⁻¹ 50Hz	n _a min ⁻¹ 10-50Hz	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
20	3.9 - 20	725	76.37	11100	1.10						
22	4.4 - 22	655	68.95	11500	1.25						
25	4.9 - 25	575	60.66	12000	1.40						
26	5.2 - 26	545	57.28	12200	1.50						
31	6.2 - 31	465	48.77	12600	1.75						
34	6.8 - 34	420	44.32	12700	1.95						
39	7.8 - 39	365	38.39	12900	2.2						
-	8.4 - 42	340	35.62	13000	2.4	K	67	DRU	90LJ4	50	606
50	9.9 - 50	285	30.22	13000	2.8	KF	67	DRU	90LJ4	56	607
55	11 - 55	260	27.28	13000	3.1	KA	67	DRU	90LJ4	48	608
63	13 - 63	225	24.00	13000	3.5	KAF	67	DRU	90LJ4	53	607
66	13 - 66	215	22.66	13000	3.6						
78	16 - 78	184	19.30	13000	4.1						
86	17 - 86	167	17.54	13000	4.4						
99	20 - 99	145	15.19	13000	4.8						
120	24 - 120	119	12.48	13000	4.5						
141	28 - 141	102	10.63	13000	4.9						
25	4.9 - 25	580	60.81*	7790	1.05						
26	5.2 - 26	545	57.42*	8050	1.10						
31	6.1 - 31	465	48.89	8580	1.30						
34	6.8 - 34	420	44.43	8780	1.40						
39	7.8 - 39	365	38.49	9020	1.65						
-	8.4 - 42	340	35.70	9130	1.75						
50	9.9 - 50	285	30.28	9080	2.1						
55	11 - 55	260	27.34	8900	2.3	K	57	DRU	90LJ4	44	600
62	12 - 62	225	24.05	8660	2.6	KF	57	DRU	90LJ4	49	601
66	13 - 66	215	22.71	8550	2.8	KA	57	DRU	90LJ4	42	602
78	16 - 78	185	19.34	8240	3.1	KAF	57	DRU	90LJ4	48	601
85	17 - 85	168	17.57	8060	3.3						
99	20 - 99	145	15.22	7780	3.7						
113	23 - 113	126	13.25	7500	4.0						
126	25 - 126	114	11.92	7200	3.6						
133	27 - 133	108	11.26	7100	3.9						
156	31 - 156	92	9.59	6800	4.4						
172	34 - 172	83	8.71	6630	4.7						
-	6.8 - 34	420	44.44	8180	1.20						
40	7.9 - 40	360	37.98	8050	1.40						
43	8.6 - 43	330	34.81	7970	1.50						
49	9.8 - 49	290	30.55	7820	1.70						
52	10 - 52	275	28.95	7750	1.80	K	49	DRU	90LJ4	50	596
59	12 - 59	240	25.34	7580	2.1	KF	49	DRU	90LJ4	52	597
66	13 - 66	215	22.83	7430	2.3	KA	49	DRU	90LJ4	47	598
75	15 - 75	191	20.03	7240	2.6	KAF	49	DRU	90LJ4	52	597
85	17 - 85	169	17.67	7050	3.0						
96	19 - 96	150	15.67	6860	3.3						
112	22 - 112	128	13.38	6610	3.7						
38	7.6 - 38	375	39.61	6220	1.05						
42	8.5 - 42	335	35.39	6330	1.20						
-	12 - 58	245	25.91	6140	1.60						
69	14 - 69	205	21.81	5990	1.90						
77	15 - 77	187	19.58	5890	2.1						
89	18 - 89	161	16.86	5730	2.4						
95	19 - 95	151	15.86	5660	2.5						
110	22 - 110	130	13.65	5490	2.8	K	47	DRU	90LJ4	39	590
123	25 - 123	116	12.19	5360	3.0	KF	47	DRU	90LJ4	42	591
127	25 - 127	112	11.77	5260	2.5	KA	47	DRU	90LJ4	38	592
142	28 - 142	101	10.56	5140	2.8	KAF	47	DRU	90LJ4	41	591
165	33 - 165	87	9.10	4960	3.2						
175	35 - 175	82	8.56	4890	3.3						
204	41 - 204	70	7.36	4710	3.6						
228	46 - 228	63	6.58	4580	3.8						
258	52 - 258	56	5.81	4430	4.1						
324	65 - 324	44	4.64	4170	4.6						

P _m = 1.5 kW																	
n _a min ⁻¹ 50Hz	n _a min ⁻¹ 10-50Hz	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg							
-	8.3 - 41	345	36.22	5840	0.85	K	39	DRU	90LJ4	38	586						
49	9.8 - 49	290	30.72	5820	1.00												
54	11 - 54	260	27.73	5790	1.15												
61	12 - 61	230	24.40	5720	1.30												
65	13 - 65	220	23.04	5690	1.35												
76	15 - 76	187	19.62	5570	1.55												
84	17 - 84	170	17.83	5500	1.70												
97	19 - 97	147	15.44	5370	1.90												
112	22 - 112	128	13.44	5230	2.1												
-	28 - 141	101	10.61	5270	2.8												
167	33 - 167	86	9.00	5050	3.5												
185	37 - 185	78	8.12	4910	3.9												
-	17 - 87	164	17.15	2950	1.10	KF	37	DRU	90LJ4	32	580						
-	20 - 98	146	15.31	2940	1.20												
-	23 - 115	125	13.08	2920	1.30												
-	29 - 143	100	10.49	2860	1.60												
-	34 - 168	85	8.91	2800	1.90												
-	38 - 188	76	7.96	2750	2.0												
-	44 - 221	65	6.80	2670	2.3												
-	47 - 236	61	6.37	2640	2.4												
-	56 - 280	51	5.36	2550	2.7												
-	75 - 377	38	3.98	2380	3.3												
-	18 - 92	144	16.29	3010	0.90							KA	29	DRU	90LJ4	26	573
-	22 - 111	119	13.47	2970	1.10												
-	25 - 126	106	11.94	2930	1.25												
-	33 - 164	81	9.17	2820	1.60												
-	40 - 201	66	7.48	2720	1.85												
-	43 - 216	63	6.95	2820	1.80												
-	52 - 261	52	5.75	2700	2.1												
-	59 - 294	46	5.10	2620	2.4												
-	77 - 383	35	3.92	2440	3.5												
-	94 - 470	29	3.19	2310	3.8												

P _m = 2.2 kW											
n _a min ⁻¹ 50Hz	n _a min ⁻¹ 10-50Hz	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
-	2.0 - 9.8	2140	153.21*	40000	2.0						
-	2.1 - 11	1960	140.28	40000	2.2						
12	2.4 - 12	1730	123.93*	40000	2.5						
14	2.9 - 14	1470	105.13	40000	2.9						
16	3.1 - 16	1350	96.80	40000	3.2						
17	3.5 - 17	1210	86.52	40000	3.5						
19	3.9 - 19	1090	77.89*	40000	3.9						
21	4.3 - 21	980	70.54	40000	4.3						
24	4.8 - 24	870	62.55	40000	4.9						
-	2.4 - 12	1770	126.91*	28300	1.50						
-	2.6 - 13	1620	115.82	28400	1.65						
15	2.9 - 15	1430	102.71*	28500	1.90						
17	3.5 - 17	1200	86.34	28700	2.2						
19	3.8 - 19	1110	79.34	28700	2.4						
21	4.3 - 21	980	70.46	28800	2.7						
24	4.8 - 24	880	63.00*	28800	3.1						
26	5.3 - 26	790	56.64	28900	3.4						
31	6.1 - 31	685	49.16	28900	3.9						
34	6.8 - 34	615	44.02	29000	4.2						
41	8.2 - 41	510	36.52*	28700	4.9						


P_m = 2.2 kW

n_a min ⁻¹ 50Hz	n_a min ⁻¹ 10-50Hz	M_a Nm	i	$F_{Ra}^{1)}$ N	SEW f_B					m kg	
-	3.1 - 15	1350	97.05	16600	1.15						
-	3.4 - 17	1240	88.97	17200	1.25						
19	3.8 - 19	1090	78.07	17900	1.40						
20	4.1 - 20	1030	73.99	18200	1.50						
23	4.6 - 23	900	64.75	18600	1.70						
26	5.1 - 26	810	58.34	18900	1.90						
29	5.9 - 29	715	51.18	19200	2.2	K	77	DRU	100MJ4	80	612
33	6.6 - 33	630	45.16	19400	2.5	KF	77	DRU	100MJ4	88	613
37	7.5 - 37	560	40.04	19600	2.8	KA	77	DRU	100MJ4	73	614
-	7.8 - 39	535	38.39	19600	2.8	KAF	77	DRU	100MJ4	80	613
-	8.5 - 43	490	35.20	19700	3.1						
49	9.7 - 49	430	30.89	19800	3.6						
51	10 - 51	405	29.27	19800	3.8						
59	12 - 59	355	25.62	19900	4.3						
65	13 - 65	320	23.08	20000	4.8						
-	5.2 - 26	800	57.28	10500	1.00						
-	6.2 - 31	680	48.77	11400	1.20						
-	6.8 - 34	620	44.32	11800	1.30						
-	7.8 - 39	535	38.39	12200	1.50						
-	9.9 - 50	420	30.22	12700	1.95						
-	11 - 55	380	27.28	12900	2.1						
-	13 - 63	335	24.00	13000	2.4						
-	13 - 66	315	22.66	13000	2.5	K	67	DRU	100MJ4	55	606
-	16 - 78	270	19.30	13000	2.8	KF	67	DRU	100MJ4	61	607
-	17 - 86	245	17.54	13000	3.0	KA	67	DRU	100MJ4	52	608
-	20 - 99	210	15.19	13000	3.3	KAF	67	DRU	100MJ4	58	607
-	23 - 114	185	13.22	13000	3.6						
-	24 - 120	175	12.48	13000	3.0						
-	28 - 141	149	10.63	13000	3.4						
-	31 - 155	135	9.66	13000	3.5						
-	36 - 179	117	8.37	13000	3.8						
-	41 - 206	102	7.28	12500	4.1						
-	58 - 288	73	5.20	11500	4.8						
-	7.8 - 39	535	38.49	8120	1.10						
-	9.9 - 50	420	30.28	8200	1.40						
-	11 - 55	380	27.34	8100	1.55						
-	12 - 62	335	24.05	7960	1.80						
-	13 - 66	315	22.71	7890	1.90						
-	16 - 78	270	19.34	7680	2.1						
-	17 - 85	245	17.57	7540	2.3	K	57	DRU	100MJ4	49	600
-	20 - 99	210	15.22	7330	2.5	KF	57	DRU	100MJ4	54	601
-	23 - 113	186	13.25	7120	2.8	KA	57	DRU	100MJ4	47	602
-	25 - 126	167	11.92	6800	2.5	KAF	57	DRU	100MJ4	53	601
-	27 - 133	158	11.26	6720	2.6						
-	31 - 156	134	9.59	6480	3.0						
-	34 - 172	122	8.71	6340	3.2						
-	40 - 199	106	7.55	6120	3.5						
-	46 - 228	92	6.57	5910	3.8						
-	64 - 320	66	4.69	5410	4.6						
-	7.9 - 40	530	37.98	6830	0.95						
-	8.6 - 43	485	34.81	6850	1.05						
49	9.8 - 49	425	30.55	6840	1.15						
52	10 - 52	405	28.95	6820	1.25						
59	12 - 59	350	25.34	6760	1.40	K	49	DRU	100MJ4	55	596
66	13 - 66	315	22.83	6700	1.55	KF	49	DRU	100MJ4	57	597
75	15 - 75	280	20.03	6600	1.80	KA	49	DRU	100MJ4	52	598
85	17 - 85	245	17.67	6480	2.0	KAF	49	DRU	100MJ4	57	597
96	19 - 96	215	15.67	6360	2.2						
112	22 - 112	187	13.38	6180	2.5						
-	26 - 132	159	11.37	6390	3.1						
-	29 - 144	146	10.42	6250	3.3						
164	33 - 164	128	9.14	6040	3.9						

P_m = 2.2 kW											
n_a min⁻¹ 50Hz	n_a min⁻¹ 10-50Hz	M_a Nm	i	F_{Ra}¹⁾ N	SEW f_B					m kg	
-	14 - 69	305	21.81	5250	1.30						
-	15 - 77	270	19.58	5220	1.45						
-	18 - 89	235	16.86	5160	1.60						
-	19 - 95	220	15.86	5120	1.70						
-	22 - 110	191	13.65	5030	1.90						
-	25 - 123	171	12.19	4940	2.0	K	47	DRU	100MJ4	43	590
-	25 - 127	165	11.77	4840	1.70	KF	47	DRU	100MJ4	47	591
-	28 - 142	148	10.56	4760	1.90	KA	47	DRU	100MJ4	43	592
-	33 - 165	127	9.10	4640	2.2	KAF	47	DRU	100MJ4	45	591
-	35 - 175	120	8.56	4580	2.2						
-	41 - 204	103	7.36	4450	2.4						
-	46 - 228	92	6.58	4340	2.6						
-	52 - 258	81	5.81	4220	2.8						
-	65 - 324	65	4.64	4000	3.2						
-	12 - 61	340	24.40	4790	0.90						
-	13 - 65	320	23.04	4800	0.95						
-	15 - 76	270	19.62	4820	1.05						
-	17 - 84	245	17.83	4810	1.15						
-	19 - 97	215	15.44	4770	1.30						
-	22 - 112	188	13.44	4720	1.45	K	39	DRU	100MJ4	42	586
-	33 - 167	126	9.00	4820	2.4	KF	39	DRU	100MJ4	44	587
-	37 - 185	114	8.12	4700	2.6	KA	39	DRU	100MJ4	41	588
-	42 - 210	100	7.15	4560	3.0	KAF	39	DRU	100MJ4	43	587
-	44 - 222	95	6.75	4490	3.2						
-	52 - 261	80	5.75	4310	3.4						
-	57 - 287	73	5.22	4200	3.5						
-	66 - 332	63	4.52	4040	3.8						
-	76 - 381	55	3.94	3890	3.9						


P_m = 3.0 kW											
n_a min⁻¹ 50Hz	n_a min⁻¹ 10-50Hz	M_a Nm	i	F_{Ra}¹⁾ N	SEW f_B					m kg	
12	2.4 - 12	2360	123.93*	40000	1.80						
14	2.9 - 14	2000	105.13	40000	2.1						
16	3.1 - 16	1840	96.80	40000	2.3						
17	3.5 - 17	1650	86.52	40000	2.6	K	97	DRU	100LJ4	180	624
19	3.9 - 19	1480	77.89*	40000	2.9	KF	97	DRU	100LJ4	200	625
21	4.3 - 21	1340	70.54	40000	3.2	KA	97	DRU	100LJ4	160	626
24	4.8 - 24	1190	62.55	40000	3.6	KAF	97	DRU	100LJ4	185	625
27	5.3 - 27	1080	56.55	40000	4.0						
31	6.3 - 31	910	47.93*	40000	4.7						
15	2.9 - 15	1960	102.71*	28100	1.40						
17	3.5 - 17	1640	86.34	28400	1.65						
19	3.8 - 19	1510	79.34	28500	1.80						
21	4.3 - 21	1340	70.46	28600	2.0						
24	4.8 - 24	1200	63.00*	28700	2.2	K	87	DRU	100LJ4	120	618
26	5.3 - 26	1080	56.64	28700	2.5	KF	87	DRU	100LJ4	130	619
31	6.1 - 31	930	49.16	28800	2.9	KA	87	DRU	100LJ4	105	620
34	6.8 - 34	840	44.02	28900	3.1	KAF	87	DRU	100LJ4	120	619
41	8.2 - 41	695	36.52*	28000	3.6						
48	9.6 - 48	595	31.39	27000	4.5						
54	11 - 54	530	27.88	26200	4.9						


P_m = 3.0 kW

n_a min ⁻¹ 50Hz	n_a min ⁻¹ 10-50Hz	M_a Nm	i	$F_{Ra}^{1)}$ N	SEW f_B		m kg	
19	3.8 - 19	1490	78.07	15800	1.05			
20	4.1 - 20	1410	73.99	16300	1.10			
23	4.6 - 23	1230	64.75	17300	1.25			
26	5.1 - 26	1110	58.34	17800	1.40			
29	5.9 - 29	970	51.18	18400	1.60			
33	6.6 - 33	860	45.16	18800	1.80			
37	7.5 - 37	760	40.04	19100	2.0			
49	9.7 - 49	585	30.89	19500	2.6	K 77 DRU 100LJ4	83	612
51	10 - 51	555	29.27	19600	2.8	KF 77 DRU 100LJ4	91	613
59	12 - 59	485	25.62	19700	3.2	KA 77 DRU 100LJ4	76	614
65	13 - 65	440	23.08	19800	3.5	KAF 77 DRU 100LJ4	83	613
74	15 - 74	385	20.25	19900	3.9			
84	17 - 84	340	17.87	19900	4.2			
95	19 - 95	300	15.84	20000	4.6			
121	24 - 121	235	12.36	18800	4.2			
138	28 - 138	205	10.84	18200	4.8			
49	9.8 - 49	580	30.55	5720	0.85			
52	10 - 52	550	28.95	5760	0.90			
59	12 - 59	480	25.34	5830	1.05			
66	13 - 66	435	22.83	5860	1.15			
75	15 - 75	380	20.03	5860	1.30	K 49 DRU 100LJ4	58	596
85	17 - 85	335	17.67	5830	1.50	KF 49 DRU 100LJ4	60	597
96	19 - 96	295	15.67	5780	1.65	KA 49 DRU 100LJ4	55	598
112	22 - 112	255	13.38	5690	1.85	KAF 49 DRU 100LJ4	60	597
164	33 - 164	175	9.14	5820	2.9			
173	35 - 173	165	8.66	5750	3.0			
198	40 - 198	145	7.58	5560	3.5			
220	44 - 220	130	6.83	5410	3.8			


10.3 Auswahltabellen K..DRU...J (IE4), 87 Hz


P _m = 0.25 kW											
	n _a min ⁻¹ 10-87Hz	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
-	2.1 - 18	133	145.14*	9830	4.5	K	57	DRU	71SJ4	31	600
						KF	57	DRU	71SJ4	35	601
						KA	57	DRU	71SJ4	29	602
						KAF	57	DRU	71SJ4	34	601
-	2.3 - 20	121	131.87*	8110	3.3	K	47	DRU	71SJ4	25	590
-	2.5 - 21	111	121.48*	8140	3.6	KF	47	DRU	71SJ4	28	591
-	2.9 - 25	96	104.37	8180	4.2	KA	47	DRU	71SJ4	24	592
-	3.3 - 29	83	90.86	8210	4.8	KAF	47	DRU	71SJ4	27	591
-	2.8 - 25	97	106.38	5890	2.1	K KF KA KAF	37	DRU	71SJ4	19	580
-	3.1 - 27	90	97.81	5780	2.2						
-	3.6 - 31	76	83.69	5560	2.6						
-	4.1 - 36	66	72.54	5360	3.0						
-	4.4 - 38	62	67.80	5270	3.2						
-	5.1 - 45	54	58.60	5070	3.7						
-	6.0 - 52	46	49.79	4850	4.4						
-	6.7 - 59	41	44.46	4700	4.9						
-	5.5 - 48	46	54.89	4900	2.9	K	29	DRU	71SJ4	12	573
-	6.0 - 52	42	50.35	4790	3.1	KF	29	DRU	71SJ4	14	577
-	7.0 - 61	36	42.87	4580	3.6	KA	29	DRU	71SJ4	12	579
-	8.1 - 71	31	36.96	4390	4.0	KAF	29	DRU	71SJ4	13	577
-	6.7 - 59	37	44.48	4170	1.85	K KF KA KAF	19	DRU	71SJ4	11	567
-	7.4 - 64	34	40.63	4070	2.0						
-	8.7 - 76	29	34.29	3890	2.2						
-	10 - 89	24	29.29	3720	2.5						
-	11 - 96	23	27.16	3640	2.7						
-	12 - 108	20	24.06	3560	3.9						
-	14 - 119	19	21.98	3460	4.3						
-	16 - 141	16	18.55	3290	5.1						
-	19 - 165	13	15.84	3140	5.9						
-	20 - 178	12	14.69	3070	6.4						
-	24 - 205	11	12.70	2940	7.4						
-	25 - 220	10	11.84	2870	7.8						
-	29 - 253	8.8	10.32	2750	8.7						
-	31 - 272	8.3	9.58	2710	7.6						


P _m = 0.37 kW											
	n_a min⁻¹ 10-87Hz	M_a Nm	i	F_{Ra}¹⁾ N	SEW f_B					m kg	
-	2.1 - 18	196	144.79*	13000	4.2	K	67	DRU	71SJ4	36	606
-	2.4 - 21	167	123.54	13000	4.9	KF	67	DRU	71SJ4	42	607
						KA	67	DRU	71SJ4	34	608
						KAF	67	DRU	71SJ4	39	607
-	2.1 - 18	196	145.14*	9640	3.0	K	57	DRU	71SJ4	31	600
-	2.4 - 21	168	123.85	9730	3.6	KF	57	DRU	71SJ4	35	601
-	2.8 - 24	147	108.29	9790	4.1	KA	57	DRU	71SJ4	29	602
-	2.9 - 25	139	102.88*	9820	4.3	KAF	57	DRU	71SJ4	34	601
-	3.3 - 29	122	90.26*	9860	4.9						
-	2.3 - 20	178	131.87*	7880	2.2						
-	2.5 - 21	164	121.48*	7940	2.4						
-	2.9 - 25	141	104.37	8040	2.8	K	47	DRU	71SJ4	25	590
-	3.3 - 29	123	90.86	8100	3.2	KF	47	DRU	71SJ4	28	591
-	3.5 - 31	115	85.12*	8130	3.5	KA	47	DRU	71SJ4	24	592
-	4.0 - 35	102	75.20*	8160	3.9	KAF	47	DRU	71SJ4	27	591
-	4.3 - 37	95	69.84	8180	4.2						
-	4.7 - 41	86	63.30*	8200	4.7						
-	5.2 - 45	79	58.24	7500	3.8	K	39	DRU	71SJ4	24	586
						KF	39	DRU	71SJ4	25	587
						KA	39	DRU	71SJ4	23	588
						KAF	39	DRU	71SJ4	24	587

P _m = 0.37 kW											
	n _a min ⁻¹ 10-87Hz	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
-	2.8 - 25	144	106.38	5470	1.40	K KF KA KAF	37	DRU	71SJ4	19	580
-	3.1 - 27	132	97.81	5390	1.50					21	581
-	3.6 - 31	113	83.69	5220	1.75					18	582
-	4.1 - 36	98	72.54	5070	2.0					20	581
-	4.4 - 38	92	67.80	5000	2.2						
-	5.1 - 45	79	58.60	4830	2.5						
-	6.0 - 52	67	49.79	4650	3.0						
-	6.7 - 59	60	44.46	4520	3.3						
-	7.9 - 69	51	37.97	4340	3.9						
-	8.4 - 73	48	35.57	4260	4.2						
-	10 - 87	41	29.96	4070	4.9						
-	5.5 - 48	68	54.89	4680	1.90	K KF KA KAF	29	DRU	71SJ4	12	573
-	6.0 - 52	62	50.35	4590	2.1					14	577
-	7.0 - 61	53	42.87	4410	2.4					12	579
-	8.1 - 71	45	36.96	4240	2.7					13	577
-	10.0 - 87	37	30.11	4020	3.1						
-	10 - 88	37	29.69	4030	3.5						
-	11 - 96	34	27.23	3940	3.8						
-	12 - 105	31	24.91	3810	3.6						
-	14 - 118	27	22.08	3680	3.9						
-	6.7 - 59	55	44.48	3950	1.25	K KF KA KAF	19	DRU	71SJ4	11	567
-	7.4 - 64	50	40.63	3870	1.35					11	570
-	8.7 - 76	42	34.29	3720	1.50					11	572
-	10 - 89	36	29.29	3580	1.70					11	570
-	11 - 96	33	27.16	3510	1.80						
-	12 - 108	30	24.06	3460	2.6						
-	14 - 119	28	21.98	3370	2.9						
-	16 - 141	23	18.55	3220	3.4						
-	19 - 165	20	15.84	3070	4.0						
-	20 - 178	18	14.69	3010	4.3						
-	24 - 205	16	12.70	2880	5.0						
-	25 - 220	15	11.84	2820	5.3						
-	29 - 253	13	10.32	2710	5.9						
-	31 - 272	12	9.58	2680	5.1						
-	37 - 323	10	8.09	2540	7.7						
-	43 - 378	8.9	6.91	2420	9.0						
-	47 - 407	8.2	6.41	2360	9.7						

P _m = 0.55 kW											
	n _a min ⁻¹ 10-87Hz	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
-	2.4 - 21	245	123.54	13000	3.3	K	67	DRU	71MJ4	36	606
-	2.8 - 24	215	108.03	13000	3.8	KF	67	DRU	71MJ4	42	607
-	2.9 - 25	205	102.62	13000	4.0	KA	67	DRU	71MJ4	34	608
-	3.3 - 29	181	90.04	13000	4.5	KAF	67	DRU	71MJ4	39	607
-	2.4 - 21	245	123.85	9470	2.4	K KF KA KAF	57	DRU	71MJ4	31	600
-	2.8 - 24	215	108.29	9570	2.8					35	601
-	2.9 - 25	205	102.88*	9610	2.9					29	602
-	3.3 - 29	182	90.26*	9690	3.3					34	601
-	3.9 - 34	154	76.56*	9770	3.9						
-	4.3 - 38	139	69.12	9820	4.3						
-	4.9 - 43	122	60.81*	9860	4.9						
-	2.9 - 25	210	104.37	7720	1.90	K KF KA KAF	47	DRU	71MJ4	25	590
-	3.3 - 29	183	90.86	7860	2.2					28	591
-	3.5 - 31	171	85.12*	7920	2.3					24	592
-	4.0 - 35	151	75.20*	8000	2.6					27	591
-	4.3 - 37	140	69.84	8040	2.9						
-	4.7 - 41	127	63.30*	8020	3.1						
-	5.3 - 46	114	56.83	7800	3.5						
-	6.1 - 53	98	48.95*	7500	4.1						
-	6.5 - 57	93	46.03*	7380	4.3						

P_m = 0.55 kW											
	n_a min⁻¹ 10-87Hz	M_a Nm	i	F_{Ra}¹⁾ N	SEW f_B					m kg	
-	6.0 - 53	100	49.69	7280	3.0	K	39	DRU	71MJ4	24	586
-	6.9 - 60	87	43.45	7040	3.4	KF	39	DRU	71MJ4	25	587
-	7.3 - 63	83	41.28	6940	3.6	KA	39	DRU	71MJ4	23	588
						KAF	39	DRU	71MJ4	24	587
-	3.6 - 31	168	83.69	4720	1.20	K	37	DRU	71MJ4	19	580
-	4.1 - 36	146	72.54	4640	1.35						
-	4.4 - 38	136	67.80	4590	1.45						
-	5.1 - 45	118	58.60	4480	1.70						
-	6.0 - 52	100	49.79	4350	2.0						
-	6.7 - 59	90	44.46	4250	2.2						
-	7.9 - 69	76	37.97	4110	2.6						
-	8.4 - 73	72	35.57	4050	2.8						
-	10 - 87	60	29.96	3890	3.3						
-	10 - 91	58	28.83	3860	3.5						
-	12 - 104	50	24.99	3720	4.0						
-	13 - 112	47	23.36	3660	4.2						
-	15 - 129	41	20.19	3520	4.6						
-	7.0 - 61	78	42.87	4150	1.65	K	29	DRU	71MJ4	12	573
-	8.1 - 71	68	36.96	4020	1.80						
-	10.0 - 87	55	30.11	3840	2.1						
-	12 - 105	46	24.91	3660	2.4						
-	13 - 113	43	23.19	3630	3.0						
-	14 - 118	40	22.08	3550	2.6						
-	15 - 131	37	19.99	3490	3.5	KAF	29	DRU	71MJ4	13	577
-	8.7 - 76	63	34.29	3470	1.00	K	19	DRU	71MJ4	11	567
-	10 - 89	54	29.29	3360	1.15						
-	11 - 96	50	27.16	3310	1.20						
-	16 - 141	35	18.55	3100	2.3						
-	19 - 165	30	15.84	2970	2.7						
-	20 - 178	27	14.69	2920	2.9						
-	24 - 205	24	12.70	2800	3.4						
-	25 - 220	22	11.84	2750	3.6						
-	29 - 253	19	10.32	2640	3.9						
-	37 - 323	15	8.09	2500	5.2						
-	43 - 378	13	6.91	2380	6.1						
-	47 - 407	12	6.41	2330	6.5						
-	54 - 471	11	5.54	2220	7.6						
-	58 - 506	9.8	5.16	2180	8.1						
-	67 - 580	8.6	4.50	2090	9.3						

P_m = 0.75 kW											
	n_a min⁻¹ 10-87Hz	M_a Nm	i	F_{Ra}¹⁾ N	SEW f_B					m kg	
-	1.5 - 13	540	197.37	29000	5.0	K	87	DRU	80SJ4	105	618
						KF	87	DRU	80SJ4	110	619
						KA	87	DRU	80SJ4	91	620
						KAF	87	DRU	80SJ4	105	619
-	1.9 - 17	420	154.02	19800	3.7	K	77	DRU	80SJ4	66	612
-	2.2 - 19	370	135.28	19900	4.2	KF	77	DRU	80SJ4	74	613
-	2.3 - 20	350	128.52	19900	4.4	KA	77	DRU	80SJ4	58	614
-	2.6 - 23	310	113.56	20000	5.0	KAF	77	DRU	80SJ4	66	613
-	2.4 - 21	335	123.54	13000	2.4	K	67	DRU	80SJ4	41	606
-	2.8 - 24	295	108.03	13000	2.8						
-	2.9 - 25	280	102.62	13000	2.9						
-	3.3 - 29	245	90.04	13000	3.3						
-	3.9 - 34	205	76.37	13000	3.9						
-	4.4 - 38	189	68.95	13000	4.3						
-	4.9 - 43	166	60.66	13000	4.9						


P _m = 0.75 kW											
	n _a min ⁻¹ 10-87Hz	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
-	2.4 - 21	335	123.85	9130	1.75	K KF KA KAF	57 57 57 57	DRU DRU DRU DRU	80SJ4 80SJ4 80SJ4 80SJ4	35 40 33 39	600 601 602 601
-	2.8 - 24	295	108.29	9300	2.0						
-	2.9 - 25	280	102.88*	9350	2.1						
-	3.3 - 29	245	90.26*	9470	2.4						
-	3.9 - 34	210	76.56*	9600	2.9						
-	4.3 - 38	190	69.12	9660	3.2						
-	4.9 - 43	167	60.81*	9740	3.6						
-	5.2 - 45	158	57.42*	9760	3.8						
-	6.1 - 53	134	48.89	9830	4.5						
-	6.8 - 59	122	44.43	9570	4.9						
-	5.0 - 43	165	60.27	9000	3.0	K	49	DRU	80SJ4	40	596
-	5.7 - 49	145	52.94	8860	3.4	KF	49	DRU	80SJ4	42	597
-	6.0 - 52	138	50.29	8740	3.6	KA	49	DRU	80SJ4	38	598
						KAF	49	DRU	80SJ4	43	597
-	2.9 - 25	285	104.37	7180	1.40	K KF KA KAF	47 47 47 47	DRU DRU DRU DRU	80SJ4 80SJ4 80SJ4 80SJ4	30 33 29 32	590 591 592 591
-	3.3 - 29	245	90.86	7460	1.60						
-	3.5 - 31	230	85.12*	7570	1.70						
-	4.0 - 35	205	75.20*	7740	1.95						
-	4.3 - 37	192	69.84	7820	2.1						
-	4.7 - 41	174	63.30*	7670	2.3						
-	5.3 - 46	156	56.83	7480	2.6						
-	6.1 - 53	134	48.95*	7230	3.0						
-	6.5 - 57	126	46.03*	7120	3.2						
-	7.6 - 66	109	39.61	6860	3.7						
-	8.5 - 74	97	35.39	6670	4.1						
-	9.6 - 83	86	31.30	6450	4.7						
-	10 - 89	80	29.32	6340	5.0						
-	6.0 - 53	136	49.69	6970	2.2	K KF KA KAF	39 39 39 39	DRU DRU DRU DRU	80SJ4 80SJ4 80SJ4 80SJ4	28 30 27 29	586 587 588 587
-	6.9 - 60	119	43.45	6760	2.5						
-	7.3 - 63	113	41.28	6680	2.6						
-	8.3 - 72	99	36.22	6470	3.0						
-	9.8 - 85	84	30.72	6210	3.6						
-	11 - 94	76	27.73	6050	3.9						
-	4.1 - 36	199	72.54	4150	1.00	K KF KA KAF	37 37 37 37	DRU DRU DRU DRU	80SJ4 80SJ4 80SJ4 80SJ4	22 24 22 23	580 581 582 581
-	4.4 - 38	186	67.80	4140	1.10						
-	5.1 - 45	161	58.60	4090	1.25						
-	6.0 - 52	137	49.79	4020	1.45						
-	6.7 - 59	122	44.46	3960	1.65						
-	7.9 - 69	104	37.97	3860	1.90						
-	8.4 - 73	98	35.57	3820	2.0						
-	10 - 87	82	29.96	3690	2.4						
-	10 - 91	79	28.83	3670	2.5						
-	12 - 104	69	24.99	3560	2.9						
-	13 - 112	64	23.36	3500	3.0						
-	15 - 129	55	20.19	3390	3.3						
-	17 - 152	47	17.15	3260	3.8						
-	20 - 170	42	15.31	3170	4.2						
-	23 - 200	36	13.08	3040	4.6						
-	25 - 215	33	12.14	2980	4.8						
-	7.0 - 61	107	42.87	3870	1.20						
-	8.1 - 71	92	36.96	3780	1.30						
-	10.0 - 87	75	30.11	3640	1.55						
-	12 - 105	62	24.91	3500	1.75						
-	13 - 113	59	23.19	3490	2.2						
-	14 - 118	55	22.08	3400	1.90						
-	15 - 131	51	19.99	3370	2.5						
-	18 - 160	42	16.29	3200	3.1						
-	22 - 194	34	13.47	3050	3.8						


P_m = 0.75 kW

	n_a min ⁻¹ 10-87Hz	M_a Nm	i	$F_{Ra}^{1)}$ N	SEW f_B					m kg	
-	10 - 89	73	29.29	3120	0.85						
-	11 - 96	68	27.16	3090	0.90						
-	16 - 141	47	18.55	2970	1.70						
-	19 - 165	40	15.84	2860	2.0						
-	20 - 178	37	14.69	2810	2.1						
-	24 - 205	32	12.70	2710	2.5	K	19	DRU	80SJ4	14	567
-	25 - 220	30	11.84	2660	2.6	KF	19	DRU	80SJ4	15	570
-	29 - 253	26	10.32	2570	2.9	KA	19	DRU	80SJ4	14	572
-	37 - 323	21	8.09	2450	3.8	KAF	19	DRU	80SJ4	14	570
-	43 - 378	18	6.91	2340	4.5						
-	47 - 407	17	6.41	2290	4.8						
-	54 - 471	14	5.54	2200	5.5						
-	58 - 506	13	5.16	2150	6.0						
-	67 - 580	12	4.50	2060	6.8						


P_m = 1.1 kW

	n_a min ⁻¹ 10-87Hz	M_a Nm	i	$F_{Ra}^{1)}$ N	SEW f_B					m kg	
-	1.7 - 15	700	174.19	28900	3.9	K	87	DRU	80MJ4	105	618
-	1.8 - 16	660	164.34*	28900	4.1	KF	87	DRU	80MJ4	115	619
-	2.0 - 18	590	147.32*	29000	4.5	KA	87	DRU	80MJ4	94	620
						KAF	87	DRU	80MJ4	105	619
-	2.2 - 19	540	135.28	19600	2.9						
-	2.3 - 20	515	128.52	19700	3.0	K	77	DRU	80MJ4	68	612
-	2.6 - 23	455	113.56	19800	3.4	KF	77	DRU	80MJ4	77	613
-	3.1 - 27	390	97.05	19900	4.0	KA	77	DRU	80MJ4	61	614
-	3.4 - 29	355	88.97	19900	4.3	KAF	77	DRU	80MJ4	69	613
-	3.8 - 33	310	78.07	20000	4.9						
-	2.8 - 24	430	108.03	12700	1.90						
-	2.9 - 25	410	102.62	12800	2.0						
-	3.3 - 29	360	90.04	12900	2.3						
-	3.9 - 34	305	76.37	13000	2.7	K	67	DRU	80MJ4	44	606
-	4.4 - 38	275	68.95	13000	3.0	KF	67	DRU	80MJ4	50	607
-	4.9 - 43	240	60.66	13000	3.4	KA	67	DRU	80MJ4	41	608
-	5.2 - 46	230	57.28	13000	3.6	KAF	67	DRU	80MJ4	47	607
-	6.2 - 54	196	48.77	13000	4.2						
-	6.8 - 59	178	44.32	13000	4.6						
-	2.8 - 24	435	108.29	8720	1.40						
-	2.9 - 25	410	102.88*	8820	1.45						
-	3.3 - 29	360	90.26*	9040	1.65						
-	3.9 - 34	305	76.56*	9260	1.95						
-	4.3 - 38	275	69.12	9370	2.2	K	57	DRU	80MJ4	38	600
-	4.9 - 43	240	60.81*	9480	2.5	KF	57	DRU	80MJ4	43	601
-	5.2 - 45	230	57.42*	9530	2.6	KA	57	DRU	80MJ4	36	602
-	6.1 - 53	197	48.89	9420	3.0	KAF	57	DRU	80MJ4	42	601
-	6.8 - 59	179	44.43	9200	3.4						
-	7.8 - 68	155	38.49	8870	3.9						
-	8.4 - 73	144	35.70	8700	4.2						
-	9.9 - 86	122	30.28	8330	4.9						
-	5.7 - 49	210	52.94	8370	2.4	K	49	DRU	80MJ4	43	596
-	6.0 - 52	200	50.29	8280	2.5	KF	49	DRU	80MJ4	45	597
-	6.8 - 59	179	44.44	8060	2.8	KA	49	DRU	80MJ4	40	598
-	7.9 - 69	153	37.98	7770	3.3	KAF	49	DRU	80MJ4	45	597
-	8.6 - 75	140	34.81	7600	3.6						


P _m = 1.1 kW											
	n _a min ⁻¹ 10-87Hz	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
-	3.3 - 29	365	90.86	6380	1.10	K KF KA KAF	47 47 47 47	DRU DRU DRU DRU	80MJ4 80MJ4 80MJ4 80MJ4	32 35 31 34	590 591 592 591
-	3.5 - 31	340	85.12*	6640	1.15						
-	4.0 - 35	300	75.20*	7040	1.30						
-	4.3 - 37	280	69.84	7150	1.40						
-	4.7 - 41	250	63.30*	7050	1.55						
-	5.3 - 46	225	56.83	6930	1.75						
-	6.1 - 53	197	48.95*	6750	2.0						
-	6.5 - 57	185	46.03*	6670	2.2						
-	7.6 - 66	159	39.61	6480	2.5						
-	8.5 - 74	142	35.39	6320	2.8						
-	9.6 - 83	126	31.30	6150	3.2						
-	10 - 89	118	29.32	6060	3.4						
-	12 - 101	104	25.91	5880	3.8						
-	12 - 108	97	24.06	5780	4.1						
-	14 - 120	88	21.81	5630	4.6						
-	6.9 - 60	175	43.45	6280	1.70	K KF KA KAF	39 39 39 39	DRU DRU DRU DRU	80MJ4 80MJ4 80MJ4 80MJ4	31 33 30 32	586 587 588 587
-	7.3 - 63	166	41.28	6230	1.80						
-	8.3 - 72	146	36.22	6080	2.1						
-	9.8 - 85	124	30.72	5870	2.4						
-	11 - 94	112	27.73	5740	2.7						
-	12 - 107	98	24.40	5580	3.0						
-	13 - 113	93	23.04	5510	3.2						
-	15 - 133	79	19.62	5300	3.7						
-	6.0 - 52	200	49.79	3440	1.00	K KF KA KAF	37 37 37 37	DRU DRU DRU DRU	80MJ4 80MJ4 80MJ4 80MJ4	24 27 24 26	580 581 582 581
-	6.7 - 59	179	44.46	3440	1.10						
-	7.9 - 69	153	37.97	3420	1.30						
-	8.4 - 73	143	35.57	3400	1.40						
-	10 - 87	121	29.96	3340	1.65						
-	12 - 104	101	24.99	3270	2.0						
-	13 - 112	94	23.36	3230	2.1						
-	15 - 129	81	20.19	3160	2.3						
-	17 - 152	69	17.15	3060	2.6						
-	20 - 170	62	15.31	2990	2.8						
-	23 - 200	53	13.08	2890	3.1						
-	25 - 215	49	12.14	2840	3.3						
-	29 - 249	42	10.49	2750	3.8						
-	34 - 293	36	8.91	2640	4.5						
-	38 - 328	32	7.96	2560	4.8						
-	8.1 - 71	135	36.96	3340	0.90	K KF KA KAF	29 29 29 29	DRU DRU DRU DRU	80MJ4 80MJ4 80MJ4 80MJ4	18 20 18 19	573 577 579 577
-	10.0 - 87	110	30.11	3290	1.05						
-	12 - 105	91	24.91	3210	1.20						
-	14 - 118	81	22.08	3150	1.30						
-	15 - 131	75	19.99	3160	1.75						
-	18 - 160	61	16.29	3030	2.1						
-	22 - 194	50	13.47	2900	2.6						
-	25 - 219	45	11.94	2820	2.9						
-	33 - 285	34	9.17	2640	3.8						
-	35 - 306	33	8.53	2670	3.8						
-	19 - 165	59	15.84	2670	1.35	K KF KA KAF	19 19 19 19	DRU DRU DRU DRU	80MJ4 80MJ4 80MJ4 80MJ4	17 17 17 17	567 570 572 570
-	20 - 178	55	14.69	2630	1.45						
-	24 - 205	47	12.70	2560	1.70						
-	25 - 220	44	11.84	2520	1.80						
-	29 - 253	39	10.32	2450	1.95						
-	43 - 378	26	6.91	2280	3.0						
-	47 - 407	24	6.41	2230	3.3						
-	54 - 471	21	5.54	2140	3.8						
-	58 - 506	20	5.16	2100	4.1						
-	67 - 580	17	4.50	2020	4.7						

P _m = 1.5 kW											
	n _a min ⁻¹ 10-87Hz	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
-	1.7 - 15	960	176.05*	40000	4.5	K	97	DRU	90MJ4	170	624
						KF	97	DRU	90MJ4	190	625
						KA	97	DRU	90MJ4	150	626
						KAF	97	DRU	90MJ4	175	625
-	2.0 - 18	800	147.32*	28900	3.3	K	87	DRU	90MJ4	110	618
-	2.4 - 21	695	126.91*	28900	3.9	KF	87	DRU	90MJ4	120	619
-	2.6 - 23	635	115.82	28900	4.2	KA	87	DRU	90MJ4	97	620
-	2.9 - 25	560	102.71*	29000	4.8	KAF	87	DRU	90MJ4	110	619
-	2.6 - 23	620	113.56	19400	2.5	K KF KA KAF	77	DRU	90MJ4	72	612
-	3.1 - 27	530	97.05	19600	2.9						
-	3.4 - 29	485	88.97	19700	3.2						
-	3.8 - 33	425	78.07	19800	3.6						
-	4.1 - 35	405	73.99	19800	3.8						
-	4.6 - 40	355	64.75	19900	4.4						
-	5.1 - 45	320	58.34	20000	4.8						
-	3.3 - 29	490	90.04	12400	1.65						
-	3.9 - 34	415	76.37	12700	1.95						
-	4.4 - 38	375	68.95	12900	2.2						
-	4.9 - 43	330	60.66	13000	2.5						
-	5.2 - 46	310	57.28	13000	2.6						
-	6.2 - 54	265	48.77	13000	3.1						
-	6.8 - 59	240	44.32	13000	3.4						
-	7.8 - 68	210	38.39	13000	3.8						
-	8.4 - 73	196	35.62	13000	4.2						
-	9.9 - 86	166	30.22	13000	5.0						
-	3.3 - 29	495	90.26*	8440	1.20	K KF KA KAF	57	DRU	90MJ4	42	600
-	3.9 - 34	420	76.56*	8790	1.45						
-	4.3 - 38	375	69.12	8970	1.60						
-	4.9 - 43	330	60.81*	9160	1.80						
-	5.2 - 45	315	57.42*	9230	1.90						
-	6.1 - 53	265	48.89	8950	2.2						
-	6.8 - 59	240	44.43	8780	2.5						
-	7.8 - 68	210	38.49	8500	2.8						
-	8.4 - 73	196	35.70	8360	3.1						
-	9.9 - 86	166	30.28	8040	3.6						
-	11 - 95	150	27.34	7840	4.0						
-	12 - 109	132	24.05	7590	4.5						
-	13 - 115	125	22.71	7480	4.8						
-	6.8 - 59	240	44.44	7590	2.0	K KF KA KAF	49	DRU	90MJ4	47	596
-	7.9 - 69	205	37.98	7370	2.4						
-	8.6 - 75	191	34.81	7240	2.6						
-	9.8 - 85	168	30.55	7040	3.0						
-	10 - 90	159	28.95	6960	3.1						
-	12 - 103	139	25.34	6750	3.6						
-	13 - 114	125	22.83	6580	4.0						
-	4.7 - 41	345	63.30*	6340	1.15	K KF KA KAF	47	DRU	90MJ4	36	590
-	5.3 - 46	310	56.83	6300	1.30						
-	6.1 - 53	265	48.95*	6200	1.50						
-	6.5 - 57	250	46.03*	6160	1.60						
-	7.6 - 66	215	39.61	6030	1.85						
-	8.5 - 74	194	35.39	5930	2.1						
-	12 - 101	142	25.91	5590	2.8						
-	14 - 120	120	21.81	5390	3.3						
-	15 - 133	108	19.58	5260	3.7						
-	18 - 155	93	16.86	5080	4.1						
-	19 - 165	87	15.86	5000	4.4						
-	22 - 191	75	13.65	4820	4.8						
-	25 - 222	65	11.77	4610	4.3						
-	28 - 247	58	10.56	4480	4.8						

P_m = 1.5 kW

	n_a min ⁻¹ 10-87Hz	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
-	8.3 - 72	199	36.22	5620	1.50						
-	9.8 - 85	169	30.72	5490	1.80						
-	11 - 94	152	27.73	5400	1.95						
-	12 - 107	134	24.40	5270	2.2	K	39	DRU	90MJ4	35	586
-	13 - 113	126	23.04	5220	2.4	KF	39	DRU	90MJ4	36	587
-	15 - 133	108	19.62	5050	2.7	KA	39	DRU	90MJ4	34	588
-	17 - 146	98	17.83	4940	3.0	KAF	39	DRU	90MJ4	35	587
-	19 - 169	85	15.44	4790	3.3						
-	22 - 194	74	13.44	4630	3.7						
-	8.4 - 73	195	35.57	2930	1.00						
-	10 - 87	164	29.96	2950	1.20						
-	15 - 129	111	20.19	2890	1.65						
-	17 - 152	94	17.15	2830	1.90						
-	20 - 170	84	15.31	2790	2.1	K	37	DRU	90MJ4	29	580
-	23 - 200	72	13.08	2720	2.3	KF	37	DRU	90MJ4	31	581
-	29 - 249	58	10.49	2610	2.8	KA	37	DRU	90MJ4	29	582
-	34 - 293	49	8.91	2520	3.3	KAF	37	DRU	90MJ4	30	581
-	38 - 328	44	7.96	2460	3.5						
-	44 - 384	37	6.80	2370	4.0						
-	47 - 410	35	6.37	2340	4.2						
-	56 - 487	29	5.36	2240	4.8						
-	12 - 105	124	24.91	2880	0.90						
-	14 - 118	110	22.08	2860	0.95						
-	18 - 160	83	16.29	2830	1.55						
-	22 - 194	69	13.47	2740	1.90	K	29	DRU	90MJ4	23	573
-	25 - 219	61	11.94	2680	2.1	KF	29	DRU	90MJ4	24	577
-	33 - 285	47	9.17	2530	2.8	KA	29	DRU	90MJ4	23	579
-	40 - 349	38	7.48	2420	3.2	KAF	29	DRU	90MJ4	24	577
-	43 - 375	36	6.95	2450	3.1						
-	52 - 454	30	5.75	2330	3.7						

P_m = 2.2 kW

	n_a min ⁻¹ 10-87Hz	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
-	1.7 - 15	1410	176.05*	40000	3.0	K	97	DRU	90LJ4	170	624
-	2.0 - 17	1230	153.21*	40000	3.5	KF	97	DRU	90LJ4	190	625
-	2.1 - 19	1120	140.28	40000	3.8	KA	97	DRU	90LJ4	150	626
-	2.4 - 21	990	123.93*	40000	4.3	KAF	97	DRU	90LJ4	175	625
-	2.0 - 18	1180	147.32*	28700	2.3						
-	2.4 - 21	1020	126.91*	28800	2.6						
-	2.6 - 23	930	115.82	28800	2.9	K	87	DRU	90LJ4	110	618
-	2.9 - 25	820	102.71*	28900	3.3	KF	87	DRU	90LJ4	120	619
-	3.5 - 30	695	86.34	28900	3.9	KA	87	DRU	90LJ4	100	620
-	3.8 - 33	635	79.34	28900	4.2	KAF	87	DRU	90LJ4	115	619
-	4.3 - 37	565	70.46	29000	4.8						
-	2.6 - 23	910	113.56	18600	1.70						
-	3.1 - 27	780	97.05	19000	2.0						
-	3.4 - 29	715	88.97	19200	2.2						
-	3.8 - 33	625	78.07	19400	2.5						
-	4.1 - 35	595	73.99	19500	2.6	K	77	DRU	90LJ4	75	612
-	4.6 - 40	520	64.75	19700	3.0	KF	77	DRU	90LJ4	83	613
-	5.1 - 45	465	58.34	19700	3.3	KA	77	DRU	90LJ4	68	614
-	5.9 - 51	410	51.18	19800	3.8	KAF	77	DRU	90LJ4	76	613
-	6.6 - 58	360	45.16	19900	4.3						
-	7.5 - 65	320	40.04	20000	4.8						
-	7.8 - 68	305	38.39	20000	4.8						

P_m = 2.2 kW											
	n_a min⁻¹ 10-87Hz	M_a Nm	i	F_{Ra}¹⁾ N	SEW f_B					m kg	
-	3.3 - 29	720	90.04	11100	1.15	K KF KA KAF	67 67 67 67	DRU DRU DRU DRU	90LJ4 90LJ4 90LJ4 90LJ4	50 56 48 53	606 607 608 607
-	3.9 - 34	610	76.37	11800	1.35						
-	4.4 - 38	555	68.95	12100	1.50						
-	4.9 - 43	485	60.66	12500	1.70						
-	5.2 - 46	460	57.28	12600	1.80						
-	6.2 - 54	390	48.77	12800	2.1						
-	6.8 - 59	355	44.32	13000	2.3						
-	7.8 - 68	305	38.39	13000	2.6						
-	8.4 - 73	285	35.62	13000	2.9						
-	9.9 - 86	240	30.22	13000	3.4						
-	11 - 96	215	27.28	13000	3.7						
-	13 - 109	193	24.00	13000	4.1						
-	13 - 115	182	22.66	13000	4.3						
-	16 - 135	155	19.30	13000	4.9						
-	4.3 - 38	555	69.12	7980	1.10	K KF KA KAF	57 57 57 57	DRU DRU DRU DRU	90LJ4 90LJ4 90LJ4 90LJ4	44 49 42 48	600 601 602 601
-	4.9 - 43	485	60.81*	8310	1.25						
-	5.2 - 45	460	57.42*	8270	1.30						
-	6.1 - 53	390	48.89	8130	1.50						
-	6.8 - 59	355	44.43	8030	1.70						
-	7.8 - 68	305	38.49	7860	1.95						
-	8.4 - 73	285	35.70	7760	2.1						
-	9.9 - 86	240	30.28	7530	2.5						
-	11 - 95	220	27.34	7380	2.7						
-	12 - 109	194	24.05	7180	3.1						
-	13 - 115	183	22.71	7100	3.3						
-	16 - 135	156	19.34	6840	3.7						
-	17 - 149	142	17.57	6690	3.9						
-	20 - 171	122	15.22	6460	4.4						
-	23 - 197	107	13.25	6230	4.8						
-	25 - 219	96	11.92	5980	4.3						
-	27 - 232	91	11.26	5890	4.6						
-	6.8 - 59	355	44.44	6770	1.40	K KF KA KAF	49 49 49 49	DRU DRU DRU DRU	90LJ4 90LJ4 90LJ4 90LJ4	50 52 47 52	596 597 598 597
-	7.9 - 69	305	37.98	6660	1.65						
-	8.6 - 75	280	34.81	6600	1.80						
-	9.8 - 85	245	30.55	6480	2.0						
-	10 - 90	230	28.95	6420	2.1						
-	12 - 103	200	25.34	6280	2.5						
-	13 - 114	184	22.83	6160	2.7						
-	15 - 130	161	20.03	6000	3.1						
-	17 - 148	142	17.67	5850	3.5						
-	19 - 167	126	15.67	5690	3.9						
-	6.1 - 53	390	48.95*	5250	1.00	K KF KA KAF	47 47 47 47	DRU DRU DRU DRU	90LJ4 90LJ4 90LJ4 90LJ4	39 42 38 41	590 591 592 591
-	6.5 - 57	370	46.03*	5260	1.10						
-	7.6 - 66	315	39.61	5260	1.25						
-	8.5 - 74	280	35.39	5240	1.40						
-	12 - 101	205	25.91	5090	1.90						
-	14 - 120	176	21.81	4960	2.3						
-	15 - 133	158	19.58	4880	2.5						
-	18 - 155	136	16.86	4750	2.8						
-	19 - 165	128	15.86	4700	3.0						
-	22 - 191	110	13.65	4550	3.3						
-	25 - 214	98	12.19	4440	3.6						
-	25 - 222	95	11.77	4370	3.0						
-	28 - 247	85	10.56	4260	3.3						
-	33 - 287	73	9.10	4120	3.8						
-	35 - 305	69	8.56	4060	3.9						
-	41 - 354	59	7.36	3910	4.2						
-	46 - 397	53	6.58	3800	4.5						
-	52 - 449	47	5.81	3680	4.9						

P_m = 2.2 kW

	n_a min⁻¹ 10-87Hz	M_a Nm	i	F_{Ra}¹⁾ N	SEW f_B					m kg	
-	8.3 - 72	290	36.22	4820	1.05						
-	9.8 - 85	245	30.72	4810	1.20						
-	11 - 94	220	27.73	4780	1.35						
-	12 - 107	196	24.40	4740	1.55	K	39	DRU	90LJ4	38	586
-	13 - 113	185	23.04	4710	1.60	KF	39	DRU	90LJ4	39	587
-	15 - 133	158	19.62	4620	1.85	KA	39	DRU	90LJ4	37	588
-	17 - 146	144	17.83	4550	2.0	KAF	39	DRU	90LJ4	38	587
-	19 - 169	124	15.44	4450	2.2						
-	22 - 194	108	13.44	4340	2.5						
-	28 - 246	85	10.61	4380	3.3						
-	15 - 129	162	20.19	2420	1.15						
-	17 - 152	138	17.15	2430	1.30						
-	20 - 170	123	15.31	2430	1.40						
-	23 - 200	105	13.08	2410	1.55	K	37	DRU	90LJ4	32	580
-	29 - 249	84	10.49	2370	1.90	KF	37	DRU	90LJ4	34	581
-	34 - 293	72	8.91	2320	2.2	KA	37	DRU	90LJ4	32	582
-	38 - 328	64	7.96	2280	2.4	KAF	37	DRU	90LJ4	33	581
-	44 - 384	55	6.80	2210	2.7						
-	47 - 410	51	6.37	2190	2.8						
-	56 - 487	43	5.36	2110	3.2						
-	75 - 656	32	3.98	1980	3.9						
-	18 - 160	122	16.29	2490	1.05						
-	22 - 194	101	13.47	2460	1.30	K	29	DRU	90LJ4	26	573
-	25 - 219	89	11.94	2420	1.45	KF	29	DRU	90LJ4	27	577
-	33 - 285	69	9.17	2340	1.90	KA	29	DRU	90LJ4	25	579
-	40 - 349	56	7.48	2260	2.2	KAF	29	DRU	90LJ4	26	577
-	43 - 375	53	6.95	2340	2.1						
-	52 - 454	44	5.75	2240	2.5						
-	59 - 512	39	5.10	2170	2.8						

P_m = 3.0 kW

	n_a min⁻¹ 10-87Hz	M_a Nm	i	F_{Ra}¹⁾ N	SEW f_B					m kg	
-	2.0 - 17	1680	153.21*	40000	2.6						
-	2.1 - 19	1530	140.28	40000	2.8	K	97	DRU	100MJ4	175	624
-	2.4 - 21	1360	123.93*	40000	3.2	KF	97	DRU	100MJ4	195	625
-	2.9 - 25	1150	105.13	40000	3.7	KA	97	DRU	100MJ4	155	626
-	3.1 - 27	1060	96.80	40000	4.0	KAF	97	DRU	100MJ4	180	625
-	3.5 - 30	940	86.52	40000	4.5						
-	2.4 - 21	1390	126.91*	28500	1.95						
-	2.6 - 23	1270	115.82	28600	2.1						
-	2.9 - 25	1120	102.71*	28700	2.4	K	87	DRU	100MJ4	115	618
-	3.5 - 30	940	86.34	28800	2.9	KF	87	DRU	100MJ4	125	619
-	3.8 - 33	870	79.34	28800	3.1	KA	87	DRU	100MJ4	105	620
-	4.3 - 37	770	70.46	28600	3.5	KAF	87	DRU	100MJ4	115	619
-	4.8 - 41	690	63.00*	27900	3.9						
-	5.3 - 46	620	56.64	27200	4.3						
-	3.1 - 27	1060	97.05	18000	1.45						
-	3.4 - 29	970	88.97	18400	1.60						
-	3.8 - 33	850	78.07	18800	1.80						
-	4.1 - 35	810	73.99	19000	1.90						
-	4.6 - 40	710	64.75	19200	2.2	K	77	DRU	100MJ4	80	612
-	5.1 - 45	640	58.34	19400	2.4	KF	77	DRU	100MJ4	88	613
-	5.9 - 51	560	51.18	19600	2.8	KA	77	DRU	100MJ4	73	614
-	6.6 - 58	495	45.16	19700	3.1	KAF	77	DRU	100MJ4	80	613
-	7.5 - 65	435	40.04	19800	3.5						
-	7.8 - 68	420	38.39	19800	3.6						
-	8.5 - 74	385	35.20	19900	4.0						
-	9.7 - 85	335	30.89	19900	4.6						
-	10 - 89	320	29.27	20000	4.8						

P_m = 3.0 kW													
	n_a min⁻¹ 10-87Hz	M_a Nm	i	F_{Ra}¹⁾ N	SEW f_B							m kg	
-	4.4 - 38	755	68.95	10800	1.10	K KF KA KAF	67	DRU	100MJ4	55	606		
-	4.9 - 43	665	60.66	11500	1.25								
-	5.2 - 46	625	57.28	11700	1.30								
-	6.2 - 54	535	48.77	12200	1.55								
-	6.8 - 59	485	44.32	12500	1.70								
-	7.8 - 68	420	38.39	12700	1.90								
-	9.9 - 86	330	30.22	13000	2.5								
-	11 - 96	295	27.28	13000	2.7								
-	13 - 109	260	24.00	13000	3.0								
-	13 - 115	245	22.66	13000	3.1								
-	16 - 135	210	19.30	13000	3.6								
-	17 - 149	192	17.54	13000	3.9								
-	20 - 172	167	15.19	13000	4.2								
-	23 - 197	145	13.22	12600	4.6								
-	24 - 209	137	12.48	12200	3.9								
-	28 - 246	117	10.63	11800	4.3								
-	31 - 270	106	9.66	11500	4.5								
-	36 - 312	92	8.37	11100	4.8								
-	6.1 - 53	535	48.89	7190	1.10	K KF KA KAF	57	DRU	100MJ4	49	600		
-	6.8 - 59	485	44.43	7180	1.25								
-	7.8 - 68	420	38.49	7120	1.40								
-	9.9 - 86	330	30.28	6950	1.80								
-	11 - 95	300	27.34	6860	2.0								
-	12 - 109	260	24.05	6720	2.3								
-	13 - 115	245	22.71	6660	2.4								
-	16 - 135	210	19.34	6470	2.7								
-	17 - 149	193	17.57	6350	2.9								
-	20 - 171	167	15.22	6160	3.2								
-	23 - 197	145	13.25	5980	3.5								
-	25 - 219	131	11.92	5720	3.2								
-	27 - 232	124	11.26	5640	3.4								
-	31 - 272	105	9.59	5440	3.9								
-	34 - 300	96	8.71	5320	4.1								
-	40 - 346	83	7.55	5130	4.4								
-	46 - 397	72	6.57	4950	4.8								
-	7.9 - 69	415	37.98	5860	1.20	K KF KA KAF	49	DRU	100MJ4	55	596		
-	8.6 - 75	380	34.81	5860	1.30								
-	9.8 - 85	335	30.55	5830	1.50								
-	10 - 90	315	28.95	5810	1.55								
-	12 - 103	275	25.34	5740	1.80								
-	13 - 114	250	22.83	5680	2.0								
-	15 - 130	215	20.03	5580	2.3								
-	17 - 148	194	17.67	5470	2.6								
-	19 - 167	172	15.67	5360	2.9								
-	22 - 195	147	13.38	5200	3.2								
-	26 - 230	125	11.37	5350	4.0								
-	8.5 - 74	385	35.39	4450	1.05	K KF KA KAF	47	DRU	100MJ4	43	590		
-	14 - 120	235	21.81	4480	1.65								
-	15 - 133	210	19.58	4440	1.85								
-	18 - 155	185	16.86	4380	2.0								
-	19 - 165	174	15.86	4340	2.2								
-	22 - 191	150	13.65	4250	2.4								
-	25 - 214	134	12.19	4170	2.6								
-	25 - 222	129	11.77	4090	2.2								
-	28 - 247	116	10.56	4010	2.4								
-	33 - 287	100	9.10	3900	2.8								
-	35 - 305	94	8.56	3860	2.9								
-	41 - 354	81	7.36	3740	3.1								
-	46 - 397	72	6.58	3640	3.3								
-	52 - 449	64	5.81	3540	3.6								
-	65 - 563	51	4.64	3350	4.0								

P_m = 3.0 kW

	n_a min ⁻¹ 10-87Hz	M_a Nm	i	$F_{Ra}^{1)}$ N	SEW f_B					m kg	
-	9.8 - 85	335	30.72	4040	0.90						
-	11 - 94	300	27.73	4090	1.00						
-	12 - 107	265	24.40	4120	1.10						
-	13 - 113	250	23.04	4130	1.20						
-	15 - 133	215	19.62	4120	1.35	K	39	DRU	100MJ4	42	586
-	17 - 146	196	17.83	4100	1.50	KF	39	DRU	100MJ4	44	587
-	19 - 169	170	15.44	4060	1.65	KA	39	DRU	100MJ4	41	588
-	22 - 194	148	13.44	4000	1.85	KAF	39	DRU	100MJ4	43	587
-	33 - 290	99	9.00	4040	3.0						
-	37 - 321	89	8.12	3940	3.4						
-	42 - 365	78	7.15	3820	3.8						

P_m = 4.0 kW

	n_a min ⁻¹ 10-87Hz	M_a Nm	i	$F_{Ra}^{1)}$ N	SEW f_B					m kg	
-	2.4 - 21	1810	123.93*	40000	2.4						
-	2.9 - 25	1530	105.13	40000	2.8	K	97	DRU	100LJ4	180	624
-	3.1 - 27	1410	96.80	40000	3.0	KF	97	DRU	100LJ4	200	625
-	3.5 - 30	1260	86.52	40000	3.4	KA	97	DRU	100LJ4	160	626
-	3.9 - 34	1130	77.89*	39200	3.8	KAF	97	DRU	100LJ4	185	625
-	4.3 - 37	1030	70.54	38300	4.2						
-	4.8 - 42	910	62.55	37200	4.7						
-	2.9 - 25	1500	102.71*	28500	1.80						
-	3.5 - 30	1260	86.34	28600	2.1	K	87	DRU	100LJ4	120	618
-	3.8 - 33	1160	79.34	28200	2.3	KF	87	DRU	100LJ4	130	619
-	4.3 - 37	1030	70.46	27600	2.6	KA	87	DRU	100LJ4	105	620
-	4.8 - 41	920	63.00*	27000	2.9	KAF	87	DRU	100LJ4	120	619
-	5.3 - 46	820	56.64	26400	3.3						
-	6.1 - 53	715	49.16	25600	3.8						
-	6.8 - 59	640	44.02	25000	4.0						
-	8.2 - 71	530	36.52*	23900	4.7						
-	3.8 - 33	1140	78.07	17700	1.35						
-	4.1 - 35	1080	73.99	18000	1.45	K	77	DRU	100LJ4	83	612
-	4.6 - 40	940	64.75	18500	1.65	KF	77	DRU	100LJ4	91	613
-	5.1 - 45	850	58.34	18800	1.80	KA	77	DRU	100LJ4	76	614
-	5.9 - 51	745	51.18	19100	2.1	KAF	77	DRU	100LJ4	83	613
-	6.6 - 58	660	45.16	19400	2.4						
-	7.5 - 65	585	40.04	19500	2.6						
-	9.7 - 85	450	30.89	19800	3.4						
-	10 - 89	425	29.27	19800	3.6						
-	12 - 102	370	25.62	19400	4.1						
-	13 - 113	335	23.08	18900	4.6						
-	9.8 - 85	445	30.55	5030	1.10						
-	10 - 90	420	28.95	5050	1.20	K	49	DRU	100LJ4	58	596
-	12 - 103	370	25.34	5080	1.35	KF	49	DRU	100LJ4	60	597
-	13 - 114	330	22.83	5080	1.50	KA	49	DRU	100LJ4	55	598
-	15 - 130	290	20.03	5050	1.70	KAF	49	DRU	100LJ4	60	597
-	17 - 148	255	17.67	5010	1.95						
-	19 - 167	225	15.67	4950	2.1						
-	22 - 195	196	13.38	4850	2.4						
-	33 - 286	134	9.14	4890	3.7						
-	35 - 301	127	8.66	4830	3.9						



10.4 Geometrisch mögliche Kombinationen K..DRE..J (IE2)

K19, $n_e=1400 \text{ min}^{-1}$						80 Nm	
n_a min^{-1}	M_{amax} Nm	F_{Ra} N	$\varphi_{(R)}$ °	i	DRE71SJ_FU	DRE71SJ DRE71MJ_FU DRE80SJ_FU	DRE71MJ DRE80SJ DRE80MJ_FU
 2							
24	70	4330	-	58.68			
26	70	4330	-	53.88			
28	70	4330	-	49.69			
31	69	4340	-	44.48			
34	67	4350	-	40.63			
41	64	4370	-	34.29			
44	80	4260	-	31.74			
48	61	4200	-	29.29			
48	80	4120	-	29.14			
52	60	4090	-	27.16			
52	80	3990	-	26.88			
58	80	3820	-	24.06			
64	80	3680	-	21.98			
75	80	3430	-	18.55			
88	80	3210	-	15.84			
95	80	3110	-	14.69			
110	80	2930	-	12.70			
118	79	2850	-	11.84			
136	76	2720	-	10.32			
146	63	2910	-	9.58			
173	80	2590	-	8.09			
203	80	2420	-	6.91			
218	80	2340	-	6.41			
253	80	2200	-	5.54			
271	80	2140	-	5.16			
311	80	2010	-	4.50			

K29, n _e =1400 min ⁻¹						130 Nm		
n _a min ⁻¹	M _{amax} Nm	F _{Ra} N	Φ _(/R) °	i	DRE71SJ_FU	DRE71SJ DRE71MJ_FU DRE80SJ_FU	DRE71MJ DRE80SJ DRE80MJ_FU	DRE90MJ DRE90MJ_FU DRE90LJ_FU
 2								
19	130	4980	-	71.93				
21	130	4980	-	66.25				
23	130	4980	-	61.28				
26	130	4980	-	54.89				
28	130	4980	-	50.35				
33	128	4790	-	42.87				
36	130	4720	-	38.90				
38	122	4560	-	36.96				
39	130	4560	-	35.83				
42	130	4410	-	33.15				
46	115	4250	-	30.11				
47	130	4210	-	29.69				
51	130	4060	-	27.23				
56	109	3980	-	24.91				
60	130	3790	-	23.19				

K29, $n_e=1400 \text{ min}^{-1}$					130 Nm			
n_a min^{-1}	M_{amax} Nm	F_{Ra} N	$\Phi_{(R)}$ °	i	DRE71SJ_FU	DRE71SJ DRE71MJ_FU DRE80SJ_FU	DRE71MJ DRE80SJ DRE80MJ_FU	DRE90MJ DRE90MJ_FU DRE90LJ_FU
63	105	3820	-	22.08				
70	130	3550	-	19.99				
86	130	3240	-	16.29				
104	130	2970	-	13.47				
117	130	2810	-	11.94				
141	110	3000	-	9.90				
153	130	2470	-	9.17				
164	122	2740	-	8.53				
187	123	2300	-	7.48				
201	112	2580	-	6.95				
243	112	2370	-	5.75				
275	110	2260	-	5.10				
357	126	1910	-	3.92				
439	110	1830	-	3.19				

K37, $n_e=1400 \text{ min}^{-1}$					200 Nm			
n_a min^{-1}	M_{amax} Nm	F_{Ra} N	$\Phi_{(R)}$ °	i	DRE71SJ_FU	DRE71SJ DRE71MJ_FU DRE80SJ_FU	DRE71MJ DRE80SJ DRE80MJ_FU	DRE90MJ DRE90MJ_FU DRE90LJ_FU
 3								
13	200	5640	6.8	106.38				
14	200	5640	6.8	97.81				
17	200	5640	6.9	83.69				
19	200	5520	6.9	72.54				
21	200	5360	6.9	67.80				
24	200	5020	6.9	58.60				
28	200	4660	7	49.79				
31	200	4420	7	44.46				
37	200	4100	7	37.97				
39	200	3970	7.1	35.57				
47	200	3650	7.1	29.96				
49	200	3580	8.1	28.83				
56	200	3330	8.1	24.99				
60	195	3260	8.2	23.36				
69	185	3110	8.3	20.19				
82	180	2900	8.4	17.15				
91	175	2780	8.5	15.31				
107	165	2650	8.6	13.08				
115	160	2600	11.9	12.14				
133	160	2410	12.2	10.49				
157	160	2200	12.4	8.91				
176	155	2110	12.5	7.96				
206	150	1980	12.8	6.80				
220	145	1950	12.9	6.37				
261	140	1810	13.2	5.36				
352	125	1660	13	3.98				

K37R17, $n_e=1400 \text{ min}^{-1}$					200 Nm	
n_a min^{-1}	M_{amax} Nm	F_{Ra} N	$\Phi_{(R)}$ '	i	DRE71SJ_FU	DRE71MJ_FU DRE80SJ_FU
 3 3						
0.20	200	5640	-	6832		
0.24	200	5640	-	5922		
0.25	200	5640	-	5491		
0.29	200	5640	-	4759		
0.34	200	5640	-	4160		
0.38	200	5640	-	3645		
0.44	200	5640	-	3205		
0.50	200	5640	-	2801		
0.57	200	5640	-	2454		
0.65	200	5640	-	2166		
0.74	200	5640	-	1891		
0.84	200	5640	-	1660		
0.95	200	5640	-	1466		
1.1	200	5640	-	1288		
1.2	200	5640	-	1136		
 3 2						
1.4	200	5640	-	996		
1.6	200	5640	-	876		
1.8	200	5640	-	761		
2.1	200	5640	-	671		
2.4	200	5640	-	585		
2.7	200	5640	-	512		
3.1	200	5640	-	451		
3.5	200	5640	-	396		
4.0	200	5640	-	346		
4.6	200	5640	-	304		
5.2	200	5640	-	267		
6.0	200	5640	-	234		
6.8	200	5640	-	205		
7.7	200	5640	-	181		
8.8	200	5640	-	160		
10	200	5640	-	136		
11	200	5640	-	127		
13	200	5640	-	110		
15	200	5640	-	96		

K39, $n_e=1400 \text{ min}^{-1}$					300 Nm				
n_a min^{-1}	M_{amax} Nm	F_{Ra} N	$\Phi_{(R)}$ '	i	DRE71SJ_FU	DRE71SJ DRE71MJ_FU DRE80SJ_FU	DRE71MJ DRE80SJ DRE80MJ_FU	DRE80MJ DRE90MJ DRE90MJ_FU DRE90LJ_FU	DRE90LJ DRE100MJ_FU
 2									
24	300	7500	-	58.24					
28	300	7440	-	49.69					
32	300	7000	-	43.45					
34	300	6840	-	41.28					
39	300	6440	-	36.22					
46	300	5960	-	30.72					
50	300	5670	-	27.73					
57	300	5330	-	24.40					

K39, $n_e=1400 \text{ min}^{-1}$					300 Nm				
n_a min^{-1}	M_{amax} Nm	F_{Ra} N	$\Phi_{(R)}$ °	i	DRE71SJ_FU	DRE71SJ DRE71MJ_FU DRE80SJ_FU	DRE71MJ DRE80SJ DRE80MJ_FU	DRE80MJ DRE90MJ DRE90MJ_FU DRE90LJ_FU	DRE90LJ DRE100MJ_FU
61	300	5180	-	23.04					
71	295	4820	-	19.62					
79	290	4630	-	17.83					
91	280	4380	-	15.44					
104	270	4160	-	13.44					
110	250	4930	-	12.73					
116	255	4790	-	12.09					
132	285	4360	-	10.61					
156	300	3950	-	9.00					
172	300	3760	-	8.12					
196	300	3530	-	7.15					
207	300	3430	-	6.75					
243	275	3300	-	5.75					
268	260	3240	-	5.22					
310	240	3130	-	4.52					
355	215	3070	-	3.94					
498	170	2870	-	2.81					

K39R17, n _e =1400 min ⁻¹					300 Nm	
n _a min ⁻¹	M _{amax} Nm	F _{Ra} N	Φ _(/R) °	i	DRE71SJ_FU	DRE71MJ_FU DRE80SJ_FU
 2  3						
0.35	300	7500	-	4057		
0.42	300	7500	-	3370		
0.48	300	7500	-	2906		
0.56	300	7500	-	2508		
0.59	300	7500	-	2367		
0.65	300	7500	-	2162		
0.74	300	7500	-	1881		
0.79	300	7500	-	1762		
0.86	300	7500	-	1622		
0.94	300	7500	-	1494		
1.1	300	7500	-	1321		
1.2	300	7500	-	1169		
1.3	300	7500	-	1093		
 2  2						
1.5	300	7500	-	956		
1.7	300	7500	-	814		
2.0	300	7500	-	711		
2.3	300	7500	-	605		
2.8	300	7500	-	504		
3.1	300	7500	-	454		
3.5	300	7500	-	399		
3.8	300	7500	-	365		
4.5	300	7500	-	312		
4.7	300	7500	-	299		
5.5	300	7500	-	254		
6.0	300	7500	-	234		
6.7	300	7500	-	210		

19391609/DE – 06/2017

K39R17, $n_e=1400 \text{ min}^{-1}$					300 Nm	
n_a min^{-1}	M_{amax} Nm	F_{Ra} N	$\varphi_{(R)}$ °	i	DRE71SJ_FU	DRE71MJ_FU DRE80SJ_FU
7.4	300	7500	-	189		
8.0	300	7500	-	174		
9.0	300	7500	-	156		
9.9	300	7500	-	142		
12	300	7500	-	117		
19	295	7500	-	75		

K47, $n_e=1400 \text{ min}^{-1}$					400 Nm				
n_a min^{-1}	M_{amax} Nm	F_{Ra} N	$\varphi_{(R)}$ °	i	DRE71SJ_FU	DRE71SJ DRE71MJ_FU DRE80SJ_FU	DRE71MJ DRE80SJ DRE80MJ_FU	DRE80MJ DRE90MJ DRE90MJ_FU DRE90LJ_FU	DRE90LJ DRE100MJ_FU
 3									
11	400	5920	6.4	131.87*					
12	400	5920	6.4	121.48*					
13	400	5920	6.4	104.37					
15	400	5920	6.4	90.86					
16	400	5920	6.4	85.12*					
19	400	5920	6.5	75.20*					
20	400	5920	6.5	69.84					
22	400	5920	6.5	63.30*					
25	400	5920	6.5	56.83					
29	400	5920	6.6	48.95*					
30	400	5920	6.6	46.03*					
35	400	5920	6.6	39.61					
40	400	5920	6.7	35.39					
45	400	5700	7.5	31.30					
48	400	5520	7.5	29.32					
54	400	5170	7.6	25.91					
58	400	4970	7.7	24.06					
64	400	4710	7.7	21.81					
72	400	4440	7.7	19.58					
83	380	4220	7.8	16.86					
88	380	4080	7.9	15.86					
103	360	3890	8	13.65					
115	350	3720	8.3	12.19					
119	280	4060	10.5	11.77					
133	280	3830	10.6	10.56					
154	280	3540	10.7	9.10					
164	270	3500	10.8	8.56					
190	250	3380	11	7.36					
213	240	3270	11.5	6.58					
241	230	3140	11.8	5.81					
302	205	2980	12	4.64					

K47R37, $n_e=1400 \text{ min}^{-1}$					400 Nm				
n_a min^{-1}	M_{amax} Nm	F_{Ra} N	$\varphi_{(R)}$ °	i	DRE71SJ_FU	DRE71SJ DRE71MJ_FU DRE80SJ_FU	DRE71MJ DRE80SJ DRE80MJ_FU	DRE90MJ DRE90MJ_FU DRE90LJ_FU	DRE90LJ DRE100MJ_FU
 3  3									
0.14	400	5920	-	10138					
0.16	400	5920	-	8534					

K47R37, $n_e=1400 \text{ min}^{-1}$					400 Nm				
n_a min^{-1}	M_{amax} Nm	F_{Ra} N	$\Phi_{(R)}$ °	i	DRE71SJ_FU	DRE71SJ DRE71MJ_FU DRE80SJ_FU	DRE71MJ DRE80SJ DRE80MJ_FU	DRE90MJ DRE90MJ_FU DRE90LJ_FU	DRE90LJ DRE100MJ_FU
0.18	400	5920	-	7662					
0.21	400	5920	-	6826					
0.23	400	5920	-	5983					
0.27	400	5920	-	5159					
0.30	400	5920	-	4601*					
0.36	400	5920	-	3940					
0.40	400	5920	-	3477					
0.46	400	5920	-	3043					
0.51	400	5920	-	2733					
0.59	400	5920	-	2354					
0.68	400	5920	-	2063					
0.77	400	5920	-	1819					
0.88	400	5920	-	1586					
1.0	400	5920	-	1388					
 3  2									
1.1	400	5920	-	1222					
1.3	400	5920	-	1097					
1.5	400	5920	-	945					
1.7	400	5920	-	831*					
1.9	400	5920	-	718*					
2.2	400	5920	-	639					
2.5	400	5920	-	552					
2.8	400	5920	-	495					
3.3	400	5920	-	426					
3.7	400	5920	-	375					
4.3	400	5920	-	327					
4.8	400	5920	-	289					
5.5	400	5920	-	256					
6.2	400	5920	-	225					
7.1	400	5920	-	198					
8.2	400	5920	-	171					
9.2	400	5920	-	153					
11	400	5920	-	131					
12	400	5920	-	112					
14	400	5920	-	99					
15	400	5920	-	94					

K49, n _e =1400 min ⁻¹										500 Nm
n _a min ⁻¹	M _{amax} Nm	F _{Ra} N	Φ _(/R) °	i	DRE71SJ_FU	DRE71SJ DRE71MJ_FU DRE80SJ_FU	DRE71MJ DRE80SJ DRE80MJ_FU	DRE80MJ DRE90MJ DRE90MJ_FU DRE90LJ_FU	DRE90LJ DRE100MJ_FU	DRE100MJ
 2										
19	475	9000	-	75.20						
20	445	9000	-	70.19						
23	500	9000	-	60.27						
26	500	8590	-	52.94						
28	500	8380	-	50.29						
32	500	7900	-	44.44						
37	500	7310	-	37.98						
40	500	7000	-	34.81						

K49, $n_e=1400 \text{ min}^{-1}$										500 Nm
n_a min^{-1}	M_{amax} Nm	F_{Ra} N	$\Phi_{(R)}$ °	i	DRE71SJ_FU	DRE71SJ DRE71MJ_FU DRE80SJ_FU	DRE71MJ DRE80SJ DRE80MJ_FU	DRE80MJ DRE90MJ DRE90MJ_FU DRE90LJ_FU	DRE90LJ DRE100MJ_FU	DRE100MJ
46	500	6550	-	30.55						
48	500	6370	-	28.95						
55	500	5940	-	25.34						
61	500	5610	-	22.83						
70	500	5220	-	20.03						
79	500	4860	-	17.67						
89	490	4590	-	15.67						
105	470	4320	-	13.38						
123	495	5000	-	11.37						
134	480	4860	-	10.42						
153	500	4460	-	9.14						
162	500	4340	-	8.66						
185	500	4050	-	7.58						
205	500	3840	-	6.83						
234	500	3570	-	5.99						
265	485	3400	-	5.29						
299	465	3270	-	4.69						
350	440	3110	-	4.00						

K49R37, $n_e=1400 \text{ min}^{-1}$										500 Nm
n_a min^{-1}	M_{amax} Nm	F_{Ra} N	$\Phi_{(R)}$ °	i	DRE71SJ_FU	DRE71SJ DRE71MJ_FU DRE80SJ_FU	DRE71MJ DRE80SJ DRE80MJ_FU	DRE90MJ DRE90MJ_FU DRE90LJ_FU	DRE90LJ DRE100MJ_FU	
 2  3										
0.20	500	9000	-	7137						
0.23	500	9000	-	5991						
0.27	500	9000	-	5120						
0.35	500	9000	-	4034						
0.39	500	9000	-	3580						
0.45	500	9000	-	3081						
0.50	500	9000	-	2773						
0.55	500	9000	-	2545						
0.59	500	9000	-	2372						
0.66	500	9000	-	2118						
0.72	500	9000	-	1941						
0.80	500	9000	-	1741						
0.86	500	9000	-	1632						
0.92	500	9000	-	1521						
1.1	500	9000	-	1228						
1.4	500	9000	-	1000						
 2  2										
0.98	500	9000	-	1424						
1.1	500	9000	-	1309						
1.2	500	9000	-	1120						
1.5	500	9000	-	908						
1.7	500	9000	-	802						
2.0	500	9000	-	701						
2.2	500	9000	-	645						
2.4	500	9000	-	595						
2.6	500	9000	-	543						

K49R37, $n_e=1400 \text{ min}^{-1}$					500 Nm				
n_a min^{-1}	M_{amax} Nm	F_{Ra} N	$\Phi_{(R)}$ °	i	DRE71SJ_FU	DRE71SJ DRE71MJ_FU DRE80SJ_FU	DRE71MJ DRE80SJ DRE80MJ_FU	DRE90MJ DRE90MJ_FU DRE90LJ_FU	DRE90LJ DRE100MJ_FU
2.8	500	9000	-	501					
3.1	500	9000	-	449					
3.5	500	9000	-	401					
3.9	500	9000	-	360					
4.2	500	9000	-	330					
4.7	500	9000	-	300					
5.1	500	9000	-	274					
5.8	500	9000	-	243					
6.5	500	9000	-	217					
7.3	500	9000	-	193					
8.0	500	9000	-	176					
9.2	500	9000	-	152					
11	500	9000	-	125					
14	500	9000	-	99					

K57, $n_e=1400 \text{ min}^{-1}$					600 Nm				
n_a min^{-1}	M_{amax} Nm	F_{Ra} N	$\Phi_{(R)}$ °	i	DRE71SJ_FU	DRE71SJ DRE71MJ_FU DRE80SJ_FU	DRE71MJ DRE80SJ DRE80MJ_FU	DRE80MJ DRE90MJ DRE90MJ_FU DRE90LJ_FU	DRE90LJ DRE100MJ_FU
 3									
9.6	600	7630	5.9	145.14*					
11	600	7630	5.9	123.85					
13	600	7630	5.9	108.29					
14	600	7630	5.9	102.88*					
16	600	7630	5.9	90.26*					
18	600	7630	5.9	76.56*					
20	600	7630	6	69.12					
23	600	7630	6	60.81*					
24	600	7630	6	57.42*					
29	600	7630	6	48.89					
32	600	7630	6.1	44.43					
36	600	7630	6.1	38.49					
39	600	7630	6.8	35.70					
46	600	7300	6.9	30.28					
51	600	6930	6.9	27.34					
58	600	6480	6.9	24.05					
62	600	6280	6.9	22.71					
72	575	5910	7	19.34					
80	555	5740	7.2	17.57					
92	535	5430	7.3	15.22					
106	510	5190	7.4	13.25					
117	415	5150	9.4	11.92					
124	415	4990	9.5	11.26					
146	405	4650	9.6	9.59					
161	390	4520	10	8.71					
185	365	4360	10.2	7.55					
213	345	4180	10.4	6.57					
299	300	3800	11	4.69					

K57R37, $n_e=1400 \text{ min}^{-1}$					600 Nm				
n_a min^{-1}	M_{amax} Nm	F_{Ra} N	$\Phi_{(R)}$ °	i	DRE71SJ_FU	DRE71SJ DRE71MJ_FU DRE80SJ_FU	DRE71MJ DRE80SJ DRE80MJ_FU	DRE90MJ DRE90MJ_FU DRE90LJ_FU	DRE90LJ DRE100MJ_FU
 3 3									
0.12	600	7630	-	12169					
0.13	600	7630	-	11162*					
0.15	600	7630	-	9503					
0.16	600	7630	-	8547					
0.19	600	7630	-	7277					
0.22	600	7630	-	6478*					
0.25	600	7630	-	5662*					
0.28	600	7630	-	5033					
0.32	600	7630	-	4340					
0.36	600	7630	-	3854					
0.41	600	7630	-	3390					
0.48	600	7630	-	2924					
0.54	600	7630	-	2593					
0.62	600	7630	-	2249					
0.70	600	7630	-	1986					
 3 2									
0.80	600	7630	-	1743					
0.91	600	7630	-	1539					
1.0	600	7630	-	1354					
1.2	600	7630	-	1174					
1.4	600	7630	-	1036*					
1.5	600	7630	-	906*					
1.7	600	7630	-	806					
2.0	600	7630	-	699					
2.3	600	7630	-	615					
2.6	600	7630	-	544*					
3.0	600	7630	-	473					
3.3	600	7630	-	421					
3.9	600	7630	-	362					
4.4	600	7630	-	319					
5.0	600	7630	-	280					
5.7	600	7630	-	246					
6.5	600	7630	-	215					
7.3	600	7630	-	192					
8.4	600	7630	-	166					
9.7	600	7630	-	145					
11	600	7630	-	129					
13	600	7630	-	111					
14	600	7630	-	97					

K67, $n_e=1400 \text{ min}^{-1}$					820 Nm				
n_a min^{-1}	M_{amax} Nm	F_{Ra} N	$\Phi_{(R)}$ °	i	DRE71SJ_FU	DRE71SJ DRE71MJ_FU DRE80SJ_FU	DRE71MJ DRE80SJ DRE80MJ_FU	DRE80MJ DRE90MJ DRE90MJ_FU DRE90LJ_FU	DRE90LJ DRE100MJ_FU
 3									
9.7	820	10300	6.2	144.79*					
11	820	10300	6.2	123.54					
13	820	10300	6.1	108.03					

K67, $n_e=1400 \text{ min}^{-1}$						820 Nm			
n_a min^{-1}	M_{amax} Nm	F_{Ra} N	$\varphi_{(R)}$ °	i	DRE71SJ_FU	DRE71SJ DRE71MJ_FU DRE80SJ_FU	DRE71MJ DRE80SJ DRE80MJ_FU	DRE80MJ DRE90MJ DRE90MJ_FU DRE90LJ_FU	DRE90LJ DRE100MJ_FU
14	820	10300	6.1	102.62					
16	820	10300	6.2	90.04					
18	820	10300	6.2	76.37					
20	820	10300	6.2	68.95					
23	820	10300	6.2	60.66					
24	820	10300	6.2	57.28					
29	820	10300	6.3	48.77					
32	820	10300	6.3	44.32					
36	800	10500	6.4	38.39					
39	820	10300	7.1	35.62					
46	820	10300	7.1	30.22					
51	820	10300	7.1	27.28					
58	800	10500	7.2	24.00					
62	780	10700	7.2	22.66					
73	760	10800	7.3	19.30					
80	740	11000	7.5	17.54					
92	700	11300	7.5	15.19					
106	670	11500	7.6	13.22					
112	530	12300	8.6	12.48					
132	500	11800	8.8	10.63					
145	480	11500	9.1	9.66					
167	440	11100	9.3	8.37					
192	420	10700	9.4	7.28					
269	350	9860	10	5.20					

K67R37, $n_e=1400 \text{ min}^{-1}$						820 Nm			
n_a min^{-1}	M_{amax} Nm	F_{Ra} N	$\varphi_{(R)}$ °	i	DRE71SJ_FU	DRE71SJ DRE71MJ_FU DRE80SJ_FU	DRE71MJ DRE80SJ DRE80MJ_FU	DRE90MJ DRE90MJ_FU DRE90LJ_FU	DRE90LJ DRE100MJ_FU
 3  3									
0.12	820	10300	-	12139					
0.13	820	10300	-	11134					
0.15	820	10300	-	9479					
0.17	820	10300	-	8173					
0.19	820	10300	-	7259					
0.22	820	10300	-	6462					
0.25	820	10300	-	5648					
0.29	820	10300	-	4846					
0.32	820	10300	-	4329					
0.37	820	10300	-	3750					
0.42	820	10300	-	3315					
0.48	820	10300	-	2917					
0.55	820	10300	-	2532					
0.62	820	10300	-	2244					
0.71	820	10300	-	1981					
 3  2									
0.81	820	10300	-	1739					
0.91	820	10300	-	1535					
1.0	820	10300	-	1351					
1.2	820	10300	-	1171					

K67R37, $n_e=1400 \text{ min}^{-1}$						820 Nm			
n_a min^{-1}	M_{amax} Nm	F_{Ra} N	$\Phi_{(R)}$ °	i	DRE71SJ_FU	DRE71SJ DRE71MJ_FU DRE80SJ_FU	DRE71MJ DRE80SJ DRE80MJ_FU	DRE90MJ DRE90MJ_FU DRE90LJ_FU	DRE90LJ DRE100MJ_FU
1.4	820	10300	-	1034					
1.6	820	10300	-	903					
1.8	820	10300	-	793					
2.0	820	10300	-	697					
2.3	820	10300	-	613					
2.6	820	10300	-	542					
3.0	820	10300	-	471					
3.3	820	10300	-	420					
3.9	820	10300	-	361					
4.3	820	10300	-	323					
5.0	820	10300	-	279					
5.7	820	10300	-	246					
6.5	820	10300	-	217					
7.3	820	10300	-	191					
8.4	820	10300	-	166					
9.7	820	10300	-	144					
11	820	10300	-	122					

K77, n _e =1400 min ⁻¹										1550 Nm
n _a min ⁻¹	M _{amax} Nm	F _{Ra} N	Φ _(R) °	i	DRE71SJ_FU	DRE71SJ DRE71MJ_FU DRE80SJ_FU	DRE71MJ DRE80SJ DRE80MJ_FU	DRE80MJ DRE90MJ DRE90MJ_FU DRE90LJ_FU	DRE90LJ DRE100MJ_FU	DRE100MJ
 3										
7.3	1450	16100	5.4	192.18						
7.8	1450	16100	5.4	179.37						
9.1	1550	15400	5.4	154.02						
10	1550	15400	5.4	135.28						
11	1550	15400	5.4	128.52						
12	1550	15400	5.4	113.56						
14	1550	15400	5.4	97.05						
16	1550	15400	5.4	88.97						
18	1550	15400	5.4	78.07						
19	1550	15400	5.4	73.99						
22	1550	15400	5.5	64.75						
24	1550	15400	5.5	58.34						
27	1550	15400	5.5	51.18						
31	1550	15400	5.5	45.16						
35	1550	15400	5.6	40.04						
36	1500	15700	6	38.39						
40	1550	15400	6	35.20						
45	1550	15400	6.1	30.89						
48	1550	15400	6.1	29.27						
55	1550	15400	6.1	25.62						
61	1550	15400	6.3	23.08						
69	1500	15700	6.3	20.25						
78	1450	16100	6.3	17.87						
88	1400	15500	6.4	15.84						
104	1340	14800	6.5	13.52						
113	1000	15100	7.9	12.36						
129	990	14400	7.8	10.84						

K77, $n_e=1400 \text{ min}^{-1}$										1550 Nm
n_a min^{-1}	M_{amax} Nm	F_{Ra} N	$\varphi_{(R)}$ °	i	DRE71SJ_FU	DRE71SJ DRE71MJ_FU DRE80SJ_FU	DRE71MJ DRE80SJ DRE80MJ_FU	DRE80MJ DRE90MJ DRE90MJ_FU DRE90LJ_FU	DRE90LJ DRE100MJ_FU	DRE100MJ
146	940	13900	7.9	9.56						
165	890	13500	8.2	8.48						
193	820	13100	8.3	7.24						

K77R37, $n_e=1400 \text{ min}^{-1}$										1550 Nm
n_a min^{-1}	M_{amax} Nm	F_{Ra} N	$\varphi_{(R)}$ °	i	DRE71SJ_FU	DRE71SJ DRE71MJ_FU DRE80SJ_FU	DRE71MJ DRE80SJ DRE80MJ_FU	DRE90MJ DRE90MJ_FU DRE90LJ_FU	DRE90LJ DRE100MJ_FU	
 3  3										
0.09	1550	15400	-	15310						
0.10	1550	15400	-	14043						
0.12	1550	15400	-	11955						
0.14	1550	15400	-	10217						
0.16	1550	15400	-	8809						
0.19	1550	15400	-	7528						
0.21	1550	15400	-	6606						
0.24	1550	15400	-	5774						
0.28	1550	15400	-	5089						
0.31	1550	15400	-	4489						
0.35	1550	15400	-	3961						
0.40	1550	15400	-	3485						
0.48	1550	15400	-	2901						
0.52	1550	15400	-	2717						
0.59	1550	15400	-	2370						
 3  2										
0.68	1550	15400	-	2050						
0.79	1550	15400	-	1772						
0.92	1550	15400	-	1514						
1.0	1550	15400	-	1388						
1.1	1550	15400	-	1218						
1.3	1550	15400	-	1053						
1.5	1550	15400	-	924						
1.7	1550	15400	-	815						
2.0	1550	15400	-	709						
2.3	1550	15400	-	622						
2.5	1550	15400	-	552						
2.9	1550	15400	-	485						
3.3	1550	15400	-	428						
3.8	1550	15400	-	367						
4.3	1550	15400	-	328						
4.8	1550	15400	-	290						
5.6	1550	15400	-	252						
6.3	1550	15400	-	221						
7.2	1550	15400	-	195						
8.0	1550	15400	-	175						
9.1	1550	15400	-	154						

19391609/DE – 06/2017



K87, n _e =1400 min ⁻¹					2700 Nm				
n _a min ⁻¹	M _{amax} Nm	F _{Ra} N	Φ _(R) °	i	DRE71MJ_FU DRE80SJ_FU	DRE71MJ DRE80SJ DRE80MJ_FU	DRE80MJ DRE90MJ DRE90MJ_FU DRE90LJ_FU	DRE90LJ DRE100MJ_FU	DRE100MJ
 3									
7.1	2700	27300	5.3	197.37					
8.0	2700	27300	5.3	174.19					
8.5	2700	27300	5.3	164.34*					
9.5	2700	27300	5.4	147.32*					
11	2700	27300	5.4	126.91*					
12	2700	27300	5.4	115.82					
14	2700	27300	5.4	102.71*					
16	2700	27300	5.4	86.34					
18	2700	27300	5.4	79.34					
20	2700	27300	5.4	70.46					
22	2700	26200	5.4	63.00*					
25	2700	25000	5.5	56.64					
28	2700	23500	5.5	49.16					
32	2600	22800	5.5	44.02					
38	2500	21400	5.5	36.52*					
45	2700	19200	6.1	31.39					
50	2600	18500	6.1	27.88					
56	2500	18000	6.1	24.92					
62	2300	17900	6.2	22.41					
72	2300	16800	6.3	19.45					
80	2200	16300	6.3	17.42					
88	1800	16000	6.5	16.00					
97	2100	15300	6.4	14.45					
111	2000	14800	6.5	12.56					
125	1500	14900	6.7	11.17					
140	1500	14200	6.8	10.00					
169	1400	13500	7	8.29					
194	1300	13200	7.1	7.21					

K87R57, n _e =1400 min ⁻¹										2700 Nm
n _a min ⁻¹	M _{amax} Nm	F _{Ra} N	φ _(/R) °	i	DRE71SJ_FU	DRE71SJ DRE71MJ_FU DRE80SJ_FU	DRE71MJ DRE80SJ DRE80MJ_FU	DRE80MJ DRE90MJ DRE90MJ_FU DRE90LJ_FU	DRE90LJ DRE100MJ_FU	
 3  3										
0.09	2700	27300	-	14829						
0.11	2700	27300	-	13168						
0.12	2700	27300	-	11737						
0.14	2700	27300	-	10217						
0.15	2700	27300	-	9073						
0.18	2700	27300	-	7854						
0.20	2700	27300	-	6832						
0.24	2700	27300	-	5930						
0.27	2700	27300	-	5240						
0.31	2700	27300	-	4562						
0.35	2700	27300	-	4037						
0.39	2700	27300	-	3609						
0.45	2700	27300	-	3107						
0.51	2700	27300	-	2728						

K87R57, $n_e=1400 \text{ min}^{-1}$					2700 Nm				
n_a min^{-1}	M_{amax} Nm	F_{Ra} N	$\Phi_{(R)}$ °	i	DRE71SJ_FU	DRE71SJ DRE71MJ_FU DRE80SJ_FU	DRE71MJ DRE80SJ DRE80MJ_FU	DRE80MJ DRE90MJ DRE90MJ_FU DRE90LJ_FU	DRE90LJ DRE100MJ_FU
0.59	2700	27300	-	2371					
 3  2									
0.67	2700	27300	-	2088					
0.76	2700	27300	-	1854					
0.84	2700	27300	-	1657					
0.99	2700	27300	-	1415					
1.1	2700	27300	-	1229					
1.3	2700	27300	-	1078					
1.5	2700	27300	-	951					
1.7	2700	27300	-	837					
1.9	2700	27300	-	726					
2.2	2700	27300	-	638					
2.5	2700	27300	-	562*					
3.0	2700	27300	-	474*					
3.3	2700	27300	-	426					
3.8	2700	27300	-	373					
4.2	2700	27300	-	330					
4.8	2700	27300	-	294					
5.6	2700	27300	-	250					
5.9	2700	27300	-	236					
7.0	2700	27300	-	201					
7.7	2700	27300	-	183					
8.8	2700	27300	-	159					
9.9	2600	27400	-	141					

K97, $n_e=1400 \text{ min}^{-1}$					4300 Nm				
n_a min^{-1}	M_{amax} Nm	F_{Ra} N	$\Phi_{(R)}$ °	i	DRE71MJ_FU DRE80SJ_FU	DRE71MJ DRE80SJ DRE80MJ_FU	DRE80MJ DRE90MJ DRE90MJ_FU DRE90LJ_FU	DRE90LJ DRE100MJ_FU	DRE100MJ
 3									
8.0	4300	40000	6.8	176.05*					
9.1	4300	40000	6.8	153.21*					
10.0	4300	40000	6.8	140.28					
11	4300	40000	6.8	123.93*					
13	4300	40000	6.8	105.13					
14	4300	40000	6.8	96.80					
16	4300	38800	6.8	86.52					
18	4300	37100	6.8	77.89*					
20	4300	35600	6.9	70.54					
22	4300	33800	6.9	62.55					
25	4300	32300	6.9	56.55					
29	4300	30000	6.9	47.93*					
33	4300	28300	6.9	41.87					
37	4300	27100	7.4	38.30					
41	4300	25700	7.5	34.23					
45	4300	24500	7.5	30.82					
50	4300	23300	7.5	27.91					
57	4300	22000	7.6	24.75					
63	4300	20900	7.6	22.37					

K97, $n_e=1400 \text{ min}^{-1}$									4300 Nm
n_a min^{-1}	M_{amax} Nm	F_{Ra} N	$\varphi_{(R)}$ °	i	DRE71MJ_FU DRE80SJ_FU	DRE71MJ DRE80SJ DRE80MJ_FU	DRE80MJ DRE90MJ DRE90MJ_FU DRE90LJ_FU	DRE90LJ DRE100MJ_FU	DRE100MJ
74	4300	19100	7.6	18.96					
85	4300	17800	7.7	16.56					
101	4300	16100	7.7	13.85					
117	3890	16200	7.8	11.99					
134	2870	16400	9.7	10.41					
161	2660	15800	9.8	8.71					
186	2400	15700	10	7.54					


K97R57, $n_e=1400 \text{ min}^{-1}$									4300 Nm
n_a min^{-1}	M_{amax} Nm	F_{Ra} N	$\varphi_{(R)}$ °	i	DRE71SJ_FU	DRE71SJ DRE71MJ_FU DRE80SJ_FU	DRE71MJ DRE80SJ DRE80MJ_FU	DRE80MJ DRE90MJ DRE90MJ_FU DRE90LJ_FU	DRE90LJ DRE100MJ_FU
 3									
0.08	4300	40000	-	18091					
0.08	4300	40000	-	16666					
0.09	4300	40000	-	14897					
0.11	4300	40000	-	13182					
0.12	4300	40000	-	11677					
0.14	4300	40000	-	10317					
0.15	4300	40000	-	9083					
0.17	4300	40000	-	8054					
0.20	4300	40000	-	6970					
0.23	4300	40000	-	6027					
0.26	4300	40000	-	5391					
0.30	4300	40000	-	4669					
0.34	4300	40000	-	4082					
0.39	4300	40000	-	3583					
0.45	4300	40000	-	3108*					
0.51	4300	40000	-	2757					
 3  2									
0.58	4300	40000	-	2419					
0.66	4300	40000	-	2123					
0.75	4300	40000	-	1856					
0.86	4300	40000	-	1625					
0.98	4300	40000	-	1430					
1.1	4300	40000	-	1261					
1.3	4300	40000	-	1102					
1.5	4300	40000	-	957					
1.6	4300	40000	-	855					
1.9	4300	40000	-	743					
2.1	4300	40000	-	652*					
2.4	4300	40000	-	573					
2.8	4300	40000	-	504					
3.2	4300	40000	-	437					
3.7	4300	40000	-	382*					
4.1	4300	40000	-	342*					
4.6	4300	40000	-	305					
5.4	4300	40000	-	258					

K97R57, $n_e=1400 \text{ min}^{-1}$					4300 Nm				
n_a min^{-1}	M_{amax} Nm	F_{Ra} N	$\varphi_{(R)}$ °	i	DRE71SJ_FU	DRE71SJ DRE71MJ_FU DRE80SJ_FU	DRE71MJ DRE80SJ DRE80MJ_FU	DRE80MJ DRE90MJ DRE90MJ_FU DRE90LJ_FU	DRE90LJ DRE100MJ_FU
6.0	4300	40000	-	232					
7.0	4300	40000	-	199					


10.5 Auswahltabellen K..DRE..J (IE2), 50 Hz


P_m = 0.37 kW											
n_a min⁻¹ 50Hz	n_a min⁻¹ 10-50Hz	M_a Nm	i	F_{Ra}¹⁾ N	SEW f_B					m kg	
-	1.6 - 7.8	450	192.18	19800	3.2	K	77	DRE	71SJ4	63	612
-	1.7 - 8.4	420	179.37	19800	3.4	KF	77	DRE	71SJ4	71	613
9.7	1.9 - 9.7	360	154.02	19900	4.3	KA	77	DRE	71SJ4	55	614
11	2.2 - 11	315	135.28	20000	4.9	KAF	77	DRE	71SJ4	63	613
-	2.1 - 10	340	144.79*	13000	2.4	K	67	DRE	71SJ4	36	606
12	2.4 - 12	290	123.54	13000	2.8					42	607
14	2.8 - 14	250	108.03	13000	3.2					34	608
15	2.9 - 15	240	102.62	13000	3.4					39	607
17	3.3 - 17	210	90.04	13000	3.9						
20	3.9 - 20	180	76.37	13000	4.6						
-	2.1 - 10	340	145.14*	9120	1.75	K	57	DRE	71SJ4	31	600
12	2.4 - 12	290	123.85	9320	2.1					35	601
14	2.8 - 14	255	108.29	9450	2.4					29	602
15	2.9 - 15	240	102.88*	9490	2.5					34	601
17	3.3 - 17	210	90.26*	9590	2.8						
20	3.9 - 20	180	76.56*	9690	3.3						
22	4.3 - 22	163	69.12	9750	3.7						
25	4.9 - 25	143	60.81*	9800	4.2						
26	5.2 - 26	135	57.42*	9830	4.4						
-	4.0 - 20	177	75.20	9000	2.7	K	49	DRE	71SJ4	37	596
-	4.3 - 21	165	70.19	9000	2.7	KF	49	DRE	71SJ4	39	597
25	5.0 - 25	142	60.27	9000	3.5	KA	49	DRE	71SJ4	35	598
						KAF	49	DRE	71SJ4	39	597
-	2.3 - 11	310	131.87*	6960	1.30	K	47	DRE	71SJ4	25	590
-	2.5 - 12	285	121.48*	7180	1.40					28	591
14	2.9 - 14	245	104.37	7490	1.65					24	592
17	3.3 - 17	210	90.86	7690	1.85					27	591
18	3.5 - 18	200	85.12*	7770	2.0						
20	4.0 - 20	177	75.20*	7890	2.3						
21	4.3 - 21	164	69.84	7940	2.4						
24	4.7 - 24	149	63.30*	8010	2.7						
26	5.3 - 26	134	56.83	8060	3.0						
31	6.1 - 31	115	48.95*	8120	3.5						
33	6.5 - 33	108	46.03*	8140	3.7						
38	7.6 - 38	93	39.61	8180	4.3						
42	8.5 - 42	83	35.39	8210	4.8						
-	5.2 - 26	137	58.24	7500	2.2	K	39	DRE	71SJ4	24	586
30	6.0 - 30	117	49.69	7500	2.6	KF	39	DRE	71SJ4	25	587
35	6.9 - 35	102	43.45	7500	2.9	KA	39	DRE	71SJ4	23	588
36	7.3 - 36	97	41.28	7500	3.1	KAF	39	DRE	71SJ4	24	587
41	8.3 - 41	85	36.22	7500	3.5						
18	3.6 - 18	197	83.69	5670	1.00	K	37	DRE	71SJ4	19	580
21	4.1 - 21	171	72.54	5620	1.15					21	581
22	4.4 - 22	160	67.80	5560	1.25					18	582
26	5.1 - 26	138	58.60	5430	1.45					20	581
30	6.0 - 30	117	49.79	5260	1.70						
34	6.7 - 34	105	44.46	5140	1.90						
40	7.9 - 40	89	37.97	4970	2.2						
42	8.4 - 42	84	35.57	4900	2.4						
50	10 - 50	71	29.96	4700	2.8						
52	10 - 52	68	28.83	4660	3.0						
60	12 - 60	59	24.99	4490	3.4						
64	13 - 64	55	23.36	4420	3.5						
74	15 - 74	48	20.19	4250	3.9						
87	17 - 87	40	17.15	4070	4.5						
98	20 - 98	36	15.31	3940	4.8						

P_m = 0.37 kW


n _a min ⁻¹ 50Hz	n _a min ⁻¹ 10-50Hz	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
-	5.5 - 27	118	54.89	5070	1.10						
-	6.0 - 30	108	50.35	5110	1.20						
35	7.0 - 35	92	42.87	5020	1.40						
41	8.1 - 41	79	36.96	4860	1.55						
50	10.0 - 50	64	30.11	4630	1.80	K	29	DRE	71SJ4	12	573
-	10 - 51	65	29.69	4670	2.0	KF	29	DRE	71SJ4	14	577
-	11 - 55	60	27.23	4570	2.2	KA	29	DRE	71SJ4	12	579
60	12 - 60	53	24.91	4420	2.0	KAF	29	DRE	71SJ4	13	577
65	13 - 65	51	23.19	4380	2.6						
68	14 - 68	47	22.08	4280	2.2						
75	15 - 75	44	19.99	4210	3.0						
92	18 - 92	36	16.29	3980	3.6						
44	8.7 - 44	73	34.29	4190	0.85						
51	10 - 51	63	29.29	4060	0.95						
55	11 - 55	58	27.16	4000	1.05						
-	12 - 62	53	24.06	3990	1.50						
-	14 - 68	48	21.98	3900	1.65						
81	16 - 81	41	18.55	3740	1.95						
95	19 - 95	35	15.84	3590	2.3						
102	20 - 102	32	14.69	3520	2.5	K	19	DRE	71SJ4	11	567
118	24 - 118	28	12.70	3380	2.9	KF	19	DRE	71SJ4	11	570
127	25 - 127	26	11.84	3310	3.0	KA	19	DRE	71SJ4	11	572
145	29 - 145	23	10.32	3190	3.4	KAF	19	DRE	71SJ4	11	570
-	31 - 157	21	9.58	3160	2.9						
185	37 - 185	18	8.09	3010	4.4						
217	43 - 217	15	6.91	2870	5.2						
234	47 - 234	14	6.41	2800	5.6						
271	54 - 271	12	5.54	2680	6.5						
291	58 - 291	12	5.16	2620	6.9						
333	67 - 333	10	4.50	2510	8.0						

P_m = 0.55 kW

n _a min ⁻¹ 50Hz	n _a min ⁻¹ 10-50Hz	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
-	1.5 - 7.6	690	197.37	28900	3.9	K	87	DRE	71MJ4	99	618
8.6	1.7 - 8.6	605	174.19	29000	4.4	KF	87	DRE	71MJ4	110	619
9.1	1.8 - 9.1	575	164.34*	29000	4.7	KA	87	DRE	71MJ4	87	620
						KAF	87	DRE	71MJ4	100	619
-	1.9 - 9.7	535	154.02	19600	2.9						
11	2.2 - 11	470	135.28	19700	3.3	K	77	DRE	71MJ4	64	612
12	2.3 - 12	450	128.52	19800	3.4	KF	77	DRE	71MJ4	72	613
13	2.6 - 13	395	113.56	19900	3.9	KA	77	DRE	71MJ4	56	614
15	3.1 - 15	335	97.05	19900	4.6	KAF	77	DRE	71MJ4	64	613
17	3.4 - 17	310	88.97	20000	5.0						
-	2.4 - 12	430	123.54	12700	1.90						
14	2.8 - 14	375	108.03	12900	2.2						
15	2.9 - 15	355	102.62	12900	2.3						
17	3.3 - 17	315	90.04	13000	2.6	K	67	DRE	71MJ4	39	606
20	3.9 - 20	265	76.37	13000	3.1	KF	67	DRE	71MJ4	45	607
22	4.4 - 22	240	68.95	13000	3.4	KA	67	DRE	71MJ4	36	608
25	4.9 - 25	210	60.66	13000	3.9	KAF	67	DRE	71MJ4	42	607
26	5.2 - 26	200	57.28	13000	4.1						
31	6.2 - 31	171	48.77	13000	4.8						


P _m = 0.55 kW																	
n _a min ⁻¹ 50Hz	n _a min ⁻¹ 10-50Hz	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg							
-	2.4 - 12	430	123.85	8730	1.40	K KF KA KAF	57 57 57 57	DRE DRE DRE DRE	71MJ4 71MJ4 71MJ4 71MJ4	33 38 31 37	600 601 602 601						
14	2.8 - 14	375	108.29	8970	1.60												
15	2.9 - 15	360	102.88*	9050	1.65												
17	3.3 - 17	315	90.26*	9220	1.90												
20	3.9 - 20	265	76.56*	9400	2.2												
22	4.3 - 22	240	69.12	9490	2.5												
25	4.9 - 25	210	60.81*	9590	2.8												
26	5.2 - 26	200	57.42*	9630	3.0												
31	6.1 - 31	171	48.89	9720	3.5												
34	6.8 - 34	156	44.43	9770	3.9												
39	7.8 - 39	135	38.49	9830	4.5	K KF KA KAF	49 49 49 49	DRE DRE DRE DRE	71MJ4 71MJ4 71MJ4 71MJ4	38 40 36 40	596 597 598 597						
42	8.4 - 42	125	35.70	9860	4.8												
-	5.0 - 25	210	60.27	9000	2.4												
28	5.7 - 28	185	52.94	9000	2.7												
30	6.0 - 30	176	50.29	9000	2.8												
34	6.8 - 34	156	44.44	9000	3.2												
40	7.9 - 40	133	37.98	9000	3.8												
-	2.9 - 14	365	104.37	6380	1.10							K KF KA KAF	47 47 47 47	DRE DRE DRE DRE	71MJ4 71MJ4 71MJ4 71MJ4	27 31 26 29	590 591 592 591
17	3.3 - 17	315	90.86	6890	1.25												
18	3.5 - 18	295	85.12*	7080	1.35												
20	4.0 - 20	260	75.20*	7360	1.50												
21	4.3 - 21	240	69.84	7500	1.65												
24	4.7 - 24	220	63.30*	7650	1.80												
26	5.3 - 26	199	56.83	7780	2.0												
31	6.1 - 31	171	48.95*	7910	2.3												
33	6.5 - 33	161	46.03*	7960	2.5												
38	7.6 - 38	139	39.61	8050	2.9												
42	8.5 - 42	124	35.39	7960	3.2												
48	9.6 - 48	110	31.30	7720	3.6												
51	10 - 51	103	29.32	7580	3.9												
58	12 - 58	91	25.91	7340	4.4												
62	12 - 62	84	24.06	7190	4.8												
-	6.0 - 30	174	49.69	7500	1.70	K KF KA KAF	39 39 39 39	DRE DRE DRE DRE	71MJ4 71MJ4 71MJ4 71MJ4	26 28 25 27	586 587 588 587						
35	6.9 - 35	152	43.45	7500	1.95												
36	7.3 - 36	145	41.28	7500	2.1												
41	8.3 - 41	127	36.22	7500	2.4												
49	9.8 - 49	108	30.72	7420	2.8												
54	11 - 54	97	27.73	7230	3.1												
61	12 - 61	85	24.40	6990	3.5												
65	13 - 65	81	23.04	6890	3.7												
30	6.0 - 30	174	49.79	4740	1.15	K KF KA KAF	37 37 37 37	DRE DRE DRE DRE	71MJ4 71MJ4 71MJ4 71MJ4	20 22 20 21	580 581 582 581						
34	6.7 - 34	156	44.46	4680	1.30												
40	7.9 - 40	133	37.97	4570	1.50												
42	8.4 - 42	124	35.57	4520	1.60												
50	10 - 50	105	29.96	4390	1.90												
-	10 - 52	101	28.83	4360	2.0												
60	12 - 60	88	24.99	4230	2.3												
64	13 - 64	82	23.36	4170	2.4												
74	15 - 74	71	20.19	4040	2.6												
87	17 - 87	60	17.15	3890	3.0												
98	20 - 98	54	15.31	3780	3.3												
115	23 - 115	46	13.08	3640	3.6												
124	25 - 124	42	12.14	3570	3.8												
143	29 - 143	37	10.49	3430	4.4												
-	7.0 - 35	136	42.87	4570	0.95							K KF KA KAF	29 29 29 29	DRE DRE DRE DRE	71MJ4 71MJ4 71MJ4 71MJ4	14 15 13 15	573 577 579 577
41	8.1 - 41	118	36.96	4470	1.05												
50	10.0 - 50	96	30.11	4320	1.20												
60	12 - 60	79	24.91	4160	1.35												
-	13 - 65	75	23.19	4160	1.70												
68	14 - 68	70	22.08	4060	1.50												
75	15 - 75	65	19.99	4020	2.0												
92	18 - 92	53	16.29	3820	2.5												
111	22 - 111	44	13.47	3640	3.0												
126	25 - 126	39	11.94	3530	3.4												
-	30 - 152	33	9.90	3420	3.4												

P_m = 0.55 kW


n _a min ⁻¹ 50Hz	n _a min ⁻¹ 10-50Hz	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
-	16 - 81	60	18.55	3540	1.35						
95	19 - 95	52	15.84	3410	1.55						
102	20 - 102	48	14.69	3360	1.65						
118	24 - 118	41	12.70	3240	1.95						
127	25 - 127	38	11.84	3180	2.0	K	19	DRE	71MJ4	12	567
145	29 - 145	34	10.32	3070	2.3	KF	19	DRE	71MJ4	13	570
-	37 - 185	27	8.09	2940	3.0	KA	19	DRE	71MJ4	12	572
217	43 - 217	23	6.91	2810	3.5	KAF	19	DRE	71MJ4	12	570
234	47 - 234	21	6.41	2750	3.8						
271	54 - 271	18	5.54	2630	4.3						
291	58 - 291	17	5.16	2580	4.7						
333	67 - 333	15	4.50	2470	5.3						

10


P_m = 0.75 kW

n _a min ⁻¹ 50Hz	n _a min ⁻¹ 10-50Hz	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
-	1.5 - 7.6	940	197.37	28800	2.9						
8.6	1.7 - 8.6	830	174.19	28900	3.2	K	87	DRE	71MJ4	99	618
9.1	1.8 - 9.1	780	164.34*	28900	3.4	KF	87	DRE	71MJ4	110	619
10	2.0 - 10	700	147.32*	28900	3.8	KA	87	DRE	71MJ4	87	620
12	2.4 - 12	605	126.91*	29000	4.5	KAF	87	DRE	71MJ4	100	619
13	2.6 - 13	550	115.82	29000	4.9						
-	1.9 - 9.7	735	154.02	19200	2.1						
11	2.2 - 11	645	135.28	19400	2.4						
12	2.3 - 12	610	128.52	19500	2.5	K	77	DRE	71MJ4	64	612
13	2.6 - 13	540	113.56	19600	2.9	KF	77	DRE	71MJ4	72	613
15	3.1 - 15	460	97.05	19800	3.3	KA	77	DRE	71MJ4	56	614
17	3.4 - 17	420	88.97	19800	3.6	KAF	77	DRE	71MJ4	64	613
19	3.8 - 19	370	78.07	19900	4.2						
20	4.1 - 20	350	73.99	19900	4.4						
-	2.4 - 12	585	123.54	12000	1.40						
14	2.8 - 14	515	108.03	12300	1.60						
15	2.9 - 15	490	102.62	12500	1.65						
17	3.3 - 17	425	90.04	12700	1.90						
20	3.9 - 20	360	76.37	12900	2.2	K	67	DRE	71MJ4	39	606
22	4.4 - 22	325	68.95	13000	2.5	KF	67	DRE	71MJ4	45	607
25	4.9 - 25	285	60.66	13000	2.8	KA	67	DRE	71MJ4	36	608
26	5.2 - 26	270	57.28	13000	3.0	KAF	67	DRE	71MJ4	42	607
31	6.2 - 31	230	48.77	13000	3.5						
34	6.8 - 34	210	44.32	13000	3.9						
39	7.8 - 39	183	38.39	13000	4.4						
42	8.4 - 42	170	35.62	13000	4.8						
-	2.4 - 12	590	123.85	7700	1.00						
14	2.8 - 14	515	108.29	8290	1.15						
15	2.9 - 15	490	102.88*	8460	1.20						
17	3.3 - 17	430	90.26*	8740	1.40						
20	3.9 - 20	365	76.56*	9030	1.65						
22	4.3 - 22	330	69.12	9170	1.80	K	57	DRE	71MJ4	33	600
25	4.9 - 25	290	60.81*	9320	2.1	KF	57	DRE	71MJ4	38	601
26	5.2 - 26	270	57.42*	9380	2.2	KA	57	DRE	71MJ4	31	602
31	6.1 - 31	230	48.89	9520	2.6	KAF	57	DRE	71MJ4	37	601
34	6.8 - 34	210	44.43	9590	2.8						
39	7.8 - 39	184	38.49	9680	3.3						
42	8.4 - 42	170	35.70	9720	3.5						
50	9.9 - 50	145	30.28	9800	4.2						
55	11 - 55	130	27.34	9760	4.6						
-	5.0 - 25	285	60.27	9000	1.75						
28	5.7 - 28	250	52.94	9000	2.0						
30	6.0 - 30	240	50.29	9000	2.1	K	49	DRE	71MJ4	38	596
34	6.8 - 34	210	44.44	9000	2.4	KF	49	DRE	71MJ4	40	597
40	7.9 - 40	181	37.98	9000	2.8	KA	49	DRE	71MJ4	36	598
43	8.6 - 43	166	34.81	9000	3.0	KAF	49	DRE	71MJ4	40	597
49	9.8 - 49	146	30.55	8870	3.4						
52	10 - 52	138	28.95	8750	3.6						

P_m = 0.75 kW


n_a min ⁻¹ 50Hz	n_a min ⁻¹ 10-50Hz	M_a Nm	i	$F_{Ra}^{1)}$ N	SEW f_B					m kg	
20	4.0 - 20	355	75.20*	6450	1.10						
21	4.3 - 21	330	69.84	6740	1.20						
24	4.7 - 24	300	63.30*	7040	1.30						
26	5.3 - 26	270	56.83	7300	1.45						
31	6.1 - 31	230	48.95*	7570	1.70						
33	6.5 - 33	215	46.03*	7660	1.80						
38	7.6 - 38	189	39.61	7810	2.1	K	47	DRE	71MJ4	27	590
42	8.5 - 42	169	35.39	7620	2.4	KF	47	DRE	71MJ4	31	591
48	9.6 - 48	149	31.30	7410	2.7	KA	47	DRE	71MJ4	26	592
51	10 - 51	140	29.32	7300	2.9	KAF	47	DRE	71MJ4	29	591
58	12 - 58	124	25.91	7090	3.2						
62	12 - 62	115	24.06	6960	3.5						
69	14 - 69	104	21.81	6790	3.8						
77	15 - 77	94	19.58	6600	4.3						
89	18 - 89	80	16.86	6340	4.7						
127	25 - 127	56	11.77	5720	5.0						
-	6.0 - 30	235	49.69	7500	1.25						
35	6.9 - 35	205	43.45	7500	1.45						
36	7.3 - 36	197	41.28	7500	1.50						
41	8.3 - 41	173	36.22	7330	1.75	K	39	DRE	71MJ4	26	586
49	9.8 - 49	147	30.72	7080	2.0	KF	39	DRE	71MJ4	28	587
54	11 - 54	132	27.73	6930	2.3	KA	39	DRE	71MJ4	25	588
61	12 - 61	116	24.40	6720	2.6	KAF	39	DRE	71MJ4	27	587
65	13 - 65	110	23.04	6640	2.7						
76	15 - 76	94	19.62	6380	3.1						
84	17 - 84	85	17.83	6230	3.4						
97	19 - 97	74	15.44	6000	3.8						
40	7.9 - 40	181	37.97	4130	1.10						
42	8.4 - 42	170	35.57	4110	1.20						
50	10 - 50	143	29.96	4040	1.40						
-	10 - 52	138	28.83	4020	1.45						
60	12 - 60	119	24.99	3940	1.70						
64	13 - 64	112	23.36	3900	1.75						
74	15 - 74	96	20.19	3810	1.90	K	37	DRE	71MJ4	20	580
87	17 - 87	82	17.15	3690	2.2	KF	37	DRE	71MJ4	22	581
98	20 - 98	73	15.31	3610	2.4	KA	37	DRE	71MJ4	20	582
115	23 - 115	62	13.08	3480	2.6	KAF	37	DRE	71MJ4	21	581
124	25 - 124	58	12.14	3430	2.8						
143	29 - 143	50	10.49	3310	3.2						
168	34 - 168	43	8.91	3180	3.8						
188	38 - 188	38	7.96	3090	4.1						
221	44 - 221	32	6.80	2960	4.6						
236	47 - 236	30	6.37	2910	4.8						
50	10.0 - 50	131	30.11	3970	0.90						
60	12 - 60	108	24.91	3870	1.00						
-	13 - 65	103	23.19	3920	1.25						
68	14 - 68	96	22.08	3800	1.10						
75	15 - 75	89	19.99	3810	1.45	K	29	DRE	71MJ4	14	573
92	18 - 92	72	16.29	3650	1.80	KF	29	DRE	71MJ4	15	577
111	22 - 111	60	13.47	3500	2.2	KA	29	DRE	71MJ4	13	579
126	25 - 126	53	11.94	3400	2.5	KAF	29	DRE	71MJ4	15	577
-	30 - 152	45	9.90	3350	2.5						
164	33 - 164	41	9.17	3190	3.2						
176	35 - 176	39	8.53	3210	3.2						
201	40 - 201	33	7.48	3020	3.7						
216	43 - 216	31	6.95	3030	3.6						

P_m = 0.75 kW


n _a min ⁻¹ 50Hz	n _a min ⁻¹ 10-50Hz	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
-	16 - 81	82	18.55	3310	0.95						
95	19 - 95	70	15.84	3220	1.15						
102	20 - 102	65	14.69	3180	1.25						
118	24 - 118	56	12.70	3080	1.40						
127	25 - 127	52	11.84	3040	1.50	K	19	DRE	71MJ4	12	567
145	29 - 145	46	10.32	2950	1.65	KF	19	DRE	71MJ4	13	570
-	37 - 185	37	8.09	2860	2.2	KA	19	DRE	71MJ4	12	572
217	43 - 217	31	6.91	2740	2.6	KAF	19	DRE	71MJ4	12	570
234	47 - 234	29	6.41	2680	2.8						
271	54 - 271	25	5.54	2580	3.2						
291	58 - 291	23	5.16	2530	3.4						
333	67 - 333	20	4.50	2430	3.9						


10

P_m = 1.1 kW

n _a min ⁻¹ 50Hz	n _a min ⁻¹ 10-50Hz	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
8.5	1.7 - 8.5	1230	176.05*	40000	3.5	K	97	DRE	80SJ4	160	624
9.8	2.0 - 9.8	1070	153.21*	40000	4.0	KF	97	DRE	80SJ4	180	625
11	2.1 - 11	980	140.28	40000	4.4	KA	97	DRE	80SJ4	145	626
12	2.4 - 12	860	123.93*	40000	5.0	KAF	97	DRE	80SJ4	170	625
-	1.5 - 7.6	1380	197.37	28600	1.95						
8.6	1.7 - 8.6	1210	174.19	28700	2.2						
9.1	1.8 - 9.1	1150	164.34*	28700	2.4						
10	2.0 - 10	1030	147.32*	28800	2.6	K	87	DRE	80SJ4	105	618
12	2.4 - 12	880	126.91*	28800	3.0	KF	87	DRE	80SJ4	110	619
13	2.6 - 13	810	115.82	28900	3.3	KA	87	DRE	80SJ4	91	620
15	2.9 - 15	715	102.71*	28900	3.8	KAF	87	DRE	80SJ4	105	619
17	3.5 - 17	600	86.34	29000	4.5						
19	3.8 - 19	555	79.34	29000	4.9						
-	1.9 - 9.7	1070	154.02	18000	1.45						
11	2.2 - 11	940	135.28	18500	1.65						
12	2.3 - 12	900	128.52	18700	1.70						
13	2.6 - 13	795	113.56	19000	1.95						
15	3.1 - 15	675	97.05	19300	2.3	K	77	DRE	80SJ4	66	612
17	3.4 - 17	620	88.97	19400	2.5	KF	77	DRE	80SJ4	74	613
19	3.8 - 19	545	78.07	19600	2.8	KA	77	DRE	80SJ4	58	614
20	4.1 - 20	515	73.99	19700	3.0	KAF	77	DRE	80SJ4	66	613
23	4.6 - 23	450	64.75	19800	3.4						
26	5.1 - 26	405	58.34	19800	3.8						
29	5.9 - 29	355	51.18	19900	4.3						
33	6.6 - 33	315	45.16	20000	4.9						
14	2.8 - 14	755	108.03	10800	1.10						
15	2.9 - 15	715	102.62	11100	1.15						
17	3.3 - 17	630	90.04	11700	1.30						
20	3.9 - 20	530	76.37	12200	1.55						
22	4.4 - 22	480	68.95	12500	1.70						
25	4.9 - 25	420	60.66	12700	1.95						
26	5.2 - 26	400	57.28	12800	2.0	K	67	DRE	80SJ4	41	606
31	6.2 - 31	340	48.77	13000	2.4	KF	67	DRE	80SJ4	47	607
34	6.8 - 34	310	44.32	13000	2.6	KA	67	DRE	80SJ4	39	608
39	7.8 - 39	265	38.39	13000	3.0	KAF	67	DRE	80SJ4	44	607
42	8.4 - 42	245	35.62	13000	3.3						
50	9.9 - 50	210	30.22	13000	3.9						
55	11 - 55	191	27.28	13000	4.3						
63	13 - 63	168	24.00	13000	4.8						
66	13 - 66	159	22.66	13000	4.9						


P_m = 1.1 kW											
n_a min⁻¹ 50Hz	n_a min⁻¹ 10-50Hz	M_a Nm	i	F_{Ra}¹⁾ N	SEW f_B					m kg	
20	3.9 - 20	535	76.56*	8140	1.10	K KF KA KAF	57	DRE	80SJ4	35	600
22	4.3 - 22	480	69.12	8500	1.25						
25	4.9 - 25	425	60.81*	8770	1.40						
26	5.2 - 26	400	57.42*	8870	1.50						
31	6.1 - 31	340	48.89	9120	1.75						
34	6.8 - 34	310	44.43	9240	1.95						
39	7.8 - 39	265	38.49	9400	2.2						
42	8.4 - 42	250	35.70	9470	2.4						
50	9.9 - 50	210	30.28	9590	2.8						
55	11 - 55	191	27.34	9360	3.1						
62	12 - 62	168	24.05	9060	3.6						
66	13 - 66	159	22.71	8930	3.8						
78	16 - 78	135	19.34	8570	4.2						
85	17 - 85	123	17.57	8350	4.5						
126	25 - 126	84	11.92	7430	5.0						
-	5.0 - 25	420	60.27	9000	1.20	K KF KA KAF	49	DRE	80SJ4	40	596
28	5.7 - 28	370	52.94	9000	1.35						
30	6.0 - 30	350	50.29	9000	1.40						
34	6.8 - 34	310	44.44	9000	1.60						
40	7.9 - 40	265	37.98	8750	1.90						
43	8.6 - 43	240	34.81	8600	2.0						
49	9.8 - 49	210	30.55	8380	2.3						
52	10 - 52	200	28.95	8280	2.5						
59	12 - 59	177	25.34	8040	2.8						
66	13 - 66	160	22.83	7850	3.1						
75	15 - 75	140	20.03	7610	3.6						
26	5.3 - 26	395	56.83	5950	1.00	K KF KA KAF	47	DRE	80SJ4	30	590
31	6.1 - 31	340	48.95*	6640	1.15						
33	6.5 - 33	320	46.03*	6850	1.25						
38	7.6 - 38	275	39.61	7140	1.45						
42	8.5 - 42	245	35.39	7020	1.60						
48	9.6 - 48	215	31.30	6880	1.80						
51	10 - 51	205	29.32	6800	1.95						
58	12 - 58	181	25.91	6650	2.2						
62	12 - 62	168	24.06	6550	2.4						
69	14 - 69	153	21.81	6420	2.6						
77	15 - 77	137	19.58	6270	2.9						
89	18 - 89	118	16.86	6060	3.2						
95	19 - 95	111	15.86	5970	3.4						
110	22 - 110	96	13.65	5760	3.8						
123	25 - 123	85	12.19	5590	4.1						
127	25 - 127	82	11.77	5510	3.4						
142	28 - 142	74	10.56	5360	3.8						
165	33 - 165	64	9.10	5150	4.4						
175	35 - 175	60	8.56	5070	4.5						
204	41 - 204	52	7.36	4860	4.8						
-	6.0 - 30	345	49.69	6800	0.85	K KF KA KAF	39	DRE	80SJ4	28	586
35	6.9 - 35	300	43.45	6750	1.00						
36	7.3 - 36	285	41.28	6720	1.05						
41	8.3 - 41	250	36.22	6630	1.20						
49	9.8 - 49	215	30.72	6490	1.40						
54	11 - 54	194	27.73	6390	1.55						
61	12 - 61	171	24.40	6260	1.75						
65	13 - 65	161	23.04	6190	1.85						
76	15 - 76	137	19.62	6000	2.1						
84	17 - 84	125	17.83	5890	2.3						
97	19 - 97	108	15.44	5700	2.6						
112	22 - 112	94	13.44	5520	2.9						
118	24 - 118	89	12.73	5710	2.8						
124	25 - 124	85	12.09	5630	3.0						
141	28 - 141	74	10.61	5430	3.8						


P _m = 1.1 kW													
n _a min ⁻¹ 50Hz	n _a min ⁻¹ 10-50Hz	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg			
60	12 - 60	175	24.99	3440	1.15								
64	13 - 64	164	23.36	3430	1.20								
74	15 - 74	141	20.19	3400	1.30								
87	17 - 87	120	17.15	3340	1.50								
98	20 - 98	107	15.31	3300	1.65								
115	23 - 115	92	13.08	3220	1.80								
124	25 - 124	85	12.14	3180	1.90								
143	29 - 143	74	10.49	3100	2.2								
168	34 - 168	62	8.91	3000	2.6								
188	38 - 188	56	7.96	2930	2.8								
221	44 - 221	48	6.80	2830	3.1								
236	47 - 236	45	6.37	2780	3.2								
280	56 - 280	38	5.36	2670	3.7								
377	75 - 377	28	3.98	2470	4.5								
-	13 - 65	151	23.19	3490	0.85								
75	15 - 75	130	19.99	3440	1.00								
92	18 - 92	106	16.29	3350	1.25								
111	22 - 111	88	13.47	3250	1.50								
126	25 - 126	78	11.94	3180	1.65								
-	30 - 152	66	9.90	3210	1.65								
164	33 - 164	60	9.17	3020	2.2								
176	35 - 176	57	8.53	3090	2.1								
201	40 - 201	49	7.48	2880	2.5								
216	43 - 216	46	6.95	2930	2.4								
261	52 - 261	38	5.75	2790	2.9								
294	59 - 294	34	5.10	2700	3.2								
102	20 - 102	96	14.69	2860	0.85								
118	24 - 118	83	12.70	2810	0.95								
127	25 - 127	77	11.84	2790	1.05								
145	29 - 145	67	10.32	2730	1.15								
-	37 - 185	54	8.09	2720	1.50								
217	43 - 217	46	6.91	2620	1.75								
234	47 - 234	43	6.41	2580	1.90								
271	54 - 271	37	5.54	2480	2.2								
291	58 - 291	34	5.16	2440	2.3								
333	67 - 333	30	4.50	2350	2.7								

P _m = 1.5 kW											
n _a min ⁻¹ 50Hz	n _a min ⁻¹ 10-50Hz	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
8.5	1.7 - 8.5	1680	176.05*	40000	2.6	K KF KA KAF	97 97 97 97	DRE DRE DRE DRE	80MJ4 80MJ4 80MJ4 80MJ4	165 185 145 170	624 625 626 625
9.8	2.0 - 9.8	1460	153.21*	40000	2.9						
11	2.1 - 11	1330	140.28	40000	3.2						
12	2.4 - 12	1180	123.93*	40000	3.6						
14	2.9 - 14	1000	105.13	40000	4.3						
16	3.1 - 16	920	96.80	40000	4.7						
-	1.7 - 8.6	1660	174.19	28300	1.60	K KF KA KAF	87 87 87 87	DRE DRE DRE DRE	80MJ4 80MJ4 80MJ4 80MJ4	105 115 94 105	618 619 620 619
-	1.8 - 9.1	1560	164.34*	28400	1.70						
10	2.0 - 10	1400	147.32*	28500	1.90						
12	2.4 - 12	1210	126.91*	28700	2.2						
13	2.6 - 13	1100	115.82	28700	2.4						
15	2.9 - 15	980	102.71*	28800	2.8						
17	3.5 - 17	820	86.34	28900	3.3						
19	3.8 - 19	755	79.34	28900	3.6						
21	4.3 - 21	670	70.46	28900	4.0						
24	4.8 - 24	600	63.00*	29000	4.5						
26	5.3 - 26	540	56.64	29000	5.0						


P_m = 1.5 kW											
n_a min⁻¹ 50Hz	n_a min⁻¹ 10-50Hz	M_a Nm	i	F_{Ra}¹⁾ N	SEW f_B					m kg	
-	2.2 - 11	1290	135.28	17000	1.20						
-	2.3 - 12	1220	128.52	17300	1.25						
13	2.6 - 13	1080	113.56	18000	1.45						
15	3.1 - 15	920	97.05	18600	1.65						
17	3.4 - 17	840	88.97	18800	1.80						
19	3.8 - 19	745	78.07	19100	2.1	K	77	DRE	80MJ4	68	612
20	4.1 - 20	705	73.99	19200	2.2	KF	77	DRE	80MJ4	77	613
23	4.6 - 23	615	64.75	19500	2.5	KA	77	DRE	80MJ4	61	614
26	5.1 - 26	555	58.34	19600	2.8	KAF	77	DRE	80MJ4	69	613
29	5.9 - 29	485	51.18	19700	3.2						
33	6.6 - 33	430	45.16	19800	3.6						
37	7.5 - 37	380	40.04	19900	4.0						
39	7.8 - 39	365	38.39	19900	4.1						
43	8.5 - 43	335	35.20	19900	4.6						
20	3.9 - 20	725	76.37	11100	1.10						
22	4.4 - 22	655	68.95	11500	1.25						
25	4.9 - 25	575	60.66	12000	1.40						
26	5.2 - 26	545	57.28	12200	1.50						
31	6.2 - 31	465	48.77	12600	1.75						
34	6.8 - 34	420	44.32	12700	1.95						
39	7.8 - 39	365	38.39	12900	2.2	K	67	DRE	80MJ4	44	606
42	8.4 - 42	340	35.62	13000	2.4	KF	67	DRE	80MJ4	50	607
50	9.9 - 50	285	30.22	13000	2.8	KA	67	DRE	80MJ4	41	608
55	11 - 55	260	27.28	13000	3.1	KAF	67	DRE	80MJ4	47	607
63	13 - 63	225	24.00	13000	3.5						
66	13 - 66	215	22.66	13000	3.6						
78	16 - 78	184	19.30	13000	4.1						
86	17 - 86	167	17.54	13000	4.4						
99	20 - 99	145	15.19	13000	4.8						
120	24 - 120	119	12.48	13000	4.5						
141	28 - 141	102	10.63	13000	4.9						
25	4.9 - 25	580	60.81*	7790	1.05						
26	5.2 - 26	545	57.42*	8050	1.10						
31	6.1 - 31	465	48.89	8580	1.30						
34	6.8 - 34	420	44.43	8780	1.40						
39	7.8 - 39	365	38.49	9020	1.65						
42	8.4 - 42	340	35.70	9130	1.75						
50	9.9 - 50	285	30.28	9080	2.1						
55	11 - 55	260	27.34	8900	2.3	K	57	DRE	80MJ4	38	600
62	12 - 62	225	24.05	8660	2.6	KF	57	DRE	80MJ4	43	601
66	13 - 66	215	22.71	8550	2.8	KA	57	DRE	80MJ4	36	602
78	16 - 78	185	19.34	8240	3.1	KAF	57	DRE	80MJ4	42	601
85	17 - 85	168	17.57	8060	3.3						
99	20 - 99	145	15.22	7780	3.7						
113	23 - 113	126	13.25	7500	4.0						
126	25 - 126	114	11.92	7200	3.6						
133	27 - 133	108	11.26	7100	3.9						
156	31 - 156	92	9.59	6800	4.4						
172	34 - 172	83	8.71	6630	4.7						
-	5.7 - 28	505	52.94	8270	1.00						
-	6.0 - 30	480	50.29	8250	1.05						
34	6.8 - 34	420	44.44	8180	1.20						
40	7.9 - 40	360	37.98	8050	1.40						
43	8.6 - 43	330	34.81	7970	1.50	K	49	DRE	80MJ4	43	596
49	9.8 - 49	290	30.55	7820	1.70	KF	49	DRE	80MJ4	45	597
52	10 - 52	275	28.95	7750	1.80	KA	49	DRE	80MJ4	40	598
59	12 - 59	240	25.34	7580	2.1	KAF	49	DRE	80MJ4	45	597
66	13 - 66	215	22.83	7430	2.3						
75	15 - 75	191	20.03	7240	2.6						
85	17 - 85	169	17.67	7050	3.0						
96	19 - 96	150	15.67	6860	3.3						
112	22 - 112	128	13.38	6610	3.7						


P_m = 1.5 kW

n _a min ⁻¹ 50Hz	n _a min ⁻¹ 10-50Hz	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
38	7.6 - 38	375	39.61	6220	1.05						
42	8.5 - 42	335	35.39	6330	1.20						
-	9.6 - 48	295	31.30	6270	1.35						
-	10 - 51	280	29.32	6230	1.45						
58	12 - 58	245	25.91	6140	1.60						
-	12 - 62	225	24.06	6080	1.75						
69	14 - 69	205	21.81	5990	1.90						
77	15 - 77	187	19.58	5890	2.1						
89	18 - 89	161	16.86	5730	2.4	K	47	DRE	80MJ4	32	590
95	19 - 95	151	15.86	5660	2.5	KF	47	DRE	80MJ4	35	591
110	22 - 110	130	13.65	5490	2.8	KA	47	DRE	80MJ4	31	592
123	25 - 123	116	12.19	5360	3.0	KAF	47	DRE	80MJ4	34	591
127	25 - 127	112	11.77	5260	2.5						
142	28 - 142	101	10.56	5140	2.8						
165	33 - 165	87	9.10	4960	3.2						
175	35 - 175	82	8.56	4890	3.3						
204	41 - 204	70	7.36	4710	3.6						
228	46 - 228	63	6.58	4580	3.8						
258	52 - 258	56	5.81	4430	4.1						
324	65 - 324	44	4.64	4170	4.6						
41	8.3 - 41	345	36.22	5840	0.85						
49	9.8 - 49	290	30.72	5820	1.00						
54	11 - 54	260	27.73	5790	1.15						
61	12 - 61	230	24.40	5720	1.30						
65	13 - 65	220	23.04	5690	1.35						
76	15 - 76	187	19.62	5570	1.55	K	39	DRE	80MJ4	31	586
84	17 - 84	170	17.83	5500	1.70	KF	39	DRE	80MJ4	33	587
97	19 - 97	147	15.44	5370	1.90	KA	39	DRE	80MJ4	30	588
112	22 - 112	128	13.44	5230	2.1	KAF	39	DRE	80MJ4	32	587
-	24 - 118	122	12.73	5520	2.1						
-	25 - 124	115	12.09	5450	2.2						
141	28 - 141	101	10.61	5270	2.8						
167	33 - 167	86	9.00	5050	3.5						
185	37 - 185	78	8.12	4910	3.9						
-	17 - 87	164	17.15	2950	1.10						
-	20 - 98	146	15.31	2940	1.20						
-	23 - 115	125	13.08	2920	1.30						
-	25 - 124	116	12.14	2900	1.40	K	37	DRE	80MJ4	24	580
-	29 - 143	100	10.49	2860	1.60	KF	37	DRE	80MJ4	27	581
-	34 - 168	85	8.91	2800	1.90	KA	37	DRE	80MJ4	24	582
-	38 - 188	76	7.96	2750	2.0	KAF	37	DRE	80MJ4	26	581
-	44 - 221	65	6.80	2670	2.3						
-	47 - 236	61	6.37	2640	2.4						
-	56 - 280	51	5.36	2550	2.7						
-	75 - 377	38	3.98	2380	3.3						
-	18 - 92	144	16.29	3010	0.90						
-	22 - 111	119	13.47	2970	1.10						
-	25 - 126	106	11.94	2930	1.25						
-	33 - 164	81	9.17	2820	1.60	K	29	DRE	80MJ4	18	573
-	35 - 176	77	8.53	2960	1.60	KF	29	DRE	80MJ4	20	577
-	40 - 201	66	7.48	2720	1.85	KA	29	DRE	80MJ4	18	579
-	43 - 216	63	6.95	2820	1.80	KAF	29	DRE	80MJ4	19	577
-	52 - 261	52	5.75	2700	2.1						
-	59 - 294	46	5.10	2620	2.4						
-	77 - 383	35	3.92	2440	3.5						
-	94 - 470	29	3.19	2310	3.8						
-	29 - 145	92	10.32	2480	0.85						
-	43 - 217	63	6.91	2490	1.30	K	19	DRE	80MJ4	17	567
-	47 - 234	58	6.41	2450	1.40	KF	19	DRE	80MJ4	17	570
-	54 - 271	50	5.54	2380	1.60	KA	19	DRE	80MJ4	17	572
-	58 - 291	47	5.16	2340	1.70	KAF	19	DRE	80MJ4	17	570
-	67 - 333	41	4.50	2270	1.95						


P _m = 2.2 kW											m kg	
n _a min ⁻¹ 50Hz	n _a min ⁻¹ 10-50Hz	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B							
8.5	1.7 - 8.5	2460	176.05*	40000	1.75	K KF KA KAF	97 97 97 97	DRE DRE DRE DRE	90MJ4 90MJ4 90MJ4 90MJ4	170 190 150 175	624 625 626 625	
9.8	2.0 - 9.8	2140	153.21*	40000	2.0							
11	2.1 - 11	1960	140.28	40000	2.2							
12	2.4 - 12	1730	123.93*	40000	2.5							
14	2.9 - 14	1470	105.13	40000	2.9							
16	3.1 - 16	1350	96.80	40000	3.2							
17	3.5 - 17	1210	86.52	40000	3.5							
19	3.9 - 19	1090	77.89*	40000	3.9							
21	4.3 - 21	980	70.54	40000	4.3							
24	4.8 - 24	870	62.55	40000	4.9							
10	2.0 - 10	2060	147.32*	28000	1.30	K KF KA KAF	87 87 87 87	DRE DRE DRE DRE	90MJ4 90MJ4 90MJ4 90MJ4	110 120 96 110	618 619 620 619	
12	2.4 - 12	1770	126.91*	28300	1.50							
13	2.6 - 13	1620	115.82	28400	1.65							
15	2.9 - 15	1430	102.71*	28500	1.90							
17	3.5 - 17	1200	86.34	28700	2.2							
19	3.8 - 19	1110	79.34	28700	2.4							
21	4.3 - 21	980	70.46	28800	2.7							
24	4.8 - 24	880	63.00*	28800	3.1							
26	5.3 - 26	790	56.64	28900	3.4							
31	6.1 - 31	685	49.16	28900	3.9							
34	6.8 - 34	615	44.02	29000	4.2							
41	8.2 - 41	510	36.52*	28700	4.9							
15	3.1 - 15	1350	97.05	16600	1.15	K KF KA KAF	77 77 77 77	DRE DRE DRE DRE	90MJ4 90MJ4 90MJ4 90MJ4	73 81 65 73	612 613 614 613	
17	3.4 - 17	1240	88.97	17200	1.25							
19	3.8 - 19	1090	78.07	17900	1.40							
20	4.1 - 20	1030	73.99	18200	1.50							
23	4.6 - 23	900	64.75	18600	1.70							
26	5.1 - 26	810	58.34	18900	1.90							
29	5.9 - 29	715	51.18	19200	2.2							
33	6.6 - 33	630	45.16	19400	2.5							
37	7.5 - 37	560	40.04	19600	2.8							
39	7.8 - 39	535	38.39	19600	2.8							
43	8.5 - 43	490	35.20	19700	3.1							
49	9.7 - 49	430	30.89	19800	3.6							
51	10 - 51	405	29.27	19800	3.8							
59	12 - 59	355	25.62	19900	4.3							
65	13 - 65	320	23.08	20000	4.8							
26	5.2 - 26	800	57.28	10500	1.00	K KF KA KAF	67 67 67 67	DRE DRE DRE DRE	90MJ4 90MJ4 90MJ4 90MJ4	48 53 45 51	606 607 608 607	
31	6.2 - 31	680	48.77	11400	1.20							
34	6.8 - 34	620	44.32	11800	1.30							
39	7.8 - 39	535	38.39	12200	1.50							
42	8.4 - 42	495	35.62	12400	1.65							
50	9.9 - 50	420	30.22	12700	1.95							
55	11 - 55	380	27.28	12900	2.1							
63	13 - 63	335	24.00	13000	2.4							
66	13 - 66	315	22.66	13000	2.5							
78	16 - 78	270	19.30	13000	2.8							
86	17 - 86	245	17.54	13000	3.0							
99	20 - 99	210	15.19	13000	3.3							
114	23 - 114	185	13.22	13000	3.6							
120	24 - 120	175	12.48	13000	3.0							
141	28 - 141	149	10.63	13000	3.4							
155	31 - 155	135	9.66	13000	3.5							
179	36 - 179	117	8.37	13000	3.8							
206	41 - 206	102	7.28	12500	4.1							
288	58 - 288	73	5.20	11500	4.8							

P_m = 2.2 kW											
n_a min⁻¹ 50Hz	n_a min⁻¹ 10-50Hz	M_a Nm	i	F_{Ra}¹⁾ N	SEW f_B					m kg	
39	7.8 - 39	535	38.49	8120	1.10	K KF KA KAF	57 57 57 57	DRE DRE DRE DRE	90MJ4 90MJ4 90MJ4 90MJ4	42	600
42	8.4 - 42	500	35.70	8320	1.20					47	601
50	9.9 - 50	420	30.28	8200	1.40					40	602
55	11 - 55	380	27.34	8100	1.55					45	601
62	12 - 62	335	24.05	7960	1.80						
66	13 - 66	315	22.71	7890	1.90						
78	16 - 78	270	19.34	7680	2.1						
85	17 - 85	245	17.57	7540	2.3						
99	20 - 99	210	15.22	7330	2.5						
113	23 - 113	186	13.25	7120	2.8						
126	25 - 126	167	11.92	6800	2.5						
133	27 - 133	158	11.26	6720	2.6						
156	31 - 156	134	9.59	6480	3.0	K KF KA KAF	49 49 49 49	DRE DRE DRE DRE	90MJ4 90MJ4 90MJ4 90MJ4	47	596
172	34 - 172	122	8.71	6340	3.2					49	597
199	40 - 199	106	7.55	6120	3.5					45	598
228	46 - 228	92	6.57	5910	3.8					50	597
320	64 - 320	66	4.69	5410	4.6						
34	6.8 - 34	620	44.44	6760	0.80						
40	7.9 - 40	530	37.98	6830	0.95						
43	8.6 - 43	485	34.81	6850	1.05						
49	9.8 - 49	425	30.55	6840	1.15						
52	10 - 52	405	28.95	6820	1.25						
59	12 - 59	350	25.34	6760	1.40						
66	13 - 66	315	22.83	6700	1.55						
75	15 - 75	280	20.03	6600	1.80						
85	17 - 85	245	17.67	6480	2.0						
96	19 - 96	215	15.67	6360	2.2						
112	22 - 112	187	13.38	6180	2.5						
132	26 - 132	159	11.37	6390	3.1						
144	29 - 144	146	10.42	6250	3.3						
164	33 - 164	128	9.14	6040	3.9						
58	12 - 58	360	25.91	5260	1.10	K KF KA KAF	47 47 47 47	DRE DRE DRE DRE	90MJ4 90MJ4 90MJ4 90MJ4	36	590
69	14 - 69	305	21.81	5250	1.30					39	591
77	15 - 77	270	19.58	5220	1.45					35	592
89	18 - 89	235	16.86	5160	1.60					38	591
95	19 - 95	220	15.86	5120	1.70						
110	22 - 110	191	13.65	5030	1.90						
123	25 - 123	171	12.19	4940	2.0						
127	25 - 127	165	11.77	4840	1.70						
142	28 - 142	148	10.56	4760	1.90						
165	33 - 165	127	9.10	4640	2.2						
175	35 - 175	120	8.56	4580	2.2						
204	41 - 204	103	7.36	4450	2.4						
228	46 - 228	92	6.58	4340	2.6						
258	52 - 258	81	5.81	4220	2.8						
324	65 - 324	65	4.64	4000	3.2						
61	12 - 61	340	24.40	4790	0.90	K KF KA KAF	39 39 39 39	DRE DRE DRE DRE	90MJ4 90MJ4 90MJ4 90MJ4	35	586
65	13 - 65	320	23.04	4800	0.95					36	587
76	15 - 76	270	19.62	4820	1.05					34	588
84	17 - 84	245	17.83	4810	1.15					35	587
97	19 - 97	215	15.44	4770	1.30						
112	22 - 112	188	13.44	4720	1.45						
141	28 - 141	149	10.61	5000	1.90						
167	33 - 167	126	9.00	4820	2.4						
185	37 - 185	114	8.12	4700	2.6						
210	42 - 210	100	7.15	4560	3.0						
222	44 - 222	95	6.75	4490	3.2						
261	52 - 261	80	5.75	4310	3.4						
287	57 - 287	73	5.22	4200	3.5						
332	66 - 332	63	4.52	4040	3.8						
381	76 - 381	55	3.94	3890	3.9						

P _m = 2.2 kW											
n _a min ⁻¹ 50Hz	n _a min ⁻¹ 10-50Hz	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
143	29 - 143	147	10.49	2440	1.10	K KF KA KAF	37	DRE	90MJ4	29	580
168	34 - 168	125	8.91	2440	1.30					31	581
188	38 - 188	112	7.96	2430	1.40					29	582
221	44 - 221	95	6.80	2400	1.60					31	581
236	47 - 236	89	6.37	2380	1.65						
280	56 - 280	75	5.36	2330	1.85						
377	75 - 377	56	3.98	2220	2.2						
126	25 - 126	155	11.94	2490	0.85	K KF KA KAF	29	DRE	90MJ4	23	573
164	33 - 164	119	9.17	2480	1.10					24	577
201	40 - 201	97	7.48	2450	1.25					23	579
216	43 - 216	92	6.95	2630	1.20					24	577
261	52 - 261	76	5.75	2540	1.45						
294	59 - 294	68	5.10	2470	1.60						
383	77 - 383	52	3.92	2330	2.4						
470	94 - 470	42	3.19	2220	2.6						

P _m = 3.0 kW											
n _a min ⁻¹ 50Hz	n _a min ⁻¹ 10-50Hz	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
-	1.7 - 8.5	3360	176.05*	40000	1.30	K KF KA KAF	97	DRE	90LJ4	170	624
9.8	2.0 - 9.8	2920	153.21*	40000	1.45					190	625
11	2.1 - 11	2670	140.28	40000	1.60					150	626
12	2.4 - 12	2360	123.93*	40000	1.80					175	625
14	2.9 - 14	2000	105.13	40000	2.1						
16	3.1 - 16	1840	96.80	40000	2.3						
17	3.5 - 17	1650	86.52	40000	2.6						
19	3.9 - 19	1480	77.89*	40000	2.9						
21	4.3 - 21	1340	70.54	40000	3.2						
24	4.8 - 24	1190	62.55	40000	3.6						
27	5.3 - 27	1080	56.55	40000	4.0						
31	6.3 - 31	910	47.93*	40000	4.7						
12	2.4 - 12	2420	126.91*	27600	1.10	K KF KA KAF	87	DRE	90LJ4	110	618
13	2.6 - 13	2210	115.82	27800	1.20					120	619
15	2.9 - 15	1960	102.71*	28100	1.40					99	620
17	3.5 - 17	1640	86.34	28400	1.65					110	619
19	3.8 - 19	1510	79.34	28500	1.80						
21	4.3 - 21	1340	70.46	28600	2.0						
24	4.8 - 24	1200	63.00*	28700	2.2						
26	5.3 - 26	1080	56.64	28700	2.5						
31	6.1 - 31	930	49.16	28800	2.9						
34	6.8 - 34	840	44.02	28900	3.1						
41	8.2 - 41	695	36.52*	28000	3.6						
48	9.6 - 48	595	31.39	27000	4.5						
54	11 - 54	530	27.88	26200	4.9						
19	3.8 - 19	1490	78.07	15800	1.05	K KF KA KAF	77	DRE	90LJ4	75	612
20	4.1 - 20	1410	73.99	16300	1.10					84	613
23	4.6 - 23	1230	64.75	17300	1.25					68	614
26	5.1 - 26	1110	58.34	17800	1.40					76	613
29	5.9 - 29	970	51.18	18400	1.60						
33	6.6 - 33	860	45.16	18800	1.80						
37	7.5 - 37	760	40.04	19100	2.0						
39	7.8 - 39	730	38.39	19200	2.0						
43	8.5 - 43	670	35.20	19300	2.3						
49	9.7 - 49	585	30.89	19500	2.6						
51	10 - 51	555	29.27	19600	2.8						
59	12 - 59	485	25.62	19700	3.2						
65	13 - 65	440	23.08	19800	3.5						
74	15 - 74	385	20.25	19900	3.9						
84	17 - 84	340	17.87	19900	4.2						
95	19 - 95	300	15.84	20000	4.6						
121	24 - 121	235	12.36	18800	4.2						
138	28 - 138	205	10.84	18200	4.8						


P_m = 3.0 kW

n_a min ⁻¹ 50Hz	n_a min ⁻¹ 10-50Hz	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
39	7.8 - 39	730	38.39	11000	1.10	K KF KA KAF	67	DRE	90LJ4	51	606
-	8.4 - 42	680	35.62	11400	1.20						
50	9.9 - 50	575	30.22	12000	1.40						
55	11 - 55	520	27.28	12300	1.55						
63	13 - 63	455	24.00	12600	1.75						
66	13 - 66	430	22.66	12700	1.80						
78	16 - 78	365	19.30	12900	2.1						
86	17 - 86	330	17.54	13000	2.2						
99	20 - 99	290	15.19	13000	2.4						
114	23 - 114	250	13.22	13000	2.6						
120	24 - 120	235	12.48	13000	2.2						
141	28 - 141	200	10.63	13000	2.5						
155	31 - 155	184	9.66	13000	2.6						
179	36 - 179	160	8.37	12700	2.8						
206	41 - 206	139	7.28	12300	3.0						
288	58 - 288	99	5.20	11300	3.5						
50	9.9 - 50	575	30.28	7190	1.05	K KF KA KAF	57	DRE	90LJ4	45	600
55	11 - 55	520	27.34	7190	1.15						
62	12 - 62	455	24.05	7160	1.30						
66	13 - 66	430	22.71	7130	1.40						
78	16 - 78	365	19.34	7040	1.55						
85	17 - 85	335	17.57	6960	1.65						
99	20 - 99	290	15.22	6820	1.85						
113	23 - 113	250	13.25	6680	2.0						
126	25 - 126	225	11.92	6350	1.80						
133	27 - 133	215	11.26	6300	1.95						
156	31 - 156	183	9.59	6120	2.2						
172	34 - 172	166	8.71	6010	2.3						
199	40 - 199	144	7.55	5840	2.5						
228	46 - 228	125	6.57	5660	2.8						
320	64 - 320	90	4.69	5230	3.4						
49	9.8 - 49	580	30.55	5720	0.85	K KF KA KAF	49	DRE	90LJ4	50	596
52	10 - 52	550	28.95	5760	0.90						
59	12 - 59	480	25.34	5830	1.05						
66	13 - 66	435	22.83	5860	1.15						
75	15 - 75	380	20.03	5860	1.30						
85	17 - 85	335	17.67	5830	1.50						
96	19 - 96	295	15.67	5780	1.65						
112	22 - 112	255	13.38	5690	1.85						
132	26 - 132	215	11.37	6120	2.3						
144	29 - 144	199	10.42	6000	2.4						
164	33 - 164	175	9.14	5820	2.9						
173	35 - 173	165	8.66	5750	3.0						
198	40 - 198	145	7.58	5560	3.5						
220	44 - 220	130	6.83	5410	3.8						
77	15 - 77	370	19.58	4460	1.05	K KF KA KAF	47	DRE	90LJ4	39	590
89	18 - 89	320	16.86	4500	1.20						
95	19 - 95	300	15.86	4510	1.25						
110	22 - 110	260	13.65	4500	1.40						
123	25 - 123	230	12.19	4470	1.50						
127	25 - 127	220	11.77	4360	1.25						
142	28 - 142	200	10.56	4330	1.40						
165	33 - 165	174	9.10	4260	1.60						
175	35 - 175	163	8.56	4230	1.65						
204	41 - 204	141	7.36	4140	1.80						
228	46 - 228	126	6.58	4070	1.90						
258	52 - 258	111	5.81	3980	2.1						
324	65 - 324	88	4.64	3810	2.3						


P_m = 3.0 kW													
n_a min⁻¹ 50Hz	n_a min⁻¹ 10-50Hz	M_a Nm	i	F_{Ra}¹⁾ N	SEW f_B							m kg	
84	17 - 84	340	17.83	4030	0.85	K KF KA KAF	39	DRE	90LJ4	38	586		
97	19 - 97	290	15.44	4100	0.95								
112	22 - 112	255	13.44	4130	1.05								
-	28 - 141	200	10.61	4690	1.40								
167	33 - 167	172	9.00	4560	1.75								
185	37 - 185	155	8.12	4470	1.95								
210	42 - 210	137	7.15	4350	2.2								
222	44 - 222	129	6.75	4300	2.3								
261	52 - 261	110	5.75	4140	2.5								
287	57 - 287	100	5.22	4050	2.6								
332	66 - 332	86	4.52	3910	2.8	K KF KA KAF	37	DRE	90LJ4	32	580		
381	76 - 381	75	3.94	3780	2.9								
533	107 - 533	54	2.81	3450	3.2								
-	38 - 188	152	7.96	2060	1.00								
-	44 - 221	130	6.80	2080	1.15								
-	47 - 236	122	6.37	2090	1.20								
-	56 - 280	102	5.36	2080	1.35								
-	75 - 377	76	3.98	2040	1.65								
-	33 - 164	163	9.17	2100	0.80	K KF KA KAF	29	DRE	90LJ4	26	573		
-	40 - 201	133	7.48	2130	0.95								
-	43 - 216	126	6.95	2410	0.90								
-	52 - 261	104	5.75	2350	1.10								
-	59 - 294	92	5.10	2310	1.20								
-	77 - 383	71	3.92	2210	1.80								
-	94 - 470	58	3.19	2120	1.90								

P_m = 4.0 kW													
n_a min⁻¹ 50Hz	n_a min⁻¹ 10-50Hz	M_a Nm	i	F_{Ra}¹⁾ N	SEW f_B							m kg	
-	2.0 - 9.8	3900	153.21*	40000	1.10	K KF KA KAF	97	DRE	100MJ4	175	624		
-	2.1 - 11	3570	140.28	40000	1.20								
12	2.4 - 12	3150	123.93*	40000	1.35								
14	2.9 - 14	2670	105.13	40000	1.60								
16	3.1 - 16	2460	96.80	40000	1.75								
17	3.5 - 17	2200	86.52	40000	1.95								
19	3.9 - 19	1980	77.89*	40000	2.2								
21	4.3 - 21	1790	70.54	40000	2.4								
24	4.8 - 24	1590	62.55	40000	2.7								
27	5.3 - 27	1440	56.55	40000	3.0	K KF KA KAF	87	DRE	100MJ4	115	618		
31	6.3 - 31	1220	47.93*	39800	3.5								
39	7.8 - 39	970	38.30	37800	4.4								
44	8.8 - 44	870	34.23	36800	4.9								
15	2.9 - 15	2610	102.71*	27400	1.05								
17	3.5 - 17	2190	86.34	27900	1.25								
19	3.8 - 19	2020	79.34	28000	1.35								
21	4.3 - 21	1790	70.46	28200	1.50								
24	4.8 - 24	1600	63.00*	28400	1.70								
26	5.3 - 26	1440	56.64	28500	1.85								
31	6.1 - 31	1250	49.16	28600	2.2								
34	6.8 - 34	1120	44.02	28000	2.3								
41	8.2 - 41	930	36.52*	27000	2.7								
48	9.6 - 48	795	31.39	26200	3.4								
54	11 - 54	705	27.88	25500	3.7								
60	12 - 60	630	24.92	24900	3.9								
67	13 - 67	570	22.41	24300	4.0								
77	15 - 77	495	19.45	23500	4.6								
86	17 - 86	440	17.42	22900	5.0								
94	19 - 94	405	16.00	22100	4.4								

P_m = 4.0 kW

n _a min ⁻¹ 50Hz	n _a min ⁻¹ 10-50Hz	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
26	5.1 - 26	1480	58.34	15800	1.05						
29	5.9 - 29	1300	51.18	16900	1.20						
33	6.6 - 33	1150	45.16	17700	1.35						
37	7.5 - 37	1010	40.04	18200	1.50						
-	7.8 - 39	970	38.39	18400	1.55						
-	8.5 - 43	890	35.20	18700	1.75						
49	9.7 - 49	785	30.89	19000	1.95						
51	10 - 51	745	29.27	19100	2.1						
59	12 - 59	650	25.62	19400	2.4	K	77	DRE	100MJ4	80	612
65	13 - 65	585	23.08	19500	2.6	KF	77	DRE	100MJ4	88	613
74	15 - 74	515	20.25	19700	2.9	KA	77	DRE	100MJ4	73	614
84	17 - 84	450	17.87	19800	3.2	KAF	77	DRE	100MJ4	80	613
95	19 - 95	400	15.84	19700	3.5						
111	22 - 111	340	13.52	19000	3.9						
121	24 - 121	310	12.36	18400	3.2						
138	28 - 138	275	10.84	17800	3.6						
157	31 - 157	240	9.56	17300	3.9						
177	35 - 177	215	8.48	16800	4.1						
207	41 - 207	184	7.24	16100	4.5						
-	9.9 - 50	765	30.22	10700	1.05						
-	11 - 55	690	27.28	11300	1.20						
-	13 - 63	610	24.00	11800	1.30						
-	13 - 66	575	22.66	12000	1.35						
-	16 - 78	490	19.30	12400	1.55						
-	17 - 86	445	17.54	12600	1.65	K	67	DRE	100MJ4	55	606
-	20 - 99	385	15.19	12900	1.80	KF	67	DRE	100MJ4	61	607
-	23 - 114	335	13.22	13000	2.0	KA	67	DRE	100MJ4	52	608
-	24 - 120	315	12.48	13000	1.65	KAF	67	DRE	100MJ4	58	607
-	28 - 141	270	10.63	13000	1.85						
-	31 - 155	245	9.66	12700	1.95						
-	36 - 179	210	8.37	12400	2.1						
-	41 - 206	185	7.28	12000	2.3						
-	58 - 288	132	5.20	11100	2.6						
-	13 - 66	575	22.71	6190	1.05						
-	16 - 78	490	19.34	6230	1.15						
-	17 - 85	445	17.57	6230	1.25						
-	20 - 99	385	15.22	6190	1.40						
-	23 - 113	335	13.25	6120	1.50	K	57	DRE	100MJ4	49	600
-	25 - 126	300	11.92	5790	1.35	KF	57	DRE	100MJ4	54	601
-	27 - 133	285	11.26	5760	1.45	KA	57	DRE	100MJ4	47	602
-	31 - 156	240	9.59	5670	1.65	KAF	57	DRE	100MJ4	53	601
-	34 - 172	220	8.71	5600	1.75						
-	40 - 199	192	7.55	5480	1.90						
-	46 - 228	167	6.57	5350	2.1						
-	64 - 320	119	4.69	5010	2.5						
66	13 - 66	580	22.83	4810	0.85						
75	15 - 75	505	20.03	4940	1.00						
85	17 - 85	450	17.67	5020	1.10						
96	19 - 96	395	15.67	5070	1.25						
112	22 - 112	340	13.38	5080	1.40						
-	26 - 132	285	11.37	5790	1.70	K	49	DRE	100MJ4	55	596
-	29 - 144	265	10.42	5700	1.80	KF	49	DRE	100MJ4	57	597
164	33 - 164	230	9.14	5550	2.1	KA	49	DRE	100MJ4	52	598
173	35 - 173	220	8.66	5490	2.3	KAF	49	DRE	100MJ4	57	597
198	40 - 198	193	7.58	5340	2.6						
220	44 - 220	174	6.83	5210	2.9						
250	50 - 250	153	5.99	5050	3.3						
284	57 - 284	135	5.29	4900	3.6						
320	64 - 320	119	4.69	4760	3.9						


P_m = 4.0 kW										
n_a min⁻¹ 50Hz	n_a min⁻¹ 10-50Hz	M_a Nm	i	F_{Ra}¹⁾ N	SEW f_B					m kg
-	22 - 110	345	13.65	3840	1.05					
-	25 - 123	310	12.19	3880	1.15					
-	28 - 142	265	10.56	3780	1.05					
-	33 - 165	230	9.10	3800	1.20	K	47	DRE	100MJ4	43 590
-	35 - 175	215	8.56	3790	1.25	KF	47	DRE	100MJ4	47 591
-	41 - 204	188	7.36	3770	1.35	KA	47	DRE	100MJ4	43 592
-	46 - 228	168	6.58	3730	1.45	KAF	47	DRE	100MJ4	45 591
-	52 - 258	148	5.81	3680	1.55					
-	65 - 324	118	4.64	3570	1.75					
-	33 - 167	225	9.00	4230	1.30					
-	37 - 185	205	8.12	4170	1.45					
-	42 - 210	182	7.15	4090	1.65	K	39	DRE	100MJ4	42 586
-	44 - 222	172	6.75	4050	1.75	KF	39	DRE	100MJ4	44 587
-	52 - 261	146	5.75	3930	1.90	KA	39	DRE	100MJ4	41 588
-	57 - 287	133	5.22	3860	1.95	KAF	39	DRE	100MJ4	43 587
-	66 - 332	115	4.52	3740	2.1					
-	76 - 381	100	3.94	3630	2.1					
-	107 - 533	72	2.81	3350	2.4					



10.6 Auswahltabellen K..DRE..J (IE2), 87 Hz


P _m = 0.55 kW											
	n _a min ⁻¹ 10-87Hz	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
-	1.6 - 14	385	192.18	19900	3.8	K	77	DRE	71SJ4	63	612
-	1.7 - 15	360	179.37	19900	4.0	KF	77	DRE	71SJ4	71	613
-						KA	77	DRE	71SJ4	55	614
-						KAF	77	DRE	71SJ4	63	613
-	2.1 - 18	290	144.79*	13000	2.8	K	67	DRE	71SJ4	36	606
-	2.4 - 21	245	123.54	13000	3.3	KF	67	DRE	71SJ4	42	607
-	2.8 - 24	215	108.03	13000	3.8	KA	67	DRE	71SJ4	34	608
-	2.9 - 25	205	102.62	13000	4.0	KAF	67	DRE	71SJ4	39	607
-	3.3 - 29	181	90.04	13000	4.5						
-	2.1 - 18	290	145.14*	9320	2.0						
-	2.4 - 21	245	123.85	9470	2.4						
-	2.8 - 24	215	108.29	9570	2.8	K	57	DRE	71SJ4	31	600
-	2.9 - 25	205	102.88*	9610	2.9	KF	57	DRE	71SJ4	35	601
-	3.3 - 29	182	90.26*	9690	3.3	KA	57	DRE	71SJ4	29	602
-	3.9 - 34	154	76.56*	9770	3.9	KAF	57	DRE	71SJ4	34	601
-	4.3 - 38	139	69.12	9820	4.3						
-	4.9 - 43	122	60.81*	9860	4.9						
-	4.0 - 35	151	75.20	9000	3.1	K	49	DRE	71SJ4	37	596
-	4.3 - 37	141	70.19	9000	3.1	KF	49	DRE	71SJ4	39	597
-						KA	49	DRE	71SJ4	35	598
-						KAF	49	DRE	71SJ4	39	597
-	2.3 - 20	265	131.87*	7350	1.50						
-	2.5 - 21	240	121.48*	7500	1.65						
-	2.9 - 25	210	104.37	7720	1.90						
-	3.3 - 29	183	90.86	7860	2.2	K	47	DRE	71SJ4	25	590
-	3.5 - 31	171	85.12*	7920	2.3	KF	47	DRE	71SJ4	28	591
-	4.0 - 35	151	75.20*	8000	2.6	KA	47	DRE	71SJ4	24	592
-	4.3 - 37	140	69.84	8040	2.9	KAF	47	DRE	71SJ4	27	591
-	4.7 - 41	127	63.30*	8020	3.1						
-	5.3 - 46	114	56.83	7800	3.5						
-	6.1 - 53	98	48.95*	7500	4.1						
-	6.5 - 57	93	46.03*	7380	4.3						
-	5.2 - 45	117	58.24	7500	2.6	K	39	DRE	71SJ4	24	586
-	6.0 - 53	100	49.69	7280	3.0	KF	39	DRE	71SJ4	25	587
-	6.9 - 60	87	43.45	7040	3.4	KA	39	DRE	71SJ4	23	588
-	7.3 - 63	83	41.28	6940	3.6	KAF	39	DRE	71SJ4	24	587
-	3.1 - 27	197	97.81	4800	1.00						
-	3.6 - 31	168	83.69	4720	1.20						
-	4.1 - 36	146	72.54	4640	1.35						
-	4.4 - 38	136	67.80	4590	1.45						
-	5.1 - 45	118	58.60	4480	1.70						
-	6.0 - 52	100	49.79	4350	2.0	K	37	DRE	71SJ4	19	580
-	6.7 - 59	90	44.46	4250	2.2	KF	37	DRE	71SJ4	21	581
-	7.9 - 69	76	37.97	4110	2.6	KA	37	DRE	71SJ4	18	582
-	8.4 - 73	72	35.57	4050	2.8	KAF	37	DRE	71SJ4	20	581
-	10 - 87	60	29.96	3890	3.3						
-	10 - 91	58	28.83	3860	3.5						
-	12 - 104	50	24.99	3720	4.0						
-	13 - 112	47	23.36	3660	4.2						
-	15 - 129	41	20.19	3520	4.6						
-	5.5 - 48	100	54.89	4360	1.30						
-	6.0 - 52	92	50.35	4280	1.40						
-	7.0 - 61	78	42.87	4150	1.65						
-	8.1 - 71	68	36.96	4020	1.80	K	29	DRE	71SJ4	12	573
-	10.0 - 87	55	30.11	3840	2.1	KF	29	DRE	71SJ4	14	577
-	10 - 88	55	29.69	3870	2.3	KA	29	DRE	71SJ4	12	579
-	11 - 96	51	27.23	3790	2.5	KAF	29	DRE	71SJ4	13	577
-	12 - 105	46	24.91	3660	2.4						
-	13 - 113	43	23.19	3630	3.0						
-	14 - 118	40	22.08	3550	2.6						
-	15 - 131	37	19.99	3490	3.5						

19391609/DE – 06/2017

P _m = 0.55 kW																	
	n _a min ⁻¹ 10-87Hz	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg							
-	6.7 - 59	81	44.48	3620	0.85												
-	7.4 - 64	74	40.63	3570	0.90												
-	8.7 - 76	63	34.29	3470	1.00												
-	10 - 89	54	29.29	3360	1.15												
-	11 - 96	50	27.16	3310	1.20												
-	12 - 108	45	24.06	3310	1.80												
-	14 - 119	41	21.98	3230	1.95												
-	16 - 141	35	18.55	3100	2.3												
-	19 - 165	30	15.84	2970	2.7							K	19	DRE	71SJ4	11	567
-	20 - 178	27	14.69	2920	2.9							KF	19	DRE	71SJ4	11	570
-	24 - 205	24	12.70	2800	3.4							KA	19	DRE	71SJ4	11	572
-	25 - 220	22	11.84	2750	3.6							KAF	19	DRE	71SJ4	11	570
-	29 - 253	19	10.32	2640	3.9												
-	31 - 272	18	9.58	2630	3.4												
-	37 - 323	15	8.09	2500	5.2												
-	43 - 378	13	6.91	2380	6.1												
-	47 - 407	12	6.41	2330	6.5												
-	54 - 471	11	5.54	2220	7.6												
-	58 - 506	9.8	5.16	2180	8.1												
-	67 - 580	8.6	4.50	2090	9.3												

P _m = 0.75 kW											
	n _a min ⁻¹ 10-87Hz	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
-	1.5 - 13	540	197.37	29000	5.0	K	87	DRE	71MJ4	99	618
						KF	87	DRE	71MJ4	110	619
						KA	87	DRE	71MJ4	87	620
						KAF	87	DRE	71MJ4	100	619
-	1.9 - 17	420	154.02	19800	3.7	K	77	DRE	71MJ4	64	612
-	2.2 - 19	370	135.28	19900	4.2	KF	77	DRE	71MJ4	72	613
-	2.3 - 20	350	128.52	19900	4.4	KA	77	DRE	71MJ4	56	614
-	2.6 - 23	310	113.56	20000	5.0	KAF	77	DRE	71MJ4	64	613
-	2.4 - 21	335	123.54	13000	2.4	K KF KA KAF	67 67 67 67	DRE DRE DRE DRE	71MJ4 71MJ4 71MJ4 71MJ4	39 45 36 42	606 607 608 607
-	2.8 - 24	295	108.03	13000	2.8						
-	2.9 - 25	280	102.62	13000	2.9						
-	3.3 - 29	245	90.04	13000	3.3						
-	3.9 - 34	205	76.37	13000	3.9						
-	4.4 - 38	189	68.95	13000	4.3						
-	4.9 - 43	166	60.66	13000	4.9						
-	2.4 - 21	335	123.85	9130	1.75	K KF KA KAF	57 57 57 57	DRE DRE DRE DRE	71MJ4 71MJ4 71MJ4 71MJ4	33 38 31 37	600 601 602 601
-	2.8 - 24	295	108.29	9300	2.0						
-	2.9 - 25	280	102.88*	9350	2.1						
-	3.3 - 29	245	90.26*	9470	2.4						
-	3.9 - 34	210	76.56*	9600	2.9						
-	4.3 - 38	190	69.12	9660	3.2						
-	4.9 - 43	167	60.81*	9740	3.6						
-	5.2 - 45	158	57.42*	9760	3.8						
-	6.1 - 53	134	48.89	9830	4.5						
-	6.8 - 59	122	44.43	9570	4.9						
-	5.0 - 43	165	60.27	9000	3.0	K	49	DRE	71MJ4	38	596
-	5.7 - 49	145	52.94	8860	3.4	KF	49	DRE	71MJ4	40	597
-	6.0 - 52	138	50.29	8740	3.6	KA	49	DRE	71MJ4	36	598
						KAF	49	DRE	71MJ4	40	597


P_m = 0.75 kW

	n_a min⁻¹ 10-87Hz	M_a Nm	i	F_{Ra}¹⁾ N	SEW f_B					m kg	
-	2.9 - 25	285	104.37	7180	1.40						
-	3.3 - 29	245	90.86	7460	1.60						
-	3.5 - 31	230	85.12*	7570	1.70						
-	4.0 - 35	205	75.20*	7740	1.95						
-	4.3 - 37	192	69.84	7820	2.1						
-	4.7 - 41	174	63.30*	7670	2.3	K	47	DRE	71MJ4	27	590
-	5.3 - 46	156	56.83	7480	2.6	KF	47	DRE	71MJ4	31	591
-	6.1 - 53	134	48.95*	7230	3.0	KA	47	DRE	71MJ4	26	592
-	6.5 - 57	126	46.03*	7120	3.2	KAF	47	DRE	71MJ4	29	591
-	7.6 - 66	109	39.61	6860	3.7						
-	8.5 - 74	97	35.39	6670	4.1						
-	9.6 - 83	86	31.30	6450	4.7						
-	10 - 89	80	29.32	6340	5.0						
-	6.0 - 53	136	49.69	6970	2.2	K	39	DRE	71MJ4	26	586
-	6.9 - 60	119	43.45	6760	2.5	KF	39	DRE	71MJ4	28	587
-	7.3 - 63	113	41.28	6680	2.6	KA	39	DRE	71MJ4	25	588
-	8.3 - 72	99	36.22	6470	3.0	KAF	39	DRE	71MJ4	27	587
-	9.8 - 85	84	30.72	6210	3.6						
-	11 - 94	76	27.73	6050	3.9						
-	4.1 - 36	199	72.54	4150	1.00						
-	4.4 - 38	186	67.80	4140	1.10						
-	5.1 - 45	161	58.60	4090	1.25						
-	6.0 - 52	137	49.79	4020	1.45						
-	6.7 - 59	122	44.46	3960	1.65						
-	7.9 - 69	104	37.97	3860	1.90						
-	8.4 - 73	98	35.57	3820	2.0	K	37	DRE	71MJ4	20	580
-	10 - 87	82	29.96	3690	2.4	KF	37	DRE	71MJ4	22	581
-	10 - 91	79	28.83	3670	2.5	KA	37	DRE	71MJ4	20	582
-	12 - 104	69	24.99	3560	2.9	KAF	37	DRE	71MJ4	21	581
-	13 - 112	64	23.36	3500	3.0						
-	15 - 129	55	20.19	3390	3.3						
-	17 - 152	47	17.15	3260	3.8						
-	20 - 170	42	15.31	3170	4.2						
-	23 - 200	36	13.08	3040	4.6						
-	25 - 215	33	12.14	2980	4.8						
-	7.0 - 61	107	42.87	3870	1.20						
-	8.1 - 71	92	36.96	3780	1.30						
-	10.0 - 87	75	30.11	3640	1.55	K	29	DRE	71MJ4	14	573
-	12 - 105	62	24.91	3500	1.75	KF	29	DRE	71MJ4	15	577
-	13 - 113	59	23.19	3490	2.2	KA	29	DRE	71MJ4	13	579
-	14 - 118	55	22.08	3400	1.90	KAF	29	DRE	71MJ4	15	577
-	15 - 131	51	19.99	3370	2.5						
-	18 - 160	42	16.29	3200	3.1						
-	22 - 194	34	13.47	3050	3.8						
-	10 - 89	73	29.29	3120	0.85						
-	11 - 96	68	27.16	3090	0.90						
-	16 - 141	47	18.55	2970	1.70						
-	19 - 165	40	15.84	2860	2.0						
-	20 - 178	37	14.69	2810	2.1						
-	24 - 205	32	12.70	2710	2.5	K	19	DRE	71MJ4	12	567
-	25 - 220	30	11.84	2660	2.6	KF	19	DRE	71MJ4	13	570
-	29 - 253	26	10.32	2570	2.9	KA	19	DRE	71MJ4	12	572
-	37 - 323	21	8.09	2450	3.8	KAF	19	DRE	71MJ4	12	570
-	43 - 378	18	6.91	2340	4.5						
-	47 - 407	17	6.41	2290	4.8						
-	54 - 471	14	5.54	2200	5.5						
-	58 - 506	13	5.16	2150	6.0						
-	67 - 580	12	4.50	2060	6.8						


10


P_m = 1.1 kW											
	n_a min⁻¹ 10-87Hz	M_a Nm	i	F_{Ra}¹⁾ N	SEW f_B					m kg	
-	1.5 - 13	790	197.37	28900	3.4	K	87	DRE	71MJ4	99	618
-	1.7 - 15	700	174.19	28900	3.9	KF	87	DRE	71MJ4	110	619
-	1.8 - 16	660	164.34*	28900	4.1	KA	87	DRE	71MJ4	87	620
-	2.0 - 18	590	147.32*	29000	4.5	KAF	87	DRE	71MJ4	100	619
-	1.9 - 17	615	154.02	19500	2.5	K KF KA KAF	77	DRE	71MJ4	64	612
-	2.2 - 19	540	135.28	19600	2.9					72	613
-	2.3 - 20	515	128.52	19700	3.0					56	614
-	2.6 - 23	455	113.56	19800	3.4					64	613
-	3.1 - 27	390	97.05	19900	4.0						
-	3.4 - 29	355	88.97	19900	4.3						
-	3.8 - 33	310	78.07	20000	4.9						
-	2.4 - 21	495	123.54	12400	1.65	K KF KA KAF	67	DRE	71MJ4	39	606
-	2.8 - 24	430	108.03	12700	1.90					45	607
-	2.9 - 25	410	102.62	12800	2.0					36	608
-	3.3 - 29	360	90.04	12900	2.3					42	607
-	3.9 - 34	305	76.37	13000	2.7						
-	4.4 - 38	275	68.95	13000	3.0						
-	4.9 - 43	240	60.66	13000	3.4						
-	5.2 - 46	230	57.28	13000	3.6						
-	6.2 - 54	196	48.77	13000	4.2						
-	6.8 - 59	178	44.32	13000	4.6						
-	2.4 - 21	495	123.85	8420	1.20	K KF KA KAF	57	DRE	71MJ4	33	600
-	2.8 - 24	435	108.29	8720	1.40					38	601
-	2.9 - 25	410	102.88*	8820	1.45					31	602
-	3.3 - 29	360	90.26*	9040	1.65					37	601
-	3.9 - 34	305	76.56*	9260	1.95						
-	4.3 - 38	275	69.12	9370	2.2						
-	4.9 - 43	240	60.81*	9480	2.5						
-	5.2 - 45	230	57.42*	9530	2.6						
-	6.1 - 53	197	48.89	9420	3.0						
-	6.8 - 59	179	44.43	9200	3.4						
-	7.8 - 68	155	38.49	8870	3.9						
-	8.4 - 73	144	35.70	8700	4.2						
-	9.9 - 86	122	30.28	8330	4.9						
-	5.0 - 43	240	60.27	8600	2.1	K KF KA KAF	49	DRE	71MJ4	38	596
-	5.7 - 49	210	52.94	8370	2.4					40	597
-	6.0 - 52	200	50.29	8280	2.5					36	598
-	6.8 - 59	179	44.44	8060	2.8					40	597
-	7.9 - 69	153	37.98	7770	3.3						
-	8.6 - 75	140	34.81	7600	3.6						
-	3.3 - 29	365	90.86	6380	1.10	K KF KA KAF	47	DRE	71MJ4	27	590
-	3.5 - 31	340	85.12*	6640	1.15					31	591
-	4.0 - 35	300	75.20*	7040	1.30					26	592
-	4.3 - 37	280	69.84	7150	1.40					29	591
-	4.7 - 41	250	63.30*	7050	1.55						
-	5.3 - 46	225	56.83	6930	1.75						
-	6.1 - 53	197	48.95*	6750	2.0						
-	6.5 - 57	185	46.03*	6670	2.2						
-	7.6 - 66	159	39.61	6480	2.5						
-	8.5 - 74	142	35.39	6320	2.8						
-	9.6 - 83	126	31.30	6150	3.2						
-	10 - 89	118	29.32	6060	3.4						
-	12 - 101	104	25.91	5880	3.8						
-	12 - 108	97	24.06	5780	4.1						
-	14 - 120	88	21.81	5630	4.6						
-	6.0 - 53	200	49.69	6420	1.50	K KF KA KAF	39	DRE	71MJ4	26	586
-	6.9 - 60	175	43.45	6280	1.70					28	587
-	7.3 - 63	166	41.28	6230	1.80					25	588
-	8.3 - 72	146	36.22	6080	2.1					27	587
-	9.8 - 85	124	30.72	5870	2.4						
-	11 - 94	112	27.73	5740	2.7						
-	12 - 107	98	24.40	5580	3.0						
-	13 - 113	93	23.04	5510	3.2						
-	15 - 133	79	19.62	5300	3.7						


P_m = 1.1 kW


	n_a min ⁻¹ 10-87Hz	M_a Nm	i	$F_{Ra}^{1)}$ N	SEW f_B					m kg	
-	6.0 - 52	200	49.79	3440	1.00						
-	6.7 - 59	179	44.46	3440	1.10						
-	7.9 - 69	153	37.97	3420	1.30						
-	8.4 - 73	143	35.57	3400	1.40						
-	10 - 87	121	29.96	3340	1.65						
-	10 - 91	116	28.83	3330	1.70						
-	12 - 104	101	24.99	3270	2.0	K	37	DRE	71MJ4	20	580
-	13 - 112	94	23.36	3230	2.1	KF	37	DRE	71MJ4	22	581
-	15 - 129	81	20.19	3160	2.3	KA	37	DRE	71MJ4	20	582
-	17 - 152	69	17.15	3060	2.6	KAF	37	DRE	71MJ4	21	581
-	20 - 170	62	15.31	2990	2.8						
-	23 - 200	53	13.08	2890	3.1						
-	25 - 215	49	12.14	2840	3.3						
-	29 - 249	42	10.49	2750	3.8						
-	34 - 293	36	8.91	2640	4.5						
-	38 - 328	32	7.96	2560	4.8						
-	7.0 - 61	157	42.87	3370	0.80						
-	8.1 - 71	135	36.96	3340	0.90						
-	10.0 - 87	110	30.11	3290	1.05						
-	12 - 105	91	24.91	3210	1.20						
-	13 - 113	87	23.19	3250	1.50	K	29	DRE	71MJ4	14	573
-	14 - 118	81	22.08	3150	1.30	KF	29	DRE	71MJ4	15	577
-	15 - 131	75	19.99	3160	1.75	KA	29	DRE	71MJ4	13	579
-	18 - 160	61	16.29	3030	2.1	KAF	29	DRE	71MJ4	15	577
-	22 - 194	50	13.47	2900	2.6						
-	25 - 219	45	11.94	2820	2.9						
-	30 - 264	38	9.90	2780	2.9						
-	33 - 285	34	9.17	2640	3.8						
-	35 - 306	33	8.53	2670	3.8						
-	16 - 141	69	18.55	2740	1.15						
-	19 - 165	59	15.84	2670	1.35						
-	20 - 178	55	14.69	2630	1.45						
-	24 - 205	47	12.70	2560	1.70						
-	25 - 220	44	11.84	2520	1.80	K	19	DRE	71MJ4	12	567
-	29 - 253	39	10.32	2450	1.95	KF	19	DRE	71MJ4	13	570
-	37 - 323	31	8.09	2370	2.6	KA	19	DRE	71MJ4	12	572
-	43 - 378	26	6.91	2280	3.0	KAF	19	DRE	71MJ4	12	570
-	47 - 407	24	6.41	2230	3.3						
-	54 - 471	21	5.54	2140	3.8						
-	58 - 506	20	5.16	2100	4.1						
-	67 - 580	17	4.50	2020	4.7						

P_m = 1.5 kW

	n_a min ⁻¹ 10-87Hz	M_a Nm	i	$F_{Ra}^{1)}$ N	SEW f_B					m kg	
-	1.7 - 15	960	176.05*	40000	4.5	K	97	DRE	80SJ4	160	624
						KF	97	DRE	80SJ4	180	625
						KA	97	DRE	80SJ4	145	626
						KAF	97	DRE	80SJ4	170	625
-	1.5 - 13	1080	197.37	28700	2.5						
-	1.7 - 15	950	174.19	28800	2.8	K	87	DRE	80SJ4	105	618
-	1.8 - 16	900	164.34*	28800	3.0	KF	87	DRE	80SJ4	110	619
-	2.0 - 18	800	147.32*	28900	3.3	KA	87	DRE	80SJ4	91	620
-	2.4 - 21	695	126.91*	28900	3.9	KAF	87	DRE	80SJ4	105	619
-	2.6 - 23	635	115.82	28900	4.2						
-	2.9 - 25	560	102.71*	29000	4.8						

P _m = 1.5 kW											
	n _a min ⁻¹ 10-87Hz	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
-	1.9 - 17	840	154.02	18800	1.85	K KF KA KAF	77 77 77 77	DRE DRE DRE DRE	80SJ4 80SJ4 80SJ4 80SJ4	66 74 58 66	612 613 614 613
-	2.2 - 19	740	135.28	19200	2.1						
-	2.3 - 20	705	128.52	19200	2.2						
-	2.6 - 23	620	113.56	19400	2.5						
-	3.1 - 27	530	97.05	19600	2.9						
-	3.4 - 29	485	88.97	19700	3.2						
-	3.8 - 33	425	78.07	19800	3.6						
-	4.1 - 35	405	73.99	19800	3.8						
-	4.6 - 40	355	64.75	19900	4.4						
-	5.1 - 45	320	58.34	20000	4.8						
-	2.4 - 21	675	123.54	11400	1.20	K KF KA KAF	67 67 67 67	DRE DRE DRE DRE	80SJ4 80SJ4 80SJ4 80SJ4	41 47 39 44	606 607 608 607
-	2.8 - 24	590	108.03	11900	1.40						
-	2.9 - 25	560	102.62	12100	1.45						
-	3.3 - 29	490	90.04	12400	1.65						
-	3.9 - 34	415	76.37	12700	1.95						
-	4.4 - 38	375	68.95	12900	2.2						
-	4.9 - 43	330	60.66	13000	2.5						
-	5.2 - 46	310	57.28	13000	2.6						
-	6.2 - 54	265	48.77	13000	3.1						
-	6.8 - 59	240	44.32	13000	3.4						
-	7.8 - 68	210	38.39	13000	3.8						
-	8.4 - 73	196	35.62	13000	4.2						
-	9.9 - 86	166	30.22	13000	5.0						
-	2.8 - 24	590	108.29	7680	1.00	K KF KA KAF	57 57 57 57	DRE DRE DRE DRE	80SJ4 80SJ4 80SJ4 80SJ4	35 40 33 39	600 601 602 601
-	2.9 - 25	560	102.88*	7920	1.05						
-	3.3 - 29	495	90.26*	8440	1.20						
-	3.9 - 34	420	76.56*	8790	1.45						
-	4.3 - 38	375	69.12	8970	1.60						
-	4.9 - 43	330	60.81*	9160	1.80						
-	5.2 - 45	315	57.42*	9230	1.90						
-	6.1 - 53	265	48.89	8950	2.2						
-	6.8 - 59	240	44.43	8780	2.5						
-	7.8 - 68	210	38.49	8500	2.8						
-	8.4 - 73	196	35.70	8360	3.1						
-	9.9 - 86	166	30.28	8040	3.6						
-	11 - 95	150	27.34	7840	4.0						
-	12 - 109	132	24.05	7590	4.5						
-	13 - 115	125	22.71	7480	4.8						
-	5.0 - 43	330	60.27	7960	1.50	K KF KA KAF	49 49 49 49	DRE DRE DRE DRE	80SJ4 80SJ4 80SJ4 80SJ4	40 42 38 43	596 597 598 597
-	5.7 - 49	290	52.94	7810	1.70						
-	6.0 - 52	275	50.29	7750	1.80						
-	6.8 - 59	240	44.44	7590	2.0						
-	7.9 - 69	205	37.98	7370	2.4						
-	8.6 - 75	191	34.81	7240	2.6						
-	9.8 - 85	168	30.55	7040	3.0						
-	10 - 90	159	28.95	6960	3.1						
-	12 - 103	139	25.34	6750	3.6						
-	13 - 114	125	22.83	6580	4.0						
-	4.3 - 37	380	69.84	6150	1.05	K KF KA KAF	47 47 47 47	DRE DRE DRE DRE	80SJ4 80SJ4 80SJ4 80SJ4	30 33 29 32	590 591 592 591
-	4.7 - 41	345	63.30*	6340	1.15						
-	5.3 - 46	310	56.83	6300	1.30						
-	6.1 - 53	265	48.95*	6200	1.50						
-	6.5 - 57	250	46.03*	6160	1.60						
-	7.6 - 66	215	39.61	6030	1.85						
-	8.5 - 74	194	35.39	5930	2.1						
-	9.6 - 83	172	31.30	5800	2.3						
-	10 - 89	161	29.32	5730	2.5						
-	12 - 101	142	25.91	5590	2.8						
-	12 - 108	132	24.06	5510	3.0						
-	14 - 120	120	21.81	5390	3.3						
-	15 - 133	108	19.58	5260	3.7						
-	18 - 155	93	16.86	5080	4.1						
-	19 - 165	87	15.86	5000	4.4						
-	22 - 191	75	13.65	4820	4.8						
-	25 - 222	65	11.77	4610	4.3						
-	28 - 247	58	10.56	4480	4.8						

P_m = 1.5 kW										
	n_a min⁻¹ 10-87Hz	M_a Nm	i	F_{Ra}¹⁾ N	SEW f_B					m kg
-	6.0 - 53	270	49.69	5800	1.10					
-	6.9 - 60	235	43.45	5740	1.25					
-	7.3 - 63	225	41.28	5710	1.30					
-	8.3 - 72	199	36.22	5620	1.50					
-	9.8 - 85	169	30.72	5490	1.80					
-	11 - 94	152	27.73	5400	1.95	K	39	DRE	80SJ4	28 586
-	12 - 107	134	24.40	5270	2.2	KF	39	DRE	80SJ4	30 587
-	13 - 113	126	23.04	5220	2.4	KA	39	DRE	80SJ4	27 588
-	15 - 133	108	19.62	5050	2.7	KAF	39	DRE	80SJ4	29 587
-	17 - 146	98	17.83	4940	3.0					
-	19 - 169	85	15.44	4790	3.3					
-	22 - 194	74	13.44	4630	3.7					
-	24 - 205	70	12.73	4770	3.6					
-	25 - 216	66	12.09	4700	3.8					
-	8.4 - 73	195	35.57	2930	1.00					
-	10 - 87	164	29.96	2950	1.20					
-	10 - 91	158	28.83	2950	1.25					
-	12 - 104	137	24.99	2930	1.45					
-	13 - 112	128	23.36	2920	1.50					
-	15 - 129	111	20.19	2890	1.65					
-	17 - 152	94	17.15	2830	1.90	K	37	DRE	80SJ4	22 580
-	20 - 170	84	15.31	2790	2.1	KF	37	DRE	80SJ4	24 581
-	23 - 200	72	13.08	2720	2.3	KA	37	DRE	80SJ4	22 582
-	25 - 215	67	12.14	2680	2.4	KAF	37	DRE	80SJ4	23 581
-	29 - 249	58	10.49	2610	2.8					
-	34 - 293	49	8.91	2520	3.3					
-	38 - 328	44	7.96	2460	3.5					
-	44 - 384	37	6.80	2370	4.0					
-	47 - 410	35	6.37	2340	4.2					
-	56 - 487	29	5.36	2240	4.8					
-	12 - 105	124	24.91	2880	0.90					
-	13 - 113	118	23.19	2960	1.10					
-	14 - 118	110	22.08	2860	0.95					
-	15 - 131	102	19.99	2920	1.30					
-	18 - 160	83	16.29	2830	1.55	K	29	DRE	80SJ4	16 573
-	22 - 194	69	13.47	2740	1.90	KF	29	DRE	80SJ4	17 577
-	25 - 219	61	11.94	2680	2.1	KA	29	DRE	80SJ4	15 579
-	30 - 264	52	9.90	2690	2.1	KAF	29	DRE	80SJ4	17 577
-	33 - 285	47	9.17	2530	2.8					
-	35 - 306	44	8.53	2590	2.8					
-	40 - 349	38	7.48	2420	3.2					
-	43 - 375	36	6.95	2450	3.1					
-	52 - 454	30	5.75	2330	3.7					
-	16 - 141	95	18.55	2480	0.85					
-	19 - 165	81	15.84	2450	1.00					
-	20 - 178	75	14.69	2430	1.05					
-	24 - 205	65	12.70	2380	1.25					
-	25 - 220	60	11.84	2360	1.30	K	19	DRE	80SJ4	14 567
-	29 - 253	53	10.32	2300	1.45	KF	19	DRE	80SJ4	15 570
-	37 - 323	42	8.09	2280	1.90	KA	19	DRE	80SJ4	14 572
-	43 - 378	36	6.91	2200	2.2	KAF	19	DRE	80SJ4	14 570
-	47 - 407	33	6.41	2160	2.4					
-	54 - 471	29	5.54	2080	2.8					
-	58 - 506	27	5.16	2040	3.0					
-	67 - 580	23	4.50	1970	3.4					

P_m = 2.2 kW										
	n_a min⁻¹ 10-87Hz	M_a Nm	i	F_{Ra}¹⁾ N	SEW f_B					m kg
-	1.7 - 15	1410	176.05*	40000	3.0	K	97	DRE	80MJ4	165 624
-	2.0 - 17	1230	153.21*	40000	3.5	KF	97	DRE	80MJ4	185 625
-	2.1 - 19	1120	140.28	40000	3.8	KA	97	DRE	80MJ4	145 626
-	2.4 - 21	990	123.93*	40000	4.3	KAF	97	DRE	80MJ4	170 625

P_m = 2.2 kW											
	n_a min⁻¹ 10-87Hz	M_a Nm	i	F_{Ra}¹⁾ N	SEW f_B					m kg	
-	1.7 - 15	1400	174.19	28500	1.95	K KF KA KAF	87	DRE	80MJ4	105	618
-	1.8 - 16	1320	164.34*	28600	2.0					115	619
-	2.0 - 18	1180	147.32*	28700	2.3					94	620
-	2.4 - 21	1020	126.91*	28800	2.6					105	619
-	2.6 - 23	930	115.82	28800	2.9						
-	2.9 - 25	820	102.71*	28900	3.3						
-	3.5 - 30	695	86.34	28900	3.9						
-	3.8 - 33	635	79.34	28900	4.2						
-	4.3 - 37	565	70.46	29000	4.8						
-	2.2 - 19	1080	135.28	17900	1.40	K KF KA KAF	77	DRE	80MJ4	68	612
-	2.3 - 20	1030	128.52	18200	1.50					77	613
-	2.6 - 23	910	113.56	18600	1.70					61	614
-	3.1 - 27	780	97.05	19000	2.0					69	613
-	3.4 - 29	715	88.97	19200	2.2						
-	3.8 - 33	625	78.07	19400	2.5						
-	4.1 - 35	595	73.99	19500	2.6						
-	4.6 - 40	520	64.75	19700	3.0						
-	5.1 - 45	465	58.34	19700	3.3						
-	5.9 - 51	410	51.18	19800	3.8						
-	6.6 - 58	360	45.16	19900	4.3						
-	7.5 - 65	320	40.04	20000	4.8						
-	7.8 - 68	305	38.39	20000	4.8						
-	3.3 - 29	720	90.04	11100	1.15	K KF KA KAF	67	DRE	80MJ4	44	606
-	3.9 - 34	610	76.37	11800	1.35					50	607
-	4.4 - 38	555	68.95	12100	1.50					41	608
-	4.9 - 43	485	60.66	12500	1.70					47	607
-	5.2 - 46	460	57.28	12600	1.80						
-	6.2 - 54	390	48.77	12800	2.1						
-	6.8 - 59	355	44.32	13000	2.3						
-	7.8 - 68	305	38.39	13000	2.6						
-	8.4 - 73	285	35.62	13000	2.9						
-	9.9 - 86	240	30.22	13000	3.4						
-	11 - 96	215	27.28	13000	3.7						
-	13 - 109	193	24.00	13000	4.1						
-	13 - 115	182	22.66	13000	4.3						
-	16 - 135	155	19.30	13000	4.9						
-	4.3 - 38	555	69.12	7980	1.10	K KF KA KAF	57	DRE	80MJ4	38	600
-	4.9 - 43	485	60.81*	8310	1.25					43	601
-	5.2 - 45	460	57.42*	8270	1.30					36	602
-	6.1 - 53	390	48.89	8130	1.50					42	601
-	6.8 - 59	355	44.43	8030	1.70						
-	7.8 - 68	305	38.49	7860	1.95						
-	8.4 - 73	285	35.70	7760	2.1						
-	9.9 - 86	240	30.28	7530	2.5						
-	11 - 95	220	27.34	7380	2.7						
-	12 - 109	194	24.05	7180	3.1						
-	13 - 115	183	22.71	7100	3.3						
-	16 - 135	156	19.34	6840	3.7						
-	17 - 149	142	17.57	6690	3.9						
-	20 - 171	122	15.22	6460	4.4						
-	23 - 197	107	13.25	6230	4.8						
-	25 - 219	96	11.92	5980	4.3						
-	27 - 232	91	11.26	5890	4.6						
-	5.7 - 49	425	52.94	6840	1.15	K KF KA KAF	49	DRE	80MJ4	43	596
-	6.0 - 52	400	50.29	6820	1.25					45	597
-	6.8 - 59	355	44.44	6770	1.40					40	598
-	7.9 - 69	305	37.98	6660	1.65					45	597
-	8.6 - 75	280	34.81	6600	1.80						
-	9.8 - 85	245	30.55	6480	2.0						
-	10 - 90	230	28.95	6420	2.1						
-	12 - 103	200	25.34	6280	2.5						
-	13 - 114	184	22.83	6160	2.7						
-	15 - 130	161	20.03	6000	3.1						
-	17 - 148	142	17.67	5850	3.5						
-	19 - 167	126	15.67	5690	3.9						


P_m = 2.2 kW											
	n_a min⁻¹ 10-87Hz	M_a Nm	i	F_{Ra}¹⁾ N	SEW f_B					m kg	
-	6.1 - 53	390	48.95*	5250	1.00						
-	6.5 - 57	370	46.03*	5260	1.10						
-	7.6 - 66	315	39.61	5260	1.25						
-	8.5 - 74	280	35.39	5240	1.40						
-	9.6 - 83	250	31.30	5190	1.60						
-	10 - 89	235	29.32	5160	1.70						
-	12 - 101	205	25.91	5090	1.90						
-	12 - 108	194	24.06	5040	2.1						
-	14 - 120	176	21.81	4960	2.3						
-	15 - 133	158	19.58	4880	2.5	K	47	DRE	80MJ4	32	590
-	18 - 155	136	16.86	4750	2.8	KF	47	DRE	80MJ4	35	591
-	19 - 165	128	15.86	4700	3.0	KA	47	DRE	80MJ4	31	592
-	22 - 191	110	13.65	4550	3.3	KAF	47	DRE	80MJ4	34	591
-	25 - 214	98	12.19	4440	3.6						
-	25 - 222	95	11.77	4370	3.0						
-	28 - 247	85	10.56	4260	3.3						
-	33 - 287	73	9.10	4120	3.8						
-	35 - 305	69	8.56	4060	3.9						
-	41 - 354	59	7.36	3910	4.2						
-	46 - 397	53	6.58	3800	4.5						
-	52 - 449	47	5.81	3680	4.9						
-	6.9 - 60	345	43.45	4780	0.85						
-	7.3 - 63	330	41.28	4800	0.90						
-	8.3 - 72	290	36.22	4820	1.05						
-	9.8 - 85	245	30.72	4810	1.20						
-	11 - 94	220	27.73	4780	1.35						
-	12 - 107	196	24.40	4740	1.55	K	39	DRE	80MJ4	31	586
-	13 - 113	185	23.04	4710	1.60	KF	39	DRE	80MJ4	33	587
-	15 - 133	158	19.62	4620	1.85	KA	39	DRE	80MJ4	30	588
-	17 - 146	144	17.83	4550	2.0	KAF	39	DRE	80MJ4	32	587
-	19 - 169	124	15.44	4450	2.2						
-	22 - 194	108	13.44	4340	2.5						
-	24 - 205	102	12.73	4580	2.4						
-	25 - 216	97	12.09	4530	2.6						
-	28 - 246	85	10.61	4380	3.3						
-	13 - 112	188	23.36	2380	1.05						
-	15 - 129	162	20.19	2420	1.15						
-	17 - 152	138	17.15	2430	1.30						
-	20 - 170	123	15.31	2430	1.40						
-	23 - 200	105	13.08	2410	1.55	K	37	DRE	80MJ4	24	580
-	25 - 215	98	12.14	2400	1.65	KF	37	DRE	80MJ4	27	581
-	29 - 249	84	10.49	2370	1.90	KA	37	DRE	80MJ4	24	582
-	34 - 293	72	8.91	2320	2.2	KAF	37	DRE	80MJ4	26	581
-	38 - 328	64	7.96	2280	2.4						
-	44 - 384	55	6.80	2210	2.7						
-	47 - 410	51	6.37	2190	2.8						
-	56 - 487	43	5.36	2110	3.2						
-	75 - 656	32	3.98	1980	3.9						
-	15 - 131	149	19.99	2490	0.85						
-	18 - 160	122	16.29	2490	1.05						
-	22 - 194	101	13.47	2460	1.30						
-	25 - 219	89	11.94	2420	1.45	K	29	DRE	80MJ4	18	573
-	33 - 285	69	9.17	2340	1.90	KF	29	DRE	80MJ4	20	577
-	35 - 306	65	8.53	2450	1.85	KA	29	DRE	80MJ4	18	579
-	40 - 349	56	7.48	2260	2.2	KAF	29	DRE	80MJ4	19	577
-	43 - 375	53	6.95	2340	2.1						
-	52 - 454	44	5.75	2240	2.5						
-	59 - 512	39	5.10	2170	2.8						
-	24 - 205	95	12.70	2070	0.85						
-	25 - 220	89	11.84	2070	0.90						
-	29 - 253	77	10.32	2050	1.00	K	19	DRE	80MJ4	17	567
-	43 - 378	53	6.91	2060	1.50	KF	19	DRE	80MJ4	17	570
-	47 - 407	49	6.41	2030	1.65	KA	19	DRE	80MJ4	17	572
-	54 - 471	42	5.54	1970	1.90	KAF	19	DRE	80MJ4	17	570
-	58 - 506	39	5.16	1940	2.0						
-	67 - 580	34	4.50	1880	2.3						


P_m = 3.0 kW											
	n_a min⁻¹ 10-87Hz	M_a Nm	i	F_{Ra}¹⁾ N	SEW f_B					m kg	
-	1.7 - 15	1930	176.05*	40000	2.2	K KF KA KAF	97	DRE	90MJ4	170	624
-	2.0 - 17	1680	153.21*	40000	2.6					190	625
-	2.1 - 19	1530	140.28	40000	2.8					150	626
-	2.4 - 21	1360	123.93*	40000	3.2					175	625
-	2.9 - 25	1150	105.13	40000	3.7						
-	3.1 - 27	1060	96.80	40000	4.0						
-	3.5 - 30	940	86.52	40000	4.5						
-	2.0 - 18	1610	147.32*	28400	1.65	K KF KA KAF	87	DRE	90MJ4	110	618
-	2.4 - 21	1390	126.91*	28500	1.95					120	619
-	2.6 - 23	1270	115.82	28600	2.1					96	620
-	2.9 - 25	1120	102.71*	28700	2.4					110	619
-	3.5 - 30	940	86.34	28800	2.9						
-	3.8 - 33	870	79.34	28800	3.1						
-	4.3 - 37	770	70.46	28600	3.5						
-	4.8 - 41	690	63.00*	27900	3.9						
-	5.3 - 46	620	56.64	27200	4.3						
-	2.6 - 23	1240	113.56	17200	1.25	K KF KA KAF	77	DRE	90MJ4	73	612
-	3.1 - 27	1060	97.05	18000	1.45					81	613
-	3.4 - 29	970	88.97	18400	1.60					65	614
-	3.8 - 33	850	78.07	18800	1.80					73	613
-	4.1 - 35	810	73.99	19000	1.90						
-	4.6 - 40	710	64.75	19200	2.2						
-	5.1 - 45	640	58.34	19400	2.4						
-	5.9 - 51	560	51.18	19600	2.8						
-	6.6 - 58	495	45.16	19700	3.1						
-	7.5 - 65	435	40.04	19800	3.5						
-	7.8 - 68	420	38.39	19800	3.6						
-	8.5 - 74	385	35.20	19900	4.0						
-	9.7 - 85	335	30.89	19900	4.6						
-	10 - 89	320	29.27	20000	4.8						
-	4.4 - 38	755	68.95	10800	1.10	K KF KA KAF	67	DRE	90MJ4	48	606
-	4.9 - 43	665	60.66	11500	1.25					53	607
-	5.2 - 46	625	57.28	11700	1.30					45	608
-	6.2 - 54	535	48.77	12200	1.55					51	607
-	6.8 - 59	485	44.32	12500	1.70						
-	7.8 - 68	420	38.39	12700	1.90						
-	8.4 - 73	390	35.62	12800	2.1						
-	9.9 - 86	330	30.22	13000	2.5						
-	11 - 96	295	27.28	13000	2.7						
-	13 - 109	260	24.00	13000	3.0						
-	13 - 115	245	22.66	13000	3.1						
-	16 - 135	210	19.30	13000	3.6						
-	17 - 149	192	17.54	13000	3.9						
-	20 - 172	167	15.19	13000	4.2						
-	23 - 197	145	13.22	12600	4.6						
-	24 - 209	137	12.48	12200	3.9						
-	28 - 246	117	10.63	11800	4.3						
-	31 - 270	106	9.66	11500	4.5						
-	36 - 312	92	8.37	11100	4.8						
-	6.1 - 53	535	48.89	7190	1.10	K KF KA KAF	57	DRE	90MJ4	42	600
-	6.8 - 59	485	44.43	7180	1.25					47	601
-	7.8 - 68	420	38.49	7120	1.40					40	602
-	8.4 - 73	390	35.70	7080	1.55					45	601
-	9.9 - 86	330	30.28	6950	1.80						
-	11 - 95	300	27.34	6860	2.0						
-	12 - 109	260	24.05	6720	2.3						
-	13 - 115	245	22.71	6660	2.4						
-	16 - 135	210	19.34	6470	2.7						
-	17 - 149	193	17.57	6350	2.9						
-	20 - 171	167	15.22	6160	3.2						
-	23 - 197	145	13.25	5980	3.5						
-	25 - 219	131	11.92	5720	3.2						
-	27 - 232	124	11.26	5640	3.4						
-	31 - 272	105	9.59	5440	3.9						
-	34 - 300	96	8.71	5320	4.1						
-	40 - 346	83	7.55	5130	4.4						
-	46 - 397	72	6.57	4950	4.8						


P_m = 3.0 kW											
	n_a min⁻¹ 10-87Hz	M_a Nm	i	F_{Ra}¹⁾ N	SEW f_B					m kg	
-	6.8 - 59	485	44.44	5830	1.05						
-	7.9 - 69	415	37.98	5860	1.20						
-	8.6 - 75	380	34.81	5860	1.30						
-	9.8 - 85	335	30.55	5830	1.50						
-	10 - 90	315	28.95	5810	1.55	K	49	DRE	90MJ4	47	596
-	12 - 103	275	25.34	5740	1.80	KF	49	DRE	90MJ4	49	597
-	13 - 114	250	22.83	5680	2.0	KA	49	DRE	90MJ4	45	598
-	15 - 130	215	20.03	5580	2.3	KAF	49	DRE	90MJ4	50	597
-	17 - 148	194	17.67	5470	2.6						
-	19 - 167	172	15.67	5360	2.9						
-	22 - 195	147	13.38	5200	3.2						
-	26 - 230	125	11.37	5350	4.0						
-	8.5 - 74	385	35.39	4450	1.05						
-	12 - 101	280	25.91	4510	1.40						
-	14 - 120	235	21.81	4480	1.65						
-	15 - 133	210	19.58	4440	1.85						
-	18 - 155	185	16.86	4380	2.0						
-	19 - 165	174	15.86	4340	2.2						
-	22 - 191	150	13.65	4250	2.4	K	47	DRE	90MJ4	36	590
-	25 - 214	134	12.19	4170	2.6	KF	47	DRE	90MJ4	39	591
-	25 - 222	129	11.77	4090	2.2	KA	47	DRE	90MJ4	35	592
-	28 - 247	116	10.56	4010	2.4	KAF	47	DRE	90MJ4	38	591
-	33 - 287	100	9.10	3900	2.8						
-	35 - 305	94	8.56	3860	2.9						
-	41 - 354	81	7.36	3740	3.1						
-	46 - 397	72	6.58	3640	3.3						
-	52 - 449	64	5.81	3540	3.6						
-	65 - 563	51	4.64	3350	4.0						
-	9.8 - 85	335	30.72	4040	0.90						
-	11 - 94	300	27.73	4090	1.00						
-	12 - 107	265	24.40	4120	1.10						
-	13 - 113	250	23.04	4130	1.20						
-	15 - 133	215	19.62	4120	1.35	K	39	DRE	90MJ4	35	586
-	17 - 146	196	17.83	4100	1.50	KF	39	DRE	90MJ4	36	587
-	19 - 169	170	15.44	4060	1.65	KA	39	DRE	90MJ4	34	588
-	22 - 194	148	13.44	4000	1.85	KAF	39	DRE	90MJ4	35	587
-	28 - 246	116	10.61	4200	2.5						
-	33 - 290	99	9.00	4040	3.0						
-	37 - 321	89	8.12	3940	3.4						
-	42 - 365	78	7.15	3820	3.8						
-	20 - 170	168	15.31	2020	1.05						
-	23 - 200	144	13.08	2060	1.15						
-	29 - 249	115	10.49	2090	1.40	K	37	DRE	90MJ4	29	580
-	34 - 293	98	8.91	2080	1.65	KF	37	DRE	90MJ4	31	581
-	38 - 328	87	7.96	2060	1.80	KA	37	DRE	90MJ4	29	582
-	44 - 384	75	6.80	2030	2.0	KAF	37	DRE	90MJ4	31	581
-	47 - 410	70	6.37	2020	2.1						
-	56 - 487	59	5.36	1970	2.4						
-	75 - 656	44	3.98	1870	2.9						
-	22 - 194	137	13.47	2130	0.95						
-	25 - 219	122	11.94	2140	1.05						
-	33 - 285	94	9.17	2120	1.40						
-	40 - 349	76	7.48	2080	1.60	K	29	DRE	90MJ4	23	573
-	43 - 375	72	6.95	2220	1.55	KF	29	DRE	90MJ4	24	577
-	52 - 454	60	5.75	2130	1.85	KA	29	DRE	90MJ4	23	579
-	59 - 512	53	5.10	2080	2.1	KAF	29	DRE	90MJ4	24	577
-	77 - 667	41	3.92	1950	3.1						
-	94 - 818	33	3.19	1860	3.3						

P_m = 4.0 kW											
	n_a min⁻¹ 10-87Hz	M_a Nm	i	F_{Ra}¹⁾ N	SEW f_B					m kg	
-	1.7 - 15	2570	176.05*	40000	1.65	K KF KA KAF	97	DRE	90LJ4	170	624
-	2.0 - 17	2240	153.21*	40000	1.90						
-	2.1 - 19	2050	140.28	40000	2.1						
-	2.4 - 21	1810	123.93*	40000	2.4						
-	2.9 - 25	1530	105.13	40000	2.8						
-	3.1 - 27	1410	96.80	40000	3.0						
-	3.5 - 30	1260	86.52	40000	3.4						
-	3.9 - 34	1130	77.89*	39200	3.8						
-	4.3 - 37	1030	70.54	38300	4.2						
-	4.8 - 42	910	62.55	37200	4.7						
-	2.0 - 18	2150	147.32*	27900	1.25	K KF KA KAF	87	DRE	90LJ4	110	618
-	2.4 - 21	1850	126.91*	28200	1.45						
-	2.6 - 23	1690	115.82	28300	1.60						
-	2.9 - 25	1500	102.71*	28500	1.80						
-	3.5 - 30	1260	86.34	28600	2.1						
-	3.8 - 33	1160	79.34	28200	2.3						
-	4.3 - 37	1030	70.46	27600	2.6						
-	4.8 - 41	920	63.00*	27000	2.9						
-	5.3 - 46	820	56.64	26400	3.3						
-	6.1 - 53	715	49.16	25600	3.8						
-	6.8 - 59	640	44.02	25000	4.0						
-	8.2 - 71	530	36.52*	23900	4.7						
-	3.1 - 27	1420	97.05	16200	1.10	K KF KA KAF	77	DRE	90LJ4	75	612
-	3.4 - 29	1300	88.97	16900	1.20						
-	3.8 - 33	1140	78.07	17700	1.35						
-	4.1 - 35	1080	73.99	18000	1.45						
-	4.6 - 40	940	64.75	18500	1.65						
-	5.1 - 45	850	58.34	18800	1.80						
-	5.9 - 51	745	51.18	19100	2.1						
-	6.6 - 58	660	45.16	19400	2.4						
-	7.5 - 65	585	40.04	19500	2.6						
-	7.8 - 68	560	38.39	19600	2.7						
-	8.5 - 74	515	35.20	19700	3.0						
-	9.7 - 85	450	30.89	19800	3.4						
-	10 - 89	425	29.27	19800	3.6						
-	12 - 102	370	25.62	19400	4.1						
-	13 - 113	335	23.08	18900	4.6						
-	6.2 - 54	710	48.77	11200	1.15	K KF KA KAF	67	DRE	90LJ4	51	606
-	6.8 - 59	645	44.32	11600	1.25						
-	7.8 - 68	560	38.39	12100	1.40						
-	8.4 - 73	520	35.62	12300	1.55						
-	9.9 - 86	440	30.22	12700	1.85						
-	11 - 96	395	27.28	12800	2.0						
-	13 - 109	350	24.00	13000	2.3						
-	13 - 115	330	22.66	13000	2.4						
-	16 - 135	280	19.30	13000	2.7						
-	17 - 149	255	17.54	13000	2.9						
-	20 - 172	220	15.19	12700	3.1						
-	23 - 197	193	13.22	12300	3.5						
-	24 - 209	183	12.48	11900	2.9						
-	28 - 246	156	10.63	11500	3.2						
-	31 - 270	141	9.66	11200	3.4						
-	36 - 312	122	8.37	10900	3.6						
-	41 - 358	107	7.28	10500	3.9						
-	58 - 502	76	5.20	9610	4.6						


P_m = 4.0 kW

	n_a min⁻¹ 10-87Hz	M_a Nm	i	F_{Ra}¹⁾ N	SEW f_B					m kg	
-	7.8 - 68	560	38.49	6200	1.05						
-	8.4 - 73	520	35.70	6220	1.15						
-	9.9 - 86	440	30.28	6220	1.35						
-	11 - 95	400	27.34	6200	1.50						
-	12 - 109	350	24.05	6150	1.70						
-	13 - 115	330	22.71	6120	1.80						
-	16 - 135	280	19.34	6010	2.0						
-	17 - 149	255	17.57	5930	2.2	K	57	DRE	90LJ4	45	600
-	20 - 171	220	15.22	5800	2.4	KF	57	DRE	90LJ4	49	601
-	23 - 197	194	13.25	5660	2.6	KA	57	DRE	90LJ4	43	602
-	25 - 219	174	11.92	5390	2.4	KAF	57	DRE	90LJ4	48	601
-	27 - 232	165	11.26	5340	2.5						
-	31 - 272	140	9.59	5180	2.9						
-	34 - 300	128	8.71	5080	3.1						
-	40 - 346	110	7.55	4920	3.3						
-	46 - 397	96	6.57	4770	3.6						
-	64 - 556	69	4.69	4390	4.4						
-	7.9 - 69	555	37.98	4860	0.90						
-	8.6 - 75	505	34.81	4940	1.00						
-	9.8 - 85	445	30.55	5030	1.10						
-	10 - 90	420	28.95	5050	1.20						
-	12 - 103	370	25.34	5080	1.35						
-	13 - 114	330	22.83	5080	1.50	K	49	DRE	90LJ4	50	596
-	15 - 130	290	20.03	5050	1.70	KF	49	DRE	90LJ4	52	597
-	17 - 148	255	17.67	5010	1.95	KA	49	DRE	90LJ4	47	598
-	19 - 167	225	15.67	4950	2.1	KAF	49	DRE	90LJ4	52	597
-	22 - 195	196	13.38	4850	2.4						
-	26 - 230	166	11.37	5160	3.0						
-	29 - 251	152	10.42	5050	3.1						
-	33 - 286	134	9.14	4890	3.7						
-	35 - 301	127	8.66	4830	3.9						
-	12 - 101	375	25.91	3790	1.05						
-	14 - 120	315	21.81	3870	1.25						
-	15 - 133	285	19.58	3900	1.40						
-	18 - 155	245	16.86	3900	1.55						
-	19 - 165	230	15.86	3900	1.65						
-	22 - 191	200	13.65	3870	1.80	K	47	DRE	90LJ4	39	590
-	25 - 214	178	12.19	3830	1.95	KF	47	DRE	90LJ4	42	591
-	25 - 222	172	11.77	3740	1.65	KA	47	DRE	90LJ4	38	592
-	28 - 247	155	10.56	3700	1.80	KAF	47	DRE	90LJ4	41	591
-	33 - 287	133	9.10	3640	2.1						
-	35 - 305	125	8.56	3600	2.2						
-	41 - 354	108	7.36	3520	2.3						
-	46 - 397	96	6.58	3450	2.5						
-	52 - 449	85	5.81	3370	2.7						
-	65 - 563	68	4.64	3210	3.0						
-	12 - 107	355	24.40	3350	0.85						
-	13 - 113	335	23.04	3400	0.90						
-	15 - 133	285	19.62	3500	1.05						
-	17 - 146	260	17.83	3540	1.10						
-	19 - 169	225	15.44	3570	1.25						
-	22 - 194	197	13.44	3580	1.35	K	39	DRE	90LJ4	38	586
-	28 - 246	155	10.61	3980	1.85	KF	39	DRE	90LJ4	39	587
-	33 - 290	132	9.00	3850	2.3	KA	39	DRE	90LJ4	37	588
-	37 - 321	119	8.12	3770	2.5	KAF	39	DRE	90LJ4	38	587
-	42 - 365	105	7.15	3670	2.9						
-	44 - 387	99	6.75	3620	3.0						
-	52 - 454	84	5.75	3480	3.3						
-	57 - 500	76	5.22	3400	3.4						
-	66 - 577	66	4.52	3280	3.6						
-	76 - 663	58	3.94	3170	3.7						

P _m = 4.0 kW											
	n _a min ⁻¹ 10-87Hz	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
-	29 - 249	154	10.49	1740	1.05						
-	34 - 293	130	8.91	1780	1.25	K	37	DRE	90LJ4	32	580
-	38 - 328	116	7.96	1800	1.35	KF	37	DRE	90LJ4	34	581
-	44 - 384	100	6.80	1810	1.50	KA	37	DRE	90LJ4	32	582
-	47 - 410	93	6.37	1810	1.55	KAF	37	DRE	90LJ4	33	581
-	56 - 487	78	5.36	1790	1.80						
-	75 - 656	58	3.98	1740	2.1						
-	25 - 219	162	11.94	1770	0.80						
-	33 - 285	125	9.17	1840	1.05						
-	40 - 349	102	7.48	1850	1.20	K	29	DRE	90LJ4	26	573
-	43 - 375	96	6.95	2060	1.15	KF	29	DRE	90LJ4	27	577
-	52 - 454	80	5.75	2000	1.40	KA	29	DRE	90LJ4	26	579
-	59 - 512	71	5.10	1960	1.55	KAF	29	DRE	90LJ4	27	577
-	77 - 667	54	3.92	1860	2.3						
-	94 - 818	44	3.19	1780	2.5						


P _m = 5.5 kW											
	n _a min ⁻¹ 10-87Hz	M _a Nm	i	F _{Ra} ¹⁾ N	SEW f _B					m kg	
-	2.0 - 17	3080	153.21*	40000	1.40	K KF KA KAF	97 97 97 97	DRE DRE DRE DRE	100MJ4 100MJ4 100MJ4 100MJ4	175 195 155 180	624 625 626 625
-	2.1 - 19	2820	140.28	40000	1.50						
-	2.4 - 21	2490	123.93*	40000	1.70						
-	2.9 - 25	2110	105.13	39900	2.0						
-	3.1 - 27	1940	96.80	39300	2.2						
-	3.5 - 30	1740	86.52	38500	2.5						
-	3.9 - 34	1560	77.89*	37700	2.7						
-	4.3 - 37	1410	70.54	37000	3.0						
-	4.8 - 42	1250	62.55	36000	3.4						
-	5.3 - 46	1130	56.55	35300	3.8						
-	6.3 - 54	960	47.93*	34000	4.5						
-	2.4 - 21	2550	126.91*	27500	1.05	K KF KA KAF	87 87 87 87	DRE DRE DRE DRE	100MJ4 100MJ4 100MJ4 100MJ4	115 125 105 115	618 619 620 619
-	2.6 - 23	2330	115.82	27500	1.15						
-	2.9 - 25	2060	102.71*	27200	1.30						
-	3.5 - 30	1730	86.34	26800	1.55						
-	3.8 - 33	1590	79.34	26500	1.70						
-	4.3 - 37	1410	70.46	26000	1.90						
-	4.8 - 41	1260	63.00*	25600	2.1						
-	5.3 - 46	1130	56.64	25100	2.4						
-	6.1 - 53	980	49.16	24500	2.7						
-	6.8 - 59	880	44.02	24000	2.9						
-	8.2 - 71	730	36.52*	23100	3.4						
-	9.6 - 83	630	31.39	22400	4.3						
-	11 - 94	560	27.88	21800	4.6						
-	12 - 105	500	24.92	21200	5.0						
-	4.1 - 35	1480	73.99	15800	1.05	K KF KA KAF	77 77 77 77	DRE DRE DRE DRE	100MJ4 100MJ4 100MJ4 100MJ4	80 88 73 80	612 613 614 613
-	4.6 - 40	1300	64.75	16900	1.20						
-	5.1 - 45	1170	58.34	17600	1.30						
-	5.9 - 51	1020	51.18	18200	1.50						
-	6.6 - 58	900	45.16	18600	1.70						
-	7.5 - 65	800	40.04	19000	1.90						
-	7.8 - 68	770	38.39	19100	1.95						
-	8.5 - 74	705	35.20	19200	2.2						
-	9.7 - 85	620	30.89	19500	2.5						
-	10 - 89	585	29.27	19300	2.6						
-	12 - 102	515	25.62	18700	3.0						
-	13 - 113	460	23.08	18300	3.3						
-	15 - 129	405	20.25	17800	3.7						
-	17 - 146	355	17.87	17300	4.0						
-	19 - 165	315	15.84	16800	4.4						
-	22 - 193	270	13.52	16200	4.9						
-	24 - 211	245	12.36	15700	4.0						
-	28 - 241	215	10.84	15200	4.5						
-	31 - 273	192	9.56	14700	4.9						

P_m = 5.5 kW


	n_a min⁻¹ 10-87Hz	M_a Nm	i	F_{Ra}¹⁾ N	SEW f_B					m kg	
-	7.8 - 68	770	38.39	10700	1.05	K	67	DRE	100MJ4	55	606
-	9.9 - 86	605	30.22	11900	1.35						
-	11 - 96	545	27.28	12200	1.50						
-	13 - 109	480	24.00	12500	1.65						
-	13 - 115	455	22.66	12600	1.70						
-	16 - 135	385	19.30	12800	1.95						
-	17 - 149	350	17.54	12500	2.1						
-	20 - 172	305	15.19	12200	2.3						
-	23 - 197	265	13.22	11900	2.5						
-	24 - 209	250	12.48	11500	2.1						
-	28 - 246	210	10.63	11100	2.3						
-	31 - 270	194	9.66	10900	2.5						
-	36 - 312	168	8.37	10500	2.6						
-	41 - 358	146	7.28	10200	2.9						
-	58 - 502	105	5.20	9420	3.3						
-	11 - 95	550	27.34	5220	1.10	K	57	DRE	100MJ4	49	600
-	12 - 109	480	24.05	5280	1.25						
-	13 - 115	455	22.71	5300	1.30						
-	16 - 135	385	19.34	5310	1.50						
-	17 - 149	350	17.57	5300	1.55						
-	20 - 171	305	15.22	5250	1.75						
-	23 - 197	265	13.25	5180	1.90						
-	25 - 219	235	11.92	4910	1.75						
-	27 - 232	225	11.26	4880	1.85						
-	31 - 272	193	9.59	4790	2.1						
-	34 - 300	175	8.71	4720	2.2						
-	40 - 346	152	7.55	4620	2.4						
-	46 - 397	132	6.57	4500	2.6						
-	64 - 556	94	4.69	4200	3.2						
-	9.8 - 85	610	30.55	3820	0.80	K	49	DRE	100MJ4	55	596
-	10 - 90	580	28.95	3900	0.85						
-	12 - 103	505	25.34	4080	1.00						
-	13 - 114	455	22.83	4170	1.10						
-	15 - 130	400	20.03	4260	1.25						
-	17 - 148	355	17.67	4310	1.40						
-	19 - 167	315	15.67	4330	1.55						
-	22 - 195	265	13.38	4320	1.75						
-	26 - 230	225	11.37	4870	2.2						
-	29 - 251	205	10.42	4790	2.3						
-	33 - 286	184	9.14	4660	2.7						
-	35 - 301	174	8.66	4610	2.9						
-	40 - 344	153	7.58	4470	3.3						
-	44 - 382	137	6.83	4370	3.6						
-	15 - 133	390	19.58	3080	1.00	K	47	DRE	100MJ4	43	590
-	18 - 155	335	16.86	3200	1.10						
-	19 - 165	315	15.86	3240	1.20						
-	22 - 191	270	13.65	3300	1.30						
-	25 - 214	245	12.19	3320	1.45						
-	25 - 222	235	11.77	3220	1.20						
-	28 - 247	210	10.56	3240	1.30						
-	33 - 287	183	9.10	3230	1.55						
-	35 - 305	172	8.56	3220	1.55						
-	41 - 354	148	7.36	3190	1.70						
-	46 - 397	132	6.58	3160	1.80						
-	52 - 449	117	5.81	3110	1.95						
-	65 - 563	93	4.64	3010	2.2						

P_m = 5.5 kW											
	n_a min⁻¹ 10-87Hz	M_a Nm	i	F_{Ra}¹⁾ N	SEW f_B					m kg	
-	17 - 146	355	17.83	2700	0.80						
-	19 - 169	310	15.44	2840	0.90						
-	22 - 194	270	13.44	2940	1.00						
-	33 - 290	181	9.00	3570	1.65						
-	37 - 321	164	8.12	3520	1.85	K	39	DRE	100MJ4	42	586
-	42 - 365	144	7.15	3440	2.1	KF	39	DRE	100MJ4	44	587
-	44 - 387	136	6.75	3410	2.2	KA	39	DRE	100MJ4	41	588
-	52 - 454	116	5.75	3300	2.4	KAF	39	DRE	100MJ4	43	587
-	57 - 500	105	5.22	3240	2.5						
-	66 - 577	91	4.52	3140	2.6						
-	76 - 663	79	3.94	3040	2.7						
-	107 - 928	57	2.81	2800	3.0						



33 013 00 17

KF19B..**KAF19B..**

Ø 120
max. DR71M







Ø 160



(→ 176)	DR71S	DR71M	DR80S	DR80M			
AC	139	139	156	156			
AD	119	119	128	128			
ADS	129	129	139	139			
L	368	393	403	434			
LS	436	461	484	515			
LB	202	227	237	268			
LBS	270	295	318	349			





33 014 00 17

KHF19B..



(→ 176)	DR71S	DR71M	DR80S	DR80M				
AC	139	139	156	156				
AD	119	119	128	128				
ADS	129	129	139	139				
L	368	393	403	434				
LS	436	461	484	515				
LB	202	227	237	268				
LBS	270	295	318	349				





33 015 00 17

KF19..**KAF19..****Ø 120**
max. DR71M**Ø 160**






(→ 176)	DR71S	DR71M	DR80S	DR80M				
AC	139	139	156	156				
AD	119	119	128	128				
ADS	129	129	139	139				
L	368	393	403	434				
LS	436	461	484	515				
LB	202	227	237	268				
LBS	270	295	318	349				

33 016 00 17

KHF19..




(→ 176)	DR71S	DR71M	DR80S	DR80M				
AC	139	139	156	156				
AD	119	119	128	128				
ADS	129	129	139	139				
L	368	393	403	434				
LS	436	461	484	515				
LB	202	227	237	268				
LBS	270	295	318	349				



(→ 176)	DR71S	DR71M	DR80S	DR80M				
AC	139	139	156	156				
AD	119	119	128	128				
ADS	129	129	139	139				
L	368	393	403	434				
LS	436	461	484	515				
LB	202	227	237	268				
LBS	270	295	318	349				

33 018 00 17

K29..




10

19391609/DE – 06/2017

(→ 176)	DR71S	DR71M	DR80S	DR80M	DR90M	DR90L		
AC	139	139	156	156	179	179		
AD	119	119	128	128	140	140		
ADS	129	129	139	139	150	150		
L	399	424	434	465	469	489		
LS	467	492	515	546	562	582		
LB	202	227	237	268	272	292		
LBS	270	295	318	349	365	385		


33 020 00 17

KF29B..




KAF29B..


$\phi 160$




$\phi 200$



$\phi 30$ H7
DIN 6985-3




$\phi 25$ H7



(→ 176)	DR71S	DR71M	DR80S	DR80M	DR90M	DR90L		
AC	139	139	156	156	179	179		
AD	119	119	128	128	140	140		
ADS	129	129	139	139	150	150		
L	399	424	434	465	469	489		
LS	467	492	515	546	562	582		
LB	202	227	237	268	272	292		
LBS	270	295	318	349	365	385		


KHF29B..



(→ 176)	DR71S	DR71M	DR80S	DR80M	DR90M	DR90L		
AC	139	139	156	156	179	179		
AD	119	119	128	128	140	140		
ADS	129	129	139	139	150	150		
L	399	424	434	465	469	489		
LS	467	492	515	546	562	582		
LB	202	227	237	268	272	292		
LBS	270	295	318	349	365	385		


33 022 00 17

KF29..




KAF29..


ø 160




ø 200



**ø 30 H7
DIN 6985-3**




ø 25 H7



(→ 176)	DR71S	DR71M	DR80S	DR80M	DR90M	DR90L		
AC	139	139	156	156	179	179		
AD	119	119	128	128	140	140		
ADS	129	129	139	139	150	150		
L	397	422	432	463	467	487		
LS	465	490	513	544	560	580		
LB	202	227	237	268	272	292		
LBS	270	295	318	349	365	385		



33 023 00 17

KHF29..

(→ 176)	DR71S	DR71M	DR80S	DR80M	DR90M	DR90L		
AC	139	139	156	156	179	179		
AD	119	119	128	128	140	140		
ADS	129	129	139	139	150	150		
L	397	422	432	463	467	487		
LS	465	490	513	544	560	580		
LB	202	227	237	268	272	292		
LBS	270	295	318	349	365	385		


KA29..

33 024 00 17




10


KA29..





KH29..



**Ø 30 H7
DIN 6885-3**




Ø 25 H7



19391609/DE – 06/2017


(→ 176)	DR71S	DR71M	DR80S	DR80M	DR90M	DR90L		
AC	139	139	156	156	179	179		
AD	119	119	128	128	140	140		
ADS	129	129	139	139	150	150		
L	397	422	432	463	467	487		
LS	465	490	513	544	560	580		
LB	202	227	237	268	272	292		
LBS	270	295	318	349	365	385		



(→ 176)	DR71S	DR71M	DR80S	DR80M	DR90M	DR90L		
AC	139	139	156	156	179	179		
AD	119	119	128	128	140	140		
ADS	129	129	139	139	150	150		
L	404	429	439	470	474	494		
LS	472	497	520	551	567	587		
LB	202	227	237	268	272	292		
LBS	270	295	318	349	365	385		

KF37..

33 026 00 17




10

KAF37..

KHF37..

KVF37..








19391609/DE – 06/2017

(→ 176)	DR71S	DR71M	DR80S	DR80M	DR90M	DR90L		
AC	139	139	156	156	179	179		
AD	119	119	128	128	140	140		
ADS	129	129	139	139	150	150		
L	413	438	448	479	483	503		
LS	481	506	529	560	576	596		
LB	202	227	237	268	272	292		
LBS	270	295	318	349	365	385		

KA37..


33 027 00 17

**KA37..****KH37..****KV37..**

(→ 176)	DR71S	DR71M	DR80S	DR80M	DR90M	DR90L		
AC	139	139	156	156	179	179		
AD	119	119	128	128	140	140		
ADS	129	129	139	139	150	150		
L	413	438	448	479	483	503		
LS	481	506	529	560	576	596		
LB	202	227	237	268	272	292		
LBS	270	295	318	349	365	385		

KAZ37..


33 028 00 17



KAZ37..


KHZ37..

KVZ37..



(→ 176)	DR71S	DR71M	DR80S	DR80M	DR90M	DR90L		
AC	139	139	156	156	179	179		
AD	119	119	128	128	140	140		
ADS	129	129	139	139	150	150		
L	413	438	448	479	483	503		
LS	481	506	529	560	576	596		
LB	202	227	237	268	272	292		
LBS	270	295	318	349	365	385		

33 029 00 17


KZ37..

(→ 176)	DR71S	DR71M	DR80S	DR80M	DR90M	DR90L		
AC	139	139	156	156	179	179		
AD	119	119	128	128	140	140		
ADS	129	129	139	139	150	150		
L	413	438	448	479	483	503		
LS	481	506	529	560	576	596		
LB	202	227	237	268	272	292		
LBS	270	295	318	349	365	385		

19391609/DE – 06/2017

KT37..

33 030 00 17




10

19391609/DE – 06/2017

(→ 176)	DR71S	DR71M	DR80S	DR80M	DR90M	DR90L		
AC	139	139	156	156	179	179		
AD	119	119	128	128	140	140		
ADS	129	129	139	139	150	150		
L	413	438	448	479	483	503		
LS	481	506	529	560	576	596		
LB	202	227	237	268	272	292		
LBS	270	295	318	349	365	385		

33 031 00 17


K39..

(→ 176)	DR71S	DR71M	DR80S	DR80M	DR90M	DR90L	DR100M	
AC	139	139	156	156	179	179	197	
AD	119	119	128	128	140	140	157	
ADS	129	129	139	139	150	150	158	
L	446	471	480	511	513	533	563	
LS	514	539	561	592	606	626	656	
LB	196	221	230	261	263	283	313	
LBS	264	289	311	342	356	376	406	

19391609/DE – 06/2017


33 032 00 17

KF39..




KAF39..







KHF39..



(→ 176)	DR71S	DR71M	DR80S	DR80M	DR90M	DR90L	DR100M	
AC	139	139	156	156	179	179	197	
AD	119	119	128	128	140	140	157	
ADS	129	129	139	139	150	150	158	
L	447	472	481	512	514	534	564	
LS	515	540	562	593	607	627	657	
LB	196	221	230	261	263	283	313	
LBS	264	289	311	342	356	376	406	

KA39..






33 033 00 17

K.. /T**KA39..****KH39..** **$\phi 35$ H7** **$\phi 30$ H7**

(→ 176)	DR71S	DR71M	DR80S	DR80M	DR90M	DR90L	DR100M
AC	139	139	156	156	179	179	197
AD	119	119	128	128	140	140	157
ADS	129	129	139	139	150	150	158
L	447	472	481	512	514	534	564
LS	515	540	562	593	607	627	657
LB	196	221	230	261	263	283	313
LBS	264	289	311	342	356	376	406





KT39..

33 034 00 17





(→ 176)	DR71S	DR71M	DR80S	DR80M	DR90M	DR90L	DR100M	
AC	139	139	156	156	179	179	197	
AD	119	119	128	128	140	140	157	
ADS	129	129	139	139	150	150	158	
L	447	472	481	512	514	534	564	
LS	515	540	562	593	607	627	657	
LB	196	221	230	261	263	283	313	
LBS	264	289	311	342	356	376	406	

33 035 00 17

K47..**KA47B..****KH47B..****KV47B..**





(→ 176)	DR71S	DR71M	DR80S	DR80M	DR90M	DR90L	DR100M	
AC	139	139	156	156	179	179	197	
AD	119	119	128	128	140	140	157	
ADS	129	129	139	139	150	150	158	
L	433	458	467	498	500	520	550	
LS	501	526	548	579	593	613	643	
LB	196	221	230	261	263	283	313	
LBS	264	289	311	342	356	376	406	

Technical drawing of the GEW 165 motor showing dimensions in mm. The drawing includes a side view of the motor with dimensions: total length LS, mounting bracket length L, mounting bracket hole spacing 243, mounting bracket hole diameter 166, mounting bracket hole offset LB, mounting bracket hole diameter 160, mounting bracket hole offset 7.2, mounting bracket hole diameter 165, mounting bracket hole offset 11, and mounting bracket hole diameter AC.



Technical drawing of a metal enclosure with the following dimensions and features:



- Top View:**
 - Overall width: 125 mm (78 mm + 75 mm + 25 mm)
 - Overall height: $\varnothing 200$ mm
- Front View:**
 - Overall length: 132 mm
 - Mounting flange width: 75 mm (center-to-center)
 - Bottom flange width: 75 mm
 - Bottom flange thickness: 22 mm
 - Bottom flange outer diameter: $\varnothing 35^{H7}$
 - Bottom flange inner diameter: $\varnothing 50$
- Side View:**
 - Flange thickness: 10 mm
 - Flange outer diameter: 38.3 mm
- Material and Thread:**
 - Material: ISO 4017
 - Thread: M12x30-8.8



(→ 176)	DR71S	DR71M	DR80S	DR80M	DR90M	DR90L	DR100M	
AC	139	139	156	156	179	179	197	
AD	119	119	128	128	140	140	157	
ADS	129	129	139	139	150	150	158	
L	439	464	473	504	506	526	556	
LS	507	532	554	585	599	619	649	
LB	196	221	230	261	263	283	313	
LBS	264	289	311	342	356	376	406	

KA47..




33 037 00 17



KA47..

KH47..


KV47..



(→ 176)	DR71S	DR71M	DR80S	DR80M	DR90M	DR90L	DR100M
AC	139	139	156	156	179	179	197
AD	119	119	128	128	140	140	157
ADS	129	129	139	139	150	150	158
L	439	464	473	504	506	526	556
LS	507	532	554	585	599	619	649
LB	196	221	230	261	263	283	313
LBS	264	289	311	342	356	376	406

33 038 00 17


KAZ47..



KAZ47..


KHZ47..

KVZ47..



(→ 176)	DR71S	DR71M	DR80S	DR80M	DR90M	DR90L	DR100M	
AC	139	139	156	156	179	179	197	
AD	119	119	128	128	140	140	157	
ADS	129	129	139	139	150	150	158	
L	439	464	473	504	506	526	556	
LS	507	532	554	585	599	619	649	
LB	196	221	230	261	263	283	313	
LBS	264	289	311	342	356	376	406	

33 039 00 17


KZ47..

(→ 176)	DR71S	DR71M	DR80S	DR80M	DR90M	DR90L	DR100M	
AC	139	139	156	156	179	179	197	
AD	119	119	128	128	140	140	157	
ADS	129	129	139	139	150	150	158	
L	439	464	473	504	506	526	556	
LS	507	532	554	585	599	619	649	
LB	196	221	230	261	263	283	313	
LBS	264	289	311	342	356	376	406	

19391609/DE – 06/2017

KT47..

33 040 00 17




10

19391609/DE – 06/2017

(→ 176)	DR71S	DR71M	DR80S	DR80M	DR90M	DR90L	DR100M	
AC	139	139	156	156	179	179	197	
AD	119	119	128	128	140	140	157	
ADS	129	129	139	139	150	150	158	
L	439	464	473	504	506	526	556	
LS	507	532	554	585	599	619	649	
LB	196	221	230	261	263	283	313	
LBS	264	289	311	342	356	376	406	

33 041 00 17


K49..

(→ 176)	DR71S	DR71M	DR80S	DR80M	DR90M	DR90L	DR100M	DR100L/LC
AC	139	139	156	156	179	179	197	197
AD	119	119	128	128	140	140	157	157
ADS	129	129	139	139	150	150	158	158
L	496	521	530	561	563	583	613	643
LS	564	589	611	642	656	676	706	736
LB	189	214	223	254	256	276	306	336
LBS	257	282	304	335	349	369	399	429

19391609/DE – 06/2017


33 042 00 17

KF49..



KAF49..

KHF49..








19391609/DE – 06/2017

(→ 176)	DR71S	DR71M	DR80S	DR80M	DR90M	DR90L	DR100M	DR100L/LC
AC	139	139	156	156	179	179	197	197
AD	119	119	128	128	140	140	157	157
ADS	129	129	139	139	150	150	158	158
L	495	520	529	560	562	582	612	642
LS	563	588	610	641	655	675	705	735
LB	189	214	223	254	256	276	306	336
LBS	257	282	304	335	349	369	399	429





KT49..

33 044 00 17



(→ 176)	DR71S	DR71M	DR80S	DR80M	DR90M	DR90L	DR100M	DR100L/LC
AC	139	139	156	156	179	179	197	197
AD	119	119	128	128	140	140	157	157
ADS	129	129	139	139	150	150	158	158
L	495	520	529	560	562	582	612	642
LS	563	588	610	641	655	675	705	735
LB	189	214	223	254	256	276	306	336
LBS	257	282	304	335	349	369	399	429


33 045 00 17

K57..**KA57B..****KH57B..****KV57B..**

(→ 176)	DR71S	DR71M	DR80S	DR80M	DR90M	DR90L	DR100M	
AC	139	139	156	156	179	179	197	
AD	119	119	128	128	140	140	157	
ADS	129	129	139	139	150	150	158	
L	449	474	483	514	516	536	566	
LS	517	542	564	595	609	629	659	
LB	196	221	230	261	263	283	313	
LBS	264	289	311	342	356	376	406	

KF57..


33 046 00 17



KAF57..

KHF57..


KVF57..



(→ 176)	DR71S	DR71M	DR80S	DR80M	DR90M	DR90L	DR100M	
AC	139	139	156	156	179	179	197	
AD	119	119	128	128	140	140	157	
ADS	129	129	139	139	150	150	158	
L	465	490	499	530	532	552	582	
LS	533	558	580	611	625	645	675	
LB	196	221	230	261	263	283	313	
LBS	264	289	311	342	356	376	406	

KAZ57..


33 048 00 17



KAZ57..


KHZ57..

KVZ57..



(→ 📄 176)	DR71S	DR71M	DR80S	DR80M	DR90M	DR90L	DR100M	
AC	139	139	156	156	179	179	197	
AD	119	119	128	128	140	140	157	
ADS	129	129	139	139	150	150	158	
L	465	490	499	530	532	552	582	
LS	533	558	580	611	625	645	675	
LB	196	221	230	261	263	283	313	
LBS	264	289	311	342	356	376	406	

33 049 00 17


KZ57..

(→ 176)	DR71S	DR71M	DR80S	DR80M	DR90M	DR90L	DR100M	
AC	139	139	156	156	179	179	197	
AD	119	119	128	128	140	140	157	
ADS	129	129	139	139	150	150	158	
L	465	490	499	530	532	552	582	
LS	533	558	580	611	625	645	675	
LB	196	221	230	261	263	283	313	
LBS	264	289	311	342	356	376	406	

19391609/DE – 06/2017

KT57..

33 050 00 17







10







19391609/DE – 06/2017

(→ 176)	DR71S	DR71M	DR80S	DR80M	DR90M	DR90L	DR100M	
AC	139	139	156	156	179	179	197	
AD	119	119	128	128	140	140	157	
ADS	129	129	139	139	150	150	158	
L	465	490	499	530	532	552	582	
LS	533	558	580	611	625	645	675	
LB	196	221	230	261	263	283	313	
LBS	264	289	311	342	356	376	406	

33 051 00 17

K67..**KA67B..****KH67B..****KV67B..**



(→ 176)	DR71S	DR71M	DR80S	DR80M	DR90M	DR90L	DR100M	
AC	139	139	156	156	179	179	197	
AD	119	119	128	128	140	140	157	
ADS	129	129	139	139	150	150	158	
L	465	490	499	530	532	552	582	
LS	533	558	580	611	625	645	675	
LB	196	221	230	261	263	283	313	
LBS	264	289	311	342	356	376	406	

[illegible]


(→ 176)	DR71S	DR71M	DR80S	DR80M	DR90M	DR90L	DR100M	
AC	139	139	156	156	179	179	197	
AD	119	119	128	128	140	140	157	
ADS	129	129	139	139	150	150	158	
L	470	495	504	535	537	557	587	
LS	538	563	585	616	630	650	680	
LB	196	221	230	261	263	283	313	
LBS	264	289	311	342	356	376	406	

33 053 00 17


KA67..




KA67..



KH67..




KV67..



(→ 176)	DR71S	DR71M	DR80S	DR80M	DR90M	DR90L	DR100M
AC	139	139	156	156	179	179	197
AD	119	119	128	128	140	140	157
ADS	129	129	139	139	150	150	158
L	470	495	504	535	537	557	587
LS	538	563	585	616	630	650	680
LB	196	221	230	261	263	283	313
LBS	264	289	311	342	356	376	406

KAZ67..


33 054 00 17



KAZ67..

KHZ67..


KVZ67..



19391609/DE – 06/2017

(→ 176)	DR71S	DR71M	DR80S	DR80M	DR90M	DR90L	DR100M	
AC	139	139	156	156	179	179	197	
AD	119	119	128	128	140	140	157	
ADS	129	129	139	139	150	150	158	
L	470	495	504	535	537	557	587	
LS	538	563	585	616	630	650	680	
LB	196	221	230	261	263	283	313	
LBS	264	289	311	342	356	376	406	

33 055 00 17






KZ67..

(→ 176)	DR71S	DR71M	DR80S	DR80M	DR90M	DR90L	DR100M	
AC	139	139	156	156	179	179	197	
AD	119	119	128	128	140	140	157	
ADS	129	129	139	139	150	150	158	
L	470	495	504	535	537	557	587	
LS	538	563	585	616	630	650	680	
LB	196	221	230	261	263	283	313	
LBS	264	289	311	342	356	376	406	

19391609/DE – 06/2017

KT67..

33 056 00 17







10



19391609/DE – 06/2017

(→ 176)	DR71S	DR71M	DR80S	DR80M	DR90M	DR90L	DR100M	
AC	139	139	156	156	179	179	197	
AD	119	119	128	128	140	140	157	
ADS	129	129	139	139	150	150	158	
L	470	495	504	535	537	557	587	
LS	538	563	585	616	630	650	680	
LB	196	221	230	261	263	283	313	
LBS	264	289	311	342	356	376	406	

33 057 00 17





K77..**KA77B..****KH77B..****KV77B..**

(→ 176)	DR71S	DR71M	DR80S	DR80M	DR90M	DR90L	DR100M	DR100L/LC
AC	139	139	156	156	179	179	197	197
AD	119	119	128	128	140	140	157	157
ADS	129	129	139	139	150	150	158	158
L	503	528	537	568	570	590	620	650
LS	571	596	618	649	663	683	713	743
LB	189	214	223	254	256	276	306	336
LBS	257	282	304	335	349	369	399	429








Technical drawing of a cylindrical component with the following dimensions:

- Top View:
 - Overall diameter: $\varnothing 300$
 - Central hole diameter: 37
 - Distance from center to flange edge: 108
 - Distance from center to main body edge: 105
- Side View:
 - Total length: 183
 - Main body length: 105
 - Flange length: 70
- Cross-sectional View:
 - Central hole diameter: $\varnothing 50\ H7$
 - Wall thickness: 32
 - Flange thickness: 14
 - Flange outer diameter: 53.8
- Callout: ISO 4017 M16x45-8.8



(→ 📄 176)	DR71S	DR71M	DR80S	DR80M	DR90M	DR90L	DR100M	DR100L/LC
AC	139	139	156	156	179	179	197	197
AD	119	119	128	128	140	140	157	157
ADS	129	129	139	139	150	150	158	158
L	501	526	535	566	568	588	618	648
LS	569	594	616	647	661	681	711	741
LB	189	214	223	254	256	276	306	336
LBS	257	282	304	335	349	369	399	429


33 059 00 17

KA77..**KA77..****KH77..****KV77..**

(→ 176)	DR71S	DR71M	DR80S	DR80M	DR90M	DR90L	DR100M	DR100L/LC
AC	139	139	156	156	179	179	197	197
AD	119	119	128	128	140	140	157	157
ADS	129	129	139	139	150	150	158	158
L	501	526	535	566	568	588	618	648
LS	569	594	616	647	661	681	711	741
LB	189	214	223	254	256	276	306	336
LBS	257	282	304	335	349	369	399	429

KAZ77..


33 060 00 17



KAZ77..


KHZ77..

KVZ77..



(→ 176)	DR71S	DR71M	DR80S	DR80M	DR90M	DR90L	DR100M	DR100L/LC
AC	139	139	156	156	179	179	197	197
AD	119	119	128	128	140	140	157	157
ADS	129	129	139	139	150	150	158	158
L	501	526	535	566	568	588	618	648
LS	569	594	616	647	661	681	711	741
LB	189	214	223	254	256	276	306	336
LBS	257	282	304	335	349	369	399	429

33 061 00 17



KZ77..

(→ 176)	DR71S	DR71M	DR80S	DR80M	DR90M	DR90L	DR100M	DR100L/LC
AC	139	139	156	156	179	179	197	197
AD	119	119	128	128	140	140	157	157
ADS	129	129	139	139	150	150	158	158
L	501	526	535	566	568	588	618	648
LS	569	594	616	647	661	681	711	741
LB	189	214	223	254	256	276	306	336
LBS	257	282	304	335	349	369	399	429


19391609/DE – 06/2017

KT77..

33 062 00 17












10



(→ 176)	DR71S	DR71M	DR80S	DR80M	DR90M	DR90L	DR100M	DR100L/LC
AC	139	139	156	156	179	179	197	197
AD	119	119	128	128	140	140	157	157
ADS	129	129	139	139	150	150	158	158
L	501	526	535	566	568	588	618	648
LS	569	594	616	647	661	681	711	741
LB	189	214	223	254	256	276	306	336
LBS	257	282	304	335	349	369	399	429

19391609/DE – 06/2017


33 063 00 17

K87..**KA87B..****KH87B..****KV87B..**

(→ 176)	DR71M	DR80S	DR80M	DR90M	DR90L	DR100M	DR100L/LC
AC	139	156	156	179	179	197	197
AD	119	128	128	140	140	157	157
ADS	129	139	139	150	150	158	158
L	598	607	638	640	660	690	720
LS	666	688	719	733	753	783	813
LB	209	218	249	251	271	301	331
LBS	277	299	330	344	364	394	424


33 064 00 17

KF87..




10


KAF87..



KHF87..



KVF87..





19391609/DE – 06/2017

(→ 176)	DR71M	DR80S	DR80M	DR90M	DR90L	DR100M	DR100L/LC	
AC	139	156	156	179	179	197	197	
AD	119	128	128	140	140	157	157	
ADS	129	139	139	150	150	158	158	
L	599	608	639	641	661	691	721	
LS	667	689	720	734	754	784	814	
LB	209	218	249	251	271	301	331	
LBS	277	299	330	344	364	394	424	

KA87..




33 065 00 17



KA87..

KH87..


KV87..



(→ 176)	DR71M	DR80S	DR80M	DR90M	DR90L	DR100M	DR100L/LC	
AC	139	156	156	179	179	197	197	
AD	119	128	128	140	140	157	157	
ADS	129	139	139	150	150	158	158	
L	599	608	639	641	661	691	721	
LS	667	689	720	734	754	784	814	
LB	209	218	249	251	271	301	331	
LBS	277	299	330	344	364	394	424	

KAZ87..


33 066 00 17



KAZ87..


KHZ87..

KVZ87..



(→ 176)	DR71M	DR80S	DR80M	DR90M	DR90L	DR100M	DR100L/LC	
AC	139	156	156	179	179	197	197	
AD	119	128	128	140	140	157	157	
ADS	129	139	139	150	150	158	158	
L	599	608	639	641	661	691	721	
LS	667	689	720	734	754	784	814	
LB	209	218	249	251	271	301	331	
LBS	277	299	330	344	364	394	424	

33 067 00 17



KZ87..

(→ 176)	DR71M	DR80S	DR80M	DR90M	DR90L	DR100M	DR100L/LC	
AC	139	156	156	179	179	197	197	
AD	119	128	128	140	140	157	157	
ADS	129	139	139	150	150	158	158	
L	599	608	639	641	661	691	721	
LS	667	689	720	734	754	784	814	
LB	209	218	249	251	271	301	331	
LBS	277	299	330	344	364	394	424	


19391609/DE – 06/2017

KT87..

33 068 00 17










10



(→ 176)	DR71M	DR80S	DR80M	DR90M	DR90L	DR100M	DR100L/LC	
AC	139	156	156	179	179	197	197	
AD	119	128	128	140	140	157	157	
ADS	129	139	139	150	150	158	158	
L	599	608	639	641	661	691	721	
LS	667	689	720	734	754	784	814	
LB	209	218	249	251	271	301	331	
LBS	277	299	330	344	364	394	424	

19391609/DE – 06/2017



Technical drawing of the GEW 400 motor showing dimensions: LS, L, LBS, LB, 435, 277, $\varnothing 17.5$, $\varnothing 400$, 32.3, $\varnothing 300$, GEW, and AC.



(→ 📄 176)	DR80S	DR80M	DR90M	DR90L	DR100M	DR100L/LC		
AC	156	156	179	179	197	197		
AD	128	128	140	140	157	157		
ADS	139	139	150	150	158	158		
L	648	679	681	701	731	761		
LS	729	760	774	794	824	854		
LB	213	244	246	266	296	326		
LBS	294	325	339	359	389	419		

KA97..




33 071 00 17



KA97..

KH97..


KV97..



(→ 176)	DR80S	DR80M	DR90M	DR90L	DR100M	DR100L/LC		
AC	156	156	179	179	197	197		
AD	128	128	140	140	157	157		
ADS	139	139	150	150	158	158		
L	648	679	681	701	731	761		
LS	729	760	774	794	824	854		
LB	213	244	246	266	296	326		
LBS	294	325	339	359	389	419		

KAZ97..


33 072 00 17



KAZ97..


KHZ97..

KVZ97..



(→ 176)	DR80S	DR80M	DR90M	DR90L	DR100M	DR100L/LC		
AC	156	156	179	179	197	197		
AD	128	128	140	140	157	157		
ADS	139	139	150	150	158	158		
L	648	679	681	701	731	761		
LS	729	760	774	794	824	854		
LB	213	244	246	266	296	326		
LBS	294	325	339	359	389	419		

33 073 00 17


KZ97..

(→ 176)	DR80S	DR80M	DR90M	DR90L	DR100M	DR100L/LC		
AC	156	156	179	179	197	197		
AD	128	128	140	140	157	157		
ADS	139	139	150	150	158	158		
L	648	679	681	701	731	761		
LS	729	760	774	794	824	854		
LB	213	244	246	266	296	326		
LBS	294	325	339	359	389	419		

19391609/DE – 06/2017

KT97..

33 074 00 17



10

19391609/DE – 06/2017

(→ 176)	DR80S	DR80M	DR90M	DR90L	DR100M	DR100L/LC		
AC	156	156	179	179	197	197		
AD	128	128	140	140	157	157		
ADS	139	139	150	150	158	158		
L	648	679	681	701	731	761		
LS	729	760	774	794	824	854		
LB	213	244	246	266	296	326		
LBS	294	325	339	359	389	419		