



9 R..

9.1 R..VU/VZ..DR/DT/DV..


R..VU/VZ..DR/DT/DV..




RF..VU/VZ..DR/DT/DV..




R..F VU/VZ..DR/DT/DV..





RM..VU/VZ..DR/DT/DV..




RX..VU/VZ..DR/DT/DV..













RXF..VU/VZ..DR/DT/DV..




50499AXX




9.2 R..VU/VZ..DR/DT/DV.. [kW]


R = 1:5 ... R = 1:6																																																																															
P _m /P _{a2} [kW]	n _{a1} [1/min]	-	n _{a2}	i	M _{a1} [Nm]	M _{a2}								m [kg]																																																																	
0.25 / 0.18	0.20	-	0.96	3065	3000	1840	-		R	97 R57	VU/VZ	01 DR	63L4	140	-																																																																
	0.22	-	1.1	2722	3000	1630	-																																																																								
	0.26	-	1.3	2311	3000	1390	-																																																																								
	0.29	-	1.4	2078	3000	1250	-																																																																								
	0.33	-	1.6	1823	2670	1090	-																																																																								
	0.38	-	1.9	1583	2320	950	-																																																																								
	0.43	-	2.1	1396	2050	840	-																																																																								
	0.49	-	2.4	1228	1800	735	-																																																																								
	0.57	-	2.8	1069	1570	640	-																																																																								
	0.64	-	3.1	938	1370	565	-																																																																								
	0.73	-	3.6	824	1210	495	-																																																																								
	0.82	-	4.0	737	1080	440	-																																																																								
	0.97	-	4.7	625	930	380	-										R	97 R57	VU/VZ	01 DR	63L4	135	-																																																								
	1.1	-	5.4	549	820	335	-																																																																								
	1.3	-	6.3	466	695	285	-																																																																								
	1.4	-	7.0	420	625	255	-																																																																								
	1.6	-	8.0	370	550	225	-																																																																								
	1.7	-	8.5	349	520	215	-																																																																								
	2.0	-	9.9	297	440	181	-																																																																								
	2.7	-	13	227	340	138	-																																																																								
	0.35	-	1.7	1737	1550	1040	-																		R	87 R57	VU/VZ	01 DR	63L4	100	-																																																
	0.40	-	1.9	1524	1550	910	-																																																																								
	0.46	-	2.3	1303	1550	780	-																																																																								
	0.53	-	2.6	1143	1550	685	-																																																																								
	0.68	-	3.3	885	1300	530	-																																																																								
	0.78	-	3.8	776	1140	465	-																																																																								
	0.88	-	4.3	685	1000	410	-																																																																								
	1.0	-	4.9	599	880	360	-																																																																								
	1.1	-	5.5	538	800	330	-																										R	87 R57	VU/VZ	01 DR	63L4	99	-																																								
	1.3	-	6.2	472	700	290	-																																																																								
	1.5	-	7.4	400	595	245	-																																																																								
	1.7	-	8.2	361	535	220	-																																																																								
	2.0	-	9.8	300	445	183	-																																																																								
	2.4	-	12	256	380	156	-																																																																								
	3.1	-	15	195	290	119	-																																																																								
	0.64	-	3.1	940	820	565	-																																		R	77 R37	VU/VZ	01 DR	63L4	64	-																																
	0.74	-	3.6	821	820	495	-																																																																								
	0.83	-	4.0	731	820	440	-																																																																								
	0.94	-	4.6	646	820	390	-																																																																								
	1.1	-	5.3	560	820	335	-																																																																								
	1.2	-	5.7	520	775	315	-																																										R	77 R37	VU/VZ	01 DR	63L4	63	-																								
	1.3	-	6.5	451	670	275	-																																																																								
	1.4	-	7.0	422	630	255	-																																																																								
	1.7	-	8.1	365	545	220	-																																																																								
	1.9	-	9.5	310	460	189	-																																																																								
	2.2	-	11	276	410	168	-																																																																								
	2.6	-	13	236	350	144	-																																																																								
	2.7	-	13	221	330	135	-																																																																								
	3.2	-	16	186	275	113	-																																																																								
	0.94	-	4.6	646	600	390	-																																																		R	67 R37	VU/VZ	01 DR	63L4	59	-																
	1.1	-	5.1	574	600	345	-																																																																								
	1.2	-	6.0	495	600	295	-																																																																								
	1.4	-	6.7	443	600	270	-																																																										R	67 R37	VU/VZ	01 DR	63L4	58	-								
	1.6	-	7.7	384	570	235	-																																																																								
	1.7	-	8.2	359	535	220	-																																																																								
	1.9	-	9.5	310	460	189	-																																																																								
	2.3	-	11	264	395	161	-																																																																								
	2.6	-	13	235	350	143	-																																																																								
	3.0	-	15	201	300	123	-																																																																								
	3.3	-	16	181	270	110	-																																																																								
	3.8	-	19	159	235	97	-																																																																								
	1.3	-	6.3	471	450	285	-																																																																		R	57 R37	VU/VZ	01 DR	63L4	53	-
	1.7	-	8.3	357	450	215	-																																																																								
	1.9	-	9.2	319	450	191	-																																																																								




R = 1:5 ... R = 1:6

P_m/P_{a2} [kW]	n_{a1} [1/min]	-	n_{a2}	i	M_{a1} [Nm]	M_{a2}						m [kg]	
0.25 / 0.18	2.1	-	10	290	430	177	-						
	2.3	-	11	262	390	160	-						
	2.5	-	12	246	365	150	-						
	2.8	-	13	220	325	134	-	R	57 R37	VU/VZ	01 DR	63L4	52 -
	3.2	-	16	188	280	115	-	RF	57 R37	VU/VZ	01 DR	63L4	55 -
	3.8	-	19	159	235	97	-						
	4.1	-	20	146	215	89	-						
	4.5	-	22	134	199	82	-						
	2.0	-	9.8	301	300	183	-						
	2.4	-	12	255	300	155	-						
	2.6	-	13	228	300	139	-						
	3.1	-	15	195	290	119	-	R	47 R37	VU/VZ	01 DR	63L4	47 -
	3.3	-	16	182	270	111	-	RF	47 R37	VU/VZ	01 DR	63L4	47 -
	3.9	-	19	154	230	94	-						
	4.7	-	23	129	192	79	-						
	5.5	-	27	109	162	66	-						
	6.2	-	30	98	146	60	-						
	3.4	-	17	176.88	280	115	-	R	47	VU/VZ	01 DR	63L4	37 228
	3.7	-	18	162.94	260	106	-	RF	47	VU/VZ	01 DR	63L4	37 229
	4.3	-	21	139.99	220	91	-						
	4.5	-	22	134.82	200	87	-	R	37	VU/VZ	01 DR	63L4	33 226
	4.9	-	24	123.66	196	80	-	RF	37	VU/VZ	01 DR	63L4	34 227
	5.7	-	28	105.28	166	68	-						
	4.5	-	22	135.09	130	87	-						
	4.9	-	24	123.91	130	80	-						
	5.7	-	28	105.49	130	68	-						
	6.6	-	32	90.96	130	59	-						
	7.1	-	35	84.78	130	55	-						
	8.2	-	40	74.11	117	48	-						
	8.7	-	42	69.47	110	45	-						
	9.9	-	48	61.30	97	40	-	R	27	VU/VZ	01 DR	63L4	29 224
	11	-	53	55.87	88	36	-	RF	27	VU/VZ	01 DR	63L4	30 225
	13	-	61	48.17	76	31	-						
	13	-	66	44.90	71	29	-						
	15	-	75	39.25	62	25	-						
	16	-	80	36.79	58	24	-						
	19	-	91	32.47	51	21	-						
	21	-	103	28.78	46	19	-						
	25	-	121	24.47	39	16	-						
	21	-	104	28.37	45	18	-						
	23	-	113	26.09	41	17	-						
	27	-	132	22.32	35	14	-						
	31	-	153	19.35	31	13	-						
	33	-	163	18.08	29	12	-						
	39	-	189	15.63	25	10	-						
	45	-	222	13.28*	21	8.6	-	R	27	VU/VZ	01 DR	63L4	29 224
	51	-	249	11.86	19	7.7	-	RF	27	VU/VZ	01 DR	63L4	29 225
	60	-	291	10.13	16	6.6	-						
	64	-	314	9.41	15	6.1	-						
	74	-	362	8.16	13	5.3	-						
	79	-	387	7.63*	12	4.9	-						
	92	-	448	6.59	10	4.3	-						
	108	-	527	5.60*	8.9	3.6	-						
	100	-	486	6.07	9.6	3.9	-	RX	67	VU/VZ	01 DR	63L4	36 214
	117	-	570	5.18	8.2	3.4	-	RXF	67	VU/VZ	01 DR	63L4	40 215
	133	-	651	4.53	7.2	2.9	-						





R = 1:5 ... R = 1:6															
P _m /P _{a2} [kW]	n _{a1} [1/min]	-	n _{a2}	i	M _{a1} [Nm]	M _{a2}						m [kg]			
0.25 / 0.18	110	-	537	5.50*	8.7	3.6	-								
	119	-	582	5.07	8.0	3.3	-								
	139	-	678	4.35	6.9	2.8	-								
	159	-	779	3.79	6.0	2.5	-								
	170	-	831	3.55*	5.6	2.3	-								
	192	-	940	3.14	5.0	2.0	-	RX	57	VU/VZ	01	DR	63L4	33	212
	208	-	1015	2.91	4.6	1.9	-	RXF	57	VU/VZ	01	DR	63L4	35	213
	229	-	1120	2.64*	4.2	1.7	-								
	255	-	1245	2.37	3.7	1.5	-								
	296	-	1445	2.04	3.2	1.3	-								
	315	-	1535	1.92*	3.0	1.2	-								
366	-	1790	1.65	2.6	1.1	-									
0.37 / 0.28	0.18	-	1.0	1987	4300	2550	-								
	0.20	-	1.1	1827	4300	2340	-	R	107 R77	VU/VZ	11	DT	80K6	220	-
	0.22	-	1.3	1599	4300	2050	-	RF	107 R77	VU/VZ	11	DT	80K6	225	-
	0.26	-	1.5	1400	4300	1800	-								
	0.29	-	1.7	1226	4300	1570	-								
	0.23	-	1.3	1583	3000	2030	-	R	97 R57	VU/VZ	11	DT	80K6	150	-
	0.26	-	1.5	1396	3000	1790	-	RF	97 R57	VU/VZ	11	DT	80K6	165	-
	0.29	-	1.7	1228	3000	1580	-								
	0.27	-	1.4	2311	3000	1960	-								
	0.29	-	1.5	2078	3000	1760	-								
	0.34	-	1.7	1823	3000	1550	-								
	0.39	-	2.0	1583	3000	1340	-								
	0.44	-	2.2	1396	3000	1180	-	R	97 R57	VU/VZ	01	DT	71D4	140	-
	0.50	-	2.6	1228	2660	1040	-	RF	97 R57	VU/VZ	01	DT	71D4	160	-
	0.57	-	2.9	1069	2320	910	-								
	0.65	-	3.3	938	2030	795	-								
	0.74	-	3.8	824	1790	700	-								
	0.83	-	4.2	737	1600	625	-								
	0.97	-	5.0	632	1370	535	-								
	0.98	-	5.0	625	1380	540	-								
	1.1	-	5.7	549	1210	475	-								
	1.3	-	6.7	466	1030	400	-								
	1.5	-	7.5	420	920	360	-	R	97 R57	VU/VZ	01	DT	71D4	140	-
	1.7	-	8.5	370	810	320	-	RF	97 R57	VU/VZ	01	DT	71D4	155	-
	1.8	-	9.0	349	770	300	-								
	2.1	-	11	297	655	255	-								
	2.7	-	14	227	500	195	-								
	0.54	-	2.7	1143	1550	970	-								
	0.69	-	3.5	885	1550	750	-	R	87 R57	VU/VZ	01	DT	71D4	100	-
	0.79	-	4.0	776	1550	660	-	RF	87 R57	VU/VZ	01	DT	71D4	110	-
	0.89	-	4.6	685	1490	580	-								
	1.0	-	5.2	599	1300	510	-								
	1.1	-	5.8	538	1180	465	-								
	1.3	-	6.6	472	1040	405	-								
	1.5	-	7.8	400	880	345	-	R	87 R57	VU/VZ	01	DT	71D4	100	-
	1.7	-	8.7	361	795	310	-	RF	87 R57	VU/VZ	01	DT	71D4	105	-
	2.0	-	10	300	660	260	-								
	2.4	-	12	256	565	220	-								
	3.1	-	16	195	430	168	-								
	0.95	-	4.9	646	820	550	-	R	77 R37	VU/VZ	01	DT	71D4	66	-
	1.1	-	5.6	560	820	475	-	RF	77 R37	VU/VZ	01	DT	71D4	72	-
	1.3	-	6.4	488	820	415	-								
	1.4	-	7.0	451	820	390	-								
	1.4	-	7.4	422	820	365	-								
	1.7	-	8.6	365	800	315	-								
	2.0	-	10	310	685	265	-	R	77 R37	VU/VZ	01	DT	71D4	65	-
	2.2	-	11	276	610	240	-	RF	77 R37	VU/VZ	01	DT	71D4	70	-
	2.6	-	13	236	520	205	-								
	2.8	-	14	221	485	190	-								
	3.3	-	17	186	410	160	-								





R = 1:5 ... R = 1:6


P_m/P_{a2} [kW]	n_{a1} [1/min]	n_{a2}	i	M_{a1} [Nm]	M_{a2} [Nm]			m [kg]	
0.37 / 0.28	1.4	- 7.1	443	600	380	-			
	1.6	- 8.2	384	600	330	-			
	1.7	- 8.7	359	600	310	-			
	2.0	- 10	310	600	265	-			
	2.3	- 12	264	580	225	-	R 67 R37	VU/VZ 01 DT 71D4	60 -
	2.6	- 13	235	515	200	-	RF 67 R37	VU/VZ 01 DT 71D4	63 -
	3.1	- 16	201	445	173	-			
	3.4	- 17	181	400	156	-			
	3.9	- 20	159	350	137	-			
	1.7	- 8.7	359	450	310	-			
	1.9	- 9.7	324	450	280	-			
	2.1	- 11	290	450	250	-			
	2.3	- 12	262	450	225	-			
	2.5	- 13	246	450	210	-	R 57 R37	VU/VZ 01 DT 71D4	53 -
	2.8	- 14	220	450	189	-	RF 57 R37	VU/VZ 01 DT 71D4	57 -
	3.3	- 17	188	415	162	-			
	3.9	- 20	159	350	137	-			
	4.2	- 21	146	320	126	-			
	4.6	- 23	134	295	115	-			
	2.7	- 14	228	300	196	-			
	3.1	- 16	195	300	168	-			
	3.4	- 17	182	300	157	-			
	4.0	- 20	154	300	133	-	R 47 R37	VU/VZ 01 DT 71D4	48 -
	4.8	- 24	129	285	111	-	RF 47 R37	VU/VZ 01 DT 71D4	49 -
	5.6	- 29	109	240	94	-			
	6.2	- 32	98	215	84	-			
0.37 / 0.30	2.1	- 12	166.59	820	230	-	R 77	VU/VZ 11 DT 80K6	67 234
	2.5	- 14	145.67	820	200	-	RF 77	VU/VZ 11 DT 80K6	72 235
	2.6	- 15	138.39	820	192	-			
	2.9	- 17	121.42	745	168	-			
	2.3	- 13	158.14	600	220	-			
	2.6	- 15	137.67	600	191	-			
	2.8	- 16	128.97	600	179	-			
	3.1	- 18	113.94	600	158	-	R 67	VU/VZ 11 DT 80K6	58 232
	3.4	- 20	105.83	600	147	-	RF 67	VU/VZ 11 DT 80K6	62 233
	3.7	- 22	95.91	590	133	-			
	4.2	- 24	86.11	530	119	-			
	3.1	- 16	199.81	465	183	-			
	3.3	- 17	184.07	430	168	-			
	3.9	- 20	158.14	370	145	-	R 67	VU/VZ 01 DT 71D4	50 232
	4.5	- 23	137.67	320	126	-	RF 67	VU/VZ 01 DT 71D4	54 233
	4.8	- 24	128.97	300	118	-			
	3.3	- 17	186.89	435	171	-			
	3.6	- 18	172.17	405	158	-	R 57	VU/VZ 01 DT 71D4	44 230
	4.1	- 21	147.92	345	135	-	RF 57	VU/VZ 01 DT 71D4	47 -
	4.8	- 24	128.77	300	118	-			
	3.5	- 18	176.88	300	162	-			
	3.8	- 19	162.94	300	149	-			
	4.4	- 22	139.99	300	128	-			
	5.0	- 26	121.87	285	112	-	R 47	VU/VZ 01 DT 71D4	39 228
	5.4	- 27	114.17	265	104	-	RF 47	VU/VZ 01 DT 71D4	39 229
	6.1	- 31	100.86	235	92	-			
	6.5	- 33	93.68	220	86	-			
	4.5	- 23	134.82	200	123	-			
	5.0	- 25	123.66	200	113	-			
	5.8	- 30	105.28	200	96	-			
	6.8	- 35	90.77	200	83	-			
	7.2	- 37	84.61	198	77	-	R 37	VU/VZ 01 DT 71D4	34 226
	8.3	- 42	73.96	173	68	-	RF 37	VU/VZ 01 DT 71D4	36 227
	8.8	- 45	69.33	162	63	-			
	10	- 51	61.18	143	56	-			
	11	- 56	55.76	130	51	-			
	13	- 65	48.08	112	44	-			





R = 1:5 ... R = 1:6													
P _m /P _{a2} [kW]	n _{a1} [1/min]	n _{a2}	i	M _{a1} [Nm]	M _{a2} [Nm]						m [kg]		
0.37 / 0.30	4.5	- 23	135.09	130	124	-							
	4.9	- 25	123.91	130	113	-							
	5.8	- 30	105.49	130	97	-							
	6.7	- 34	90.96	130	83	-							
	7.2	- 37	84.78	130	78	-							
	8.3	- 42	74.11	130	68	-							
	8.8	- 45	69.47	130	64	-							
	10	- 51	61.30	130	56	-	R	27	VU/VZ	01 DT	71D4	31	224
	11	- 56	55.87	130	51	-	RF	27	VU/VZ	01 DT	71D4	31	225
	13	- 65	48.17	113	44	-							
	14	- 70	44.90	105	41	-							
	16	- 80	39.25	92	36	-							
	17	- 85	36.79	86	34	-							
	19	- 96	32.47	76	30	-							
	21	- 109	28.78	67	26	-							
	25	- 128	24.47	57	22	-							
	22	- 110	28.37	66	26	-							
	23	- 120	26.09	61	24	-							
	27	- 140	22.32	52	20	-							
	32	- 162	19.35	45	18	-							
	34	- 173	18.08	42	17	-							
	39	- 200	15.63	37	14	-							
	46	- 236	13.28*	31	12	-	R	27	VU/VZ	01 DT	71D4	30	224
	52	- 264	11.86	28	11	-	RF	27	VU/VZ	01 DT	71D4	31	225
	60	- 309	10.13	24	9.3	-							
	65	- 333	9.41	22	8.6	-							
	75	- 384	8.16	19	7.5	-							
	80	- 411	7.63*	18	7.0	-							
	93	- 475	6.59	15	6.0	-							
	109	- 559	5.60*	13	5.1	-							
	123	- 627	5.00*	12	4.6	-							
101	- 516	6.07	14	5.6	-		RX	67	VU/VZ	01 DT	71D4	37	214
118	- 605	5.18	12	4.7	-		RXF	67	VU/VZ	01 DT	71D4	41	215
135	- 692	4.53	11	4.1	-								
111	- 570	5.50*	13	5.0	-								
121	- 618	5.07	12	4.6	-								
141	- 720	4.35	10	4.0	-								
162	- 827	3.79	8.9	3.5	-								
173	- 882	3.55*	8.3	3.2	-								
195	- 998	3.14	7.3	2.9	-		RX	57	VU/VZ	01 DT	71D4	34	212
210	- 1075	2.91	6.8	2.7	-		RXF	57	VU/VZ	01 DT	71D4	36	213
232	- 1185	2.64*	6.2	2.4	-								
258	- 1320	2.37	5.5	2.2	-								
300	- 1535	2.04	4.8	1.9	-								
319	- 1630	1.92*	4.5	1.8	-								
371	- 1900	1.65	3.9	1.5	-								
0.55 / 0.42	0.13	- 0.78	4018	8000	5120	-							
	0.15	- 0.89	3514	8000	4480	-							
	0.16	- 0.94	3338	8000	4250	-							
	0.18	- 1.1	2929	8000	3730	-							
	0.21	- 1.3	2484	8000	3160	-							
	0.24	- 1.4	2242	8000	2860	-							
	0.29	- 1.7	1863	8000	2370	-	R	137 R77	VU/VZ	11 DT	80K4	295	-
	0.34	- 2.0	1586	7120	2020	-	RF	137 R77	VU/VZ	11 DT	80K4	315	-
	0.38	- 2.2	1391	6240	1770	-							
	0.42	- 2.5	1256	5640	1600	-							
	0.48	- 2.8	1105	4960	1410	-							
	0.51	- 3.0	1043	4680	1330	-							
	0.60	- 3.5	888	3990	1130	-							
	0.76	- 4.5	699	3140	890	-							




R = 1:5 ... R = 1:6													
P _m /P _{a2} [kW]	n _{a1} - n _{a2} [1/min]	i	M _{a1} [Nm]	M _{a2}								m [kg]	
0.55 / 0.42	0.94 - 5.5	564	2570	730	-								
	1.0 - 6.0	517	2360	670	-								
	1.2 - 6.9	453	2060	585	-	R	137 R77	VU/VZ	11 DT	80K4	290	-	
	1.4 - 8.3	376	1710	485	-	RF	137 R77	VU/VZ	11 DT	80K4	315	-	
	1.6 - 9.2	339	1540	440	-								
	1.8 - 11	297	1350	385	-								
	0.23 - 1.4	2280	4300	2900	-								
	0.26 - 1.5	2067	4300	2630	-								
	0.31 - 1.9	1693	4300	2160	-								
	0.34 - 2.0	1550	4300	1970	-								
	0.38 - 2.2	1407	4300	1790	-								
	0.44 - 2.6	1209	4300	1540	-	R	107 R77	VU/VZ	11 DT	80K4	215	-	
	0.50 - 3.0	1055	4300	1340	-	RF	107 R77	VU/VZ	11 DT	80K4	220	-	
	0.58 - 3.4	919	4120	1170	-								
	0.65 - 3.8	815	3660	1040	-								
	0.74 - 4.4	717	3220	910	-								
	0.85 - 5.0	626	2810	800	-								
	1.0 - 5.9	528	2370	675	-								
	1.1 - 6.7	469	2140	605	-								
	1.2 - 7.3	426	1940	550	-								
	1.4 - 8.3	377	1720	490	-								
	1.6 - 9.6	325	1480	420	-	R	107 R77	VU/VZ	11 DT	80K4	215	-	
	1.9 - 11	284	1290	365	-	RF	107 R77	VU/VZ	11 DT	80K4	220	-	
	2.1 - 12	256	1170	330	-								
	2.4 - 14	220	1000	285	-								
	3.1 - 18	172	785	220	-								
	0.34 - 2.0	1583	3000	2020	-								
	0.38 - 2.2	1396	3000	1780	-								
	0.43 - 2.6	1228	3000	1560	-								
	0.50 - 2.9	1069	3000	1360	-	R	97 R57	VU/VZ	11 DT	80K4	150	-	
	0.57 - 3.3	938	3000	1190	-	RF	97 R57	VU/VZ	11 DT	80K4	165	-	
	0.65 - 3.8	824	3000	1050	-								
	0.72 - 4.2	737	3000	940	-								
	0.84 - 5.0	632	2840	810	-								
	0.85 - 5.0	625	2850	810	-								
	0.97 - 5.7	549	2500	710	-								
	1.1 - 6.7	466	2120	605	-								
	1.3 - 7.5	420	1910	545	-	R	97 R57	VU/VZ	11 DT	80K4	145	-	
	1.4 - 8.4	370	1690	480	-	RF	97 R57	VU/VZ	11 DT	80K4	165	-	
	1.5 - 9.0	349	1590	450	-								
	1.8 - 11	297	1350	385	-								
	2.0 - 12	270	1230	350	-								
	2.4 - 14	227	1030	295	-								
	0.69 - 4.0	776	1550	990	-	R	87 R57	VU/VZ	11 DT	80K4	110	-	
	0.78 - 4.6	685	1550	870	-	RF	87 R57	VU/VZ	11 DT	80K4	115	-	
	0.89 - 5.2	599	1550	765	-								
	0.99 - 5.8	538	1550	695	-								
	1.1 - 6.6	472	1550	610	-								
	1.3 - 7.8	400	1550	515	-								
	1.5 - 8.7	361	1550	465	-	R	87 R57	VU/VZ	11 DT	80K4	110	-	
	1.8 - 10	300	1370	390	-	RF	87 R57	VU/VZ	11 DT	80K4	115	-	
	2.1 - 12	256	1170	330	-								
	2.3 - 13	232	1060	300	-								
	2.7 - 16	195	890	250	-								
	1.4 - 7.3	422	820	555	-								
	1.7 - 8.5	365	820	480	-								
	2.0 - 10	310	820	405	-								
	2.2 - 11	276	810	360	-	R	77 R37	VU/VZ	01 DT	80K4	67	-	
	2.6 - 13	236	695	310	-	RF	77 R37	VU/VZ	01 DT	80K4	72	-	
	2.8 - 14	221	650	290	-								
	3.3 - 17	186	550	245	-								





R = 1:5 ... R = 1:6																	
P _m /P _{a2} [kW]	n _{a1} [1/min]	-	n _{a2}	i	M _{a1} [Nm]	M _{a2} [Nm]										m [kg]	
0.55 / 0.42	2.0	-	10	310	600	405	-	R RF	67 R37 67 R37	VU/VZ VU/VZ	01 01	DT DT	80K4 80K4	62	-		
	2.3	-	12	264	600	345	-							65	-		
	2.6	-	13	235	600	310	-										
	3.0	-	15	201	590	265	-										
	3.4	-	17	181	535	235	-										
	3.8	-	19	159	470	210	-										
	2.8	-	14	220	450	290	-	R RF	57 R37 57 R37	VU/VZ VU/VZ	01 01	DT DT	80K4 80K4	55	-		
	3.2	-	16	188	450	245	-							59	-		
	3.8	-	19	159	450	210	-										
	4.2	-	21	146	430	191	-										
	4.6	-	23	134	395	176	-										
	4.0	-	20	154	300	200	-	R RF	47 R37 47 R37	VU/VZ VU/VZ	01 01	DT DT	80K4 80K4	50	-		
	4.7	-	24	129	300	169	-							51	-		
	5.6	-	28	109	300	143	-										
	6.2	-	32	98	290	128	-										
0.55 / 0.45	3.2	-	19	166.59	810	230	-	R RF	77 77	VU/VZ VU/VZ	11 11	DT DT	80K4 80K4	67	234		
	3.7	-	21	145.67	705	200	-							72	235		
	3.9	-	23	138.39	670	190	-										
	4.4	-	26	121.42	590	167	-										
	5.2	-	30	102.99	500	142	-										
	3.1	-	15	199.81	600	280	-	R RF	67 67	VU/VZ VU/VZ	01 01	DT DT	80K4 80K4	52	232		
	3.3	-	17	184.07	575	255	-							56	233		
	3.9	-	20	158.14	495	220	-										
	4.4	-	22	137.67	430	192	-										
	4.7	-	24	128.97	405	180	-										
	5.4	-	27	113.94	355	159	-	R RF	57 57	VU/VZ VU/VZ	01 01	DT DT	80K4 80K4	46	230		
	5.8	-	29	105.83	330	147	-							49	-		
	6.4	-	32	95.91	300	134	-										
	3.3	-	17	186.89	450	260	-										
	3.6	-	18	172.17	450	240	-										
	4.1	-	21	147.92	450	205	-	R RF	47 47	VU/VZ VU/VZ	01 01	DT DT	80K4 80K4	41	228		
	4.7	-	24	128.77	405	179	-							41	229		
	5.1	-	26	120.63	380	168	-										
	5.7	-	29	106.58	335	148	-										
	6.2	-	31	98.99	310	138	-										
	3.5	-	17	176.88	300	245	-	R RF	37 37	VU/VZ VU/VZ	01 01	DT DT	80K4 80K4				
	3.8	-	19	162.94	300	225	-										
	4.4	-	22	139.99	300	195	-										
	5.0	-	25	121.87	300	170	-										
	5.4	-	27	114.17	300	159	-										
	6.0	-	31	100.86	300	140	-	R RF	37 37	VU/VZ VU/VZ	01 01	DT DT	80K4 80K4	36	226		
	6.5	-	33	93.68	295	130	-							38	227		
	7.2	-	36	84.90	265	118	-										
	8.0	-	41	76.23	240	106	-										
	8.9	-	45	68.54	215	95	-										
	9.5	-	48	64.21	200	89	-	R RF	37 37	VU/VZ VU/VZ	01 01	DT DT	80K4 80K4				
	11	-	54	56.73	178	79	-										
	4.5	-	23	134.82	200	188	-										
	4.9	-	25	123.66	200	172	-										
	5.8	-	29	105.28	200	147	-										
	6.7	-	34	90.77	200	126	-	R RF	37 37	VU/VZ VU/VZ	01 01	DT DT	80K4 80K4				
	7.2	-	36	84.61	200	118	-										
	8.2	-	42	73.96	200	103	-										
	8.8	-	45	69.33	200	97	-										
	10	-	50	61.18	191	85	-										
	11	-	55	55.76	175	78	-	R RF	37 37	VU/VZ VU/VZ	01 01	DT DT	80K4 80K4				
	13	-	64	48.08	150	67	-										
	14	-	69	44.81	140	62	-										




R = 1:5 ... R = 1:6									
P_m/P_{a2} [kW]	n_{a1} [1/min]	-	n_{a2}	i	M_{a1} [Nm]	M_{a2} [Nm]			m [kg]
0.55 / 0.45	6.7	-	34	90.96	130	127	-		
	7.2	-	36	84.78	130	118	-		
	8.2	-	42	74.11	130	103	-		
	8.8	-	44	69.47	130	97	-		
	10	-	50	61.30	130	85	-		
	11	-	55	55.87	130	78	-		
	13	-	64	48.17	130	67	-	R	27
	14	-	69	44.90	130	63	-	RF	27
	16	-	79	39.25	123	55	-	VU/VZ	01 DT 80K4
	17	-	84	36.79	115	51	-	VU/VZ	01 DT 80K4
	19	-	95	32.47	102	45	-		32 224
	21	-	107	28.78	90	40	-		32 225
	25	-	126	24.47	77	34	-		
	22	-	109	28.37	89	40	-		
	23	-	118	26.09	82	36	-		
	27	-	138	22.32	70	31	-		
	32	-	160	19.35	61	27	-		
	34	-	171	18.08	57	25	-		
	39	-	198	15.63	49	22	-		
	46	-	232	13.28*	42	19	-	R	27
	51	-	260	11.86	37	17	-	RF	27
	60	-	305	10.13	32	14	-	VU/VZ	01 DT 80K4
	65	-	328	9.41	29	13	-	VU/VZ	01 DT 80K4
	75	-	378	8.16	26	11	-		31 224
	80	-	405	7.63*	24	11	-		32 225
	93	-	468	6.59	21	9.2	-		
	109	-	551	5.60*	18	7.8	-		
	122	-	617	5.00*	16	7.0	-		
	101	-	509	6.07	19	8.4	-	RX	67
	118	-	596	5.18	16	7.2	-	RXF	67
	135	-	682	4.53	14	6.3	-	VU/VZ	01 DT 80K4
								VU/VZ	01 DT 80K4
	111	-	561	5.50*	17	7.7	-		39 214
	120	-	609	5.07	16	7.1	-		43 215
	140	-	710	4.35	14	6.1	-		
	161	-	815	3.79	12	5.3	-		
	172	-	870	3.55*	11	4.9	-		
	194	-	983	3.14	9.8	4.4	-	RX	57
	210	-	1060	2.91	9.1	4.1	-	RXF	57
	231	-	1170	2.64*	8.3	3.7	-	VU/VZ	01 DT 80K4
	258	-	1305	2.37	7.4	3.3	-	VU/VZ	01 DT 80K4
	299	-	1515	2.04	6.4	2.8	-		36 212
	318	-	1610	1.92*	6.0	2.7	-		38 213
	370	-	1870	1.65	5.2	2.3	-		
0.75 / 0.58	0.11	-	0.64	4926	13000	8390	-		
	0.12	-	0.73	4325	13000	7370	-	R	147 R77
	0.14	-	0.85	3754	13000	6400	-	RF	147 R77
	0.16	-	0.96	3302	13000	5630	-	VU/VZ	11 DT 80N4
	0.18	-	1.1	2898	12800	4940	-	VU/VZ	11 DT 80N4
	0.21	-	1.2	2555	11400	4420	-		430 -
	0.24	-	1.4	2211	9890	3820	-		440 -
	0.27	-	1.6	1951	8730	3370	-		
	0.31	-	1.9	1705	7630	2950	-		
	0.35	-	2.1	1536	6870	2660	-		
	0.40	-	2.4	1329	5940	2300	-	R	147 R77
	0.46	-	2.7	1166	5220	2020	-	RF	147 R77
	0.60	-	3.6	889	3980	1540	-	VU/VZ	11 DT 80N4
	0.86	-	5.1	619	2770	1070	-	VU/VZ	11 DT 80N4
	0.96	-	5.7	558	2500	970	-		430 -
	1.1	-	6.5	489	2190	850	-		435 -
	1.3	-	7.7	415	1860	720	-		





R = 1:5 ... R = 1:6														
P _m /P _{a2} [kW]	n _{a1} - n _{a2} [1/min]	i	M _{a1} [Nm]	M _{a2}								m [kg]		
0.75 / 0.58	0.13 - 0.79	4018	8000	6950	-									
	0.15 - 0.90	3514	8000	6080	-									
	0.16 - 0.95	3338	8000	5770	-									
	0.18 - 1.1	2929	8000	5070	-									
	0.22 - 1.3	2484	8000	4300	-									
	0.24 - 1.4	2242	8000	3880	-									
	0.29 - 1.7	1863	8000	3220	-	R	137 R77	VU/VZ	11	DT	80N4	295	-	
	0.34 - 2.0	1586	7090	2740	-	RF	137 R77	VU/VZ	11	DT	80N4	315	-	
	0.38 - 2.3	1391	6220	2410	-									
	0.43 - 2.5	1256	5620	2170	-									
	0.48 - 2.9	1105	4940	1910	-									
	0.51 - 3.0	1043	4670	1800	-									
	0.60 - 3.6	888	3970	1540	-									
	0.76 - 4.5	699	3130	1210	-									
	0.95 - 5.6	564	2560	990	-									
	1.0 - 6.1	517	2350	910	-									
	1.2 - 7.0	453	2060	795	-	R	137 R77	VU/VZ	11	DT	80N4	295	-	
	1.4 - 8.4	376	1710	660	-	RF	137 R77	VU/VZ	11	DT	80N4	315	-	
	1.6 - 9.4	339	1540	595	-									
	1.8 - 11	297	1350	520	-									
	0.33 - 2.0	1599	4300	2770	-									
	0.38 - 2.3	1400	4300	2420	-									
	0.44 - 2.6	1226	4300	2120	-	R	107 R77	VU/VZ	11	DT	80N4	220	-	
	0.48 - 2.9	1104	4300	1910	-	RF	107 R77	VU/VZ	11	DT	80N4	225	-	
	0.57 - 3.4	939	4200	1620	-									
	0.65 - 3.9	822	3680	1420	-									
	1.1 - 6.8	469	2130	820	-									
	1.2 - 7.5	426	1930	750	-									
	1.4 - 8.4	377	1710	660	-									
	1.6 - 9.8	325	1480	570	-	R	107 R77	VU/VZ	11	DT	80N4	215	-	
	1.9 - 11	284	1290	500	-	RF	107 R77	VU/VZ	11	DT	80N4	220	-	
	2.1 - 12	256	1160	450	-									
	2.4 - 14	220	1000	385	-									
	3.1 - 18	172	780	300	-									
	0.50 - 3.0	1069	3000	1850	-									
	0.57 - 3.4	938	3000	1620	-									
	0.65 - 3.9	824	3000	1430	-	R	97 R57	VU/VZ	11	DT	80N4	150	-	
	0.73 - 4.3	737	3000	1270	-	RF	97 R57	VU/VZ	11	DT	80N4	165	-	
	0.85 - 5.0	632	2830	1090	-									
	0.86 - 5.1	625	2840	1100	-									
	0.97 - 5.8	549	2490	960	-									
	1.2 - 6.8	466	2120	820	-									
	1.3 - 7.6	420	1910	740	-									
	1.4 - 8.6	370	1680	650	-	R	97 R57	VU/VZ	11	DT	80N4	145	-	
	1.5 - 9.1	349	1580	615	-	RF	97 R57	VU/VZ	11	DT	80N4	165	-	
	1.8 - 11	297	1350	520	-									
	2.0 - 12	270	1230	475	-									
	2.4 - 14	227	1030	400	-									
	0.99 - 5.9	538	1550	940	-									
	1.1 - 6.7	472	1550	830	-									
	1.3 - 7.9	400	1550	700	-									
	1.5 - 8.8	361	1550	635	-	R	87 R57	VU/VZ	11	DT	80N4	110	-	
	1.8 - 11	300	1360	525	-	RF	87 R57	VU/VZ	11	DT	80N4	115	-	
	2.1 - 12	256	1160	450	-									
	2.3 - 14	232	1050	405	-									
	2.7 - 16	195	890	340	-									
	2.0 - 10	310	820	550	-									
	2.2 - 11	276	810	490	-									
	2.6 - 13	236	695	420	-	R	77 R37	VU/VZ	01	DT	80N4	68	-	
	2.8 - 14	221	650	395	-	RF	77 R37	VU/VZ	01	DT	80N4	73	-	
	3.3 - 17	186	545	330	-									




R = 1:5 ... R = 1:6													
P_m/P_{a2} [kW]	n_{a1} [1/min]	-	n_{a2}	i	M_{a1} [Nm]	M_{a2} [Nm]							
												m [kg]	
0.75 / 0.58	2.6	-	13	235	600	420	-	R RF	67 R37 67 R37	VU/VZ VU/VZ	01 01	DT DT	80N4 80N4
	3.1	-	16	201	590	360	-						
	3.4	-	17	181	530	320	-						
	3.9	-	20	159	465	285	-						
0.75 / 0.62	3.2	-	19	166.59	800	310	-	R RF	77 77	VU/VZ VU/VZ	11 11	DT DT	80N4 80N4
	3.7	-	22	145.67	705	270	-						
	3.9	-	23	138.39	670	260	-						
	4.4	-	26	121.42	585	225	-						
	5.2	-	31	102.99	495	192	-	R RF	67 67	VU/VZ VU/VZ	01 01	DT DT	80N4 80N4
	3.1	-	16	199.81	600	380	-						
	3.3	-	17	184.07	575	350	-						
	3.9	-	20	158.14	495	300	-						
	4.5	-	23	137.67	430	260	-	R RF	57 57	VU/VZ VU/VZ	01 01	DT DT	80N4 80N4
	4.8	-	24	128.97	400	245	-						
	3.3	-	17	186.89	450	355	-						
	3.6	-	18	172.17	450	325	-						
	4.1	-	21	147.92	450	280	-	R RF	47 47	VU/VZ VU/VZ	01 01	DT DT	80N4 80N4
	4.8	-	24	128.77	400	245	-						
	5.1	-	26	120.63	375	230	-						
	5.8	-	29	106.58	330	200	-						
	6.2	-	32	98.99	310	187	-	R RF	47 47	VU/VZ VU/VZ	01 01	DT DT	80N4 80N4
	4.4	-	22	139.99	300	265	-						
	5.0	-	26	121.87	300	230	-						
	5.4	-	27	114.17	300	215	-						
	6.1	-	31	100.86	300	191	-	R RF	47 47	VU/VZ VU/VZ	01 01	DT DT	80N4 80N4
	6.5	-	33	93.68	290	177	-						
	7.2	-	37	84.90	265	161	-						
	8.0	-	41	76.23	240	144	-						
	8.9	-	46	68.54	215	130	-	R RF	37 37	VU/VZ VU/VZ	01 01	DT DT	80N4 80N4
	9.5	-	49	64.21	200	121	-						
	5.8	-	30	105.28	200	199	-						
	6.8	-	35	90.77	200	172	-						
	7.2	-	37	84.61	200	160	-	R RF	37 37	VU/VZ VU/VZ	01 01	DT DT	80N4 80N4
	8.3	-	42	73.96	200	140	-						
	8.8	-	45	69.33	200	131	-						
	10	-	51	61.18	191	116	-						
	11	-	56	55.76	174	105	-	R RF	27 27	VU/VZ VU/VZ	01 01	DT DT	80N4 80N4
	13	-	65	48.08	150	91	-						
	14	-	70	44.81	140	85	-						
	10	-	51	61.30	130	116	-						
	11	-	56	55.87	130	106	-	R RF	27 27	VU/VZ VU/VZ	01 01	DT DT	80N4 80N4
	13	-	65	48.17	130	91	-						
	14	-	70	44.90	130	85	-						
	16	-	80	39.25	122	74	-						
	17	-	85	36.79	115	70	-	R RF	27 27	VU/VZ VU/VZ	01 01	DT DT	80N4 80N4
	19	-	96	32.47	101	61	-						
	21	-	109	28.78	90	54	-						
	25	-	128	24.47	76	46	-						
	22	-	110	28.37	89	54	-	R RF	27 27	VU/VZ VU/VZ	01 01	DT DT	80N4 80N4
	23	-	120	26.09	81	49	-						
	27	-	140	22.32	70	42	-						
	32	-	162	19.35	60	37	-						
	34	-	173	18.08	56	34	-	R RF	27 27	VU/VZ VU/VZ	01 01	DT DT	80N4 80N4
	39	-	200	15.63	49	30	-						
	46	-	236	13.28*	41	25	-						
	52	-	264	11.86	37	22	-						
	60	-	309	10.13	32	19	-	R RF	27 27	VU/VZ VU/VZ	01 01	DT DT	80N4 80N4
	65	-	333	9.41	29	18	-						
	75	-	384	8.16	25	15	-						
	80	-	411	7.63*	24	14	-						
	93	-	475	6.59	21	13	-	R RF	27 27	VU/VZ VU/VZ	01 01	DT DT	80N4 80N4
	109	-	559	5.60*	18	11	-						
	123	-	627	5.00*	16	9.5	-						





R = 1:5 ... R = 1:6																
P _m /P _{a2} [kW]	n _{a1} [1/min]	-	n _{a2}	i	M _{a1} [Nm]	M _{a2}								m [kg]		
0.75 / 0.62	101	-	516	6.07	19	12	-	RX RXF	67 67	VU/VZ VU/VZ	01 01	DT DT	80N4 80N4	40 44	214 215	
	118	-	605	5.18	16	9.8	-									
	135	-	692	4.53	14	8.6	-									
	111	-	570	5.50*	17	10	-	RX RXF	57 57	VU/VZ VU/VZ	01 01	DT DT	80N4 80N4	37 39	212 213	
	121	-	618	5.07	16	9.6	-									
	141	-	720	4.35	14	8.2	-									
	162	-	827	3.79	12	7.2	-									
	173	-	882	3.55*	11	6.7	-									
	195	-	998	3.14	9.8	5.9	-									
	210	-	1075	2.91	9.1	5.5	-									
	232	-	1185	2.64*	8.2	5.0	-									
	258	-	1320	2.37	7.4	4.5	-									
	300	-	1535	2.04	6.4	3.9	-									
	319	-	1630	1.92*	6.0	3.6	-									
	371	-	1900	1.65	5.1	3.1	-									
	1.1 / 0.84	0.14	-	0.86	3754	13000	9150	-	R RF	147 R77 147 R77	VU/VZ VU/VZ	11 11	DT DT	90S4 90S4	435 445	- -
		0.16	-	0.98	3302	13000	8050	-								
		0.19	-	1.1	2898	13000	7060	-								
0.21		-	1.3	2555	13000	6320	-	R RF	147 R77 147 R77	VU/VZ VU/VZ	11 11	DT DT	90S4 90S4	435 440	- -	
0.24		-	1.5	2211	12800	5470	-									
0.27		-	1.7	1951	11300	4830	-									
0.31		-	1.9	1705	9850	4220	-									
0.35		-	2.1	1536	8880	3800	-									
0.40		-	2.4	1329	7680	3290	-									
0.46		-	2.8	1166	6740	2890	-									
0.60		-	3.6	889	5140	2200	-									
0.87		-	5.2	619	3580	1530	-									
0.96		-	5.8	558	3220	1380	-									
1.1		-	6.6	489	2830	1210	-									
1.3		-	7.8	415	2400	1030	-									
0.26		-	1.6	2073	8000	5130	-	R RF	137 R77 137 R77	VU/VZ VU/VZ	11 11	DT DT	90S4 90S4	310 330	- -	
0.29		-	1.8	1839	8000	4550	-									
0.34		-	2.0	1598	8000	3960	-									
0.38		-	2.3	1397	8000	3460	-									
0.44		-	2.6	1226	7080	3030	-									
0.49		-	3.0	1090	6300	2700	-									
0.56		-	3.4	951	5500	2350	-									
0.65		-	3.9	831	4800	2060	-									
0.73		-	4.4	730	4220	1810	-									
0.96		-	5.8	560	3240	1390	-									
1.4		-	8.4	381	2200	940	-									
0.38		-	2.3	1400	4300	3470	-	R RF	107 R77 107 R77	VU/VZ VU/VZ	11 11	DT DT	90S4 90S4	225 230	- -	
0.44		-	2.6	1226	4300	3030	-									
0.49		-	2.9	1104	4300	2730	-									
0.57		-	3.4	939	4300	2320	-									
0.65		-	3.9	822	4300	2030	-									
1.4		-	8.7	369	2130	910	-									
1.1		-	6.9	469	2750	1180	-	R RF	107 R77 107 R77	VU/VZ VU/VZ	11 11	DT DT	90S4 90S4	220 225	- -	
1.3		-	7.6	426	2500	1070	-									
1.4		-	8.5	377	2210	950	-									
1.7		-	9.9	325	1910	820	-									
1.9		-	11	284	1670	715	-									
2.1		-	13	256	1500	645	-									
2.4		-	15	220	1290	555	-									
3.1		-	19	172	1010	430	-									
0.65		-	3.9	824	3000	2040	-	R RF	97 R57 97 R57	VU/VZ VU/VZ	11 11	DT DT	90S4 90S4	155 170	- -	
0.73		-	4.4	737	3000	1820	-									
0.85		-	5.1	632	3000	1560	-									





R = 1:5 ... R = 1:6																
P _m /P _{a2} [kW]	n _{a1} [1/min]	-	n _{a2}	i	M _{a1} [Nm]	M _{a2}								m [kg]		
1.1 / 0.84	0.86	-	5.2	625	3000	1570	-	R RF	97 R57 97 R57	VU/VZ VU/VZ	11 11	DT DT	90S4 90S4	150	-	
	0.98	-	5.9	549	3000	1380	-							-		
	1.2	-	6.9	466	2730	1170	-							-		
	1.3	-	7.7	420	2460	1060	-							-		
	1.4	-	8.7	370	2170	930	-							-		
	1.5	-	9.2	349	2050	880	-							-		
	1.8	-	11	297	1740	745	-							-		
	2.0	-	12	270	1580	680	-							-		
	2.4	-	14	227	1330	570	-							-		
	1.3	-	8.1	400	1550	1010	-	R RF	87 R57 87 R57	VU/VZ VU/VZ	11 11	DT DT	90S4 90S4	115	-	
	1.5	-	8.9	361	1550	910	-							-		
	1.8	-	11	300	1550	755	-							-		
	2.1	-	13	256	1500	645	-							-		
	2.3	-	14	232	1360	585	-							-		
	2.8	-	17	195	1140	490	-							-		
	1.1 / 0.90	2.4	-	14	216.54	1550	600	-	R RF	87 87	VU/VZ VU/VZ	21 21	DT DT	90S4 90S4	120	236
		2.5	-	15	205.71	1550	570	-							-	
		2.8	-	17	181.77	1550	505	-							-	
3.3		-	20	155.34	1550	430	-	-								
3.6		-	22	142.41	1440	395	-	-								
4.1		-	25	124.97	1270	345	-	-								
4.3		-	26	118.43*	1200	330	-	R RF	77 77	VU/VZ VU/VZ	11 11	DT DT	90S4 90S4	73	234	
3.2		-	19	166.59	820	445	-							-		
3.7		-	22	145.67	820	390	-							-		
3.9		-	23	138.39	820	370	-							-		
4.4		-	27	121.42	755	325	-							-		
5.2		-	31	102.99	640	275	-							-		
3.4		-	20	158.14	600	420	-	R RF	67 67	VU/VZ VU/VZ	11 11	DT DT	90S4 90S4	65	232	
3.9		-	23	137.67	600	370	-							-		
4.2		-	25	128.97	600	345	-							-		
4.7		-	28	113.94	600	305	-							-		
5.1		-	30	105.83	600	285	-							-		
5.6		-	34	95.91	600	255	-							-		
6.2		-	37	86.11	535	230	-							-		
3.6		-	22	147.92	450	395	-							R RF	57 57	VU/VZ VU/VZ
4.2		-	25	128.77	450	345	-	-								
4.5		-	27	120.63	450	320	-	-								
5.0		-	30	106.58	450	285	-	-								
5.4		-	33	98.99	450	265	-	-								
6.0		-	36	89.71	450	240	-	-								
6.7		-	40	80.55	450	215	-	-								
7.8		-	47	69.23	430	185	-	-								
8.3		-	50	64.85	405	173	-	-								
9.4		-	56	57.29	355	153	-	-								
10		-	61	53.22	330	142	-	-								
11		-	67	48.23	300	129	-	-								
5.3		-	32	100.86	300	270	-	R RF	47 47	VU/VZ VU/VZ	11 11	DT DT	90S4 90S4	53	228	
5.7		-	34	93.68	300	250	-							-		
6.3		-	38	84.90	300	225	-							-		
7.0		-	42	76.23	300	205	-							-		
7.8		-	47	68.54	300	183	-							-		
8.3		-	50	64.21	300	171	-							-		
9.5		-	57	56.73	300	151	-							-		
10		-	61	52.69	300	141	-							-		
11		-	67	47.75	300	128	-							-		
13		-	75	42.87	265	114	-							-		
15		-	87	36.93	230	99	-							-		
15		-	93	34.73	215	93	-	-								





R = 1:5 ... R = 1:6																							
P _m /P _{a2} [kW]	n _{a1} [1/min]	-	n _{a2}	i	M _{a1} [Nm]	M _{a2}							m [kg]										
1.1 / 0.90	7.2	-	44	73.96	200	197	-	R RF	37 37	VU/VZ VU/VZ	11 11	DT DT	90S4 90S4	51 52	226 227								
	7.7	-	46	69.33	200	185	-																
	8.8	-	53	61.18	200	163	-																
	9.6	-	58	55.76	200	149	-																
	11	-	67	48.08	200	128	-																
	12	-	72	44.81	200	120	-																
	14	-	82	39.17	200	105	-																
	15	-	88	36.72	200	98	-																
	17	-	99	32.40	200	87	-																
	19	-	112	28.73	179	77	-																
	22	-	132	24.42	152	65	-																
	24	-	145	22.27	139	59	-	R RF	37 37	VU/VZ VU/VZ	11 11	DT DT	90S4 90S4	50 52	226 227								
	28	-	167	19.31	120	52	-																
	30	-	178	18.05	113	48	-																
	34	-	206	15.60	97	42	-																
	40	-	243	13.25	83	35	-																
	45	-	272	11.83	74	32	-																
	53	-	319	10.11	63	27	-																
	57	-	340	9.47	59	25	-																
	67	-	404	7.97	50	21	-																
	80	-	483	6.67	42	18	-																
	95	-	568	5.67	35	15	-																
	106	-	636	5.06	32	14	-																
	104	-	622	5.18	32	14	-	RX RXF	67 67	VU/VZ VU/VZ	11 11	DT DT	90S4 90S4	51 55	214 215								
	118	-	711	4.53	28	12	-																
	125	-	749	4.30*	27	12	-																
	123	-	740	4.35	27	12	-	RX RXF	57 57	VU/VZ VU/VZ	11 11	DT DT	90S4 90S4	48 50	212 213								
	142	-	850	3.79	24	10	-																
	151	-	907	3.55*	22	9.5	-																
	171	-	1025	3.14	20	8.4	-																
	184	-	1105	2.91	18	7.8	-																
	203	-	1220	2.64*	17	7.0	-																
	226	-	1360	2.37	15	6.3	-																
	263	-	1580	2.04	13	5.4	-																
	279	-	1675	1.92*	12	5.1	-																
	325	-	1950	1.65	10	4.4	-																
	362	-	2175	1.48	9.2	4.0	-																
	413	-	2475	1.30	8.1	3.5	-																
1.5 / 1.2	0.21	-	1.3	2555	13000	8580	-									R RF	147 R77 147 R77	VU/VZ VU/VZ	11 11	DT DT	90L4 90L4	435 445	- -
	0.24	-	1.5	2211	12800	7430	-																
	0.28	-	1.7	1951	11300	6550	-																
	0.32	-	1.9	1705	9840	5730	-																
	0.35	-	2.1	1536	8860	5160	-																
	0.40	-	2.4	1329	7670	4460	-																
	0.46	-	2.8	1166	6730	3920	-																
	0.60	-	3.6	889	5130	2990	-																
	0.34	-	2.0	1598	8000	5370	-	R RF	137 R77 137 R77	VU/VZ VU/VZ	11 11	DT DT	90L4 90L4	310 335	- -								
	0.38	-	2.3	1397	8000	4690	-																
	0.44	-	2.6	1226	7070	4120	-																
	0.49	-	3.0	1090	6290	3660	-																
	0.56	-	3.4	951	5490	3190	-																
	0.65	-	3.9	831	4790	2790	-																
	0.74	-	4.4	730	4210	2450	-																
	0.96	-	5.8	560	3230	1880	-																
	1.4	-	8.5	381	2200	1280	-																
	0.57	-	3.5	939	4300	3150	-									R RF	107 R77 107 R77	VU/VZ VU/VZ	11 11	DT DT	90L4 90L4	230 235	- -
	0.65	-	4.0	822	4300	2760	-																
1.5	-	8.8	369	2130	1240	-																	
1.7	-	10	323	1860	1080	-																	




R = 1:5 ... R = 1:6																
P _m /P _{a2} [kW]	n _{a1} [1/min]	-	n _{a2}	i	M _{a1} [Nm]	M _{a2} [Nm]									m [kg]	
1.5 / 1.2	1.2	-	6.9	469	2750	1600	-	R RF	107 R77 107 R77	VU/VZ VU/VZ	11 DT 11 DT	90L4 90L4	220 230	-		
	1.3	-	7.6	426	2490	1450	-									
	1.4	-	8.6	377	2210	1290	-									
	1.7	-	10	325	1900	1110	-									
	1.9	-	11	284	1660	970	-									
	2.1	-	13	256	1500	870	-									
	2.4	-	15	220	1290	750	-									
	3.1	-	19	172	1010	585	-									
	0.98	-	5.9	549	3000	1870	-	R RF	97 R57 97 R57	VU/VZ VU/VZ	11 DT 11 DT	90L4 90L4	155 170	-		
	1.2	-	7.0	466	2730	1590	-									
	1.3	-	7.7	420	2460	1430	-									
	1.4	-	8.8	370	2170	1260	-									
	1.5	-	9.3	349	2040	1190	-									
	1.8	-	11	297	1740	1010	-									
	2.0	-	12	270	1580	920	-									
	2.4	-	14	227	1330	775	-									
	1.8	-	11	300	1550	1020	-	R RF	87 R57 87 R57	VU/VZ VU/VZ	11 DT 11 DT	90L4 90L4	115 125	-		
	2.1	-	13	256	1500	870	-									
	2.3	-	14	232	1360	790	-									
	2.8	-	17	195	1140	665	-									
	1.5 / 1.2	2.4	-	14	216.54	1550	820	-	R RF	87 87	VU/VZ VU/VZ	21 DT 21 DT	90L4 90L4	120 130	236 237	
2.5		-	15	205.71	1550	775	-									
2.8		-	17	181.77	1550	685	-									
3.3		-	20	155.34	1550	585	-									
3.6		-	22	142.41	1440	535	-									
4.1		-	25	124.97	1270	470	-									
4.3		-	26	118.43*	1200	445	-									
3.2		-	19	166.59	820	605	-	R RF	77 77	VU/VZ VU/VZ	11 DT 11 DT	90L4 90L4	75 80	234 235		
3.7		-	22	145.67	820	530	-									
3.9		-	23	138.39	820	500	-									
4.4		-	27	121.42	755	440	-									
5.2		-	31	102.99	640	375	-									
5.8		-	35	92.97	580	335	-									
3.4		-	21	158.14	600	575	-								R RF	67 67
3.9		-	24	137.67	600	500	-									
4.2		-	25	128.97	600	465	-									
4.7		-	28	113.94	600	415	-									
5.1		-	31	105.83	600	385	-									
5.6		-	34	95.91	595	345	-									
6.2		-	38	86.11	535	310	-									
4.5		-	27	120.63	450	435	-	R RF	57 57	VU/VZ VU/VZ	11 DT 11 DT	90L4 90L4	60 63	230 231		
5.0		-	30	106.58	450	385	-									
5.4		-	33	98.99	450	360	-									
6.0		-	36	89.71	450	325	-									
6.7		-	40	80.55	450	290	-									
7.8		-	47	69.23	430	250	-									
8.3		-	50	64.85	405	235	-									
9.4		-	57	57.29	355	210	-									
10		-	61	53.22	330	193	-									
11		-	67	48.23	300	175	-									
7.0		-	43	76.23	300	275	-	R RF	47 47	VU/VZ VU/VZ	11 DT 11 DT	90L4 90L4	55 55	228 229		
7.8		-	47	68.54	300	250	-									
8.4		-	51	64.21	300	235	-									
9.5	-	57	56.73	300	205	-										
10	-	62	52.69	300	191	-										
11	-	68	47.75	295	173	-										
13	-	76	42.87	265	155	-										
15	-	88	36.93	230	134	-										
15	-	93	34.73	215	126	-										





R = 1:5 ... R = 1:6																
P _m /P _{a2} [kW]	n _{a1} [1/min]	-	n _{a2}	i	M _{a1} [Nm]	M _{a2} [Nm]									m [kg]	
1.5 / 1.2	11	-	67	48.08	200	174	-	R RF	37 37	VU/VZ VU/VZ	11 11	DT DT	90L4 90L4	53 54	226 227	
	12	-	72	44.81	200	162	-									
	14	-	83	39.17	200	142	-									
	15	-	88	36.72	200	133	-									
	17	-	100	32.40	200	117	-									
	19	-	113	28.73	179	104	-									
	22	-	133	24.42	152	89	-	R RF	37 37	VU/VZ VU/VZ	11 11	DT DT	90L4 90L4	52 54	226 227	
	24	-	146	22.27	139	81	-									
	28	-	168	19.31	120	70	-									
	30	-	180	18.05	112	65	-									
	34	-	208	15.60	97	57	-									
	41	-	245	13.25	82	48	-									
	45	-	274	11.83	74	43	-									
	53	-	321	10.11	63	37	-									
	57	-	342	9.47	59	34	-									
	67	-	407	7.97	50	29	-									
	81	-	486	6.67	42	24	-									
	95	-	572	5.67	35	21	-									
	106	-	641	5.06	32	18	-									
	104	-	626	5.18	32	19	-	RX RXF	67 67	VU/VZ VU/VZ	11 11	DT DT	90L4 90L4	53 57	214 215	
	119	-	716	4.53	28	16	-									
	125	-	754	4.30*	27	16	-									
	124	-	746	4.35	27	16	-	RX RXF	57 57	VU/VZ VU/VZ	11 11	DT DT	90L4 90L4	50 52	212 213	
	142	-	856	3.79	24	14	-									
	151	-	914	3.55*	22	13	-									
	171	-	1035	3.14	20	11	-									
	185	-	1115	2.91	18	11	-									
	204	-	1230	2.64*	16	9.6	-									
	227	-	1370	2.37	15	8.6	-									
	263	-	1590	2.04	13	7.4	-									
	280	-	1690	1.92*	12	7.0	-									
	326	-	1965	1.65	10	6.0	-									
	363	-	2190	1.48	9.2	5.4	-									
	413	-	2495	1.30	8.1	4.7	-									
2.2 / 1.7	0.30	-	1.8	1705	13000	8720	-	R RF	147 R77 147 R77	VU/VZ VU/VZ	21 21	DV DV	100M4 100M4	460 470	- -	
	0.33	-	2.0	1536	13000	7860	-									
	0.38	-	2.3	1329	13000	6800	-									
	0.44	-	2.7	1166	13000	5960	-									
	0.50	-	3.0	1029	12500	5260	-									
	0.57	-	3.5	889	10800	4550	-									
	0.65	-	4.0	784	9540	4010	-									
	0.73	-	4.5	695	8460	3550	-									
	0.82	-	5.0	619	7530	3170	-									
	0.91	-	5.6	558	6790	2850	-									
	1.0	-	6.4	489	5950	2500	-									
	1.2	-	7.5	415	5050	2120	-									
	0.47	-	2.9	1090	8000	5580	-	R RF	137 R77 137 R77	VU/VZ VU/VZ	21 21	DV DV	100M4 100M4	335 360	- -	
	0.54	-	3.3	951	8000	4860	-									
	0.61	-	3.8	831	8000	4250	-									
	0.70	-	4.3	730	8000	3730	-									
	0.81	-	5.0	629	7650	3220	-									
	0.91	-	5.6	560	6810	2860	-									
	1.0	-	6.4	490	5960	2510	-									
	1.2	-	7.3	428	5210	2190	-									
	1.3	-	8.2	381	4640	1950	-									
	1.6	-	9.7	323	3930	1650	-									
	1.8	-	11	291	3540	1490	-									
	2.0	-	12	255	3100	1300	-									
	2.3	-	14	223	2710	1140	-									
	2.6	-	16	197	2400	1010	-									
	2.9	-	18	175	2130	900	-									
	0.83	-	5.1	614	4300	3140	-	R RF	107 R77 107 R77	VU/VZ VU/VZ	21 21	DV DV	100M4 100M4	255 260	- -	
	0.94	-	5.7	544	4300	2780	-									
1.0	-	6.3	492	4300	2520	-										





R = 1:5 ... R = 1:6												
P_m/P_{a2} [kW]	n_{a1} [1/min]	-	n_{a2}	i	M_{a1} [Nm]	M_{a2} [Nm]						
											m [kg]	
2.2 / 1.7	1.1	-	6.6	469	4300	2440	-					
	1.2	-	7.3	426	4300	2210	-					
	1.4	-	8.3	377	4300	1960	-					
	1.6	-	9.6	325	4010	1690	-					
	1.8	-	11	284	3510	1470	-					
	2.0	-	12	256	3160	1330	-					
	2.3	-	14	220	2720	1140	-					
	2.6	-	16	193	2380	1000	-					
	3.0	-	18	172	2120	890	-					
	1.4	-	8.4	370	3000	1920	-					
	1.5	-	8.9	349	3000	1810	-					
	1.7	-	10	297	3000	1540	-					
	1.9	-	12	270	3000	1400	-					
	2.2	-	14	227	2800	1180	-					
2.2 / 1.8	2.4	-	14	216.54	1550	1190	-					
	2.5	-	15	205.71	1550	1130	-					
	2.8	-	17	181.77	1550	1000	-					
	3.3	-	20	155.34	1550	860	-					
	3.6	-	22	142.41	1550	785	-					
	4.1	-	25	124.97	1550	690	-					
	4.3	-	26	118.43*	1550	655	-					
	4.9	-	30	103.65	1360	570	-					
	3.5	-	21	145.67	820	800	-					
	3.7	-	23	138.39	820	765	-					
	4.2	-	26	121.42	820	670	-					
	5.0	-	30	102.99	820	570	-					
	5.5	-	34	92.97	820	515	-					
	6.2	-	38	81.80	820	450	-					
	6.6	-	40	77.24	820	425	-					
	7.8	-	47	65.77	820	365	-					
	8.8	-	54	57.68	755	320	-					
	4.8	-	29	105.83	600	585	-					
	5.3	-	32	95.91	600	530	-					
	5.9	-	36	86.11	600	475	-					
	6.9	-	42	74.17	600	410	-					
	7.3	-	45	69.75	600	385	-					
	8.3	-	51	61.26	600	340	-					
	9.0	-	55	56.89	600	315	-					
	9.9	-	60	51.56	600	285	-					
	6.3	-	39	80.55	450	445	-					
	7.4	-	45	69.23	450	380	-					
	7.9	-	48	64.85	450	360	-					
	8.9	-	54	57.29	450	315	-					
	9.6	-	59	53.22	450	295	-					
	11	-	65	48.23	450	265	-					
	12	-	72	43.30	450	240	-					
	14	-	84	37.30*	450	205	-					
	15	-	89	35.07	450	194	-					
	17	-	103	30.18	395	167	-					
	19	-	116	26.97	355	149	-					
	9.7	-	59	52.69	300	290	-					
	11	-	65	47.75	300	265	-					
	12	-	73	42.87	300	235	-					
	14	-	84	36.93	300	205	-					
	15	-	90	34.73	300	192	-					
	17	-	104	29.88	300	165	-					
	19	-	117	26.70	300	147	-					
	22	-	132	23.59	300	130	-					




R = 1:5 ... R = 1:6															
P _m /P _{a2} [kW]	n _{a1} [1/min]	-	n _{a2}	i	M _{a1} [Nm]	M _{a2}								m [kg]	
2.2 / 1.8	22	-	134	23.28	300	128	-	R RF	47 47	VU/VZ VU/VZ	21 21	DV DV	100M4 100M4	82 82	228 229
	23	-	143	21.81	285	120	-								
	26	-	162	19.27	255	106	-								
	28	-	174	17.89	235	99	-								
	31	-	192	16.22	215	90	-								
	35	-	214	14.56	191	80	-								
	41	-	248	12.54	165	69	-								
	43	-	264	11.79	155	65	-								
	50	-	307	10.15	133	56	-								
	56	-	344	9.07	119	50	-								
	64	-	389	8.01	105	44	-								
	66	-	402	7.76*	102	43	-								
	73	-	448	6.96	91	38	-								
	85	-	519	6.00	79	33	-								
	90	-	553	5.64*	74	31	-								
	105	-	642	4.85	64	27	-								
	117	-	718	4.34	57	24	-								
	133	-	814	3.83	50	21	-								
	90	-	553	5.63	74	31	-	RX RXF	77 77	VU/VZ VU/VZ	21 21	DV DV	100M4 100M4	92	216
	95	-	582	5.35*	70	30	-							94	217
	108	-	659	4.73	62	26	-								
	112	-	688	4.53	59	25	-	RX RXF	67 67	VU/VZ VU/VZ	21 21	DV DV	100M4 100M4	81	214
	118	-	725	4.30*	56	24	-							85	215
	135	-	827	3.77	50	21	-								
	134	-	822	3.79	50	21	-	RX RXF	57 57	VU/VZ VU/VZ	21 21	DV DV	100M4 100M4	78	212
	144	-	878	3.55*	47	20	-							80	213
	162	-	992	3.14	41	17	-								
	175	-	1070	2.91	38	16	-								
	193	-	1180	2.64*	35	15	-								
	215	-	1315	2.37	31	13	-								
	250	-	1530	2.04	27	11	-								
	265	-	1625	1.92*	25	11	-								
	309	-	1890	1.65	22	9.1	-								
	344	-	2105	1.48	19	8.2	-								
	392	-	2395	1.30	17	7.2	-								
3.0 / 2.3	0.44	-	2.6	1166	13000	8180	-	R RF	147 R77 147 R77	VU/VZ VU/VZ	21 21	DV DV	100L4 100L4	465	-
	0.49	-	3.0	1029	12500	7220	-							475	-
	0.57	-	3.5	889	10800	6230	-								
	0.65	-	4.0	784	9550	5500	-								
	0.73	-	4.5	695	8470	4870	-								
	0.82	-	5.0	619	7540	4340	-								
	0.91	-	5.5	558	6800	3910	-								
	1.0	-	6.3	489	5960	3430	-								
	1.2	-	7.5	415	5060	2910	-	R RF	137 R77 137 R77	VU/VZ VU/VZ	21 21	DV DV	100L4 100L4	340	-
	0.70	-	4.2	730	8000	5120	-							365	-
	0.81	-	4.9	629	7670	4410	-								
	0.91	-	5.5	560	6820	3930	-								
	1.0	-	6.3	490	5970	3440	-								
	1.2	-	7.2	428	5220	3000	-								
	1.3	-	8.1	381	4640	2670	-								
	1.6	-	9.6	323	3940	2260	-								
	1.8	-	11	291	3550	2040	-								
	2.0	-	12	255	3110	1790	-								
	2.3	-	14	223	2720	1560	-								
	2.6	-	16	197	2400	1380	-								
	2.9	-	18	175	2130	1230	-								
	1.2	-	7.3	426	4300	3030	-	R RF	107 R77 107 R77	VU/VZ VU/VZ	21 21	DV DV	100L4 100L4	255	-
	1.4	-	8.2	377	4300	2680	-							260	-
	1.6	-	9.5	325	4020	2310	-								
	1.8	-	11	284	3510	2020	-								
	2.0	-	12	256	3170	1820	-								
	2.3	-	14	220	2720	1570	-								
	2.6	-	16	193	2390	1370	-								
	3.0	-	18	172	2130	1220	-								



R = 1:5 ... R = 1:6															
P_m/P_{a2} [kW]	n_{a1} [1/min]	n_{a2}	i	M_{a1} [Nm]	M_{a2} [Nm]									m [kg]	
3.0 / 2.3	1.7	- 10	297	3000	2110	-	R RF	97 97	R57 R57	VU/VZ VU/VZ	21 21	DV DV	100L4 100L4	185	-
	1.9	- 11	270	3000	1920	-								205	-
	2.2	- 14	227	2810	1620	-									
3.0 / 2.5	3.3	- 20	155.34	1550	1170	-	R RF	87 87		VU/VZ VU/VZ	21 21	DV DV	100L4 100L4	130	236
	3.6	- 22	142.41	1550	1080	-								140	237
	4.1	- 25	124.97	1550	950	-									
	4.3	- 26	118.43*	1550	900	-									
	4.9	- 30	103.65	1360	785	-									
	5.5	- 33	93.38	1230	705	-									
	6.2	- 38	81.92	1080	620	-									
	7.0	- 43	72.57	950	550	-									
	4.9	- 30	102.99	820	780	-	R RF	77 77		VU/VZ VU/VZ	21 21	DV DV	100L4 100L4	105	234
	5.5	- 33	92.97	820	705	-								110	235
	6.2	- 38	81.80	820	620	-									
	6.6	- 40	77.24	820	585	-									
	7.7	- 47	65.77	820	495	-									
	8.8	- 54	57.68	760	435	-									
	9.8	- 59	52.07	685	395	-									
	11	- 68	45.81	600	345	-									
	12	- 72	43.26	570	325	-									
	6.9	- 42	74.17	600	560	-	R RF	67 67		VU/VZ VU/VZ	21 21	DV DV	100L4 100L4	98	232
	7.3	- 44	69.75	600	530	-								100	233
	8.3	- 51	61.26	600	465	-									
	8.9	- 54	56.89	600	430	-									
	9.9	- 60	51.56	600	390	-									
	11	- 67	46.29	600	350	-									
	8.9	- 54	57.29	450	435	-	R RF	57 57		VU/VZ VU/VZ	21 21	DV DV	100L4 100L4	92	230
	9.6	- 58	53.22	450	405	-								95	231
	11	- 64	48.23	450	365	-									
	12	- 71	43.30	450	325	-									
	14	- 83	37.30*	450	280	-									
	15	- 88	35.07	450	265	-									
	17	- 103	30.18	395	230	-									
	19	- 115	26.97	355	205	-									
	14	- 84	36.93	300	280	-	R RF	47 47		VU/VZ VU/VZ	21 21	DV DV	100L4 100L4	87	228
	15	- 89	34.73	300	265	-								87	229
	17	- 104	29.88	300	225	-									
	19	- 116	26.70	300	200	-									
	22	- 131	23.59	300	178	-									
	22	- 133	23.28	300	176	-	R RF	47 47		VU/VZ VU/VZ	21 21	DV DV	100L4 100L4	86	228
	23	- 142	21.81	285	165	-								86	229
	26	- 161	19.27	255	146	-									
	28	- 173	17.89	235	135	-									
	31	- 191	16.22	215	123	-									
	35	- 213	14.56	191	110	-									
	41	- 247	12.54	165	95	-									
	43	- 262	11.79	155	89	-									
	50	- 305	10.15	133	77	-									
	56	- 341	9.07	119	69	-									
	64	- 386	8.01	105	61	-									
	66	- 399	7.76*	102	59	-									
	73	- 445	6.96	92	53	-									
	85	- 516	6.00	79	45	-									
	90	- 549	5.64*	74	43	-									
	105	- 638	4.85	64	37	-									
	117	- 713	4.34	57	33	-									
	133	- 808	3.83	50	29	-									
	90	- 550	5.63	74	43	-	RX RXF	77 77		VU/VZ VU/VZ	21 21	DV DV	100L4 100L4	96	216
	95	- 578	5.35*	70	41	-								98	217
	108	- 654	4.73	62	36	-									
	112	- 683	4.53	60	34	-	RX RXF	67 67		VU/VZ VU/VZ	21 21	DV DV	100L4 100L4	85	214
	118	- 720	4.30*	57	33	-								89	215
	135	- 821	3.77	50	29	-									





R = 1:5 ... R = 1:6											
P_m/P_{a2} [kW]	n_{a1} [1/min]	-	n_{a2}	i	M_{a1} [Nm]	M_{a2}					
										m [kg]	
3.0 / 2.5	134	-	816	3.79	50	29	-	RX RXF	57 57	VU/VZ VU/VZ	21 21
	143	-	872	3.55*	47	27	-				
	162	-	985	3.14	41	24	-				
	175	-	1065	2.91	38	22	-				
	193	-	1170	2.64*	35	20	-				
	215	-	1305	2.37	31	18	-				
	249	-	1515	2.04	27	15	-				
	265	-	1610	1.92*	25	15	-				
	308	-	1875	1.65	22	13	-				
	344	-	2090	1.48	20	11	-				
	391	-	2380	1.30	17	9.8	-				
4.0 / 3.1	0.57	-	3.5	889	13000	8470	-	R RF	147 R77 147 R77	VU/VZ VU/VZ	31 31
	0.65	-	3.9	784	13000	7470	-				
	0.73	-	4.4	695	13000	6620	-				
	0.82	-	5.0	619	13000	5900	-				
	0.91	-	5.5	558	12100	5320	-				
	1.0	-	6.3	489	10600	4660	-				
	1.2	-	7.4	415	9000	3950	-	R RF	137 R77 137 R77	VU/VZ VU/VZ	31 31
	0.91	-	5.5	560	8000	5340	-				
	1.0	-	6.3	490	8000	4670	-				
	1.2	-	7.2	428	8000	4080	-				
	1.3	-	8.1	381	8000	3630	-				
	1.6	-	9.5	323	7010	3080	-				
	1.8	-	11	291	6310	2770	-				
	2.0	-	12	255	5530	2430	-				
	2.3	-	14	223	4840	2120	-				
	2.6	-	16	197	4270	1880	-				
	2.9	-	18	175	3800	1670	-				
	1.6	-	9.4	325	4300	3140	-	R RF	107 R77 107 R77	VU/VZ VU/VZ	31 31
	1.8	-	11	284	4300	2750	-				
	2.0	-	12	256	4300	2480	-				
	2.3	-	14	220	4300	2130	-				
	2.6	-	16	193	4250	1870	-				
	3.0	-	18	172	3790	1660	-				
4.0 / 3.3	2.7	-	16	186.30	3000	1910	-	R RF	97 97	VU/VZ VU/VZ	31 31
	3.0	-	18	170.02	3000	1750	-				
	3.4	-	20	150.78	3000	1550	-				
	4.0	-	24	126.75	2960	1300	-				
	4.4	-	26	116.48	2720	1200	-				
	4.9	-	30	103.44	2420	1060	-	R RF	87 87	VU/VZ VU/VZ	31 31
	4.9	-	30	103.65	1550	1070	-				
	5.5	-	33	93.38	1550	960	-				
	6.2	-	37	81.92	1550	840	-				
	7.0	-	42	72.57	1550	745	-				
	8.0	-	48	63.68*	1490	655	-				
	8.5	-	51	60.35*	1410	620	-				
	9.7	-	58	52.82	1240	545	-				
	11	-	64	47.58	1110	490	-				
	12	-	73	41.74	980	430	-				
	9.8	-	59	52.07	820	535	-	R RF	77 77	VU/VZ VU/VZ	31 31
	11	-	67	45.81	820	470	-				
	12	-	71	43.26	820	445	-				
	14	-	83	36.83	820	380	-				
	15	-	92	33.47	785	345	-				
	18	-	106	29.00	680	300	-				
	20	-	122	25.23	590	260	-				
	9.9	-	59	51.56	600	530	-	R RF	67 67	VU/VZ VU/VZ	31 31
	11	-	66	46.29	600	475	-				
	13	-	77	39.88*	580	410	-				
	12	-	71	43.30	450	445	-	R RF	57 57	VU/VZ VU/VZ	31 31
	14	-	82	37.30*	450	385	-				
	15	-	87	35.07	450	360	-				
	17	-	102	30.18	450	310	-				
	19	-	114	26.97	450	275	-				





R = 1:5 ... R = 1:6


P_m/P_{a2} [kW]	n_{a1} [1/min]	n_{a2}	i	M_{a1} [Nm]	M_{a2} [Nm]			m [kg]	
4.0 / 3.3	27	- 165	18.60*	435	191	-			
	30	- 183	16.79	395	173	-			
	35	- 208	14.77*	345	152	-			
	37	- 220	13.95*	325	143	-			
	43	- 258	11.88	280	122	-			
	47	- 284	10.79	250	111	-			
	55	- 328	9.35	220	96	-	R 57	VU/VZ 31 DV 112M4	125 230
	56	- 339	9.06	210	93	-	RF 57	VU/VZ 31 DV 112M4	130 231
	64	- 385	7.97	186	82	-			
	68	- 407	7.53	176	77	-			
	80	- 479	6.41	150	66	-			
	88	- 527	5.82	136	60	-			
	101	- 607	5.05	118	52	-			
	116	- 699	4.39	103	45	-			
	71	- 428	7.16*	168	74	-	RX 97	VU/VZ 31 DV 112M4	170 220
	78	- 468	6.56	153	67	-	RXF 97	VU/VZ 31 DV 112M4	180 221
	88	- 530	5.79	135	60	-			
	92	- 552	5.56*	130	57	-	RX 87	VU/VZ 31 DV 112M4	145 218
	101	- 605	5.07	119	52	-	RXF 87	VU/VZ 31 DV 112M4	150 219
	113	- 682	4.50*	105	46	-			
	126	- 759	4.04*	95	42	-			
	138	- 829	3.70	87	38	-			
	157	- 944	3.25*	76	33	-			
	166	- 996	3.08*	72	32	-			
	189	- 1135	2.70	63	28	-	RX 77	VU/VZ 31 DV 112M4	130 216
	210	- 1260	2.43	57	25	-	RXF 77	VU/VZ 31 DV 112M4	130 217
	240	- 1440	2.13	50	22	-			
	271	- 1630	1.88*	44	19	-			
	306	- 1835	1.67	39	17	-			
	359	- 2160	1.42	33	15	-			
5.5 / 4.2	0.51	- 3.1	999	18000	12900	-			
	0.59	- 3.6	861	18000	11100	-			
	0.67	- 4.1	760	16500	9800	-	R 167 R97	VU/VZ 31 DV 132S4	820 -
	0.78	- 4.7	656	14200	8460	-	RF 167 R97	VU/VZ 31 DV 132S4	830 -
	1.0	- 6.1	503	10900	6490	-			
	1.4	- 8.2	376	8140	4850	-			
	1.5	- 9.2	335	7250	4320	-			
	0.74	- 4.4	695	13000	8970	-			
	0.83	- 5.0	619	13000	7990	-	R 147 R77	VZ 31 DV 132S4	510 -
	0.92	- 5.5	558	12100	7200	-	RF 147 R77	VZ 31 DV 132S4	510 -
	1.1	- 6.3	489	10600	6310	-			
	1.2	- 7.4	415	8990	5350	-			
	1.2	- 7.2	428	8000	5520	-			
	1.3	- 8.1	381	8000	4920	-			
	1.6	- 9.6	323	6990	4170	-			
	1.8	- 11	291	6300	3750	-	R 137 R77	VZ 31 DV 132S4	380 -
	2.0	- 12	255	5520	3290	-	RF 137 R77	VZ 31 DV 132S4	405 -
	2.3	- 14	223	4830	2880	-			
	2.6	- 16	197	4270	2540	-			
	2.9	- 18	175	3790	2260	-			
	2.3	- 14	220	4300	2880	-	R 107 R77	VZ 31 DV 132S4	290 -
	2.6	- 16	193	4240	2530	-	RF 107 R77	VZ 31 DV 132S4	300 -
	3.0	- 18	172	3780	2250	-			
5.5 / 4.5	2.7	- 17	186.30	3000	2590	-			
	3.0	- 18	170.02	3000	2370	-			
	3.4	- 20	150.78	3000	2100	-			
	4.0	- 24	126.75	2960	1760	-	R 97	VU/VZ 31 DV 132S4	215 238
	4.4	- 27	116.48	2720	1620	-	RF 97	VU/VZ 31 DV 132S4	230 239
	4.9	- 30	103.44	2420	1440	-			
	5.5	- 33	92.48	2160	1290	-			
	6.2	- 37	83.15	1940	1160	-			





R = 1:5 ... R = 1:6																							
P _m /P _{a2} [kW]	n _{a1} [1/min]	-	n _{a2}	i	M _{a1} [Nm]	M _{a2}								m [kg]									
5.5 / 4.5	5.5	-	33	93.38	1550	1300	-	R RF	87 87	VU/VZ VU/VZ	31 31	DV DV	132S4 132S4	170 180	236 237								
	6.2	-	38	81.92	1550	1140	-																
	7.0	-	43	72.57	1550	1010	-																
	8.0	-	49	63.68*	1490	890	-																
	8.5	-	51	60.35*	1410	840	-																
	9.7	-	58	52.82	1230	735	-																
	11	-	65	47.58	1110	660	-																
	12	-	74	41.74	970	580	-	R RF	77 77	VU/VZ VU/VZ	31 31	DV DV	132S4 132S4	145 150	234 235								
	14	-	84	36.84*	860	515	-																
	11	-	67	45.81	820	635	-																
	12	-	71	43.26	820	600	-																
	14	-	84	36.83	820	510	-																
	15	-	92	33.47	780	465	-																
	18	-	107	29.00	675	405	-																
	20	-	122	25.23	590	350	-	R RF	67 67	VU/VZ VU/VZ	31 31	DV DV	132S4 132S4	140 145	232 233								
	13	-	77	39.88*	580	555	-																
	14	-	82	37.50	570	520	-																
	16	-	96	32.27	540	450	-																
	18	-	107	28.83	520	400	-																
	17	-	102	30.18	450	420	-																
	19	-	115	26.97	450	375	-																
	27	-	166	18.60*	435	260	-	R RF	57 57	VU/VZ VU/VZ	31 31	DV DV	132S4 132S4	130 135	230 231								
	30	-	184	16.79	390	235	-																
	35	-	209	14.77*	345	205	-																
	37	-	221	13.95*	325	194	-																
	43	-	260	11.88	275	165	-																
	47	-	286	10.79	250	150	-																
	55	-	330	9.35	220	130	-																
	56	-	341	9.06	210	126	-																
	64	-	388	7.97	186	111	-																
	68	-	410	7.53	176	105	-																
	80	-	482	6.41	150	89	-																
	88	-	531	5.82	136	81	-																
	101	-	612	5.05	118	70	-																
	116	-	704	4.39	103	61	-																
	71	-	431	7.16*	167	100	-	RX RXF	97 97	VU/VZ VU/VZ	31 31	DV DV	132S4 132S4	175 185	220 221								
	78	-	471	6.56	153	91	-																
	88	-	533	5.79	135	81	-																
	92	-	556	5.56*	130	77	-	RX RXF	87 87	VU/VZ VU/VZ	31 31	DV DV	132S4 132S4	150 155	218 219								
	101	-	609	5.07	118	71	-																
	114	-	686	4.50*	105	63	-																
	127	-	765	4.04*	94	56	-	RX RXF	77 77	VU/VZ VU/VZ	31 31	DV DV	132S4 132S4	135 135	216 217								
	138	-	835	3.70	86	52	-																
	157	-	950	3.25*	76	45	-																
	166	-	1005	3.08*	72	43	-																
	189	-	1145	2.70	63	38	-																
	210	-	1270	2.43	57	34	-																
	240	-	1450	2.13	50	30	-																
	272	-	1645	1.88*	44	26	-																
	306	-	1850	1.67	39	23	-																
	360	-	2175	1.42	33	20	-																
7.5 / 5.8	0.66	-	4.0	760	18000	13800	-									R RF	167 R97 167 R97	VU/VZ VU/VZ	41 41	DV DV	132M4 132M4	890 900	- -
	0.77	-	4.6	656	18000	11900	-																
	0.87	-	5.2	579	18000	10500	-																
	1.0	-	6.0	503	18000	9110	-																
	1.2	-	7.0	432	18000	7820	-																
	1.3	-	8.1	376	16600	6810	-																
	1.5	-	9.1	335	14800	6070	-																
	1.7	-	10	303	13300	5490	-																
	1.8	-	11	279	12300	5050	-																




R = 1:5 ... R = 1:6													
P _m /P _{a2} [kW]	n _{a1} - n _{a2} [1/min]	i	M _{a1} [Nm]	M _{a2} [Nm]								m [kg]	
7.5 / 5.8	0.72 - 4.4	695	13000	12600	-	R RF	147 R77 147 R77	VU/VZ VU/VZ	41 41	DV DV	132M4 132M4	570	-
	0.81 - 4.9	619	13000	11200	-							580	-
	0.90 - 5.4	558	13000	10100	-								
	1.0 - 6.2	489	13000	8860	-								
	1.2 - 7.3	415	13000	7520	-								
	1.6 - 9.4	323	8000	5850	-	R RF	137 R77 137 R77	VU/VZ VU/VZ	41 41	DV DV	132M4 132M4	450	-
	1.7 - 10	291	8000	5270	-							470	-
	2.0 - 12	255	8000	4620	-								
	2.2 - 14	223	8000	4040	-								
	2.6 - 15	197	8000	3570	-								
2.9 - 17	175	7710	3170	-									
7.5 / 6.2	2.5 - 15	203.16	4300	3970	-	R RF	107 107	VU/VZ VU/VZ	41 41	DV DV	132M4 132M4	335	240
	2.9 - 18	172.34	4300	3370	-							345	241
	3.2 - 19	158.68	4300	3100	-								
	3.5 - 21	141.83	4300	2770	-								
	3.9 - 24	127.68	4300	2490	-								
	4.4 - 26	115.63	4300	2260	-	R RF	97 97	VU/VZ VU/VZ	41 41	DV DV	132M4 132M4	280	238
	4.0 - 24	126.75	3000	2480	-							300	239
	4.3 - 26	116.48	3000	2280	-								
	4.9 - 29	103.44	3000	2020	-								
	5.4 - 33	92.48	3000	1810	-								
	6.0 - 36	83.15	3000	1620	-	R RF	97 97	VU/VZ VU/VZ	41 41	DV DV	132M4 132M4	210	234
	7.0 - 42	72.17	3000	1410	-							220	235
	7.7 - 46	65.21	3000	1270	-								
	8.4 - 51	59.92	2850	1170	-								
	8.3 - 50	60.35*	1550	1180	-							R RF	87 87
	9.5 - 57	52.82	1550	1030	-	245	237						
	11 - 64	47.58	1550	930	-								
	12 - 73	41.74	1550	820	-								
	14 - 82	36.84*	1550	720	-								
	15 - 93	32.66*	1550	640	-	R RF	77 77	VU/VZ VU/VZ	41 41	DV DV	132M4 132M4	215	234
	18 - 109	27.88	1320	545	-							220	235
	14 - 82	36.83	820	720	-								
	15 - 91	33.47	820	655	-								
	17 - 105	29.00	820	565	-								
	20 - 120	25.23	780	495	-	R RF	77 77	VU/VZ VU/VZ	41 41	DV DV	132M4 132M4	210	234
	27 - 161	18.80	780	365	-							220	235
	28 - 170	17.82*	780	350	-								
	32 - 194	15.60	740	305	-								
	36 - 216	14.05	670	275	-								
	41 - 246	12.33	585	240	-	R RF	77 77	VU/VZ VU/VZ	41 41	DV DV	132M4 132M4	275	222
	46 - 279	10.88	515	215	-							290	223
	52 - 314	9.64	460	188	-								
	59 - 353	8.59	410	168	-								
	65 - 392	7.74	370	151	-								
	74 - 446	6.79	325	133	-	R RF	77 77	VU/VZ VU/VZ	41 41	DV DV	132M4 132M4	245	220
	84 - 506	5.99*	285	117	-							250	221
	95 - 571	5.31*	250	104	-								
	76 - 457	6.63*	315	130	-	RX RXF	107 107	VU/VZ VU/VZ	41 41	DV DV	132M4 132M4		
	90 - 540	5.61	265	110	-								
	97 - 584	5.19	245	101	-								
	87 - 524	5.79	275	113	-	RX RXF	97 97	VU/VZ VU/VZ	41 41	DV DV	132M4 132M4	245	220
	102 - 617	4.91	235	96	-							250	221
	111 - 671	4.52	215	88	-								





R = 1:5 ... R = 1:6																
P _m /P _{a2} [kW]	n _{a1} [1/min]	-	n _{a2}	i	M _{a1} [Nm]	M _{a2} [Nm]						m [kg]				
7.5 / 6.2	112	-	674	4.50*	215	88	-	RX RXF	87 87	VU/VZ VU/VZ	41 41	DV DV	132M4 132M4	220 225	218 219	
	133	-	802	3.78	180	74	-									
	144	-	871	3.48	165	68	-									
	163	-	981	3.09	147	60	-									
	182	-	1100	2.76*	131	54	-									
	203	-	1220	2.48	118	48	-									
	234	-	1410	2.15	102	42	-									
	260	-	1570	1.93	92	38	-									
	314	-	1895	1.60*	76	31	M2									
	362	-	2180	1.39	66	27	M2									
9.2 / 7.0	0.87	-	5.3	579	18000	12600	-	R RF	167 R97 167 R97	VU/VZ VU/VZ	41 41	DV DV	132ML4 132ML4	900 910	- -	
	1.0	-	6.1	503	18000	10900	-									
	1.2	-	7.1	432	18000	9400	-									
	1.3	-	8.1	376	16500	8180	-									
	1.5	-	9.1	335	14700	7290	-									
	1.7	-	10	303	13300	6590	-									
	1.8	-	11	279	12300	6070	-	R RF	147 R87 147 R87	VU/VZ VU/VZ	41 41	DV DV	132ML4 132ML4	610 620	- -	
	1.2	-	7.2	426	13000	9270	-									
	1.4	-	8.3	368	13000	8010	-									
	1.5	-	9.4	326	13000	7090	-									
	1.8	-	11	280	12300	6090	-									
	2.0	-	12	247	10900	5370	-									
	2.4	-	14	214	9410	4660	-									
	2.7	-	16	189	8310	4110	-									
	3.2	-	19	159	6990	3460	-	R RF	137 R77 137 R77	VU/VZ VU/VZ	41 41	DV DV	132ML4 132ML4	460 480	- -	
	2.0	-	12	255	8000	5550	-									
	2.3	-	14	223	8000	4850	-									
	2.6	-	16	197	8000	4290	-									
	2.9	-	17	175	7700	3810	-	9.2 / 7.5	R RF	107 107	VU/VZ VU/VZ	41 41	DV DV	132ML4 132ML4	345 355	240 241
	3.2	-	19	158.68	4300	3720	-									
3.6	-	22	141.83	4300	3330	-										
3.9	-	24	127.68	4300	3000	-										
4.4	-	26	115.63	4300	2710	-										
4.9	-	30	102.53	4300	2410	-										
5.4	-	33	92.70	4300	2170	-	R RF		97 97	VU/VZ VU/VZ	41 41	DV DV	132ML4 132ML4	290 310	238 239	
5.4	-	33	92.48	3000	2170	-										
6.0	-	37	83.15	3000	1950	-										
7.0	-	42	72.17	3000	1690	-										
7.7	-	47	65.21	3000	1530	-										
8.4	-	51	59.92	2840	1410	-										
9.5	-	57	53.21	2520	1250	-										
11	-	64	47.58	2260	1120	-										R RF
9.5	-	58	52.82	1550	1240	-										
11	-	64	47.58	1550	1120	-										
12	-	73	41.74	1550	980	-										
14	-	83	36.84*	1550	860	-										
15	-	93	32.66*	1550	765	-										
18	-	110	27.88	1320	655	-										
18	-	110	27.84*	1320	655	-	R RF	87 87	VU/VZ VU/VZ	41 41	DV DV	132ML4 132ML4	250 255	236 237		
22	-	130	23.40	1110	550	-										
23	-	142	21.51	1020	505	-										
26	-	160	19.10	910	450	-										
29	-	179	17.08*	810	400	-										




R = 1:5 ... R = 1:6														m			
P _m /P _{a2} [kW]	n _{a1} [1/min]	-	n _{a2} [1/min]	i	M _{a1} [Nm]	M _{a2} [Nm]											
9.2 / 7.5	27	-	162	18.80	780	440	-										
	28	-	171	17.82*	780	420	-										
	32	-	196	15.60	740	365	-										
	36	-	217	14.05	665	330	-										
	41	-	248	12.33	585	290	-										
	46	-	281	10.88	515	255	-	R	77	VU/VZ	41	DV	132ML4	220	234		
	52	-	317	9.64	455	225	-	RF	77	VU/VZ	41	DV	132ML4	230	235		
	59	-	355	8.59	405	200	-										
	65	-	394	7.74	365	182	-										
	74	-	450	6.79	320	159	-										
	84	-	510	5.99*	285	141	-										
	95	-	575	5.31*	250	125	-										
	76	-	460	6.63*	315	156	-										
	90	-	544	5.61	265	132	-										
	97	-	588	5.19	245	122	-	RX	107	VU/VZ	41	DV	132ML4	285	222		
	108	-	657	4.65	220	109	-	RXF	107	VU/VZ	41	DV	132ML4	300	223		
	120	-	727	4.20*	199	99	-										
	132	-	801	3.81	181	89	-										
	87	-	527	5.79	275	136	-										
	103	-	622	4.91	235	115	-										
	111	-	675	4.52	215	106	-										
	125	-	756	4.04	192	95	-										
	138	-	839	3.64*	173	85	-										
	153	-	925	3.30	157	77	-	RX	97	VU/VZ	41	DV	132ML4	255	220		
	172	-	1045	2.92	139	69	-	RXF	97	VU/VZ	41	DV	132ML4	260	221		
	191	-	1155	2.64	125	62	M2										
	225	-	1365	2.24*	106	53	M2										
	257	-	1560	1.96	93	46	M2,4										
	307	-	1860	1.64	78	39	M2,4										
	355	-	2150	1.42	67	33	M2,4										
	112	-	678	4.50*	215	106	-										
	133	-	808	3.78	179	89	-										
	145	-	877	3.48	165	82	-										
	163	-	988	3.09	147	73	-										
	182	-	1105	2.76*	131	65	-	RX	87	VU/VZ	41	DV	132ML4	230	218		
	203	-	1230	2.48	118	58	-	RXF	87	VU/VZ	41	DV	132ML4	235	219		
	234	-	1420	2.15	102	50	-										
	261	-	1580	1.93	92	45	M2										
	315	-	1910	1.60*	76	38	M2										
	362	-	2195	1.39	66	33	M2										
11.0 / 8.4	1.0	-	6.1	503	18000	13100	-										
	1.2	-	7.1	432	18000	11300	-										
	1.3	-	8.1	376	16500	9820	-	R	167 R97	VU/VZ	41	DV	160M4	900	-		
	1.5	-	9.1	335	14700	8750	-	RF	167 R97	VU/VZ	41	DV	160M4	910	-		
	1.7	-	10	303	13300	7910	-										
	1.8	-	11	279	12300	7280	-										
	1.4	-	8.3	368	13000	9610	-										
	1.5	-	9.4	326	13000	8510	-										
	1.8	-	11	280	12300	7310	-										
	2.0	-	12	247	10900	6450	-	R	147 R87	VU/VZ	41	DV	160M4	620	-		
	2.4	-	14	214	9410	5590	-	RF	147 R87	VU/VZ	41	DV	160M4	620	-		
	2.7	-	16	189	8310	4930	-										
	3.2	-	19	159	6990	4150	-										
	2.3	-	14	223	8000	5820	-	R	137 R77	VU/VZ	41	DV	160M4	465	-		
	2.6	-	16	197	8000	5140	-	RF	137 R77	VU/VZ	41	DV	160M4	485	-		
	2.9	-	17	175	7700	4570	-										
11.0 / 9.0	3.6	-	22	141.83	4300	3990	-										
	3.9	-	24	127.68	4300	3590	-										
	4.4	-	26	115.63	4300	3260	-										
	4.9	-	30	102.53	4300	2890	-	R	107	VU/VZ	41	DV	160M4	350	240		
	5.4	-	33	92.70	4300	2610	-	RF	107	VU/VZ	41	DV	160M4	355	241		
	6.4	-	39	78.57	3730	2210	-										
	6.9	-	42	72.88	3460	2050	-										
	7.7	-	47	65.60*	3110	1850	-										





R = 1:5 ... R = 1:6															
P _m /P _{a2} [kW]	n _{a1} [1/min]	-	n _{a2}	i	M _{a1} [Nm]	M _{a2}								m [kg]	
11.0 / 9.0	7.0	-	42	72.17	3000	2030	-	R RF	97 97	VU/VZ VU/VZ	41 41	DV DV	160M4 160M4	295 310	238 239
	7.7	-	47	65.21	3000	1840	-								
	8.4	-	51	59.92	2840	1690	-								
	9.5	-	57	53.21	2520	1500	-								
	11	-	64	47.58	2260	1340	-								
	12	-	71	42.78	2030	1200	-								
	14	-	82	37.13	1760	1050	-	R RF	87 87	VU/VZ VU/VZ	41 41	DV DV	160M4 160M4	255 260	236 237
	11	-	64	47.58	1550	1340	-								
	12	-	73	41.74	1550	1180	-								
	14	-	83	36.84*	1550	1040	-								
	15	-	93	32.66*	1550	920	-								
	18	-	110	27.88	1320	785	-								
	18	-	110	27.84*	1320	785	-	R RF	87 87	VU/VZ VU/VZ	41 41	DV DV	160M4 160M4	255 260	236 237
	22	-	130	23.40	1110	660	-								
	23	-	142	21.51	1020	605	-								
	26	-	160	19.10	910	540	-								
	29	-	179	17.08*	810	480	-								
	33	-	199	15.35	730	430	-								
	28	-	171	17.82*	780	500	-	R RF	77 77	VU/VZ VU/VZ	41 41	DV DV	160M4 160M4	225 230	234 235
	32	-	196	15.60	740	440	-								
	36	-	217	14.05	665	395	-								
	41	-	248	12.33	585	345	-								
	46	-	281	10.88	515	305	-								
	52	-	317	9.64	455	270	-								
	59	-	355	8.59	405	240	-								
	65	-	394	7.74	365	220	-								
	74	-	450	6.79	320	191	-								
	84	-	510	5.99*	285	169	-								
	95	-	575	5.31*	250	150	-	RX RXF	107 107	VU/VZ VU/VZ	41 41	DV DV	160M4 160M4	290 305	222 223
	76	-	460	6.63*	315	187	-								
	90	-	544	5.61	265	158	-								
	97	-	588	5.19	245	146	-	RX RXF	97 97	VU/VZ VU/VZ	41 41	DV DV	160M4 160M4	255 265	220 221
	87	-	527	5.79	275	163	-								
	103	-	622	4.91	235	138	-								
	111	-	675	4.52	215	127	-	RX RXF	87 87	VU/VZ VU/VZ	41 41	DV DV	160M4 160M4	235 240	218 219
	112	-	678	4.50*	215	127	-								
	133	-	808	3.78	179	106	-								
	145	-	877	3.48	165	98	-								
	163	-	988	3.09	147	87	-								
	182	-	1105	2.76*	131	78	-								
	203	-	1230	2.48	118	70	-								
	234	-	1420	2.15	102	61	-								
	261	-	1580	1.93	92	54	M2								
	315	-	1910	1.60*	76	45	M2								
	362	-	2195	1.39	66	39	M2,4	R RF	147 147	VU VU	51 51	DV DV	160L4 160L4	680 690	244 245
1.4	-	8.2	376	18000	13200	-									
1.5	-	9.2	335	18000	11800	-									
1.7	-	10	303	18000	10700	-									
1.8	-	11	279	18000	9820	-									
1.8	-	11	280	13000	9850	-									
2.1	-	13	247	13000	8690	-	R RF	147 R87 147 R87	VU VU	51 51	DV DV	160L4 160L4	730 730	- -	
2.4	-	14	214	13000	7530	-									
2.7	-	16	189	13000	6650	-									
3.2	-	19	159	12300	5600	-									
15.0 / 12.3	4.3	-	26	119.86	10000	4550	-	R RF	147 147	VU VU	51 51	DV DV	160L4 160L4	680 690	244 245
	4.7	-	28	109.31	9140	4150	-								
	4.5	-	27	113.72	8000	4320	-	R RF	137 137	VU VU	51 51	DV DV	160L4 160L4	550 570	242 243
	5.0	-	30	103.20*	8000	3920	-								
	5.8	-	35	88.70*	7420	3370	-								
	6.4	-	38	80.91*	6770	3070	-								





R = 1:5 ... R = 1:6												
P _m /P _{a2} [kW]	n _{a1} [1/min]	-	n _{a2}	i	M _{a1} [Nm]	M _{a2}						
											m [kg]	
15.0 / 12.3	5.0	-	30	102.53	4300	3890	-					
	5.5	-	33	92.70	4300	3520	-					
	6.5	-	39	78.57	4300	2980	M2					
	7.0	-	42	72.88	4300	2770	-	R	107	VU	51 DV 160L4	465 240
	7.8	-	47	65.60*	4300	2490	-	RF	107	VU	51 DV 160L4	470 241
	8.7	-	52	59.41	4300	2250	-					
	9.8	-	59	52.68	4300	2000	-					
	11	-	65	47.63	3980	1810	-					
	9.7	-	58	53.21	3000	2020	-					
	11	-	65	47.58	3000	1810	-					
	12	-	72	42.78	3000	1620	-	R	97	VU	51 DV 160L4	405 238
	14	-	83	37.13	3000	1410	-	RF	97	VU	51 DV 160L4	425 239
	15	-	93	33.25	2780	1260	-					
	19	-	112	27.58	2310	1050	M2					
	21	-	124	25.03	2090	950	-					
	23	-	138	22.37	1870	850	-					
	26	-	154	20.14	1680	765	-	R	97	VU	51 DV 160L4	405 238
	28	-	170	18.24	1530	690	-	RF	97	VU	51 DV 160L4	420 239
	32	-	191	16.17	1350	615	-					
	24	-	144	21.51	1500	820	-					
	27	-	162	19.10	1440	725	-					
	30	-	181	17.08*	1390	650	-					
	33	-	202	15.35	1280	585	-					
	39	-	232	13.33	1120	505	-					
	43	-	259	11.93	1000	455	-	R	87	VU	51 DV 160L4	360 236
	52	-	313	9.90*	830	375	M2	RF	87	VU	51 DV 160L4	370 237
	56	-	339	9.14*	765	345	-					
	63	-	377	8.22	690	310	-					
	72	-	434	7.13	595	270	-					
	80	-	484	6.39	535	245	-					
	97	-	584	5.30*	445	200	M2					
	99	-	596	5.19	435	197	-					
	110	-	666	4.65	390	177	-	RX	107	VU	51 DV 160L4	405 222
	122	-	737	4.20*	350	159	-	RXF	107	VU	51 DV 160L4	420 223
	114	-	685	4.52	380	172	-					
	127	-	766	4.04	340	153	-					
	141	-	850	3.64*	305	138	-					
	156	-	938	3.30	275	125	-					
	176	-	1060	2.92	245	111	-	RX	97	VU	51 DV 160L4	370 220
	195	-	1170	2.64	220	100	M2	RXF	97	VU	51 DV 160L4	375 221
	229	-	1380	2.24*	187	85	M2					
	262	-	1580	1.96	164	74	M2,4					
	313	-	1885	1.64	137	62	M2,4					
	362	-	2180	1.42	119	54	M2,4					
18.5 / 14.1	1.4	-	8.3	376	18000	16300	-					
	1.5	-	9.3	335	18000	14500	-	R	167 R97	VU	51 DV 180M4	1060 -
	1.7	-	10	303	18000	13100	-	RF	167 R97	VU	51 DV 180M4	1070 -
	1.8	-	11	279	18000	12100	-					
	2.4	-	15	214	13000	9270	-					
	2.7	-	16	189	13000	8190	-	R	147 R87	VU	51 DV 180M4	780 -
18.5 / 15.2	3.2	-	20	159	12300	6890	-	RF	147 R87	VU	51 DV 180M4	780 -
	4.3	-	26	119.86	10000	5600	-					
	4.7	-	28	109.31	9140	5110	-	R	147	VU	51 DV 180M4	730 244
	5.4	-	33	94.60*	7910	4420	-	RF	147	VU	51 DV 180M4	740 245
	4.5	-	27	113.72	8000	5320	-					
	5.0	-	30	103.20*	8000	4820	-	R	137	VU	51 DV 180M4	600 242
	5.8	-	35	88.70*	7410	4150	M2	RF	137	VU	51 DV 180M4	620 243
	6.4	-	38	80.91*	6760	3780	-					





R = 1:5 ... R = 1:6															
P _m /P _{a2} [kW]	n _{a1} [1/min]	-	n _{a2}	i	M _{a1} [Nm]	M _{a2}								m [kg]	
18.5 / 15.2	6.5	-	40	78.57	4300	3670	M2								
	7.1	-	43	72.88	4300	3410	-								
	7.8	-	47	65.60*	4300	3070	-	R	107	VU	51	DV	180M4	520	240
	8.7	-	52	59.41	4300	2780	-	RF	107	VU	51	DV	180M4	520	241
	9.8	-	59	52.68	4300	2460	-								
	11	-	65	47.63	3980	2230	-								
	9.7	-	58	53.21	3000	2490	-								
	11	-	65	47.58	3000	2220	-								
	12	-	73	42.78	3000	2000	-	R	97	VU	51	DV	180M4	455	238
	14	-	84	37.13	3000	1740	-	RF	97	VU	51	DV	180M4	475	239
	15	-	93	33.25	2780	1550	-								
	19	-	113	27.58	2300	1290	M2								
	21	-	124	25.03	2090	1170	-								
	23	-	139	22.37	1870	1050	-								
	26	-	154	20.14	1680	940	-	R	97	VU	51	DV	180M4	455	238
	28	-	170	18.24	1520	850	-	RF	97	VU	51	DV	180M4	470	239
	32	-	192	16.17	1350	755	-								
	24	-	144	21.51	1500	1010	-								
	27	-	163	19.10	1440	890	-								
	30	-	182	17.08*	1390	800	-								
	34	-	202	15.35	1280	715	-								
	39	-	233	13.33	1110	625	-								
	43	-	260	11.93	1000	560	-	R	87	VU	51	DV	180M4	410	236
	52	-	314	9.90*	830	465	M2	RF	87	VU	51	DV	180M4	420	237
	56	-	340	9.14*	765	425	-								
	63	-	378	8.22	685	385	-								
	72	-	436	7.13	595	335	-								
	80	-	486	6.39	535	300	-								
	97	-	586	5.30*	445	250	M2								
	99	-	598	5.19	435	245	-								
	111	-	668	4.65	390	215	-	RX	107	VU	51	DV	180M4	455	222
	122	-	739	4.20*	350	196	-	RXF	107	VU	51	DV	180M4	470	223
	114	-	687	4.52	380	210	-								
	127	-	769	4.04	340	189	-								
	141	-	853	3.64*	305	170	-								
	156	-	941	3.30	275	154	-								
	176	-	1065	2.92	245	137	M2	RX	97	VU	51	DV	180M4	420	220
	195	-	1175	2.64	220	123	M2	RXF	97	VU	51	DV	180M4	425	221
	230	-	1385	2.24*	187	105	M2								
	262	-	1585	1.96	164	92	M2,4								
	314	-	1895	1.64	137	77	M2,4								
	362	-	2185	1.42	119	66	M2,4								
22 / 16.8	1.5	-	9.3	335	18000	17200	-	R	167 R97	VU	51	DV	180L4	1080	-
	1.7	-	10	303	18000	15500	-	RF	167 R97	VU	51	DV	180L4	1090	-
	1.8	-	11	279	18000	14300	-								
	2.7	-	16	189	13000	9700	-	R	147 R87	VU	51	DV	180L4	790	-
22 / 18.0	3.2	-	20	159	12300	8160	-	RF	147 R87	VU	51	DV	180L4	800	-
	4.7	-	28	109.31	9140	6050	-	R	147	VU	51	DV	180L4	750	244
	5.4	-	33	94.60*	7910	5240	-	RF	147	VU	51	DV	180L4	750	245
	4.5	-	27	113.72	8000	6290	-								
	5.0	-	30	103.20*	8000	5710	-								
	5.8	-	35	88.70*	7410	4910	M2	R	137	VU	51	DV	180L4	610	242
	6.4	-	38	80.91*	6760	4480	-	RF	137	VU	51	DV	180L4	640	243
	7.0	-	42	73.49	6140	4070	-								
	7.1	-	43	72.88	4300	4030	-								
	7.8	-	47	65.60*	4300	3630	-								
	8.7	-	52	59.41	4300	3290	-	R	107	VU	51	DV	180L4	530	240
	9.8	-	59	52.68	4300	2920	-	RF	107	VU	51	DV	180L4	540	241
	11	-	65	47.63	3980	2640	-								
	13	-	77	40.37*	3370	2230	M2								




R = 1:5 ... R = 1:6															
P_m/P_{a2} [kW]	n_{a1} [1/min]	n_{a2}	i	M_{a1} [Nm]	M_{a2}									m [kg]	
22 / 18.0	11	- 65	47.58	3000	2630	-	R RF	97 97	VU VU	51 51	DV DV	180L4 180L4	470 485	238 239	
	12	- 73	42.78	3000	2370	-									
	14	- 84	37.13	3000	2060	-									
	15	- 93	33.25	2780	1840	M2									
	19	- 113	27.58	2300	1530	M2									
	21	- 124	25.03	2090	1390	-	R RF	97 97	VU VU	51 51	DV DV	180L4 180L4	465 485	238 239	
	23	- 139	22.37	1870	1240	-									
	26	- 154	20.14	1680	1110	-									
	28	- 170	18.24	1520	1010	-									
	32	- 192	16.17	1350	900	-									
	35	- 212	14.62	1220	810	-	R RF	87 87	VU VU	51 51	DV DV	180L4 180L4	425 435	236 237	
	24	- 144	21.51	1500	1190	-									
	27	- 163	19.10	1440	1060	-									
	30	- 182	17.08*	1390	950	-									
	34	- 202	15.35	1280	850	-									
	39	- 233	13.33	1110	740	-									
	43	- 260	11.93	1000	660	M2									
	52	- 314	9.90*	830	550	M2									
	56	- 340	9.14*	765	505	-									
	63	- 378	8.22	685	455	-									
	72	- 436	7.13	595	395	-									
	80	- 486	6.39	535	355	M2									
	97	- 586	5.30*	445	295	M2									
	99	- 598	5.19	435	285	-	RX RXF	107 107	VU VU	51 51	DV DV	180L4 180L4	470 485	222 223	
	111	- 668	4.65	390	255	-									
	122	- 739	4.20*	350	235	-									
	114	- 687	4.52	380	250	-	RX RXF	97 97	VU VU	51 51	DV DV	180L4 180L4	435 440	220 221	
	127	- 769	4.04	340	225	-									
	141	- 853	3.64*	305	200	-									
	156	- 941	3.30	275	183	-									
	176	- 1065	2.92	245	162	M2									
	195	- 1175	2.64	220	146	M2									
	230	- 1385	2.24*	187	124	M2,4									
	262	- 1585	1.96	164	109	M2,4									
	314	- 1895	1.64	137	91	M2,4									
	362	- 2185	1.42	119	79	M2,4									



R = 1:4																
P _m /P _{a2} [kW]	n _{a1}	-	n _{a2}	i	M _{a1}	M _{a2}									m [kg]	
30 / 23	2.7	-	13	200	18000	17500	M1-6	R	167	R107	VU	6	DV	200L4	1250	-
	3.2	-	15	169	18000	14800	M1-6	RF	167	R107	VU	6	DV	200L4	1260	-
30 / 25	2.9	-	14	186.93*	18000	17700	-	R RF	167	R107	VU	6	DV	200L4	1140	246
	3.6	-	17	153.07	18000	14500	-								1140	247
	3.9	-	18	139.98	18000	13200	-									
	4.5	-	21	121.81*	18000	11500	-									
	5.1	-	24	107.49	18000	10200	-									
	5.9	-	27	93.19	16200	8800	-	R RF	147	R107	VU	6	DV	200L4	870	244
	4.6	-	21	119.86	13000	11300	-									
	5.0	-	23	109.31	13000	10300	-									
	5.8	-	27	94.60*	13000	8930	-									
	6.6	-	30	83.47	13000	7880	-								880	245
	7.6	-	35	72.09	12500	6810	M2	R RF	137	R107	VU	6	DV	200L4	740	242
	8.2	-	38	66.99	11700	6330	-									
	6.8	-	31	80.91*	8000	7640	-									
	7.5	-	34	73.49	8000	6940	-									
	8.4	-	39	65.20	8000	6160	-									
	9.3	-	43	59.17*	8000	5590	-	R RF	137	R107	VU	6	DV	200L4	760	243
	11	-	50	50.86*	8000	4800	-									
	12	-	57	44.39	7730	4190	-									
	14	-	63	40.37*	4300	3810	-									
	16	-	72	35.26	4300	3330	M2	R RF	107	R107	VU	6	DV	200L4	660	240
	19	-	86	29.49	4300	2780	M2								670	241
	22	-	102	24.90*	4300	2350	-									
	24	-	112	22.62	3940	2140	-									
	27	-	126	20.07	3490	1900	-	R RF	107	R107	VU	6	DV	200L4		
	30	-	139	18.21	3170	1720	-									
	35	-	162	15.65	2720	1480	-									
	40	-	185	13.66	2380	1290	-									
	47	-	218	11.59	2020	1090	M2								650	240
	54	-	250	10.13	1760	960	M2								660	241
	64	-	295	8.56	1490	810	M2,4									
	70	-	322	7.86	1370	740	-									
	82	-	380	6.66	1160	630	M2									
	94	-	434	5.82	1010	550	M2									
	112	-	514	4.92	860	465	M2,4									





R = 1:3															
P_m/P_{a2} [kW]	n_{a1} [1/min]	n_{a2}	i	M_{a1} [Nm]	M_{a2} [Nm]								m [kg]		
37 / 30	6.4	- 19	107.49	18000	14800	-	R RF	167 167	VU VU	6 6	DV DV	225S4 225S4	1220	246	
	7.4	- 22	93.19	18000	12800	-							1230	247	
	8.3	- 25	82.91*	17300	11400	-									
	9.3	- 28	73.70*	15400	10100	-									
	10	- 31	67.40	14000	9250	-									
	12	- 36	58.65	12200	8050	-									
	10	- 31	66.99	13000	9190	-	R RF	147 147	VU VU	6 6	DV DV	225S4 225S4	950	244	
	11	- 34	61.09	12700	8380	-							960	245	
	13	- 39	52.87	11000	7260	-									
	15	- 45	46.65	9720	6400	-									
	15	- 47	44.39	8000	6090	-	R RF	137 137	VU VU	6 6	DV DV	225S4 225S4	820	242	
	18	- 55	37.65	7840	5170	-							840	243	
	21	- 63	32.91	6850	4520	M2									
	25	- 75	27.83	5800	3820	M2									
	23	- 71	29.49	4300	4050	M2	R RF	107 107	VU VU	6 6	DV DV	225S4 225S4	740	240	
													750	241	
		28	- 84	24.90*	4300	3420	-	R RF	107 107	VU VU	6 6	DV DV	225S4 225S4	740	240
		30	- 92	22.62	4300	3100	-							740	241
		34	- 104	20.07	4180	2750	-								
		38	- 115	18.21	3790	2500	-								
		44	- 133	15.65	3260	2150	-								
		50	- 153	13.66	2850	1870	-								
		59	- 180	11.59	2410	1590	-								
		68	- 206	10.13	2110	1390	-								
		80	- 244	8.56	1780	1170	M2								
		88	- 266	7.86	1640	1080	-								
		103	- 313	6.66	1390	910	-								
		118	- 359	5.82	1210	800	-								
		140	- 424	4.92	1020	675	M2								
45 / 37	7.4	- 22	93.19	18000	15800	-	R RF	167 167	VU VU	6 6	DV DV	225M4 225M4	1250	246	
	8.3	- 25	82.91*	17300	14000	-							1260	247	
	9.3	- 28	73.70*	15400	12500	-									
	10	- 31	67.40	14000	11400	-									
	12	- 36	58.65	12200	9930	-									
	13	- 40	51.76	10800	8760	-									
	15	- 47	44.87	9350	7600	-	R RF	147 147	VU VU	6 6	DV DV	225M4 225M4	980	244	
	11	- 34	61.09	12700	10300	-							990	245	
	13	- 39	52.87	11000	8950	-									
	15	- 45	46.65	9720	7900	-									
	17	- 52	40.29	8390	6820	-									
	19	- 59	35.64	7420	6030	-									
	23	- 70	29.95	6240	5070	M2									
	28	- 86	24.19	5040	4090	M2,4									
	18	- 55	37.65	7840	6370	M2	R RF	137 137	VU VU	6 6	DV DV	225M4 225M4	850	242	
	21	- 63	32.91	6850	5570	M2							870	243	
	25	- 75	27.83	5800	4710	M2,4									
		28	- 84	24.90*	4300	4220	-	R RF	107 107	VU VU	6 6	DV DV	225M4 225M4	770	240
		30	- 92	22.62	4300	3830	-							770	241
		34	- 104	20.07	4180	3400	-								
		38	- 115	18.21	3790	3080	-								
		44	- 133	15.65	3260	2650	-								
		50	- 153	13.66	2850	2310	-								
		59	- 180	11.59	2410	1960	-								
		68	- 206	10.13	2110	1710	M2								
		80	- 244	8.56	1780	1450	M2								
		88	- 266	7.86	1640	1330	-								
		103	- 313	6.66	1390	1130	-								
	118	- 359	5.82	1210	990	M2									
	140	- 424	4.92	1020	830	M2									





R = 1:7... R = 1:8


P_m/P_{a2} [kW]	n_{a1} [1/min]	n_{a2}	i	M_{a1} [Nm]	M_{a2} [Nm]								m [kg]	
0.37 / 0.28	0.16	- 1.1	2280	4300	2450	-	R	107 R77	VU/VZ	11	DT	80K6	215	-
	0.17	- 1.2	2067	4300	2220	-	RF	107 R77	VU/VZ	11	DT	80K6	220	-
	0.18	- 1.2	1987	4300	2130	-								
	0.20	- 1.4	1827	4300	1960	-								
	0.22	- 1.6	1599	4300	1720	-								
	0.26	- 1.8	1400	4300	1500	-	R	107 R77	VU/VZ	11	DT	80K6	220	-
	0.29	- 2.0	1226	4300	1320	-	RF	107 R77	VU/VZ	11	DT	80K6	225	-
	0.32	- 2.2	1104	4300	1180	-								
	0.38	- 2.6	939	4300	1010	-								
	0.44	- 3.0	822	4300	880	-								
	0.76	- 5.3	469	2710	510	-								
	0.84	- 5.8	426	2460	465	-								
	0.95	- 6.6	377	2180	410	-								
	1.1	- 7.6	325	1880	355	-	R	107 R77	VU/VZ	11	DT	80K6	215	-
	1.3	- 8.7	284	1640	310	-	RF	107 R77	VU/VZ	11	DT	80K6	220	-
	1.4	- 9.7	256	1480	280	-								
	1.6	- 11	220	1270	240	-								
	2.1	- 14	172	990	187	-								
	0.23	- 1.6	1583	3000	1700	-								
	0.26	- 1.8	1396	3000	1500	-								
	0.29	- 2.0	1228	3000	1320	-								
	0.33	- 2.3	1069	3000	1150	-	R	97 R57	VU/VZ	11	DT	80K6	150	-
	0.38	- 2.6	938	3000	1010	-	RF	97 R57	VU/VZ	11	DT	80K6	165	-
	0.43	- 3.0	824	3000	880	-								
	0.49	- 3.4	737	3000	790	-								
	0.57	- 3.9	632	3000	680	-								
	0.57	- 4.0	625	3000	680	-								
	0.65	- 4.5	549	3000	600	-								
	0.77	- 5.3	466	2690	510	-								
	0.85	- 5.9	420	2430	460	-	R	97 R57	VU/VZ	11	DT	80K6	145	-
	0.97	- 6.7	370	2140	405	-	RF	97 R57	VU/VZ	11	DT	80K6	165	-
	1.0	- 7.1	349	2020	380	-								
	1.2	- 8.3	297	1720	325	-								
	1.3	- 9.2	270	1560	295	-								
	1.6	- 11	227	1310	245	-								
	0.46	- 3.2	776	1550	830	-	R	87 R57	VU/VZ	11	DT	80K6	110	-
	0.52	- 3.6	685	1550	735	-	RF	87 R57	VU/VZ	11	DT	80K6	115	-
	0.60	- 4.1	599	1550	645	-								
	0.66	- 4.6	538	1550	585	-								
	0.76	- 5.2	472	1550	515	-								
	0.89	- 6.2	400	1550	435	-								
	0.99	- 6.9	361	1550	395	-	R	87 R57	VU/VZ	11	DT	80K6	110	-
	1.2	- 8.2	300	1550	325	-	RF	87 R57	VU/VZ	11	DT	80K6	115	-
	1.4	- 9.7	256	1480	280	-								
	1.5	- 11	232	1340	255	-								
	1.8	- 13	195	1130	215	-								
	0.85	- 5.9	422	820	460	-								
	0.98	- 6.8	365	820	400	-								
	1.2	- 8.0	310	820	340	-	R	77 R37	VU/VZ	11	DT	80K6	75	-
	1.3	- 9.0	276	820	300	-	RF	77 R37	VU/VZ	11	DT	80K6	80	-
	1.5	- 10	236	820	255	-								
	1.6	- 11	221	820	240	-								
	1.9	- 13	186	820	205	-								
	1.2	- 8.0	310	600	340	-								
	1.4	- 9.4	264	600	290	-								
	1.5	- 11	235	600	255	-	R	67 R37	VU/VZ	11	DT	80K6	70	-
	1.8	- 12	201	600	220	-	RF	67 R37	VU/VZ	11	DT	80K6	73	-
	2.0	- 14	181	600	197	-								
	2.2	- 16	159	600	173	-								





R = 1:7... R = 1:8															
P _m /P _{a2} [kW]	n _{a1} [1/min]	-	n _{a2}	i	M _{a1} [Nm]	M _{a2}								m [kg]	
0.37 / 0.28	1.6	-	11	220	450	240	-	R RF	57 R37 57 R37	VU/VZ VU/VZ	11 11	DT DT	80K6 80K6	63	-
	1.9	-	13	188	450	205	-							67	-
	2.2	-	16	159	450	173	-							-	-
	2.5	-	17	146	450	159	-							-	-
	2.7	-	18	134	450	146	-	R RF	47 R37 47 R37	VU/VZ VU/VZ	11 11	DT DT	80K6 80K6	58	-
	2.3	-	16	154	300	168	-							59	-
	2.8	-	19	129	300	141	-							-	-
	3.3	-	23	109	300	119	-							-	-
	3.6	-	25	98	300	107	-							-	-
	0.37 / 0.30	2.1	-	15	166.59	820	193							-	R RF
2.5		-	17	145.67	820	169	-	72	235						
2.6		-	18	138.39	820	160	-	-	-						
2.9		-	20	121.42	745	141	-	-	-						
2.3		-	16	158.14	600	183	-	R RF	67 67	VU/VZ VU/VZ	11 11	DT DT	80K6 80K6	58	232
2.6		-	18	137.67	600	159	-							62	233
2.8		-	19	128.97	600	149	-							-	-
3.1		-	22	113.94	600	132	-							-	-
3.4		-	23	105.83	600	123	-							-	-
3.7		-	26	95.91	590	111	-							-	-
4.2		-	29	86.11	530	100	-							-	-
4.8		-	33	74.17	455	86	-							-	-
5.1		-	35	69.75	430	81	-							-	-
2.4		-	17	147.92	450	171	-							R RF	57 57
2.8		-	19	128.77	450	149	-	55	231						
3.0		-	21	120.63	450	140	-	-	-						
3.4		-	23	106.58	450	123	-	-	-						
3.6		-	25	98.99	450	115	-	-	-						
4.0		-	28	89.71	450	104	-	-	-						
4.4		-	31	80.55	450	93	-	-	-						
5.2		-	36	69.23	425	80	-	-	-						
5.5		-	38	64.85	400	75	-	-	-						
6.2		-	43	57.29	350	66	-	-	-						
6.7		-	47	53.22	325	62	-	R RF	47 47	VU/VZ VU/VZ	11 11	DT DT	80K6 80K6	47	228
2.6		-	18	139.99	300	162	-							47	229
2.9		-	20	121.87	300	141	-							-	-
3.1		-	22	114.17	300	132	-							-	-
3.6		-	25	100.86	300	117	-							-	-
3.8		-	26	93.68	300	108	-							-	-
4.2		-	29	84.90	300	98	-							-	-
4.7		-	32	76.23	300	88	-							-	-
5.2		-	36	68.54	300	79	-							-	-
5.6		-	39	64.21	300	74	-							-	-
6.3		-	44	56.73	300	66	-	R RF	37 37	VU/VZ VU/VZ	11 11	DT DT	80K6 80K6	45	226
6.8		-	47	52.69	300	61	-							46	227
7.5		-	52	47.75	295	55	-							-	-
8.3		-	58	42.87	265	50	-							-	-
9.7		-	67	36.93	225	43	-							-	-
10		-	71	34.73	215	40	-							-	-
3.4		-	24	105.28	200	122	-							-	-
3.9		-	27	90.77	200	105	-							-	-
4.2		-	29	84.61	200	98	-							-	-
4.8		-	33	73.96	200	86	-							-	-
5.2		-	36	69.33	200	80	-	-	-						
5.8		-	40	61.18	200	71	-	-	-						
6.4		-	44	55.76	200	65	-	-	-						
7.4		-	51	48.08	200	56	-	-	-						
8.0		-	55	44.81	200	52	-	-	-						
9.1		-	63	39.17	200	45	-	-	-						
9.7		-	67	36.72	200	43	-	-	-						
11	-	76	32.40	199	38	-	-	-							
12	-	86	28.73	177	33	-	-	-							
15	-	101	24.42	150	28	-	-	-							



R = 1:7... R = 1:8															
P _m /P _{a2} [kW]	n _{a1} [1/min]	n _{a2}	i	M _{a1} [Nm]	M _{a2}								m [kg]		
0.37 / 0.30	16	-	111	22.27	137	26	-								
	19	-	128	19.31	119	22	-								
	20	-	137	18.05	111	21	-								
	23	-	159	15.60	96	18	-								
	27	-	187	13.25	81	15	-								
	30	-	209	11.83	73	14	-	R	37	VU/VZ	11	DT	80K6	44	226
	35	-	245	10.11	62	12	-	RF	37	VU/VZ	11	DT	80K6	46	227
	38	-	261	9.47	58	11	-								
	45	-	311	7.97	49	9.2	-								
	54	-	371	6.67	41	7.7	-								
	63	-	437	5.67	35	6.6	-								
	71	-	489	5.06	31	5.9	-								
	69	-	478	5.18	32	6.0	-	RX	67	VU/VZ	11	DT	80K6	45	214
	79	-	546	4.53	28	5.2	-	RXF	67	VU/VZ	11	DT	80K6	49	215
	83	-	576	4.30*	26	5.0	-								
	82	-	569	4.35	27	5.0	-								
	94	-	653	3.79	23	4.4	-								
	101	-	697	3.55*	22	4.1	-								
	114	-	788	3.14	19	3.6	-								
	123	-	851	2.91	18	3.4	-								
	135	-	938	2.64*	16	3.1	-	RX	57	VU/VZ	11	DT	80K6	42	212
	151	-	1045	2.37	15	2.7	-	RXF	57	VU/VZ	11	DT	80K6	44	213
	175	-	1215	2.04	13	2.4	-								
	186	-	1290	1.92*	12	2.2	-								
	217	-	1500	1.65	10	1.9	-								
	242	-	1670	1.48	9.1	1.7	-								
	275	-	1905	1.30	8.0	1.5	-								
0.55 / 0.42	0.25	-	1.8	1407	4300	2270	-								
	0.30	-	2.0	1209	4300	1950	-								
	0.34	-	2.4	1055	4300	1700	-								
	0.39	-	2.7	919	4300	1480	-	R	107 R77	VU/VZ	11	DT	80N6	215	-
	0.44	-	3.0	815	4300	1310	-	RF	107 R77	VU/VZ	11	DT	80N6	220	-
	0.50	-	3.5	717	4080	1150	-								
	0.57	-	4.0	626	3570	1010	-								
	0.68	-	4.7	528	3010	850	-								
	0.76	-	5.3	469	2710	765	-								
	0.84	-	5.8	426	2460	695	-								
	0.95	-	6.6	377	2180	615	-								
	1.1	-	7.6	325	1880	530	-	R	107 R77	VU/VZ	11	DT	80N6	215	-
	1.3	-	8.7	284	1640	465	-	RF	107 R77	VU/VZ	11	DT	80N6	220	-
	1.4	-	9.7	256	1480	420	-								
	1.6	-	11	220	1270	360	-								
	2.1	-	14	172	990	280	-								
	0.33	-	2.3	1069	3000	1720	-								
	0.38	-	2.6	938	3000	1510	-								
	0.43	-	3.0	824	3000	1330	-	R	97 R57	VU/VZ	11	DT	80N6	150	-
	0.49	-	3.4	737	3000	1190	-	RF	97 R57	VU/VZ	11	DT	80N6	165	-
	0.57	-	3.9	632	3000	1020	-								
	0.57	-	4.0	625	3000	1020	-								
	0.65	-	4.5	549	3000	900	-								
	0.77	-	5.3	466	2690	760	-								
	0.85	-	5.9	420	2430	685	-								
	0.97	-	6.7	370	2140	605	-	R	97 R57	VU/VZ	11	DT	80N6	145	-
	1.0	-	7.1	349	2020	570	-	RF	97 R57	VU/VZ	11	DT	80N6	165	-
1.2	-	8.3	297	1720	485	-									
1.3	-	9.2	270	1560	440	-									
1.6	-	11	227	1310	370	-									




R = 1:7... R = 1:8														
P _m /P _{a2} [kW]	n _{a1} [1/min]	-	n _{a2}	i	M _{a1} [Nm]	M _{a2}						m [kg]		
0.55 / 0.42	0.66	-	4.6	538	1550	880	-	R RF	87 R57 87 R57	VU/VZ VU/VZ	11 DT 11 DT	80N6 80N6	110	-
	0.76	-	5.2	472	1550	770	-						115	-
	0.89	-	6.2	400	1550	655	-							
	0.99	-	6.9	361	1550	590	-							
	1.2	-	8.2	300	1550	490	-							
	1.4	-	9.7	256	1480	420	-							
	1.5	-	11	232	1340	380	-							
	1.8	-	13	195	1130	320	-							
	1.3	-	9.0	276	820	450	-	R RF	77 R37 77 R37	VU/VZ VU/VZ	11 DT 11 DT	80N6 80N6	76	-
	1.5	-	10	236	820	385	-						81	-
	1.6	-	11	221	820	360	-							
	1.9	-	13	186	820	305	-							
	1.8	-	12	201	600	330	-	R RF	67 R37 67 R37	VU/VZ VU/VZ	11 DT 11 DT	80N6 80N6	71	-
	2.0	-	14	181	600	295	-						74	-
	2.2	-	16	159	600	260	-							
	2.2	-	16	159	450	260	-	R RF	57 R37 57 R37	VU/VZ VU/VZ	11 DT 11 DT	80N6 80N6	64	-
	2.5	-	17	146	450	240	-						68	-
	2.7	-	18	134	450	220	-							
0.55 / 0.45	2.1	-	15	166.59	820	290	-	R RF	77 77	VU/VZ VU/VZ	11 DT 11 DT	80N6 80N6	68	234
	2.5	-	17	145.67	820	255	-						73	235
	2.6	-	18	138.39	820	240	-							
	2.9	-	20	121.42	745	210	-							
	2.3	-	16	158.14	600	275	-	R RF	67 67	VU/VZ VU/VZ	11 DT 11 DT	80N6 80N6	59	232
	2.6	-	18	137.67	600	240	-						63	233
	2.8	-	19	128.97	600	225	-							
	3.1	-	22	113.94	600	198	-							
	3.4	-	23	105.83	600	184	-							
	3.7	-	26	95.91	590	167	-							
	2.4	-	17	147.92	450	255	-						R RF	57 57
	2.8	-	19	128.77	450	225	-	56	231					
	3.0	-	21	120.63	450	210	-							
	3.4	-	23	106.58	450	185	-							
	3.6	-	25	98.99	450	172	-							
	4.0	-	28	89.71	450	156	-							
	4.4	-	31	80.55	450	140	-							
	5.2	-	36	69.23	425	120	-							
	5.5	-	38	64.85	400	113	-							
	6.2	-	43	57.29	350	100	-							
	6.7	-	47	53.22	325	92	-							
	2.6	-	18	139.99	300	245	-	R RF	47 47	VU/VZ VU/VZ	11 DT 11 DT	80N6 80N6		
	2.9	-	20	121.87	300	210	-						48	229
	3.1	-	22	114.17	300	198	-							
	3.6	-	25	100.86	300	175	-							
	3.8	-	26	93.68	300	163	-							
	4.2	-	29	84.90	300	147	-							
	4.7	-	32	76.23	300	132	-							
	5.2	-	36	68.54	300	119	-							
	5.6	-	39	64.21	300	112	-							
	6.3	-	44	56.73	300	99	-							
	6.8	-	47	52.69	300	92	-							
	7.5	-	52	47.75	295	83	-							
	8.3	-	58	42.87	265	74	-							
	9.7	-	67	36.93	225	64	-							
	10	-	71	34.73	215	60	-							




R = 1:7... R = 1:8





P_m/P_{a2} [kW]	n_{a1} [1/min]	-	n_{a2}	i	M_{a1} [Nm]	M_{a2} [Nm]			m [kg]	
0.55 / 0.45	3.4	-	24	105.28	200	183	-			
	3.9	-	27	90.77	200	158	-			
	4.2	-	29	84.61	200	147	-			
	4.8	-	33	73.96	200	128	-			
	5.2	-	36	69.33	200	120	-			
	5.8	-	40	61.18	200	106	-			
	6.4	-	44	55.76	200	97	-	R 37	VU/VZ 11 DT 80N6	46 226
	7.4	-	51	48.08	200	84	-	RF 37	VU/VZ 11 DT 80N6	47 227
	8.0	-	55	44.81	200	78	-			
	9.1	-	63	39.17	200	68	-			
	9.7	-	67	36.72	200	64	-			
	11	-	76	32.40	199	56	-			
	12	-	86	28.73	177	50	-			
	15	-	101	24.42	150	42	-			
	16	-	111	22.27	137	39	-			
	19	-	128	19.31	119	34	-			
	20	-	137	18.05	111	31	-			
	23	-	159	15.60	96	27	-			
	27	-	187	13.25	81	23	-			
	30	-	209	11.83	73	21	-	R 37	VU/VZ 11 DT 80N6	45 226
	35	-	245	10.11	62	18	-	RF 37	VU/VZ 11 DT 80N6	47 227
	38	-	261	9.47	58	16	-			
	45	-	311	7.97	49	14	-			
	54	-	371	6.67	41	12	-			
	63	-	437	5.67	35	9.8	-			
	71	-	489	5.06	31	8.8	-			
	83	-	573	4.32	27	7.5	-			
	69	-	478	5.18	32	9.0	-	RX 67	VU/VZ 11 DT 80N6	46 214
	79	-	546	4.53	28	7.9	-	RXF 67	VU/VZ 11 DT 80N6	50 215
	83	-	576	4.30*	26	7.5	-			
	82	-	569	4.35	27	7.6	-			
	94	-	653	3.79	23	6.6	-			
	101	-	697	3.55*	22	6.2	-			
	114	-	788	3.14	19	5.5	-			
	123	-	851	2.91	18	5.1	-			
	135	-	938	2.64*	16	4.6	-	RX 57	VU/VZ 11 DT 80N6	43 212
	151	-	1045	2.37	15	4.1	-	RXF 57	VU/VZ 11 DT 80N6	45 213
	175	-	1215	2.04	13	3.5	-			
	186	-	1290	1.92*	12	3.3	-			
	217	-	1500	1.65	10	2.9	-			
	242	-	1670	1.48	9.1	2.6	-			
	275	-	1905	1.30	8.0	2.3	-			
0.75 / 0.58	0.14	-	0.97	2555	13000	5670	-			
	0.16	-	1.1	2211	12600	4900	-			
	0.18	-	1.3	1951	11100	4330	-			
	0.21	-	1.4	1705	9710	3780	-	R 147 R77	VU/VZ 11 DT 90S6	435 -
	0.23	-	1.6	1536	8750	3410	-	RF 147 R77	VU/VZ 11 DT 90S6	440 -
	0.27	-	1.9	1329	7570	2950	-			
	0.31	-	2.1	1166	6640	2590	-			
	0.40	-	2.8	889	5060	1970	-			
	0.13	-	0.93	2658	8000	5900	-			
	0.15	-	1.0	2412	8000	5350	-			
	0.17	-	1.2	2073	8000	4600	-			
	0.19	-	1.4	1839	8000	4080	-			
	0.22	-	1.6	1598	8000	3540	-			
	0.26	-	1.8	1397	7960	3100	-	R 137 R77	VU/VZ 11 DT 90S6	310 -
	0.29	-	2.0	1226	6980	2720	-	RF 137 R77	VU/VZ 11 DT 90S6	330 -
	0.33	-	2.3	1090	6210	2420	-			
	0.38	-	2.6	951	5420	2110	-			
	0.43	-	3.0	831	4730	1840	-			
	0.49	-	3.4	730	4160	1620	-			




R = 1:7... R = 1:8

P_m/P_{a2} [kW]	n_{a1} - n_{a2} [1/min]	i	M_{a1} [Nm]	M_{a2} [Nm]			m [kg]		
0.75 / 0.58	0.26 - 1.8	1400	4300	3110	-				
	0.29 - 2.0	1226	4300	2720	-				
	0.32 - 2.2	1104	4300	2450	-	R	107 R77	VU/VZ 11 DT 90S6	225 -
	0.38 - 2.6	939	4300	2080	-	RF	107 R77	VU/VZ 11 DT 90S6	230 -
	0.44 - 3.0	822	4300	1820	-				
	0.76 - 5.3	469	2710	1060	-				
	0.84 - 5.8	426	2460	960	-				
	0.95 - 6.6	377	2180	850	-				
	1.1 - 7.6	325	1880	730	-	R	107 R77	VU/VZ 11 DT 90S6	220 -
	1.3 - 8.7	284	1640	640	-	RF	107 R77	VU/VZ 11 DT 90S6	225 -
	1.4 - 9.7	256	1480	575	-				
	1.6 - 11	220	1270	495	-				
	2.1 - 14	172	990	385	-				
	0.49 - 3.4	737	3000	1630	-	R	97 R57	VU/VZ 11 DT 90S6	155 -
	0.57 - 3.9	632	3000	1400	-	RF	97 R57	VU/VZ 11 DT 90S6	170 -
	0.57 - 4.0	625	3000	1410	-				
	0.65 - 4.5	549	3000	1240	-				
	0.77 - 5.3	466	2690	1050	-				
	0.85 - 5.9	420	2430	950	-	R	97 R57	VU/VZ 11 DT 90S6	150 -
	0.97 - 6.7	370	2140	830	-	RF	97 R57	VU/VZ 11 DT 90S6	170 -
	1.0 - 7.1	349	2020	785	-				
	1.2 - 8.3	297	1720	670	-				
	1.3 - 9.2	270	1560	610	-				
	1.6 - 11	227	1310	510	-				
	0.89 - 6.2	400	1550	900	-				
	0.99 - 6.9	361	1550	810	-				
	1.2 - 8.2	300	1550	675	-	R	87 R57	VU/VZ 11 DT 90S6	115 -
	1.4 - 9.7	256	1480	575	-	RF	87 R57	VU/VZ 11 DT 90S6	120 -
	1.5 - 11	232	1340	525	-				
	1.8 - 13	195	1130	440	-				
0.75 / 0.62	1.6 - 11	221	820	500	-	R	77 R37	VU/VZ 11 DT 90S6	81 -
	1.9 - 13	186	820	420	-	RF	77 R37	VU/VZ 11 DT 90S6	87 -
	1.6 - 12	216.54	1550	500	-				
	1.7 - 13	205.71	1550	475	-				
	1.9 - 14	181.77	1550	420	-	R	87	VU/VZ 21 DT 90S6	120 236
	2.2 - 17	155.34	1530	355	-	RF	87	VU/VZ 21 DT 90S6	125 237
	2.4 - 18	142.41	1400	330	-				
	2.7 - 21	124.97	1230	290	-				
	2.1 - 15	166.59	820	400	-				
	2.5 - 17	145.67	820	350	-	R	77	VU/VZ 11 DT 90S6	73 234
	2.6 - 18	138.39	820	330	-	RF	77	VU/VZ 11 DT 90S6	78 235
	2.9 - 20	121.42	745	290	-				
	3.5 - 24	102.99	635	245	-				
	2.3 - 16	158.14	600	380	-				
	2.6 - 18	137.67	600	330	-				
	2.8 - 19	128.97	600	310	-	R	67	VU/VZ 11 DT 90S6	65 232
	3.1 - 22	113.94	600	275	-	RF	67	VU/VZ 11 DT 90S6	68 233
	3.4 - 23	105.83	600	255	-				
	3.7 - 26	95.91	590	230	-				
	2.4 - 17	147.92	450	355	-				
	2.8 - 19	128.77	450	310	-				
	3.0 - 21	120.63	450	290	-				
	3.4 - 23	106.58	450	255	-				
	3.6 - 25	98.99	450	235	-				
	4.0 - 28	89.71	450	215	-	R	57	VU/VZ 11 DT 90S6	58 230
	4.4 - 31	80.55	450	193	-	RF	57	VU/VZ 11 DT 90S6	61 231
	5.2 - 36	69.23	425	166	-				
	5.5 - 38	64.85	400	155	-				
	6.2 - 43	57.29	350	137	-				
	6.7 - 47	53.22	325	127	-				





R = 1:7... R = 1:8																									
P _m /P _{a2} [kW]	n _{a1} [1/min]	-	n _{a2}	i	M _{a1} [Nm]	M _{a2} [Nm]						m [kg]													
0.75 / 0.62	2.9	-	20	121.87	300	290	-		R	47	VU/VZ	11	DT	90S6	53	228									
	3.1	-	22	114.17	300	275	-																		
	3.6	-	25	100.86	300	240	-																		
	3.8	-	26	93.68	300	225	-																		
	4.2	-	29	84.90	300	205	-																		
	4.7	-	32	76.23	300	182	-																		
	5.2	-	36	68.54	300	164	-																		
	5.6	-	39	64.21	300	154	-																		
	6.3	-	44	56.73	300	136	-																		
	6.8	-	47	52.69	300	126	-																		
	7.5	-	52	47.75	295	114	-																		
	8.3	-	58	42.87	265	103	-																		
	9.7	-	67	36.93	225	88	-																		
	10	-	71	34.73	215	83	-																		
	4.8	-	33	73.96	200	177	-										R	37	VU/VZ	11	DT	90S6	51	226	
	5.2	-	36	69.33	200	166	-																		
	5.8	-	40	61.18	200	146	-																		
	6.4	-	44	55.76	200	133	-																		
	7.4	-	51	48.08	200	115	-																		
	8.0	-	55	44.81	200	107	-																		
	9.1	-	63	39.17	200	94	-																		
	9.7	-	67	36.72	200	88	-																		
	11	-	76	32.40	199	78	-																		
	12	-	86	28.73	177	69	-																		
	15	-	101	24.42	150	58	-																		
	16	-	111	22.27	137	53	-																		RF
	19	-	128	19.31	119	46	-																		
	20	-	137	18.05	111	43	-																		
	23	-	159	15.60	96	37	-																		
	27	-	187	13.25	81	32	-																		
	30	-	209	11.83	73	28	-																		
	35	-	245	10.11	62	24	-																		
	38	-	261	9.47	58	23	-																		
	45	-	311	7.97	49	19	-																		
	54	-	371	6.67	41	16	-																		
	63	-	437	5.67	35	14	-																		
	71	-	489	5.06	31	12	-																		
	69	-	478	5.18	32	12	-										RX	67	VU/VZ	11	DT	90S6	51	214	
	79	-	546	4.53	28	11	-																		
	83	-	576	4.30*	26	10	-																		
	82	-	569	4.35	27	10	-										RXF	57	VU/VZ	11	DT	90S6	48	212	
	94	-	653	3.79	23	9.1	-																		
	101	-	697	3.55*	22	8.5	-																		
	114	-	788	3.14	19	7.5	-																		
	123	-	851	2.91	18	7.0	-																		
	135	-	938	2.64*	16	6.3	-																		
	151	-	1045	2.37	15	5.7	-																		
	175	-	1215	2.04	13	4.9	-																		
	186	-	1290	1.92*	12	4.6	-																		
	217	-	1500	1.65	10	3.9	-																		
	242	-	1670	1.48	9.1	3.5	-																		
	275	-	1905	1.30	8.0	3.1	-																		
1.1 / 0.84	0.14	-	0.99	2555	13000	8050	-		R	147	R77	VU/VZ	11	DT	90L6	435									-
	0.16	-	1.1	2211	12600	6960	-																		
	0.18	-	1.3	1951	11100	6150	-																		
	0.21	-	1.5	1705	9680	5370	-																		
	0.23	-	1.7	1536	8720	4840	-																		
	0.27	-	1.9	1329	7540	4190	-																		
	0.31	-	2.2	1166	6620	3670	-																		
	0.40	-	2.9	889	5050	2800	-																		
									RF	147	R77	VU/VZ	11	DT	90L6	445	-								





R = 1:7... R = 1:8


P_m/P_{a2} [kW]	n_{a1} - n_{a2} [1/min]	i	M_{a1} [Nm]	M_{a2} [Nm]			m [kg]		
1.1 / 0.84	0.22 - 1.6	1598	8000	5030	-				
	0.26 - 1.8	1397	7930	4400	-				
	0.29 - 2.1	1226	6960	3860	-				
	0.33 - 2.3	1090	6190	3430	-				
	0.38 - 2.7	951	5400	3000	-	R	137 R77	VU/VZ 11 DT 90L6	310 -
	0.43 - 3.0	831	4720	2620	-	RF	137 R77	VU/VZ 11 DT 90L6	335 -
	0.49 - 3.5	730	4140	2300	-				
	0.64 - 4.5	560	3180	1760	-				
	0.94 - 6.6	381	2160	1200	-				
	0.38 - 2.7	939	4300	2960	-				
	0.44 - 3.1	822	4300	2590	-	R	107 R77	VU/VZ 11 DT 90L6	230 -
	0.97 - 6.9	369	2090	1160	-	RF	107 R77	VU/VZ 11 DT 90L6	235 -
	1.1 - 7.8	323	1830	1020	-				
	0.77 - 5.4	469	2700	1500	-				
	0.84 - 5.9	426	2460	1360	-				
	0.95 - 6.7	377	2170	1210	-				
	1.1 - 7.8	325	1870	1040	-	R	107 R77	VU/VZ 11 DT 90L6	220 -
	1.3 - 8.9	284	1640	910	-	RF	107 R77	VU/VZ 11 DT 90L6	230 -
	1.4 - 9.9	256	1480	820	-				
	1.6 - 12	220	1270	705	-				
	2.1 - 15	172	990	550	-				
	0.65 - 4.6	549	3000	1760	-				
	0.77 - 5.4	466	2690	1490	-				
	0.85 - 6.0	420	2420	1340	-				
	0.97 - 6.8	370	2130	1180	-	R	97 R57	VU/VZ 11 DT 90L6	155 -
	1.0 - 7.2	349	2010	1120	-	RF	97 R57	VU/VZ 11 DT 90L6	170 -
	1.2 - 8.5	297	1710	950	-				
	1.3 - 9.4	270	1560	860	-				
	1.6 - 11	227	1310	725	-				
	1.4 - 9.9	256	1480	820	-				
	1.6 - 11	232	1340	740	-	R	87 R57	VU/VZ 11 DT 90L6	115 -
	1.8 - 13	195	1120	625	-	RF	87 R57	VU/VZ 11 DT 90L6	125 -
1.1 / 0.90	1.6 - 12	216.54	1550	705	-				
	1.7 - 13	205.71	1550	670	-				
	1.9 - 14	181.77	1550	595	-				
	2.2 - 17	155.34	1530	505	-	R	87	VU/VZ 21 DT 90L6	120 236
	2.4 - 18	142.41	1400	465	-	RF	87	VU/VZ 21 DT 90L6	130 237
	2.7 - 21	124.97	1230	410	-				
	2.9 - 22	118.43*	1160	385	-				
	2.1 - 15	166.59	820	565	-				
	2.5 - 17	145.67	820	495	-				
	2.6 - 18	138.39	820	470	-				
	3.0 - 21	121.42	745	415	-	R	77	VU/VZ 11 DT 90L6	75 234
	3.5 - 25	102.99	630	350	-	RF	77	VU/VZ 11 DT 90L6	80 235
	3.9 - 27	92.97	570	315	-				
	4.4 - 31	81.80	500	280	-				
	2.8 - 20	128.97	600	440	-				
	3.1 - 22	113.94	600	385	-				
	3.4 - 24	105.83	600	360	-	R	67	VU/VZ 11 DT 90L6	67 232
	3.7 - 26	95.91	585	325	-	RF	67	VU/VZ 11 DT 90L6	70 233
	4.2 - 29	86.11	525	295	-				
	4.8 - 34	74.17	455	250	-				




R = 1:7... R = 1:8															
P _m /P _{a2} [kW]	n _{a1} [1/min]	-	n _{a2}	i	M _{a1} [Nm]	M _{a2} [Nm]								m [kg]	
1.1 / 0.90	2.8	-	20	128.77	450	440	-	R RF	57 57	VU/VZ VU/VZ	11 11	DT DT	90L6 90L6	60 63	230 231
	3.0	-	21	120.63	450	410	-								
	3.4	-	24	106.58	450	360	-								
	3.6	-	26	98.99	450	335	-								
	4.0	-	28	89.71	450	305	-								
	4.5	-	31	80.55	450	275	-								
	5.2	-	37	69.23	425	235	-								
	5.5	-	39	64.85	395	220	-								
	6.3	-	44	57.29	350	195	-								
	6.7	-	48	53.22	325	181	-								
	7.4	-	52	48.23	295	164	-								
	8.3	-	58	43.30	265	147	-								
	9.6	-	68	37.30*	230	127	-								
	10	-	72	35.07	215	119	-								
	12	-	84	30.18	185	103	-								
	13	-	94	26.97	165	92	-								
4.2	-	30	84.90	300	290	-	R RF	47 47	VU/VZ VU/VZ	11 11	DT DT	90L6 90L6	55 55	228 229	
4.7	-	33	76.23	300	260	-									
5.2	-	37	68.54	300	235	-									
5.6	-	39	64.21	300	220	-									
6.3	-	45	56.73	300	193	-									
6.8	-	48	52.69	300	179	-									
7.5	-	53	47.75	290	162	-									
8.4	-	59	42.87	265	146	-									
9.7	-	69	36.93	225	126	-									
10	-	73	34.73	215	118	-									
6.4	-	45	55.76	200	189	-	R RF	37 37	VU/VZ VU/VZ	11 11	DT DT	90L6 90L6	53 54	226 227	
7.5	-	53	48.08	200	163	-									
8.0	-	56	44.81	200	152	-									
9.2	-	65	39.17	200	133	-									
9.8	-	69	36.72	200	125	-									
11	-	78	32.40	198	110	-									
12	-	88	28.73	176	98	-									
15	-	104	24.42	150	83	-									
16	-	114	22.27	136	76	-	R RF	37 37	VU/VZ VU/VZ	11 11	DT DT	90L6 90L6	52 54	226 227	
19	-	131	19.31	118	66	-									
20	-	140	18.05	111	61	-									
23	-	162	15.60	96	53	-									
27	-	191	13.25	81	45	-									
30	-	214	11.83	72	40	-									
35	-	250	10.11	62	34	-									
38	-	267	9.47	58	32	-									
45	-	317	7.97	49	27	-									
54	-	379	6.67	41	23	-									
63	-	446	5.67	35	19	-									
71	-	500	5.06	31	17	-									
69	-	488	5.18	32	18	-	RX RXF	67 67	VU/VZ VU/VZ	11 11	DT DT	90L6 90L6	53 57	214 215	
79	-	559	4.53	28	15	-									
83	-	588	4.30*	26	15	-									
82	-	582	4.35	27	15	-	RX RXF	57 57	VU/VZ VU/VZ	11 11	DT DT	90L6 90L6	50 52	212 213	
95	-	668	3.79	23	13	-									
101	-	713	3.55*	22	12	-									
114	-	806	3.14	19	11	-									
123	-	869	2.91	18	9.9	-									
136	-	958	2.64*	16	9.0	-									
151	-	1070	2.37	15	8.1	-									
176	-	1240	2.04	13	6.9	-									
187	-	1320	1.92*	12	6.5	-									
217	-	1535	1.65	10	5.6	-									
242	-	1710	1.48	9.1	5.0	-									
276	-	1945	1.30	8.0	4.4	-									



R = 1:7... R = 1:8																					
P _m /P _{a2} [kW]	n _{a1} [1/min]	-	n _{a2}	i	M _{a1} [Nm]	M _{a2} [Nm]							m [kg]								
1.5 / 1.2	0.20	-	1.5	1705	13000	7060	-	R RF	147 R77 147 R77	VU/VZ VU/VZ	21 21	DV DV	100M6 100M6	460	-						
	0.22	-	1.7	1536	13000	6360	-							470	-						
	0.26	-	2.0	1329	13000	5500	-														
	0.29	-	2.3	1166	13000	4830	-														
	0.33	-	2.6	1029	12300	4260	-														
	0.38	-	3.0	889	10600	3680	-														
	0.43	-	3.4	784	9390	3250	-														
	0.49	-	3.8	695	8320	2880	-														
	0.55	-	4.2	619	7410	2560	-														
	0.61	-	4.7	558	6680	2310	-														
	0.70	-	5.4	489	5850	2020	-														
	0.82	-	6.3	415	4970	1720	-														
	0.31	-	2.4	1090	8000	4510	-	R RF	137 R77 137 R77	VU/VZ VU/VZ	21 21	DV DV	100M6 100M6	335	-						
	0.36	-	2.8	951	8000	3940	-							360	-						
	0.41	-	3.2	831	8000	3440	-														
	0.47	-	3.6	730	8000	3020	-														
	0.54	-	4.2	629	7530	2600	-														
	0.61	-	4.7	560	6700	2320	-														
	0.69	-	5.4	490	5870	2030	-														
	0.79	-	6.2	428	5120	1770	-														
	0.89	-	6.9	381	4560	1580	-														
	1.1	-	8.2	323	3870	1340	-														
	1.2	-	9.0	291	3480	1200	-														
	1.3	-	10	255	3050	1060	-														
	1.5	-	12	223	2670	920	-														
	1.7	-	13	197	2360	820	-														
	1.9	-	15	175	2100	725	-														
	0.63	-	4.8	544	4300	2250	-	R RF	107 R77 107 R77	VU/VZ VU/VZ	21 21	DV DV	100M6 100M6	255	-						
	0.69	-	5.4	492	4300	2040	-							260	-						
	0.82	-	6.3	417	4300	1730	-														
	0.73	-	5.6	469	4300	1970	-														
	0.80	-	6.2	426	4300	1790	-														
	0.90	-	7.0	377	4300	1580	-														
	1.1	-	8.1	325	3950	1370	-							R RF	107 R77 107 R77	VU/VZ VU/VZ	21 21	DV DV	100M6 100M6	250	-
	1.2	-	9.3	284	3450	1190	-													255	-
	1.3	-	10	256	3110	1080	-														
	1.6	-	12	220	2670	920	-														
	1.8	-	14	193	2350	810	-														
	2.0	-	15	172	2090	725	-														
	0.92	-	7.1	370	3000	1550	-	R RF	97 R57 97 R57	VU/VZ VU/VZ	21 21	DV DV	100M6 100M6	180	-						
	0.97	-	7.5	349	3000	1470	-							200	-						
	1.2	-	8.9	297	3000	1250	-														
	1.3	-	9.8	270	3000	1130	-														
	1.5	-	12	227	2760	950	-														
1.5 / 1.2	1.6	-	12	216.54	1550	970	-	R RF	87 87	VU/VZ VU/VZ	21 21	DV DV	100M6 100M6	130	236						
	1.7	-	13	205.71	1550	920	-							135	237						
	1.9	-	14	181.77	1550	810	-														
	2.2	-	17	155.34	1550	695	-														
	2.4	-	18	142.41	1550	635	-														
	2.7	-	21	124.97	1550	560	-														
	2.9	-	22	118.43*	1530	530	-	R RF	77 77	VU/VZ VU/VZ	21 21	DV DV	100M6 100M6	100	234						
	3.3	-	25	103.65	1340	465	-							105	235						
	2.8	-	22	121.42	820	540	-														
	3.3	-	26	102.99	820	460	-														
	3.7	-	28	92.97	820	415	-														
	4.2	-	32	81.80	820	365	-														
	4.4	-	34	77.24	820	345	-	R RF	67 67	VU/VZ VU/VZ	21 21	DV DV	100M6 100M6	94	232						
	5.2	-	40	65.77	820	295	-							98	233						
	3.2	-	25	105.83	600	475	-														
	3.6	-	27	95.91	600	430	-														
	4.0	-	31	86.11	600	385	-														
	4.6	-	35	74.17	600	330	-														
	4.9	-	38	69.75	600	310	-														





R = 1:7... R = 1:8													
P _m /P _{a2} [kW]	n _{a1} [1/min]	-	n _{a2}	i	M _{a1} [Nm]	M _{a2}							m [kg]
1.5 / 1.2	3.4	-	27	98.99	450	440	-	-					
	3.8	-	29	89.71	450	400	-	-					
	4.2	-	33	80.55	450	360	-	-					
	4.9	-	38	69.23	450	310	-	-					
	5.2	-	41	64.85	450	290	-	-					
	5.9	-	46	57.29	450	255	-	-					
	6.4	-	49	53.22	450	240	-	-					
	7.0	-	55	48.23	450	215	-	-					
	7.9	-	61	43.30	450	193	-	-					
	9.1	-	71	37.30*	450	167	-	-					
	9.7	-	75	35.07	450	157	-	-					
	11	-	87	30.18	390	135	-	-					
	13	-	98	26.97	350	120	-	-					
	5.3	-	41	64.21	300	285	-	-					
	6.0	-	46	56.73	300	255	-	-					
	6.5	-	50	52.69	300	235	-	-					
	7.1	-	55	47.75	300	215	-	-					
	7.9	-	61	42.87	300	191	-	-					
	9.2	-	71	36.93	300	165	-	-					
	9.8	-	76	34.73	300	155	-	-					
	11	-	88	29.88	300	133	-	-					
	13	-	99	26.70	300	119	-	-					
	14	-	112	23.59	300	105	-	-					
	15	-	113	23.28	300	104	-	-					
	16	-	121	21.81	280	97	-	-					
	18	-	137	19.27	250	86	-	-					
	19	-	147	17.89	230	80	-	-					
	21	-	162	16.22	210	72	-	-					
	23	-	181	14.56	188	65	-	-					
	27	-	210	12.54	162	56	-	-					
	29	-	223	11.79	152	53	-	-					
	34	-	259	10.15	131	45	-	-					
	38	-	290	9.07	117	41	-	-					
	42	-	328	8.01	103	36	-	-					
	44	-	339	7.76*	100	35	-	-					
	49	-	378	6.96	90	31	-	-					
	57	-	439	6.00	78	27	-	-					
	60	-	467	5.64*	73	25	-	-					
	70	-	543	4.85	63	22	-	-					
	78	-	606	4.34	56	19	-	-					
	89	-	687	3.83	50	17	-	-					
	60	-	467	5.63	73	25	-	-					
	64	-	492	5.35*	69	24	-	-					
	72	-	556	4.73	61	21	-	-					
	75	-	581	4.53	59	20	-	-					
	79	-	612	4.30*	56	19	-	-					
	90	-	698	3.77	49	17	-	-					
	90	-	694	3.79	49	17	-	-					
	96	-	741	3.55*	46	16	-	-					
	108	-	838	3.14	41	14	-	-					
	117	-	904	2.91	38	13	-	-					
	129	-	997	2.64*	34	12	-	-					
	144	-	1110	2.37	31	11	-	-					
	167	-	1290	2.04	26	9.1	-	-					
	177	-	1370	1.92*	25	8.6	-	-					
	206	-	1595	1.65	21	7.4	-	-					
	230	-	1780	1.48	19	6.6	-	-					
	262	-	2025	1.30	17	5.8	-	-					




R = 1:7... R = 1:8

P_m/P_{a2} [kW]	n_{a1} - n_{a2} [1/min]	i	M_{a1} [Nm]	M_{a2} [Nm]			m [kg]	
2.2 / 1.7	0.29 - 2.3	1166	13000	6910	-			
	0.33 - 2.6	1029	13000	6100	-			
	0.38 - 3.0	889	13000	5270	-			
	0.44 - 3.4	784	13000	4650	-			
	0.49 - 3.9	695	13000	4120	-	R	147 R77	VU/VZ 31 DV 112M6 500 -
	0.55 - 4.3	619	13000	3670	-	RF	147 R77	VU/VZ 31 DV 112M6 510 -
	0.61 - 4.8	558	12000	3310	-			
	0.70 - 5.5	489	10500	2900	-			
	0.82 - 6.5	415	8930	2460	-			
	0.47 - 3.7	730	8000	4330	-			
	0.54 - 4.3	629	8000	3730	-			
	0.61 - 4.8	560	8000	3320	-			
	0.70 - 5.5	490	8000	2910	-			
	0.80 - 6.3	428	8000	2540	-			
	0.90 - 7.1	381	8000	2260	-	R	137 R77	VU/VZ 31 DV 112M6 375 -
	1.1 - 8.3	323	6950	1920	-	RF	137 R77	VU/VZ 31 DV 112M6 400 -
	1.2 - 9.2	291	6270	1730	-			
	1.3 - 11	255	5490	1510	-			
	1.5 - 12	223	4800	1320	-			
	1.7 - 14	197	4240	1170	-			
	1.9 - 15	175	3770	1040	-			
2.2 / 1.8	0.91 - 7.1	377	4300	2270	-			
	1.1 - 8.3	325	4300	1960	-			
	1.2 - 9.5	284	4300	1710	-	R	107 R77	VU/VZ 31 DV 112M6 285 -
	1.3 - 11	256	4300	1540	-	RF	107 R77	VU/VZ 31 DV 112M6 290 -
	1.6 - 12	220	4300	1320	-			
	1.8 - 14	193	4220	1160	-			
	2.0 - 16	172	3760	1040	-			
	1.3 - 10	270	3000	1630	-	R	97 R57	VU/VZ 31 DV 112M6 220 -
	1.5 - 12	227	3000	1370	-	RF	97 R57	VU/VZ 31 DV 112M6 240 -
	1.8 - 14	186.30	3000	1190	-			
	2.0 - 16	170.02	3000	1090	-	R	97	VU/VZ 31 DV 112M6 210 238
	2.3 - 18	150.78	3000	960	-	RF	97	VU/VZ 31 DV 112M6 225 239
2.2 / 1.8	2.7 - 21	126.75	2940	810	-			
	2.9 - 23	116.48	2700	745	-			
	2.4 - 19	142.41	1550	910	-			
	2.7 - 22	124.97	1550	800	-			
	2.9 - 23	118.43*	1550	755	-			
	3.3 - 26	103.65	1550	665	-			
	3.7 - 29	93.38	1550	595	-	R	87	VU/VZ 31 DV 112M6 165 236
	4.2 - 33	81.92	1550	525	-	RF	87	VU/VZ 31 DV 112M6 175 237
	4.7 - 37	72.57	1550	465	-			
	5.4 - 42	63.68*	1480	405	-			
	5.7 - 45	60.35*	1400	385	-			
	6.5 - 51	52.82	1230	340	-			
	5.2 - 41	65.77	820	420	-			
	5.9 - 47	57.68	820	370	-			
	6.6 - 52	52.07	820	335	-			
	7.5 - 59	45.81	820	295	-	R	77	VU/VZ 31 DV 112M6 140 234
	7.9 - 62	43.26	820	275	-	RF	77	VU/VZ 31 DV 112M6 145 235
	9.3 - 73	36.83	820	235	-			
	10 - 80	33.47	775	215	-			
	12 - 93	29.00	675	185	-			
2.2 / 1.8	4.9 - 39	69.75	600	445	-			
	6.6 - 52	51.56	600	330	-			
	7.4 - 58	46.29	600	295	-			
	8.6 - 67	39.88*	580	255	-	R	67	VU/VZ 31 DV 112M6 135 232
	9.1 - 72	37.50	570	240	-	RF	67	VU/VZ 31 DV 112M6 135 233
	11 - 83	32.27	540	205	-			
	12 - 93	28.83	520	184	-			




R = 1:7... R = 1:8																
P _m /P _{a2} [kW]	n _{a1} [1/min]	-	n _{a2}	i	M _{a1} [Nm]	M _{a2} [Nm]									m [kg]	
2.2 / 1.8	7.1	-	56	48.23	450	310	-	R RF	57 57	VU/VZ VU/VZ	31 31	DV DV	112M6 112M6	125 130	230 231	
	7.9	-	62	43.30	450	275	-									
	9.2	-	72	37.30*	450	240	-									
	9.7	-	77	35.07	450	225	-									
	11	-	89	30.18	450	193	-									
	13	-	100	26.97	450	172	-									
	18	-	145	18.60*	430	119	-	R RF	57 57	VU/VZ VU/VZ	31 31	DV DV	112M6 112M6	125 130	230 231	
	20	-	160	16.79	390	107	-									
	23	-	182	14.77*	345	94	-									
	24	-	193	13.95*	325	89	-									
	29	-	226	11.88	275	76	-									
	32	-	249	10.79	250	69	-									
	37	-	288	9.35	215	60	-									
	38	-	297	9.06	210	58	-									
	43	-	337	7.97	185	51	-									
	45	-	357	7.53	175	48	-									
	53	-	419	6.41	149	41	-									
	59	-	462	5.82	135	37	-									
	68	-	532	5.05	117	32	-									
	78	-	612	4.39	102	28	-									
	61	-	484	5.56*	129	36	-	RX RXF	87 87	VU/VZ VU/VZ	31 31	DV DV	112M6 112M6	145 150	218 219	
	67	-	530	5.07	118	32	-									
	76	-	597	4.50*	105	29	-									
	85	-	665	4.04*	94	26	-	RX RXF	77 77	VU/VZ VU/VZ	31 31	DV DV	112M6 112M6	130 130	216 217	
	92	-	727	3.70	86	24	-									
	105	-	827	3.25*	76	21	-									
	111	-	873	3.08*	72	20	-									
	126	-	996	2.70	63	17	-									
	140	-	1105	2.43	56	16	-									
	160	-	1260	2.13	50	14	-									
	182	-	1430	1.88*	44	12	-									
	204	-	1610	1.67	39	11	-									
	240	-	1895	1.42	33	9.1	-									
3.0 / 2.3	0.38	-	3.0	889	13000	7170	-	R RF	147 R77 147 R77	VZ VZ	31 31	DV DV	132S6 132S6	510 510	- -	
	0.44	-	3.4	784	13000	6330	-									
	0.49	-	3.9	695	13000	5610	-									
	0.55	-	4.3	619	13000	5000	-									
	0.61	-	4.8	558	12000	4500	-									
	0.70	-	5.5	489	10500	3950	-									
	0.82	-	6.5	415	8930	3350	-	R RF	137 R77 137 R77	VZ VZ	31 31	DV DV	132S6 132S6	380 405	- -	
	0.70	-	5.5	490	8000	3950	-									
	0.80	-	6.3	428	8000	3450	-									
	0.90	-	7.1	381	8000	3070	-									
	1.1	-	8.3	323	6950	2610	-									
	1.2	-	9.2	291	6270	2350	-									
	1.3	-	11	255	5490	2060	-									
	1.5	-	12	223	4800	1800	-									
	1.7	-	14	197	4240	1590	-									
	1.9	-	15	175	3770	1410	-									
	1.2	-	9.5	284	4300	2330	-	R RF	107 R77 107 R77	VZ VZ	31 31	DV DV	132S6 132S6	290 300	- -	
	1.3	-	11	256	4300	2100	-									
	1.6	-	12	220	4300	1800	-									
	1.8	-	14	193	4220	1580	-									
	2.0	-	16	172	3760	1410	-									
	2.0	-	16	172	3760	1410	-									
3.0 / 2.5	1.8	-	14	186.30	3000	1620	-	R RF	97 97	VU/VZ VU/VZ	31 31	DV DV	132S6 132S6	215 230	238 239	
	2.0	-	16	170.02	3000	1480	-									
	2.3	-	18	150.78	3000	1310	-									
	2.7	-	21	126.75	2940	1100	-									
	2.9	-	23	116.48	2700	1010	-									



R = 1:7... R = 1:8

P_m/P_{a2} [kW]	n_{a1} [1/min]	n_{a2}	i	M_{a1} [Nm]	M_{a2} [Nm]			m [kg]	
3.0 / 2.5	2.7	- 22	124.97	1550	1090	-			
	2.9	- 23	118.43*	1550	1030	-			
	3.3	- 26	103.65	1550	900	-			
	3.7	- 29	93.38	1550	810	-			
	4.2	- 33	81.92	1550	715	-	R 87	VU/VZ 31 DV 132S6	170 236
	4.7	- 37	72.57	1550	630	-	RF 87	VU/VZ 31 DV 132S6	180 237
	5.4	- 42	63.68*	1480	555	-			
	5.7	- 45	60.35*	1400	525	-			
	6.5	- 51	52.82	1230	460	-			
	7.2	- 57	47.58	1100	415	-			
	5.9	- 47	57.68	820	500	-			
	6.6	- 52	52.07	820	455	-			
	7.5	- 59	45.81	820	400	-			
	7.9	- 62	43.26	820	375	-	R 77	VU/VZ 31 DV 132S6	145 234
	9.3	- 73	36.83	820	320	-	RF 77	VU/VZ 31 DV 132S6	150 235
	10	- 80	33.47	775	290	-			
	12	- 93	29.00	675	250	-			
	14	- 107	25.23	585	220	-			
	6.6	- 52	51.56	600	450	-			
	7.4	- 58	46.29	600	405	-			
	8.6	- 67	39.88*	580	345	-	R 67	VU/VZ 31 DV 132S6	140 232
	9.1	- 72	37.50	570	325	-	RF 67	VU/VZ 31 DV 132S6	145 233
	11	- 83	32.27	540	280	-			
	12	- 93	28.83	520	250	-			
	7.1	- 56	48.23	450	420	-			
	7.9	- 62	43.30	450	375	-			
	9.2	- 72	37.30*	450	325	-	R 57	VU/VZ 31 DV 132S6	135 230
	9.7	- 77	35.07	450	305	-	RF 57	VU/VZ 31 DV 132S6	135 231
	11	- 89	30.18	450	265	-			
	13	- 100	26.97	450	235	-			
	18	- 145	18.60*	430	162	-			
	20	- 160	16.79	390	146	-			
	23	- 182	14.77*	345	129	-			
	24	- 193	13.95*	325	121	-			
	29	- 226	11.88	275	103	-			
	32	- 249	10.79	250	94	-			
	37	- 288	9.35	215	81	-	R 57	VU/VZ 31 DV 132S6	130 230
	38	- 297	9.06	210	79	-	RF 57	VU/VZ 31 DV 132S6	135 231
	43	- 337	7.97	185	69	-			
	45	- 357	7.53	175	66	-			
	53	- 419	6.41	149	56	-			
	59	- 462	5.82	135	51	-			
	68	- 532	5.05	117	44	-			
	78	- 612	4.39	102	38	-			
	48	- 375	7.16*	166	62	-	RX 97	VU/VZ 31 DV 132S6	175 220
	52	- 410	6.56	152	57	-	RXF 97	VU/VZ 31 DV 132S6	185 221
	59	- 464	5.79	134	50	-			
	61	- 484	5.56*	129	48	-	RX 87	VU/VZ 31 DV 132S6	150 218
	67	- 530	5.07	118	44	-	RXF 87	VU/VZ 31 DV 132S6	155 219
	76	- 597	4.50*	105	39	-			
	85	- 665	4.04*	94	35	-			
	92	- 727	3.70	86	32	-			
	105	- 827	3.25*	76	28	-			
	111	- 873	3.08*	72	27	-			
	126	- 996	2.70	63	24	-	RX 77	VU/VZ 31 DV 132S6	135 216
	140	- 1105	2.43	56	21	-	RXF 77	VU/VZ 31 DV 132S6	135 217
	160	- 1260	2.13	50	19	-			
	182	- 1430	1.88*	44	16	-			
	204	- 1610	1.67	39	15	-			
	240	- 1895	1.42	33	12	-			




9.3 R..VU/VZ..DR/DT/DV.. [mm]

14 021 001


RX57..

VU ..







VZ ..




(> 151)			A	D	G	G1	K		KM	K4	O2	P3	R	V4	Z1	Z6	
							VU	VZ								VU	VZ
RX57	VU01 VZ01	DR63..	182	80	132	105	459	475	187	206	176	384	98	72	80	107	114
		DT71D	182	80	145	122	459	490	202	206	176	384	98	72	80	107	114
		DT80..	182	80	145	122	459	540	252	206	176	384	98	72	80	107	114
	VU11 VZ11	DT80..	232	100	145	122	504	569	252	232	183	437	117	88	98	115	143
		DT90..	232	100	197	154	504	590	273	232	183	437	117	88	98	115	143
	VU21 VZ21	DT90..	245	100	197	154	571	624	273	279	227	472	130	110	120	147	177
		DV100M	245	100	197	166	571	662	311	279	227	472	130	110	120	147	177
		DV100L	245	100	197	166	571	692	341	279	227	472	130	110	120	147	177







14 022 001

RXF57..**VU ..****VZ ..****ø 140****ø 160****ø 200**


(> 151)			A	D	G	G1	K		KM	K4	O2	P3	R	V4	Z1	Z6	
							VU	VZ								VU	VZ
RXF57	VU01 VZ01	DR63..	182	80	132	105	459	475	187	206	176	321	98	72	80	107	114
		DT71D	182	80	145	122	459	490	202	206	176	321	98	72	80	107	114
		DT80..	182	80	145	122	459	540	252	206	176	321	98	72	80	107	114
	VU11 VZ11	DT80..	232	100	145	122	504	569	252	232	183	374	117	88	98	115	143
		DT90..	232	100	197	154	504	590	273	232	183	374	117	88	98	115	143
	VU21 VZ21	DT90..	245	100	197	154	571	624	273	279	227	409	130	110	120	147	177
		DV100M	245	100	197	166	571	662	311	279	227	409	130	110	120	147	177
		DV100L	245	100	197	166	571	692	341	279	227	409	130	110	120	147	177






14 023 001

RX67..**VU ..****VZ ..**




(→ 151)			A	D	G	G1	K		KM	K4	O2	P3	R	V4	Z1	Z6	
							VU	VZ								VU	VZ
RX67	VU01 VZ01	DR63..	182	80	132	105	486	502	187	206	176	409	98	72	80	107	114
		DT71D	182	80	145	122	486	517	202	206	176	409	98	72	80	107	114
		DT80..	182	80	145	122	486	567	252	206	176	409	98	72	80	107	114
	VU11 VZ11	DT80..	232	100	145	122	531	596	252	232	183	462	117	88	98	115	143
		DT90..	232	100	197	154	531	617	273	232	183	462	117	88	98	115	143
	VU21 VZ21	DT90..	245	100	197	154	598	651	273	279	227	497	130	110	120	147	177
		DV100M	245	100	197	166	598	689	311	279	227	497	130	110	120	147	177
		DV100L	245	100	197	166	598	719	341	279	227	497	130	110	120	147	177




14 024 001

RXF67..**VU ..****VZ ..**



9

ø 160**ø 200****ø 250**


(→ 151)			A	D	G	G1	K		KM	K4	O2	P3	R	V4	Z1	Z6	
							VU	VZ								VU	VZ
RXF67	VU01 VZ01	DR63..	182	80	132	105	486	502	187	206	176	329	98	72	80	107	114
		DT71D	182	80	145	122	486	517	202	206	176	329	98	72	80	107	114
		DT80..	182	80	145	122	486	567	252	206	176	329	98	72	80	107	114
	VU11 VZ11	DT80..	232	100	145	122	531	596	252	232	183	382	117	88	98	115	143
		DT90..	232	100	197	154	531	617	273	232	183	382	117	88	98	115	143
		DT90..	245	100	197	154	598	651	273	279	227	417	130	110	120	147	177
	VU21 VZ21	DV100M	245	100	197	166	598	689	311	279	227	417	130	110	120	147	177
		DV100L	245	100	197	166	598	719	341	279	227	417	130	110	120	147	177






14 025 001

RX77..**VU ..****VZ ..**



(> 151)			A	D	G	G1	K		KM	K4	O2	P3	R	V4	Z1	Z6	
							VU	VZ								VU	VZ
RX77	VU21 VZ21	DT90..	245	100	197	154	616	669	273	271	227	519	130	110	120	139	169
		DV100M	245	100	197	166	616	707	311	271	227	519	130	110	120	139	169
		DV100L	245	100	197	166	616	737	341	271	227	519	130	110	120	139	169
	VU31 VZ31	DV112M	305	125	221	179	692	778	349	322	283	607	150	138	152	163	202
		DV132S	305	125	221	179	692	823	394	322	283	607	150	138	152	163	202




14 026 001

RXF77..**VU ..****VZ ..**





9

Ø 200**Ø 250**


(> 151)			A	D	G	G1	K		KM	K4	O2	P3	R	V4	Z1	Z6	
							VU	VZ								VU	VZ
RXF77	VU21 VZ21	DT90..	245	100	197	154	616	669	273	271	227	429	130	110	120	139	169
		DV100M	245	100	197	166	616	707	311	271	227	429	130	110	120	139	169
		DV100L	245	100	197	166	616	737	341	271	227	429	130	110	120	139	169
	VU31 VZ31	DV112M	305	125	221	179	692	778	349	322	283	517	150	138	152	163	202
		DV132S	305	125	221	179	692	823	394	322	283	517	150	138	152	163	202






14 027 001

RX87..**VU ..****VZ ..**



(→ 151)			A	D	G	G1	K		KM	K4	O2	P3	R	V4	Z1	Z6	
							VU	VZ								VU	VZ
RX87	VU31 VZ31	DV112M	305	125	221	179	729	815	349	317	283	639	150	138	152	158	197
		DV132S	305	125	221	179	729	860	394	317	283	639	150	138	152	158	197
	VU41 VZ41	DV132M	380	200	275	230	842	905	402	392	348	747	189	170	180	204	234
		DV132ML	380	200	275	230	842	965	462	392	348	747	189	170	180	204	234
		DV160M	380	200	275	230	842	965	462	392	348	747	189	170	180	204	234




14 028 001

RXF87..**VU ..****VZ ..**



9

ø 250**ø 300**


(→ 151)			A	D	G	G1	K		KM	K4	O2	P3	R	V4	Z1	Z6	
							VU	VZ								VU	VZ
RXF87	VU31	DV112M	305	125	221	179	729	815	349	317	283	539	150	138	152	158	197
	VZ31	DV132S	305	125	221	179	729	860	394	317	283	539	150	138	152	158	197
	VU41 VZ41	DV132M	380	200	275	230	842	905	402	392	348	647	189	170	180	204	234
		DV132ML	380	200	275	230	842	965	462	392	348	647	189	170	180	204	234
		DV160M	380	200	275	230	842	965	462	392	348	647	189	170	180	204	234






14 029 001

RX97..**VU ..****VZ ..**



(> 151)			A	D	G	G1	K		KM	K4	O2	P3	R	V4	Z1	Z6	
							VU	VZ								VU	VZ
RX97	VU31	DV112M	305	125	221	179	771	857	349	312	283	673	150	138	152	153	192
	VZ31	DV132S	305	125	221	179	771	902	394	312	283	673	150	138	152	153	192
	VU41 VZ41	DV132M	380	200	275	230	884	947	402	387	348	781	189	170	180	199	229
		DV132ML	380	200	275	230	884	1007	462	387	348	781	189	170	180	199	229
		DV160M	380	200	275	230	884	1007	462	387	348	781	189	170	180	199	229
	VU51	DV160L	460	200	331	259	968	-	503	444	398	886	220	195	200	232	-
		DV180..	460	200	331	253	968	-	575	444	398	886	220	195	200	232	-




14 030 001

RXF97..**VU ..****VZ ..**



9

ø 300**ø 350**


(→ 151)			A	D	G	G1	K		KM	K4	O2	P3	R	V4	Z1	Z6	
							VU	VZ								VU	VZ
RXF97	VU31	DV112M	305	125	221	179	771	857	349	312	283	561	150	138	152	153	192
	VZ31	DV132S	305	125	221	179	771	902	394	312	283	561	150	138	152	153	192
	VU41 VZ41	DV132M	380	200	275	230	884	947	402	387	348	669	189	170	180	199	229
		DV132ML	380	200	275	230	884	1007	462	387	348	669	189	170	180	199	229
		DV160M	380	200	275	230	884	1007	462	387	348	669	189	170	180	199	229
	VU51	DV160L	460	200	331	259	968	-	503	444	398	774	220	195	200	232	-
		DV180..	460	200	331	253	968	-	575	444	398	774	220	195	200	232	-






14 031 001

RX107..**VU ..****VZ ..**



(> 151)			A	D	G	G1	K		KM	K4	O2	P3	R	V4	Z1	Z6	
							VU	VZ								VU	VZ
RX107	VU41 VZ41	DV132M	380	200	275	230	926	989	402	381	348	823	189	170	180	193	223
		DV132ML	380	200	275	230	926	1049	462	381	348	823	189	170	180	193	223
		DV160M	380	200	275	230	926	1049	462	381	348	823	189	170	180	193	223
	VU51	DV160L	460	200	331	259	1010	-	503	438	398	928	220	195	200	226	-
		DV180..	460	200	331	253	1010	-	575	438	398	928	220	195	200	226	-




14 032 001

RXF107..**VU ..****VZ ..**






9

 $\varnothing 350$  **$\varnothing 450$** 


(→ 151)			A	D	G	G1	K		KM	K4	O2	P3	R	V4	Z1	Z6	
							VU	VZ								VU	VZ
RXF107	VU41 VZ41	DV132M	380	200	275	230	926	989	402	381	348	683	189	170	180	193	223
		DV132ML	380	200	275	230	926	1049	462	381	348	683	189	170	180	193	223
		DV160M	380	200	275	230	926	1049	462	381	348	683	189	170	180	193	223
	VU51	DV160L	460	200	331	259	1010	-	503	438	398	788	220	195	200	226	-
		DV180..	460	200	331	253	1010	-	575	438	398	788	220	195	200	226	-






14 122 001

R27..**VU..****VZ..****R27F..**




(→ 151)			A	D	G	G1	K		KM	K4	O2	P3	R	V4	Z1	Z6	
							VU	VZ								VU	VZ
R27 R27F	VU01 VZ01	DR63..	182	80	132	105	485	501	187	213	176	356	98	72	80	114	121
		DT71D	182	80	145	122	485	516	202	213	176	356	98	72	80	114	121
		DT80..	182	80	145	122	485	566	252	213	176	356	98	72	80	114	121




14 123 001

RF27..**VU..****VZ..**







9

ø 120**ø 140****ø 160**


(> 151)			A	D	G	G1	K		KM	K4	O2	P3	R	V4	Z1	Z6	
RF27	VU01 VZ01	DR63..	182	80	132	105	491	507	187	213	176	266	98	72	80	114	121
		DT71D	182	80	145	122	491	522	202	213	176	266	98	72	80	114	121
		DT80..	182	80	145	122	491	572	252	213	176	266	98	72	80	114	121






14 033 001

R37..**VU..****VZ..****R37F..**




(> 151)			A	D	G	G1	K		KM	K4	O2	P3	R	V4	Z1	Z6		(> 153)	
R37 R37F	VU01 VZ01	DR63..	182	80	132	105	493	509	187	213	176	349	98	72	80	114	121		
		DT71D	182	80	145	122	493	524	202	213	176	349	98	72	80	114	121		
		DT80..	182	80	145	122	493	574	252	213	176	349	98	72	80	114	121		
	VU11 VZ11	DT80..	232	100	145	122	538	603	252	238	183	402	117	88	98	122	150	1)	1)
		DT90..	232	100	197	154	538	624	273	238	183	402	117	88	98	122	150	1)	1)




14 034 001

RF37..**VU..****VZ..**







9

ø 120**ø 160****ø 200**


(> 151)			A	D	G	G1	K		KM	K4	O2	P3	R	V4	Z1	Z6	
RF37	VU01 VZ01	DR63..	182	80	132	105	499	515	187	213	176	259	98	72	80	114	121
		DT71D	182	80	145	122	499	530	202	213	176	259	98	72	80	114	121
		DT80..	182	80	145	122	499	580	252	213	176	259	98	72	80	114	121
	VU11 VZ11	DT80..	232	100	145	122	544	609	252	238	183	312	117	88	98	122	150
		DT90..	232	100	197	154	544	630	273	238	183	312	117	88	98	122	150





14 035 001

R47..**VU..****VZ ..****R47F..**




(> 151)			A	D	G	G1	K		KM	K4	O2	P3	R	V4	Z1	Z6		(> 153)	
							VU	VZ								VU	VZ	VU	VZ
R47 R47F	VU01 VZ01	DR63..	182	80	132	105	520	536	187	206	176	370	98	72	80	107	114		
		DT71D	182	80	145	122	520	551	202	206	176	370	98	72	80	107	114		
		DT80..	182	80	145	122	520	601	252	206	176	370	98	72	80	107	114		
	VU11 VZ11	DT80..	232	100	145	122	565	630	252	232	183	423	117	88	98	115	143		
		DT90..	232	100	197	154	565	651	273	232	183	423	117	88	98	115	143		
		DT90..	245	100	197	154	632	685	273	279	227	458	130	110	120	147	177	1)	1)
	VU21 VZ21	DV100M	245	100	197	166	632	723	311	279	227	458	130	110	120	147	177	1)	1)
		DV100L	245	100	197	166	632	753	341	279	227	458	130	110	120	147	177	1)	1)




14 036 001

RF47..**VU..****VZ ..**







9

ø 140**ø 160****ø 200**


(> 151)			A	D	G	G1	K		KM	K4	O2	P3	R	V4	Z1	Z6	
							VU	VZ								VU	VZ
RF47	VU01 VZ01	DR63..	182	80	132	105	520	536	187	206	176	255	98	72	80	107	114
		DT71D	182	80	145	122	520	551	202	206	176	255	98	72	80	107	114
		DT80..	182	80	145	122	520	601	252	206	176	255	98	72	80	107	114
	VU11 VZ11	DT80..	232	100	145	122	565	630	252	232	183	308	117	88	98	115	143
		DT90..	232	100	197	154	565	651	273	232	183	308	117	88	98	115	143
		DT90..	245	100	197	154	632	685	273	279	227	343	130	110	120	147	177
	VU21 VZ21	DV100M	245	100	197	166	632	723	311	279	227	343	130	110	120	147	177
		DV100L	245	100	197	166	632	753	341	279	227	343	130	110	120	147	177





14 037 001

**R57..
VU..****VZ..****R57F..**




(> 151)			A	D	G	G1	K		KM	K4	O2	P3	R	V4	Z1	Z6		(> 153)	
							VU	VZ								VU	VZ	VU	VZ
R57 R57F	VU01 VZ01	DR63..	182	80	132	105	542	558	187	206	176	373	98	72	80	107	114		
		DT71D	182	80	145	122	542	573	202	206	176	373	98	72	80	107	114		
		DT80..	182	80	145	122	542	623	252	206	176	373	98	72	80	107	114		
	VU11 VZ11	DT80..	232	100	145	122	587	652	252	232	183	426	117	88	98	115	143		
		DT90..	232	100	197	154	587	673	273	232	183	426	117	88	98	115	143		
	VU21 VZ21	DT90..	245	100	197	154	654	707	273	279	227	461	130	110	120	147	177	1)	1)
		DV100M	245	100	197	166	654	745	311	279	227	461	130	110	120	147	177	1)	1)
		DV100L	245	100	197	166	654	775	341	279	227	461	130	110	120	147	177	1)	1)
	VU31 VZ31	DV112M	305	125	221	179	731	817	349	331	283	549	150	138	152	172	211	1)	1)
		DV132S	305	125	221	179	731	862	394	331	283	549	150	138	152	172	211	1)	1)




14 038 001

RF57..**VU..****VZ..**







9

ø 160**ø 200****ø 250**


(> 151)			A	D	G	G1	K		KM	K4	O2	P3	R	V4	Z1	Z6	
							VU	VZ								VU	VZ
RF57	VU01 VZ01	DR63..	182	80	132	105	542	558	187	206	176	257	98	72	80	107	114
		DT71D	182	80	145	122	542	573	202	206	176	257	98	72	80	107	114
		DT80..	182	80	145	122	542	623	252	206	176	257	98	72	80	107	114
	VU11 VZ11	DT80..	232	100	145	122	587	652	252	232	183	310	117	88	98	115	143
		DT90..	232	100	197	154	587	673	273	232	183	310	117	88	98	115	143
	VU21 VZ21	DT90..	245	100	197	154	654	707	273	279	227	345	130	110	120	147	177
		DV100M	245	100	197	166	654	745	311	279	227	345	130	110	120	147	177
		DV100L	245	100	197	166	654	775	341	279	227	345	130	110	120	147	177
	VU31 VZ31	DV112M	305	125	221	179	731	817	349	331	283	433	150	138	152	172	211
		DV132S	305	125	221	179	731	862	394	331	283	433	150	138	152	172	211







14 039 001

R67..**VU..****VZ ..****R67F..**


(> 151)			A	D	G	G1	K		KM	K4	O2	P3	R	V4	Z1	Z6		(> 153)	
							VU	VZ								VU	VZ	VU	VZ
R67 R67F	VU01 VZ01	DR63..	182	80	132	105	565	581	187	206	176	379	98	72	80	107	114		
		DT71D	182	80	145	122	565	596	202	206	176	379	98	72	80	107	114		
		DT80..	182	80	145	122	565	646	252	206	176	379	98	72	80	107	114		
	VU11 VZ11	DT80..	232	100	145	122	610	675	252	232	183	432	117	88	98	115	143		
		DT90..	232	100	197	154	610	696	273	232	183	432	117	88	98	115	143		
	VU21 VZ21	DT90..	245	100	197	154	677	730	273	279	227	467	130	110	120	147	177	1)	1)
		DV100M	245	100	197	166	677	768	311	279	227	467	130	110	120	147	177	1)	1)
		DV100L	245	100	197	166	677	798	341	279	227	467	130	110	120	147	177	1)	1)
	VU31 VZ31	DV112M	305	125	221	179	754	840	349	331	283	555	150	138	152	172	211	1)	1)
		DV132S	305	125	221	179	754	885	394	331	283	555	150	138	152	172	211	1)	1)









14 040 001

RF67..
VU..

VZ ..

ø 200

ø 250



(→ 151)			A	D	G	G1	K		KM	K4	O2	P3	R	V4	Z1	Z6	
							VU	VZ								VU	VZ
RF67	VU01 VZ01	DR63..	182	80	132	105	565	581	187	206	176	249	98	72	80	107	114
		DT71D	182	80	145	122	565	596	202	206	176	249	98	72	80	107	114
		DT80..	182	80	145	122	565	646	252	206	176	249	98	72	80	107	114
	VU11 VZ11	DT80..	232	100	145	122	610	675	252	232	183	302	117	88	98	115	143
		DT90..	232	100	197	154	610	696	273	232	183	302	117	88	98	115	143
	VU21 VZ21	DT90..	245	100	197	154	677	730	273	279	227	337	130	110	120	147	177
		DV100M	245	100	197	166	677	768	311	279	227	337	130	110	120	147	177
		DV100L	245	100	197	166	677	798	341	279	227	337	130	110	120	147	177
	VU31 VZ31	DV112M	305	125	221	179	754	840	349	331	283	425	150	138	152	172	211
		DV132S	305	125	221	179	754	885	394	331	283	425	150	138	152	172	211







14 041 001

R77..**VU..****VZ ..****R77F..**


(> 151)			A	D	G	G1	K		KM	K4	O2	P3	R	V4	Z1	Z6		(> 153)	
							VU	VZ								VU	VZ	VU	VZ
R77 R77F	VU11	DT80..	232	100	145	122	624	689	252	226	183	447	117	88	98	109	137		
	VZ11	DT90..	232	100	197	154	624	710	273	226	183	447	117	88	98	109	137		
	VU21 VZ21	DT90..	245	100	197	154	689	742	273	271	227	482	130	110	120	139	169		
		DV100M	245	100	197	166	689	780	311	271	227	482	130	110	120	139	169		
		DV100L	245	100	197	166	689	810	341	271	227	482	130	110	120	139	169		
	VU31	DV112M	305	125	221	179	765	851	349	322	283	570	150	138	152	163	202	1)	1)
	VZ31	DV132S	305	125	221	179	765	896	394	322	283	570	150	138	152	163	202	1)	1)
	VU41 VZ41	DV132M	380	200	275	230	878	941	402	397	348	678	189	170	180	209	239	1)	1)
		DV132ML	380	200	275	230	878	1001	462	397	348	678	189	170	180	209	239	1)	1)
		DV160M	380	200	275	230	878	1001	462	397	348	678	189	170	180	209	239	1)	1)









14 042 001

**RF77..
VU..****VZ ..****ø 250****ø 300**


(→ 151)			A	D	G	G1	K		KM	K4	O2	P3	R	V4	Z1	Z6	
							VU	VZ								VU	VZ
RF77	VU11	DT80..	232	100	145	122	624	689	252	226	183	306	117	88	98	109	137
	VZ11	DT90..	232	100	197	154	624	710	273	226	183	306	117	88	98	109	137
	VU21 VZ21	DT90..	245	100	197	154	689	742	273	271	227	341	130	110	120	139	169
		DV100M	245	100	197	166	689	780	311	271	227	341	130	110	120	139	169
		DV100L	245	100	197	166	689	810	341	271	227	341	130	110	120	139	169
	VU31 VZ31	DV112M	305	125	221	179	765	851	349	322	283	429	150	138	152	163	202
		DV132S	305	125	221	179	765	896	394	322	283	429	150	138	152	163	202
	VU41 VZ41	DV132M	380	200	275	230	878	941	402	397	348	537	189	170	180	209	239
		DV132ML	380	200	275	230	878	1001	462	397	348	537	189	170	180	209	239
		DV160M	380	200	275	230	878	1001	462	397	348	537	189	170	180	209	239





14 043 001

R87..**VU..****VZ ..****R87F..**



(> 151)			A	D	G	G1	K		KM	K4	O2	P3	R	V4	Z1	Z6		(> 153)	
							VU	VZ								VU	VZ	VU	VZ
R87 R87F	VU21 VZ21	DT90..	245	100	197	154	757	810	273	267	227	525	130	110	120	135	165		
		DV100M	245	100	197	166	757	848	311	267	227	525	130	110	120	135	165		
		DV100L	245	100	197	166	757	878	341	267	227	525	130	110	120	135	165		
	VU31 VZ31	DV112M	305	125	221	179	832	918	349	317	283	613	150	138	152	158	197		
		DV132S	305	125	221	179	832	963	394	317	283	613	150	138	152	158	197		
		DV132M	380	200	275	230	945	1008	402	392	348	721	189	170	180	204	234	1)	1)
	VU41 VZ41	DV132ML	380	200	275	230	945	1068	462	392	348	721	189	170	180	204	234	1)	1)
		DV160M	380	200	275	230	945	1068	462	392	348	721	189	170	180	204	234	1)	1)
		DV160L	460	200	331	259	1029	-	503	449	398	826	220	195	200	237	-	1)	
	VU51	DV180..	460	200	331	253	1029	-	575	449	398	826	220	195	200	237	-	1)	




14 044 001

RF87..**VU..****VZ ..**





9

ø 300**ø 350**


(> 151)			A	D	G	G1	K		KM	K4	O2	P3	R	V4	Z1	Z6	
							VU	VZ								VU	VZ
RF87	VU21 VZ21	DT90..	245	100	197	154	757	810	273	267	227	345	130	110	120	135	165
		DV100M	245	100	197	166	757	848	311	267	227	345	130	110	120	135	165
		DV100L	245	100	197	166	757	878	341	267	227	345	130	110	120	135	165
	VU31 VZ31	DV112M	305	125	221	179	832	918	349	317	283	433	150	138	152	158	197
		DV132S	305	125	221	179	832	963	394	317	283	433	150	138	152	158	197
	VU41 VZ41	DV132M	380	200	275	230	945	1008	402	392	348	541	189	170	180	204	234
		DV132ML	380	200	275	230	945	1068	462	392	348	541	189	170	180	204	234
		DV160M	380	200	275	230	945	1068	462	392	348	541	189	170	180	204	234
	VU51	DV160L	460	200	331	259	1029	-	503	449	398	646	220	195	200	237	-
		DV180..	460	200	331	253	1029	-	575	449	398	646	220	195	200	237	-





14 045 001

R97..**VU..****VZ ..**



R97			A	D	G	G1	K		KM	K4	O2	P3	R	V4	Z1	Z6	
							VU	VZ								VU	VZ
	VU31 VZ31	DV112M	305	125	221	179	895	981	349	312	283	660	150	138	152	153	192
		DV132S	305	125	221	179	895	1026	394	312	283	660	150	138	152	153	192
	VU41 VZ41	DV132M	380	200	275	230	1008	1071	402	387	348	768	189	170	180	199	229
		DV132ML	380	200	275	230	1008	1131	462	387	348	768	189	170	180	199	229
		DV160M	380	200	275	230	1008	1131	462	387	348	768	189	170	180	199	229
	VU51	DV160L	460	200	331	259	1092	-	503	444	398	873	220	195	200	232	-
		DV180..	460	200	331	253	1092	-	575	444	398	873	220	195	200	232	-




14 046 001

RF97..**VU..****VZ ..**






9




(> 151)			A	D	G	G1	K		KM	K4	O2	P3	R	V4	Z1	Z6	
							VU	VZ								VU	VZ
RF97	VU31 VZ31	DV112M	305	125	221	179	895	981	349	312	283	435	150	138	152	153	192
		DV132S	305	125	221	179	895	1026	394	312	283	435	150	138	152	153	192
	VU41 VZ41	DV132M	380	200	275	230	1008	1071	402	387	348	543	189	170	180	199	229
		DV132ML	380	200	275	230	1008	1131	462	387	348	543	189	170	180	199	229
		DV160M	380	200	275	230	1008	1131	462	387	348	543	189	170	180	199	229
	VU51	DV160L	460	200	331	259	1092	-	503	444	398	648	220	195	200	232	-
		DV180..	460	200	331	253	1092	-	575	444	398	648	220	195	200	232	-





14 047 001

R107..**VU..****VZ ..**



(→ 151)			A	D	G	G1	K		KM	K4	O2	P3	R	V4	Z1	Z6		(→ 153)	
							VU	VZ								VU	VZ	VU	VZ
R107	VU41 VZ41	DV132M	380	200	275	230	1057	1120	402	381	348	783	189	170	180	193	223		
		DV132ML	380	200	275	230	1057	1180	462	381	348	783	189	170	180	193	223		
		DV160M	380	200	275	230	1057	1180	462	381	348	783	189	170	180	193	223		
	VU51	DV160L	460	200	331	259	1141	-	503	438	398	888	220	195	200	226	-		
		DV180..	460	200	331	253	1141	-	575	438	398	888	220	195	200	226	-		
	VU6	DV200..	574	385	394	285	1200	-	623	662	490	1035	155	245	214	336	-	1)	
		DV225..	574	385	394	289	1200	-	690	662	490	1035	155	245	249	301	-	1)	




14 048 001

RF107..**VU..****VZ ..**


9




(> 151)			A	D	G	G1	K		KM	K4	O2	P3	R	V4	Z1	Z6	
							VU	VZ								VU	VZ
RF107	VU41 VZ41	DV132M	380	200	275	230	1057	1120	402	381	348	533	189	170	180	193	223
		DV132ML	380	200	275	230	1057	1180	462	381	348	533	189	170	180	193	223
		DV160M	380	200	275	230	1057	1180	462	381	348	533	189	170	180	193	223
	VU51	DV160L	460	200	331	259	1141	-	503	438	398	638	220	195	200	226	-
		DV180..	460	200	331	253	1141	-	575	438	398	638	220	195	200	226	-
	VU6	DV200..	574	385	394	285	1200	-	623	662	490	785	155	245	214	336	-
		DV225..	574	385	394	289	1200	-	690	662	490	785	155	245	249	301	-



14 049 001

**R137..
VU..**



(→ 151)			A	D	G	G1	K	KM	K4	O2	P3	R	V4	Z1	Z6
R137	VU51	DV160L	460	200	331	259	1228	503	431	398	948	220	195	200	219
		DV180..	460	200	331	253	1228	575	431	398	948	220	195	200	219
	VU6	DV200..	574	385	394	285	1287	623	655	490	1095	155	245	214	329
		DV225..	574	385	394	289	1287	690	655	490	1095	155	245	249	294





14 050 001

RF137..


VU..




9

 $\varnothing 450$  **$\varnothing 550$** 


(→ 151)			A	D	G	G1	K	KM	K4	O2	P3	R	V4	Z1	Z6
RF137	VU51	DV160L	460	200	331	259	1228	503	431	398	633	220	195	200	219
		DV180..	460	200	331	253	1228	575	431	398	633	220	195	200	219
	VU6	DV200..	574	385	394	285	1287	623	655	490	780	155	245	214	329
		DV225..	574	385	394	289	1287	690	655	490	780	155	245	249	294



14 051 001

**R147..
VU..**


(> 151)			A	D	G	G1	K	KM	K4	O2	P3	R	V4	Z1	Z6
R147	VU51	DV160L	460	200	331	259	1326	503	423	398	980	220	195	200	211
		DV180..	460	200	331	253	1326	575	423	398	980	220	195	200	211
	VU6	DV200..	574	385	394	285	1385	623	647	490	1127	155	245	214	321
		DV225..	574	385	394	289	1385	690	647	490	1127	155	245	249	286





14 052 001

RF147..


VU..




9

 $\varnothing 450$  **$\varnothing 550$** 

(→ 151)			A	D	G	G1	K	KM	K4	O2	P3	R	V4	Z1	Z6
RF147	VU51	DV160L	460	200	331	259	1326	503	423	398	625	220	195	200	211
		DV180..	460	200	331	253	1326	575	423	398	625	220	195	200	211
	VU6	DV200..	574	385	394	285	1385	623	647	490	772	155	245	214	321
		DV225..	574	385	394	289	1385	690	647	490	772	155	245	249	286





14 053 001

**R167..
VU..**

(→ 151)			A	D	G	G1	K	KM	K4	O2	P3	R	V4	Z1	Z6
R167	VU6	DV200..	574	385	394	285	1505	623	672	490	1171	155	245	214	346
		DV225..	574	385	394	289	1505	690	672	490	1171	155	245	249	311

RF167..
VU..

VA2004

